

## Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	RIGHT ANGLE SMA-MALE 1 RETURN LOSS (dB)	RIGHT ANGLE SMA-MALE 2 RETURN LOSS (dB)
100.0	0.02	44.4	44.9
200.0	0.04	40.2	41.3
300.0	0.05	38.2	39.1
400.0	0.05	37.1	37.7
500.0	0.06	36.4	37.0
600.0	0.07	36.2	37.0
700.0	0.07	36.4	37.4
800.0	0.08	37.0	38.3
900.0	0.08	38.1	39.8
1000.0	0.09	40.2	41.9
1100.0	0.09	43.3	43.8
1500.0	0.11	42.5	39.3
1750.0	0.12	36.8	36.0
2000.0	0.13	35.3	35.3
2250.0	0.13	37.6	39.2
2500.0	0.14	41.9	43.7
2750.0	0.14	42.1	42.5
3000.0	0.15	37.4	36.3
3250.0	0.16	33.0	32.7
3500.0	0.16	31.9	32.2
3750.0	0.16	33.1	34.2
4000.0	0.17	37.6	39.4
4250.0	0.17	41.7	41.3
4500.0	0.18	39.6	37.4
5000.0	0.19	31.1	31.1
5500.0	0.19	31.9	33.2
6000.0	0.19	38.5	38.1
6500.0	0.20	39.8	35.0
7000.0	0.20	35.3	35.3
7500.0	0.21	34.5	37.0
8000.0	0.21	34.4	33.9
8500.0	0.22	35.3	34.0
9000.0	0.22	33.3	35.6
9500.0	0.23	28.1	29.6
10000.0	0.24	27.5	28.0
10500.0	0.23	30.0	31.5
11000.0	0.25	26.7	28.4
11500.0	0.27	23.3	24.2
12000.0	0.26	26.8	28.6
12500.0	0.26	26.1	28.0
13000.0	0.32	20.9	21.8
13500.0	0.32	21.7	23.2
14000.0	0.28	24.5	26.6
14500.0	0.33	22.7	24.7
15000.0	0.37	19.5	20.6
15500.0	0.32	22.6	25.1
16000.0	0.32	23.1	25.7
16500.0	0.37	21.2	22.7
17000.0	0.34	23.8	26.5
17500.0	0.34	24.6	27.1
18000.0	0.38	20.1	21.1