

Typical Performance Data

FREQ.	Insertion Loss	Input Return Loss	Output Return Loss	FREQ.	Group Delay
(MHz)	(dB)	(dB)	(dB)	(MHz)	(ns)
1	43.38	28.96	29.29	2350	0.51
5	43.34	29.56	29.57	2360	0.51
10	43.12	29.49	29.53	2370	0.50
15	42.79	29.52	29.53	2390	0.50
25	41.87	29.51	29.49	2400	0.49
50	39.04	32.18	31.39	2410	0.49
100	34.62	29.86	29.47	2420	0.48
150	31.57	28.51	28.26	2430	0.48
180	30.12	28.03	27.90	2440	0.48
200	29.27	27.91	27.70	2450	0.48
300	26.02	26.52	26.35	2480	0.47
350	24.75	25.84	25.69	2500	0.46
500	21.80	24.02	23.94	2510	0.46
600	20.31	22.85	22.88	2520	0.46
750	18.53	21.32	21.31	2530	0.45
900	17.17	19.97	19.93	2540	0.45
1000	16.47	19.14	19.12	2550	0.45
1100	15.94	18.32	18.30	2560	0.45
1250	15.52	17.28	17.26	2580	0.44
1300	15.51	16.94	16.94	2600	0.44
1400	15.79	16.38	16.39	2620	0.44
1500	16.62	15.94	15.92	2640	0.44
1600	18.33	15.78	15.77	2650	0.43
1800	16.79	17.57	17.51	2660	0.43
1810	16.18	17.82	17.76	2670	0.43
1900	10.97	21.73	21.67	2680	0.43
2000	6.86	33.46	33.55	2690	0.43
2150	3.94	26.96	27.11	2700	0.43
2200	3.49	24.73	24.83	2710	0.43
2300	2.97	21.73	21.81	2730	0.43
2350	2.82	20.66	20.70	2750	0.43
2400	2.70	19.71	19.73	2780	0.43
2500	2.59	18.29	18.30	2800	0.43
2600	2.54	17.30	17.36	2820	0.43
2800	2.62	16.54	16.50	2840	0.43
3000	2.95	17.44	17.31	2850	0.43
3100	3.30	18.73	18.53	2860	0.43
3150	3.56	19.77	19.59	2880	0.43
3800	15.93	16.24	16.13	2900	0.44
4000	17.07	16.14	15.95	2910	0.44
5000	15.36	20.60	20.29	2920	0.44
6000	16.82	22.16	21.75	2940	0.44
7000	18.34	21.42	21.14	2950	0.44
8000	18.94	22.19	22.28	2960	0.45
9000	17.95	19.72	19.89	2980	0.45
9500	15.43	15.92	15.86	3000	0.45
10000	13.48	13.38	13.25	3010	0.45
10500	17.26	18.03	17.91	3020	0.45
11000	20.73	23.29	22.52	3030	0.46
11500	22.61	23.52	21.60	3050	0.46
12000	23.44	20.76	18.99	3060	0.46
12500	23.68	18.44	16.86	3070	0.47
13000	23.57	16.70	15.24	3080	0.47
14000	22.96	14.44	13.24	3090	0.47
15000	22.14	13.23	12.29	3100	0.47
16000	21.25	12.85	12.20	3110	0.47
17000	20.40	12.79	12.83	3120	0.47
18000	19.70	12.65	13.75	3130	0.48
19000	19.26	12.11	13.44	3140	0.48
20000	19.15	10.83	11.05	3150	0.48