

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	SMA-MALE 1 RETURN LOSS (dB)	SMA-MALE 2 RETURN LOSS (dB)
100.0	0.22	46.4	44.8
200.0	0.30	45.1	43.8
300.0	0.37	43.8	43.2
400.0	0.42	42.4	41.9
500.0	0.47	42.0	41.0
600.0	0.52	41.5	40.7
700.0	0.56	41.1	40.3
800.0	0.60	40.5	39.9
900.0	0.64	40.4	39.6
1000.0	0.67	39.8	39.2
1100.0	0.70	39.9	39.0
1250.0	0.75	39.9	38.7
1500.0	0.82	39.9	38.5
1750.0	0.89	39.5	37.9
2000.0	0.95	39.3	37.6
2001.0	0.95	37.9	36.9
2250.0	1.00	37.8	37.0
2500.0	1.06	37.6	37.0
2750.0	1.11	37.6	37.2
3000.0	1.16	37.5	37.2
3250.0	1.22	37.3	37.4
3500.0	1.26	37.0	37.6
3750.0	1.31	36.8	37.8
4000.0	1.35	36.5	38.0
4250.0	1.41	36.2	38.2
4500.0	1.45	36.0	38.4
5000.0	1.52	35.4	38.8
5500.0	1.60	35.2	39.2
6000.0	1.69	35.1	39.7
6500.0	1.76	34.2	37.8
7000.0	1.84	33.8	36.9
7500.0	1.91	32.8	35.3
8000.0	1.98	31.8	33.7
8500.0	2.05	30.8	32.1
9000.0	2.12	29.8	30.6
9500.0	2.18	28.2	29.2
10000.0	2.26	26.9	27.7
10500.0	2.29	23.5	24.9
11000.0	2.29	23.6	25.0
11500.0	2.33	23.7	25.2
12000.0	2.40	23.8	25.4
12500.0	2.44	24.0	25.6
13000.0	2.53	24.2	25.8
13500.0	2.68	24.5	26.1
14000.0	2.75	24.8	26.5
14500.0	2.80	24.6	26.4
15000.0	2.90	24.5	26.4
15500.0	2.95	24.5	26.5
16000.0	3.00	24.7	26.5
16500.0	3.13	24.4	26.4
17000.0	3.16	24.3	26.6
17500.0	3.19	24.7	27.0
18000.0	3.33	19.3	20.8