

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	SMA-MALE RETURN LOSS (dB)	SMA-FEMALE BULKHEAD RETURN LOSS (dB)
100.0	0.02	51.3	49.9
500.0	0.06	49.0	37.5
1000.0	0.09	36.6	36.6
1100.0	0.09	37.1	36.3
1200.0	0.10	36.6	36.8
1300.0	0.10	36.7	38.7
1400.0	0.10	36.6	40.5
1500.0	0.11	37.1	39.3
1600.0	0.12	38.7	37.7
1700.0	0.12	40.2	37.0
1800.0	0.13	39.1	37.4
1900.0	0.13	37.0	36.3
2000.0	0.12	35.4	34.4
2400.0	0.13	31.5	32.3
3000.0	0.14	34.8	38.7
4000.0	0.17	26.2	26.2
5000.0	0.17	41.6	38.0
5500.0	0.18	27.3	26.7
6000.0	0.20	24.9	26.2
6500.0	0.19	28.5	31.4
7000.0	0.19	42.2	38.1
7500.0	0.19	28.2	32.2
8000.0	0.21	25.8	29.5
8500.0	0.21	30.0	30.6
9000.0	0.20	33.1	31.5
9500.0	0.21	25.6	27.6
10000.0	0.22	26.9	26.7
10500.0	0.21	28.4	26.2
11000.0	0.24	24.9	25.0
11500.0	0.24	24.3	24.3
12000.0	0.25	24.6	23.2
12500.0	0.25	25.0	24.5
13000.0	0.24	26.2	27.3
13500.0	0.25	23.8	23.6
14000.0	0.23	23.8	23.1
14500.0	0.28	27.3	30.0
15000.0	0.33	25.5	26.2
15500.0	0.29	25.4	24.4
16000.0	0.30	28.3	32.3
16500.0	0.31	32.4	27.9
17000.0	0.32	24.4	23.4
17500.0	0.31	24.0	27.7
18000.0	0.31	29.5	29.9