

*Typical Performance Data*

FREQUENCY (MHz)	INSERTION LOSS (dB)	RIGHT ANGLE SMA-MALE RETURN LOSS (dB)	SMA-FEMALE BULKHEAD RETURN LOSS (dB)
100.0	0.03	46.5	48.7
200.0	0.05	40.9	44.5
300.0	0.06	37.3	41.5
400.0	0.07	35.3	39.3
500.0	0.08	34.6	37.5
600.0	0.09	35.2	36.9
700.0	0.10	37.0	37.8
800.0	0.11	41.0	40.9
900.0	0.11	45.2	47.1
1000.0	0.12	41.7	51.9
1100.0	0.12	37.9	43.4
1250.0	0.13	34.9	37.4
1500.0	0.15	35.6	35.9
1750.0	0.16	39.3	39.1
2000.0	0.18	35.4	37.3
2250.0	0.19	34.7	34.7
2500.0	0.19	36.5	35.1
2750.0	0.20	33.6	33.9
3000.0	0.21	32.7	32.6
3250.0	0.22	34.8	32.3
3500.0	0.23	31.4	30.8
3750.0	0.24	29.8	29.6
4000.0	0.25	34.7	31.9
4250.0	0.26	33.4	32.6
4500.0	0.27	27.8	28.3
5000.0	0.28	45.7	39.7
5500.0	0.29	26.5	26.0
6000.0	0.30	29.7	34.1
6500.0	0.31	27.3	25.6
7000.0	0.33	25.9	26.9
7500.0	0.34	28.1	27.0
8000.0	0.36	24.9	24.3
8500.0	0.36	29.8	31.0
9000.0	0.39	25.5	25.3
9500.0	0.38	31.8	33.9
10000.0	0.40	25.8	26.9
10500.0	0.40	33.0	37.2
11000.0	0.42	30.0	30.8
11500.0	0.44	28.6	31.4
12000.0	0.45	35.6	30.7
12500.0	0.46	28.2	28.3
13000.0	0.44	34.6	30.3
13500.0	0.50	29.3	28.1
14000.0	0.49	27.7	26.4
14500.0	0.49	29.3	26.9
15000.0	0.54	25.3	24.4
15500.0	0.53	26.1	25.3
16000.0	0.65	25.3	25.3
16500.0	0.57	22.8	21.8
17000.0	0.53	29.8	33.8
17500.0	0.64	22.0	22.2
18000.0	0.60	22.7	22.3

