

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	RIGHT ANGLE SMP-FEMALE 1 RETURN LOSS (dB)	RIGHT ANGLE SMP-FEMALE 2 RETURN LOSS (dB)
10	0.01	51.61	57.50
100	0.03	42.31	47.36
200	0.05	40.16	46.24
300	0.06	39.98	48.37
400	0.07	41.27	51.77
500	0.09	43.21	47.96
600	0.10	44.14	44.21
700	0.10	42.46	41.96
800	0.11	40.64	41.17
900	0.12	39.61	40.76
1000	0.13	40.25	40.00
1100	0.13	42.08	38.42
1200	0.14	46.69	36.15
1300	0.14	48.07	34.73
1400	0.15	42.92	33.69
1500	0.15	39.32	33.26
1600	0.16	37.17	33.05
1800	0.17	37.19	32.35
2000	0.18	44.77	31.07
2500	0.20	33.33	31.39
3000	0.21	47.07	28.39
3500	0.25	31.21	26.98
4000	0.25	35.70	26.45
4500	0.27	34.59	25.93
5000	0.31	30.10	24.75
5500	0.28	42.54	26.14
6000	0.33	27.45	23.76
6500	0.32	29.50	25.29
7000	0.33	32.60	25.91
7500	0.38	24.23	21.38
8000	0.34	34.42	32.12
8500	0.39	23.87	20.83
9000	0.38	22.86	22.31
9500	0.37	29.56	27.95
10000	0.43	19.82	18.72
10500	0.38	26.97	26.71
11000	0.41	21.23	20.85
11500	0.44	19.61	18.18
12000	0.40	29.70	28.88
12500	0.44	17.85	17.73
13000	0.44	25.09	21.01
13500	0.43	19.10	20.48
14000	0.46	18.55	17.09
14500	0.43	25.11	24.68
15000	0.46	16.95	17.16
15500	0.45	26.86	20.95
16000	0.44	19.18	20.99
16500	0.47	18.29	19.66
17000	0.45	28.09	26.48
17500	0.48	18.14	19.96
18000	0.45	29.00	35.63