

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	N-MALE 1 RETURN LOSS (dB)	N-MALE 2 RETURN LOSS (dB)
10.0	0.00	58.96	58.74
50.0	0.01	55.09	54.46
60.0	0.01	55.34	54.45
70.0	0.01	55.67	54.79
80.0	0.01	55.82	55.83
90.0	0.01	55.38	57.05
100.0	0.01	54.67	59.05
200.0	0.00	53.91	55.87
300.0	0.01	56.45	47.47
400.0	0.01	52.28	44.88
500.0	0.03	47.64	44.73
600.0	0.03	45.62	47.50
700.0	0.04	44.39	52.81
800.0	0.05	44.31	58.87
900.0	0.05	44.84	53.74
1000.0	0.06	45.73	50.57
1500.0	0.07	43.93	42.46
2000.0	0.09	38.58	40.39
2500.0	0.09	41.94	49.15
3000.0	0.10	41.85	43.27
3500.0	0.11	35.51	31.97
4000.0	0.12	33.24	29.97
4500.0	0.13	34.16	35.31
5000.0	0.15	28.60	29.48
5500.0	0.18	26.73	25.43
6000.0	0.20	26.98	25.86
6500.0	0.22	30.50	27.86
7000.0	0.23	28.60	29.67
7500.0	0.32	26.11	29.73
8000.0	0.32	26.25	28.64
8500.0	0.26	32.03	27.15
9000.0	0.27	35.99	31.17
9500.0	0.19	31.95	24.22
10000.0	0.17	29.88	25.46
10500.0	0.23	33.44	27.31
11000.0	0.17	32.39	30.34
11500.0	0.29	27.36	28.51
12000.0	0.26	27.16	23.76
12500.0	0.29	33.41	25.66
13000.0	0.29	40.76	30.12
13500.0	0.28	29.29	29.83
14000.0	0.38	28.92	26.31
14500.0	0.30	21.98	26.86
15000.0	0.26	22.09	29.05
15500.0	0.27	24.22	25.85
16000.0	0.24	23.92	22.19
16500.0	0.30	23.02	25.71
17000.0	0.23	21.67	22.09
17500.0	0.34	19.84	21.00
18000.0	0.33	21.90	19.59