

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	SMA-MALE RETURN LOSS (dB)	RIGHT ANGLE SMA-MALE RETURN LOSS (dB)
10.0	0.00	47.1	49.4
50.0	0.01	51.1	53.9
100.0	0.01	49.1	47.1
150.0	0.01	47.2	45.9
200.0	0.02	45.4	43.4
250.0	0.02	43.9	41.8
300.0	0.02	42.7	41.1
350.0	0.02	40.9	39.3
400.0	0.02	40.0	38.5
450.0	0.02	39.1	37.5
500.0	0.03	38.5	36.9
550.0	0.03	37.7	36.4
600.0	0.03	37.4	36.1
650.0	0.03	37.2	35.8
700.0	0.03	37.0	35.9
750.0	0.03	37.1	36.2
800.0	0.03	36.8	36.2
850.0	0.04	36.8	36.5
900.0	0.04	36.5	36.6
950.0	0.04	36.7	37.2
1000.0	0.04	36.8	37.7
1200.0	0.04	37.9	40.9
1400.0	0.05	39.1	42.3
1600.0	0.05	39.0	39.8
1800.0	0.06	37.3	37.0
2000.0	0.06	34.7	35.3
2200.0	0.06	32.7	33.4
2400.0	0.07	31.4	32.4
2600.0	0.07	31.6	32.9
2800.0	0.07	33.0	34.5
3000.0	0.07	37.5	39.5
3600.0	0.08	33.6	34.8
4000.0	0.08	31.0	31.8
4600.0	0.09	31.3	31.4
5000.0	0.10	30.2	30.4
5600.0	0.11	29.2	30.2
6000.0	0.11	27.7	27.6
6600.0	0.12	30.8	34.4
7000.0	0.12	29.4	31.1
7600.0	0.13	29.4	31.3
8000.0	0.13	29.9	34.9
8600.0	0.14	27.6	28.2
9000.0	0.15	29.0	29.6
9600.0	0.15	34.5	36.3
10000.0	0.16	27.4	27.8
10600.0	0.16	36.7	37.5
11000.0	0.16	30.1	30.1
11600.0	0.17	32.1	37.6
12000.0	0.17	34.9	33.9
12600.0	0.17	40.3	38.4
13000.0	0.18	37.3	37.9
13600.0	0.18	36.2	38.7
14000.0	0.19	37.8	36.8
14600.0	0.20	28.0	28.3
15000.0	0.20	39.1	39.3
15600.0	0.21	27.3	26.8
16000.0	0.21	30.9	30.4
16600.0	0.22	29.6	28.4
17000.0	0.24	27.0	25.5
17600.0	0.23	34.7	37.0
18000.0	0.24	29.7	26.1