



CERAMIC

Bandpass Filter

BFHK-1272+

Mini-Circuits

50Ω 11.9 to 12.8 GHz

THE BIG DEAL

- Ultra-High Stopband Rejection Structure – 100 dB typical
- Surface mountable pick and place standard case style
- Standard small 1812 (4.5mm x 3.2mm) case style
- High quality distributed filter topology
- Wide rejection band
- Shielded construction preventing filter from de-tuning
- Reduced footprint area by employing LGA (land grid array)
- Suited for very high-volume production
- Protected by US Patents 11,638,370 and 11,744,057



Generic photo used for illustration purposes only

CASE STYLE: NM1812C-3

+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our website for methodologies and qualifications

APPLICATIONS

- Test and Measurement
- Aerospace and Defense Signal Conditioning

PRODUCT OVERVIEW

The BFHK-1272+ LTCC Band Pass Filter achieves a miniature size and high repeatability of performance by utilizing a proprietary LTCC material system and distributed filter topology. The passband loss at 11.9 – 12.8 GHz is as low as 2.9 dB, with typical stopband rejections at 100 dB up to 31 GHz. This model handles up to 1W RF input power, and provides a wide operating temperature range from -55 to +125°C. Utilizing a proprietary LTCC material system and a distributed filter topology, this filter is able to achieve repeatable performance on a lot-to-lot basis, up to mmWave frequencies.

KEY FEATURES

Feature	Advantages
Ultra-High Rejection	Typical stopband rejections at 100 dB up to 31 GHz
Cost effective	LTCC is scalable technology that is cost effective due to ease of production in high quantities.
Small size (4.5mm x 3.2mm)	Allows for high layout density of circuit boards, while minimizing effects of parasitics.
Surface Mountable	Suitable for very high volume automated assembly process.

REV. A
ECO-019695
BFHK-1272+
WY/CP/PS
231102





CERAMIC

Bandpass Filter

BFHK-1272+

ELECTRICAL SPECIFICATIONS¹ AT 25°C

Parameter	F#	Frequency (GHz)	Min.	Typ.	Max.	Units
Pass Band	Center Frequency	—	—	12.3	—	GHz
	Insertion Loss	F1-F2	11.9 - 12.8	2.9	4.5	dB
	Return Loss	F1-F2	11.9 - 12.8	—	10	dB
Stop Band, Lower	Insertion Loss	DC-F3	2.0 - 8.6	70	80	dB
Stop Band, Upper	Insertion Loss	F4-F5	16.7 - 18	70	90	dB
			18 - 31	80	100	dB
			31 - 38	55	70	dB


1. Measured on Mini-Circuits Test Board TB-BFHK-1272C+ with feedline losses removed by normalization of S12 and S21 traces to measurement of TB thru-line

MAXIMUM RATINGS


Parameter	Ratings
Operating Temperature	-55°C to 125°C
Storage Temperature	-55°C to 125°C
RF Power Input	1W max.

Permanent damage may occur if any of these limits are exceeded

TYPICAL FREQUENCY RESPONSE



FUNCTIONAL SCHEMATIC







CERAMIC

Bandpass Filter


BFHK-1272+

EVALUATION BOARD MCL P/N: TB-BFHK-1272C+ SUGGESTED PCB LAYOUT: PL-730




- NOTES:**
- PCB IS MULTILAYER PCB, SEE STACK-UP DIAGRAM.
 - TRACE WIDTH & GAP PARAMETERS ARE SHOWN FOR MEGTRON6 R-5775(G), CLOTH STYLE:1080 WITH DIELECTRIC THICKNESS .0051; COPPER: 1/2 OZ.+PLATING. FOR OTHER MATERIALS TRACE WIDTH AND GAP MAY NEED TO BE MODIFIED.
 - COPPER LAYER 4 OF THE PCB ARE CONTINUOUS GROUND PLANE.
- DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)
 - DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

LAYER 2, B-VIA & PTH



LAYER 3 & PTH





PAD CONNECTIONS

INPUT	1
OUTPUT	2
GROUND	3

PRODUCT MARKING: F443

OUTLINE DRAWING



Weight: .126 grams.
 Dimensions are in inches (mm). Tolerances: 2 Pl.±.01; 3 Pl. ±.005






CERAMIC

Bandpass Filter

BFHK-1272+

TYPICAL PERFORMANCE DATA

Frequency (MHz)	Insertion Loss (dB)	Return Loss (dB)
50	107.12	0.07
1500	111.56	0.32
2000	109.36	0.28
4500	106.56	0.55
6000	109.36	0.79
7500	95.84	0.80
8600	82.61	0.78
10500	38.71	1.29
11900	2.23	34.79
12300	2.29	22.04
12800	2.60	24.54
15000	70.66	1.57
16700	106.57	1.25
18000	125.11	1.24
20000	117.63	1.61



- NOTES**
- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
 - B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
 - C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the standard. Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

