

Ceramic Band Pass Filter

BFCN-2555+

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	RETURN LOSS (dB)
50	81.46	0.06
200	82.15	0.14
500	62.32	0.23
1000	52.18	0.31
1970	37.86	0.74
2000	36.18	0.80
2200	20.62	1.82
2300	10.23	5.06
2350	6.16	11.04
2500	3.78	18.11
2555	3.73	16.46
2610	3.87	12.77
2850	7.85	17.08
2920	14.80	5.83
3000	24.74	2.69
3200	39.85	1.20
3250	40.88	1.11
3700	44.06	0.74
4500	39.38	0.62
5500	29.82	0.63

REV. X1
BFCN-2555+
080219
Page 1 of 1



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED RoHS compliant
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see

