### Surface Mount

# Coaxial-Ceramic Resonator Filters and Multiplexers

DC to 6 GHz  $50\Omega$ 

# The Big Deal

- Low insertion loss with excellent power handling
- Passbands up to 6 GHz
- Fractional bandwidth from <1 to 25%</li>
- Low profile designs with min. height of 0.120"
- Excellent temperature stability
- Rugged construction to handle demanding environmental conditions



### **Product Overview**

Mini-Circuits' Coaxial-Ceramic Resonator filters offer low insertion loss in very small form factors, using ceramic material with high dielectric constant and superior Q factor. Bandpass and bandstop filters, diplexer and multiplexer designs can be constructed using this technology. Low insertion loss combined with excellent power handling makes these filters well suited for transmitter and receiver signal chains. Advanced filter design and construction can achieve stopband width greater than 3x the center frequency as high as 20 GHz.

All our coaxial-ceramic resonator filters are built with rugged construction, qualified to withstand multiple demanding reflow cycles. Excellent repeatability across units is achieved through precise tuning and process control.

# **Key Features**

Feature	Advantages
Low insertion loss	Low signal loss results in better SNR in signal chain
Fast roll-off	Higher selectivity results in better adjacent channel rejection and dynamic range
Wide stop band	Wide spur-free stopband results in better receiver sensitivity
Excellent power handling	Well suited for transmitter applications
Rugged Construction	These filter assemblies have been qualified over a wide range of thermal, mechanical and environmental conditions including withstanding the stress of extensive solder reflow cycles
Small Size	Very well suited for high performance applications where size is a constraint.
Temperature stability	Very minimal change in electrical performance across temperature makes these filters suitable for a wide range of operating conditions.

A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document

A. Performance and quality attributes and continuous not expressly stated in this specification occurrent are interned to be excluded and to find form a part or this specification as B. Electrical specifications and performance data contained in this specification document are becomen the part of the specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

# **Bandpass Filter**

 $50\Omega$ 2000 to 2300 MHz

# CBP-2150AN+



Generic photo used for illustration purposes only CASE STYLE: TJ2826-1

Тур.

2150

1.2

1.4

60

26

40

50

20

20

35

Max.

1.8

1.8

Unit

MHz

dB

:1

dB

dB

dB

dB

### **Features**

- · Low Insertion loss
- · Minimal Insertion loss variation over operating temperature
- · Low-profile shielded package

### **Applications**

- Broadcast
- PMR Communications
- · Fixed mobile

Operating Temperature	-40°C to 85°C
Storage Temperature	-55°C to 100°C
RF Power Input	10 W at 25°C

**Maximum Ratings** 

Parameter

Pass Band

Stop Band, Lower

Stop Band, Upper

Permanent damage may occur if any of these limits are exceeded.

Center Frequency


Insertion Loss

Insertion Loss


Insertion Loss

**VSWR** 

### **Functional Schematic**



### **Typical Frequency Response**



+RoHS Compliant The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

### Typical Performance Data at 25°C

Electrical Specifications at 25°C

F1-F2

F1-F2

DC-F3

F3-F4

F5-F6

F6-F7

Frequency (MHz)

2000 - 2300

2000 - 2300


DC - 1500


1500 - 1700


2760 - 3200


3200 - 3620

Frequency (MHz)	Insertion Loss (dB)	VSWR (:1)	Frequency (MHz)	Group Delay (ns)
1	100.60	172.74	2000	2.00
10	102.64	356.53	2015	1.92
100	113.14	790.59	2030	1.86
1000	64.78	158.94	2045	1.80
1500	58.28	65.28	2060	1.75
1700	27.24	32.57	2075	1.71
1860	3.00	1.93	2090	1.67
2000	1.11	1.25	2105	1.65
2100	0.96	1.30	2120	1.64
2150	0.85	1.12	2135	1.63
2200	0.82	1.10	2150	1.61
2300	0.86	1.24	2165	1.61
2425	3.09	3.66	2180	1.60
2660	20.18	65.24	2195	1.59
2760	26.53	102.24	2210	1.58
3000	46.94	124.26	2225	1.57
3100	50.17	112.31	2240	1.57
3200	42.86	105.73	2250	1.57
3500	39.86	58.65	2275	1.60
3620	40.44	40.90	2300	1.66









A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.

B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.

C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

### **Pad Connections**


INPUT	1
OUTPUT	4
GROUND	2,3,5,6,7,8,9,10,11,12

Demo Board MCL P/N: TB-1099+ Suggested PCB Layout (PL-630)

### SUGGESTED MOUNTING CONFIGURATION FOR TJ2826-1 CASE STYLE ø.020, PTH FOR GROUND **PACKAGE** OUTLINE 4x.020±.002 2x.040±.002 TRACE WIDTH, SEE NOTE#1 SPACE WIDTH SEE NOTE#1 RF IN RF OUT Ø.020 PTH, SHALL BE PLUGGED TO PREVENT PIN #1 SOLDER WICKING, 7 PLCS. MARKED "A". MARKED


### NOTES:

- TRACE WIDTH IS SHOWN FOR ROGERS (R04350B) WITH DIELECTRIC THICKNESS .020"±.0015". COPPER: 1/2 0Z. EACH SIDE.
   FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
   BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.



DENOTES COPPER LAND PATTERN FREE OF SOLDERMASK

### **Outline Drawing**



### Outline Dimensions (inch )

Α	В	С	D	Е	F	G	Н	J	K	L	М
.472	.394	.110	.060	.322	.075	.244	.160	.157	.317	.095	.120
12.00	10.00	2.79	1.52	8.19	1.91	6.19	4.06	4.00	8.06	2.41	3.05
N	Р	Q	R	S	Т	U	V	W	Х	Υ	Wt.
				-		∪ <b>.434</b>					

Note: Please refer to case style drawing for details

Notes
A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Puchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp