

Surface Mount Diplexer

RDP-2R15+

50Ω DC to 2150 MHz
(DC-20, 950-2150 MHz)



CASE STYLE: CK605

The Big Deal

- Low insertion loss
- High stopband insertion loss
- Miniature shielded package

Product Overview

RDP-2R15+ is a low-pass + high-pass combination device. Low pass port is designed for DC to 20 MHz and high pass port is designed for 950 to 2150 MHz. This diplexer can be used to pass, IF, pilot carrier or clock synchronizing signal, SATCOM modems, air-traffic control and other multiband radio systems.

Key Features

Feature	Advantages
Low passband insertion loss	Suitable for high performance application.
Extended stopband rejection	Spurious rejection and avoids using additional filters.
Shielded case.	Reduced interference with the surrounding components.



ISO 9001 ISO 14001 AS 9100 CERTIFIED

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 The Design Engineers Search Engine  Provides ACTUAL Data Instantly at minicircuits.com

IF/RF MICROWAVE COMPONENTS

For detailed performance specs
& shopping online see web site

Notes: 1. Performance and quality attributes and conditions not expressly stated in this specification sheet are intended to be excluded and do not form a part of this specification sheet. 2. Electrical specifications and performance data contained herein are based on Mini-Circuit's applicable established test performance criteria and measurement instructions. 3. The parts covered by this specification sheet are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp.

Surface Mount Diplexer

RDP-2R15+

50Ω DC to 2150 MHz (DC-20, 950-2150 MHz)

Maximum Ratings


Operating Temperature	-40°C to 85°C
Storage Temperature	-55°C to 100°C
RF Power Input	2W at 25°C

Permanent damage may occur if any of these limits are exceeded. These ratings are not intended for continuous normal operation

Pin Connections

HIGH PASS PORT	14
LOW PASS PORT	10
COMMON PORT	2
GROUND	1,3-9,11-13,15,16


Outline Drawing



Outline Dimensions (inch/mm)

	A	B	C	D	E	F	G	H	J	K
	.500	.500	.180	.100	.080	.115	.060	.040	.540	.060
	12.7	12.7	4.572	2.54	2.032	2.921	1.524	1.016	13.72	1.524
	L	M	N	P	Q	R	S	T	wt.	
	.100	.135	.135	.115	.140	.070	.150	.070		grams
	2.54	3.429	3.429	2.921	3.556	1.778	3.81	1.778		1.0

Demo Board MCL P/N: TB-10+ Suggested PCB Layout (PL-012)



- NOTES: 1. TRACE WIDTH IS SHOWN FOR FR4 WITH DIELECTRIC THICKNESS .030" ± .002"; COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.

- Blue area DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)
- Hatched area DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

Features

- Low insertion loss
- 50Ω Impedance
- Combination of Low pass and High pass filters
- Miniature shielded package
- Aqueous washable

Applications

- SATCOM modem
- Air-traffic control



Generic photo used for illustration purposes only
CASE STYLE: CK605

+RoHS Compliant
The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications


Electrical Specifications at 25°C

Parameter	Port	Frequency (MHz)	Min.	Typ.	Max.	Unit			
Pass Band	Insertion Loss	Low Pass	DC-20	-	0.5	1.5	dB		
		High Pass	950-2150	-	0.6	1.5			
	Return Loss	Flatness	High pass	950-2150	-	± 0.1	-	dB	
		Low Pass	DC-20	12	18	-	dB		
			High Pass	950-2150	15	21			-
			Common	DC-20	15	20			-
Stop Band Isolation	High Pass	DC-250	20	30	-	dB			
		DC-20	-	86	-				

Typical Performance Data at 25°C

FREQUENCY (MHz)	INSERTION LOSS (dB)			RETURN LOSS (dB)	
	Low Pass Port	High Pass Port	Common Port	Low Pass Port	High Pass Port
1	0.22	108.92	32.17	31.85	0.00
10	0.28	96.23	32.40	23.23	0.00
20	0.46	87.25	20.50	17.94	0.01
30	0.77	89.86	17.14	15.42	0.02
40	5.78	86.18	2.56	2.32	0.03
50	15.23	79.32	0.71	0.68	0.04
60	23.43	76.90	0.42	0.46	0.06
70	30.25	74.57	0.31	0.38	0.08
100	45.94	67.00	0.18	0.26	0.17
140	61.39	55.91	0.13	0.17	0.33
250	73.23	31.77	0.18	0.09	1.00
330	66.27	19.46	0.34	0.08	1.63
420	59.77	8.74	1.18	0.07	2.80
480	56.65	3.86	3.35	0.07	4.83
520	55.69	2.00	6.15	0.08	7.32
540	55.54	1.44	7.93	0.08	8.85
600	55.91	0.67	14.06	0.08	13.76
800	58.07	0.43	19.22	0.11	21.91
950	59.29	0.39	20.06	0.13	26.85
1000	59.25	0.38	20.75	0.14	29.18
1500	62.06	0.36	30.83	0.21	28.00
2150	58.86	0.46	21.58	0.28	28.15

Functional Schematic



Mini-Circuits®
ISO 9001 ISO 14001 AS 9100 CERTIFIED
The Design Engineers Search Engine
IF/RF MICROWAVE COMPONENTS

For detailed performance specs & shopping online see web site

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 The Design Engineers Search Engine Provides ACTUAL Data Instantly at minicircuits.com

Notes: 1. Performance and quality attributes and conditions not expressly stated in this specification sheet are intended to be excluded and do not form a part of this specification sheet. 2. Electrical specifications and performance data contained herein are based on Mini-Circuit's applicable established test performance criteria and measurement instructions. 3. The parts covered by this specification sheet are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp.

REV.0R
M133609
EDU1494
RDP-2R15+
URJ
200501
Page 2 of 3

