

Test Cable, N-Male/N-Male

CBL-0.5M-NMNM+

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	N-MALE 1 RETURN LOSS (dB)	N-MALE 2 RETURN LOSS (dB)
0.3	0.00	54.92	59.64
0.7	0.01	55.27	56.63
1.0	0.01	54.75	55.81
3.0	0.01	53.54	53.73
5.0	0.01	52.01	52.19
7.0	0.02	50.94	51.22
9.0	0.02	49.48	49.81
10.0	0.02	48.87	49.24
30.0	0.03	46.68	47.13
50.0	0.05	44.37	44.69
70.0	0.05	42.63	42.54
90.0	0.06	41.40	40.88
100.0	0.07	41.34	41.20
200.0	0.10	40.98	41.87
300.0	0.12	39.77	40.97
400.0	0.14	40.99	40.52
500.0	0.16	39.27	37.82
600.0	0.17	40.45	38.65
700.0	0.18	38.41	37.78
800.0	0.20	39.17	38.57
900.0	0.21	38.01	37.83
1000.0	0.22	36.84	36.81
1500.0	0.27	37.14	38.37
2000.0	0.32	35.48	36.91
2500.0	0.36	34.71	35.39
3000.0	0.39	35.10	34.70
3500.0	0.43	36.49	36.11
4000.0	0.46	38.53	37.08
4500.0	0.51	42.00	36.90
5000.0	0.53	40.41	35.86
5500.0	0.55	37.12	35.10
6000.0	0.58	35.72	34.05
6500.0	0.67	39.92	40.80
7000.0	0.68	42.31	46.61
7500.0	0.69	38.23	41.69
8000.0	0.70	33.54	34.16
8500.0	0.79	30.88	30.31
9000.0	0.81	28.70	28.53
9500.0	0.77	26.21	27.42
10000.0	0.80	25.61	27.32
10500.0	0.86	26.19	26.94
11000.0	0.87	25.45	25.82
11500.0	0.90	25.65	25.82
12000.0	0.93	24.27	23.40
12500.0	0.93	23.98	23.48
13000.0	0.91	22.27	21.48
13500.0	1.08	23.00	22.36
14000.0	1.07	22.57	21.83
14500.0	1.03	22.74	22.43
15000.0	1.10	23.09	22.32
15500.0	1.09	23.77	23.13
16000.0	1.15	24.30	24.01
16500.0	1.14	26.36	25.33
17000.0	1.13	27.97	26.74
17500.0	1.16	30.35	29.23
18000.0	1.28	30.74	28.94