

Test Cable, N-Male/N-Male

CBL-25FT-NMNM+

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	N-MALE 1 RETURN LOSS (dB)	N-MALE 2 RETURN LOSS (dB)
0.3	0.04	46.06	46.06
334	1.56	46.06	40.09
667	2.26	40.09	36.61
1000	2.81	36.61	34.15
1333	3.29	34.15	32.26
1667	3.74	34.15	32.26
2000	4.11	34.15	30.71
2667	4.78	34.15	32.26
3333	5.48	34.15	32.26
4000	6.05	40.09	34.15
4667	6.65	36.61	30.71
5333	7.15	40.09	32.26
6000	7.77	36.61	29.42
7000	8.29	32.26	27.32
8000	9.02	29.42	27.32
9000	9.84	30.71	27.32
10000	10.58	28.30	27.32
11000	10.95	25.66	28.30
12000	11.55	27.32	30.71
12857	12.08	29.42	40.09
13714	12.57	30.71	32.26
14571	13.25	23.69	26.44
15429	13.58	21.66	27.32
16286	13.92	22.61	28.30
17143	14.48	21.23	24.29
18000	15.13	22.61	21.23

REV. X1
CBL-25FT-NMNM+
070723
Page 1 of 1



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED RoHS compliant

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see

