

 50Ω Wideband

10 MHz to 10 GHz



CASE STYLE: GU1414

The Big Deal

- Extremely Wideband
- Very high DC current up to 200mA
- Very low insertion loss,<1dB
- Well matched, VSWR1.1:1

Product Overview

TCBT-14+ is the world's smallest footprint wideband Bias-Tee measuring 3.8 mm x 3.8 mm which utilizes a unique design to cover a frequency range of 10 MHz to 10 GHz without resonances that are typically observed over such broad bands. It is designed to handle 1W of RF power and 200 mA current and is suitable for automated pick and place operation.

Key Features

Feature	Advantages
Extremely wideband: 10 MHz to 10 GHz	Broad bandwidth enables biasing of wideband MMIC amplifiers or other active circuits starting at extremely low frequencies through microwave bands.
DC Current, 200 mA	Able to support most Class-A MMIC amplifiers with a P1dB of up to 22 dBm need less than 200 mA.
Low Insertion Loss: 0.2 dB typ. To 3 GHz 0.5 dB typ. to 5 GHz 1.0 dB typ. at 10 GHz	When used at the output of the amplifiers in a typical bias application; the low loss of the TCBT-14+ exhibits minimal impact on gain and over temperature improving reliability.
Excellent matching: 1:1.1 over 0.1- 4 GHz 1.2:1 over entire band	Excellent VSWR of TCBT minimizes interaction effects and resulting gain ripple. Use of TCBT-14+ with Mini-Circuits MMIC amplifiers has shown performance improvements over traditional L-C networks over the entire band.

Notes

A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.

B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.

C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.ninicircuits.com/MCLStore/terms.jsp

Bias-Tee

10 MHz to 10 GHz 50Ω Widehand

Maximum Ratings


Operating Temperature	-40°C to 85°C
Storage Temperature	-55°C to 100°C
RF Power	30dBm max.
Voltage at DC port	25V max.
Input Current	200mA

Permanent damage may occur if any of these limits are exceeded.


Pad Terminations

RF	2
RF&DC	1
DC	3
NOT USED	4

Outline Drawing




PCB Land Pattern



Outline Dimensions (inch)

Α	В	С	D	E	F	G	Н	J
.150	.150	.14	.025	.100	.043	.030	.050	.087
3.81	3.81	3.56	0.64	2.54	1.09	0.76	1.27	2.21
K	L	М	N	Р	Q	R		wt
K .193	.066		N .081		_	R 0.013		wt grams

Demo Board MCL P/N: TB-510+ Suggested PCB Layout (PL-321)



.014, 2 PL.—I I—

CAPACITOR CI: .010 UF, 0603 SIZE.

NOTES: 1. COPLANAR WAYEQUIDE PARAMETERS ARE SHOWN FOR ROSCESS ROASSOS BWITH DIELECTRIC THICKNESS. 020" ± .0015"; COPPER: 1/2 .02. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.

2. FOOTPRINT OF CI IS SHOWN FOR REFERENCE.

3. BOTTOM SIDE OF THE PGB IS CONTINUOUS GROUND PLANE.

DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)

DENOTES COPPER LAYOUT WITH SMOBC MASK

Features

- wideband, 10 to 10000 MHz
- low insertion loss, 0.5 dB typ.
- excellent VSWR, 1.25:1 typ.
- miniature surface mount 0.15"x0.15"
- aqueous washable
- protected by US Patent 8,644,029

Applications

- · biasing amplifiers
- biasing of laser diodes
- · biasing of active antennas



TCBT-14+

CASE STYLE: GU1414

+RoHS Compliant The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications



Bias-Tee Electrical Specifications


	FREQUENCY (MHz) INSERTION LOSS (dB)		ISOLATION (dB) (RF port to DC port) (RF&DC port to DC port)			VSWR (:1)				
		L M U		L	M	U	L	M	U	
f _L	f_{\cup}	Тур. Мах.	Тур. Мах.	Тур. Мах.	Typ. Min.	Typ. Min.	Typ. Min.	Тур. Мах.	Тур. Мах.	Тур. Мах.
10	10000	0.1 0.5	0.35 0.8	0.8 1.6	55 30	33 18	22 15	1.05 1.3	1.2 1.5	1.3 1.5

External C1(0.01µF) is required. See functional schematic and PCB layout.

Typical Performance Data


FREQUENCY (MHz)				R (:1) urrent	ISOLATION (dB) 0mA		
	0mA	200mA	0mA	200mA	RF-DC	RF & DC - DC	
10.00	0.11	0.11	1.21	1.21	35.29	34.85	
100.00	0.04	0.04	1.02	1.02	67.27	76.84	
500.00	0.07	0.07	1.03	1.03	58.28	56.42	
1000.00	0.12	0.12	1.05	1.05	51.44	48.45	
1450.00	0.13	0.13	1.04	1.04	44.41	42.96	
2050.00	0.16	0.16	1.02	1.02	39.31	37.44	
2500.00	0.18	0.18	1.03	1.03	35.19	34.15	
3100.00	0.21	0.21	1.03	1.03	30.85	29.35	
4000.00	0.30	0.30	1.16	1.16	27.39	25.43	
5050.00	0.47	0.48	1.08	1.08	25.68	23.02	
6100.00	0.66	0.66	1.20	1.20	22.61	19.71	
7000.00	0.86	0.85	1.25	1.25	22.68	18.80	
8050.00	0.78	0.77	1.11	1.11	20.55	18.49	
9100.00	0.70	0.69	1.22	1.21	21.37	18.82	
10000.00	0.99	0.97	1.09	1.09	20.70	17.68	


Functional Schematic





- OBS


 Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
 Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
 The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits website at www.minicircuits.com/MCLStore/terms.jsp











Notes
A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.

B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.

C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits website at www.minicircuits.com/MCLStore/terms.jsp