

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	N-MALE 1 RETURN LOSS (dB)	N-MALE 2 RETURN LOSS (dB)
100	0.03	46.8	50.7
200	0.05	51.8	46.1
300	0.06	46.7	46.2
400	0.07	44.8	45.6
500	0.08	43.3	44.5
600	0.09	42.6	43.2
700	0.09	42.1	42.1
800	0.10	42.4	41.6
900	0.11	42.8	41.6
1000	0.11	44.4	43.0
1100	0.11	45.9	45.1
1250	0.12	48.8	50.7
1500	0.13	46.7	47.8
1750	0.13	43.3	42.5
2000	0.14	42.6	42.1
2001	0.14	42.6	42.1
2250	0.15	43.5	44.7
2500	0.16	46.2	56.7
2750	0.17	41.8	42.6
3000	0.17	35.7	36.2
3250	0.19	35.1	35.9
3500	0.18	41.4	48.7
3750	0.19	34.0	34.8
4000	0.21	29.6	29.7
4250	0.21	32.9	32.8
4500	0.22	36.7	40.8
5000	0.22	27.7	27.5
5500	0.24	27.7	27.8
6000	0.24	32.9	33.0
6500	0.21	24.3	23.5
7000	0.25	34.2	32.2
7500	0.29	25.5	24.4
8000	0.29	24.3	22.8
8500	0.28	35.9	34.9
9000	0.18	21.5	21.5
9500	0.26	26.5	26.6
10000	0.31	26.5	26.8
10500	0.30	23.2	24.4
11000	0.29	43.8	35.2
11500	0.34	26.3	29.4
12000	0.35	30.0	30.8
12500	0.33	32.7	31.6
13000	0.33	30.6	34.6
13500	0.34	29.9	27.7
14000	0.31	24.0	29.6
14500	0.38	34.4	26.8
15000	0.34	22.6	28.2
15500	0.36	23.0	23.8
16000	0.35	25.2	29.0
16500	0.32	21.6	25.2
17000	0.37	32.0	34.8
17500	0.40	21.7	26.3
18000	0.39	28.3	27.8