

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	N-MALE 1 RETURN LOSS (dB)	N-MALE 2 RETURN LOSS (dB)
100	0.07	28.4	28.5
200	0.10	41.3	41.5
300	0.13	28.4	28.4
400	0.15	35.5	35.6
500	0.18	29.5	29.5
600	0.18	31.9	32.0
700	0.20	31.0	31.0
800	0.22	29.9	30.0
900	0.22	34.2	34.0
1000	0.24	28.8	28.8
1100	0.25	39.8	39.5
1250	0.28	30.5	30.2
1500	0.30	40.3	40.5
1750	0.35	29.0	28.8
2000	0.34	32.6	32.5
2001	0.34	32.8	32.6
2250	0.35	39.8	40.3
2500	0.39	29.9	30.1
2750	0.40	33.9	34.6
3000	0.42	40.2	39.0
3250	0.44	30.3	31.9
3500	0.44	36.0	37.7
3750	0.47	40.0	40.0
4000	0.50	31.6	34.2
4250	0.50	35.3	38.2
4500	0.51	45.8	53.7
5000	0.55	32.9	34.1
5500	0.58	30.0	30.9
6000	0.60	38.2	34.4
6500	0.65	32.1	32.8
7000	0.71	25.6	24.6
7500	0.69	25.8	25.1
8000	0.71	36.4	43.8
8500	0.73	25.9	25.5
9000	0.82	21.6	21.3
9500	0.79	23.0	23.1
10000	0.81	29.1	29.4
10500	0.80	24.7	26.4
11000	0.97	22.3	22.3
11500	0.96	23.6	23.2
12000	0.87	33.7	34.4
12500	0.89	37.9	41.2
13000	0.91	25.1	25.0
13500	0.95	26.5	25.4
14000	0.99	32.5	33.8
14500	1.03	34.2	28.9
15000	1.01	31.8	25.7
15500	1.02	33.8	30.4
16000	0.98	36.3	26.2
16500	1.13	35.6	24.0
17000	1.11	38.3	30.0
17500	1.12	36.2	31.0
18000	1.12	35.4	26.2