

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	SMA-MALE 1 RETURN LOSS (dB)	SMA-MALE 2 RETURN LOSS (dB)
100	0.02	37.5	37.5
200	0.03	31.9	31.8
300	0.03	29.6	29.4
400	0.04	28.6	28.5
500	0.04	29.2	29.2
600	0.05	31.6	31.3
700	0.05	37.0	36.0
800	0.06	50.7	47.1
900	0.06	34.7	37.1
1000	0.07	29.5	30.7
1100	0.08	27.5	28.0
1250	0.08	27.6	27.1
1500	0.09	40.0	39.9
1750	0.11	28.8	28.6
2000	0.11	28.8	28.5
2001	0.11	28.8	28.5
2250	0.12	54.3	56.0
2500	0.12	30.2	30.5
2750	0.13	34.4	31.8
3000	0.14	37.7	42.3
3250	0.14	34.7	33.9
3500	0.15	37.7	34.4
3750	0.16	36.9	37.0
4000	0.15	41.9	38.4
4250	0.17	30.5	29.8
4500	0.18	32.7	35.0
5000	0.20	27.2	27.4
5500	0.20	26.4	26.6
6000	0.23	28.5	29.4
6500	0.23	26.4	27.5
7000	0.24	23.3	23.1
7500	0.26	23.5	23.7
8000	0.25	30.0	30.6
8500	0.25	37.5	32.6
9000	0.25	30.3	27.1
9500	0.27	29.9	30.6
10000	0.28	28.9	35.6
10500	0.29	23.3	24.8
11000	0.29	26.7	25.6
11500	0.29	38.7	33.7
12000	0.32	27.0	27.4
12500	0.34	22.5	23.4
13000	0.27	25.4	23.9
13500	0.35	25.7	29.4
14000	0.34	25.5	35.9
14500	0.32	29.3	37.3
15000	0.35	30.4	42.8
15500	0.35	25.1	32.7
16000	0.35	26.9	30.2
16500	0.35	28.6	30.0
17000	0.35	27.3	30.3
17500	0.40	33.7	33.8
18000	0.45	27.8	27.5