

Adapter, N Female to N Female

NFFL-NF50+

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	N-FEMALE 1 VSWR (:1)	N-FEMALE 2 VSWR (:1)
10	0.000	1.00	1.00
100	0.002	1.01	1.01
500	0.013	1.04	1.04
1000	0.024	1.07	1.07
1500	0.034	1.09	1.09
2000	0.041	1.09	1.09
2500	0.043	1.08	1.08
3000	0.044	1.06	1.06
3500	0.044	1.03	1.03
4000	0.048	1.01	1.01
4500	0.055	1.04	1.04
5000	0.061	1.08	1.08
5500	0.058	1.10	1.10
6000	0.050	1.11	1.11
6500	0.041	1.09	1.09
7000	0.033	1.06	1.06
7500	0.030	1.02	1.02
8000	0.034	1.07	1.07
8500	0.058	1.13	1.13
9000	0.086	1.19	1.19
9500	0.089	1.25	1.25
10000	0.098	1.28	1.28
10500	0.099	1.27	1.27
11000	0.082	1.23	1.23
11500	0.057	1.14	1.14
12000	0.044	1.05	1.05
12500	0.047	1.10	1.10
13000	0.084	1.22	1.22
13500	0.145	1.35	1.35
14000	0.204	1.46	1.46
14500	0.243	1.51	1.51
15000	0.238	1.51	1.51
15500	0.205	1.45	1.45
16000	0.148	1.35	1.35
16500	0.098	1.22	1.22
17000	0.064	1.10	1.10
17500	0.063	1.04	1.04
18000	0.084	1.16	1.16