

Typical Performance Data

| FREQUENCY (MHz) | ATTENUATION (dB) | VSWR (:1) |
|--------------------|---------------------|--------------|
| 10 | 4.88 | 1.13 |
| 50 | 4.89 | 1.14 |
| 100 | 4.89 | 1.12 |
| 200 | 4.90 | 1.11 |
| 300 | 4.90 | 1.10 |
| 400 | 4.91 | 1.10 |
| 500 | 4.91 | 1.10 |
| 1000 | 4.93 | 1.09 |
| 1500 | 4.94 | 1.09 |
| 2000 | 4.93 | 1.09 |
| 2500 | 4.92 | 1.09 |
| 3000 | 4.91 | 1.09 |
| 3500 | 4.89 | 1.08 |
| 4000 | 4.91 | 1.06 |
| 4500 | 4.90 | 1.04 |
| 5000 | 4.91 | 1.04 |
| 5500 | 4.91 | 1.08 |
| 6000 | 4.90 | 1.11 |
| 6500 | 4.91 | 1.15 |
| 7000 | 4.92 | 1.17 |
| 7500 | 4.94 | 1.19 |
| 8000 | 4.94 | 1.19 |
| 8500 | 4.95 | 1.15 |
| 9000 | 4.97 | 1.14 |
| 9500 | 4.96 | 1.12 |
| 10000 | 4.96 | 1.11 |
| 10500 | 4.97 | 1.12 |
| 11000 | 4.97 | 1.14 |
| 11500 | 4.98 | 1.15 |
| 12000 | 4.99 | 1.17 |
| 12500 | 5.01 | 1.19 |
| 13000 | 5.01 | 1.20 |
| 13500 | 5.02 | 1.22 |
| 14000 | 5.04 | 1.23 |
| 14500 | 5.05 | 1.25 |
| 15000 | 5.05 | 1.26 |
| 15500 | 5.04 | 1.26 |
| 16000 | 5.04 | 1.24 |
| 16500 | 5.03 | 1.24 |
| 17000 | 5.02 | 1.23 |
| 17500 | 5.02 | 1.24 |
| 18000 | 5.05 | 1.27 |