

Coaxial Band Pass Filter

ZX75-12+

Typical Performance Data

| FREQUENCY (MHz) | INSERTION LOSS (dB) | RETURN LOSS (dB) |
|--------------------|---------------------------|------------------------|
| 0.3 | 100.39 | 0.01 |
| 7.0 | 53.30 | 0.28 |
| 7.5 | 36.73 | 0.49 |
| 8.0 | 14.55 | 1.79 |
| 8.2 | 5.51 | 7.81 |
| 8.5 | 3.45 | 7.87 |
| 9.0 | 1.85 | 20.08 |
| 11.0 | 1.31 | 15.62 |
| 12.0 | 1.26 | 16.04 |
| 13.0 | 1.59 | 11.12 |
| 15.0 | 2.09 | 11.31 |
| 15.7 | 4.10 | 6.46 |
| 16.0 | 6.58 | 3.79 |
| 16.6 | 15.51 | 1.48 |
| 18.0 | 37.07 | 0.57 |
| 20.0 | 60.12 | 0.29 |
| 100.0 | 94.22 | 0.07 |
| 1000.0 | 67.12 | 0.74 |
| 3000.0 | 59.03 | 2.83 |

REV. X1
ZX75-12+
080928
Page 1 of 1



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED RoHS compliant
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see

