

Typical Performance Data

FREQ.	Insertion Loss	Input Return Loss	Output Return Loss	FREQ.	Group Delay
(MHz)	(dB)	(dB)	(dB)	(MHz)	(ns)
25	99.52	35.65	36.07	19250	0.29
50	103.48	36.50	36.68	19275	0.29
100	105.02	41.71	39.95	19300	0.29
200	95.88	36.75	35.44	19325	0.29
300	92.28	34.96	33.85	19350	0.29
500	86.96	32.53	31.48	19375	0.29
700	84.29	31.68	30.45	19400	0.29
1000	80.65	30.30	29.33	19425	0.29
1200	79.30	29.81	28.80	19450	0.29
1400	78.20	29.52	28.69	19475	0.29
1600	76.71	30.72	29.52	19500	0.29
1800	76.09	29.07	28.63	19525	0.29
2000	75.20	29.88	29.57	19550	0.29
2500	73.27	30.22	31.03	19575	0.29
3000	69.80	32.53	34.97	19600	0.29
3500	65.41	33.42	35.13	19625	0.29
4000	61.36	31.63	29.03	19650	0.29
4500	58.06	27.29	24.52	19675	0.29
5000	55.36	24.45	21.57	19700	0.29
5500	53.48	22.05	19.48	19725	0.29
6000	52.28	20.09	17.67	19750	0.29
6500	51.81	18.52	16.45	19775	0.29
7000	52.16	17.76	15.73	19800	0.29
8000	56.70	16.53	14.75	19825	0.29
9000	63.34	16.28	15.11	19850	0.29
10000	59.54	18.17	18.02	19875	0.29
11000	58.48	22.57	22.92	19900	0.30
12050	30.31	16.52	16.66	19925	0.30
12550	20.27	15.65	17.01	19950	0.30
13525	10.03	15.87	20.85	19975	0.30
19500	5.14	14.65	11.98	20000	0.30
19600	5.14	15.24	12.08	20025	0.30
19700	5.16	15.86	12.20	20050	0.30
19800	5.16	16.70	12.35	20075	0.30
20000	5.18	18.85	12.60	20100	0.30
20100	5.19	20.46	12.73	20125	0.30
20200	5.24	22.50	12.76	20150	0.30
20300	5.25	25.43	12.77	20175	0.30
20400	5.31	29.13	12.74	20200	0.30
20500	5.33	35.28	12.62	20225	0.30
24100	10.07	15.92	8.97	20250	0.30
25800	19.92	14.91	9.63	20275	0.30
26700	30.22	13.33	9.68	20300	0.30
27000	34.56	12.51	9.60	20325	0.30
27200	37.73	11.95	9.52	20350	0.30
27400	41.08	11.42	9.46	20375	0.30
27600	44.66	11.04	9.37	20400	0.30
27800	48.33	10.77	9.25	20425	0.30
28000	52.23	10.55	9.14	20450	0.30
28300	58.35	10.30	8.91	20475	0.30
28600	61.07	10.15	8.73	20500	0.30
28900	60.83	10.08	8.53	20525	0.30
29200	60.09	10.15	8.34	20550	0.30
29500	59.53	10.20	8.16	20575	0.30
29800	59.31	10.28	8.09	20600	0.30
30000	58.70	10.39	8.01	20625	0.30
30500	59.36	10.60	8.06	20650	0.30
31000	56.81	10.87	8.29	20675	0.30
31500	54.29	11.09	8.81	20700	0.30
32000	49.27	11.25	9.87	20725	0.30