




## MMIC DIE

# X3 Frequency Multiplier **CY3-223-D+**

50Ω Output 10 to 22 GHz

### THE BIG DEAL

- Ultra-wideband, output from 10 to 22 GHz
- Wide input power range, +12 to +18 dBm
- Low Conversion Loss, 17 dB Typ.
- Good Fundamental and Harmonic Suppression:  
F1 > +34 dBc; F2 > +45 dBc; F4 > +50 dBc.



#### +RoHS Compliant

The +Suffix identifies RoHS Compliance.  
See our website for methodologies and qualifications

### APPLICATIONS

- 5G MIMO and Back Haul Radio Systems
- Satellite Communications
- Test and Measurement Equipment
- Radar, EW, and ECM Defense Systems

SEE ORDERING INFORMATION ON THE LAST PAGE

### PRODUCT OVERVIEW

Mini-Circuits' CY3-223-D+ is an ultra-wideband MMIC Frequency Tripler, converting input frequencies from 3.33 to 7.33 GHz into output frequencies from 10 to 22 GHz. Its wide output range makes this model suitable for broadband systems as well as a wide variety of narrow-band applications. The CY3-223-D+ die utilizes GaAs HBT technology and is suitable for chip and wire assemblies.

### KEY FEATURES

Feature	Advantages
Broadband, 10 to 22 GHz output	With an output frequency range spanning 10 to 22 GHz, this multiplier supports broadband applications such as defense and instrumentation as well as a wide range of narrowband system requirements including 5G.
Excellent fundamental and harmonic suppression: <ul style="list-style-type: none"> <li>• F1, +30 dBc</li> <li>• F2, +45 dBc</li> <li>• F4, +50 dBc</li> </ul>	Reduces spurious signals and the need for additional filtering.
Unpackaged Die	Enable user to integrate it directly into hybrids.
Wide input power range, +12 to +18 dBm	Wide input power signal range accommodates different input signal levels while still maintaining a low Conversion Loss.

REV. A  
ECO-018288  
CY3-223-D+  
MCL NY  
230711





MMIC DIE

# X3 Frequency Multiplier **CY3-223-D+**

50Ω Output 10 to 22 GHz

## ELECTRICAL SPECIFICATIONS<sup>1</sup> AT 25°C AND Z<sub>0</sub> = 50Ω, UNLESS NOTED OTHERWISE

Parameter	Condition (GHz)	RF Input = +12 dBm			Unit
		Min.	Typ.	Max.	
Multiplication Factor			3		
Frequency Range, Input (F1)		3.33		7.33	GHz
Frequency Range, Output (F2)		10	-	22	GHz
Input Power		+12		+18	dBm
Conversion Loss	3.33		22.0		dB
	4		18.0		
	5		16.4		
	6		18.2		
	7.33		22.1		
Harmonic Output <sup>2</sup>	F1	3.33		45.8	dBc
		4		49.8	
		5		46.6	
		6		44.9	
		7.33		22.1	
	F2	3.3		86.1	dBc
		4		71.9	
		5		55.1	
		6		45.0	
		7.33		39.9	
	F3	3.33		47.9	dBc
		4		48.9	
		5		56.2	
		6		51.7	
		7.33		40.9	

1. Die soldered in a 4x4 mm 24L MCLP and measured on Mini-Circuits Characterization Test Board TB-CY3-223C+.  
 2. Harmonics of input frequency below the power level of F3.

## MAXIMUM RATINGS<sup>3</sup>

Parameter	Ratings
Operating Temperature	-40°C to +85°C
Storage Temperature	-65°C to +150°C
RF Input Power	+22 dBm (5 minute max) +19 dBm (Continuous)

3. Permanent damage may occur if any of these limits are exceeded.






# MMIC DIE

# X3 Frequency Multiplier **CY3-223-D+**


50Ω Output 10 to 22 GHz

## SIMPLIFIED SCHEMATIC AND PAD DESCRIPTION



Function	Pad Number	Description
RF-IN	1	RF-Input Pad.
RF-OUT	4	RF-Output Pad.
Ground	2, 3, 5, 6 & Bottom of Die	The bond pads are connected to back-side through vias and do not require wire-bond connections to ground.

## BONDING PAD POSITION




## DIMENSIONS IN μM, TYPICAL

L1	L2	L3	H1	H2	H3	H4
85	2375	2460	1620	1810	2000	2170

Thickness	Die Size	Pad Size 1 & 4	Pad Size 2, 3, 5, & 6
100	2460 x 2170	92 x 172	92 x 92

## ASSEMBLY DIAGRAM



1. Recommended bond length for RF-IN & RF-Out: 305 μm (12mils)
2. Recommended amount of bonding wires per port: 3





MMIC DIE

# X3 Frequency Multiplier **CY3-223-D+**

50Ω Output 10 to 22 GHz

## APPLICATION AND CHARACTERIZATION CIRCUIT





Fig 1. Application and Characterization Circuit

Note: This block diagram is used for characterization.

(DUT is soldered onto a 4x4 24L MCLP and measured on Mini-Circuits Characterization test board TB-CY3-223C+) Conversion Loss and Harmonic Output are measured using Agilent E4448A PSA Spectrum Analyzer

## ASSEMBLY PROCEDURE

1. Storage  
Die should be stored in a dry nitrogen purged desiccators or equivalent.
2.  ESD  
MMIC HBT Multiplier die are susceptible to electrostatic and mechanical damage. Die are supplied in antistatic protected material, which should be open in clean room conditions at an appropriately grounded anti-static workstation.
3. Die Handling and Attachment  
Devices need careful handling using correctly designed collets, it is recommended to handle the chip along the edges with a custom design collet. The die mounting surface must be clean and flat. Using conductive silver filled epoxy, recommended epoxies are Ablestik 84-1 LMISR4 or equivalents. Apply sufficient epoxy to meet required epoxy bond line thickness, epoxy fillet height and epoxy coverage around total periphery. Parts shall be cured in a nitrogen filled atmosphere per manufacturer's cure condition.
4. Wire Bonding  
Bond pad openings in the surface passivation above the bond pads are provided to allow wire bonding to the die gold bond pads. Thermo-sonic bonding is used with minimized ultrasonic content. Bond force, time, ultrasonic power and temperature are all critical parameters. Suggested wire is pure gold, 1mil diameter. Bonds must be made from the bond pads on the die to the packaged or substrate. All bond wire length and bond wire height should be kept as short as possible unless specified by the Assembly Drawing to minimize performance degradation due to undesirable series inductance






MMIC DIE

# X3 Frequency Multiplier CY3-223-D+


50Ω Output 10 to 22 GHz

## TYPICAL PERFORMANCE CURVES


Conversion Loss X3 Output  
Temperature = +25°C




Harmonic X1 Output  
Temperature = +25°C



Harmonic X2 Output  
Temperature = +25°C



Harmonic X4 Output  
Temperature = +25°C






MMIC DIE

# X3 Frequency Multiplier **CY3-223-D+**


50Ω Output 10 to 22 GHz

## TYPICAL PERFORMANCE CURVES


**Conversion Loss X3 Output**  
RF In = +12dBm




**Harmonic X1 Output**  
RF In = +12dBm



**Harmonic X2 Output**  
RF In = +12dBm



**Harmonic X4 Output**  
RF In = +12dBm





MMIC DIE


# X3 Frequency Multiplier **CY3-223-D+**

Mini-Circuits


50Ω Output 10 to 22 GHz

## TYPICAL PERFORMANCE CURVES


**Conversion Loss X3 Output**  
RF In = +15dBm




**Harmonic X1 Output**  
RF In = +15dBm



**Harmonic X2 Output**  
RF In = +15dBm



**Harmonic X4 Output**  
RF In = +15dBm






MMIC DIE

# X3 Frequency Multiplier **CY3-223-D+**


50Ω Output 10 to 22 GHz

## TYPICAL PERFORMANCE CURVES


**Conversion Loss X3 Output**  
RF In = +18dBm




**Harmonic X1 Output**  
RF In = +18dBm



**Harmonic X2 Output**  
RF In = +18dBm



**Harmonic X4 Output**  
RF In = +18dBm







MMIC DIE

# X3 Frequency Multiplier **CY3-223-D+**

50Ω Output 10 to 22 GHz

**ADDITIONAL DETAILED TECHNICAL INFORMATION IS AVAILABLE ON OUR DASH BOARD.**

<b>Performance Data</b>	Data Table	
	Swept Graphs	
<b>Case Style</b>	Die	
<b>Die Ordering and packaging information</b>	Quantity, Package	Model No.
	Gel – Pak: 5, 10, 50	CY3-223-DG+
	Medium†, Partial wafer: KGD*<440	CY3-223-DP+
	Full Wafer	CY3-223-DF+
<b>Die Marking</b>	EL-MUL-2	
<b>Environmental Ratings</b>	ENV80	

\*Known Good Die ('KGD') means that the die in question have been subjected to Mini-Circuits DC test performance criteria and measurement instructions and that the parametric data of such die fall within a predefined range. While DC testing is not definitive, it does provide a higher degree of confidence that die is capable of meeting typical RF electrical performance specified by Mini-Circuits.

### NOTES

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained there in. For a full statement of the standard. Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)
- D. Mini-Circuits does not warrant the accuracy or completeness of the information, text, graphics and other items contained within this document and same are provided as an accommodation and on an As is basis, with all faults.
- E. Purchasers of this part are solely responsible for proper storing, handling, assembly and processing of Known Good Dice (including, without limitation, proper ESD preventative measures, die preparation, die attach, wire bonding and related assembly and test activities), and Mini-Circuits assumes no responsibility therefor or for environmental effects on Known Good Dice.
- F. Mini-Circuits and the Mini-Circuits logo are registered trademarks of Scientific Components Corporation d/b/a Mini-Circuits. All other third-party trademarks are the property of their respective owners. A reference to any third-party trademark does not constitute or imply any endorsement, affiliation, sponsorship, or recommendation by any such third-party of Mini-Circuits or its products.

