



MMIC DIE


# Wideband Amplifier

AVA-054-D+

50Ω DC to 50 GHz

## THE BIG DEAL

- Wideband, DC to 50 GHz
- Gain Flatness,  $\pm 2.2$  dB
- Typical P1dB, +19 dBm
- May be used as a replacement model for MAAM-011109-DIE<sup>a,b</sup>



## APPLICATIONS

- 5G MIMO and Back Haul Radio Systems
- Satellite Ka-band Communications
- Test and Measurement Equipment
- Radar, EW, and ECM Defense Systems

### +RoHS Compliant

The +Suffix identifies RoHS Compliance.  
See our website for methodologies and qualifications

SEE ORDERING INFORMATION ON THE LAST PAGE

## PRODUCT OVERVIEW

AVA-054-D+ is a GaAs PHEMT MMIC Distributed Amplifier designed for use in microwave and millimeter wave transceiver systems and signal sources operating from 0.05 to 50 GHz. The amplifier provides 16 dB of Gain, +19 dBm P1dB and +26 dBm OIP3 while operating from a +5V supply with 160mA current consumption. The MMIC Amplifier includes an on chip power detector for power monitoring and the Gain can be varied over a 20 dB range with a control voltage. The AVA-054-D+ performance characteristics and features makes the device useful for a wide range of Test and Measurement Equipment and Defense Systems operating in frequency ranges from 0.05-50 GHz.

## KEY FEATURES

Features	Advantages
Wideband: DC to 50 GHz	General purpose wideband amplifier is suitable for various applications.
Gain: 16.5 dB $\pm$ 1.5 dB from 0.1 to 45 GHz.	Minimizes the number of gain stages required to achieve published Gain, reducing component count, cost and complexity.
P1dB: +19.5 dBm $\pm$ 1.6 dB	Useful as a driver amplifier. Can be used as a final amplifier in local oscillator chains to drive +17 dBm mixers.
On Chip Power Detector	Enables power monitoring and AGC loops.
Adjustable Gain with control voltage	Useful temperature compensation and AGC of wide bandwidth signal chains.
Unpackaged die	Enables user to integrate it directly into hybrids.

A. Suitability for model replacement within a particular system must be determined by and is solely the responsibility of the customer based on, among other things, electrical performance criteria, stimulus conditions, application and compatibility with other components and environmental conditions and stresses.

B. The MAAM-011109-DIE part number is used for identification and comparison purposes only.

REV. OR  
ECO-014452  
AVA-054-D+  
MCL NY  
220804



MMIC DIE

## Wideband Amplifier

AVA-054-D+

Mini-Circuits

50Ω DC to 50 GHz

ELECTRICAL SPECIFICATIONS<sup>1</sup> AT 25°C, VC = OPEN, VDD = +5V, Z<sub>O</sub> = 50Ω, UNLESS NOTED OTHERWISE

Parameter	Condition (GHz)	VDD = +5V, IDD = 160mA			Units
		Min.	Typ.	Max.	
Frequency Range		DC		50	GHz
Gain <sup>2</sup>	0.1		17.3		dB
	10		15.6		
	20		16.1		
	30		17.4		
	40		17.4		
	50		13		
Input Return Loss	0.1		12		dB
	10		15		
	20		17		
	30		22		
	40		12		
	50		25		
Output Return Loss	0.1		27		dB
	10		21		
	20		16		
	30		16		
	40		14		
	50		12		
Reverse Isolation	0.1-50		36		dB
Output Power at 1 dB Compression	0.1		20.7		dBm
	10		20.0		
	20		19.3		
	30		17.9		
	40		17.0		
	50		--		
Output Third-Order Intercept (Pout = +5 dBm/Tone)	0.1		32		dBm
	10		27.3		
	20		26.9		
	30		22.5		
	40		20.8		
	50		--		
Noise Figure	0.1		5.5		dB
	10		3.1		
	20		4.0		
	30		5.5		
	40		7.8		
	50		11.8		
Device Operating Voltage (VDD)			+5.0		V
Device Operating Current (IDD)			160.0		mA
Device Gate Voltage (VGG)			-0.76		V
Device Gate Current (IGG)			-0.24		µA
Thermal Resistance, Junction-to-Ground Lead (θJC)			17.8		°C/W

1. Die is soldered and measured on Mini-Circuits die characterization board. See Characterization &amp; Application Circuit (Fig. 2).

2. If VC is open, the measured voltage is +1.33V.

Mini-Circuits®



MMIC DIE

# Wideband Amplifier

AVA-054-D+

50Ω DC to 50 GHz


## MAXIMUM RATINGS<sup>3</sup>

Parameter	Ratings
Operating Temperature	-40°C to +85°C
Junction Temperature	+150°C <sup>4</sup>
Total Power Dissipation	1.8W
Input Power (CW)	+17dBm
Drain Voltage (VDD)	+7.5V
Gate Voltage (VGG)	-1.6V to -0.5V
Drain Current (IDD)	240mA
Gate Current (IGG)	-5mA to 0mA
Control Voltage (VC)	-1V to 1.2V


3. Permanent damage may occur if these limits are exceeded.

4.  $T_j = +85^\circ\text{C} + (\text{VDD})(\text{IDD})^{\alpha}/(\text{eJC}) = +99^\circ\text{C}$ . Keeping  $T_j$  below +99°C will ensure MTTF > 100 Years.

FIG 1. GAIN VS. CONTROL VOLTAGE (VC)




## SIMPLIFIED SCHEMATIC AND PAD DESCRIPTION



Function	Pad Number	Description
RF-IN	1	RF Input Pad
VGG	3	Gate Bias Pad
VC	4, 11	Gain Control Pads
RF-OUT & VDD	6	RF Output and Drain Pad
VDET	8	Voltage Detector Pad
VD	9	Alternative Drain Bias Pad, connects to Pad #6 internally.
VD1	10	Alternative Drain Bias Pad. It is terminated by C2
GROUND	2, 5, 7, 12, & Bottom of die	The bond pads are connected to backside through vias and do no require wire-bond connections to ground.

## BONDING PAD POSITION



## DIMENSIONS IN μm, TYP.

L1	L2	L3	L4	L5	L6	L7	L8		
88	112	363	520	1040	1285	1882	1970		
H1	H2	H3	H4	H5	H6	H7	H8	H9	H10
89	341	471	601	633	841	971	1101	1211	1300
Thickness	Die size	Pad size 1,6	Pad size 2, 5, 7, 12	Pad size 3, 8, 9, 10, & 11	Pad size 4				
100	1970 x 1300	73 x 113	91 x 86	93 x 73	73 x 93				




MMIC DIE

# Wideband Amplifier

AVA-054-D+

50Ω DC to 50 GHz

## CHARACTERIZATION & APPLICATION CIRCUIT



Component	Size	Value	Part Number	Manufacturer
C1, C3, & C6	100pF	22x22mil	MA4M3100	MACOM Inc.
C2	820pF	20x20mil	SKT02C821M11A6	TECDIA Inc.
C4, C5, & C7	0.1μF	0402	GRM155R71C104KA88D	Murata
R1	200Ω	0603	RK73H1JTTD2001F	KOA

Fig 2. Characterization & Application Circuit

Note: This block diagram is used for characterization (Die is attached and wire-bonded on die characterization test board). Gain, Return Loss, Output Power at 1dB Compression (P1dB), Output IP3 (OIP3) and Noise Figure measured using Agilent's N5245B Microwave Network Analyzer.

### Conditions:

1. VDD = +5V,
2. VGG is set to obtain desired IDD as shown in specification table.
3. Gain and Return Loss: Pin= -25 dBm
4. Output IP3 (OIP3): Two Tones, spaced 1 MHz apart, +5 dBm/Tone at output.

### Switch ON/OFF sequence:

1. To switch the amplifier ON:
  - a. Set VGG = -1.2V. Apply VGG.
  - b. Set VDD = +5V. Apply VDD
  - c. Adjust VGG to get IDD = 160mA (Typically, VGG = -0.76V)
  - d. Apply RF Signal.

### 2. To switch the amplifier OFF:

- a. Turn off RF Signal
- b. Adjust VGG down to -1.2V.
- c. Turn off VDD.
- d. Turn off VGG



MMIC DIE


# Wideband Amplifier

AVA-054-D+

Mini-Circuits

50Ω DC to 50 GHz

## ASSEMBLY DRAWING




Note: Tested on die characterization board with following bond lengths:

1. Typical bond length for RF-IN: 360µm (14mils)
2. Typical bond length for RF-OUT & VDD: 360µm (14mils)
3. Typical bond lengths from die, capacitors, VGG, VDET, and VC were kept as short as possible.
4. Components list given in Figure 2.

**FIG. 3 OUTPUT POWER VS. VDET**

Pout vs. V\_det



## ASSEMBLY PROCEDURE

1. Storage  
Die should be stored in a dry nitrogen purged desiccators or equivalent.
2.  ESD  
MMIC PHEMT amplifier die are susceptible to electrostatic and mechanical damage. Die are supplied in antistatic protected material, which should be open in clean room conditions at an appropriately grounded anti-static workstation.
3. Die Handling and Attachment  
Devices need careful handling using correctly designed collets, it is recommended to handle the chip along the edges with a custom design collet. The die mounting surface must be clean and flat. Using conductive silver filled epoxy, recommended epoxies are Ablestik 84-1 LMISR4 or equivalents. Apply sufficient epoxy to meet required epoxy bond line thickness, epoxy fillet height and epoxy coverage around total periphery. Parts shall be cured in a nitrogen filled atmosphere per manufacturer's cure condition. The surface of the chip has exposed air bridges and should not be touched with vacuum collet, tweezers or fingers.
4. Wire Bonding  
Bond pad openings in the surface passivation above the bond pads are provided to allow wire bonding to the die gold bond pads. Thermo-sonic bonding is used with minimized ultrasonic content. Bond force, time, ultrasonic power and temperature are all critical parameters. Suggested wire is pure gold, 1mil diameter. Bonds must be made from the bond pads on the die to the packaged or substrate. All bond wire length and bond wire height should be kept as short as possible unless specified by the Assembly Drawing to minimize performance degradation due to undesirable series inductance.











MMIC DIE

## Wideband Amplifier

AVA-054-D+

50Ω DC to 50 GHz



Mini-Circuits®










MMIC DIE

# Wideband Amplifier

AVA-054-D+

Mini-Circuits

50Ω DC to 50 GHz



Mini-Circuits®

www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

PAGE 7 OF 8



MMIC DIE

# Wideband Amplifier

AVA-054-D+

Mini-Circuits

50Ω DC to 50 GHz

ADDITIONAL DETAILED TECHNICAL INFORMATION IS AVAILABLE ON OUR DASH BOARD.

<b>Performance Data</b>	Data Table Swept Graphs S-Parameter (S2P Files) Data Set with and without port extension(.zip file)	
<b>Case Style</b>	Die	
<b>Die Ordering and packaging information</b>	Quantity, Package  Gel – Pak: 5, 10, 50, 100, KGD* Medium <sup>†</sup> , Partial wafer: KGD*<768 Full Wafer	Model No.  AVA-054-DG+ AVA-054-DP+ AVA-054-DF+
	†Available upon request contact sales representative Refer to AN-60-067	
<b>Die Marking</b>	EL-AMP-13	
<b>Environmental Ratings</b>	ENV80	

\*Known Good Die ('KGD') means that the die in question have been subjected to Mini-Circuits DC test performance criteria and measurement instructions and that the parametric data of such die fall within predefined range. While DC testing is not definitive, it does provide a higher degree of confidence that die are capable of meeting typical RF electrical parameters specified by Mini-Circuits.

## NOTES

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained there in. For a full statement of the standard. Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/terms/viewterm.html](http://www.minicircuits.com/terms/viewterm.html)
- D. Mini-Circuits does not warrant the accuracy or completeness of the information, text, graphics and other items contained within this document and same are provided as an accommodation and on an As is basis, with all faults.
- E. Purchasers of this part are solely responsible for proper storing, handling, assembly and processing of Known Good Die (including, without limitation, proper ESD preventative measures, die preparation, die attach, wire bonding and related assembly and test activities), and Mini-Circuits assumes no responsibility therefor or for environmental effects on Known Good Die.
- F. Mini-Circuits and the Mini-Circuits logo are registered trademarks of Scientific Components Corporation d/b/a Mini-Circuits. All other third-party trademarks are the property of their respective owners. A reference to any third-party trademark does not constitute or imply any endorsement, affiliation, sponsorship, or recommendation by any such third-party of Mini-Circuits or its products.

*Typical Performance Data***Definitions:**

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vdd = 5V, Idd = 160mA @ Temperature = +25°C

FREQ (MHz)	Gain (dB)	Isolation (dB)	Input Return Loss (dB)	Output Return Loss (dB)	Stability		IP-3 Output (dBm)	1dB Comp. Output (dBm)	Noise Figure (dB)
					K	Measure			
50	18.91	89.04	7.67	24.81	1326.15	1.17	31.83	20.97	7.41
100	17.19	79.82	11.77	26.94	630.52	1.06	31.84	20.89	6.10
500	15.79	67.89	19.81	28.57	198.98	1.01	34.24	20.69	5.04
1000	15.49	62.32	18.33	23.33	107.66	1.01	32.59	20.72	5.01
2000	15.30	56.33	15.05	18.62	53.80	1.02	31.06	20.46	4.90
3000	15.17	52.88	13.20	18.69	36.08	1.03	28.96	20.45	4.94
4000	15.04	50.29	12.25	20.32	26.96	1.05	27.56	20.37	4.71
5000	14.88	47.85	11.88	22.78	20.70	1.06	28.73	20.48	4.49
6000	14.84	45.85	13.34	21.73	16.83	1.04	27.34	20.88	3.92
7000	14.87	44.11	17.40	15.92	13.86	0.99	26.85	20.63	3.59
8000	14.91	42.58	18.55	12.88	11.32	0.96	28.42	21.09	3.61
9000	15.16	41.41	15.16	14.38	9.59	0.99	28.09	20.68	3.65
10000	15.55	40.56	13.73	23.75	8.50	1.04	27.43	20.02	3.49
11000	15.70	39.89	13.85	23.15	7.76	1.03	26.49	20.06	3.31
12000	15.71	39.10	14.42	18.31	7.03	1.02	26.11	19.98	3.27
13000	15.80	38.12	14.68	18.90	6.25	1.02	26.03	20.42	3.38
14000	15.90	37.05	15.20	21.85	5.53	1.02	25.91	20.60	3.40
15000	15.85	36.01	15.95	19.57	4.95	1.01	25.29	20.53	4.35
16000	15.55	35.30	13.77	13.96	4.52	0.99	24.06	20.38	3.71
17000	15.24	34.76	11.08	12.01	4.13	1.00	25.56	20.25	4.03
18000	15.31	33.99	10.37	13.83	3.76	1.04	25.26	19.90	4.33
19000	15.67	33.09	11.84	17.97	3.46	1.04	25.62	19.93	4.37
20000	15.95	32.44	15.44	14.87	3.20	0.98	26.27	19.69	4.32
21000	16.18	31.91	17.99	13.18	2.94	0.94	26.22	19.68	4.46
22000	16.61	31.13	17.71	15.09	2.61	0.96	25.97	19.53	4.66
23000	16.99	30.52	16.60	15.02	2.33	0.96	25.14	18.05	4.76
24000	17.25	29.97	17.07	14.04	2.13	0.94	24.42	18.19	4.91
25000	17.39	29.47	15.26	15.43	1.99	0.95	24.18	18.36	5.11
26000	16.96	29.53	11.12	12.17	1.91	0.98	22.68	17.11	5.52
27000	16.52	29.64	10.40	10.35	1.89	0.98	23.01	17.59	5.90
28000	16.74	29.19	11.71	11.73	1.91	0.96	23.68	18.22	6.24
29000	17.17	28.61	17.61	19.79	1.94	0.94	23.40	18.23	6.32
30000	17.18	28.61	23.78	14.90	1.92	0.90	21.87	18.19	6.47
32000	17.83	28.23	13.22	19.94	1.70	0.96	22.04	18.17	6.95
34000	18.37	28.09	12.37	10.53	1.41	0.90	21.71	17.47	7.43
36000	17.81	28.96	15.61	7.43	1.56	0.77	20.09	17.70	7.61
38000	17.18	29.66	21.97	11.87	2.07	0.89	19.53	18.75	8.02
40000	17.11	30.27	12.16	13.42	2.19	0.95	18.81	18.37	8.99
42000	17.60	29.92	17.83	10.00	1.91	0.87	19.65	16.81	10.03
44000	15.49	32.74	15.90	6.48	2.85	0.77	--	--	10.45
46000	15.49	35.53	26.62	14.86	4.91	0.96	--	--	9.91
48000	12.67	33.86	10.01	10.56	4.84	0.98	--	--	11.63
50000	11.75	32.33	23.56	10.28	4.87	0.90	--	--	12.59

*Typical Performance Data***Definitions:**

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vdd = 5V, Idd = 150mA @ Temperature = +25°C

FREQ (MHz)	Gain (dB)	Isolation (dB)	Input Return Loss (dB)	Output Return Loss (dB)	Stability		IP-3 Output (dBm)	1dB Comp. Output (dBm)	Noise Figure (dB)
					K	Measure			
50	18.63	82.66	7.66	25.41	657.02	1.17	30.19	21.13	6.87
100	16.93	82.57	11.77	27.79	891.98	1.07	30.38	21.03	5.75
500	15.52	68.62	19.70	29.14	223.24	1.01	32.30	20.84	4.83
1000	15.22	63.40	18.23	23.20	125.70	1.01	32.55	20.88	4.87
2000	15.03	57.12	14.90	18.38	60.66	1.02	32.62	20.63	4.81
3000	14.90	53.44	12.97	18.32	39.54	1.04	30.54	20.61	4.85
4000	14.76	50.68	11.98	19.83	28.97	1.05	28.86	20.55	4.62
5000	14.61	48.08	11.63	22.11	21.82	1.06	30.11	20.62	4.29
6000	14.58	45.93	13.03	21.12	17.42	1.04	27.75	21.07	3.76
7000	14.62	44.11	16.90	15.64	14.21	0.99	27.28	20.75	3.44
8000	14.65	42.61	18.07	12.72	11.66	0.96	27.12	21.13	3.47
9000	14.88	41.46	14.88	14.16	9.92	0.99	29.03	20.75	3.40
10000	15.26	40.62	13.55	22.69	8.82	1.04	26.29	20.14	3.33
11000	15.42	39.93	13.75	23.55	8.04	1.03	25.46	20.18	3.12
12000	15.43	39.13	14.29	18.32	7.28	1.02	24.98	20.03	3.12
13000	15.52	38.16	14.49	18.70	6.46	1.02	24.91	20.47	3.20
14000	15.92	37.05	14.61	22.04	5.49	1.02	24.75	20.66	3.29
15000	16.00	35.96	15.15	21.20	4.83	1.01	24.40	20.16	4.24
16000	15.68	35.21	13.22	14.88	4.42	1.00	23.46	19.70	3.62
17000	15.38	34.64	10.69	12.64	4.01	1.02	24.40	19.76	3.94
18000	15.42	33.87	10.09	14.46	3.66	1.06	24.32	19.34	4.19
19000	15.75	32.97	11.61	19.42	3.39	1.04	24.46	19.21	4.28
20000	16.07	32.31	15.18	16.15	3.14	0.98	24.70	18.98	4.23
21000	16.26	31.79	17.72	14.14	2.90	0.95	24.64	18.75	4.41
22000	16.57	31.07	17.30	16.18	2.62	0.97	24.35	18.60	4.57
23000	16.92	30.49	16.18	16.08	2.35	0.97	23.91	17.59	4.62
24000	17.21	29.96	16.72	14.77	2.14	0.95	23.22	17.81	4.75
25000	17.42	29.45	14.54	16.39	1.98	0.96	22.86	17.88	4.82
26000	17.07	29.47	10.79	12.87	1.89	0.99	22.00	16.35	5.06
27000	16.70	29.55	10.49	10.57	1.85	0.98	22.08	16.72	5.30
28000	16.92	29.12	12.02	11.34	1.87	0.94	22.28	17.39	5.47
29000	17.47	28.52	17.73	18.86	1.87	0.93	21.97	17.36	5.54
30000	17.49	28.48	24.47	16.28	1.86	0.91	21.33	17.09	5.74
32000	17.86	28.29	12.65	21.03	1.71	0.96	21.13	17.23	6.40
34000	18.83	28.26	11.71	11.55	1.38	0.93	23.95	17.00	6.76
36000	18.21	29.22	16.34	7.68	1.57	0.77	20.42	16.37	7.07
38000	17.63	29.88	22.31	12.51	2.04	0.89	20.53	17.65	7.29
40000	17.33	30.39	11.27	13.41	2.15	0.95	21.15	17.23	7.96
42000	18.55	30.15	16.45	11.64	1.82	0.90	29.72	15.51	8.73
44000	16.36	33.12	16.89	6.94	2.79	0.79	---	---	9.40
46000	16.38	36.31	26.12	14.37	4.83	0.95	---	---	9.49
48000	14.27	36.09	9.35	10.59	5.11	1.00	---	---	11.69
50000	14.42	32.95	39.03	10.63	3.91	0.90	---	---	12.21

*Typical Performance Data***Definitions:**

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vdd = 5V, Idd = 170mA @ Temperature = +25°C

FREQ (MHz)	GAIN (dB)	ISOLATION (dB)	INPUT RETURN LOSS (dB)	OUTPUT RETURN LOSS (dB)	STABILITY		IP-3 OUTPUT (dBm)	1dB COMP. OUTPUT (dBm)	NOISE FIGURE (dB)
					K	MEASURE			
50	19.13	94.96	7.70	24.51	2559.19	1.17	38.14	20.87	7.31
100	17.42	80.30	11.79	26.50	649.01	1.06	37.69	20.78	6.00
500	16.02	66.94	19.81	28.14	173.68	1.01	33.81	20.61	4.98
1000	15.72	61.79	18.33	23.33	98.64	1.01	30.95	20.64	4.93
2000	15.55	55.63	15.17	18.75	48.29	1.02	29.90	20.37	4.87
3000	15.44	52.32	13.43	18.91	32.90	1.03	28.93	20.35	4.88
4000	15.32	49.86	12.54	20.64	24.96	1.05	27.82	20.28	4.70
5000	15.16	47.60	12.18	23.33	19.58	1.06	29.51	20.40	4.39
6000	15.12	45.73	13.72	22.22	16.15	1.04	28.81	20.74	3.87
7000	15.13	44.07	17.98	16.14	13.44	0.99	28.82	20.53	3.58
8000	15.17	42.59	19.06	13.02	11.04	0.96	29.67	21.01	3.56
9000	15.44	41.39	15.48	14.49	9.30	0.99	29.95	20.62	3.54
10000	15.84	40.53	13.93	24.20	8.22	1.04	29.06	19.95	3.49
11000	16.00	39.88	13.97	22.79	7.50	1.03	30.33	19.99	3.28
12000	16.03	39.08	14.54	18.07	6.77	1.02	34.26	19.93	3.21
13000	16.13	38.09	14.87	18.73	6.00	1.02	34.24	20.37	3.39
14000	16.22	37.02	15.46	21.22	5.32	1.02	33.49	20.54	3.36
15000	16.15	36.03	16.29	18.43	4.79	1.00	32.24	20.51	4.32
16000	15.85	35.34	13.98	13.30	4.38	0.98	33.90	20.38	3.66
17000	15.52	34.83	11.20	11.48	4.01	0.99	32.09	20.24	3.98
18000	15.59	34.07	10.44	13.20	3.66	1.03	32.37	19.89	4.30
19000	15.96	33.17	11.91	16.89	3.37	1.03	34.05	19.93	4.34
20000	16.24	32.53	15.54	14.03	3.12	0.97	32.57	19.68	4.29
21000	16.49	31.99	18.16	12.49	2.85	0.93	37.07	19.72	4.51
22000	16.97	31.17	18.52	14.28	2.52	0.94	34.97	19.56	4.63
23000	17.40	30.53	17.39	14.33	2.23	0.94	28.22	18.04	4.72
24000	17.70	29.97	17.52	13.54	2.02	0.93	31.28	18.08	4.84
25000	17.86	29.44	15.68	14.71	1.89	0.94	30.91	18.30	5.11
26000	17.39	29.54	11.18	11.57	1.82	0.96	24.52	17.13	5.52
27000	16.92	29.68	10.29	10.14	1.80	0.98	26.98	17.58	5.96
28000	17.10	29.24	11.56	11.90	1.84	0.96	29.77	18.25	6.32
29000	17.49	28.68	17.38	19.25	1.89	0.94	27.10	18.33	6.45
30000	17.46	28.74	22.56	13.75	1.88	0.89	22.74	18.37	6.61
32000	18.29	28.23	14.41	17.97	1.63	0.93	23.24	18.30	7.11
34000	19.00	28.03	12.18	10.15	1.30	0.89	22.87	17.41	7.47
36000	18.59	28.75	14.99	7.20	1.38	0.76	21.55	17.79	7.76
38000	17.89	29.40	23.23	11.20	1.85	0.87	20.80	18.74	8.12
40000	17.70	30.29	12.81	12.29	2.04	0.92	19.43	18.31	9.04
42000	18.50	29.62	17.21	8.60	1.62	0.83	20.41	16.78	10.14
44000	16.47	32.08	16.77	5.80	2.27	0.72	---	---	10.31
46000	16.38	34.70	26.03	14.50	4.04	0.95	---	---	9.59
48000	14.00	31.48	9.69	10.90	3.22	0.98	---	---	11.54
50000	12.83	30.99	21.07	9.76	3.66	0.88	---	---	12.97

*Typical Performance Data***Definitions:**

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vdd = 5V, Idd = 160mA @ Temperature = -45°C

FREQ (MHz)	GAIN (dB)	ISOLATION (dB)	INPUT RETURN LOSS (dB)	OUTPUT RETURN LOSS (dB)	STABILITY		IP-3 OUTPUT (dBm)	1dB COMP. OUTPUT (dBm)	NOISE FIGURE (dB)
					K	MEASURE			
50	19.37	86.28	8.24	24.97	938.70	1.15	30.58	19.16	3.29
100	17.71	78.70	12.12	27.19	524.98	1.06	31.67	19.09	3.61
500	16.39	66.47	19.12	28.19	157.39	1.01	30.71	18.92	4.06
1000	16.12	61.42	17.35	22.93	89.90	1.01	35.82	18.88	4.23
2000	16.04	55.28	14.88	18.54	43.72	1.02	35.42	18.71	4.08
3000	16.04	51.81	13.85	18.34	29.04	1.03	34.34	18.67	4.16
4000	16.06	49.26	13.41	19.41	21.57	1.03	33.17	18.63	4.00
5000	16.04	47.05	13.26	22.85	16.84	1.04	34.06	18.84	3.81
6000	16.03	45.36	15.36	22.08	14.13	1.02	34.90	19.04	3.33
7000	16.18	43.54	21.38	15.29	11.25	0.98	32.88	18.96	3.29
8000	16.15	42.63	21.02	12.68	9.92	0.95	28.74	18.97	3.18
9000	16.40	41.72	16.38	13.95	8.66	0.98	32.13	19.03	3.25
10000	16.91	40.82	14.66	20.50	7.52	1.02	31.11	18.99	3.10
11000	17.13	40.26	14.51	26.14	6.93	1.03	32.68	19.07	2.94
12000	17.20	39.62	14.81	17.85	6.31	1.01	32.37	19.15	2.87
13000	17.36	38.69	15.20	16.90	5.55	1.01	32.13	19.37	2.92
14000	17.56	37.54	16.02	21.43	4.87	1.01	31.65	19.56	2.85
15000	17.60	36.38	17.08	21.59	4.28	1.00	30.82	19.63	3.82
16000	17.36	35.55	13.95	14.82	3.84	0.99	29.93	19.27	3.18
17000	17.07	34.88	10.84	12.77	3.44	1.01	30.34	19.26	3.41
18000	17.07	34.09	10.18	13.80	3.11	1.04	29.40	18.82	3.74
19000	17.41	33.14	11.55	19.13	2.87	1.04	29.12	18.94	3.74
20000	17.68	32.45	14.30	17.16	2.68	0.98	28.65	19.03	3.84
21000	17.86	31.98	16.38	14.15	2.49	0.94	27.74	19.12	3.96
22000	18.28	31.24	18.99	17.03	2.26	0.94	27.80	18.86	4.11
23000	18.74	30.68	21.90	16.85	2.04	0.93	27.43	18.82	4.11
24000	19.08	30.18	21.64	14.26	1.84	0.90	26.10	18.49	4.20
25000	19.49	29.51	19.62	18.23	1.69	0.90	25.10	18.88	4.27
26000	19.14	29.53	11.81	11.38	1.57	0.90	24.48	18.70	4.48
27000	18.66	29.68	10.08	9.72	1.48	0.95	23.59	18.25	4.58
28000	18.94	29.10	10.27	12.65	1.48	0.97	24.11	18.24	4.78
29000	19.30	28.51	14.48	18.85	1.53	0.92	23.68	18.89	4.84
30000	19.27	28.47	17.54	15.82	1.54	0.88	23.01	18.79	5.31
32000	19.75	28.25	19.62	15.77	1.46	0.85	23.27	18.35	6.18
34000	20.71	27.85	11.55	10.78	1.16	0.82	20.91	18.22	6.61
36000	21.04	27.87	13.24	7.58	1.03	0.72	19.79	19.33	7.10
38000	20.41	28.13	17.89	7.61	1.15	0.71	19.28	18.96	7.99
40000	20.23	28.90	15.56	6.61	1.18	0.69	19.21	18.82	8.79
42000	21.20	27.46	17.71	4.48	0.82	0.49	15.28	16.91	9.10
44000	19.12	30.12	15.70	4.90	1.24	0.65	---	---	9.54
46000	18.95	32.04	33.06	13.39	2.26	0.91	---	---	9.05
48000	19.70	24.78	9.12	8.11	0.96	0.62	---	---	10.92
50000	17.74	26.58	17.46	13.13	1.47	0.84	---	---	10.70

# MMIC Amplifier Die

AVA-054-D+

## Typical Performance Data

### Definitions:

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vdd = 5V, Idd = 150mA @ Temperature = -45°C

FREQ (MHz)	Gain (dB)	Isolation (dB)	Input Return Loss (dB)	Output Return Loss (dB)	Stability		IP-3 Output (dBm)	1dB Comp. Output (dBm)	Noise Figure (dB)
					K	Measure			
50	19.30	90.11	8.24	25.06	1470.79	1.15	33.76	19.10	3.16
100	17.64	80.11	12.13	27.34	622.63	1.06	34.72	19.04	3.54
500	16.32	66.73	19.17	28.21	163.51	1.01	30.99	18.90	4.03
1000	16.05	61.49	17.33	22.83	91.34	1.01	34.85	18.84	4.17
2000	15.96	55.31	14.89	18.48	44.27	1.02	34.74	18.70	4.03
3000	15.97	51.88	13.85	18.30	29.50	1.03	33.83	18.65	4.10
4000	15.99	49.35	13.41	19.45	21.97	1.03	33.12	18.62	3.92
5000	15.97	47.12	13.27	22.73	17.11	1.04	34.11	18.79	3.72
6000	15.96	45.45	15.43	21.75	14.40	1.02	34.39	19.01	3.18
7000	16.11	43.63	21.48	15.17	11.46	0.98	33.08	18.90	2.99
8000	16.08	42.70	20.86	12.57	10.06	0.95	29.41	18.94	3.06
9000	16.34	41.80	16.27	13.93	8.79	0.98	32.60	18.96	3.12
10000	16.84	40.93	14.61	20.78	7.68	1.02	31.55	18.91	3.29
11000	17.08	40.31	14.53	25.95	7.01	1.03	30.91	19.05	2.84
12000	17.15	39.67	14.92	17.65	6.38	1.01	33.54	19.06	2.75
13000	17.31	38.72	15.20	16.82	5.60	1.01	33.25	19.24	2.74
14000	17.52	37.55	16.06	21.79	4.90	1.01	32.55	19.42	2.77
15000	17.55	36.38	17.11	21.83	4.31	1.00	31.96	19.15	3.64
16000	17.30	35.54	13.82	14.83	3.85	0.99	30.79	19.08	2.97
17000	17.01	34.88	10.69	12.63	3.44	1.01	31.05	19.03	3.36
18000	17.01	34.08	10.10	13.70	3.12	1.04	29.80	18.88	3.57
19000	17.36	33.11	11.45	19.55	2.88	1.04	29.44	19.03	3.61
20000	17.63	32.43	14.42	17.18	2.69	0.98	29.13	18.94	3.65
21000	17.80	31.97	16.59	13.82	2.50	0.94	27.94	19.04	3.79
22000	18.23	31.23	18.99	16.77	2.27	0.94	28.19	18.90	3.93
23000	18.70	30.67	21.40	17.10	2.05	0.93	27.93	18.42	3.98
24000	19.04	30.16	21.47	14.50	1.85	0.90	26.52	18.01	4.01
25000	19.44	29.51	19.40	18.12	1.70	0.91	25.34	18.21	4.08
26000	19.07	29.56	11.62	11.23	1.58	0.91	24.80	17.72	4.28
27000	18.63	29.69	9.95	9.70	1.48	0.96	23.74	17.36	4.35
28000	18.94	29.07	10.48	12.47	1.48	0.96	24.26	17.30	4.52
29000	19.28	28.51	14.79	18.56	1.53	0.91	24.05	18.19	4.60
30000	19.20	28.52	16.83	15.79	1.55	0.89	23.18	18.34	4.69
32000	19.69	28.31	19.96	15.28	1.47	0.85	23.11	18.16	5.82
34000	20.62	27.95	11.29	10.92	1.17	0.83	20.96	18.32	6.38
36000	21.03	27.90	13.52	7.39	1.03	0.71	20.49	18.88	6.73
38000	20.27	28.39	17.51	7.95	1.20	0.74	20.29	18.07	7.52
40000	19.99	29.26	14.82	7.02	1.27	0.73	19.06	17.76	8.20
42000	20.99	27.94	17.80	5.53	0.95	0.59	15.17	17.59	8.65
44000	19.16	30.43	15.36	4.88	1.27	0.66	---	---	9.04
46000	18.93	32.36	29.08	12.69	2.32	0.90	---	---	8.67
48000	19.49	25.16	9.37	9.46	1.04	0.70	---	---	10.36
50000	17.72	26.81	16.57	12.64	1.49	0.85	---	---	10.32



ISO 9001 ISO 14001 AS 9100 CERTIFIED

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: [www.minicircuits.com](http://www.minicircuits.com)

IF/RF MICROWAVE COMPONENTS



REV. OR

AVA-054-D+

7/21/2022

Page 5 of 9

*Typical Performance Data***Definitions:**

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vdd = 5V, Idd = 170mA @ Temperature = -45°C

FREQ (MHz)	Gain (dB)	Isolation (dB)	Input Return Loss (dB)	Output Return Loss (dB)	Stability		IP-3 Output (dBm)	1dB Comp. Output (dBm)	Noise Figure (dB)
					K	Measure			
50	19.36	83.64	8.23	24.69	693.05	1.15	28.44	19.24	3.42
100	17.70	80.85	12.10	26.80	672.87	1.06	29.08	19.17	3.76
500	16.38	66.38	19.19	27.81	155.96	1.01	30.16	19.05	4.20
1000	16.11	61.26	17.35	22.94	88.36	1.01	37.33	18.93	4.33
2000	16.02	55.06	14.90	18.70	42.75	1.02	36.58	18.79	4.22
3000	16.02	51.63	13.86	18.58	28.53	1.03	34.79	18.74	4.27
4000	16.04	49.12	13.42	19.80	21.29	1.03	33.12	18.71	4.11
5000	16.01	46.94	13.23	23.39	16.69	1.04	33.89	18.91	4.01
6000	16.00	45.22	15.39	22.24	13.96	1.02	33.53	19.13	3.41
7000	16.16	43.33	21.39	15.38	11.02	0.98	32.56	19.07	3.44
8000	16.11	42.51	20.82	12.83	9.84	0.95	27.94	19.07	3.30
9000	16.35	41.61	16.20	14.25	8.62	0.98	31.30	19.15	3.34
10000	16.85	40.95	14.54	22.29	7.71	1.03	30.50	19.10	37.02
11000	17.05	40.20	14.41	25.94	6.94	1.03	34.77	19.28	3.05
12000	17.12	39.60	14.90	17.74	6.35	1.01	31.10	19.28	3.07
13000	17.28	38.71	15.28	17.04	5.63	1.01	30.95	19.53	3.13
14000	17.47	37.60	16.21	22.44	4.96	1.01	30.49	19.79	3.13
15000	17.49	36.47	17.28	21.34	4.39	1.00	29.77	19.42	4.02
16000	17.23	35.67	13.92	14.77	3.94	0.99	29.08	19.44	3.44
17000	16.94	35.02	10.78	12.69	3.53	1.01	29.53	19.39	3.75
18000	16.95	34.21	10.17	13.88	3.20	1.04	29.25	19.28	4.06
19000	17.30	33.26	11.54	20.11	2.95	1.04	28.70	19.29	4.07
20000	17.56	32.59	14.55	17.41	2.76	0.98	28.30	19.38	21.60
21000	17.73	32.10	16.72	13.90	2.56	0.94	27.39	19.47	4.21
22000	18.16	31.35	18.97	17.20	2.32	0.95	27.43	19.35	4.37
23000	18.61	30.78	21.34	17.25	2.09	0.93	27.08	19.05	4.34
24000	18.94	30.28	21.71	14.77	1.89	0.91	25.76	18.55	4.45
25000	19.30	29.64	19.62	18.33	1.74	0.91	24.79	18.73	4.54
26000	18.92	29.69	11.87	11.18	1.62	0.91	24.33	18.24	4.76
27000	18.50	29.80	10.12	9.96	1.53	0.96	23.51	18.00	4.93
28000	18.79	29.18	10.59	13.04	1.54	0.97	23.97	18.14	5.14
29000	19.13	28.61	14.99	19.68	1.58	0.92	23.88	18.91	5.20
30000	19.06	28.58	17.16	16.67	1.59	0.89	23.43	18.92	13.46
32000	19.62	28.27	19.40	16.18	1.48	0.86	22.79	18.93	6.48
34000	20.42	27.98	11.60	10.16	1.18	0.82	20.68	19.00	7.08
36000	20.79	27.90	13.68	7.96	1.08	0.73	19.98	19.10	7.49
38000	20.23	28.00	17.49	7.97	1.17	0.73	19.47	18.64	8.54
40000	20.19	28.55	14.82	6.00	1.10	0.65	18.87	17.89	17.52
42000	21.00	27.11	17.87	3.86	0.75	0.43	15.94	17.77	9.59
44000	18.75	29.70	16.02	5.06	1.27	0.66	---	---	10.14
46000	18.57	31.63	32.57	16.23	2.31	0.93	---	---	9.62
48000	19.00	24.95	8.42	7.04	0.96	0.64	---	---	11.46
50000	17.23	26.50	18.73	12.58	1.51	0.85	---	---	11.62



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: [www.minicircuits.com](http://www.minicircuits.com)

IF/RF MICROWAVE COMPONENTS



REV. OR

AVA-054-D+

7/21/2022

Page 6 of 9

*Typical Performance Data***Definitions:**

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vdd = 5V, Idd = 160mA @ Temperature = +85°C

FREQ (MHz)	Gain (dB)	Isolation (dB)	Input Return Loss (dB)	Output Return Loss (dB)	Stability		IP-3 Output (dBm)	1dB Comp. Output (dBm)	Noise Figure (dB)
					K	Measure			
50	18.82	84.01	7.35	25.10	739.25	1.18	34.03	20.76	8.85
100	17.10	81.50	11.58	27.46	770.74	1.07	34.25	20.65	7.40
500	15.64	69.85	20.28	28.89	254.00	1.01	30.85	20.40	5.66
1000	15.34	63.64	18.97	22.98	127.72	1.01	30.97	20.42	5.44
2000	15.14	57.20	15.26	18.20	60.58	1.01	32.05	20.16	5.32
3000	14.98	53.40	13.13	18.14	39.05	1.03	32.47	20.12	5.37
4000	14.82	50.41	12.03	19.70	27.90	1.05	32.56	20.05	5.20
5000	14.66	47.84	11.75	21.81	21.14	1.06	33.24	20.11	4.92
6000	14.64	45.64	13.23	20.26	16.74	1.04	31.80	20.44	4.31
7000	14.65	43.83	17.10	15.20	13.68	0.99	32.18	20.19	3.97
8000	14.62	42.51	17.85	12.70	11.55	0.96	31.54	20.62	3.97
9000	14.80	41.53	14.87	14.05	10.08	0.99	31.34	20.29	3.95
10000	15.20	40.63	13.80	21.57	8.90	1.03	30.86	19.72	3.82
11000	15.39	39.92	14.24	21.76	8.07	1.03	30.53	19.73	3.68
12000	15.40	39.13	14.82	17.60	7.31	1.01	30.11	19.54	3.59
13000	15.50	38.11	14.82	17.86	6.44	1.01	29.84	19.95	3.79
14000	15.62	36.94	14.86	20.24	5.60	1.02	29.49	20.08	3.80
15000	15.60	35.80	15.25	22.04	4.97	1.02	29.04	19.91	4.70
16000	15.36	34.98	13.40	16.72	4.51	1.01	28.71	19.44	4.12
17000	15.10	34.33	11.14	14.24	4.09	1.03	28.29	19.46	4.39
18000	15.13	33.53	10.56	15.89	3.72	1.06	27.99	19.06	4.64
19000	15.42	32.68	12.12	20.49	3.44	1.04	27.62	19.01	4.73
20000	15.69	32.01	15.01	18.94	3.20	1.00	27.35	18.75	4.72
21000	15.89	31.48	16.80	17.67	2.97	0.98	26.88	18.50	4.93
22000	16.17	30.82	16.52	19.72	2.69	0.98	26.25	18.30	5.01
23000	16.45	30.30	16.45	17.61	2.45	0.97	26.40	17.48	5.11
24000	16.70	29.76	17.96	15.97	2.25	0.95	25.99	17.80	5.26
25000	16.84	29.23	15.78	18.98	2.11	0.96	25.80	17.90	5.32
26000	16.45	29.25	11.06	13.94	2.01	1.00	25.63	16.67	5.60
27000	16.07	29.30	10.52	10.97	1.95	0.99	25.66	16.83	5.91
28000	16.27	28.82	11.61	11.16	1.93	0.94	25.34	17.23	6.05
29000	16.82	28.11	17.89	19.36	1.93	0.93	25.01	17.16	5.96
30000	16.94	28.01	26.47	16.94	1.88	0.91	24.78	17.12	6.23
32000	17.35	27.79	11.90	22.25	1.70	0.97	24.73	17.21	6.86
34000	17.81	27.67	13.41	11.73	1.49	0.91	25.25	16.23	7.26
36000	17.31	28.41	17.41	8.27	1.64	0.79	24.79	16.25	7.49
38000	16.73	28.83	18.97	12.15	2.00	0.89	23.64	17.13	7.78
40000	16.87	28.76	11.89	15.84	1.96	0.95	23.61	16.36	8.29
42000	16.97	28.69	19.08	12.15	1.89	0.90	23.30	14.86	9.11
44000	14.72	31.66	14.78	7.32	2.88	0.81	---	---	9.73
46000	15.43	33.39	26.30	19.08	3.96	0.97	---	---	10.06
48000	11.96	32.35	10.47	10.44	4.46	0.97	---	---	12.00
50000	11.47	30.88	28.76	10.26	4.28	0.90	---	---	12.54

*Typical Performance Data***Definitions:**

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vdd = 5V, Idd = 150mA @ Temperature = +85°C

FREQ (MHz)	Gain (dB)	Isolation (dB)	Input Return Loss (dB)	Output Return Loss (dB)	Stability		IP-3 Output (dBm)	1dB Comp. Output (dBm)	Noise Figure (dB)
					K	Measure			
50	18.74	86.96	7.33	25.24	1046.81	1.18	34.13	20.61	8.47
100	17.00	80.07	11.58	27.69	661.38	1.07	33.19	20.48	7.09
500	15.55	70.11	20.23	29.16	264.43	1.01	32.28	20.29	5.44
1000	15.25	64.23	18.93	23.07	138.12	1.01	34.73	20.29	5.46
2000	15.04	57.66	15.21	18.27	64.60	1.02	34.51	20.04	5.32
3000	14.87	53.82	13.04	18.23	41.47	1.03	34.14	20.00	5.33
4000	14.70	50.85	11.93	19.83	29.72	1.05	33.67	19.93	5.16
5000	14.53	48.21	11.65	22.09	22.36	1.06	33.49	19.98	4.84
6000	14.50	45.94	13.11	20.59	17.60	1.04	33.20	20.31	4.22
7000	14.52	44.08	16.93	15.39	14.30	0.99	32.85	20.08	3.93
8000	14.49	42.75	17.64	12.86	12.07	0.96	32.52	20.47	3.89
9000	14.66	41.74	14.74	14.24	10.50	1.00	31.85	20.17	3.85
10000	15.05	40.86	13.70	22.02	9.30	1.04	31.29	19.62	3.77
11000	15.24	40.16	14.22	22.07	8.44	1.03	31.09	19.61	3.63
12000	15.24	39.36	14.78	17.78	7.65	1.02	30.67	19.40	3.56
13000	15.34	38.33	14.78	18.07	6.73	1.02	30.44	19.80	3.71
14000	15.45	37.16	14.85	20.53	5.86	1.02	30.15	19.92	3.70
15000	15.43	36.02	15.23	22.26	5.20	1.02	29.64	19.72	4.68
16000	15.19	35.19	13.38	16.80	4.71	1.02	29.31	19.26	4.06
17000	14.93	34.53	11.12	14.40	4.27	1.03	29.25	19.27	4.37
18000	14.97	33.72	10.56	16.17	3.87	1.06	28.71	18.85	4.63
19000	15.26	32.86	12.11	21.01	3.58	1.04	28.49	18.78	4.69
20000	15.52	32.20	14.95	19.52	3.33	1.00	28.29	18.55	4.63
21000	15.71	31.65	16.69	18.29	3.09	0.99	27.62	18.31	4.84
22000	15.98	31.01	16.24	20.49	2.81	0.99	26.93	18.13	4.97
23000	16.23	30.50	16.29	18.14	2.56	0.98	27.06	17.34	5.05
24000	16.47	29.95	17.86	16.52	2.36	0.96	26.66	17.66	5.18
25000	16.58	29.45	15.74	19.59	2.22	0.97	26.39	17.78	5.26
26000	16.18	29.46	11.15	14.14	2.12	1.00	26.21	16.60	5.57
27000	15.81	29.49	10.56	11.19	2.06	1.00	26.24	16.78	5.82
28000	16.02	29.02	11.52	11.39	2.03	0.95	26.21	17.10	6.03
29000	16.56	28.30	17.64	20.09	2.02	0.94	25.72	17.03	6.00
30000	16.69	28.18	26.33	17.50	1.97	0.92	25.23	17.04	6.11
32000	17.04	28.00	11.69	23.62	1.79	0.98	25.22	17.08	6.79
34000	17.40	27.95	13.72	11.89	1.61	0.92	25.93	16.05	7.17
36000	16.90	28.67	17.07	8.68	1.78	0.81	24.89	16.04	7.45
38000	16.35	29.04	18.08	12.88	2.14	0.91	23.84	16.92	7.71
40000	16.43	28.96	12.16	16.97	2.10	0.97	23.97	16.09	8.34
42000	16.27	29.09	19.99	12.77	2.14	0.92	23.55	14.66	9.11
44000	14.11	31.89	14.16	7.76	3.21	0.84	---	---	9.70
46000	14.70	33.62	27.35	20.12	4.43	0.98	---	---	10.07
48000	11.14	33.44	10.80	10.56	5.56	0.97	---	---	12.24
50000	10.43	31.70	29.63	10.02	5.25	0.89	---	---	12.42

*Typical Performance Data***Definitions:**

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)









Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)








TEST CONDITIONS: Vdd = 5V, Idd = 170mA @ Temperature = +85°C

FREQ (MHz)	GAIN (dB)	ISOLATION (dB)	INPUT RETURN LOSS (dB)	OUTPUT RETURN LOSS (dB)	STABILITY		IP-3 OUTPUT (dBm)	1dB COMP. OUTPUT (dBm)	NOISE FIGURE (dB)
					K	MEASURE			
50	18.92	85.03	7.33	24.86	820.83	1.18	29.74	21.05	9.38
100	17.20	79.80	11.58	27.06	626.38	1.07	30.46	20.93	7.81
500	15.75	68.92	20.33	28.39	225.32	1.01	31.52	20.67	5.58
1000	15.45	62.94	19.01	22.84	116.35	1.01	31.25	20.68	5.50
2000	15.25	56.40	15.32	18.13	54.56	1.01	32.02	20.39	5.37
3000	15.10	52.66	13.25	18.02	35.40	1.03	33.33	20.31	5.43
4000	14.96	49.86	12.15	19.49	25.81	1.05	33.18	20.19	5.20
5000	14.80	47.32	11.89	21.48	19.63	1.06	39.76	20.23	4.93
6000	14.79	45.20	13.40	19.83	15.66	1.04	31.64	20.56	4.33
7000	14.80	43.43	17.30	14.95	12.83	0.99	31.18	20.28	4.04
8000	14.77	42.16	18.09	12.52	10.89	0.96	30.81	20.72	4.04
9000	14.97	41.16	15.05	13.83	9.47	0.99	35.42	20.34	3.98
10000	15.37	40.29	13.92	20.90	8.40	1.03	28.77	19.74	3.95
11000	15.57	39.56	14.27	21.26	7.59	1.03	27.97	19.78	3.76
12000	15.58	38.76	14.76	17.24	6.85	1.01	27.46	19.63	3.71
13000	15.69	37.74	14.79	17.48	6.03	1.01	27.08	20.09	3.84
14000	15.81	36.56	14.88	19.78	5.25	1.02	26.84	20.29	3.85
15000	15.80	35.45	15.24	21.73	4.67	1.02	26.59	19.81	4.76
16000	15.56	34.64	13.34	16.52	4.24	1.01	26.20	19.29	4.17
17000	15.28	34.03	11.08	13.98	3.87	1.03	26.87	19.40	4.43
18000	15.32	33.23	10.57	15.49	3.51	1.05	26.68	18.96	4.71
19000	15.61	32.39	12.15	19.58	3.26	1.04	26.68	18.93	4.80
20000	15.87	31.75	15.02	18.14	3.04	0.99	26.87	18.69	4.77
21000	16.07	31.21	16.93	16.84	2.82	0.97	26.94	18.48	4.97
22000	16.39	30.55	16.82	18.56	2.55	0.97	26.44	18.23	5.11
23000	16.69	30.03	16.67	16.80	2.31	0.96	25.81	17.28	5.20
24000	16.97	29.48	18.00	15.16	2.11	0.94	25.22	17.62	5.34
25000	17.15	28.93	15.82	17.84	1.97	0.95	25.10	17.70	5.40
26000	16.76	28.95	10.97	13.58	1.88	0.99	24.23	16.33	5.70
27000	16.35	29.04	10.44	10.66	1.82	0.98	24.12	16.55	5.94
28000	16.54	28.61	11.62	10.75	1.81	0.93	24.29	17.05	6.06
29000	17.11	27.89	17.95	18.06	1.82	0.92	23.72	16.96	6.04
30000	17.20	27.82	26.62	15.93	1.79	0.89	22.97	16.88	6.15
32000	17.71	27.57	12.09	20.10	1.60	0.95	22.70	17.00	6.93
34000	18.30	27.35	13.09	11.19	1.36	0.89	27.31	16.14	7.29
36000	17.77	28.14	17.56	7.63	1.49	0.75	22.20	16.02	7.54
38000	17.16	28.68	20.40	11.17	1.86	0.86	21.36	16.95	7.84
40000	17.35	28.67	11.65	13.91	1.82	0.93	21.69	16.28	8.38
42000	17.88	28.28	17.77	11.12	1.62	0.87	22.01	14.70	9.16
44000	15.44	31.57	15.71	6.59	2.54	0.77	---	---	9.74
46000	16.22	33.47	24.58	16.03	3.62	0.96	---	---	9.62
48000	13.05	30.85	9.84	10.38	3.32	0.96	---	---	11.93
50000	12.92	29.79	27.58	10.63	3.26	0.89	---	---	12.29

## Typical Performance Curves



## Typical Performance Curves



**Environmental Specifications****ENV80**

All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-40° to 85° C or -40° to 105° C or -55° to 105° C Ambient Environment	Refer to Individual Model Data Sheet
Storage Environment	20° to 35° C and 40 to 60% humidity (In Factory Shipped Package)	Individual Model Data Sheet