

Surface Mount Monolithic Amplifier DC-2 GHz

Product Features

- DC-2 GHz
- Single Voltage Supply
- Internally Matched to 50 Ohms
- Unconditionally Stable
- Low Performance Variation Over Temperature
- Transient Protected
- Aqueous washable
- Protected By US Patent 6,943,629



Generic photo used for illustration purposes only

ERA-50SM+

CASE STYLE: WW107

Typical Applications

- Cellular/ PCS/ 3G Base Station
- CATV, Cable Modem & DBS
- Fixed Wireless & WLAN
- Microwave Radio & Test Equipment



+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

General Description

ERA-50SM+ (RoHS compliant) is a wideband amplifier offering high dynamic range. It has repeatable performance from lot to lot. It is enclosed in an Micro-X package. ERA-50SM+ uses Darlington configuration and is fabricated using InGaP HBT technology. Expected MTTF is 450 years at 85°C case temperature.

simplified schematic and pin description



Function	Pin Number	Description
RF IN	1	RF input pin. This pin requires the use of an external DC blocking capacitor chosen for the frequency of operation.
RF-OUT and DC-IN	3	RF output and bias pin. DC voltage is present on this pin; therefore a DC blocking capacitor is necessary for proper operation. An RF choke is needed to feed DC bias without loss of RF signal due to the bias connection, as shown in "Recommended Application Circuit".
GND	2,4	Connections to ground. Use via holes as shown in "Suggested Layout for PCB Design" to reduce ground path inductance for best performance.

Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuits's applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



Electrical Specifications at 25°C and 60mA, unless noted

Parameter		Min.	Typ.	Max.	Units	Cpk
Frequency Range*		DC		2	GHz	
Gain	f=0.1 GHz	19.5	20.7	22.5	dB	≥ 1.5
	f=1 GHz	18	19.4	21		
	f=1.5 GHz	—	18.3	20		
	f=2 GHz	16	17.6	19		
Magnitude of Gain Variation versus Temperature (values are negative)	f=0.1 GHz	—	.0015	.003	dB/°C	
	f=1 GHz	—	.0024	.005		
	f=1.5 GHz	—	.0028	.006		
	f=2 GHz	—	.0033	.007		
Input Return Loss	f=0.1 GHz		35		dB	
	f=1 GHz		24			
	f=1.5 GHz		24			
Output Return Loss	f=0.1 GHz		27		dB	
	f=1 GHz		21			
	f=1.5 GHz		19			
Reverse Isolation	f=1.5 GHz	20	23	—	dB	
Output Power @ 1 dB compression	f=0.1 GHz	—	17.6	—	dBm	≥ 1.33
	f=1 GHz	16	17.2	—		
	f=1.5 GHz	—	17.1	—		
	f=2 GHz	—	15.9	—		
Saturated Output Power (at 3dB compression)	f=0.1 GHz		19		dBm	
	f=1 GHz		18			
	f=1.5 GHz		17.5			
	f=2 GHz		16.5			
Output IP3	f=0.1 GHz	30	34	—	dBm	≥ 1.33
	f=1 GHz	29	33	—		
	f=1.5 GHz	27	31	—		
Noise Figure	f=0.1 GHz	—	3.3	4.3	dB	≥ 1.33
	f=1 GHz	—	3.3	4.3		
	f=1.5 GHz	—	3.4	4.4		
	f=2 GHz	—	3.4	—		
Group Delay	f=1 GHz		120		psec	
Recommended Device Operating Current			60		mA	
Device Operating Voltage		4.2	4.4	4.6	V	≥ 1.5
Device Voltage Variation vs. Temperature at 60mA			-3.2		mV/°C	
Device Voltage Variation vs. Current at 25°C			3.8		mV/mA	
Thermal Resistance, junction-to-case ¹			177		°C/W	

*Guaranteed specification DC-2 GHz. Low frequency cut off determined by external coupling capacitors.

Absolute Maximum Ratings

Parameter	Ratings
Operating Temperature*	-45°C to 85°C
Storage Temperature	-65°C to 150°C
Operating Current	85mA
Power Dissipation	451mW
Input Power	13dBm

Note: Permanent damage may occur if any of these limits are exceeded.

These ratings are not intended for continuous normal operation.

¹Case is defined as ground leads.


*Based on typical case temperature rise 5°C above ambient.

Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



Product Marking



Markings in addition to model number designation may appear for internal quality control purposes.

Additional Detailed Technical Information

Additional information is available on our web site. To access this information enter the model number on our web site home page.

Performance data, graphs, s-parameter data set (.zip file)

Case Style: WW107

Plastic micro-x, .085 body diameter, lead finish: Matte-Tin

Tape & Reel: F4


7" Reels with 20, 50, 100, 200, 500, 1K devices

Suggested Layout for PCB Design: PL-075

Evaluation Board: TB-408-50+

Environmental Ratings: ENV08T2

Recommended Application Circuit



Test Board includes case, connectors, and components (in bold) soldered to PCB

R BIAS	
Vcc	"1%" Res. Values (ohms) for Optimum Biasing
7	40.2
8	53.6
9	68.1
10	82.5
11	97.6
12	113
13	127
14	143
15	158
16	174
17	191
18	205
19	221
20	237

Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

ESD Rating


Human Body Model (HBM): Class 1B (500 v to < 1000 v) in accordance with ANSI/ESD STM 5.1 - 2001

Machine Model (MM): Class M1 (< 100 v) in accordance with ANSI/ESD STM 5.2 - 1999

MSL Rating

Moisture Sensitivity: MSL1 in accordance with IPC/JEDECJ-STD-020C

No.	Test Required	Condition	Standard	Quantity
1	Visual Inspection	Low Power Microscope Magnification 40x	MIP-IN-0003 (MCT spec)	45 units
2	Electrical Test	Room Temperature	SCD (MCL spec)	45 units
3	SAM Analysis	Less than 10% growth in term of delamination	J-Std-020C (Jedec Standard)	45 units
4	Moisture Sensitivity Level 1	Bake at 125°C for 24 hours Soak at 85°C/85%RH for 168 hours Reflow 3 cycles at 260°C peak	J-Std-020C (Jedec Standard)	45 units

MSL Test Flow Chart**Notes**

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



Typical Performance Data

**NOTE: Use PDF Bookmarks to view DATA at required conditions
or to view GRAPHS.**

Definitions:

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: I_{cc} = 60mA, V_d = 4.40V @ Temperature = +25degC

FREQ	Gain	Isolation	Input Return Loss	Output Return Loss	Stability		IP3 Output	1dB Comp. Output	Noise Figure
(MHz)	(dB)	(dB)	(dB)	(dB)	K	Delta	(dBm)	(dBm)	(dB)
50	21.58	24.27	43.71	26.95	1.05	0.73	33.74	18.37	3.29
100	21.52	24.32	42.45	26.66	1.05	0.72	33.71	18.36	3.39
150	21.48	24.30	39.93	26.49	1.05	0.72	34.32	18.50	3.38
200	21.45	24.29	37.13	26.36	1.05	0.72	33.90	18.46	3.36
250	21.40	24.28	35.22	26.08	1.05	0.72	32.92	18.40	3.43
300	21.34	24.30	34.46	25.88	1.06	0.71	33.80	18.34	3.47
350	21.28	24.24	33.15	25.58	1.06	0.71	33.47	18.34	3.40
400	21.21	24.24	32.37	25.23	1.06	0.71	33.41	18.33	3.39
450	21.15	24.24	31.13	24.97	1.06	0.70	32.83	18.17	3.42
500	21.07	24.21	30.42	24.59	1.06	0.70	33.11	18.21	3.35
550	20.99	24.20	29.81	24.26	1.07	0.69	32.90	18.24	3.40
600	20.90	24.18	29.26	23.94	1.07	0.69	32.87	18.24	3.42
650	20.82	24.15	28.59	23.69	1.07	0.68	32.63	18.15	3.33
700	20.73	24.13	28.11	23.32	1.07	0.68	32.85	17.97	3.42
750	20.63	24.11	27.72	23.04	1.08	0.67	32.75	18.04	3.44
800	20.54	24.07	27.34	22.74	1.08	0.67	32.79	17.88	3.38
850	20.44	24.05	26.99	22.43	1.08	0.66	32.67	17.85	3.42
900	20.33	24.04	26.58	22.16	1.09	0.65	32.61	17.78	3.42
940	20.25	24.02	26.48	21.91	1.09	0.65	32.60	17.80	3.33
1000	20.12	23.97	26.17	21.63	1.09	0.64	32.35	17.69	3.34
1050	20.01	23.94	25.88	21.36	1.10	0.64	32.31	17.63	3.38
1100	19.90	23.91	25.64	21.10	1.10	0.63	32.07	17.73	3.45
1150	19.79	23.87	25.48	20.89	1.10	0.63	31.90	17.62	3.43
1200	19.67	23.85	25.37	20.67	1.11	0.62	31.88	17.61	3.40
1250	19.56	23.80	25.20	20.46	1.11	0.61	31.96	17.54	3.44
1300	19.45	23.76	25.20	20.23	1.12	0.61	31.65	17.66	3.53
1350	19.33	23.73	25.15	19.97	1.12	0.60	31.38	17.60	3.46
1400	19.22	23.69	25.29	19.80	1.12	0.60	31.11	17.51	3.40
1450	19.10	23.65	25.28	19.55	1.13	0.59	31.31	17.45	3.40
1500	18.99	23.61	25.25	19.39	1.13	0.59	31.30	17.45	3.42
1550	18.87	23.57	25.24	19.17	1.14	0.58	31.51	17.36	3.47
1600	18.76	23.52	25.25	19.02	1.14	0.58	31.44	17.23	3.41
1650	18.63	23.49	25.14	18.91	1.15	0.57	31.47	17.17	3.40
1700	18.52	23.44	25.21	18.67	1.15	0.57	31.59	17.14	3.51
1750	18.40	23.39	25.28	18.56	1.15	0.56	31.07	17.03	3.43
1800	18.28	23.34	25.42	18.39	1.16	0.56	31.00	16.85	3.51
1850	18.17	23.29	25.48	18.24	1.16	0.55	30.17	16.91	3.43
1900	18.06	23.22	25.43	18.12	1.16	0.55	30.41	16.75	3.41
1950	17.94	23.18	25.62	17.96	1.17	0.54	30.04	16.42	3.36
2000	17.83	23.12	25.58	17.82	1.17	0.54	30.32	16.46	3.39

REV. X1
ERA-50SM+
070821
Page 1 of 11



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED RoHS compliant
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see



*Typical Performance Data***Definitions:**

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Icc = 48mA, Vd = 4.35V @ Temperature = +25degC

FREQ (MHz)	Gain (dB)	Isolation (dB)	Input Return Loss (dB)	Output Return Loss (dB)	Stability		IP3 Output (dBm)	1dB Comp. Output (dBm)	Noise Figure (dB)
					K	Delta			
50	21.34	24.06	33.44	33.97	1.05	0.73	30.42	16.63	3.21
100	21.27	24.07	33.60	32.73	1.05	0.72	30.41	16.30	3.30
150	21.25	24.09	33.08	32.80	1.05	0.72	30.92	16.62	3.28
200	21.21	24.05	32.46	31.95	1.05	0.72	30.66	16.53	3.29
250	21.16	24.07	31.88	31.17	1.06	0.72	29.84	16.42	3.34
300	21.11	24.06	31.70	30.55	1.06	0.71	30.71	16.30	3.40
350	21.05	24.04	30.72	29.83	1.06	0.71	30.34	16.33	3.30
400	20.99	24.03	30.49	29.18	1.06	0.70	30.41	16.43	3.30
450	20.92	24.01	29.65	28.39	1.06	0.70	29.81	16.02	3.31
500	20.85	24.02	29.35	27.79	1.07	0.69	30.24	16.19	3.29
550	20.77	23.99	28.88	27.12	1.07	0.69	30.00	16.21	3.36
600	20.69	23.98	28.46	26.59	1.07	0.68	30.08	16.27	3.34
650	20.60	23.95	27.93	26.14	1.07	0.68	29.88	16.13	3.28
700	20.52	23.94	27.58	25.55	1.08	0.67	30.11	15.82	3.35
750	20.43	23.89	27.29	25.11	1.08	0.67	30.08	16.20	3.35
800	20.33	23.88	26.97	24.70	1.08	0.66	30.19	15.78	3.30
850	20.24	23.87	26.69	24.23	1.08	0.66	30.19	15.78	3.33
900	20.14	23.83	26.31	23.84	1.09	0.65	30.10	15.71	3.28
940	20.06	23.81	26.24	23.48	1.09	0.65	30.28	15.74	3.27
1000	19.93	23.78	25.89	23.05	1.09	0.64	29.97	15.64	3.26
1050	19.83	23.76	25.65	22.72	1.10	0.64	30.31	15.46	3.33
1100	19.72	23.72	25.41	22.35	1.10	0.63	29.88	15.87	3.38
1150	19.61	23.68	25.22	22.05	1.10	0.63	29.98	15.55	3.32
1200	19.50	23.67	25.10	21.77	1.11	0.62	29.80	15.68	3.33
1250	19.39	23.61	24.93	21.46	1.11	0.61	30.10	15.48	3.35
1300	19.28	23.59	24.93	21.21	1.12	0.61	29.88	15.80	3.40
1350	19.17	23.55	24.87	20.87	1.12	0.60	29.67	15.70	3.37
1400	19.06	23.50	24.94	20.64	1.12	0.60	29.42	15.60	3.34
1450	18.95	23.48	24.92	20.34	1.13	0.59	29.59	15.56	3.30
1500	18.83	23.44	24.87	20.13	1.13	0.59	29.71	15.65	3.35
1550	18.71	23.40	24.82	19.89	1.14	0.58	29.91	15.53	3.36
1600	18.60	23.36	24.69	19.69	1.14	0.58	29.93	15.52	3.34
1650	18.49	23.31	24.61	19.53	1.14	0.57	29.99	15.43	3.32
1700	18.37	23.28	24.65	19.26	1.15	0.57	30.28	15.61	3.44
1750	18.26	23.22	24.67	19.12	1.15	0.56	29.91	15.38	3.35
1800	18.14	23.18	24.75	18.92	1.16	0.56	29.82	15.48	3.44
1850	18.03	23.15	24.72	18.74	1.16	0.55	29.11	15.41	3.36
1900	17.92	23.10	24.62	18.59	1.16	0.55	29.21	15.46	3.31
1950	17.81	23.04	24.76	18.41	1.17	0.54	29.09	15.21	3.26
2000	17.70	23.01	24.63	18.24	1.17	0.54	29.22	15.18	3.29

REV. X1

ERA-50SM+

070821

Page 2 of 11



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED RoHS compliant
 P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see



*Typical Performance Data***Definitions:**

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: I_{cc} = 72mA, V_d = 4.44V @ Temperature = +25degC

FREQ (MHz)	Gain (dB)	Isolation (dB)	Input Return Loss (dB)	Output Return Loss (dB)	Stability		IP3 Output (dBm)	1dB Comp. Output (dBm)	Noise Figure (dB)
					K	Delta			
50	21.73	24.43	35.28	24.37	1.05	0.73	36.12	19.49	3.36
100	21.67	24.48	34.69	23.95	1.05	0.72	36.11	19.67	3.43
150	21.63	24.42	34.23	23.93	1.05	0.73	36.83	19.72	3.44
200	21.59	24.44	33.37	23.87	1.05	0.72	36.19	19.67	3.43
250	21.55	24.38	32.38	23.71	1.05	0.72	35.13	19.68	3.48
300	21.49	24.40	31.97	23.60	1.05	0.72	35.90	19.55	3.51
350	21.43	24.40	31.24	23.42	1.06	0.71	35.60	19.53	3.43
400	21.36	24.39	30.83	23.24	1.06	0.71	35.42	19.47	3.46
450	21.29	24.38	29.83	23.07	1.06	0.70	34.87	19.43	3.46
500	21.21	24.35	29.26	22.79	1.06	0.70	34.95	19.40	3.45
550	21.13	24.35	28.81	22.61	1.07	0.69	34.79	19.42	3.46
600	21.04	24.32	28.30	22.39	1.07	0.69	34.62	19.39	3.48
650	20.95	24.32	27.83	22.20	1.07	0.68	34.36	19.28	3.45
700	20.86	24.28	27.40	21.94	1.07	0.68	34.49	19.20	3.47
750	20.76	24.24	27.07	21.73	1.08	0.67	34.29	19.10	3.50
800	20.66	24.22	26.76	21.50	1.08	0.67	34.27	19.09	3.44
850	20.57	24.19	26.48	21.26	1.08	0.66	34.04	18.96	3.49
900	20.46	24.17	26.11	21.07	1.09	0.65	33.97	18.91	3.49
940	20.37	24.14	26.01	20.88	1.09	0.65	33.79	18.92	3.43
1000	20.24	24.11	25.80	20.66	1.09	0.64	33.59	18.81	3.38
1050	20.13	24.07	25.55	20.44	1.10	0.64	33.31	18.78	3.42
1100	20.02	24.03	25.35	20.25	1.10	0.63	33.19	18.68	3.50
1150	19.91	24.00	25.22	20.09	1.10	0.62	32.82	18.73	3.53
1200	19.79	23.98	25.13	19.92	1.11	0.62	32.92	18.56	3.44
1250	19.67	23.93	25.00	19.75	1.11	0.61	32.83	18.63	3.48
1300	19.56	23.88	25.00	19.55	1.12	0.61	32.52	18.58	3.59
1350	19.44	23.85	24.99	19.36	1.12	0.60	32.19	18.51	3.53
1400	19.33	23.80	25.19	19.21	1.12	0.60	31.97	18.42	3.47
1450	19.21	23.76	25.21	18.99	1.13	0.59	32.16	18.31	3.44
1500	19.09	23.73	25.19	18.85	1.13	0.59	32.08	18.22	3.49
1550	18.97	23.68	25.23	18.67	1.14	0.58	32.25	18.16	3.53
1600	18.86	23.64	25.30	18.53	1.14	0.58	32.13	17.92	3.52
1650	18.73	23.60	25.23	18.46	1.15	0.57	32.15	17.93	3.48
1700	18.62	23.54	25.33	18.24	1.15	0.57	32.14	17.75	3.63
1750	18.50	23.49	25.48	18.16	1.15	0.56	31.61	17.76	3.49
1800	18.38	23.46	25.65	18.02	1.16	0.56	31.55	17.44	3.58
1850	18.27	23.38	25.75	17.90	1.16	0.55	30.73	17.57	3.51
1900	18.15	23.33	25.76	17.77	1.16	0.55	31.03	17.33	3.50
1950	18.04	23.26	26.00	17.65	1.17	0.55	30.53	17.05	3.43
2000	17.93	23.24	26.10	17.52	1.17	0.54	30.91	17.10	3.46

REV. X1

ERA-50SM+

070821

Page 3 of 11



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED RoHS compliant
 P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see



*Typical Performance Data***Definitions:**

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Icc = 60mA, Vd = 4.64V @ Temperature = -45degC

FREQ (MHz)	Gain (dB)	Isolation (dB)	Input Return Loss (dB)	Output Return Loss (dB)	Stability		IP3 Output (dBm)	1dB Comp. Output (dBm)	Noise Figure (dB)
					K	Delta			
50	21.65	24.27	45.11	26.98	1.04	0.74	34.51	18.56	2.89
100	21.60	24.33	42.03	27.16	1.05	0.73	34.46	18.55	2.92
150	21.57	24.31	39.64	27.37	1.05	0.73	35.04	18.71	2.93
200	21.53	24.32	36.45	27.34	1.05	0.73	34.64	18.62	2.92
250	21.49	24.25	34.86	26.80	1.05	0.73	33.74	18.58	2.95
300	21.44	24.28	34.21	26.29	1.05	0.72	34.60	18.53	3.01
350	21.39	24.28	33.19	25.80	1.05	0.72	34.25	18.53	2.89
400	21.32	24.25	32.49	25.46	1.06	0.71	34.26	18.56	2.93
450	21.25	24.22	31.16	25.27	1.06	0.71	33.70	18.34	2.91
500	21.18	24.21	30.34	24.87	1.06	0.71	34.04	18.41	2.88
550	21.11	24.18	29.56	24.61	1.06	0.70	33.85	18.41	2.94
600	21.02	24.17	28.86	24.27	1.06	0.70	33.86	18.45	2.93
650	20.94	24.15	28.21	23.98	1.07	0.69	33.64	18.35	2.87
700	20.86	24.13	27.70	23.55	1.07	0.69	33.88	18.14	2.93
750	20.76	24.10	27.39	23.20	1.07	0.68	33.79	18.31	2.94
800	20.67	24.07	26.84	22.95	1.07	0.68	33.89	18.05	2.90
850	20.58	24.05	26.64	22.54	1.08	0.67	33.77	18.06	2.95
900	20.47	24.04	26.31	22.22	1.08	0.66	33.74	17.96	2.90
940	20.39	24.00	26.14	21.94	1.08	0.66	33.76	17.99	2.81
1000	20.27	23.96	25.75	21.66	1.09	0.65	33.51	17.91	2.84
1050	20.17	23.93	25.46	21.39	1.09	0.65	33.58	17.78	2.87
1100	20.05	23.89	25.28	21.13	1.09	0.64	33.33	18.00	2.95
1150	19.95	23.86	25.20	20.93	1.10	0.64	33.23	17.81	2.92
1200	19.84	23.83	25.22	20.73	1.10	0.63	33.20	17.89	2.88
1250	19.73	23.77	25.16	20.49	1.10	0.63	33.36	17.77	2.94
1300	19.62	23.75	25.06	20.29	1.11	0.62	33.06	17.96	3.00
1350	19.50	23.71	24.94	19.99	1.11	0.62	32.81	17.88	2.94
1400	19.40	23.67	24.93	19.73	1.11	0.61	32.58	17.82	2.92
1450	19.28	23.63	24.87	19.42	1.12	0.61	32.79	17.76	2.87
1500	19.18	23.58	25.00	19.06	1.12	0.60	32.84	17.80	2.93
1550	19.05	23.56	24.78	19.01	1.12	0.59	33.02	17.72	2.93
1600	18.94	23.49	25.09	18.82	1.13	0.59	32.96	17.68	2.89
1650	18.83	23.47	25.15	18.70	1.13	0.59	33.02	17.59	2.87
1700	18.71	23.41	25.21	18.55	1.13	0.58	33.23	17.65	3.01
1750	18.60	23.34	25.25	18.43	1.14	0.58	32.71	17.52	2.90
1800	18.49	23.31	25.35	18.23	1.14	0.57	32.59	17.48	3.01
1850	18.37	23.26	25.34	18.09	1.15	0.57	31.81	17.46	2.89
1900	18.26	23.22	25.34	17.92	1.15	0.56	32.10	17.38	2.91
1950	18.16	23.17	25.73	17.73	1.15	0.56	31.74	17.12	2.84
2000	18.04	23.11	25.58	17.75	1.16	0.56	32.04	17.11	2.84

REV. X1

ERA-50SM+

070821

Page 4 of 11



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED RoHS compliant
 P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see



*Typical Performance Data***Definitions:**

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Icc = 48mA, Vd = 4.59V @ Temperature = -45degC

FREQ (MHz)	Gain (dB)	Isolation (dB)	Input Return Loss (dB)	Output Return Loss (dB)	Stability		IP3 Output (dBm)	1dB Comp. Output (dBm)	Noise Figure (dB)
					K	Delta			
50	21.44	24.19	33.12	32.92	1.05	0.73	31.14	16.63	2.84
100	21.38	24.13	32.65	32.81	1.05	0.73	31.05	16.25	2.86
150	21.36	24.14	31.75	33.25	1.05	0.73	31.54	16.62	2.87
200	21.33	24.11	31.30	32.70	1.05	0.73	31.25	16.52	2.87
250	21.29	24.09	31.08	31.49	1.05	0.72	30.48	16.39	2.91
300	21.24	24.07	31.11	30.66	1.05	0.72	31.34	16.30	2.95
350	21.18	24.09	30.74	29.66	1.05	0.72	30.97	16.32	2.87
400	21.13	24.08	30.40	28.93	1.06	0.71	31.08	16.46	2.87
450	21.06	24.06	29.55	28.39	1.06	0.71	30.48	16.01	2.87
500	20.99	24.02	29.00	27.72	1.06	0.70	30.97	16.19	2.85
550	20.92	24.03	28.48	27.23	1.06	0.70	30.73	16.19	2.88
600	20.84	24.00	28.09	26.62	1.06	0.70	30.84	16.28	2.88
650	20.76	23.98	27.50	26.16	1.07	0.69	30.65	16.15	2.85
700	20.67	23.95	27.21	25.57	1.07	0.69	30.89	15.85	2.86
750	20.58	23.92	27.03	25.11	1.07	0.68	30.89	16.23	2.87
800	20.49	23.91	26.55	24.74	1.07	0.67	30.99	15.80	2.85
850	20.40	23.89	26.43	24.21	1.08	0.67	31.02	15.83	2.85
900	20.31	23.86	26.11	23.78	1.08	0.66	30.94	15.75	2.82
940	20.23	23.84	26.04	23.39	1.08	0.66	31.17	15.76	2.77
1000	20.10	23.79	25.61	22.96	1.09	0.65	30.85	15.69	2.80
1050	20.01	23.77	25.37	22.61	1.09	0.65	31.28	15.53	2.82
1100	19.90	23.74	25.23	22.29	1.09	0.64	30.80	15.94	2.89
1150	19.79	23.70	25.18	22.01	1.10	0.64	31.02	15.61	2.88
1200	19.68	23.68	25.14	21.78	1.10	0.63	30.83	15.77	2.84
1250	19.58	23.63	25.08	21.48	1.10	0.63	31.21	15.57	2.88
1300	19.47	23.61	24.98	21.23	1.11	0.62	30.98	15.89	2.95
1350	19.36	23.57	24.85	20.84	1.11	0.62	30.82	15.81	2.90
1400	19.25	23.51	24.86	20.54	1.11	0.61	30.62	15.72	2.89
1450	19.14	23.47	24.79	20.16	1.12	0.61	30.77	15.67	2.84
1500	19.04	23.44	25.01	19.74	1.12	0.60	30.98	15.80	2.83
1550	18.91	23.42	24.78	19.66	1.13	0.59	31.15	15.69	2.87
1600	18.80	23.36	24.97	19.43	1.13	0.59	31.20	15.72	2.82
1650	18.70	23.32	24.99	19.29	1.13	0.59	31.27	15.63	2.83
1700	18.58	23.28	25.03	19.12	1.13	0.58	31.67	15.86	2.99
1750	18.48	23.21	25.00	18.96	1.14	0.58	31.33	15.69	2.86
1800	18.36	23.17	25.09	18.72	1.14	0.57	31.24	15.84	2.92
1850	18.25	23.14	25.01	18.58	1.15	0.57	30.57	15.71	2.87
1900	18.14	23.09	24.93	18.37	1.15	0.56	30.68	15.83	2.82
1950	18.04	23.04	25.32	18.15	1.15	0.56	30.68	15.65	2.80
2000	17.92	22.98	25.06	18.14	1.15	0.56	30.76	15.60	2.80

REV. X1

ERA-50SM+

070821

Page 5 of 11



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED RoHS compliant
 P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see



*Typical Performance Data***Definitions:**

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Icc = 72mA, Vd = 4.68V @ Temperature = -45degC

FREQ (MHz)	Gain (dB)	Isolation (dB)	Input Return Loss (dB)	Output Return Loss (dB)	Stability		IP3 Output (dBm)	1dB Comp. Output (dBm)	Noise Figure (dB)
					K	Delta			
50	21.79	24.42	38.04	24.68	1.04	0.74	37.03	19.85	2.93
100	21.73	24.47	38.45	24.65	1.05	0.73	36.99	19.93	3.00
150	21.70	24.46	37.76	24.94	1.05	0.73	37.72	20.02	2.98
200	21.67	24.43	35.79	24.82	1.05	0.73	37.11	19.98	2.95
250	21.63	24.42	33.97	24.52	1.05	0.73	36.08	19.94	2.99
300	21.57	24.42	33.14	24.15	1.05	0.72	36.89	19.88	3.07
350	21.51	24.41	32.12	23.80	1.05	0.72	36.57	19.87	2.94
400	21.45	24.37	31.67	23.61	1.05	0.72	36.48	19.82	2.98
450	21.38	24.37	30.50	23.46	1.06	0.71	35.96	19.73	2.96
500	21.31	24.34	29.71	23.20	1.06	0.71	36.10	19.73	2.95
550	21.23	24.30	29.09	23.01	1.06	0.70	35.95	19.74	2.97
600	21.15	24.28	28.40	22.77	1.06	0.70	35.81	19.73	2.97
650	21.06	24.28	27.78	22.59	1.07	0.69	35.60	19.64	2.92
700	20.98	24.25	27.30	22.25	1.07	0.69	35.76	19.53	2.96
750	20.88	24.23	26.92	22.01	1.07	0.68	35.59	19.48	2.98
800	20.78	24.20	26.43	21.79	1.07	0.68	35.58	19.41	2.92
850	20.69	24.18	26.28	21.46	1.08	0.67	35.38	19.35	2.99
900	20.59	24.14	25.92	21.22	1.08	0.67	35.36	19.28	2.95
940	20.50	24.13	25.76	20.97	1.08	0.66	35.19	19.28	2.88
1000	20.38	24.08	25.43	20.75	1.09	0.65	35.01	19.20	2.88
1050	20.27	24.04	25.16	20.56	1.09	0.65	34.75	19.16	2.92
1100	20.16	24.00	25.00	20.34	1.09	0.64	34.68	19.15	2.98
1150	20.05	23.97	24.91	20.17	1.09	0.64	34.34	19.13	2.97
1200	19.94	23.93	24.97	20.00	1.10	0.63	34.48	19.07	2.92
1250	19.83	23.88	24.91	19.81	1.10	0.63	34.40	19.08	2.97
1300	19.71	23.86	24.84	19.64	1.11	0.62	34.09	19.10	3.04
1350	19.60	23.82	24.75	19.39	1.11	0.62	33.79	19.05	3.00
1400	19.49	23.77	24.74	19.17	1.11	0.61	33.60	18.98	2.96
1450	19.38	23.73	24.66	18.90	1.12	0.61	33.84	18.91	2.93
1500	19.28	23.68	24.75	18.58	1.12	0.60	33.75	18.86	2.96
1550	19.14	23.64	24.57	18.54	1.12	0.60	33.92	18.80	2.98
1600	19.03	23.60	24.96	18.37	1.13	0.59	33.80	18.62	2.92
1650	18.92	23.54	25.02	18.28	1.13	0.59	33.83	18.61	2.94
1700	18.81	23.51	25.14	18.14	1.13	0.58	33.88	18.48	3.08
1750	18.70	23.43	25.29	18.05	1.14	0.58	33.36	18.47	2.94
1800	18.58	23.40	25.41	17.87	1.14	0.57	33.21	18.19	3.04
1850	18.46	23.35	25.39	17.76	1.14	0.57	32.43	18.31	2.94
1900	18.35	23.31	25.36	17.59	1.15	0.56	32.84	18.08	2.93
1950	18.25	23.24	25.84	17.44	1.15	0.56	32.29	17.81	2.91
2000	18.13	23.16	25.77	17.45	1.15	0.56	32.72	17.85	2.93

REV. X1
ERA-50SM+
070821
Page 6 of 11



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED RoHS compliant
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

 Mouser Electronics Patent Pending The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see minicircuits.com

*Typical Performance Data***Definitions:**

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Icc = 60mA, Vd = 4.23V @ Temperature = +85degC

FREQ (MHz)	Gain (dB)	Isolation (dB)	Input Return Loss (dB)	Output Return Loss (dB)	Stability		IP3 Output (dBm)	1dB Comp. Output (dBm)	Noise Figure (dB)
					K	Delta			
50	21.48	24.22	42.82	27.97	1.05	0.73	33.23	18.22	3.67
100	21.41	24.24	40.57	27.07	1.05	0.72	33.20	18.23	3.74
150	21.37	24.23	38.88	26.66	1.05	0.72	33.84	18.34	3.75
200	21.33	24.23	36.51	26.31	1.05	0.72	33.41	18.34	3.74
250	21.28	24.23	34.96	26.10	1.06	0.71	32.39	18.26	3.79
300	21.23	24.18	34.29	25.86	1.06	0.71	33.23	18.17	3.83
350	21.16	24.23	33.09	25.73	1.06	0.70	32.88	18.17	3.78
400	21.09	24.17	32.57	25.52	1.06	0.70	32.80	18.14	3.81
450	21.02	24.16	31.07	25.29	1.06	0.70	32.21	18.02	3.79
500	20.94	24.16	30.33	24.95	1.07	0.69	32.45	18.05	3.78
550	20.86	24.15	29.73	24.56	1.07	0.69	32.25	18.07	3.83
600	20.77	24.14	29.21	24.29	1.07	0.68	32.18	18.06	3.82
650	20.68	24.12	28.62	23.98	1.08	0.67	31.94	17.94	3.78
700	20.59	24.08	28.14	23.57	1.08	0.67	32.11	17.83	3.84
750	20.49	24.04	27.77	23.26	1.08	0.66	31.97	17.84	3.84
800	20.38	24.03	27.24	23.07	1.08	0.66	32.00	17.72	3.79
850	20.29	24.01	26.87	22.73	1.09	0.65	31.86	17.63	3.83
900	20.18	24.00	26.48	22.53	1.09	0.64	31.77	17.59	3.84
940	20.09	23.97	26.31	22.27	1.10	0.64	31.72	17.62	3.77
1000	19.96	23.93	25.94	22.00	1.10	0.63	31.45	17.50	3.80
1050	19.85	23.92	25.70	21.73	1.10	0.63	31.39	17.44	3.79
1100	19.74	23.88	25.54	21.37	1.11	0.62	31.16	17.46	3.87
1150	19.62	23.84	25.33	21.18	1.11	0.62	30.93	17.43	3.88
1200	19.50	23.81	25.19	20.94	1.12	0.61	30.91	17.33	3.79
1250	19.39	23.76	24.99	20.68	1.12	0.60	30.94	17.33	3.84
1300	19.27	23.73	24.82	20.48	1.12	0.60	30.65	17.39	3.95
1350	19.15	23.68	24.73	20.19	1.13	0.59	30.33	17.32	3.87
1400	19.03	23.65	24.76	20.03	1.13	0.59	30.09	17.21	3.85
1450	18.92	23.62	24.75	19.76	1.14	0.58	30.25	17.14	3.80
1500	18.81	23.58	24.92	19.45	1.14	0.58	30.21	17.10	3.87
1550	18.67	23.53	24.59	19.45	1.15	0.57	30.42	16.98	3.89
1600	18.56	23.51	24.55	19.26	1.15	0.56	30.39	16.76	3.89
1650	18.43	23.46	24.43	19.07	1.16	0.56	30.40	16.74	3.81
1700	18.32	23.42	24.41	18.87	1.16	0.55	30.47	16.65	3.99
1750	18.20	23.36	24.36	18.73	1.16	0.55	29.94	16.56	3.88
1800	18.08	23.33	24.43	18.54	1.17	0.54	29.86	16.31	3.95
1850	17.96	23.28	24.35	18.42	1.17	0.54	29.06	16.40	3.86
1900	17.85	23.22	24.37	18.22	1.18	0.54	29.26	16.22	3.87
1950	17.73	23.17	24.76	18.03	1.18	0.53	28.89	15.86	3.82
2000	17.61	23.09	24.33	18.00	1.18	0.53	29.16	15.88	3.85

REV. X1

ERA-50SM+

070821

Page 7 of 11



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED RoHS compliant
 P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see



*Typical Performance Data***Definitions:**

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Icc = 48mA, Vd = 4.18V @ Temperature = +85degC

FREQ (MHz)	Gain (dB)	Isolation (dB)	Input Return Loss (dB)	Output Return Loss (dB)	Stability		IP3 Output (dBm)	1dB Comp. Output (dBm)	Noise Figure (dB)
					K	Delta			
50	21.21	24.01	31.72	37.18	1.05	0.72	30.19	16.61	3.65
100	21.15	23.97	32.46	34.84	1.05	0.72	30.15	16.32	3.69
150	21.12	24.00	32.78	33.63	1.05	0.72	30.68	16.62	3.69
200	21.08	24.01	32.43	32.72	1.06	0.71	30.39	16.57	3.69
250	21.03	23.98	32.03	31.63	1.06	0.71	29.47	16.44	3.73
300	20.97	23.97	31.47	30.95	1.06	0.71	30.35	16.38	3.78
350	20.91	23.94	30.46	30.38	1.06	0.71	29.98	16.41	3.74
400	20.84	23.94	29.92	29.51	1.06	0.70	30.01	16.47	3.73
450	20.77	23.95	29.05	28.94	1.07	0.69	29.38	16.15	3.73
500	20.70	23.91	28.67	28.17	1.07	0.69	29.78	16.24	3.75
550	20.62	23.89	28.25	27.58	1.07	0.69	29.55	16.30	3.77
600	20.54	23.87	27.92	26.98	1.07	0.68	29.59	16.34	3.78
650	20.45	23.88	27.46	26.39	1.08	0.67	29.40	16.18	3.74
700	20.36	23.85	27.06	25.81	1.08	0.67	29.60	15.94	3.77
750	20.27	23.84	26.83	25.32	1.08	0.66	29.55	16.22	3.78
800	20.17	23.81	26.37	24.98	1.09	0.66	29.62	15.85	3.76
850	20.07	23.78	26.00	24.46	1.09	0.65	29.60	15.80	3.79
900	19.97	23.78	25.62	24.14	1.09	0.64	29.51	15.77	3.76
940	19.89	23.75	25.54	23.79	1.09	0.64	29.65	15.79	3.70
1000	19.75	23.73	25.14	23.37	1.10	0.63	29.34	15.69	3.71
1050	19.65	23.68	24.94	22.98	1.10	0.63	29.59	15.53	3.76
1100	19.54	23.66	24.77	22.54	1.11	0.62	29.19	15.88	3.80
1150	19.43	23.65	24.60	22.30	1.11	0.61	29.23	15.60	3.81
1200	19.31	23.61	24.44	21.95	1.12	0.61	29.08	15.67	3.73
1250	19.20	23.57	24.23	21.62	1.12	0.60	29.30	15.50	3.80
1300	19.09	23.54	24.11	21.37	1.12	0.60	29.06	15.80	3.87
1350	18.97	23.50	23.97	21.00	1.13	0.59	28.83	15.70	3.84
1400	18.86	23.47	23.99	20.80	1.13	0.59	28.58	15.58	3.80
1450	18.74	23.43	23.92	20.47	1.14	0.58	28.72	15.52	3.75
1500	18.64	23.40	24.06	20.13	1.14	0.58	28.81	15.62	3.82
1550	18.50	23.37	23.71	20.11	1.15	0.57	29.04	15.47	3.85
1600	18.39	23.30	23.61	19.83	1.15	0.57	29.06	15.40	3.80
1650	18.28	23.28	23.50	19.63	1.15	0.56	29.11	15.32	3.75
1700	18.15	23.26	23.44	19.36	1.16	0.55	29.32	15.45	3.91
1750	18.04	23.18	23.34	19.20	1.16	0.55	28.91	15.23	3.86
1800	17.92	23.15	23.42	19.00	1.17	0.54	28.82	15.21	3.91
1850	17.81	23.08	23.35	18.85	1.17	0.54	28.09	15.20	3.84
1900	17.70	23.06	23.27	18.63	1.18	0.54	28.19	15.18	3.76
1950	17.58	23.01	23.53	18.39	1.18	0.53	28.00	14.84	3.73
2000	17.46	22.93	23.12	18.38	1.18	0.53	28.16	14.84	3.81

*Typical Performance Data***Definitions:**

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)


Output Return Loss = -S22 (dB)

TEST CONDITIONS: Icc = 72mA, Vd = 4.27V @ Temperature = +85degC


FREQ (MHz)	Gain (dB)	Isolation (dB)	Input Return Loss (dB)	Output Return Loss (dB)	Stability		IP3 Output (dBm)	1dB Comp. Output (dBm)	Noise Figure (dB)
					K	Delta			
50	21.64	24.36	35.65	24.62	1.05	0.73	35.70	19.30	3.78
100	21.57	24.41	34.22	24.13	1.05	0.72	35.75	19.46	3.82
150	21.53	24.45	33.03	23.90	1.05	0.72	36.52	19.46	3.82
200	21.49	24.34	32.09	23.72	1.05	0.72	35.81	19.47	3.80
250	21.44	24.36	31.51	23.54	1.05	0.72	34.69	19.44	3.84
300	21.38	24.35	31.38	23.52	1.06	0.71	35.38	19.30	3.90
350	21.32	24.36	31.10	23.47	1.06	0.71	35.07	19.27	3.84
400	21.24	24.36	30.79	23.35	1.06	0.70	34.84	19.17	3.85
450	21.17	24.33	29.88	23.25	1.06	0.70	34.28	19.17	3.86
500	21.09	24.32	29.32	23.03	1.07	0.69	34.28	19.09	3.84
550	21.01	24.29	28.90	22.85	1.07	0.69	34.10	19.15	3.86
600	20.92	24.28	28.44	22.60	1.07	0.68	33.89	19.10	3.90
650	20.82	24.25	27.96	22.41	1.07	0.68	33.62	18.99	3.84
700	20.73	24.24	27.59	22.13	1.08	0.67	33.68	18.93	3.87
750	20.63	24.20	27.29	21.93	1.08	0.66	33.46	18.74	3.88
800	20.52	24.17	26.88	21.79	1.08	0.66	33.41	18.79	3.84
850	20.42	24.15	26.61	21.57	1.09	0.65	33.14	18.59	3.91
900	20.31	24.14	26.30	21.43	1.09	0.64	33.06	18.56	3.89
940	20.22	24.11	26.14	21.21	1.10	0.64	32.84	18.57	3.84
1000	20.09	24.07	25.88	21.02	1.10	0.63	32.58	18.41	3.85
1050	19.98	24.04	25.66	20.80	1.10	0.63	32.31	18.40	3.84
1100	19.86	24.01	25.49	20.54	1.11	0.62	32.18	18.23	3.96
1150	19.74	23.97	25.33	20.38	1.11	0.62	31.78	18.32	3.91
1200	19.62	23.93	25.24	20.18	1.12	0.61	31.84	18.07	3.85
1250	19.51	23.90	25.09	19.99	1.12	0.60	31.74	18.15	3.90
1300	19.38	23.87	24.96	19.83	1.12	0.60	31.42	18.10	4.00
1350	19.27	23.81	24.90	19.61	1.13	0.59	31.10	18.00	3.96
1400	19.15	23.77	24.98	19.46	1.13	0.59	30.88	17.89	3.89
1450	19.03	23.74	24.99	19.24	1.14	0.58	31.06	17.78	3.87
1500	18.92	23.71	25.19	18.96	1.14	0.58	30.97	17.68	3.94
1550	18.78	23.66	24.89	18.98	1.15	0.57	31.14	17.59	3.97
1600	18.66	23.60	24.99	18.80	1.15	0.57	31.06	17.33	3.93
1650	18.54	23.56	24.87	18.66	1.16	0.56	31.03	17.34	3.90
1700	18.42	23.52	24.86	18.48	1.16	0.55	31.00	17.17	4.05
1750	18.30	23.45	24.86	18.36	1.16	0.55	30.46	17.17	3.92
1800	18.18	23.42	24.97	18.20	1.17	0.55	30.39	16.82	4.04
1850	18.06	23.36	24.93	18.11	1.17	0.54	29.61	16.98	3.94
1900	17.95	23.32	24.98	17.94	1.18	0.54	29.83	16.71	3.96
1950	17.84	23.25	25.41	17.73	1.18	0.53	29.41	16.42	3.85
2000	17.71	23.20	25.09	17.72	1.18	0.53	29.73	16.47	3.95

Typical Performance Curves


GAIN vs. TEMPERATURE




GAIN vs. CURRENT




ISOLATION vs. TEMPERATURE




ISOLATION vs. CURRENT




INPUT RETURN LOSS vs. TEMPERATURE




INPUT RETURN LOSS vs. CURRENT



OUTPUT RETURN LOSS vs. TEMPERATURE



OUTPUT RETURN LOSS vs. CURRENT



REV. X1

ERA-50SM+

070821

Page 10 of 11



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED RoHS compliant
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661




The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see




Typical Performance Curves


OUTPUT IP3 vs. TEMPERATURE




OUTPUT IP3 vs. CURRENT




OUTPUT POWER at 1dB Compression vs. TEMPERATURE




OUTPUT POWER at 1dB Compression vs. CURRENT



Noise Figure vs. TEMPERATURE




Noise Figure vs. CURRENT




Typical Performance Curves


GAIN vs. TEMPERATURE




GAIN vs. CURRENT




ISOLATION vs. TEMPERATURE




ISOLATION vs. CURRENT




INPUT RETURN LOSS vs. TEMPERATURE




INPUT RETURN LOSS vs. CURRENT



OUTPUT RETURN LOSS vs. TEMPERATURE



OUTPUT RETURN LOSS vs. CURRENT



REV. X1

ERA-50SM+

070821

Page 1 of 2



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED RoHS compliant
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see




MMIC Amplifier


ERA-50SM+

Typical Performance Curves


OUTPUT IP3 vs. TEMPERATURE




OUTPUT IP3 vs. CURRENT




OUTPUT POWER at 1dB Compression vs. TEMPERATURE




OUTPUT POWER at 1dB Compression vs. CURRENT



Noise Figure vs. TEMPERATURE



Noise Figure vs. CURRENT



REV. X1
ERA-50SM+
070821
Page 2 of 2

 **Mini-Circuits**®

IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED RoHS compliant
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661


 Mouser Electronics The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see minicircuits.com

Case Style


WW

WW107

Outline Dimensions



PCB Land Pattern



Suggested Layout,
Tolerance to be within $\pm .002$

CASE#	A	B	C	D	E	F	G	H	J	K	L	M	N	P	Q	WT. GRAMS
WW107	.012 (0.30)	.10 (2.54)	.020 (0.51)	.092 (2.34)	.085 (2.16)	.060 (1.52)	.007 (0.18)	.026 (0.66)	.235 (5.97)	.118 (3.00)	.235 (5.97)	.118 (3.00)	.072 (1.83)	.040 (1.02)	.020 (0.51)	.015

Dimensions are in inches (mm). Tolerances: 2 Pl. $\pm .03$; 3 Pl. $\pm .015$

Notes:

1. Case material: Plastic.
2. Termination finish:
 - For RoHS Case Styles: Matte tin Plate.
 - For RoHS-5 Case Styles: Tin-Lead plate.
3. RF input termination (1) identified by one or both of the following at factory option:
 - (a) diagonally cut termination, which may be 45° (ref) in either direction;
 - (b) orientation mark on the case. Model dash number is identified by color dot or alphanumeric code on case. See specification data sheet.



Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-4


INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500

Mini-Circuits ISO 9001 & ISO 14001 Certified

Tape & Reel Packaging TR-F4

DEVICE ORIENTATION IN T&R



Tape Width, mm	Device Cavity Pitch, mm	Reel Size, inches	Devices per Reel	
12	8	7	Small quantity standards (see note)	20
			7	500
		7	Standard	1000

Note: Please Consult individual model data sheet to determine device per reel availability.

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: www.minicircuits.com/pages/pdfs/tape.pdf




Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Mini-Circuits ISO 9001 & ISO 14001 Certified


THIRD ANGLE PROJECTION



REVIEWS

REV	ECN No.	DESCRIPTION	DATE	DR	AUTH
A	M100215	ADDED "PACKAGE OUTLINE" & UPDATED NOTES	08/12/05	MMG	MM
B	M100944	REMOVED AF190 & UPDATED NOTES	09/23/05	GT	MM
C	M102713	ADDED "...WITH SMOBC"	01/14/06	GF	IL
D	M108434	UPDATED DRAWING PER TB-408+	11/14/06	PW	IG

SUGGESTED MOUNTING CONFIGURATION FOR
WW107 CASE STYLE, "cb" PIN CONNECTION

NOTES:

1. TRACE WIDTH IS SHOWN FOR ROGERS R04350B WITH DIELECTRIC THICKNESS $.030" \pm .002"$; COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.
3. IF PCB DESIGN RULES ALLOW, PLACE GROUND VIAS UNDER THE LAND PATTERN FOR BETTER RF PERFORMANCE. OTHERWISE PLACE GROUND VIAS AS CLOSE TO LAND PATTERN AS POSSIBLE.



DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)



DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

UNLESS OTHERWISE SPECIFIED

INITIALS

DATE

DIMENSIONS ARE IN INCHES

DRAWN

GF

07/18/02

TOLERANCES ON:

CHECKED

LC

08/01/02

2 PL DECIMALS $\pm .005$

APPROVED

DJ

08/05/02

3 PL DECIMALS $\pm .005$

THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS.
EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE
AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY
DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO.
THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE
PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.

ASHEETA1.DWG REV:A DATE:01/12/95




Mini-Circuits®

13 Neptune Avenue
Brooklyn NY 11235


PL, cb, WW107, ERA, TB-408-XX+

SIZE	CODE IDENT	DRAWING NO:	REV:
A	15542	98-PL-075	D
FILE:	98PL075	SCALE: 8:1	SHEET: 1 OF 1

Evaluation Board and Circuit



TB-408-50+



COMPONENT	VALUE
A1	ERA-50SM(+)
C1 (NOTE 4)	2400 pF
C2 (NOTE 4)	2400 pF
C3 (bypass)	0.1 uF
R1	127 Ohms, 0.75W
R2	0 Ohm, 0.25W
CHK	Mini-Circuits TCCH-80+

Schematic Diagram

NOTE:

1. Vcc voltage: $+12 \pm 0.2V$.
2. SMA Female connectors.
3. PCB material: Rogers RO4350 or equivalent, dielectric constant=3.5, dielectric thickness=.030 inch.
4. Capacitors, C1 & C2 should be free of resonance up to the highest frequency specified.

Mini-Circuits®



Environmental Specifications

ENV08T2

All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-45° to 85°C or -40° to 85°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-65° to 150° C Ambient Environment	Individual Model Data Sheet
Thermal Shock	-55° to 100°C, 100 cycles	MIL-STD-202, Method 107, Condition A-3, except +100°C
Mechanical Shock	1.5Kg, 0.5 ms, 5 shock pulses, Y1 direction only	MIL-STD-883, Method 2002, Condition B, except Y1 direction only
Vibration (Variable Frequency)	50g peak	MIL-STD-883, Method 2007, Condition B
Autoclave	15 psig, 100% RH, 121°C, 96 hours	JESD22-A102, Condition C
HAST	130°C, 85% RH, 96 hours	JESD22-A110
Solderability	10X Magnification	J-STD-002, Para 4.2.5, Test S, 95% Coverage
Solder Reflow Heat	Sn-Pb Eutetic Process: 240°C peak Pb-Free Process: 260°C peak	J-STD-020, Table 4-1, 4-2 and 5-2; Figure 5-1
Moisture Sensitivity: Level 1	Bake at 125°C for 24 hours Soak at 85°C/85% RH for 168 hours, Reflow 3 cycles at 260°C peak	J-STD-020
Marking Resistance to Solvents	Isopropyl alcohol + mineral spirits at 25°C; terpene defluxer at 25°C; distilled water + propylene glycol monomethyl ether +	MIL-STD-202, Method 215



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
	monoethanolamine at 63°C to 70°C	