

*Drop-In*

# Monolithic Amplifier

DC-2 GHz

## Product Features

- Wideband, DC to 2 GHz
- High gain, 12.5 dB typ. at 0.1 GHz
- Internally Matched to 50 Ohms
- Low noise figure, 3.7 dB typ.
- Exact foot print substitute for MSA-0385
- Cascadable, unconditionally stable
- Aqueous washable
- Protected by US Patent 6,943,629



Generic photo used for illustration purposes only

**MAR-3+**

CASE STYLE: VV105

## Typical Applications

- Cellular
- PCN instrumentation



+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

## General Description

MAR-3+ (RoHS compliant) is a wideband amplifier offering high dynamic range. It has repeatable performance from lot to lot. It is enclosed in a Micro-X package. MAR-3+ uses Darlington configuration and is fabricated using InGaP HBT technology. Expected MTTF is 3,000 years at 85°C case temperature.

## simplified schematic and pin description



Function	Pin Number	Description
RF IN	1	RF input pin. This pin requires the use of an external DC blocking capacitor chosen for the frequency of operation.
RF-OUT and DC-IN	3	RF output and bias pin. DC voltage is present on this pin; therefore a DC blocking capacitor is necessary for proper operation. An RF choke is needed to feed DC bias without loss of RF signal due to the bias connection, as shown in "Recommended Application Circuit".
GND	2,4	Connections to ground. Use via holes as shown in "Suggested Layout for PCB Design" to reduce ground path inductance for best performance.

### Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.  
 B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.  
 C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)

**Mini-Circuits®**

[www.minicircuits.com](http://www.minicircuits.com) P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

REV. C  
M151107  
MAR-3+  
200930  
Page 1 of 4

**Electrical Specifications at 25°C and 35mA, unless noted**

Parameter		Min.	Typ. <sup>3</sup>	Max.	Units
Frequency Range*	DC			2	GHz
Gain	f=0.1 GHz	—	12.5	—	dB
	f=1 GHz	—	12.0	—	
	f=2 GHz	8.0 <sup>2</sup>	10.5	—	
Input Return Loss	f=DC to 2 GHz		17.5		dB
Output Return Loss	f=DC to 2 GHz		17.5		dB
Output Power @ 1 dB compression	f=1 GHz		+10.0		dBm
Output IP3	f=1 GHz		+23		dBm
Noise Figure	f=1 GHz		3.7		dB
Recommended Device Operating Current			35		mA
Device Operating Voltage			5.0		V
Device Voltage Variation vs. Temperature at 35 mA			-2.6		mV/°C
Device Voltage Variation vs. Current at 25°C			15.5		mV/mA
Thermal Resistance, junction-to-case <sup>1</sup>			174		°C/W

\*Guaranteed specification DC-2 GHz. Low frequency cut off determined by external coupling capacitors.

**Absolute Maximum Ratings**

Parameter	Ratings
Operating Temperature	-40°C to 85°C
Storage Temperature	-55°C to 100°C
Operating Current	70mA
Power Dissipation	400mW
Input Power	13dBm

Note: Permanent damage may occur if any of these limits are exceeded.

These ratings are not intended for continuous normal operation.

<sup>1</sup>Case is defined as ground leads.

<sup>2</sup>Full temperature range.


<sup>3</sup>Based on test data of Model MAR-3SM+ (Case Style WW107).

**Notes**

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)



## Product Marking



Markings in addition to model number designation may appear for internal quality control purposes.

## Additional Detailed Technical Information

Additional information is available on our web site. To access this information enter the model number on our web site home page.

### Performance data, graphs, s-parameter data set (.zip file)

#### Case Style: VV105

Plastic micro-x, .085 body diameter, lead finish: matte-tin


#### Tape & Reel: F20

#### Suggested Layout for PCB Design: PL-262

#### Evaluation Board: TB-432-3+

#### Environmental Ratings: ENV08T3

## Recommended Application Circuit



Test Board includes case, connectors, and components (in bold) soldered to PCB

R BIAS	
Vcc	"1%" Res. Values (ohms) for Optimum Biasing
7	57.6
8	86.6
9	115
10	143
11	169
12	200
13	226
14	255
15	287

#### Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)

**ESD Rating**


Human Body Model (HBM): Class 1B (500v to < 1000v) in accordance with ANSI/ESD STM 5.1 - 2001

Machine Model (MM): Class M1 (<100v) in accordance with ANSI/ESD STM 5.2 - 1999

**MSL Rating**

Moisture Sensitivity: MSL1 in accordance with IPC/JEDEC J-STD-020C

No.	Test Required	Condition	Standard	Quantity
1	Visual Inspection	Low Power Microscope Magnification 40x	MIP-IN-0003 (MCT spec)	45 units
2	Electrical Test	Room Temperature	SCD (MCL spec)	45 units
3	SAM Analysis	Less than 10% growth in term of delamination	J-Std-020C (Jedec Standard)	45 units
4	Moisture Sensitivity Level 1	Bake at 125°C for 24 hours Soak at 85°C/85%RH for 168 hours Reflow 3 cycles at 260°C peak	J-Std-020C (Jedec Standard)	45 units

**MSL Test Flow Chart****Notes**

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)



*Typical Performance Data*

**NOTE: Use PDF Bookmarks to view DATA at required conditions  
or to view GRAPHS.**

**Definitions:**

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Icc = 35mA, Vd = 4.94V @ Temperature = +25degC

FREQ	Gain	Isolation	Input Return Loss	Output Return Loss	Stability		IP3 Output	1dB Comp. Output	Noise Figure
(MHz)	(dB)	(dB)	(dB)	(dB)	K	Delta	(dBm)	(dBm)	(dB)
50	13.23	18.53	29.26	24.75	1.19	0.55	28.35	11.79	3.67
100	13.22	18.50	28.85	25.18	1.19	0.55	29.15	11.72	3.72
150	13.20	18.47	29.41	25.14	1.19	0.55	30.11	11.81	3.75
200	13.19	18.46	29.26	25.14	1.19	0.55	31.43	11.78	3.77
250	13.17	18.49	29.22	25.30	1.19	0.54	28.82	11.81	3.74
300	13.16	18.45	29.31	25.24	1.19	0.55	31.02	11.73	3.79
350	13.13	18.48	29.18	25.29	1.19	0.54	30.33	11.73	3.82
400	13.11	18.47	29.21	25.40	1.19	0.54	30.47	11.69	3.77
450	13.09	18.49	29.41	25.40	1.20	0.54	29.23	11.74	3.77
500	13.07	18.46	29.50	25.50	1.20	0.54	29.78	11.68	3.80
550	13.03	18.45	29.79	25.57	1.20	0.54	28.98	11.61	3.83
600	13.01	18.44	29.62	25.58	1.20	0.54	29.22	11.53	3.80
650	12.99	18.44	30.02	25.63	1.20	0.54	28.71	11.57	3.76
700	12.94	18.45	30.15	25.68	1.20	0.53	28.95	11.53	3.82
750	12.91	18.42	30.26	25.60	1.21	0.53	29.23	11.59	3.83
800	12.89	18.42	30.67	25.69	1.21	0.53	29.49	11.49	3.83
850	12.85	18.41	31.00	25.52	1.21	0.53	29.11	11.47	3.80
900	12.81	18.39	31.29	25.48	1.21	0.53	28.66	11.36	3.76
940	12.78	18.38	31.50	25.26	1.21	0.52	28.78	11.45	3.78
1000	12.73	18.38	31.82	25.00	1.22	0.52	28.02	11.35	3.75
1050	12.69	18.36	32.71	24.73	1.22	0.52	28.08	11.27	3.77
1100	12.65	18.36	32.75	24.44	1.22	0.52	27.48	11.21	3.83
1150	12.60	18.34	32.71	24.20	1.22	0.52	27.31	11.02	3.88
1200	12.54	18.34	33.56	23.76	1.23	0.51	27.03	10.92	3.85
1250	12.51	18.32	33.48	23.55	1.23	0.51	27.28	10.88	3.86
1300	12.47	18.30	34.27	23.04	1.23	0.51	26.84	10.77	3.88
1350	12.41	18.29	35.02	22.72	1.23	0.51	26.87	10.72	3.88
1400	12.35	18.27	34.33	22.25	1.23	0.50	26.35	10.76	3.88
1450	12.30	18.25	34.85	21.89	1.24	0.50	26.47	10.67	3.93
1500	12.27	18.26	34.82	21.43	1.24	0.50	26.41	10.59	3.98
1550	12.19	18.21	34.63	21.09	1.24	0.50	26.67	10.51	3.92
1600	12.15	18.22	34.28	20.76	1.24	0.50	26.53	10.36	3.94
1650	12.08	18.20	34.38	20.35	1.25	0.49	26.40	10.41	3.90
1700	12.01	18.18	33.46	20.05	1.25	0.49	26.41	10.23	3.93
1750	11.95	18.16	32.91	19.63	1.25	0.49	25.89	10.22	3.86
1800	11.91	18.14	32.61	19.39	1.25	0.49	25.42	10.06	3.85
1850	11.83	18.12	32.47	19.00	1.26	0.48	24.53	10.02	3.88
1900	11.77	18.11	31.52	18.77	1.26	0.48	24.53	9.81	3.87
1950	11.72	18.09	31.02	18.46	1.26	0.48	24.33	9.77	3.81
2000	11.66	18.07	30.39	18.18	1.27	0.48	24.26	9.71	3.88

REV. X1

MAR-3+

070907

Page 1 of 11



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED RoHS compliant  
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see



*Typical Performance Data***Definitions:**

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Icc = 28mA, Vd = 4.85V @ Temperature = +25degC

FREQ (MHz)	Gain (dB)	Isolation (dB)	Input Return Loss (dB)	Output Return Loss (dB)	Stability		IP3 Output (dBm)	1dB Comp. Output (dBm)	Noise Figure (dB)
					K	Delta			
50	12.97	18.30	25.97	22.40	1.19	0.55	24.52	9.88	3.66
100	12.99	18.33	25.82	22.50	1.19	0.54	24.71	9.73	3.67
150	12.96	18.30	26.18	22.51	1.19	0.54	25.48	9.78	3.73
200	12.94	18.31	26.11	22.72	1.19	0.54	25.53	9.77	3.73
250	12.92	18.34	26.01	22.66	1.20	0.54	24.13	9.71	3.70
300	12.91	18.31	26.04	22.76	1.20	0.54	25.36	9.73	3.75
350	12.89	18.32	26.04	22.76	1.20	0.54	24.88	9.72	3.79
400	12.87	18.29	26.02	22.90	1.20	0.54	25.10	9.83	3.72
450	12.85	18.30	26.30	23.08	1.20	0.54	24.30	9.61	3.77
500	12.83	18.29	26.18	23.02	1.20	0.54	24.87	9.69	3.78
550	12.80	18.29	26.49	23.29	1.20	0.53	24.26	9.54	3.77
600	12.78	18.28	26.38	23.28	1.20	0.53	24.51	9.64	3.77
650	12.75	18.29	26.63	23.46	1.21	0.53	24.19	9.62	3.75
700	12.72	18.27	26.70	23.61	1.21	0.53	24.44	9.53	3.80
750	12.69	18.27	26.91	23.75	1.21	0.53	24.75	9.69	3.76
800	12.65	18.27	27.05	23.82	1.21	0.53	24.92	9.38	3.79
850	12.61	18.25	27.21	23.88	1.21	0.52	24.74	9.72	3.75
900	12.61	18.24	27.42	24.01	1.21	0.52	24.39	9.44	3.73
940	12.56	18.23	27.59	23.94	1.22	0.52	24.66	9.48	3.77
1000	12.51	18.22	27.94	24.02	1.22	0.52	24.16	9.41	3.71
1050	12.46	18.20	28.26	23.90	1.22	0.52	24.49	9.37	3.75
1100	12.42	18.19	28.30	23.84	1.22	0.52	23.95	9.38	3.80
1150	12.39	18.17	28.47	23.79	1.22	0.51	24.11	9.21	3.83
1200	12.34	18.18	28.89	23.50	1.23	0.51	23.73	9.26	3.80
1250	12.30	18.15	28.66	23.43	1.23	0.51	24.14	9.12	3.80
1300	12.25	18.14	29.27	23.06	1.23	0.51	23.89	9.21	3.84
1350	12.20	18.12	29.93	22.90	1.23	0.50	24.11	9.06	3.87
1400	12.16	18.09	29.36	22.50	1.23	0.50	23.66	9.09	3.85
1450	12.10	18.09	29.59	22.24	1.24	0.50	23.69	9.10	3.89
1500	12.04	18.08	29.86	21.87	1.24	0.50	23.70	9.14	3.94
1550	12.01	18.06	29.61	21.57	1.24	0.50	23.93	9.02	3.83
1600	11.94	18.05	29.86	21.27	1.25	0.49	23.92	8.95	3.88
1650	11.88	18.05	30.10	20.90	1.25	0.49	23.95	8.92	3.87
1700	11.83	18.00	29.50	20.63	1.25	0.49	24.12	8.99	3.89
1750	11.77	18.00	29.26	20.25	1.25	0.48	23.85	8.81	3.80
1800	11.70	17.98	29.37	20.00	1.26	0.48	23.53	8.91	3.82
1850	11.65	17.94	29.34	19.61	1.26	0.48	22.85	8.75	3.84
1900	11.60	17.95	28.91	19.36	1.26	0.48	22.74	8.75	3.82
1950	11.53	17.92	28.54	19.07	1.26	0.47	22.68	8.76	3.77
2000	11.46	17.90	28.27	18.79	1.27	0.47	22.55	8.61	3.80

REV. X1

MAR-3+

070907

Page 2 of 11



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED RoHS compliant  
 P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see



*Typical Performance Data***Definitions:**

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Icc = 42mA, Vd = 5.02V @ Temperature = +25degC

FREQ (MHz)	Gain (dB)	Isolation (dB)	Input Return Loss (dB)	Output Return Loss (dB)	Stability		IP3 Output (dBm)	1dB Comp. Output (dBm)	Noise Figure (dB)
					K	Delta			
50	13.38	18.52	32.10	26.89	1.18	0.55	31.22	12.50	3.74
100	13.37	18.58	31.56	27.23	1.18	0.55	32.31	12.50	3.78
150	13.35	18.55	32.27	27.08	1.18	0.55	32.89	12.49	3.80
200	13.34	18.57	32.03	27.15	1.19	0.55	37.34	12.59	3.81
250	13.31	18.60	32.16	27.33	1.19	0.54	34.53	12.54	3.79
300	13.30	18.56	32.10	27.25	1.19	0.55	37.91	12.40	3.81
350	13.27	18.57	31.99	27.24	1.19	0.54	38.18	12.59	3.88
400	13.25	18.58	31.95	27.19	1.19	0.54	37.33	12.27	3.84
450	13.23	18.56	32.30	27.24	1.19	0.54	35.13	12.60	3.87
500	13.20	18.57	32.44	27.26	1.20	0.54	35.67	12.27	3.85
550	13.18	18.56	32.63	27.18	1.20	0.54	34.24	12.52	3.87
600	13.16	18.55	32.60	27.07	1.20	0.54	33.69	12.32	3.83
650	13.13	18.55	33.19	27.03	1.20	0.54	32.88	12.29	3.84
700	13.08	18.53	33.34	27.01	1.20	0.53	32.94	12.32	3.89
750	13.06	18.53	33.49	26.70	1.20	0.53	32.44	12.27	3.84
800	13.02	18.52	34.29	26.63	1.21	0.53	32.89	12.40	3.88
850	12.98	18.50	34.59	26.28	1.21	0.53	31.94	12.34	3.83
900	12.96	18.50	34.98	26.13	1.21	0.53	32.06	12.24	3.85
940	12.92	18.49	35.50	25.71	1.21	0.53	31.51	12.19	3.84
1000	12.87	18.48	36.01	25.31	1.21	0.52	30.77	12.10	3.80
1050	12.82	18.45	37.45	24.85	1.21	0.52	30.23	12.05	3.85
1100	12.78	18.46	37.32	24.47	1.22	0.52	29.72	11.84	3.88
1150	12.74	18.42	37.48	24.16	1.22	0.52	29.20	11.70	3.96
1200	12.68	18.44	39.04	23.58	1.22	0.51	29.31	11.56	3.89
1250	12.65	18.42	38.75	23.28	1.22	0.51	29.25	11.49	3.90
1300	12.60	18.40	39.88	22.72	1.23	0.51	28.61	11.37	3.95
1350	12.54	18.39	40.79	22.41	1.23	0.51	28.31	11.37	3.97
1400	12.48	18.38	39.73	21.86	1.23	0.51	28.01	11.37	3.91
1450	12.42	18.36	39.55	21.47	1.23	0.50	28.18	11.21	3.99
1500	12.38	18.36	38.88	21.01	1.24	0.50	28.13	11.12	4.05
1550	12.33	18.33	38.52	20.66	1.24	0.50	28.37	11.03	4.00
1600	12.27	18.32	37.19	20.32	1.24	0.50	28.13	10.85	4.01
1650	12.20	18.29	37.03	19.94	1.24	0.49	27.95	10.93	3.99
1700	12.14	18.28	35.75	19.60	1.25	0.49	27.77	10.70	4.01
1750	12.09	18.26	34.61	19.20	1.25	0.49	27.04	10.77	3.93
1800	12.01	18.25	34.00	18.98	1.26	0.49	26.59	10.51	3.96
1850	11.95	18.23	33.65	18.57	1.26	0.48	25.64	10.55	3.97
1900	11.90	18.23	32.38	18.35	1.26	0.48	25.71	10.27	3.90
1950	11.84	18.21	31.81	18.01	1.26	0.48	25.42	10.23	3.92
2000	11.77	18.18	31.23	17.79	1.26	0.48	25.35	10.24	3.92

REV. X1

MAR-3+

070907

Page 3 of 11



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED RoHS compliant  
 P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see



*Typical Performance Data***Definitions:**

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Icc = 35mA, Vd = 5.19V @ Temperature = -45degC

FREQ (MHz)	Gain (dB)	Isolation (dB)	Input Return Loss (dB)	Output Return Loss (dB)	Stability		IP3 Output (dBm)	1dB Comp. Output (dBm)	Noise Figure (dB)
					K	Delta			
50	13.33	18.55	28.44	24.88	1.18	0.55	28.74	11.95	3.02
100	13.32	18.51	27.20	24.15	1.18	0.55	28.76	11.92	3.04
150	13.31	18.52	26.76	23.52	1.18	0.55	29.45	12.01	3.08
200	13.30	18.46	26.36	23.48	1.18	0.56	29.32	11.95	3.07
250	13.27	18.54	27.17	24.19	1.19	0.55	27.77	11.89	3.04
300	13.28	18.50	28.29	25.10	1.18	0.55	28.99	11.88	3.13
350	13.26	18.50	29.46	25.90	1.19	0.55	28.58	11.96	3.13
400	13.25	18.49	30.28	26.39	1.19	0.55	28.72	11.90	3.07
450	13.24	18.48	30.84	26.50	1.19	0.55	28.00	11.92	3.10
500	13.21	18.47	30.71	26.30	1.19	0.55	28.43	11.91	3.10
550	13.19	18.46	30.71	26.30	1.19	0.55	27.91	11.79	3.11
600	13.17	18.46	30.62	26.15	1.19	0.54	28.11	11.85	3.09
650	13.15	18.45	31.16	26.38	1.19	0.54	27.81	11.81	3.10
700	13.11	18.43	31.24	26.39	1.19	0.54	28.02	11.74	3.09
750	13.08	18.42	31.31	26.04	1.19	0.54	28.44	11.86	3.07
800	13.05	18.41	31.61	25.82	1.19	0.54	28.53	11.71	3.11
850	13.01	18.40	31.56	25.50	1.20	0.54	28.31	11.85	3.03
900	13.00	18.38	31.72	25.39	1.19	0.54	27.99	11.65	3.04
940	12.95	18.37	32.11	25.19	1.20	0.54	28.10	11.74	3.09
1000	12.92	18.36	32.63	25.15	1.20	0.53	27.73	11.66	3.05
1050	12.88	18.34	33.55	24.94	1.20	0.53	27.97	11.57	3.04
1100	12.84	18.32	33.68	24.65	1.20	0.53	27.42	11.53	3.07
1150	12.81	18.32	33.94	24.39	1.20	0.53	27.47	11.38	3.15
1200	12.75	18.31	35.24	23.92	1.21	0.53	27.15	11.35	3.13
1250	12.71	18.29	35.33	23.68	1.21	0.52	27.57	11.31	3.12
1300	12.67	18.28	36.71	23.09	1.21	0.52	27.17	11.26	3.13
1350	12.63	18.25	37.26	22.85	1.21	0.52	27.38	11.19	3.14
1400	12.58	18.25	36.25	22.33	1.21	0.52	26.90	11.30	3.15
1450	12.52	18.22	36.10	21.96	1.22	0.52	26.93	11.17	3.18
1500	12.49	18.22	35.76	21.46	1.22	0.52	26.85	11.16	3.22
1550	12.43	18.23	36.86	21.24	1.22	0.51	27.06	11.05	3.16
1600	12.39	18.18	35.03	20.81	1.22	0.51	27.11	10.95	3.19
1650	12.32	18.16	34.76	20.36	1.22	0.51	27.12	10.94	3.18
1700	12.27	18.14	33.89	20.08	1.23	0.51	27.23	10.86	3.19
1750	12.20	18.13	33.20	19.62	1.23	0.50	26.87	10.77	3.11
1800	12.16	18.12	32.82	19.43	1.23	0.50	26.55	10.67	3.12
1850	12.10	18.08	32.70	19.02	1.23	0.50	25.78	10.65	3.13
1900	12.04	18.06	31.60	18.76	1.23	0.50	25.76	10.44	3.14
1950	11.98	18.04	30.91	18.39	1.24	0.50	25.62	10.52	3.09
2000	11.94	18.05	30.08	18.01	1.24	0.49	25.46	10.39	3.09

REV. X1

MAR-3+

070907

Page 4 of 11



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED RoHS compliant  
 P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see



*Typical Performance Data***Definitions:**

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Icc = 28mA, Vd = 5.12V @ Temperature = -45degC

FREQ (MHz)	Gain (dB)	Isolation (dB)	Input Return Loss (dB)	Output Return Loss (dB)	Stability		IP3 Output (dBm)	1dB Comp. Output (dBm)	Noise Figure (dB)
					K	Delta			
50	13.11	18.40	26.01	22.68	1.19	0.55	24.61	9.75	2.96
100	13.11	18.33	24.96	22.15	1.18	0.55	24.55	9.66	3.01
150	13.11	18.37	24.51	21.62	1.18	0.55	25.10	9.72	3.02
200	13.08	18.37	24.38	21.65	1.19	0.55	24.93	9.67	3.04
250	13.07	18.38	24.84	22.14	1.19	0.55	23.85	9.60	3.00
300	13.07	18.36	25.73	22.74	1.19	0.55	24.77	9.73	3.12
350	13.05	18.36	26.66	23.63	1.19	0.55	24.41	9.59	3.08
400	13.06	18.33	27.22	23.98	1.19	0.55	24.61	9.81	3.06
450	13.03	18.34	27.66	24.21	1.19	0.55	23.98	9.51	3.06
500	13.01	18.33	27.38	24.13	1.19	0.54	24.51	9.61	3.03
550	12.98	18.31	27.60	24.07	1.19	0.54	23.95	9.49	3.08
600	12.97	18.31	27.46	24.22	1.19	0.54	24.24	9.59	3.07
650	12.95	18.32	27.83	24.32	1.19	0.54	23.96	9.62	3.07
700	12.90	18.29	27.90	24.54	1.20	0.54	24.19	9.45	3.06
750	12.89	18.28	28.08	24.41	1.20	0.54	24.43	9.64	3.05
800	12.86	18.28	28.09	24.39	1.20	0.54	24.59	9.29	3.04
850	12.82	18.27	28.06	24.09	1.20	0.54	24.47	9.65	3.01
900	12.80	18.24	28.21	24.21	1.20	0.54	24.18	9.31	2.98
940	12.77	18.25	28.43	24.19	1.20	0.53	24.44	9.51	3.01
1000	12.72	18.23	28.88	24.28	1.20	0.53	24.05	9.47	3.00
1050	12.70	18.20	29.32	24.27	1.20	0.53	24.45	9.34	3.01
1100	12.65	18.20	29.44	24.14	1.21	0.53	23.98	9.43	3.04
1150	12.62	18.17	29.81	24.07	1.21	0.53	24.21	9.28	3.13
1200	12.57	18.18	30.39	23.73	1.21	0.52	23.84	9.36	3.10
1250	12.53	18.15	30.30	23.66	1.21	0.52	24.30	9.17	3.07
1300	12.50	18.15	31.33	23.26	1.21	0.52	24.06	9.28	3.11
1350	12.45	18.11	32.09	23.09	1.21	0.52	24.38	9.13	3.10
1400	12.40	18.09	31.48	22.69	1.21	0.52	23.96	9.22	3.12
1450	12.35	18.09	31.51	22.38	1.22	0.51	23.99	9.30	3.14
1500	12.32	18.07	31.66	21.95	1.22	0.51	24.03	9.33	3.19
1550	12.26	18.10	32.21	21.77	1.23	0.51	24.25	9.17	3.14
1600	12.21	18.06	31.60	21.35	1.23	0.51	24.25	9.19	3.14
1650	12.15	18.01	31.80	20.91	1.23	0.51	24.33	9.11	3.14
1700	12.10	18.00	31.12	20.66	1.23	0.50	24.57	9.20	3.13
1750	12.06	17.99	30.70	20.19	1.23	0.50	24.49	9.07	3.06
1800	12.00	17.96	30.85	20.01	1.23	0.50	24.33	9.26	3.07
1850	11.93	17.95	30.89	19.61	1.24	0.50	23.74	9.02	3.11
1900	11.88	17.93	30.28	19.32	1.24	0.50	23.58	9.15	3.07
1950	11.84	17.90	29.86	18.92	1.24	0.49	23.67	9.04	3.04
2000	11.78	17.89	29.28	18.61	1.24	0.49	23.50	9.06	3.06

REV. X1

MAR-3+

070907

Page 5 of 11



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED RoHS compliant  
 P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see



*Typical Performance Data***Definitions:**

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Icc = 42mA, Vd = 5.30V @ Temperature = -45degC

FREQ (MHz)	Gain (dB)	Isolation (dB)	Input Return Loss (dB)	Output Return Loss (dB)	Stability		IP3 Output (dBm)	1dB Comp. Output (dBm)	Noise Figure (dB)
					K	Delta			
50	13.45	18.50	31.00	26.41	1.17	0.56	32.27	12.92	3.06
100	13.45	18.56	29.15	25.86	1.18	0.56	32.40	12.98	3.06
150	13.44	18.55	28.27	24.91	1.18	0.56	33.17	12.99	3.11
200	13.42	18.55	28.03	24.89	1.18	0.56	33.16	13.03	3.14
250	13.40	18.60	28.93	25.74	1.18	0.55	30.98	13.01	3.09
300	13.40	18.57	30.19	26.76	1.18	0.55	32.47	12.86	3.20
350	13.38	18.59	32.00	27.83	1.18	0.55	32.00	13.07	3.18
400	13.37	18.57	32.97	28.23	1.18	0.55	32.10	12.72	3.13
450	13.35	18.58	33.78	28.27	1.19	0.55	31.32	13.06	3.13
500	13.33	18.56	33.60	27.97	1.19	0.55	31.65	12.75	3.16
550	13.30	18.54	33.61	27.77	1.19	0.55	31.11	12.94	3.16
600	13.29	18.54	33.71	27.55	1.19	0.55	31.24	12.69	3.15
650	13.26	18.53	34.09	27.58	1.19	0.55	30.76	12.78	3.13
700	13.22	18.51	34.46	27.48	1.19	0.54	30.95	12.84	3.19
750	13.20	18.51	34.42	26.90	1.19	0.54	31.38	12.81	3.14
800	13.17	18.50	34.91	26.55	1.19	0.54	31.51	12.82	3.15
850	13.12	18.49	34.61	26.08	1.19	0.54	31.19	12.78	3.12
900	13.11	18.48	35.28	25.91	1.19	0.54	30.84	12.76	3.07
940	13.07	18.47	35.92	25.63	1.20	0.54	30.92	12.70	3.13
1000	13.02	18.45	36.46	25.40	1.20	0.54	30.31	12.65	3.09
1050	13.00	18.43	37.87	25.04	1.20	0.53	30.36	12.55	3.08
1100	12.95	18.42	37.88	24.63	1.20	0.53	29.89	12.50	3.15
1150	12.91	18.41	38.63	24.28	1.20	0.53	29.70	12.22	3.21
1200	12.86	18.41	41.22	23.72	1.21	0.53	29.44	12.04	3.14
1250	12.82	18.37	40.82	23.42	1.21	0.53	29.63	12.12	3.15
1300	12.79	18.37	41.69	22.83	1.21	0.53	29.26	11.97	3.21
1350	12.72	18.34	41.38	22.51	1.21	0.52	29.31	12.00	3.22
1400	12.68	18.32	40.64	21.96	1.21	0.52	28.85	11.92	3.21
1450	12.63	18.33	38.29	21.56	1.22	0.52	28.91	11.84	3.26
1500	12.59	18.29	37.44	21.10	1.22	0.52	28.83	11.81	3.31
1550	12.53	18.31	38.27	20.81	1.22	0.51	29.06	11.79	3.23
1600	12.48	18.28	35.95	20.41	1.22	0.51	28.97	11.64	3.20
1650	12.42	18.25	35.45	19.96	1.22	0.51	28.89	11.64	3.23
1700	12.36	18.24	34.53	19.65	1.23	0.51	28.98	11.36	3.28
1750	12.32	18.21	33.47	19.21	1.23	0.51	28.42	11.45	3.20
1800	12.26	18.19	33.03	19.03	1.23	0.50	28.12	11.15	3.16
1850	12.20	18.16	32.78	18.64	1.23	0.50	27.12	11.20	3.21
1900	12.14	18.16	31.42	18.37	1.23	0.50	27.14	10.93	3.18
1950	12.09	18.13	30.74	17.99	1.24	0.50	26.86	11.02	3.15
2000	12.03	18.13	29.89	17.65	1.24	0.50	26.79	10.88	3.14

REV. X1

MAR-3+

070907

Page 6 of 11



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED RoHS compliant  
 P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see



*Typical Performance Data***Definitions:**

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Icc = 35mA, Vd = 4.69V @ Temperature = +85degC

FREQ (MHz)	Gain (dB)	Isolation (dB)	Input Return Loss (dB)	Output Return Loss (dB)	Stability		IP3 Output (dBm)	1dB Comp. Output (dBm)	Noise Figure (dB)
					K	Delta			
50	13.06	18.33	28.99	24.15	1.19	0.55	27.91	11.48	4.23
100	13.06	18.34	30.08	25.20	1.19	0.55	28.58	11.53	4.30
150	13.05	18.32	31.99	26.04	1.19	0.55	29.52	11.57	4.30
200	13.03	18.34	32.44	26.60	1.19	0.54	30.63	11.48	4.33
250	12.99	18.34	32.76	26.42	1.19	0.54	28.01	11.56	4.29
300	12.99	18.35	31.30	25.59	1.19	0.54	29.97	11.37	4.35
350	12.95	18.37	30.21	25.17	1.20	0.54	29.26	11.50	4.37
400	12.94	18.36	29.10	24.52	1.20	0.54	29.40	11.30	4.33
450	12.91	18.36	28.89	24.47	1.20	0.54	28.21	11.51	4.32
500	12.88	18.37	28.75	24.34	1.20	0.53	28.66	11.32	4.34
550	12.86	18.34	28.68	24.48	1.20	0.53	27.91	11.40	4.36
600	12.83	18.34	28.79	24.56	1.21	0.53	28.04	11.28	4.39
650	12.80	18.34	28.86	24.58	1.21	0.53	27.58	11.33	4.37
700	12.75	18.33	28.94	24.65	1.21	0.53	27.76	11.27	4.40
750	12.72	18.32	28.62	24.54	1.21	0.53	27.94	11.23	4.39
800	12.68	18.31	28.96	24.54	1.21	0.52	28.14	11.23	4.39
850	12.64	18.31	28.53	24.37	1.22	0.52	27.68	11.22	4.38
900	12.61	18.30	28.69	24.51	1.22	0.52	27.34	11.12	4.37
940	12.57	18.30	28.87	24.46	1.22	0.52	27.29	11.07	4.38
1000	12.52	18.29	28.88	24.40	1.22	0.52	26.66	11.01	4.34
1050	12.48	18.28	29.46	24.29	1.23	0.51	26.59	10.91	4.36
1100	12.43	18.26	29.40	24.14	1.23	0.51	26.06	10.87	4.44
1150	12.40	18.25	29.80	24.08	1.23	0.51	25.84	10.68	4.47
1200	12.33	18.25	30.43	23.79	1.24	0.51	25.67	10.52	4.42
1250	12.29	18.23	30.53	23.74	1.24	0.50	25.80	10.43	4.43
1300	12.24	18.21	31.22	23.25	1.24	0.50	25.35	10.36	4.51
1350	12.19	18.19	32.14	23.04	1.24	0.50	25.36	10.21	4.49
1400	12.12	18.18	32.06	22.53	1.25	0.50	24.86	10.30	4.50
1450	12.05	18.16	32.85	22.13	1.25	0.49	24.88	10.15	4.57
1500	12.03	18.14	33.09	21.65	1.25	0.49	24.79	10.13	4.63
1550	11.95	18.14	33.57	21.43	1.26	0.49	25.00	9.98	4.57
1600	11.90	18.15	33.27	20.92	1.26	0.49	24.94	9.81	4.51
1650	11.83	18.11	33.34	20.44	1.26	0.48	24.81	9.85	4.55
1700	11.77	18.09	33.00	20.15	1.26	0.48	24.75	9.69	4.57
1750	11.69	18.07	32.48	19.68	1.27	0.48	24.32	9.65	4.49
1800	11.64	18.05	32.09	19.43	1.27	0.48	23.90	9.49	4.51
1850	11.57	18.04	31.81	18.99	1.27	0.47	23.15	9.49	4.49
1900	11.50	18.02	30.81	18.71	1.28	0.47	23.07	9.24	4.49
1950	11.43	17.99	30.21	18.40	1.28	0.47	22.84	9.23	4.45
2000	11.37	17.98	29.29	18.15	1.28	0.46	22.76	9.12	4.49

REV. X1

MAR-3+

070907

Page 7 of 11



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED RoHS compliant  
 P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see



*Typical Performance Data***Definitions:**

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Icc = 28mA, Vd = 4.61V @ Temperature = +85degC

FREQ (MHz)	Gain (dB)	Isolation (dB)	Input Return Loss (dB)	Output Return Loss (dB)	Stability		IP3 Output (dBm)	1dB Comp. Output (dBm)	Noise Figure (dB)
					K	Delta			
50	12.79	18.12	25.29	21.58	1.19	0.55	24.11	9.79	4.19
100	12.79	18.19	26.21	22.32	1.20	0.54	24.34	9.66	4.23
150	12.77	18.16	27.53	23.07	1.20	0.54	25.13	9.83	4.28
200	12.76	18.17	27.78	23.30	1.20	0.54	25.13	9.73	4.32
250	12.72	18.17	27.66	23.34	1.20	0.54	23.66	9.70	4.26
300	12.72	18.17	27.13	22.81	1.20	0.54	24.91	9.68	4.32
350	12.68	18.15	26.32	22.44	1.20	0.54	24.45	9.68	4.33
400	12.67	18.17	25.68	22.17	1.20	0.53	24.63	9.68	4.32
450	12.64	18.18	25.57	21.98	1.21	0.53	23.82	9.59	4.30
500	12.61	18.17	25.31	22.02	1.21	0.53	24.31	9.67	4.32
550	12.59	18.19	25.57	22.11	1.21	0.53	23.74	9.51	4.35
600	12.55	18.17	25.36	22.24	1.21	0.53	23.98	9.54	4.35
650	12.53	18.18	25.58	22.40	1.21	0.53	23.66	9.57	4.34
700	12.48	18.16	25.53	22.38	1.22	0.52	23.86	9.47	4.36
750	12.46	18.15	25.42	22.43	1.22	0.52	24.16	9.66	4.32
800	12.41	18.14	25.44	22.62	1.22	0.52	24.30	9.28	4.37
850	12.39	18.14	25.44	22.55	1.22	0.52	24.09	9.59	4.31
900	12.35	18.12	25.39	22.72	1.22	0.52	23.74	9.42	4.29
940	12.31	18.11	25.39	22.81	1.23	0.52	23.94	9.44	4.37
1000	12.27	18.11	25.54	22.89	1.23	0.51	23.44	9.28	4.28
1050	12.23	18.09	25.96	23.06	1.23	0.51	23.67	9.26	4.35
1100	12.19	18.08	26.01	23.02	1.23	0.51	23.13	9.26	4.36
1150	12.14	18.07	26.11	23.14	1.24	0.51	23.20	9.11	4.43
1200	12.08	18.06	26.48	23.09	1.24	0.50	22.90	9.08	4.39
1250	12.04	18.06	26.64	23.28	1.24	0.50	23.20	8.94	4.38
1300	12.01	18.03	27.17	22.98	1.24	0.50	22.91	8.97	4.50
1350	11.95	18.02	27.61	22.92	1.25	0.50	23.09	8.88	4.48
1400	11.88	18.00	27.49	22.65	1.25	0.49	22.63	9.04	4.44
1450	11.82	17.98	28.03	22.38	1.25	0.49	22.67	8.93	4.49
1500	11.80	17.97	28.35	21.97	1.25	0.49	22.63	8.95	4.55
1550	11.72	17.96	28.47	21.84	1.26	0.49	22.82	8.74	4.48
1600	11.67	17.96	28.59	21.40	1.26	0.48	22.79	8.73	4.50
1650	11.60	17.92	28.81	20.99	1.26	0.48	22.79	8.68	4.47
1700	11.53	17.91	28.55	20.77	1.27	0.48	22.86	8.55	4.52
1750	11.47	17.88	28.46	20.26	1.27	0.47	22.56	8.50	4.46
1800	11.42	17.89	28.54	20.04	1.27	0.47	22.30	8.58	4.45
1850	11.36	17.85	28.54	19.66	1.28	0.47	21.65	8.34	4.48
1900	11.28	17.85	27.96	19.40	1.28	0.47	21.51	8.27	4.44
1950	11.21	17.80	27.48	19.07	1.28	0.46	21.42	8.27	4.43
2000	11.16	17.81	26.99	18.76	1.29	0.46	21.30	8.14	4.45

REV. X1

MAR-3+

070907

Page 8 of 11



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED RoHS compliant  
 P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see



*Typical Performance Data***Definitions:**

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Icc = 42mA, Vd = 4.78V @ Temperature = +85degC

FREQ (MHz)	Gain (dB)	Isolation (dB)	Input Return Loss (dB)	Output Return Loss (dB)	Stability		IP3 Output (dBm)	1dB Comp. Output (dBm)	Noise Figure (dB)
					K	Delta			
50	13.23	18.48	31.76	26.34	1.19	0.55	30.82	12.12	4.31
100	13.23	18.45	33.77	27.76	1.18	0.55	31.94	12.15	4.32
150	13.21	18.44	36.76	28.80	1.19	0.55	32.31	12.11	4.34
200	13.19	18.47	37.93	29.46	1.19	0.54	35.99	12.10	4.37
250	13.17	18.47	38.12	29.07	1.19	0.54	32.39	12.21	4.34
300	13.14	18.47	35.83	28.01	1.19	0.54	35.75	11.90	4.38
350	13.12	18.48	33.92	27.22	1.20	0.54	34.96	12.26	4.44
400	13.09	18.47	32.36	26.45	1.20	0.54	34.67	11.78	4.37
450	13.08	18.48	31.99	26.40	1.20	0.54	32.38	12.23	4.40
500	13.05	18.48	31.59	26.03	1.20	0.54	32.76	11.96	4.37
550	13.00	18.47	31.95	26.20	1.20	0.53	31.57	12.01	4.43
600	12.99	18.48	31.65	26.09	1.20	0.53	31.41	11.93	4.43
650	12.96	18.46	32.04	26.17	1.21	0.53	30.51	11.88	4.43
700	12.92	18.45	32.03	26.03	1.21	0.53	30.66	11.88	4.45
750	12.88	18.45	31.68	25.82	1.21	0.53	30.60	11.78	4.44
800	12.85	18.43	31.85	25.67	1.21	0.53	30.67	11.96	4.45
850	12.79	18.42	31.63	25.46	1.22	0.52	30.02	11.82	4.41
900	12.76	18.42	31.69	25.41	1.22	0.52	29.74	11.73	4.42
940	12.73	18.42	31.79	25.24	1.22	0.52	29.56	11.67	4.44
1000	12.67	18.41	32.01	25.05	1.22	0.52	28.74	11.63	4.40
1050	12.63	18.38	32.90	24.76	1.22	0.52	28.30	11.49	4.41
1100	12.58	18.35	33.04	24.49	1.22	0.51	27.93	11.37	4.46
1150	12.55	18.36	33.34	24.28	1.23	0.51	27.41	11.23	4.53
1200	12.48	18.37	34.20	23.85	1.23	0.51	27.34	10.99	4.53
1250	12.43	18.34	34.48	23.71	1.24	0.51	27.35	10.96	4.51
1300	12.38	18.33	35.87	23.10	1.24	0.50	26.83	10.87	4.58
1350	12.33	18.30	37.28	22.82	1.24	0.50	26.67	10.86	4.54
1400	12.27	18.28	36.98	22.24	1.24	0.50	26.29	10.78	4.55
1450	12.21	18.27	38.08	21.80	1.25	0.50	26.33	10.64	4.63
1500	12.16	18.26	38.44	21.22	1.25	0.49	26.18	10.61	4.66
1550	12.10	18.27	39.09	21.02	1.25	0.49	26.41	10.51	4.60
1600	12.03	18.24	37.74	20.46	1.26	0.49	26.26	10.27	4.64
1650	11.96	18.22	37.39	20.01	1.26	0.48	26.10	10.41	4.60
1700	11.90	18.20	36.31	19.71	1.26	0.48	25.95	10.14	4.61
1750	11.85	18.19	34.74	19.21	1.26	0.48	25.40	10.13	4.59
1800	11.77	18.18	33.96	18.97	1.27	0.48	24.97	9.94	4.58
1850	11.70	18.15	33.37	18.52	1.27	0.47	24.18	9.96	4.55
1900	11.65	18.14	31.81	18.29	1.27	0.47	24.10	9.70	4.55
1950	11.58	18.14	31.11	17.99	1.28	0.47	23.88	9.74	4.52
2000	11.51	18.12	30.16	17.70	1.28	0.47	23.82	9.58	4.57

REV. X1

MAR-3+

070907

Page 9 of 11



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED RoHS compliant  
 P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661




The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see




## Typical Performance Curves


GAIN vs. TEMPERATURE




GAIN vs. CURRENT




ISOLATION vs. TEMPERATURE




ISOLATION vs. CURRENT




INPUT RETURN LOSS vs. TEMPERATURE




INPUT RETURN LOSS vs. CURRENT



OUTPUT RETURN LOSS vs. TEMPERATURE




OUTPUT RETURN LOSS vs. CURRENT




## Typical Performance Curves


OUTPUT IP3 vs. TEMPERATURE




OUTPUT IP-3 vs. CURRENT




OUTPUT POWER at 1dB Compression vs. TEMPERATURE




OUTPUT POWER at 1dB Compression vs. CURRENT



Noise Figure vs. TEMPERATURE



Noise Figure vs. CURRENT



REV. X1

MAR-3+

070907

Page 11 of 11



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED RoHS compliant  
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661


Mouser Electronics Patent Pending The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see [minicircuits.com](http://minicircuits.com)

# MMIC Amplifier


MAR-3+

## Typical Performance Curves


GAIN vs. TEMPERATURE




GAIN vs. CURRENT




ISOLATION vs. TEMPERATURE




ISOLATION vs. CURRENT




INPUT RETURN LOSS vs. TEMPERATURE




INPUT RETURN LOSS vs. CURRENT



OUTPUT RETURN LOSS vs. TEMPERATURE




OUTPUT RETURN LOSS vs. CURRENT




## Typical Performance Curves


OUTPUT IP3 vs. TEMPERATURE




OUTPUT IP-3 vs. CURRENT




OUTPUT POWER at 1dB Compression vs. TEMPERATURE




OUTPUT POWER at 1dB Compression vs. CURRENT



Noise Figure vs. TEMPERATURE



Noise Figure vs. CURRENT



REV. X1

MAR-3+

070907

Page 2 of 2



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED RoHS compliant  
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661


Mouser Electronics Patent Pending The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see [minicircuits.com](http://minicircuits.com)

# Case Style

V V

VV105

## Outline Dimensions



CASE#	A	B	C	D	E	F	G	WT.GRAMS
VV105	.085 (2.16)	.060 (1.52)	.008 (0.20)	.020 (0.51)	.250 (6.35)	.012 (0.30)	.025 (0.64)	.015

Dimensions are in inches (mm). Tolerances: 2 Pl.  $\pm .03$ ; 3 Pl.  $\pm .015$

### Notes:

1. Case material: Plastic.
2. Termination finish:
  - For RoHS Case Styles: Tin-Silver alloy plate over Nickel barrier.
  - For RoHS-5 Case Styles: Tin-Lead plate.
3. RF input termination (1) identified by one or both of the following at factory option:
  - (a) diagonally cut termination, which be  $45^\circ$  (ref) in either direction;
  - (b) orientation mark on the case. Model dash number is identified by color dot or alphanumeric code on case. See specification data sheet.
4. Special Tolerances: Termination width  $\pm .005$  inch, termination thickness  $\pm .003$  inch.

 **Mini-Circuits**<sup>®</sup>


*Distribution Centers* NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified

INTERNET <http://www.minicircuits.com>

# Tape & Reel Packaging TR-F4

## DEVICE ORIENTATION IN T&R



Tape Width, mm	Device Cavity Pitch, mm	Reel Size, inches	Devices per Reel	
12	8	7	Small quantity standards (see note)	20
			7	500
		7	Standard	1000

Note: Please Consult individual model data sheet to determine device per reel availability.

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: [www.minicircuits.com/pages/pdfs/tape.pdf](http://www.minicircuits.com/pages/pdfs/tape.pdf)




Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Mini-Circuits ISO 9001 & ISO 14001 Certified


## THIRD ANGLE PROJECTION



## REVIEWS

REV OR	ECN No.	DESCRIPTION	DATE	DR	AUTH
	M109082	NEW RELEASE	12/29/06	AV	IG

SUGGESTED MOUNTING CONFIGURATION FOR  
VV105 CASE STYLE, "cb" PIN CONNECTION

NOTES:

1. TRACE WIDTH IS SHOWN FOR ROGERS R04350B WITH DIELECTRIC THICKNESS  $.030" \pm .002"$ ; COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.



DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)



DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

## UNLESS OTHERWISE SPECIFIED

DIMENSIONS ARE IN INCHES

TOLERANCES ON:

2 PL DECIMALS  $\pm .005$ 3 PL DECIMALS  $\pm .005$ ANGLES  $\pm .5^\circ$ FRACTIONS  $\pm .005$ 

## INITIALS

DRAWN

CHECKED


APPROVED

## DATE

12/28/06

12/29/06

12/29/06



THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS.  
EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE  
AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY  
DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO.  
THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE  
PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.

ASHEETA1.DWG REV:A DATE:01/12/95




**Mini-Circuits®**

13 Neptune Avenue  
Brooklyn NY 11235


PL, cb, VV105, MAR, TB-432-X+

SIZE	CODE IDENT	DRAWING NO:	REV:
A	15542	98-PL-262	OR
FILE: 98PL262	SCALE: 8:1	SHEET: 1 OF 1	

# Evaluation Board and Circuit



TB-432-3+



COMPONENT	VALUE
A1	MAR-3(+)
C1 (NOTE 4)	2400 pF
C2 (NOTE 4)	2400 pF
C3 (bypass)	0.1 uF
R1	200 Ohms, 0.75W
R2	0 Ohm, 0.25W
CHK	Mini-Circuits TCCH-80+

Schematic Diagram

NOTE:

1. Vcc voltage:  $+12 \pm 0.2\text{V}$ .
2. SMA Female connectors.
3. PCB material: Rogers R04350 or equivalent, dielectric constant=3.5, dielectric thickness=.030 inch.
4. Capacitors, C1 & C2 should be free of resonance up to the highest frequency specified.

 Mini-Circuits®



## Environmental Specifications

## ENV08T3

All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-40° to 85°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Thermal Shock	-55° to 100°C, 100 cycles	MIL-STD-202, Method 107, Condition A-3, except +100°C
Mechanical Shock	1.5Kg, 0.5 ms, 5 shock pulses, Y1 direction only	MIL-STD-883, Method 2002, Condition B, except Y1 direction only
Vibration (Variable Frequency)	50g peak	MIL-STD-883, Method 2007, Condition B
Autoclave	15 psig, 100% RH, 121°C, 96 hours	JESD22-A102, Condition C
HAST	130°C, 85% RH, 96 hours	JESD22-A110
Solderability	10X Magnification	J-STD-002, Para 4.2.5, Test S, 95% Coverage
Solder Reflow Heat	Sn-Pb Eutetic Process: 240°C peak Pb-Free Process: 260°C peak	J-STD-020, Table 4-1, 4-2 and 5-2; Figure 5-1
Moisture Sensitivity: Level 1	Bake at 125°C for 24 hours Soak at 85°C/85% RH for 168 hours, Reflow 3 cycles at 260°C peak	J-STD-020
Marking Resistance to Solvents	Isopropyl alcohol + mineral spirits at 25°C; terpene defluxer at 25°C; distilled water + propylene glycol monomethyl ether +	MIL-STD-202, Method 215



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
---------------	---------------------------	----------------

monoethanolamine at 63°C to 70°C