



Mini-Circuits

ULTRA HIGH DYNAMIC RANGE, SHUTDOWN

Monolithic Amplifier

TSS-23HLN+

50Ω

30 MHz to 2 GHz

THE BIG DEAL

- High IP3, 42.6 dBm typ. at 1GHz
- Gain, 21.8 dB typ. at 1 GHz
- Low noise figure, 1.4 dB at 1 GHz
- High P1dB, 28.5 dBm at 1 GHz
- Shutdown feature



Generic photo used for illustration purposes only

CASE STYLE: DQ1225

+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

APPLICATIONS

- Base station infrastructure
- CATV
- Cellular

PRODUCT OVERVIEW

TSS-23HLN+ (RoHS compliant) is an advanced wideband amplifier with shutdown feature. It is fabricated using E-PHEMT technology and offers extremely high dynamic range over a broad frequency range and with low noise figure. In addition, the TSS-23HLN+ has good input and output return loss over a broad frequency range. TSS-23HLN+ is enclosed in a 3mm x 3mm, 12-lead MCLP package and has very good thermal performance.

KEY FEATURES

Feature	Advantages
Broad Band: 30MHz to 2GHz	Broadband covering primary wireless communications bands: VHF, UHF, Cellular
Extremely High IP3 39.6 dBm typical at 30 MHz 42.6 dBm typical at 1GHz	The TSS-23HLN+ matches industry leading IP3 performance relative to device size and power consumption. The combination of the design and E-PHEMT Structure provides enhanced linearity over a broad frequency range as evidence in the IP3 being approximately 13-15 dB above the P1dB point. This feature makes this amplifier ideal for use in: <ul style="list-style-type: none"> • Driver amplifiers for complex waveform up converter paths • Drivers in linearized transmit systems • Secondary amplifiers in ultra-High Dynamic range receivers
Shutdown feature	Allow users to turn on and off the amplifier with pulsed signals while keeping the power supply at constant voltage to minimize DC power consumption
Low Noise Figure 1.4 dB at 1 GHz	Enables lower system noise figure performance and along with High OIP3 provides high dynamic range
High P1dB , 28.5 dBm at 1 GHz	High P1dB, High OIP3, Low NF results in a very dynamic range preventing amplifier saturation under strong interfering signals.

REV. A
ECO-011809
TSS-23HLN+
GY/RS/CP
220126



Mini-Circuits

ULTRA HIGH DYNAMIC RANGE, SHUTDOWN

Monolithic Amplifier

TSS-23HLN+

ELECTRICAL SPECIFICATIONS¹ AT 25°C & 50Ω, UNLESS NOTED OTHERWISE

Parameter	Condition (MHz)	Amplifier-ON VDD = 8V			Amplifier-OFF VDD = 8V	Units
		Min.	Typ.	Max.		
Frequency Range		30	1.4	2000	30-2000	MHz
Noise Figure	30	1.4	—	—	dB	
	500	1.4	—	—		
	1000	1.4	—	—		
	1500	1.5	—	—		
	2000	1.6	—	—		
Gain	30	20.9	23.3	25.5	-21	dB
	500	—	22.4	—	-21	
	1000	19.5	21.8	23.8	-23	
	1500	—	21.1	—	-25	
	2000	18.1	20.3	22.1	-28	
Reversed Isolation	30-2000		27		26	dB
Input Return Loss	30		11		12	dB
	500		12		12	
	1000		10		12	
	1500		11		15	
	2000		12		20	
Output Return Loss	30		15		2	dB
	500		14		2	
	1000		12		2	
	1500		10		2	
	2000		8		2	
Output Power @1dB compression AMP-ON	30		26.2			dBm
	500		27.9			
	1000		28.5			
	1500		28.1			
	2000		27.7			
Output IP3 (Pout = 0dBm/Tone)	30	—	39.6			dBm
	500	—	41.6			
	1000	—	42.6			
	1500	38.2	42.6			
	2000	—	41.8			
Device Operating Voltage (VDD)		7.6	8	8.4	8	V
Device Operating Current (ID)			236	249	8	mA
Control Voltage (VG)			0		5	V
DC Current (ID) Variation Vs. Temperature ²			-225			uA/degC
DC Current (ID) Variation Vs. Voltage			0.0263			mA/mV
Thermal Resistance			23.3			degC/W

1. Measured on Mini-Circuits Characterization test board TB-TSS-23HLN+. See Characterization Test Circuit (Fig. 1)

2. (Current at 95°C — Current at -45°C)/140

MAXIMUM RATINGS³

Parameter	Ratings
Operating Temperature (ground lead)	-40°C to 95°C
Storage Temperature	-65°C to 150°C
Total Power Dissipation	3.3W
Input Power	28 dBm (5 minutes max.) 15 dBm (continuos) for 0.03-1 GHz 18 dBm (continuos) for 1-2 GHz
DC Voltage V _{DD} ⁴ (Pad 7)	10V
DC Voltage V _G ⁵ (Pad 1)	10V

CONTROL VOLTAGE (V_G) FIG. 1

	Min.	Typ.	Max.	Units
Amplifier-ON	—	0	0.7	V
Amplifier-OFF	1.9	5	—	V

3 Permanent damage may occur if these limits are exceeded.

4 Measured by keeping VG=0V.

5 Measured by keeping Vdd=8V.

Mini-Circuits®

www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

PAGE 2 OF 5



ULTRA HIGH DYNAMIC RANGE, SHUTDOWN


Monolithic Amplifier

TSS-23HLN+

Mini-Circuits®

SWITCHING SPECIFICATIONS

Parameter		Min.	Typ.	Max.	Units
Amplifier ON to Shutdown	OFF TIME (50% Control to 10% RF)	—	5.3	—	μs
	FALL TIME (90 to 10% RF)	—	7.3	—	
Amplifier Shutdown to ON	ON TIME (50% Control to 90% RF)	—	77.7	—	μs
	RISE TIME (10% to 90% RF)	—	54.2	—	
Control Voltage Leakage		—	633.3	—	mV

SIMPLIFIED SCHEMATIC AND PAD DESCRIPTION

Function	Pad Number	Description
RF-IN	3	RF Input
RF-OUT and DC-IN	7	RF Output and DC Bias
GND	Paddle	Connections to ground.
NC	2, 4-6, 8-12	No connection, grounded externally
VG	1	Control voltage for shutdown (VG)

Mini-Circuits®

www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

PAGE 3 OF 5




ULTRA HIGH DYNAMIC RANGE, SHUTDOWN

Monolithic Amplifier

TSS-23HLN+

Mini-Circuits®

CHARACTERIZATION TEST CIRCUIT / RECOMMENDED APPLICATION CIRCUIT



Component	Size	Value	Part Number	Manufacturer
C1	0402	0.1uF	GRM155R71C104KA88D	Murata
C2	0402	1.5pF	GRM1555C1H1R5CA1D	Murata
C3	0603	2.2uF	GRM188C71E225KE11D	Murata
C4	0402	0.1uF	GRM155R71C104KA88D	Murata
C5	0603	2.2uF	GRM188C71E225KE11D	Murata
C6	0402	1000pF	GRM1555C1H102JA01D	Murata
C7	0805	10uF	GRM21BC71E106KE11L	Murata
L1	1210	15uH	LQH32DN150K53L	Murata
L2	0603	5.1nH	0603CS-5N1XJLU	Coilcraft
R1	0402	1.5KOhm	RK73H1ETTP1501F	Koa

Fig 1. Block diagram of Test Circuit used for characterization. (DUT soldered on Mini-Circuits Characterization test board TB-TSS-13LN+) Gain, Return loss, Output power at 1dB compression (P1dB), output IP3 (OIP3) and noise figure measured using Agilent's N5242A PNA-X microwave network analyzer.

Conditions:

1. Gain and Return Loss: Pin= -25dBm
2. Output IP3 (OIP3): Two tones, spaced 1 MHz apart, +0dBm/tone at output.
3. Switching Time

RF Signal: Pin=-25 dBm, fRF=500 MHz.

Vdd=8V DC, VG=Pulse signal at 1 KHz with VHIGH=5V, VLOW=0V, 50% duty cycle.

PRODUCT MARKING



Marking may contain other features or characters for internal lot control



Mini-Circuits®

ULTRA HIGH DYNAMIC RANGE, SHUTDOWN

Monolithic Amplifier

TSS-23HLN+


ADDITIONAL DETAILED TECHNICAL INFORMATION IS AVAILABLE ON OUR DASH BOARD. TO ACCESS [CLICK HERE](#)

Performance Data	Data Table Swept Graphs S-Parameter (S2P Files) Data Set (.zip file)
Case Style	DQ1225 Plastic package, exposed paddle lead finish: Matte-Tin
Tape & Reel Standard quantities available on reel	F66 7" reels with 20, 50, 100, 200, 500, 1K, or 2K devices
Suggested Layout for PCB Design	PL-619
Evaluation Board	TB-TSS-23HLN+
Environmental Ratings	ENV08T9

ESD RATING

Human Body Model (HBM): Class 1A (Pass 250 V) in accordance with ANSI/ESD STM 5.1 - 2001

MSL FLOW CHART



NOTES

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the standard. Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

Typical Performance Data

Definitions:

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 8.00V, Id = 236mA @ Temperature = +25°C

FREQ (MHz)	Gain (dB)	Isolation (dB)	Input Return Loss (dB)	Output Return Loss (dB)	Stability		IP-3 Output (dBm)	1dB Comp. Output (dBm)	Noise Figure (dB)
					K	Measure			
20	23.65	26.47	10.44	14.98	1.02	0.46	37.83	26.16	1.52
30	23.29	26.02	11.37	14.91	1.02	0.45	39.91	26.25	1.73
40	23.06	25.93	11.78	14.24	1.03	0.45	40.11	27.45	1.35
50	22.89	25.32	11.99	13.75	1.02	0.38	39.72	27.75	1.37
60	22.82	25.64	12.17	13.61	1.03	0.43	41.71	27.43	1.36
70	22.76	25.68	12.28	13.43	1.03	0.43	47.00	27.26	1.35
80	22.71	25.61	12.32	13.36	1.03	0.43	46.38	27.52	1.38
90	22.68	25.60	12.36	13.31	1.03	0.43	41.24	27.87	1.42
100	22.66	25.63	12.40	13.25	1.04	0.43	39.34	27.57	1.42
150	22.59	25.59	12.46	13.18	1.04	0.43	42.26	27.69	1.38
200	22.55	25.61	12.45	13.16	1.04	0.44	43.06	27.80	1.40
250	22.52	25.66	12.40	13.20	1.04	0.45	40.83	27.90	1.36
300	22.49	25.69	12.37	13.22	1.05	0.46	41.47	28.06	1.38
350	22.46	25.77	12.26	13.25	1.05	0.47	38.36	28.08	1.38
400	22.43	25.78	12.16	13.30	1.05	0.48	40.73	28.09	1.42
450	22.39	25.91	12.03	13.32	1.06	0.50	41.80	27.94	1.39
500	22.35	25.92	11.82	13.37	1.06	0.50	42.10	27.86	1.40
550	22.30	26.07	11.67	13.35	1.07	0.53	44.94	28.18	1.40
600	22.25	26.20	11.45	13.33	1.07	0.55	41.73	28.04	1.47
650	22.19	26.28	11.23	13.26	1.08	0.56	42.95	28.15	1.47
700	22.14	26.37	11.05	13.17	1.08	0.57	40.51	28.06	1.45
750	22.06	26.45	10.85	13.04	1.09	0.59	44.14	27.98	1.42
800	21.99	26.62	10.69	12.92	1.10	0.61	42.21	27.96	1.42
850	21.92	26.74	10.55	12.79	1.10	0.63	41.75	28.15	1.42
900	21.86	26.88	10.39	12.62	1.11	0.64	43.41	28.12	1.42
950	21.79	26.99	10.23	12.45	1.12	0.65	42.74	28.16	1.44
1000	21.72	27.09	10.12	12.21	1.13	0.67	41.51	28.43	1.41
1100	21.57	27.41	9.95	11.73	1.15	0.69	42.36	28.22	1.47
1200	21.43	27.69	9.90	11.22	1.17	0.71	43.66	28.30	1.47
1300	21.28	27.98	10.01	10.73	1.19	0.73	41.50	28.20	1.51
1400	21.15	28.31	10.21	10.26	1.22	0.74	41.93	28.13	1.51
1500	21.03	28.63	10.55	9.79	1.25	0.75	42.47	28.10	1.51
1600	20.91	28.87	11.03	9.39	1.27	0.75	42.06	27.93	1.54
1700	20.80	29.23	11.64	9.03	1.31	0.76	42.90	27.39	1.54
1800	20.67	29.57	12.31	8.73	1.34	0.77	43.16	28.00	1.56
1900	20.53	29.89	12.83	8.45	1.37	0.78	44.21	27.78	1.62
2000	20.35	30.38	12.93	8.21	1.42	0.80	41.42	27.69	1.67
2100	20.13	30.85	12.33	7.97	1.47	0.83	40.45	27.51	1.76
2200	19.85	31.39	11.10	7.77	1.51	0.86	41.81	27.48	1.91
2300	19.48	32.02	9.61	7.55	1.57	0.91	43.52	27.23	2.06
2400	19.04	32.62	8.14	7.32	1.62	0.95	43.56	26.77	2.30
2500	18.51	33.30	6.82	7.07	1.67	1.00	45.11	27.22	2.56

Typical Performance Data

Definitions:

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 7.60V, Id = 224mA @ Temperature = +25°C

FREQ (MHz)	Gain (dB)	Isolation (dB)	Input Return Loss (dB)	Output Return Loss (dB)	Stability		IP-3 Output (dBm)	1dB Comp. Output (dBm)	Noise Figure (dB)
					K	Measure			
20	23.64	26.42	10.43	14.93	1.02	0.46	37.10	25.81	1.43
30	23.29	26.11	11.40	14.80	1.02	0.46	37.46	25.89	1.34
40	23.06	25.81	11.84	14.20	1.02	0.43	42.33	27.04	1.29
50	22.88	26.31	12.33	13.56	1.05	0.50	38.72	27.41	1.33
60	22.82	25.68	12.28	13.54	1.03	0.43	42.21	27.07	1.30
70	22.76	25.60	12.37	13.37	1.03	0.42	41.75	26.92	1.30
80	22.71	25.55	12.41	13.31	1.03	0.42	39.46	27.17	1.34
90	22.68	25.60	12.48	13.23	1.04	0.43	43.53	27.22	1.36
100	22.66	25.54	12.51	13.20	1.03	0.42	37.86	27.20	1.34
150	22.59	25.59	12.56	13.09	1.04	0.43	42.24	27.31	1.42
200	22.55	25.61	12.57	13.12	1.04	0.44	42.46	27.45	1.37
250	22.52	25.58	12.54	13.19	1.04	0.44	38.55	27.57	1.34
300	22.49	25.64	12.51	13.21	1.05	0.45	41.92	27.73	1.32
350	22.46	25.68	12.41	13.30	1.05	0.46	41.61	27.71	1.35
400	22.43	25.84	12.30	13.36	1.05	0.48	41.84	27.72	1.38
450	22.40	25.86	12.16	13.43	1.06	0.49	43.02	27.61	1.34
500	22.35	25.91	11.95	13.52	1.06	0.51	42.72	27.47	1.37
550	22.30	26.04	11.76	13.52	1.07	0.53	44.56	27.81	1.39
600	22.25	26.16	11.55	13.55	1.07	0.55	47.18	27.72	1.43
650	22.19	26.23	11.34	13.49	1.08	0.56	41.99	27.76	1.43
700	22.13	26.38	11.14	13.40	1.08	0.58	43.66	27.68	1.40
750	22.06	26.47	10.93	13.31	1.09	0.60	42.19	27.59	1.40
800	21.99	26.63	10.78	13.16	1.10	0.62	42.07	27.56	1.41
850	21.92	26.74	10.63	13.04	1.11	0.63	42.16	27.83	1.41
900	21.86	26.83	10.46	12.86	1.11	0.64	40.39	27.72	1.40
950	21.79	26.98	10.31	12.66	1.12	0.66	42.83	27.75	1.41
1000	21.73	27.11	10.20	12.41	1.13	0.67	42.72	28.04	1.37
1100	21.58	27.37	10.04	11.90	1.15	0.69	41.55	27.85	1.43
1200	21.44	27.63	10.02	11.38	1.17	0.71	43.81	27.93	1.46
1300	21.30	27.95	10.14	10.84	1.19	0.73	41.71	27.82	1.43
1400	21.17	28.20	10.36	10.36	1.21	0.74	44.66	27.76	1.49
1500	21.06	28.49	10.71	9.88	1.24	0.74	43.71	27.81	1.50
1600	20.94	28.78	11.18	9.48	1.26	0.75	41.74	27.56	1.49
1700	20.83	29.16	11.75	9.15	1.30	0.76	45.53	26.99	1.50
1800	20.70	29.46	12.32	8.85	1.33	0.77	44.51	27.65	1.51
1900	20.55	29.85	12.68	8.57	1.36	0.79	43.38	27.42	1.55
2000	20.36	30.28	12.55	8.34	1.40	0.81	43.23	27.32	1.60
2100	20.13	30.67	11.83	8.12	1.43	0.84	42.43	27.13	1.72
2200	19.85	31.25	10.61	7.90	1.48	0.88	43.11	27.07	1.83
2300	19.48	31.89	9.21	7.68	1.54	0.92	41.64	26.82	1.97
2400	19.05	32.54	7.83	7.45	1.59	0.97	41.69	26.24	2.17
2500	18.54	33.13	6.58	7.19	1.61	1.02	42.32	26.73	2.47



ISO 9001 ISO 14001 AS 9100 CERTIFIED

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site

The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

IF/RF MICROWAVE COMPONENTS



REV. OR

TSS-23HLN+

2/26/2019

Page 2 of 9

Typical Performance Data

Definitions:

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 8.40V, Id = 245mA @ Temperature = +25°C

FREQ (MHz)	Gain (dB)	Isolation (dB)	Input Return Loss (dB)	Output Return Loss (dB)	Stability		IP-3 Output (dBm)	1dB Comp. Output (dBm)	Noise Figure (dB)
					K	Measure			
20	23.61	26.56	10.45	15.05	1.02	0.48	36.92	26.78	1.58
30	23.26	26.14	11.38	14.95	1.02	0.47	40.85	26.80	1.45
40	23.03	25.84	11.79	14.35	1.02	0.44	38.34	28.15	1.42
50	22.86	26.24	11.99	13.68	1.05	0.50	40.17	28.31	1.45
60	22.79	25.72	12.18	13.67	1.03	0.44	39.45	28.03	1.43
70	22.73	25.68	12.26	13.50	1.03	0.44	42.62	27.78	1.42
80	22.69	25.56	12.32	13.43	1.03	0.42	41.87	28.20	1.45
90	22.66	25.65	12.36	13.35	1.04	0.44	40.70	28.50	1.47
100	22.63	25.59	12.37	13.31	1.04	0.43	38.77	28.06	1.50
150	22.57	25.66	12.45	13.21	1.04	0.44	41.54	28.32	1.53
200	22.52	25.65	12.45	13.20	1.04	0.45	39.84	28.43	1.46
250	22.49	25.60	12.41	13.27	1.04	0.45	38.43	28.52	1.46
300	22.47	25.67	12.38	13.27	1.05	0.46	41.71	28.68	1.47
350	22.43	25.69	12.28	13.32	1.05	0.47	41.32	28.70	1.49
400	22.40	25.81	12.18	13.35	1.05	0.48	41.08	28.71	1.49
450	22.37	25.88	12.07	13.38	1.06	0.50	42.61	28.60	1.47
500	22.32	26.00	11.84	13.43	1.06	0.52	42.73	28.50	1.47
550	22.28	26.08	11.67	13.39	1.07	0.53	42.93	28.79	1.50
600	22.22	26.17	11.46	13.38	1.07	0.55	42.51	28.73	1.53
650	22.16	26.30	11.25	13.28	1.08	0.57	40.91	28.83	1.56
700	22.11	26.47	11.08	13.15	1.09	0.59	43.00	28.71	1.53
750	22.03	26.56	10.87	13.04	1.09	0.60	41.92	28.64	1.49
800	21.96	26.69	10.71	12.87	1.10	0.62	42.55	28.68	1.52
850	21.89	26.82	10.58	12.72	1.11	0.63	43.78	28.83	1.52
900	21.83	26.90	10.42	12.52	1.12	0.64	42.43	28.80	1.52
950	21.77	26.99	10.28	12.31	1.12	0.65	42.76	28.88	1.53
1000	21.70	27.19	10.17	12.07	1.13	0.67	41.46	29.05	1.50
1100	21.55	27.46	10.03	11.54	1.15	0.69	44.14	28.83	1.55
1200	21.41	27.70	10.01	11.03	1.17	0.71	41.99	28.91	1.57
1300	21.28	28.01	10.12	10.51	1.19	0.72	40.31	28.83	1.56
1400	21.15	28.32	10.35	10.05	1.22	0.73	41.65	28.74	1.62
1500	21.03	28.62	10.71	9.58	1.25	0.74	41.73	28.69	1.59
1600	20.92	28.94	11.17	9.21	1.28	0.75	41.42	28.54	1.64
1700	20.80	29.25	11.73	8.88	1.30	0.76	42.42	28.09	1.65
1800	20.67	29.56	12.29	8.58	1.33	0.76	43.53	28.60	1.63
1900	20.52	29.87	12.62	8.31	1.36	0.78	39.87	28.36	1.68
2000	20.33	30.45	12.46	8.08	1.42	0.81	42.01	28.27	1.73
2100	20.10	30.94	11.72	7.85	1.46	0.83	40.20	28.08	1.81
2200	19.81	31.50	10.51	7.62	1.51	0.87	42.19	28.07	1.93
2300	19.44	32.08	9.11	7.40	1.55	0.91	44.11	27.80	2.15
2400	19.00	32.70	7.74	7.16	1.59	0.96	43.76	27.36	2.34
2500	18.49	33.34	6.53	6.90	1.63	1.00	40.11	27.67	2.63



ISO 9001 ISO 14001 AS 9100 CERTIFIED

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site

The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

REV. OR

TSS-23HLN+

2/26/2019

Page 3 of 9

Typical Performance Data

Definitions:

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 8.00V, Id = 242mA @ Temperature = -45°C

FREQ (MHz)	Gain (dB)	Isolation (dB)	Input Return Loss (dB)	Output Return Loss (dB)	Stability		IP-3 Output (dBm)	1dB Comp. Output (dBm)	Noise Figure (dB)
					K	Measure			
20	23.76	26.40	10.24	14.93	1.01	0.45	36.70	26.47	1.33
30	23.41	26.06	11.31	14.74	1.02	0.44	39.75	26.41	1.16
40	23.18	25.80	11.81	14.16	1.02	0.42	44.92	27.86	1.06
50	23.01	26.39	12.26	13.53	1.05	0.49	43.08	28.32	1.09
60	22.94	25.62	12.31	13.50	1.03	0.41	43.00	27.83	1.07
70	22.88	25.53	12.43	13.35	1.03	0.40	43.45	27.50	1.08
80	22.83	25.55	12.49	13.31	1.03	0.40	42.89	27.90	1.07
90	22.81	25.53	12.59	13.26	1.03	0.40	40.72	28.37	1.09
100	22.78	25.51	12.64	13.24	1.03	0.40	38.32	27.93	1.09
150	22.72	25.54	12.82	13.20	1.03	0.41	43.53	28.03	1.09
200	22.68	25.56	12.81	13.19	1.04	0.42	43.68	28.14	1.09
250	22.66	25.57	12.77	13.18	1.04	0.42	37.64	28.35	1.08
300	22.64	25.63	12.71	13.15	1.04	0.43	44.39	28.51	1.11
350	22.61	25.66	12.61	13.17	1.04	0.44	38.24	28.53	1.11
400	22.58	25.74	12.55	13.23	1.05	0.45	40.29	28.49	1.12
450	22.56	25.78	12.47	13.30	1.05	0.46	42.85	28.34	1.06
500	22.52	25.85	12.27	13.35	1.05	0.47	41.88	28.23	1.08
550	22.48	25.93	12.13	13.36	1.06	0.49	42.93	28.62	1.11
600	22.44	25.96	11.93	13.35	1.06	0.50	42.94	28.44	1.12
650	22.39	26.14	11.73	13.32	1.07	0.52	42.64	28.57	1.12
700	22.34	26.20	11.58	13.23	1.07	0.53	44.02	28.47	1.11
750	22.28	26.38	11.37	13.13	1.08	0.56	45.53	28.31	1.10
800	22.21	26.49	11.23	13.01	1.08	0.57	44.99	28.37	1.12
850	22.15	26.58	11.13	12.91	1.09	0.59	43.21	28.62	1.12
900	22.10	26.67	10.97	12.78	1.10	0.60	42.90	28.58	1.13
950	22.04	26.75	10.83	12.63	1.10	0.61	42.39	28.50	1.13
1000	21.99	26.84	10.72	12.43	1.11	0.62	44.94	28.92	1.10
1100	21.86	27.18	10.57	11.96	1.13	0.65	41.04	28.80	1.12
1200	21.73	27.37	10.56	11.49	1.14	0.67	44.10	28.96	1.15
1300	21.61	27.66	10.68	10.99	1.16	0.68	45.50	28.76	1.14
1400	21.50	27.93	10.91	10.52	1.18	0.70	43.04	28.72	1.19
1500	21.39	28.22	11.29	10.06	1.20	0.71	41.48	28.82	1.19
1600	21.28	28.52	11.83	9.68	1.23	0.72	43.12	28.62	1.16
1700	21.18	28.77	12.51	9.35	1.25	0.72	41.84	27.96	1.14
1800	21.07	29.15	13.25	9.07	1.28	0.74	42.12	28.65	1.16
1900	20.95	29.54	13.79	8.82	1.32	0.76	42.87	28.52	1.21
2000	20.78	29.98	13.80	8.60	1.35	0.78	40.67	28.34	1.21
2100	20.59	30.35	13.07	8.40	1.38	0.81	41.24	28.31	1.28
2200	20.34	30.84	11.67	8.21	1.42	0.85	39.50	28.17	1.36
2300	20.02	31.40	10.04	8.00	1.45	0.90	39.92	28.01	1.51
2400	19.62	32.00	8.48	7.78	1.49	0.95	39.96	27.58	1.72
2500	19.16	32.78	7.10	7.52	1.54	1.00	40.53	27.99	1.85

*Typical Performance Data***Definitions:**

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 7.60V, Id = 229mA @ Temperature = -45°C

FREQ (MHz)	Gain (dB)	Isolation (dB)	Input Return Loss (dB)	Output Return Loss (dB)	Stability		IP-3 Output (dBm)	1dB Comp. Output (dBm)	Noise Figure (dB)
					K	Measure			
20	23.75	26.49	10.27	14.90	1.01	0.46	40.03	26.05	1.24
30	23.39	26.08	11.35	14.78	1.02	0.44	39.61	26.06	1.04
40	23.16	25.75	11.86	14.20	1.02	0.41	39.82	27.43	0.99
50	22.99	25.89	12.14	13.60	1.03	0.44	41.13	27.93	1.02
60	22.92	25.55	12.35	13.56	1.02	0.40	45.28	27.48	1.02
70	22.86	25.56	12.50	13.40	1.03	0.40	43.38	27.20	1.00
80	22.82	25.53	12.57	13.36	1.03	0.40	40.73	27.49	1.01
90	22.79	25.58	12.64	13.31	1.03	0.41	43.11	27.93	1.05
100	22.77	25.48	12.70	13.28	1.03	0.40	40.06	27.53	1.06
150	22.71	25.45	12.87	13.25	1.03	0.40	42.83	27.63	1.07
200	22.67	25.48	12.89	13.24	1.04	0.41	42.63	27.78	1.06
250	22.64	25.46	12.81	13.23	1.04	0.41	42.08	27.95	1.05
300	22.62	25.57	12.78	13.20	1.04	0.42	41.32	28.11	1.04
350	22.59	25.59	12.68	13.23	1.04	0.43	38.15	28.13	1.08
400	22.57	25.71	12.61	13.29	1.05	0.45	38.29	28.08	1.08
450	22.54	25.77	12.52	13.36	1.05	0.46	41.36	27.92	1.07
500	22.51	25.82	12.32	13.41	1.05	0.47	42.12	27.74	1.09
550	22.47	25.89	12.17	13.42	1.05	0.49	42.43	28.21	1.10
600	22.43	26.02	11.96	13.41	1.06	0.51	43.12	28.02	1.14
650	22.37	26.09	11.76	13.38	1.06	0.52	44.08	28.14	1.13
700	22.33	26.27	11.60	13.31	1.07	0.54	45.63	28.05	1.12
750	22.26	26.33	11.40	13.20	1.08	0.56	45.90	27.88	1.08
800	22.19	26.46	11.23	13.08	1.08	0.58	43.07	27.86	1.11
850	22.13	26.55	11.13	12.97	1.09	0.59	42.81	28.18	1.12
900	22.08	26.65	10.97	12.84	1.10	0.60	43.04	28.14	1.10
950	22.03	26.78	10.83	12.68	1.10	0.62	46.61	28.06	1.10
1000	21.97	26.88	10.71	12.47	1.11	0.63	46.20	28.48	1.07
1100	21.84	27.16	10.56	12.01	1.13	0.65	43.26	28.36	1.10
1200	21.72	27.38	10.55	11.51	1.14	0.67	43.83	28.52	1.15
1300	21.60	27.64	10.66	11.02	1.16	0.69	41.52	28.24	1.15
1400	21.48	27.92	10.89	10.54	1.18	0.70	43.74	28.27	1.17
1500	21.37	28.24	11.28	10.09	1.21	0.71	42.06	28.39	1.15
1600	21.27	28.50	11.81	9.70	1.23	0.72	41.84	28.11	1.17
1700	21.17	28.84	12.48	9.37	1.26	0.73	40.87	27.51	1.20
1800	21.06	29.10	13.23	9.08	1.28	0.74	42.61	28.22	1.15
1900	20.93	29.49	13.79	8.83	1.31	0.76	42.65	28.10	1.17
2000	20.77	29.89	13.82	8.62	1.35	0.78	41.28	27.91	1.26
2100	20.58	30.35	13.08	8.42	1.38	0.81	39.96	27.89	1.27
2200	20.33	30.86	11.69	8.22	1.42	0.85	40.48	27.66	1.39
2300	20.01	31.45	10.06	8.02	1.46	0.90	40.21	27.57	1.49
2400	19.62	32.03	8.50	7.80	1.50	0.95	39.05	27.12	1.64
2500	19.16	32.74	7.11	7.55	1.54	1.00	39.51	27.54	1.87



ISO 9001 ISO 14001 AS 9100 CERTIFIED

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site

The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

IF/RF MICROWAVE COMPONENTS



REV. OR

TSS-23HLN+

2/26/2019

Page 5 of 9

Typical Performance Data

Definitions:

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 8.40V, Id = 256mA @ Temperature = -45°C

FREQ (MHz)	Gain (dB)	Isolation (dB)	Input Return Loss (dB)	Output Return Loss (dB)	Stability		IP-3 Output (dBm)	1dB Comp. Output (dBm)	Noise Figure (dB)
					K	Measure			
20	23.77	26.34	10.29	14.88	1.01	0.43	38.76	26.89	1.42
30	23.42	26.09	11.27	14.68	1.02	0.44	35.66	26.72	1.20
40	23.19	25.81	11.77	14.11	1.02	0.42	44.16	28.29	1.11
50	23.02	26.34	12.06	13.46	1.04	0.49	40.90	28.68	1.11
60	22.95	25.68	12.23	13.46	1.03	0.41	40.73	28.22	1.10
70	22.89	25.65	12.36	13.32	1.03	0.41	43.31	27.82	1.08
80	22.85	25.59	12.43	13.26	1.03	0.41	42.59	28.28	1.12
90	22.82	25.58	12.50	13.20	1.03	0.41	40.91	28.78	1.10
100	22.79	25.53	12.56	13.19	1.03	0.40	39.33	28.20	1.12
150	22.73	25.53	12.71	13.16	1.03	0.41	40.96	28.40	1.10
200	22.69	25.58	12.75	13.14	1.04	0.42	40.96	28.54	1.10
250	22.67	25.53	12.66	13.13	1.04	0.41	39.02	28.71	1.10
300	22.65	25.62	12.64	13.09	1.04	0.43	40.90	28.88	1.10
350	22.62	25.65	12.55	13.13	1.04	0.43	39.89	28.90	1.13
400	22.59	25.80	12.48	13.17	1.05	0.46	39.03	28.90	1.14
450	22.57	25.79	12.39	13.25	1.05	0.46	39.88	28.76	1.07
500	22.53	25.86	12.22	13.29	1.05	0.47	44.15	28.59	1.10
550	22.49	25.92	12.06	13.31	1.05	0.49	44.06	29.04	1.12
600	22.44	26.04	11.88	13.29	1.06	0.50	42.22	28.87	1.15
650	22.40	26.13	11.69	13.25	1.06	0.52	44.07	29.00	1.18
700	22.35	26.26	11.54	13.17	1.07	0.54	43.51	28.85	1.14
750	22.28	26.40	11.34	13.08	1.08	0.56	41.09	28.75	1.12
800	22.22	26.49	11.19	12.95	1.08	0.57	43.88	28.74	1.14
850	22.15	26.56	11.10	12.86	1.09	0.59	42.62	29.06	1.16
900	22.10	26.75	10.95	12.73	1.10	0.61	44.80	29.03	1.16
950	22.05	26.80	10.81	12.57	1.10	0.61	41.84	28.95	1.17
1000	21.99	26.93	10.69	12.36	1.11	0.63	42.40	29.36	1.13
1100	21.86	27.16	10.56	11.90	1.12	0.65	44.37	29.24	1.16
1200	21.74	27.41	10.56	11.44	1.14	0.67	42.90	29.39	1.17
1300	21.62	27.70	10.67	10.94	1.16	0.69	41.76	29.21	1.19
1400	21.50	28.01	10.90	10.48	1.19	0.70	43.05	29.15	1.20
1500	21.39	28.28	11.30	10.02	1.21	0.71	44.15	29.25	1.18
1600	21.28	28.58	11.84	9.64	1.23	0.72	42.01	28.99	1.19
1700	21.18	28.88	12.51	9.31	1.26	0.73	41.41	28.41	1.22
1800	21.07	29.24	13.23	9.02	1.29	0.74	41.72	29.07	1.19
1900	20.95	29.51	13.76	8.77	1.31	0.76	41.63	28.88	1.23
2000	20.78	29.97	13.74	8.55	1.35	0.78	41.03	28.76	1.25
2100	20.58	30.49	12.98	8.35	1.40	0.82	41.53	28.72	1.31
2200	20.33	30.88	11.60	8.15	1.42	0.85	39.72	28.60	1.40
2300	20.00	31.45	9.97	7.95	1.46	0.90	40.61	28.44	1.52
2400	19.61	32.15	8.43	7.73	1.51	0.95	40.74	28.03	1.71
2500	19.15	32.84	7.05	7.47	1.55	1.00	40.13	28.38	1.86

Typical Performance Data

Definitions:

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 8.00V, Id = 211mA @ Temperature = +95°C

FREQ (MHz)	Gain (dB)	Isolation (dB)	Input Return Loss (dB)	Output Return Loss (dB)	Stability		IP-3 Output (dBm)	1dB Comp. Output (dBm)	Noise Figure (dB)
					K	Measure			
20	23.05	26.66	10.93	15.29	1.05	0.56	34.94	25.27	2.08
30	22.74	26.19	11.80	15.42	1.05	0.54	36.28	25.71	1.98
40	22.54	25.94	12.18	14.88	1.05	0.52	37.46	26.61	1.91
50	22.38	26.21	12.58	14.28	1.07	0.55	38.12	26.67	1.97
60	22.32	25.76	12.57	14.17	1.05	0.51	38.32	26.59	1.96
70	22.27	25.71	12.63	14.00	1.05	0.50	38.53	26.65	1.96
80	22.23	25.74	12.65	13.92	1.06	0.51	38.61	26.77	1.98
90	22.20	25.64	12.70	13.85	1.06	0.50	38.84	26.76	2.00
100	22.18	25.61	12.72	13.81	1.06	0.50	38.07	26.80	2.02
150	22.11	25.67	12.70	13.68	1.06	0.51	38.85	26.96	2.02
200	22.07	25.68	12.61	13.69	1.06	0.51	40.36	27.10	2.00
250	22.04	25.78	12.48	13.77	1.07	0.53	41.06	27.06	2.03
300	22.01	25.80	12.37	13.82	1.07	0.53	40.28	27.21	2.02
350	21.97	25.88	12.18	13.91	1.07	0.55	39.23	27.21	2.03
400	21.93	25.98	11.99	13.94	1.08	0.56	41.32	27.20	2.06
450	21.89	25.97	11.75	14.01	1.08	0.57	41.40	27.13	2.00
500	21.84	26.13	11.46	14.04	1.09	0.59	40.19	27.12	2.01
550	21.79	26.21	11.21	14.05	1.09	0.61	39.32	27.19	2.03
600	21.73	26.31	10.94	13.99	1.10	0.62	39.38	27.19	2.08
650	21.67	26.46	10.69	13.92	1.11	0.64	39.41	27.24	2.09
700	21.60	26.55	10.48	13.79	1.11	0.66	39.03	27.17	2.06
750	21.53	26.70	10.26	13.66	1.12	0.67	40.21	27.12	1.99
800	21.46	26.80	10.09	13.50	1.13	0.69	39.48	27.07	2.03
850	21.39	26.94	9.93	13.31	1.14	0.70	39.53	27.08	2.03
900	21.32	27.10	9.76	13.08	1.15	0.72	38.62	27.05	2.07
950	21.26	27.16	9.64	12.84	1.16	0.72	40.96	27.27	2.08
1000	21.19	27.36	9.53	12.57	1.17	0.74	40.35	27.33	2.01
1100	21.05	27.64	9.43	12.00	1.19	0.76	40.29	26.94	2.02
1200	20.92	27.87	9.45	11.40	1.21	0.77	39.61	27.10	2.08
1300	20.80	28.16	9.59	10.83	1.24	0.77	39.12	27.15	2.07
1400	20.69	28.47	9.84	10.29	1.26	0.78	39.82	27.00	2.11
1500	20.59	28.73	10.20	9.78	1.29	0.78	40.45	26.90	2.11
1600	20.48	29.09	10.66	9.33	1.32	0.79	40.33	26.78	2.13
1700	20.37	29.41	11.19	8.93	1.35	0.79	40.57	26.38	2.13
1800	20.25	29.74	11.64	8.56	1.38	0.79	40.22	26.88	2.12
1900	20.10	30.16	11.81	8.23	1.42	0.81	40.26	26.60	2.22
2000	19.91	30.63	11.54	7.95	1.46	0.83	40.09	26.55	2.25
2100	19.67	31.14	10.78	7.67	1.50	0.86	40.48	26.22	2.38
2200	19.37	31.73	9.63	7.40	1.55	0.89	38.90	26.30	2.52
2300	18.98	32.17	8.34	7.13	1.56	0.93	39.16	25.92	2.72
2400	18.52	32.91	7.12	6.88	1.62	0.97	38.43	25.52	2.99
2500	17.99	33.64	6.01	6.59	1.66	1.01	40.41	25.87	3.26



ISO 9001 ISO 14001 AS 9100 CERTIFIED

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site

The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

IF/RF MICROWAVE COMPONENTS



REV. OR

TSS-23HLN+

2/26/2019

Page 7 of 9

Typical Performance Data

Definitions:

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 7.60V, Id = 204mA @ Temperature = +95°C

FREQ (MHz)	Gain (dB)	Isolation (dB)	Input Return Loss (dB)	Output Return Loss (dB)	Stability		IP-3 Output (dBm)	1dB Comp. Output (dBm)	Noise Figure (dB)
					K	Measure			
20	23.07	26.62	10.82	15.08	1.05	0.55	35.42	24.91	1.97
30	22.76	26.18	11.83	15.23	1.05	0.53	35.82	25.39	1.84
40	22.56	25.93	12.26	14.70	1.05	0.51	38.78	26.21	1.80
50	22.40	25.67	12.65	14.18	1.05	0.49	37.90	26.34	1.85
60	22.34	25.75	12.64	14.02	1.05	0.50	37.92	26.26	1.86
70	22.28	25.70	12.72	13.85	1.05	0.50	38.82	26.35	1.84
80	22.24	25.72	12.75	13.77	1.06	0.50	38.72	26.39	1.86
90	22.22	25.63	12.81	13.71	1.05	0.49	37.80	26.43	1.90
100	22.19	25.64	12.82	13.67	1.06	0.49	36.30	26.47	1.90
150	22.13	25.63	12.82	13.55	1.06	0.50	37.08	26.61	1.92
200	22.08	25.67	12.71	13.57	1.06	0.51	38.37	26.76	1.91
250	22.05	25.71	12.59	13.65	1.06	0.52	36.73	26.73	1.89
300	22.02	25.76	12.45	13.73	1.07	0.53	38.08	26.88	1.89
350	21.98	25.87	12.25	13.82	1.07	0.54	38.97	26.89	1.91
400	21.95	25.89	12.03	13.90	1.08	0.55	38.64	26.87	1.94
450	21.91	25.99	11.78	13.98	1.08	0.57	38.89	26.81	1.88
500	21.86	26.10	11.49	14.03	1.09	0.59	42.26	26.79	1.92
550	21.81	26.23	11.24	14.06	1.09	0.61	39.94	26.88	1.93
600	21.75	26.27	10.97	14.03	1.10	0.62	38.92	26.86	1.95
650	21.68	26.44	10.69	14.00	1.11	0.64	39.20	26.92	1.98
700	21.62	26.51	10.50	13.90	1.11	0.65	40.11	26.79	1.93
750	21.55	26.65	10.26	13.78	1.12	0.67	40.80	26.79	1.91
800	21.48	26.80	10.07	13.64	1.13	0.69	40.36	26.75	1.92
850	21.41	26.89	9.92	13.48	1.14	0.70	40.45	26.78	1.93
900	21.34	27.06	9.75	13.27	1.15	0.72	39.65	26.74	1.94
950	21.28	27.15	9.62	13.01	1.15	0.73	39.79	26.94	1.95
1000	21.21	27.28	9.52	12.76	1.16	0.74	39.74	27.02	1.90
1100	21.08	27.52	9.42	12.18	1.18	0.75	38.90	26.64	1.92
1200	20.95	27.83	9.43	11.59	1.21	0.77	39.92	26.80	1.99
1300	20.83	28.17	9.58	11.00	1.24	0.78	39.76	26.76	1.98
1400	20.72	28.37	9.83	10.45	1.25	0.78	40.90	26.69	2.01
1500	20.61	28.69	10.19	9.93	1.28	0.78	39.81	26.61	1.98
1600	20.51	28.98	10.65	9.47	1.31	0.78	40.29	26.47	2.01
1700	20.40	29.37	11.18	9.07	1.35	0.79	40.96	26.06	2.03
1800	20.28	29.68	11.64	8.69	1.38	0.80	40.28	26.57	2.01
1900	20.13	30.00	11.83	8.36	1.40	0.81	40.50	26.30	2.07
2000	19.94	30.44	11.57	8.07	1.44	0.83	41.85	26.17	2.16
2100	19.70	30.98	10.82	7.80	1.48	0.86	41.28	25.91	2.27
2200	19.40	31.38	9.67	7.54	1.50	0.89	43.33	25.90	2.39
2300	19.01	32.07	8.39	7.28	1.55	0.93	40.32	25.61	2.60
2400	18.55	32.71	7.14	7.03	1.60	0.98	39.99	25.20	2.86
2500	18.02	33.32	6.03	6.75	1.61	1.02	41.45	25.55	3.17



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site
 The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

IF/RF MICROWAVE COMPONENTS



Typical Performance Data

Definitions:

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 8.40V, Id = 217mA @ Temperature = +95°C

FREQ (MHz)	Gain (dB)	Isolation (dB)	Input Return Loss (dB)	Output Return Loss (dB)	Stability		IP-3 Output (dBm)	1dB Comp. Output (dBm)	Noise Figure (dB)
					K	Measure			
20	22.95	26.84	11.00	15.20	1.06	0.58	35.89	25.50	2.23
30	22.65	26.22	11.88	15.50	1.05	0.55	35.99	25.99	2.08
40	22.45	25.97	12.22	14.99	1.05	0.53	38.01	26.91	2.02
50	22.30	25.32	12.49	14.50	1.04	0.46	37.61	26.86	2.03
60	22.24	25.79	12.56	14.28	1.06	0.52	37.08	26.87	2.03
70	22.19	25.78	12.62	14.10	1.06	0.52	39.00	26.89	2.06
80	22.15	25.76	12.64	14.02	1.06	0.52	38.35	27.05	2.06
90	22.12	25.69	12.68	13.97	1.06	0.51	39.51	27.01	2.10
100	22.10	25.74	12.68	13.90	1.06	0.52	36.29	27.09	2.10
150	22.04	25.68	12.65	13.78	1.06	0.52	38.51	27.25	2.10
200	21.99	25.71	12.55	13.78	1.07	0.52	37.98	27.36	2.09
250	21.96	25.84	12.41	13.82	1.07	0.54	36.41	27.34	2.11
300	21.93	25.87	12.29	13.88	1.08	0.55	39.07	27.44	2.07
350	21.90	25.92	12.08	13.93	1.08	0.56	38.57	27.45	2.14
400	21.86	25.98	11.88	13.96	1.08	0.57	37.93	27.49	2.16
450	21.82	26.01	11.63	14.00	1.09	0.58	38.38	27.39	2.11
500	21.77	26.15	11.35	14.01	1.09	0.60	39.20	27.39	2.11
550	21.72	26.26	11.10	13.98	1.10	0.62	40.60	27.42	2.10
600	21.66	26.41	10.85	13.91	1.11	0.64	39.14	27.49	2.15
650	21.60	26.48	10.59	13.81	1.11	0.65	38.42	27.48	2.18
700	21.54	26.64	10.40	13.66	1.12	0.67	39.26	27.41	2.13
750	21.46	26.74	10.18	13.52	1.13	0.68	38.20	27.43	2.08
800	21.40	26.85	10.01	13.33	1.14	0.69	38.82	27.39	2.14
850	21.33	26.99	9.86	13.14	1.15	0.71	39.27	27.37	2.14
900	21.26	27.14	9.71	12.89	1.16	0.72	38.82	27.28	2.13
950	21.20	27.24	9.58	12.64	1.16	0.73	38.97	27.60	2.10
1000	21.14	27.41	9.50	12.36	1.18	0.74	39.30	27.57	2.07
1100	21.01	27.70	9.41	11.78	1.20	0.76	38.67	27.24	2.11
1200	20.88	27.89	9.45	11.18	1.21	0.76	39.43	27.34	2.13
1300	20.76	28.21	9.60	10.61	1.24	0.77	39.91	27.41	2.13
1400	20.66	28.53	9.85	10.08	1.27	0.78	39.63	27.26	2.14
1500	20.55	28.85	10.21	9.57	1.30	0.78	38.78	27.14	2.18
1600	20.45	29.14	10.68	9.13	1.33	0.78	39.12	27.04	2.15
1700	20.34	29.52	11.20	8.74	1.36	0.78	39.57	26.65	2.18
1800	20.22	29.80	11.63	8.37	1.39	0.79	38.92	27.13	2.20
1900	20.06	30.27	11.78	8.04	1.43	0.80	40.18	26.85	2.28
2000	19.86	30.69	11.48	7.76	1.46	0.82	39.32	26.81	2.33
2100	19.62	31.22	10.71	7.47	1.51	0.85	39.75	26.53	2.48
2200	19.32	31.74	9.56	7.21	1.54	0.88	40.88	26.56	2.63
2300	18.93	32.39	8.29	6.94	1.59	0.92	39.93	26.17	2.83
2400	18.46	33.02	7.07	6.68	1.62	0.96	40.10	25.78	3.09
2500	17.93	33.72	5.98	6.40	1.66	1.00	40.05	26.12	3.40



ISO 9001 ISO 14001 AS 9100 CERTIFIED

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site

The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

IF/RF MICROWAVE COMPONENTS



REV. OR

TSS-23HLN+









2/26/2019

Page 9 of 9

MMIC Amplifier

TSS-23HLN+

Typical Performance Curves



 **Mini-Circuits®**
ISO 9001 ISO 14001 AS 9100 CERTIFIED

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site
 The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

IF/RF MICROWAVE COMPONENTS








minicircuits.com

REV. OR
TSS-23HLN+
2/26/2019
Page 1 of 2

MMIC Amplifier

TSS-23HLN+

Typical Performance Curves




Case Style


DQ

DQ1225

Outline Dimensions



PCB Land Pattern



SUGGESTED LAYOUT,
TOLERANCE TO BE WITHIN $\pm .002$

Weight: .02 Grams

Dimensions are in inches (mm). Tolerances: 2Pl. $\pm .01$; 3 Pl. $\pm .004$

Notes:

1. Case material: Plastic.
2. Termination finish:

For RoHS Case Styles: Tin-Silver alloy plate over Nickel barrier or Matte-Tin. All models, (+) suffix.
See Data sheet.

For RoHS-5 Case Styles: Tin-Lead plate. All models, no (+) suffix.



Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010


Mini-Circuits ISO 9001 & ISO 14001 Certified

INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Tape & Reel Packaging TR-F66

DEVICE ORIENTATION IN T&R



Tape Width, mm	Device Cavity Pitch, mm	Reel Size, inches	Devices per Reel see note	
8	4	7	Small quantity standard	20
				50
				100
				200
				500
		7	Standard	1000, 2000, 3000

Note: Please consult individual model data sheet to determine device per reel availability.

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: www.minicircuits.com/pages/pdfs/tape.pdf




Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661


Mini-Circuits ISO 9001 & ISO 14001 Certified

THIRD ANGLE PROJECTION



REVIEWS

REV OR	ECN No. M171588	DESCRIPTION NEW RELEASE	DATE 12/20/18	DR ITG	AUTH GH

SUGGESTED MOUNTING CONFIGURATION FOR
DQ1225 CASE STYLE, "12AM05" PIN CODE

COMPONENT	SIZE
C1...C7;L2;R1	0402
L1	0805

NOTES:

1. TRACE WIDTH & GAP PARAMETERS ARE SHOWN FOR ROGERS R04350B WITH DIELECTRIC THICKNESS $.020'' \pm .0015''$; COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH AND GAP MAY NEED TO BE MODIFIED.
2. CHIP COMPONENT FOOTPRINTS SHOWN FOR REFERENCE. FOR COMPONENT VALUES REFER TO TB-TSS-23LN+ OR TB-TSS-23HLN+.
3. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.



DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)



DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

UNLESS OTHERWISE SPECIFIED

DIMENSIONS ARE IN INCHES


TOLERANCES ON:

2 PL DECIMALS \pm 3 PL DECIMALS $\pm .005$ ANGLES \pm FRACTIONS \pm

DRAWN ITG 12/19/18

CHECKED GF 12/20/18

APPROVED GH 12/20/18



Mini-Circuits®



13 Neptune Avenue
Brooklyn NY 11235

PL, 12AM05, DQ1225, TB-TSS-23LN+/23HLN+

SIZE A	CODE IDENT 15542	DRAWING NO: 98-PL-619	REV: OR
FILE: 98PL619	SCALE: 8:1	SHEET: 1 OF 1	

THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS.
EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE
AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY
DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO.
THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE
PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.

Evaluation Board and Circuit



Component	Size	Value	Part Number	Manufacturer
C1	0402	0.1uF	GRM155R71C104KA88D	Murata
C2	0402	1.2pF	GRM1555C1H1R2CA1D	Murata
C3	0402	0.1uF	GRM155R71C104KA88D	Murata
C4	0402	0.1uF	GRM155R71C104KA88D	Murata
C5	0402	1000pF	GRM1555C1H102JA01D	Murata
C6	0402	10000pF	GRM155R71E103KA01D	Murata
C7	0402	0.1uF	GRM155R71C104KA88D	Murata
L1	0805	680nH	0805LS-681XJLB	Coilcraft
L2	0402	1.0nH	0402CS-1NOXJLW	Coilcraft
R1	0402	1.2KOhm	RK73H1ETTP1201F	Koa

Schematic Diagram

NOTES:

1. 50 Ohm SMA Female Connectors.
2. PCB Material: Roger R04350B or equivalent, Dielectric constant=3.5, Thickness=0.02 inch

Mini-Circuits®

**Environmental Specifications****ENV08T9**

All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-40° to 95° C / 105° C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C or -65° to 150° Ambient Environment	Individual Model Data Sheet
Thermal Shock	-55° to 100°C, 100 cycles	MIL-STD-202, Method 107, Condition A-3, except +100°C
Mechanical Shock	1.5Kg, 0.5 ms, 5 shock pulses, Y1 direction only	MIL-STD-883, Method 2002, Condition B, except Y1 direction only
Vibration (Variable Frequency)	50g peak	MIL-STD-883, Method 2007, Condition B
Autoclave	15 psig, 100% RH, 121°C, 96 hours	JESD22-A102-C, Condition C
HAST	130°C, 85% RH, 96 hours	JESD22-A110
Solderability	10X Magnification	J-STD-002, Para 4.2.5, Test S, 95% Coverage
Solder Reflow Heat	Sn-Pb Eutetic Process: 240°C peak Pb-Free Process: 260°C peak	J-STD-020C, Table 4-1, 4-2 and 5-2; Figure 5-1
Moisture Sensitivity: Level 1	Bake at 125°C for 24 hours. Soak at 85°C/85%RH for 168 hours Reflow 3 cycles at 260°C peak	J-STD-020
Marking Resistance to Solvents	Isopropyl alcohol + mineral spirits at 25°C; terpene defluxer at 25°C; distilled water + propylene glycol monomethyl ether +	MIL-STD-202, Method 215



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
	monoethanolamine at 63°C to 70°C	