

# Surface Mount Frequency Mixer

## ADE-1L+

### Level 3 (LO Power +3 dBm) 2 to 500 MHz



Generic photo used for illustration purposes only  
CASE STYLE: CD542

**+RoHS Compliant**  
The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications



Available Tape and Reel at no extra cost

Reel Size	Devices/Reel
7"	20, 50, 100, 200
13"	500, 1000


### Maximum Ratings

Operating Temperature	-40°C to 85°C
Storage Temperature	-55°C to 100°C
RF Power	50mW
IF Current	40mA
Permanent damage may occur if any of these limits are exceeded.	


### Pin Connections

LO	6
RF	3
IF	2
GROUND	1,4,5

### Outline Drawing




### PCB Land Pattern



### Outline Dimensions (inch/mm)

A	B	C	D	E	F	G
.272	.310	.220	.100	.112	.055	.100
6.91	7.87	5.59	2.54	2.84	1.40	2.54
H	J	K	L	wt		
.030	.026	.065	.300	grams		
0.76	0.66	1.65	7.62	0.20		

### Demo Board MCL P/N: TB-03 Suggested PCB Layout (PL-052)



- NOTES:
- TRACE WIDTH IS SHOWN FOR ROGERS RO4350B WITH DIELECTRIC THICKNESS .030" ± .002"; COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
  - BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.
- DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)
- DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

### Notes

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)

### Features

- low conversion loss, 5.2 dB typ.
- excellent L-R isolation, 55 dB typ.
- low profile package
- aqueous washable
- protected by US patent 6,133,525

### Applications

- cellular
- instrumentation

### Electrical Specifications

FREQUENCY (MHz)	CONVERSION LOSS (dB)	LO-RF ISOLATION (dB)			LO-IF ISOLATION (dB)			IP3 at center band (dBm)										
		L	M	U	L	M	U											
LO/RF	Mid-Band																	
$f_L$ - $f_U$	$\bar{X}$ $\sigma$ Max.	Total Range Max.																
2-500	DC-500	5.2	0.10	7.2	8.0	68	50	55	30	44	30	55	40	45	30	35	25	16


1 dB COMP.: 0 dBm typ.







L = low range [ $f_L$  to  $10 f_L$ ] M = mid range [ $10 f_L$  to  $f_U/2$ ] U = upper range [ $f_U/2$  to  $f_U$ ]  
m = mid band [ $2f_L$  to  $f_U/2$ ]

### Typical Performance Data

Frequency (MHz)		Conversion Loss (dB)	Isolation L-R (dB)	Isolation L-I (dB)	VSWR RF Port (:1)	VSWR LO Port (:1)
RF	LO	LO +3dBm	LO +3dBm	LO +3dBm	LO +3dBm	LO +3dBm
2.00	32.00	5.88	68.80	57.20	1.32	1.67
5.00	35.00	5.44	68.30	56.40	1.19	1.66
10.00	40.00	5.32	68.00	55.40	1.14	1.66
20.00	50.00	5.25	67.40	54.20	1.10	1.80
50.00	80.00	5.34	63.80	49.80	1.08	1.84
75.00	105.00	5.30	60.80	47.40	1.07	1.84
80.09	110.09	5.32	60.50	46.90	1.07	1.85
100.00	130.00	5.32	59.20	45.40	1.06	1.85
150.00	180.00	5.32	56.30	43.20	1.05	1.96
160.09	190.09	5.31	50.60	42.90	1.10	1.67
200.00	230.00	5.34	48.80	41.60	1.10	1.69
240.08	270.08	5.37	47.40	40.30	1.10	1.73
250.00	280.00	5.38	47.20	40.00	1.10	1.73
300.00	330.00	5.52	44.30	39.10	1.11	1.80
320.07	350.07	5.50	43.30	38.60	1.12	1.82
400.00	430.00	5.68	41.80	35.30	1.19	2.01
450.00	480.00	5.73	41.50	34.20	1.23	2.04
470.00	500.00	5.69	41.50	33.70	1.24	2.16
480.00	510.06	5.67	40.90	33.40	1.24	2.18
500.00	530.00	5.69	40.70	33.00	1.25	2.25

### Electrical Schematic





**Notes**

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuit's standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuit's website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)



# Frequency Mixer

# ADE-1L+

## Typical Performance Data

RF (IN) (MHz)	LO (MHz)	CONVERSION LOSS IF FIXED @IF(OUT)=30MHz (dB)			RF (IN) (MHz)	LO (MHz)	IP3 INPUT (dBm)			RF (IN) (MHz)	LO (MHz)	COMPRESSION @RF IN=0dBm (dB)		
		@LO (dBm)					@LO (dBm)					@LO (dBm)		
		0	+3	+6			0	+3	+6			0	+3	+6
2.0	32.0	6.28	5.88	5.48	10.1	40.1	25.46	20.71	26.68	10.1	40.1	1.34	0.82	0.56
5.0	35.0	5.74	5.44	5.14	50.4	80.4	20.07	21.62	18.40	50.4	80.4	1.35	0.78	0.48
10.0	40.0	5.62	5.32	4.92	90.8	120.8	24.82	21.06	20.06	90.8	120.8	1.34	0.78	0.51
50.4	80.4	6.82	6.00	5.62	110.9	140.9	21.44	21.23	27.99	110.9	140.9	1.35	0.81	0.51
90.8	120.8	6.82	6.02	5.64	151.3	181.3	30.54	24.17	26.06	151.3	181.3	1.29	0.78	0.48
110.9	140.9	6.79	6.00	5.62	171.5	201.5	21.78	18.56	20.59	171.5	201.5	1.29	0.78	0.47
151.3	181.3	6.76	5.99	5.65	211.8	241.8	21.01	23.19	20.97	211.8	241.8	1.27	0.70	0.44
171.5	201.5	6.70	5.98	5.66	232.0	262.0	18.26	17.17	18.99	232.0	262.0	1.31	0.73	0.45
211.8	241.8	6.68	6.00	5.68	272.3	302.3	37.25	19.10	23.66	272.3	302.3	1.26	0.72	0.47
232.0	262.0	6.66	6.01	5.71	292.5	322.5	19.48	15.80	14.82	292.5	322.5	1.23	0.67	0.46
272.3	302.3	6.69	6.06	5.73	332.8	362.8	29.38	15.64	14.61	332.8	362.8	1.23	0.65	0.42
292.5	322.5	6.69	6.04	5.73	353.0	383.0	18.46	21.54	15.73	353.0	383.0	1.21	0.66	0.43
332.8	362.8	6.74	6.09	5.78	393.3	423.3	19.56	16.83	15.87	393.3	423.3	1.21	0.65	0.46
353.0	383.0	6.76	6.15	5.81	413.5	443.5	21.99	16.37	16.25	413.5	443.5	1.27	0.69	0.46
393.3	423.3	6.80	6.21	5.84	453.8	483.8	16.11	13.51	12.69	453.8	483.8	1.33	0.75	0.50
453.8	483.8	6.88	6.29	5.97	474.0	504.0	17.91	13.10	11.57	474.0	504.0	1.39	0.81	0.51
474.0	504.0	6.91	6.27	5.98	514.3	544.3	13.20	13.67	12.57	514.3	544.3	1.39	0.89	0.54
514.3	544.3	7.02	6.32	5.98	534.5	564.5	11.42	13.27	13.43	534.5	564.5	1.42	0.92	0.58
534.5	564.5	7.07	6.36	6.00	574.8	604.8	7.92	11.15	14.18	574.8	604.8	1.49	1.08	0.70
574.8	604.8	7.32	6.54	6.04	595.0	625.0	6.64	9.15	14.05	595.0	625.0	1.51	1.08	0.77
595.0	625.0	7.46	6.69	6.13	635.4	665.4	4.50	5.62	9.50	635.4	665.4	1.55	1.17	0.97
635.4	665.4	7.77	7.07	6.44	655.5	685.5	3.79	4.48	7.19	655.5	685.5	1.55	1.12	0.98
655.5	685.5	7.91	7.22	6.58	695.9	725.9	3.68	4.08	5.64	695.9	725.9	1.42	1.04	0.84
695.9	725.9	8.26	7.54	6.93	716.0	746.0	3.95	4.44	5.70	716.0	746.0	1.36	0.99	0.83
756.4	786.4	8.70	7.94	7.36	756.4	786.4	4.54	5.19	6.33	756.4	786.4	1.22	0.92	0.74
776.5	806.5	8.87	8.11	7.53	776.5	806.5	4.95	5.48	6.61	776.5	806.5	1.20	0.86	0.66
816.9	846.9	8.99	8.26	7.69	816.9	846.9	6.17	6.79	8.02	816.9	846.9	1.28	0.89	0.72
837.0	867.0	9.06	8.31	7.75	837.0	867.0	6.88	8.12	9.59	837.0	867.0	1.22	0.85	0.69
877.4	907.4	9.14	8.36	7.79	877.4	907.4	8.77	9.97	12.72	877.4	907.4	1.32	0.92	0.73
897.6	927.6	9.11	8.31	7.73	897.6	927.6	10.17	10.59	14.01	897.6	927.6	1.34	0.96	0.76
937.9	967.9	9.24	8.35	7.73	937.9	967.9	12.01	12.44	14.89	937.9	967.9	1.39	1.07	0.81
958.1	988.1	9.39	8.39	7.75	958.1	988.1	11.93	14.49	17.78	958.1	988.1	1.45	1.11	0.80
998.4	1028.4	9.47	8.39	7.76	998.4	1028.4	12.16	13.51	16.27	998.4	1028.4	1.50	1.20	0.85
1018.6	1048.6	9.59	8.42	7.84	1018.6	1048.6	11.73	13.27	14.23	1018.6	1048.6	1.45	1.14	0.83
1058.9	1088.9	9.88	8.63	8.08	1058.9	1088.9	10.95	12.09	13.62	1058.9	1088.9	1.53	1.11	0.76
1079.1	1109.1	9.90	8.72	8.23	1079.1	1109.1	10.58	11.55	12.99	1079.1	1109.1	1.51	1.08	0.68
1119.4	1149.4	10.34	9.10	8.61	1119.4	1149.4	9.65	11.34	11.13	1119.4	1149.4	1.42	1.00	0.64
1139.6	1169.6	10.79	9.37	8.85	1139.6	1169.6	8.95	10.07	10.79	1139.6	1169.6	1.43	1.08	0.65
1179.9	1209.9	11.41	9.84	9.34	1179.9	1209.9	8.48	9.53	10.22	1179.9	1209.9	1.37	1.00	0.62
1200.1	1230.1	11.67	10.07	9.56	1200.1	1230.1	8.51	9.17	11.05	1200.1	1230.1	1.28	0.97	0.57

REV. X2  
ADE-1L+  
100817  
Page 1 of 5



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED • RoHS compliant  
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see



# Frequency Mixer

# ADE-1L+

## Typical Performance Data

IF (OUT) (MHz)	LO (MHz)	CONVERSION LOSS VS. IF FREQUENCY @RF(IN)=250.1MHz (dB)	IF (OUT) (MHz)	LO (MHz)	CONVERSION LOSS VS. IF FREQUENCY @RF(IN)=10.1MHz (dB)	IF (OUT) (MHz)	LO (MHz)	CONVERSION LOSS VS. IF FREQUENCY @RF(IN)=500.1MHz (dB)
		@LO (dBm)			@LO (dBm)			@LO (dBm)
		+3			+3			+3
240.0	10.1	5.99	20.2	10.1	5.79	490.0	10.1	6.38
234.1	16.0	6.00	32.2	22.1	5.55	478.0	22.1	6.36
228.2	21.9	5.99	44.2	34.1	5.53	466.0	34.1	6.33
222.3	27.8	5.98	56.2	46.1	5.48	454.0	46.1	6.32
216.4	33.7	5.97	68.2	58.1	5.47	442.0	58.1	6.30
210.5	39.6	5.94	80.2	70.1	5.49	430.0	70.1	6.32
204.6	45.5	5.94	92.2	82.1	5.48	418.0	82.1	6.26
198.7	51.4	5.91	104.2	94.1	5.52	406.0	94.1	6.18
192.8	57.3	5.90	116.2	106.1	5.49	394.0	106.1	6.14
186.9	63.2	5.89	128.2	118.1	5.56	382.0	118.1	6.13
181.0	69.1	5.88	140.2	130.1	5.54	370.0	130.1	6.09
175.1	75.0	5.89	152.2	142.1	5.51	358.0	142.1	6.09
169.2	80.9	5.85	164.2	154.1	5.54	346.0	154.1	6.08
163.3	86.8	5.85	176.2	166.1	5.53	334.0	166.1	6.07
157.4	92.7	5.86	188.2	178.1	5.56	322.0	178.1	6.05
151.5	98.6	5.84	200.2	190.1	5.54	310.0	190.1	6.04
145.6	104.5	5.83	212.2	202.1	5.56	298.0	202.1	6.03
139.7	110.4	5.82	224.2	214.1	5.60	286.0	214.1	6.01
133.8	116.3	5.81	236.2	226.1	5.55	274.0	226.1	6.00
127.9	122.2	5.80	248.2	238.1	5.61	262.0	238.1	6.02
122.1	128.0	5.79	260.2	250.1	5.63	250.0	250.1	5.62
116.2	133.9	5.77	272.2	262.1	5.62	238.0	262.1	5.99
110.3	139.8	5.76	284.2	274.1	5.62	226.0	274.1	5.98
104.4	145.7	5.75	296.2	286.1	5.68	214.0	286.1	6.06
98.5	151.6	5.78	308.2	298.1	5.68	202.0	298.1	6.07
92.6	157.5	5.78	320.2	310.1	5.70	190.0	310.1	6.09
86.7	163.4	5.77	332.2	322.1	5.70	178.0	322.1	6.10
80.8	169.3	5.78	344.2	334.1	5.74	166.0	334.1	6.12
74.9	175.2	5.74	356.2	346.1	5.73	154.0	346.1	6.14
69.0	181.1	5.76	368.2	358.1	5.73	142.0	358.1	6.18
63.1	187.0	5.77	380.2	370.1	5.71	130.0	370.1	6.17
57.2	192.9	5.73	392.2	382.1	5.72	118.0	382.1	6.20
51.3	198.8	5.78	404.2	394.1	5.80	106.0	394.1	6.19
45.4	204.7	5.77	416.2	406.1	6.16	94.0	406.1	6.17
39.5	210.6	5.78	428.2	418.1	6.24	82.0	418.1	6.18
33.6	216.5	5.78	440.2	430.1	5.94	70.0	430.1	6.27
27.7	222.4	5.81	452.2	442.1	5.92	58.0	442.1	6.25
21.8	228.3	5.79	464.2	454.1	5.89	46.0	454.1	6.23
15.9	234.2	5.87	488.2	478.1	5.91	22.0	478.1	6.36
10.0	240.1	6.09	500.2	490.1	6.01	10.0	490.1	6.28

REV. X2  
ADE-1L+  
100817  
Page 2 of 5



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED • RoHS compliant  
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see



# Frequency Mixer

# ADE-1L+

## Typical Performance Data

LO (MHz)	LO-RF ISOLATION (dB)			LO-IF ISOLATION (dB)		
	@LO (dBm)			@LO (dBm)		
	0	+3	+6	0	+3	+6
2.0	67.0	68.8	68.2	57.6	57.2	55.8
5.0	67.1	68.3	70.0	56.4	56.4	54.9
10.0	65.5	68.0	68.9	55.2	55.4	53.8
50.4	59.47	63.85	68.78	58.55	56.83	55.58
90.8	54.77	58.66	63.27	53.39	51.80	50.80
110.9	53.17	56.70	60.67	51.53	50.16	49.34
151.3	49.81	53.15	57.34	48.78	47.54	46.76
171.5	48.94	52.21	56.31	47.62	46.56	45.80
211.8	47.23	50.27	54.06	45.78	44.89	44.37
232.0	46.10	49.19	52.80	44.96	44.26	43.62
272.3	44.29	47.35	50.62	43.60	42.93	42.21
292.5	43.26	46.27	49.37	43.40	42.87	42.08
332.8	41.98	44.50	47.25	42.40	41.81	40.79
353.0	41.17	43.44	45.83	42.12	41.45	40.27
393.3	40.25	42.15	43.94	41.13	40.42	39.68
453.8	39.00	40.89	42.37	40.34	38.05	36.46
474.0	38.72	40.40	41.61	40.78	37.97	35.92
514.3	38.45	40.10	41.01	42.12	38.10	35.29
534.5	38.05	39.76	40.61	42.91	38.40	35.16
574.8	36.80	38.74	39.74	42.09	38.52	34.74
595.0	36.17	38.19	39.26	40.62	37.98	34.26
635.4	34.59	36.52	37.64	36.75	35.17	33.03
655.5	34.34	36.18	37.22	35.41	33.69	32.10
695.9	32.95	34.65	35.64	33.48	31.35	29.93
756.4	30.89	32.40	33.42	31.87	29.61	27.84
776.5	30.46	31.96	32.96	31.40	29.11	27.25
816.9	29.60	31.15	32.21	30.15	28.19	26.34
837.0	29.42	30.90	31.89	29.52	27.74	25.91
877.4	28.96	30.36	31.28	28.43	27.20	25.44
897.6	28.46	29.90	30.84	27.62	26.82	25.14
937.9	28.17	29.42	30.10	26.12	26.10	24.48
958.1	27.81	28.96	29.46	25.18	25.53	23.92
998.4	27.89	28.78	28.86	23.27	24.32	22.85
1018.6	27.66	28.27	28.06	22.33	23.46	22.03
1058.9	27.75	27.77	27.09	20.60	22.05	21.02
1079.1	27.63	27.46	26.58	19.50	21.13	20.54
1119.4	27.63	26.72	25.41	17.82	19.47	19.37
1139.6	27.77	26.50	24.98	17.04	18.72	18.86
1179.9	27.85	25.98	24.14	15.54	17.19	17.83
1200.1	27.54	25.51	23.63	14.93	16.55	17.27

RF (IN) (MHz)	LO (MHz)	RF-IF ISOLATION (dB)		
		@LO (dBm)		
		0	+3	+6
10.1	40.1	45.79	52.75	40.38
50.4	80.4	32.33	32.38	32.57
90.8	120.8	27.80	27.99	28.12
110.9	140.9	26.39	26.63	26.76
151.3	181.3	24.27	24.53	24.70
171.5	201.5	23.52	23.80	24.00
211.8	241.8	22.47	22.81	22.99
232.0	262.0	22.08	22.47	22.68
272.3	302.3	21.63	22.08	22.43
292.5	322.5	21.54	22.01	22.37
332.8	362.8	21.59	22.10	22.41
353.0	383.0	21.74	22.28	22.60
393.3	423.3	22.13	22.90	23.34
413.5	443.5	22.19	23.07	23.61
453.8	483.8	22.21	23.27	23.99
474.0	504.0	21.90	22.93	23.55
514.3	544.3	20.76	21.49	21.87
534.5	564.5	20.14	20.62	20.90
574.8	604.8	18.93	19.07	19.12
595.0	625.0	18.45	18.44	18.39
635.4	665.4	17.67	17.52	17.36
655.5	685.5	17.39	17.22	17.05
695.9	725.9	17.06	16.84	16.68
716.0	746.0	16.99	16.73	16.55
756.4	786.4	16.88	16.60	16.35
776.5	806.5	16.89	16.61	16.36
816.9	846.9	16.59	16.39	16.18
837.0	867.0	16.35	16.20	16.00
877.4	907.4	15.68	15.64	15.46
897.6	927.6	15.25	15.23	15.07
937.9	967.9	14.35	14.40	14.34
958.1	988.1	13.85	13.94	13.96
998.4	1028.4	12.94	13.08	13.24
1018.6	1048.6	12.45	12.63	12.81
1058.9	1088.9	11.63	11.81	11.91
1079.1	1109.1	11.20	11.33	11.35
1119.4	1149.4	10.36	10.35	10.26
1139.6	1169.6	9.94	9.85	9.71
1179.9	1209.9	9.17	8.91	8.64
1200.1	1230.1	8.81	8.47	8.14



# Frequency Mixer

# ADE-1L+

## Typical Performance Data

RF (IN) (MHz)	LO (MHz)	RF VSWR (:1)		
		@LO (dBm)		
		0	+3	+6
2.0	32.0	1.34	1.32	1.32
5.0	35.0	1.23	1.19	1.15
10.0	40.0	1.20	1.14	1.08
50.4	80.4	1.34	1.17	1.06
90.8	120.8	1.41	1.23	1.12
110.9	140.9	1.37	1.18	1.08
151.3	181.3	1.36	1.20	1.11
171.5	201.5	1.38	1.21	1.11
211.8	241.8	1.28	1.13	1.07
232.0	262.0	1.29	1.15	1.10
272.3	302.3	1.32	1.18	1.12
292.5	322.5	1.30	1.16	1.11
332.8	362.8	1.30	1.18	1.14
353.0	383.0	1.29	1.17	1.14
393.3	423.3	1.30	1.21	1.19
413.5	443.5	1.30	1.21	1.19
453.8	483.8	1.30	1.22	1.21
474.0	504.0	1.31	1.24	1.23
514.3	544.3	1.31	1.21	1.21
534.5	564.5	1.30	1.21	1.22
574.8	604.8	1.36	1.25	1.23
595.0	625.0	1.38	1.25	1.22
635.4	665.4	1.45	1.33	1.27
655.5	685.5	1.51	1.39	1.32
695.9	725.9	1.63	1.52	1.44
716.0	746.0	1.73	1.62	1.55
756.4	786.4	1.99	1.87	1.79
776.5	806.5	2.07	1.96	1.88
816.9	846.9	2.33	2.22	2.15
837.0	867.0	2.45	2.34	2.26
877.4	907.4	2.55	2.45	2.37
897.6	927.6	2.70	2.60	2.52
937.9	967.9	2.83	2.70	2.62
958.1	988.1	2.84	2.70	2.62
998.4	1028.4	3.05	2.90	2.82
1018.6	1048.6	3.12	2.95	2.86
1058.9	1088.9	3.14	2.95	2.87
1079.1	1109.1	3.21	3.03	2.95
1119.4	1149.4	3.26	3.04	2.95
1139.6	1169.6	3.34	3.08	2.97
1179.9	1209.9	3.43	3.10	2.96
1200.1	1230.1	3.38	3.03	2.89

LO (MHz)	LO VSWR (:1)		
	@LO (dBm)		
	0	+3	+6
2.0	1.15	1.67	2.68
5.0	1.16	1.66	2.68
10.0	1.16	1.66	2.68
50.4	1.11	1.42	2.13
90.8	1.11	1.42	2.10
110.9	1.12	1.39	2.03
151.3	1.11	1.42	2.09
171.5	1.11	1.43	2.11
211.8	1.12	1.44	2.09
232.0	1.12	1.47	2.15
272.3	1.15	1.51	2.18
292.5	1.16	1.51	2.15
332.8	1.19	1.55	2.20
353.0	1.21	1.58	2.25
393.3	1.27	1.61	2.23
413.5	1.28	1.66	2.31
453.8	1.34	1.73	2.40
474.0	1.38	1.74	2.38
514.3	1.44	1.80	2.43
534.5	1.47	1.83	2.44
574.8	1.55	1.89	2.45
595.0	1.58	1.95	2.53
635.4	1.65	2.06	2.66
655.5	1.69	2.10	2.71
695.9	1.74	2.15	2.78
716.0	1.77	2.16	2.78
756.4	1.85	2.22	2.83
776.5	1.88	2.25	2.86
816.9	1.96	2.31	2.91
837.0	2.01	2.35	2.95
877.4	2.08	2.37	2.92
897.6	2.12	2.36	2.89
937.9	2.23	2.44	2.92
958.1	2.27	2.44	2.92
998.4	2.36	2.46	2.90
1018.6	2.42	2.52	2.96
1058.9	2.57	2.60	3.01
1079.1	2.65	2.63	2.99
1119.4	2.86	2.82	3.16
1139.6	3.00	2.93	3.24
1179.9	3.21	3.08	3.31
1200.1	3.27	3.16	3.38

IF (OUT) (MHz)	IF VSWR @LO=500.1MHz (:1)		
	@LO (dBm)		
	0	+3	+6
0.1	2.01	1.66	1.45
0.2	1.97	1.63	1.43
0.5	2.04	1.69	1.48
1.0	2.14	1.76	1.52
5.0	2.08	1.71	1.50
10.0	2.12	1.73	1.51
22.3	2.06	1.77	1.61
34.5	1.99	1.73	1.51
46.8	1.97	1.67	1.51
59.0	1.92	1.63	1.47
71.3	1.93	1.67	1.49
83.5	1.96	1.68	1.52
95.8	2.02	1.73	1.56
108.0	2.03	1.75	1.56
120.3	2.04	1.76	1.58
132.5	2.02	1.74	1.57
144.8	2.04	1.74	1.58
157.0	2.03	1.74	1.57
181.5	2.06	1.77	1.60
193.8	2.11	1.81	1.64
206.0	2.15	1.84	1.67
218.3	2.17	1.86	1.67
230.5	2.15	1.85	1.67
242.8	2.12	1.82	1.65
255.0	2.10	1.80	1.64
267.3	2.09	1.80	1.63
279.5	2.11	1.81	1.65
291.8	2.12	1.82	1.66
304.0	2.13	1.84	1.67
328.5	2.13	1.85	1.67
340.8	2.13	1.85	1.68
353.0	2.13	1.84	1.68
365.3	2.11	1.84	1.68
377.5	2.12	1.85	1.69
389.8	2.15	1.88	1.72
402.0	2.19	1.92	1.76
426.5	2.21	1.94	1.77
438.8	2.19	1.92	1.76
451.0	2.17	1.90	1.75
463.3	2.16	1.90	1.76
487.8	2.22	1.96	1.81
500.0	2.18	2.06	2.01

REV. X2  
ADE-1L+  
100817  
Page 4 of 5



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED RoHS compliant  
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see



## Harmonics Tables

RF HARMONICS ORDER

	(-dBm)	(-dBc)										
0	-	-	18	33	21	27	21	46	36	47	39	57
1	-	16	0	27	14	33	23	38	39	46	41	61
2	107	73	62	63	62	61	58	73	54	70	64	69
3	111	63	70	69	61	86	57	73	59	79	64	83
4	116	89	95	89	85	78	85	83	84	89	92	102
5	121	94	87	96	84	83	77	89	86	97	84	94
6	131	103	102	92	106	96	81	91	92	105	116	101
7	114	101	101	104	98	96	89	77	86	100	101	102
8	118	100	106	114	113	98	101	99	70	93	91	98
9	117	110	108	108	113	105	97	93	100	68	103	92
10	128	107	100	111	104	97	116	97	101	96	67	90
	RF CAL	0	1	2	3	4	5	6	7	8	9	10

### LO HARMONICS ORDER

Test conditions: RF IN: 250.1 MHz; -15.00 dBm.  
 LO IN: 280.01 MHz; +3.00 dBm  
 IF OUT: 29.91 MHz; -20.89 dBm

RF HARMONICS ORDER

	(-dBm)	(-dBc)										
0	-	-	27	42	33	40	34	54	52	72	59	70
1	-	17	0	28	14	37	24	41	43	52	52	66
2	98	58	50	58	52	63	51	57	48	72	61	67
3	93	45	47	49	50	53	48	51	52	57	55	64
4	90	68	70	69	79	66	77	65	70	71	66	80
5	93	70	67	67	58	69	54	64	53	77	56	73
6	97	83	88	81	93	96	77	87	78	82	79	81
7	93	79	77	86	73	87	74	75	70	74	69	76
8	96	95	92	89	94	88	103	93	89	92	95	92
9	97	102	89	104	81	100	81	92	89	71	96	89
10	95	103	101	103	107	100	97	90	96	94	83	95
	RF CAL	0	1	2	3	4	5	6	7	8	9	10

### LO HARMONICS ORDER

Test conditions: RF IN: 250.1 MHz; -5.00 dBm.  
 LO IN: 280.01 MHz; +3.00 dBm  
 IF OUT: 29.91 MHz; -11.01 dBm

- Notes: 1. All Harmonics are in (dBc) relative to IF OUTPUT.  
 2. + entry denotes harmonics are in (dBc) above IF OUTPUT.  
 3. RF Cal represent the Harmonics level of the RF input signal to the mixer.

REV. X2  
 ADE-1L+  
 100817  
 Page 5 of 5




IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED • RoHS compliant  
 P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661




The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see [minicircuits.com](http://minicircuits.com)

## Typical Performance Curves


Conversion Loss @ IF=30MHz




Conversion Loss vs. IF @ RF=250.1MHz




Conversion Loss vs. IF @ RF=10.1MHz




Conversion Loss vs. IF @ RF=500.1MHz



IP3 Input




Compression @ RF IN=0dBm




## Typical Performance Curves


LO-RF Isolation




LO-IF Isolation




RF-IF Isolation




RF VSWR



LO VSWR



IF VSWR



## Harmonics Tables

RF HARMONICS ORDER

	(-dBm)	(-dBc)										
0	-	-	18	33	21	27	21	46	36	47	39	57
1	-	16	0	27	14	33	23	38	39	46	41	61
2	107	73	62	63	62	61	58	73	54	70	64	69
3	111	63	70	69	61	86	57	73	59	79	64	83
4	116	89	95	89	85	78	85	83	84	89	92	102
5	121	94	87	96	84	83	77	89	86	97	84	94
6	131	103	102	92	106	96	81	91	92	105	116	101
7	114	101	101	104	98	96	89	77	86	100	101	102
8	118	100	106	114	113	98	101	99	70	93	91	98
9	117	110	108	108	113	105	97	93	100	68	103	92
10	128	107	100	111	104	97	116	97	101	96	67	90
	RF CAL	0	1	2	3	4	5	6	7	8	9	10

### LO HARMONICS ORDER

Test conditions: RF IN: 250.1 MHz; -15.00 dBm.  
 LO IN: 280.01 MHz; +3.00 dBm  
 IF OUT: 29.91 MHz; -20.89 dBm

RF HARMONICS ORDER

	(-dBm)	(-dBc)										
0	-	-	27	42	33	40	34	54	52	72	59	70
1	-	17	0	28	14	37	24	41	43	52	52	66
2	98	58	50	58	52	63	51	57	48	72	61	67
3	93	45	47	49	50	53	48	51	52	57	55	64
4	90	68	70	69	79	66	77	65	70	71	66	80
5	93	70	67	67	58	69	54	64	53	77	56	73
6	97	83	88	81	93	96	77	87	78	82	79	81
7	93	79	77	86	73	87	74	75	70	74	69	76
8	96	95	92	89	94	88	103	93	89	92	95	92
9	97	102	89	104	81	100	81	92	89	71	96	89
10	95	103	101	103	107	100	97	90	96	94	83	95
	RF CAL	0	1	2	3	4	5	6	7	8	9	10

### LO HARMONICS ORDER

Test conditions: RF IN: 250.1 MHz; -5.00 dBm.  
 LO IN: 280.01 MHz; +3.00 dBm  
 IF OUT: 29.91 MHz; -11.01 dBm

- Notes: 1. All Harmonics are in (dBc) relative to IF OUTPUT.  
 2. + entry denotes harmonics are in (dBc) above IF OUTPUT.  
 3. RF Cal represent the Harmonics level of the RF input signal to the mixer.

REV. X2  
 ADE-1L+  
 100817  
 Page 3 of 3



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED • RoHS compliant  
 P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see [minicircuits.com](http://minicircuits.com)

# Case Style

# CD

CD541  
CD542  
CD636  
CD637

## Outline Dimensions



## PCB Land Pattern



Suggested Layout,  
Tolerance to be within  $\pm .002$

CASE#	A	B	C	D	E	F	G	H	J	K	L	WT, GRAM
CD541					.082 (2.08)							.15
CD542	.272 (6.91)	.310 (7.87)	.220 (5.58)	.100 (2.54)	.112 (2.84)	.055 (1.40)	.100 (2.54)	.030 (0.76)	.026 (0.66)	.065 (1.65)	.300 (7.62)	.20
CD636					.162 (4.11)							.25
CD637					.206 (5.23)							.40

Dimensions are in inches (mm). Tolerances: 2 Pl.  $\pm .01$ ; 3 Pl.  $\pm .005$

### Notes:

- Case material: Plastic.
- Termination finish:
  - For RoHS Case Styles: Tin plate over Nickel plate. All models, (+) suffix.
  - For RoHS-5 Case Styles: Tin-Lead plate. All models, no (+) suffix.

**Mini-Circuits®**

INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified

# Tape & Reel Packaging TR-F34



Tape Width, mm	Device Cavity Pitch, mm	Reel Size, inches	Devices per Reel see note	
16	12	7	Small quantity standard (see note)	20
				50
				100
				200
		13	Standard	500
				1000

Note: Availability of small reel quantity varies by model.  
Refer to pricing and availability on individual model dashboard.

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: [www.minicircuits.com/pages/pdfs/tape.pdf](http://www.minicircuits.com/pages/pdfs/tape.pdf)



INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified

THIRD ANGLE PROJECTION



REVISIONS

REV	ECN No.	DESCRIPTION	DATE	DR	AUTH
A	M101143	ADDED "gk" PIN CONNECTION, TT100 CASE STYLE & NOTE 2	10/10/05	MMG	DJ
B	M102713	ADDED "...WITH SMOBC"	01/17/06	MMG	IL
C	M108637	REMOVED "PIN 1", ADDED INDEX ON UNIT	12/01/06	MYG	FL

SUGGESTED MOUNTING CONFIGURATION  
FOR BH292, CD541/542/636/637, TT100/240 CASE  
STYLES, "gk", "ht", "hu", "nd", "w" PIN CONNECTIONS



- NOTES:** 1. TRACE WIDTH IS SHOWN FOR ROGERS R04350B WITH DIELECTRIC THICKNESS .030" ± .002"; COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.  
 2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.

- DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)
- DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

UNLESS OTHERWISE SPECIFIED	INITIALS	DATE
DIMENSIONS ARE IN INCHES	MMG	07/17/02
TOLERANCES ON:	WL	08/02/02
2 PL DECIMALS ±	DJ	08/05/02
3 PL DECIMALS ± .005		
ANGLES ±		
FRACTIONS ±		

**Mini-Circuits®** 13 Neptune Avenue  
 Brooklyn NY 11235

PL, gk/ht/hu/nd/w, BH292,  
 CD541/542/636/637, TT100/240, TB-03

SIZE A	CODE IDENT 15542	DRAWING NO: 98-PL-052	REV: C
FILE: 98PL052	SCALE: 8:1	SHEET: 1 OF 1	

Mini-Circuits®  
 THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.

THIRD ANGLE PROJECTION



REVISIONS

REV	ECN No.	DESCRIPTION	DATE	DR	AUTH
E	M119737	UPDATED PCB	10.08	MF	AD
F	M127659	UPDATED CARR	06.10	SW	SG
G	M127846	UPDATED SCHEMATIC DIAGRAM	06.10	SW	SG
H	M131840	UPDATED DWG	05.11	MF	AD




**NOTES:**

1. REFER TO -09 PAGE FOR ITEM DESCRIPTIONS.  
DESIGNATION NUMBERS ON -20 PAGE CORRESPOND TO THE NUMBERS ON -09 PAGE.
2. FOR TEXT HEIGHT & STYLE ON THE LABEL REFER TO: D3-G209.

UNLESS OTHERWISE SPECIFIED	INITIALS	DATE
DIMENSIONS ARE IN INCHES TOLERANCES ON: 2 PL DECIMALS ± 3 PL DECIMALS ± ANGLES ± FRACTIONS ±	DRAWN	S.WOLYNSKI 06.29.99
	CHECKED	SG 07.06.99
	APPROVED	MG 07.10.99

 **Mini-Circuits®** 13 Neptune Avenue  
Brooklyn NY 11235

TB,ADE,CD542/636,06MX01,50

 **Mini-Circuits®**  
THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.

ASHEETA1.DWG REV:A DATE:01/12/95

SIZE A	CODE IDENT 15542	DRAWING NO: TB-03-20	REV: H
FILE: WTB-03	SCALE: 1.5:1	SHEET: 1 OF 2	

# Evaluation Board and Circuit

For Pin Connections and DUT Orientation Refer to  
Data Sheet of the DUT



TB-03



Schematic Diagram

## Notes:

1. 50 Ohm SMA Female connectors.
2. PCB Material: Rogers R04350 or equivalent,  
Dielectric Constant=3.5, Thickness=.030 inch.

 **Mini-Circuits®**

All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-40° to 85°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Humidity	90 to 95% RH, 240 hours, 50°C	MIL-STD-202, Method 103, Condition A, Except 50°C and end-point electrical test done within 12 hours
Thermal Shock	-55° to 100°C, 100 cycles	MIL-STD-202, Method 107, Condition A-3, except +100°C
Solder Reflow Heat	Sn-Pb Eutetic Process: 225°C peak Pb-Free Process 245° - 250°C peak	J-STD-020, Table 4-1, 4-2 and 5-2, Figure 5-1
Solderability	10X Magnification	J-STD-002, 95% Coverage
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes	MIL-STD-202, Method 213, Condition A
Marking Resistance to Solvents	Isopropyl alcohol + mineral spirits at 25°C; terpene defluxer at 25°C; distilled water + proylene glycol monomethyl ether + monoethanolamine at 63°C to 70°C	MIL-STD-202, Method 215