

High IP3

# Frequency Mixer

ADE-201FMH+

Level 13 (LO Power +13 dBm) 90 to 200 MHz



CASE STYLE: CD636

## The Big Deal

- High IP3: +30 dBm
- Low conversion loss, 6.4 dB
- Excellent P1dB compression, +16 dBm at input
- High L-R isolation, 42 dB typ.
- High L-I isolation, 35 dB typ.

## Product Overview

Mini-Circuits' ADE-201FMH+ is a surface mount frequency mixer providing high IP3 performance, ideal for minimizing 3rd order intermodulation distortion in multiple carrier environments and other systems where unwanted signals may be present. It also provides high isolation, high P1dB compression point, and low conversion loss. The mixer comes in a compact, six-lead plastic case measuring 0.27 x 0.31 x 0.22", saving space in dense board layouts.

Feature	Advantages
High IP3, +30 dBm	Minimizes third order intermodulation distortion and enables high-dynamic range.
Low conversion loss, 6.4 dB	Enables lower NF front ends, improving system sensitivity.
Excellent P1dB compression, +16 dBm at input	Provides linear performance for a wide range of RF input power levels.
High L-R isolation, • L-R, 42 dB • L-I, 35 dB	Preserves signal integrity from input to output and reduces undesired signal responses that can interfere with system performance.
Small size (0.27 x 0.31 x 0.22")	Saves board space and accommodates tight layouts

### Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.  
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.  
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)



High IP3

# Frequency Mixer

## ADE-201FMH+

Level 13 (LO Power +13 dBm) 90 to 200 MHz


### Maximum Ratings

Operating Temperature	-40°C to 85°C
Storage Temperature	-55°C to 100°C
RF Power	20 dBm
LO Power	17 dBm
Permanent damage may occur if any of these limits are exceeded.	


### Pin Connections

LO	6
RF	4
IF	3
GROUND	1,2,5

### Outline Drawing



### PCB Land Pattern




Suggested Layout.  
Tolerance to be within ±.002

### Outline Dimensions (inch/mm)

A	B	C	D	E	F	G
.272	.310	.220	.100	.162	.055	.100
6.91	7.87	5.59	2.54	4.11	1.40	2.54
H	J	K	L			wt
.030	.026	.065	.300			grams
0.76	0.66	1.65	7.62			0.25

### Demo Board MCL P/N: TB-02 Suggested PCB Layout (PL-051)



- NOTES: 1. TRACE WIDTH IS SHOWN FOR ROGERS R04350B WITH DIELECTRIC THICKNESS .030" ± .002"; COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.  
2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.  
■ DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)  
■ DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

### Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.  
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.  
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)

### Features

- excellent IP3, 30 dBm typ.
- excellent P1dB compression, +16 dBm at input
- good L-R isolation, 42 dB typ.
- good L-I isolation, 35 dB typ.
- aqueous washable
- protected by U.S. patent 6,133,525

### Applications

- amateur radio
- mobil radio
- radar
- vehicle recovery system
- locator transmitters


### Electrical Specifications at 25°C

Parameter	Min.	Typ.	Max.	Unit
Frequency Range, RF	90	—	200	MHz
Frequency Range, LO	154	—	264	MHz
Frequency Range, IF	10	—	150	MHz
Conversion Loss	—	6.4	8.2	dB
LO to RF Isolation	34	42	—	dB
LO to IF Isolation	26	35	—	dB
IP3	—	30	—	dBm
RF Input Power at 1 dB Compression	—	+16	—	dBm

### Typical Performance Data

Frequency (MHz)	Conversion Loss (dB)		Isolation L-R (dB)		Isolation L-I (dB)		VSWR RF Port (:1)		VSWR LO Port (:1)		IP3 (dBm)
	LO	+13 dBm	LO	+13 dBm	LO	+13 dBm	LO	+13 dBm	LO	+13 dBm	
90.10	154.10	6.87	52.67	42.88	1.88	5.24	28.50				
100.10	164.10	6.79	50.96	40.90	1.92	5.03	29.99				
106.10	170.10	6.67	49.81	39.71	1.96	4.86	30.79				
110.10	174.10	6.57	48.93	38.94	1.98	4.70	31.12				
112.10	176.10	6.46	48.50	38.56	1.96	4.63	31.01				
114.10	178.10	6.41	48.14	38.20	1.96	4.55	31.67				
116.10	180.10	6.41	47.76	37.83	1.95	4.46	32.52				
118.10	182.10	6.39	47.29	37.44	1.94	4.35	32.32				
120.10	184.10	6.36	46.83	37.08	1.94	4.23	32.40				
130.10	194.10	6.23	45.00	35.42	1.97	3.55	33.15				
136.10	200.10	6.29	44.04	34.47	1.95	3.06	33.70				
138.10	202.10	6.26	43.81	34.16	1.94	2.89	32.69				
140.10	204.10	6.24	43.55	33.85	1.93	2.72	33.30				
142.10	206.10	6.26	43.25	33.58	1.92	2.56	32.81				
150.10	214.10	6.20	42.42	32.67	1.98	1.98	33.46				
160.10	224.10	6.28	41.79	32.22	1.94	1.61	34.49				
170.10	234.10	6.33	42.09	32.64	1.81	1.77	34.58				
180.10	244.10	6.43	43.19	33.44	1.82	2.17	34.26				
190.10	254.10	6.52	44.37	34.27	1.82	2.58	29.36				
200.10	264.10	6.55	45.33	35.02	1.69	2.94	27.92				

### Electrical Schematic



Generic photo used for illustration purposes only

CASE STYLE: CD636








+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

Available Tape and Reel at no extra cost

Reel Size	Devices/Reel
7"	20, 50, 100, 200
13"	500, 1000





**Notes**

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)



# Frequency Mixer

# ADE-201FMH+

## Typical Performance Data

RF (IN) (MHz)	LO (MHz)	CONVERSION LOSS IF FIXED @IF(OUT)=64MHz (dB)		
		@LO (dBm)		
		+10	+13	+16
40.1	104.1	7.29	7.10	6.94
50.1	114.1	7.25	6.98	6.87
60.1	124.1	7.18	6.95	6.83
72.1	136.1	7.21	7.01	6.88
82.1	146.1	7.10	6.96	6.83
92.1	156.1	7.00	6.88	6.76
106.1	170.1	6.80	6.67	6.55
114.1	178.1	6.54	6.41	6.33
126.1	190.1	6.38	6.28	6.18
136.1	200.1	6.38	6.29	6.17
146.1	210.1	6.27	6.18	6.11
158.1	222.1	6.37	6.27	6.20
168.1	232.1	6.46	6.35	6.24
180.1	244.1	6.54	6.43	6.33
190.1	254.1	6.65	6.52	6.43
200.1	264.1	6.72	6.55	6.43
212.1	276.1	6.80	6.61	6.45
222.1	286.1	6.84	6.62	6.44
232.1	296.1	6.91	6.66	6.45
244.1	308.1	7.13	6.84	6.61
254.1	318.1	7.31	6.99	6.76
266.1	330.1	7.49	7.15	6.88
276.1	340.1	7.64	7.25	6.98
286.1	350.1	7.86	7.44	7.15
298.1	362.1	8.03	7.59	7.25
308.1	372.1	8.17	7.68	7.32
320.1	384.1	8.30	7.77	7.37
330.1	394.1	8.48	7.90	7.47
340.1	404.1	8.69	8.06	7.60
352.1	416.1	8.91	8.25	7.76
362.1	426.1	9.12	8.42	7.92
372.1	436.1	9.32	8.58	8.08
384.1	448.1	9.52	8.77	8.23
394.1	458.1	9.67	8.89	8.35
406.1	470.1	9.83	9.00	8.42
416.1	480.1	9.97	9.10	8.51
426.1	490.1	10.13	9.22	8.59
438.1	502.1	10.37	9.41	8.75
448.1	512.1	10.53	9.54	8.85
460.1	524.1	10.73	9.70	8.97

RF (IN) (MHz)	LO (MHz)	IP-3 INPUT (dBm)		
		@LO (dBm)		
		+10	+13	+16
40.1	104.1	25.42	23.71	23.20
50.1	114.1	20.94	22.27	24.69
60.1	124.1	20.46	22.94	26.22
72.1	136.1	22.40	25.40	28.60
82.1	146.1	24.09	26.84	27.84
92.1	156.1	25.84	29.06	29.44
106.1	170.1	27.88	31.09	32.83
114.1	178.1	28.68	31.26	34.86
126.1	190.1	31.30	34.27	34.33
136.1	200.1	31.62	34.21	36.94
146.1	210.1	31.86	33.45	34.20
158.1	222.1	32.85	33.81	36.44
168.1	232.1	32.67	34.21	36.82
180.1	244.1	29.89	33.03	37.79
190.1	254.1	27.86	29.46	34.32
200.1	264.1	26.37	28.24	29.36
212.1	276.1	24.62	26.97	28.19
222.1	286.1	22.97	25.76	27.56
232.1	296.1	21.31	24.05	26.12
244.1	308.1	19.78	22.68	25.13
254.1	318.1	18.86	21.74	24.32
266.1	330.1	17.69	20.71	23.27
276.1	340.1	16.83	19.71	22.33
286.1	350.1	16.09	18.76	21.67
298.1	362.1	15.54	18.18	20.72
308.1	372.1	15.14	17.66	20.14
320.1	384.1	14.34	16.79	19.18
330.1	394.1	13.58	16.08	18.56
340.1	404.1	13.15	15.67	18.10
352.1	416.1	12.84	15.45	17.84
362.1	426.1	12.40	14.94	17.40
372.1	436.1	11.98	14.49	16.95
384.1	448.1	11.81	14.23	16.57
394.1	458.1	11.78	14.25	16.58
406.1	470.1	11.65	13.99	16.20
416.1	480.1	11.42	13.73	15.93
426.1	490.1	11.17	13.43	15.64
438.1	502.1	11.04	13.35	15.52
448.1	512.1	10.89	13.13	15.22
460.1	524.1	10.72	12.92	14.90

RF (IN) (MHz)	LO (MHz)	COMPRESSION @RF IN=+16dBm (dB)		
		@LO (dBm)		
		+10	+13	+16
40.1	104.1	1.77	0.85	0.39
50.1	114.1	1.85	1.03	0.55
60.1	124.1	1.82	1.03	0.62
72.1	136.1	1.48	0.83	0.50
82.1	146.1	1.22	0.69	0.43
92.1	156.1	0.99	0.56	0.35
106.1	170.1	0.69	0.39	0.28
114.1	178.1	0.60	0.37	0.26
126.1	190.1	0.46	0.28	0.23
136.1	200.1	0.40	0.23	0.23
146.1	210.1	0.36	0.27	0.21
158.1	222.1	0.33	0.25	0.19
168.1	232.1	0.38	0.24	0.22
180.1	244.1	0.57	0.34	0.26
190.1	254.1	0.78	0.42	0.27
200.1	264.1	1.10	0.57	0.35
212.1	276.1	1.63	0.75	0.42
222.1	286.1	2.26	1.05	0.55
232.1	296.1	2.93	1.47	0.71
244.1	308.1	3.75	1.98	0.94
254.1	318.1	4.33	2.46	1.15
266.1	330.1	4.97	3.01	1.47
276.1	340.1	5.31	3.36	1.72
286.1	350.1	5.58	3.65	2.00
298.1	362.1	5.91	3.99	2.28
308.1	372.1	6.21	4.31	2.55
320.1	384.1	6.74	4.83	2.99
330.1	394.1	7.16	5.28	3.40
340.1	404.1	7.52	5.63	3.73
352.1	416.1	7.94	6.08	4.14
362.1	426.1	8.22	6.33	4.41
372.1	436.1	8.35	6.52	4.59
384.1	448.1	8.41	6.60	4.66
394.1	458.1	8.50	6.72	4.80
406.1	470.1	8.72	6.94	5.04
416.1	480.1	8.88	7.17	5.27
426.1	490.1	9.09	7.41	5.49
438.1	502.1	9.31	7.64	5.76
448.1	512.1	9.49	7.84	5.95
460.1	524.1	9.57	7.92	6.08

# Frequency Mixer

# ADE-201FMH+

## Typical Performance Data

IF (OUT) (MHz)	LO (MHz)	CONVERSION LOSS VS. IF FREQUENCY @RF(IN)=146.1MHz (dB)	IF (OUT) (MHz)	LO (MHz)	CONVERSION LOSS VS. IF FREQUENCY @RF(IN)=106.1MHz (dB)	IF (OUT) (MHz)	LO (MHz)	CONVERSION LOSS VS. IF FREQUENCY @RF(IN)=186.1MHz (dB)
		@LO (dBm)			@LO (dBm)			@LO (dBm)
		+13			+13			+13
136.0	10.1	11.76	10.0	116.1	7.77	176.0	10.1	12.02
130.0	16.1	10.28	20.0	126.1	7.54	172.0	14.1	11.13
124.0	22.1	9.46	30.0	136.1	7.38	168.0	18.1	10.43
118.0	28.1	8.90	40.0	146.1	7.14	164.0	22.1	9.95
112.0	34.1	8.55	50.0	156.1	7.06	160.0	26.1	9.56
104.0	42.1	8.22	62.0	168.1	6.94	156.0	30.1	9.29
98.0	48.1	7.95	72.0	178.1	6.83	152.0	34.1	9.08
92.0	54.1	7.73	82.0	188.1	6.76	148.0	38.1	8.97
86.0	60.1	7.63	92.0	198.1	6.72	144.0	42.1	8.80
78.0	68.1	7.45	104.0	210.1	6.59	140.0	46.1	8.64
72.0	74.1	7.31	114.0	220.1	6.73	136.0	50.1	8.45
66.0	80.1	7.27	124.0	230.1	6.73	132.0	54.1	8.33
60.0	86.1	7.23	134.0	240.1	6.72	128.0	58.1	8.24
52.0	94.1	7.19	146.0	252.1	6.76	124.0	62.1	8.15
46.0	100.1	7.14	156.0	262.1	6.79	120.0	66.1	8.03
40.0	106.1	7.09	166.0	272.1	6.83	116.0	70.1	7.92
34.0	112.1	7.06	176.0	282.1	6.93	112.0	74.1	7.86
28.0	118.1	6.95	186.0	292.1	7.01	108.0	78.1	7.84
20.0	126.1	6.92	198.0	304.1	7.10	104.0	82.1	7.82
14.0	132.1	7.00	208.0	314.1	7.21	100.0	86.1	7.77
10.0	156.1	6.69	218.0	324.1	7.30	96.0	90.1	7.74
28.0	174.1	6.47	228.0	334.1	7.44	92.0	94.1	7.55
46.0	192.1	6.35	240.0	346.1	7.58	88.0	98.1	7.57
66.0	212.1	6.33	250.0	356.1	7.68	84.0	102.1	7.59
84.0	230.1	6.25	260.0	366.1	7.74	80.0	106.1	7.57
104.0	250.1	6.31	270.0	376.1	7.87	76.0	110.1	7.64
122.0	268.1	6.37	282.0	388.1	7.97	72.0	114.1	7.58
142.0	288.1	6.47	292.0	398.1	8.10	68.0	118.1	7.50
160.0	306.1	6.70	302.0	408.1	8.12	64.0	122.1	7.46
178.0	324.1	6.79	312.0	418.1	8.27	60.0	126.1	7.45
198.0	344.1	6.87	322.0	428.1	8.42	56.0	130.1	7.38
216.0	362.1	6.89	334.0	440.1	8.52	52.0	134.1	7.32
236.0	382.1	6.99	344.0	450.1	8.62	48.0	138.1	7.27
254.0	400.1	7.16	354.0	460.1	8.71	44.0	142.1	7.27
274.0	420.1	7.32	364.0	470.1	8.83	40.0	146.1	7.16
292.0	438.1	7.40	376.0	482.1	8.96	36.0	150.1	7.18
310.0	456.1	7.52	386.0	492.1	9.09	32.0	154.1	7.11
330.0	476.1	7.65	396.0	502.1	9.21	28.0	158.1	7.03
348.0	494.1	7.82	406.0	512.1	9.37	24.0	162.1	7.11
368.0	514.1	7.98	418.0	524.1	9.50	20.0	166.1	7.01

# Frequency Mixer

# ADE-201FMH+

## Typical Performance Data

LO (MHz)	LO-RF ISOLATION (dB)			LO-IF ISOLATION (dB)			RF (IN) (MHz)	LO (MHz)	RF-IF ISOLATION (dB)		
	@LO (dBm)			@LO (dBm)					@LO (dBm)		
	+10	+13	+16	+10	+13	+16			+10	+13	+16
104.1	59.34	59.12	59.35	49.17	49.03	48.98	40.1	104.1	22.32	21.53	20.61
114.1	57.58	57.59	57.74	48.21	48.04	47.93	50.1	114.1	21.17	20.61	20.11
124.1	56.61	56.82	56.96	47.32	47.13	47.00	60.1	124.1	24.33	23.84	23.52
136.1	55.39	55.36	55.19	45.90	45.81	45.67	72.1	136.1	27.85	27.27	26.94
146.1	54.04	53.80	53.70	44.43	44.28	44.15	82.1	146.1	30.37	29.99	29.90
156.1	52.54	52.42	52.12	42.67	42.52	42.36	92.1	156.1	33.69	33.38	33.46
170.1	50.12	49.81	49.62	39.91	39.71	39.50	106.1	170.1	35.95	35.82	35.80
178.1	48.39	48.14	47.93	38.42	38.20	38.01	114.1	178.1	38.53	38.24	38.15
190.1	45.95	45.71	45.58	36.29	36.05	35.86	126.1	190.1	40.42	40.53	40.89
200.1	44.26	44.04	43.90	34.71	34.47	34.27	136.1	200.1	42.57	42.70	42.77
210.1	42.90	42.80	42.64	33.28	33.08	32.89	146.1	210.1	42.15	42.16	42.16
222.1	41.97	41.86	41.99	32.37	32.24	32.37	158.1	222.1	41.05	40.96	41.17
232.1	42.06	42.00	41.99	32.60	32.51	32.51	168.1	232.1	38.65	38.90	39.25
244.1	43.25	43.19	43.12	33.51	33.44	33.37	180.1	244.1	37.46	37.74	37.80
254.1	44.51	44.37	44.34	34.33	34.27	34.22	190.1	254.1	35.86	35.97	36.14
264.1	45.50	45.33	45.25	35.09	35.02	34.96	200.1	264.1	35.55	35.43	35.63
276.1	46.12	45.87	45.74	35.91	35.83	35.77	212.1	276.1	33.92	33.55	33.39
286.1	46.69	46.43	46.24	36.57	36.47	36.40	222.1	286.1	33.78	33.54	33.09
296.1	47.85	47.59	47.34	37.25	37.16	37.09	232.1	296.1	33.56	33.20	32.91
308.1	49.58	49.22	49.01	38.03	37.96	37.89	244.1	308.1	33.24	33.24	32.79
318.1	50.56	50.06	49.72	38.60	38.51	38.46	254.1	318.1	32.71	32.75	32.27
330.1	51.43	50.86	50.49	39.04	38.99	38.93	266.1	330.1	31.73	31.63	31.33
340.1	52.41	51.86	51.35	39.26	39.20	39.16	276.1	340.1	32.13	31.92	31.74
350.1	53.39	52.80	52.30	39.37	39.35	39.32	286.1	350.1	31.08	30.89	30.57
362.1	53.99	53.24	52.74	39.45	39.44	39.42	298.1	362.1	31.96	31.51	31.04
372.1	54.30	53.63	52.98	39.58	39.58	39.59	308.1	372.1	30.86	30.32	29.78
384.1	55.17	54.23	53.50	39.69	39.73	39.76	320.1	384.1	31.79	31.30	30.83
394.1	56.07	55.23	54.46	39.96	40.04	40.08	330.1	394.1	31.22	30.31	29.84
404.1	56.83	55.80	54.93	40.16	40.24	40.30	340.1	404.1	32.54	31.65	30.91
416.1	58.21	56.98	56.00	40.39	40.50	40.59	352.1	416.1	32.40	31.22	30.54
426.1	59.99	58.58	57.45	40.38	40.50	40.60	362.1	426.1	33.38	31.83	31.11
436.1	61.33	60.02	58.70	40.39	40.54	40.67	372.1	436.1	33.93	31.97	31.15
448.1	61.00	60.05	58.93	40.30	40.43	40.57	384.1	448.1	34.83	32.46	31.44
458.1	60.72	59.72	58.58	40.21	40.36	40.53	394.1	458.1	36.10	33.29	32.10
470.1	61.17	60.72	59.72	40.07	40.22	40.37	406.1	470.1	36.80	33.34	31.96
480.1	62.33	62.80	61.90	40.24	40.41	40.55	416.1	480.1	38.64	34.25	32.50
490.1	62.08	63.09	63.17	40.34	40.52	40.73	426.1	490.1	39.87	34.25	32.05
502.1	59.55	60.84	61.21	40.56	40.74	40.98	438.1	502.1	45.69	36.81	33.86
512.1	60.05	61.16	60.77	40.57	40.79	41.02	448.1	512.1	48.76	36.97	33.49
524.1	59.75	62.58	64.88	40.42	40.65	40.87	460.1	524.1	49.76	40.36	35.20

# Frequency Mixer

# ADE-201FMH+

## Typical Performance Data

RF (IN) (MHz)	LO (MHz)	RF VSWR (:1)			LO (MHz)	LO VSWR (:1)			IF (OUT) (MHz)	IF VSWR @LO=250.1MHz (:1)		
		@LO (dBm)				@LO (dBm)				@LO (dBm)		
		+10	+13	+16		+10	+13	+16		+10	+13	+16
40.1	104.1	1.65	1.76	1.85	104.1	5.55	5.55	5.54	10.1	1.34	1.29	1.30
50.1	114.1	1.68	1.78	1.88	114.1	5.57	5.57	5.56	14.1	1.36	1.27	1.23
60.1	124.1	1.74	1.85	1.95	124.1	5.50	5.49	5.49	20.1	1.32	1.29	1.25
72.1	136.1	1.74	1.85	1.95	136.1	5.42	5.42	5.42	26.1	1.33	1.30	1.25
82.1	146.1	1.76	1.87	1.99	146.1	5.35	5.35	5.35	32.1	1.41	1.34	1.29
92.1	156.1	1.78	1.89	2.00	156.1	5.21	5.20	5.20	38.1	1.45	1.38	1.34
106.1	170.1	1.85	1.96	2.07	170.1	4.87	4.86	4.84	44.1	1.47	1.42	1.36
114.1	178.1	1.85	1.96	2.07	178.1	4.57	4.55	4.52	50.1	1.47	1.41	1.35
126.1	190.1	1.85	1.95	2.05	190.1	3.90	3.86	3.82	56.1	1.44	1.37	1.32
136.1	200.1	1.86	1.95	2.04	200.1	3.11	3.06	3.01	62.1	1.39	1.33	1.28
146.1	210.1	1.85	1.93	2.02	210.1	2.30	2.25	2.20	68.1	1.37	1.32	1.26
158.1	222.1	1.87	1.96	2.04	222.1	1.66	1.64	1.62	74.1	1.38	1.33	1.28
168.1	232.1	1.74	1.83	1.90	232.1	1.70	1.71	1.73	80.1	1.39	1.34	1.29
180.1	244.1	1.73	1.82	1.90	244.1	2.14	2.17	2.19	86.1	1.41	1.35	1.31
190.1	254.1	1.72	1.82	1.91	254.1	2.55	2.58	2.61	92.1	1.41	1.35	1.30
200.1	264.1	1.60	1.69	1.78	264.1	2.92	2.94	2.97	98.1	1.38	1.32	1.27
212.1	276.1	1.59	1.67	1.76	276.1	3.29	3.30	3.33	104.1	1.34	1.28	1.23
222.1	286.1	1.58	1.66	1.75	286.1	3.53	3.54	3.56	110.1	1.30	1.25	1.20
232.1	296.1	1.56	1.63	1.71	296.1	3.72	3.73	3.74	116.1	1.30	1.25	1.20
244.1	308.1	1.52	1.58	1.65	308.1	3.92	3.92	3.93	122.1	1.34	1.28	1.24
254.1	318.1	1.54	1.60	1.66	318.1	4.04	4.04	4.05	126.1	1.37	1.31	1.27
266.1	330.1	1.55	1.61	1.67	330.1	4.15	4.16	4.17	132.1	1.40	1.35	1.30
276.1	340.1	1.54	1.59	1.65	340.1	4.24	4.25	4.26	138.1	1.41	1.35	1.30
286.1	350.1	1.58	1.63	1.68	350.1	4.32	4.33	4.33	144.1	1.39	1.33	1.28
298.1	362.1	1.63	1.68	1.73	362.1	4.39	4.40	4.40	150.1	1.35	1.29	1.24
308.1	372.1	1.66	1.70	1.76	372.1	4.44	4.45	4.45	156.1	1.30	1.25	1.20
320.1	384.1	1.67	1.71	1.76	384.1	4.50	4.51	4.51	162.1	1.28	1.23	1.18
330.1	394.1	1.75	1.79	1.84	394.1	4.55	4.55	4.55	168.1	1.29	1.24	1.19
340.1	404.1	1.77	1.82	1.87	404.1	4.57	4.58	4.58	174.1	1.31	1.25	1.20
352.1	416.1	1.78	1.82	1.87	416.1	4.60	4.60	4.61	180.1	1.31	1.25	1.21
362.1	426.1	1.82	1.87	1.91	426.1	4.62	4.63	4.63	186.1	1.29	1.24	1.19
372.1	436.1	1.86	1.91	1.96	436.1	4.64	4.65	4.64	192.1	1.25	1.20	1.15
384.1	448.1	1.89	1.95	2.00	448.1	4.69	4.69	4.69	198.1	1.21	1.16	1.12
394.1	458.1	1.91	1.96	2.01	458.1	4.71	4.71	4.71	204.1	1.20	1.15	1.11
406.1	470.1	1.97	2.02	2.07	470.1	4.74	4.74	4.74	210.1	1.22	1.17	1.13
416.1	480.1	2.00	2.07	2.13	480.1	4.76	4.76	4.77	216.1	1.25	1.20	1.16
426.1	490.1	1.99	2.05	2.11	490.1	4.77	4.77	4.77	222.1	1.27	1.22	1.17
438.1	502.1	2.03	2.09	2.15	502.1	4.80	4.80	4.80	228.1	1.27	1.21	1.17
448.1	512.1	2.04	2.10	2.16	512.1	4.80	4.81	4.81	234.1	1.24	1.19	1.14
460.1	524.1	2.06	2.12	2.18	524.1	4.83	4.83	4.83	240.1	1.20	1.15	1.10

## Harmonics Tables

RF HARMONICS ORDER

	(-dBm)	(-dBc)										
0	---	---	-0.56	15.44	25.44	22.46	26.51	16.80	25.27	24.48	27.68	41.40
1	---	29.50	---	33.94	10.35	34.92	20.12	40.95	32.03	41.97	61.77	45.11
2	122.38	73.83	77.02	80.07	80.85	84.28	102.54	87.76	98.97	87.53	91.67	85.95
3	129.28	101.47	88.51	102.27	90.56	101.07	98.81	105.04	103.22	101.72	103.50	102.59
4	129.21	101.52	99.64	93.39	102.29	95.25	101.82	101.45	103.45	102.84	104.04	101.07
5	129.13	102.56	101.71	96.86	99.05	96.32	98.74	100.06	102.92	103.38	103.27	103.42
6	129.61	103.72	101.64	102.31	88.73	102.95	84.74	103.89	99.97	100.64	101.55	103.10
7	129.81	103.98	102.68	99.91	101.18	91.76	103.46	92.11	102.81	99.32	103.55	104.45
8	129.53	103.60	103.29	105.19	101.08	98.77	96.82	96.43	96.03	102.43	103.09	104.49
9	126.01	100.62	101.90	100.44	103.30	99.21	94.74	98.12	93.37	95.09	100.99	102.18
10	129.74	95.80	98.56	86.14	100.88	77.53	98.80	66.30	93.20	64.90	101.57	77.15
	RF CAL	0	1	2	3	4	5	6	7	8	9	10

### LO HARMONICS ORDER

Test conditions: RF IN: 146 MHz; -15 dBm.  
 LO IN: 210 MHz; +13.00 dBm  
 IF OUT: 64 MHz; -21.71 dBm

RF HARMONICS ORDER








	(-dBm)	(-dBc)										
0	---	---	9.65	25.63	35.61	32.61	36.74	26.85	35.38	33.86	36.57	53.80
1	---	29.41	---	33.93	10.34	34.94	20.04	41.00	31.73	42.05	61.21	45.18
2	111.01	63.41	67.22	69.71	71.31	73.97	96.73	77.59	87.80	77.53	81.22	75.05
3	122.59	95.34	91.54	95.00	80.38	92.75	78.34	93.60	82.03	94.92	90.20	100.03
4	125.15	101.02	108.99	92.56	104.39	96.53	103.76	107.64	105.41	114.11	108.52	108.88
5	124.02	111.63	96.65	108.83	96.73	106.54	99.77	113.37	99.81	112.48	102.15	109.09
6	120.28	110.67	104.98	110.18	92.27	109.36	88.46	109.82	98.71	111.76	105.73	111.79
7	123.18	113.06	112.84	111.38	112.78	102.21	113.83	102.45	113.89	109.52	111.81	112.78
8	123.09	113.65	112.84	114.47	110.92	107.63	107.31	108.41	107.11	112.79	113.21	114.38
9	120.32	113.98	113.11	104.92	111.26	101.54	101.42	99.67	103.60	93.51	110.38	102.18
10	123.80	109.34	110.26	102.60	113.06	90.80	111.72	80.99	110.65	80.44	111.87	91.16
	RF CAL	0	1	2	3	4	5	6	7	8	9	10

### LO HARMONICS ORDER







Test conditions: RF IN: 146 MHz; -5 dBm.  
 LO IN: 210 MHz; +13.00 dBm  
 IF OUT: 64 MHz; -11.54 dBm

- Notes:
1. All Harmonics are in (dBc) relative to IF OUTPUT
  2. + entry denotes harmonics are in (dBc) above IF OUTPUT
  3. RF Cal represents the Harmonics level of the RF Input Signal to the mixer

## Typical Performance Curves



## Typical Performance Curves



## Harmonics Tables

RF HARMONICS ORDER

	(-dBm)	(-dBc)										
0	---	---	-0.56	15.44	25.44	22.46	26.51	16.80	25.27	24.48	27.68	41.40
1	---	29.50	---	33.94	10.35	34.92	20.12	40.95	32.03	41.97	61.77	45.11
2	122.38	73.83	77.02	80.07	80.85	84.28	102.54	87.76	98.97	87.53	91.67	85.95
3	129.28	101.47	88.51	102.27	90.56	101.07	98.81	105.04	103.22	101.72	103.50	102.59
4	129.21	101.52	99.64	93.39	102.29	95.25	101.82	101.45	103.45	102.84	104.04	101.07
5	129.13	102.56	101.71	96.86	99.05	96.32	98.74	100.06	102.92	103.38	103.27	103.42
6	129.61	103.72	101.64	102.31	88.73	102.95	84.74	103.89	99.97	100.64	101.55	103.10
7	129.81	103.98	102.68	99.91	101.18	91.76	103.46	92.11	102.81	99.32	103.55	104.45
8	129.53	103.60	103.29	105.19	101.08	98.77	96.82	96.43	96.03	102.43	103.09	104.49
9	126.01	100.62	101.90	100.44	103.30	99.21	94.74	98.12	93.37	95.09	100.99	102.18
10	129.74	95.80	98.56	86.14	100.88	77.53	98.80	66.30	93.20	64.90	101.57	77.15
	RF CAL	0	1	2	3	4	5	6	7	8	9	10

### LO HARMONICS ORDER

Test conditions: RF IN: 146 MHz; -15 dBm.  
 LO IN: 210 MHz; +13.00 dBm  
 IF OUT: 64 MHz; -21.71 dBm

RF HARMONICS ORDER

	(-dBm)	(-dBc)										
0	---	---	9.65	25.63	35.61	32.61	36.74	26.85	35.38	33.86	36.57	53.80
1	---	29.41	---	33.93	10.34	34.94	20.04	41.00	31.73	42.05	61.21	45.18
2	111.01	63.41	67.22	69.71	71.31	73.97	96.73	77.59	87.80	77.53	81.22	75.05
3	122.59	95.34	91.54	95.00	80.38	92.75	78.34	93.60	82.03	94.92	90.20	100.03
4	125.15	101.02	108.99	92.56	104.39	96.53	103.76	107.64	105.41	114.11	108.52	108.88
5	124.02	111.63	96.65	108.83	96.73	106.54	99.77	113.37	99.81	112.48	102.15	109.09
6	120.28	110.67	104.98	110.18	92.27	109.36	88.46	109.82	98.71	111.76	105.73	111.79
7	123.18	113.06	112.84	111.38	112.78	102.21	113.83	102.45	113.89	109.52	111.81	112.78
8	123.09	113.65	112.84	114.47	110.92	107.63	107.31	108.41	107.11	112.79	113.21	114.38
9	120.32	113.98	113.11	104.92	111.26	101.54	101.42	99.67	103.60	93.51	110.38	102.18
10	123.80	109.34	110.26	102.60	113.06	90.80	111.72	80.99	110.65	80.44	111.87	91.16
	RF CAL	0	1	2	3	4	5	6	7	8	9	10

### LO HARMONICS ORDER

Test conditions: RF IN: 146 MHz; -5 dBm.  
 LO IN: 210 MHz; +13.00 dBm  
 IF OUT: 64 MHz; -11.54 dBm



- Notes:
1. All Harmonics are in (dBc) relative to IF OUTPUT
  2. + entry denotes harmonics are in (dBc) above IF OUTPUT
  3. RF Cal represents the Harmonics level of the RF Input Signal to the mixer

# Case Style


# CD

CD541  
CD542  
CD636  
CD637

## Outline Dimensions



## PCB Land Pattern



Suggested Layout,  
Tolerance to be within ±.002

CASE#	A	B	C	D	E	F	G	H	J	K	L	WT, GRAM
CD541					.082 (2.08)							.15
CD542	.272 (6.91)	.310 (7.87)	.220 (5.58)	.100 (2.54)	.112 (2.84)	.055 (1.40)	.100 (2.54)	.030 (0.76)	.026 (0.66)	.065 (1.65)	.300 (7.62)	.20
CD636					.162 (4.11)							.25
CD637					.206 (5.23)							.40

Dimensions are in inches (mm). Tolerances: 2 Pl. ± .01; 3 Pl. ± .005

### Notes:

- Case material: Plastic.
- Termination finish:
  - For RoHS Case Styles: Tin plate over Nickel plate. All models, (+) suffix.
  - For RoHS-5 Case Styles: Tin-Lead plate. All models, no (+) suffix.

**Mini-Circuits®**


INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified

# Tape & Reel Packaging TR-F34



Tape Width, mm	Device Cavity Pitch, mm	Reel Size, inches	Devices per Reel see note	
16	12	7	Small quantity standard (see note)	20
				50
				100
				200
		13	Standard	500
				1000

Note: Availability of small reel quantity varies by model.  
Refer to pricing and availability on individual model dashboard.

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: [www.minicircuits.com/pages/pdfs/tape.pdf](http://www.minicircuits.com/pages/pdfs/tape.pdf)




INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified


THIRD ANGLE PROJECTION





REVISIONS

REV	ECN No.	DESCRIPTION	DATE	DR	AUTH
OR	M82272	NEW RELEASE	08/05/02	MMG	DJ
A	M102713	ADDED NOTE 2 & "...WITH SMOBC"	01/17/06	MMG	IL

SUGGESTED MOUNTING CONFIGURATION  
FOR CD541/542/636/637 CASE STYLES,  
"jv", "ju", "jw" PIN CONNECTIONS



- NOTES:** 1. TRACE WIDTH IS SHOWN FOR ROGERS R04350B WITH DIELECTRIC THICKNESS .030" ± .002"; COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.  
 2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.

-  DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)  
 DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

UNLESS OTHERWISE SPECIFIED

DIMENSIONS ARE IN INCHES  
 TOLERANCES ON:  
 2 PL DECIMALS ±  
 3 PL DECIMALS ± .005  
 ANGLES ±  
 FRACTIONS ±


	INITIALS	DATE
DRAWN	MMG	07/17/02
CHECKED	WL	08/02/02
APPROVED	DJ	08/05/02



**Mini-Circuits®**

13 Neptune Avenue  
 Brooklyn NY 11235

PL, jv/ju/jw, CD541/542/636/637, ADE, TB-02



 Mini-Circuits®  
 THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.

ASHEETA1.DWG REV:A DATE:01/12/95

SIZE	CODE IDENT	DRAWING NO:	REV:
A	15542	98-PL-051	A
FILE:	98PL051	SCALE: 8:1	SHEET: 1 OF 1

# Evaluation Board and Circuit


For Pin Connections refer to Data Sheet of the DUT



Schematic Diagram

## Notes:

1. SMA Female connectors.
2. PCB Material: Rogers R04350 or equivalent,  
Dielectric Constant=3.5, Thickness=.030 inch.



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-40° to 85°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Humidity	90 to 95% RH, 240 hours, 50°C	MIL-STD-202, Method 103, Condition A, Except 50°C and end-point electrical test done within 12 hours
Thermal Shock	-55° to 100°C, 100 cycles	MIL-STD-202, Method 107, Condition A-3, except +100°C
Solder Reflow Heat	Sn-Pb Eutetic Process: 225°C peak Pb-Free Process 245° - 250°C peak	J-STD-020, Table 4-1, 4-2 and 5-2, Figure 5-1
Solderability	10X Magnification	J-STD-002, 95% Coverage
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes	MIL-STD-202, Method 213, Condition A
Marking Resistance to Solvents	Isopropyl alcohol + mineral spirits at 25°C; terpene defluxer at 25°C; distilled water + proylene glycol monomethyl ether + monoethanolamine at 63°C to 70°C	MIL-STD-202, Method 215