

# Surface Mount Frequency Mixer

Level 7 (LO Power +7 dBm) 0.05 to 250 MHz

## ADE-6+ ADE-6



CASE STYLE: CD637  
PRICE: \$4.95 ea. QTY (20)

**+RoHS Compliant**

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

### Maximum Ratings

|                                                                 |                |
|-----------------------------------------------------------------|----------------|
| Operating Temperature                                           | -40°C to 85°C  |
| Storage Temperature                                             | -55°C to 100°C |
| RF Power                                                        | 50mW           |
| IF Current                                                      | 40mA           |
| Permanent damage may occur if any of these limits are exceeded. |                |

### Pin Connections

|        |       |
|--------|-------|
| LO     | 6     |
| RF     | 3     |
| IF     | 2     |
| GROUND | 1,4,5 |

### Features

- low conversion loss, 4.6 dB typ.
- excellent L-R isolation, 40 dB typ.
- low profile package
- aqueous washable
- protected by U.S. Patent 6,133,525

### Applications


- cellular




Available Tape and Reel  
at no extra cost

| Reel Size | Devices/Reel          |
|-----------|-----------------------|
| 7"        | 20, 50, 100, 200, 500 |
| 13"       | 500, 1000             |

### Outline Drawing



#### PCB Land Pattern




Suggested Layout,  
Tolerance to be within ±.002

### Outline Dimensions (inch)

| A    | B    | C    | D    | E     | F    | G    |
|------|------|------|------|-------|------|------|
| .272 | .310 | .220 | .100 | .206  | .055 | .100 |
| 6.91 | 7.87 | 5.59 | 2.54 | 5.23  | 1.40 | 2.54 |
| H    | J    | K    | L    | wt    |      |      |
| .030 | .026 | .065 | .300 | grams |      |      |
| 0.76 | 0.66 | 1.65 | 7.62 | 0.40  |      |      |

### Demo Board MCL P/N: TB-03 Suggested PCB Layout (PL-052)



### Electrical Specifications

| FREQUENCY<br>(MHz) |        | CONVERSION LOSS<br>(dB) |          |      |                | LO-RF ISOLATION<br>(dB) |      |      |      |      |      | LO-IF ISOLATION<br>(dB) |      |      |      |    |    | IP3<br>at center<br>band<br>(dBm) |
|--------------------|--------|-------------------------|----------|------|----------------|-------------------------|------|------|------|------|------|-------------------------|------|------|------|----|----|-----------------------------------|
| LO/RF              | IF     | Mid-Band                |          |      | Total<br>Range | L                       |      | M    |      | U    |      | L                       |      | M    |      | U  |    |                                   |
|                    |        | $\overline{X}$          | $\sigma$ | Max. |                | Typ.                    | Min. | Typ. | Min. | Typ. | Min. | Typ.                    | Min. | Typ. | Min. |    |    |                                   |
|                    |        | $f_L$ - $f_U$           |          |      |                |                         |      |      |      |      |      |                         |      |      |      |    |    |                                   |
| 0.05-250           | DC-200 | 4.6                     | 0.5      | 7.0  | 8.4            | 62                      | 49   | 40   | 30   | 40   | 20   | 58                      | 44   | 45   | 24   | 25 | 15 | 10                                |

1 dB COMP.: +1 dBm typ.


L = low range [ $f_L$  to  $10 f_L$ ]  
m = mid band [ $2 f_L$  to  $f_U/2$ ]

M = mid range [ $10 f_L$  to  $f_U/2$ ]  
U = upper range [ $f_U/2$  to  $f_U$ ]

### Typical Performance Data

| Frequency (MHz) |        | Conversion Loss (dB) | Isolation L-R (dB) | Isolation L-I (dB) | VSWR RF Port (:1) | VSWR LO Port (:1) |
|-----------------|--------|----------------------|--------------------|--------------------|-------------------|-------------------|
| RF              | LO     | LO +7dBm             | LO +7dBm           | LO +7dBm           | LO +7dBm          | LO +7dBm          |
| 0.05            | 30.05  | 4.68                 | 59.77              | 56.14              | 1.58              | 2.30              |
| 10.00           | 40.00  | 4.13                 | 66.00              | 52.10              | 1.27              | 2.52              |
| 26.76           | 56.76  | 4.22                 | 68.60              | 49.00              | 1.23              | 2.55              |
| 40.00           | 70.00  | 4.19                 | 66.80              | 46.10              | 1.21              | 2.58              |
| 53.42           | 83.42  | 4.35                 | 57.30              | 45.60              | 1.18              | 2.55              |
| 60.00           | 90.00  | 4.32                 | 54.40              | 44.40              | 1.18              | 2.61              |
| 80.00           | 110.00 | 4.18                 | 56.90              | 41.50              | 1.13              | 2.55              |
| 100.00          | 130.00 | 4.49                 | 48.70              | 40.80              | 1.14              | 2.65              |
| 106.74          | 136.74 | 4.62                 | 43.60              | 42.00              | 1.15              | 2.68              |
| 120.00          | 150.00 | 4.62                 | 40.20              | 40.00              | 1.12              | 2.80              |
| 133.40          | 163.40 | 4.54                 | 38.00              | 37.00              | 1.13              | 2.76              |
| 140.00          | 170.00 | 4.64                 | 37.00              | 35.70              | 1.15              | 2.80              |
| 150.00          | 180.00 | 4.68                 | 36.30              | 34.30              | 1.13              | 2.84              |
| 160.06          | 190.06 | 4.75                 | 53.20              | 32.70              | 1.07              | 2.68              |
| 170.00          | 200.00 | 4.81                 | 54.40              | 32.20              | 1.02              | 2.76              |
| 186.72          | 216.72 | 5.14                 | 54.50              | 31.20              | 1.16              | 2.92              |
| 200.00          | 230.00 | 5.19                 | 53.80              | 31.80              | 1.28              | 2.96              |
| 213.38          | 243.38 | 5.26                 | 61.60              | 31.60              | 1.41              | 2.92              |
| 240.04          | 270.04 | 5.44                 | 42.00              | 26.40              | 1.62              | 2.72              |
| 250.00          | 280.00 | 5.44                 | 39.40              | 24.50              | 1.69              | 2.65              |

### Electrical Schematic



**Mini-Circuits**  
ISO 9001 ISO 14001 AS 9100 CERTIFIED

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 The Design Engineers Search Engine Provides ACTUAL Data Instantly at [minicircuits.com](http://minicircuits.com)

IF/RF MICROWAVE COMPONENTS







Notes: 1. Performance and quality attributes and conditions not expressly stated in this specification sheet are intended to be excluded and do not form a part of this specification sheet. 2. Electrical specifications and performance data contained herein are based on Mini-Circuit's applicable established test performance criteria and measurement instructions. 3. The parts covered by this specification sheet are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp).

For detailed performance specs  
& shopping online see web site

REV. C  
M102713  
ADE-6  
ED-7383/2  
DJ/TD/CP/AM  
120627  
Page 1 of 2

# Performance Charts

**ADE-6+**  
**ADE-6**



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 The Design Engineers Search Engine  Provides ACTUAL Data Instantly at [minicircuits.com](http://minicircuits.com)

IF/RF MICROWAVE COMPONENTS

For detailed performance specs  
& shopping online see web site

**Notes:** 1. Performance and quality attributes and conditions not expressly stated in this specification sheet are intended to be excluded and do not form a part of this specification sheet. 2. Electrical specifications and performance data contained herein are based on Mini-Circuit's applicable established test performance criteria and measurement instructions. 3. The parts covered by this specification sheet are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp).

## Typical Performance Data

| RF<br>(IN)<br>(MHz) | LO<br>(MHz) | CONVERSION LOSS<br>IF FIXED<br>@IF(OUT)=30MHz<br>(dB) |       |       | RF<br>(IN)<br>(MHz) | LO<br>(MHz) | IP3 INPUT<br>(dBm) |       |       | RF<br>(IN)<br>(MHz) | LO<br>(MHz) | COMPRESSION<br>@RF IN=+1dBm<br>(dB) |      |      |
|---------------------|-------------|-------------------------------------------------------|-------|-------|---------------------|-------------|--------------------|-------|-------|---------------------|-------------|-------------------------------------|------|------|
|                     |             | @LO (dBm)                                             |       |       |                     |             | @LO (dBm)          |       |       |                     |             | @LO (dBm)                           |      |      |
|                     |             |                                                       |       |       |                     |             |                    |       |       |                     |             |                                     |      |      |
| +4                  | +7          | +10                                                   | +4    | +7    | +10                 | +4          | +7                 | +10   |       |                     |             |                                     |      |      |
| 10.1                | 40.1        | 4.67                                                  | 4.48  | 4.59  | 10.1                | 40.1        | 16.25              | 19.53 | 20.58 | 10.1                | 40.1        | 1.98                                | 1.49 | 1.09 |
| 20.1                | 50.1        | 4.89                                                  | 4.80  | 4.63  | 20.1                | 50.1        | 19.39              | 21.60 | 16.69 | 20.1                | 50.1        | 1.62                                | 1.37 | 1.13 |
| 30.1                | 60.1        | 5.06                                                  | 4.89  | 4.70  | 30.1                | 60.1        | 19.75              | 18.81 | 15.74 | 30.1                | 60.1        | 1.68                                | 1.39 | 1.14 |
| 40.1                | 70.1        | 5.08                                                  | 4.86  | 4.74  | 40.1                | 70.1        | 19.24              | 20.68 | 14.27 | 40.1                | 70.1        | 1.61                                | 1.27 | 1.13 |
| 50.1                | 80.1        | 5.11                                                  | 4.88  | 4.74  | 50.1                | 80.1        | 19.41              | 15.59 | 14.16 | 50.1                | 80.1        | 1.52                                | 1.30 | 1.09 |
| 60.1                | 90.1        | 5.09                                                  | 4.89  | 4.79  | 60.1                | 90.1        | 19.52              | 15.02 | 13.72 | 60.1                | 90.1        | 1.59                                | 1.29 | 1.10 |
| 70.1                | 100.1       | 4.96                                                  | 4.85  | 4.75  | 70.1                | 100.1       | 13.56              | 12.76 | 12.58 | 70.1                | 100.1       | 1.59                                | 1.38 | 1.06 |
| 80.1                | 110.1       | 4.94                                                  | 4.80  | 4.73  | 80.1                | 110.1       | 10.69              | 9.65  | 9.65  | 80.1                | 110.1       | 1.61                                | 1.34 | 1.13 |
| 90.1                | 120.1       | 5.07                                                  | 4.88  | 4.74  | 90.1                | 120.1       | 12.20              | 10.87 | 11.40 | 90.1                | 120.1       | 1.44                                | 1.22 | 1.03 |
| 100.1               | 130.1       | 5.29                                                  | 5.01  | 4.83  | 100.1               | 130.1       | 15.13              | 14.15 | 15.74 | 100.1               | 130.1       | 1.28                                | 1.08 | 0.86 |
| 110.1               | 140.1       | 5.41                                                  | 5.18  | 4.97  | 110.1               | 140.1       | 12.91              | 12.66 | 14.50 | 110.1               | 140.1       | 1.24                                | 1.02 | 0.86 |
| 120.1               | 150.1       | 5.40                                                  | 5.21  | 5.07  | 120.1               | 150.1       | 11.51              | 10.56 | 10.85 | 120.1               | 150.1       | 1.32                                | 1.10 | 0.92 |
| 130.1               | 160.1       | 5.42                                                  | 5.25  | 5.12  | 130.1               | 160.1       | 11.10              | 10.94 | 11.63 | 130.1               | 160.1       | 1.41                                | 1.15 | 0.97 |
| 140.1               | 170.1       | 5.38                                                  | 5.23  | 5.15  | 140.1               | 170.1       | 9.68               | 9.77  | 10.73 | 140.1               | 170.1       | 1.58                                | 1.29 | 1.06 |
| 150.1               | 180.1       | 5.46                                                  | 5.32  | 5.25  | 150.1               | 180.1       | 8.70               | 9.07  | 10.99 | 150.1               | 180.1       | 1.78                                | 1.39 | 1.13 |
| 160.1               | 190.1       | 5.49                                                  | 5.36  | 5.30  | 160.1               | 190.1       | 8.55               | 9.32  | 11.22 | 160.1               | 190.1       | 1.97                                | 1.48 | 1.23 |
| 170.1               | 200.1       | 5.59                                                  | 5.42  | 5.36  | 170.1               | 200.1       | 9.09               | 10.21 | 12.04 | 170.1               | 200.1       | 2.09                                | 1.57 | 1.29 |
| 180.1               | 210.1       | 5.81                                                  | 5.56  | 5.43  | 180.1               | 210.1       | 7.37               | 10.22 | 12.65 | 180.1               | 210.1       | 2.28                                | 1.77 | 1.42 |
| 190.1               | 220.1       | 6.03                                                  | 5.69  | 5.48  | 190.1               | 220.1       | 3.99               | 8.08  | 11.67 | 190.1               | 220.1       | 2.46                                | 2.01 | 1.62 |
| 200.1               | 230.1       | 6.22                                                  | 5.90  | 5.52  | 200.1               | 230.1       | 1.83               | 4.49  | 8.56  | 200.1               | 230.1       | 2.61                                | 2.23 | 1.91 |
| 210.1               | 240.1       | 6.39                                                  | 6.09  | 5.70  | 210.1               | 240.1       | 1.09               | 2.66  | 5.56  | 210.1               | 240.1       | 2.64                                | 2.29 | 2.07 |
| 220.1               | 250.1       | 6.50                                                  | 6.20  | 5.88  | 220.1               | 250.1       | 0.66               | 1.54  | 3.22  | 220.1               | 250.1       | 2.69                                | 2.40 | 2.17 |
| 230.1               | 260.1       | 6.61                                                  | 6.27  | 5.94  | 230.1               | 260.1       | 0.87               | 1.52  | 2.44  | 230.1               | 260.1       | 2.64                                | 2.37 | 2.15 |
| 240.1               | 270.1       | 6.57                                                  | 6.18  | 5.84  | 240.1               | 270.1       | 1.44               | 2.17  | 3.16  | 240.1               | 270.1       | 2.69                                | 2.45 | 2.19 |
| 250.1               | 280.1       | 6.76                                                  | 6.30  | 5.91  | 250.1               | 280.1       | 2.51               | 3.49  | 5.26  | 250.1               | 280.1       | 2.51                                | 2.28 | 2.05 |
| 260.1               | 290.1       | 6.81                                                  | 6.31  | 5.87  | 260.1               | 290.1       | 4.04               | 5.50  | 8.10  | 260.1               | 290.1       | 2.44                                | 2.21 | 1.99 |
| 270.1               | 300.1       | 7.15                                                  | 6.58  | 6.15  | 270.1               | 300.1       | 5.74               | 7.53  | 10.07 | 270.1               | 300.1       | 2.18                                | 1.98 | 1.79 |
| 280.1               | 310.1       | 7.06                                                  | 6.58  | 6.25  | 280.1               | 310.1       | 7.55               | 9.08  | 11.11 | 280.1               | 310.1       | 2.15                                | 1.86 | 1.68 |
| 290.1               | 320.1       | 7.26                                                  | 6.79  | 6.48  | 290.1               | 320.1       | 8.60               | 10.12 | 11.75 | 290.1               | 320.1       | 2.11                                | 1.86 | 1.62 |
| 300.1               | 330.1       | 7.39                                                  | 7.05  | 6.85  | 300.1               | 330.1       | 9.20               | 10.44 | 11.52 | 300.1               | 330.1       | 1.95                                | 1.65 | 1.40 |
| 310.1               | 340.1       | 7.50                                                  | 7.19  | 6.98  | 310.1               | 340.1       | 9.41               | 10.42 | 11.61 | 310.1               | 340.1       | 2.03                                | 1.74 | 1.50 |
| 320.1               | 350.1       | 7.78                                                  | 7.69  | 7.35  | 320.1               | 350.1       | 9.33               | 10.26 | 11.67 | 320.1               | 350.1       | 1.90                                | 1.56 | 1.29 |
| 330.1               | 360.1       | 7.88                                                  | 7.65  | 7.54  | 330.1               | 360.1       | 8.64               | 9.28  | 10.35 | 330.1               | 360.1       | 2.01                                | 1.68 | 1.39 |
| 340.1               | 370.1       | 8.55                                                  | 8.36  | 8.31  | 340.1               | 370.1       | 8.26               | 8.96  | 10.10 | 340.1               | 370.1       | 1.73                                | 1.41 | 1.13 |
| 350.1               | 380.1       | 8.70                                                  | 8.39  | 8.41  | 350.1               | 380.1       | 7.80               | 8.44  | 9.47  | 350.1               | 380.1       | 1.80                                | 1.56 | 1.30 |
| 360.1               | 390.1       | 9.40                                                  | 9.17  | 9.09  | 360.1               | 390.1       | 7.48               | 8.23  | 9.09  | 360.1               | 390.1       | 1.45                                | 1.23 | 1.05 |
| 370.1               | 400.1       | 9.50                                                  | 9.27  | 9.20  | 370.1               | 400.1       | 7.27               | 8.20  | 9.29  | 370.1               | 400.1       | 1.45                                | 1.25 | 1.06 |
| 380.1               | 410.1       | 10.20                                                 | 9.98  | 9.70  | 380.1               | 410.1       | 7.46               | 8.50  | 9.87  | 380.1               | 410.1       | 1.29                                | 1.29 | 1.26 |
| 390.1               | 420.1       | 10.67                                                 | 10.40 | 10.27 | 390.1               | 420.1       | 8.13               | 9.43  | 11.58 | 390.1               | 420.1       | 1.18                                | 1.02 | 0.91 |
| 400.1               | 430.1       | 11.39                                                 | 11.07 | 10.89 | 400.1               | 430.1       | 8.72               | 10.77 | 13.51 | 400.1               | 430.1       | 1.09                                | 0.97 | 0.91 |

## Typical Performance Data

| IF<br>(OUT)<br>(MHz) | LO<br>(MHz) | CONVERSION LOSS<br>VS. IF FREQUENCY<br>@RF(IN)=125.1MHz<br>(dB) |
|----------------------|-------------|-----------------------------------------------------------------|
|                      |             | @LO (dBm)<br><br>+7                                             |
| 115.1                | 10.0        | 5.28                                                            |
| 112.6                | 12.5        | 5.24                                                            |
| 110.1                | 15.0        | 5.18                                                            |
| 107.6                | 17.5        | 5.14                                                            |
| 105.1                | 20.0        | 5.09                                                            |
| 102.6                | 22.5        | 5.11                                                            |
| 100.1                | 25.0        | 5.09                                                            |
| 97.6                 | 27.5        | 5.08                                                            |
| 95.1                 | 30.0        | 5.05                                                            |
| 92.6                 | 32.5        | 5.03                                                            |
| 90.1                 | 35.0        | 5.01                                                            |
| 87.6                 | 37.5        | 4.97                                                            |
| 85.1                 | 40.0        | 4.95                                                            |
| 82.6                 | 42.5        | 4.98                                                            |
| 80.1                 | 45.0        | 5.03                                                            |
| 77.6                 | 47.5        | 5.07                                                            |
| 75.1                 | 50.0        | 5.08                                                            |
| 72.6                 | 52.5        | 5.03                                                            |
| 70.1                 | 55.0        | 5.06                                                            |
| 67.6                 | 57.5        | 5.02                                                            |
| 65.1                 | 60.0        | 5.01                                                            |
| 62.6                 | 62.5        | 5.10                                                            |
| 60.1                 | 65.0        | 5.03                                                            |
| 57.6                 | 67.5        | 5.06                                                            |
| 55.1                 | 70.0        | 5.07                                                            |
| 52.6                 | 72.5        | 5.08                                                            |
| 50.1                 | 75.0        | 5.06                                                            |
| 47.6                 | 77.5        | 5.04                                                            |
| 45.1                 | 80.0        | 5.01                                                            |
| 42.6                 | 82.5        | 4.99                                                            |
| 40.1                 | 85.0        | 4.94                                                            |
| 37.6                 | 87.5        | 4.99                                                            |
| 35.1                 | 90.0        | 5.00                                                            |
| 32.6                 | 92.5        | 5.03                                                            |
| 27.6                 | 97.5        | 5.01                                                            |
| 25.1                 | 100.0       | 5.05                                                            |
| 20.1                 | 105.0       | 5.07                                                            |
| 17.6                 | 107.5       | 5.06                                                            |
| 12.6                 | 112.5       | 5.22                                                            |
| 10.1                 | 115.0       | 5.33                                                            |

| IF<br>(OUT)<br>(MHz) | LO<br>(MHz) | CONVERSION LOSS<br>VS. IF FREQUENCY<br>@RF(IN)=10MHz<br>(dB) |
|----------------------|-------------|--------------------------------------------------------------|
|                      |             | @LO (dBm)<br><br>+7                                          |
| 10.1                 | 20.1        | 4.75                                                         |
| 20.1                 | 30.1        | 4.38                                                         |
| 30.1                 | 40.1        | 4.39                                                         |
| 40.1                 | 50.1        | 4.30                                                         |
| 50.1                 | 60.1        | 4.69                                                         |
| 60.1                 | 70.1        | 4.34                                                         |
| 70.1                 | 80.1        | 4.41                                                         |
| 80.1                 | 90.1        | 4.54                                                         |
| 90.1                 | 100.1       | 4.64                                                         |
| 100.1                | 110.1       | 4.70                                                         |
| 110.1                | 120.1       | 4.67                                                         |
| 120.1                | 130.1       | 4.82                                                         |
| 130.1                | 140.1       | 4.93                                                         |
| 140.1                | 150.1       | 5.12                                                         |
| 150.1                | 160.1       | 4.90                                                         |
| 160.1                | 170.1       | 5.01                                                         |
| 170.1                | 180.1       | 5.12                                                         |
| 180.1                | 190.1       | 4.54                                                         |
| 190.1                | 200.1       | 4.70                                                         |
| 200.1                | 210.1       | 4.75                                                         |
| 210.1                | 220.1       | 4.88                                                         |
| 225.1                | 235.1       | 4.84                                                         |
| 235.1                | 245.1       | 4.87                                                         |
| 250.1                | 260.1       | 5.04                                                         |
| 260.1                | 270.1       | 4.81                                                         |
| 275.1                | 285.1       | 5.10                                                         |
| 285.1                | 295.1       | 5.06                                                         |
| 300.1                | 310.1       | 5.46                                                         |
| 310.1                | 320.1       | 5.49                                                         |
| 325.1                | 335.1       | 5.97                                                         |
| 335.1                | 345.1       | 5.70                                                         |
| 350.1                | 360.1       | 6.19                                                         |
| 360.1                | 370.1       | 6.35                                                         |
| 375.1                | 385.1       | 6.70                                                         |
| 385.1                | 395.1       | 6.97                                                         |
| 400.1                | 410.1       | 8.12                                                         |
| 410.1                | 420.1       | 8.74                                                         |
| 425.1                | 435.1       | 9.42                                                         |
| 435.1                | 445.1       | 10.01                                                        |
| 450.1                | 460.1       | 11.63                                                        |

| IF<br>(OUT)<br>(MHz) | LO<br>(MHz) | CONVERSION LOSS<br>VS. IF FREQUENCY<br>@RF(IN)=250.1MHz<br>(dB) |
|----------------------|-------------|-----------------------------------------------------------------|
|                      |             | @LO (dBm)<br><br>+7                                             |
| 240.1                | 10.0        | 7.38                                                            |
| 235.1                | 15.0        | 7.29                                                            |
| 230.1                | 20.0        | 7.28                                                            |
| 225.1                | 25.0        | 7.27                                                            |
| 220.1                | 30.0        | 7.20                                                            |
| 215.1                | 35.0        | 7.14                                                            |
| 210.1                | 40.0        | 7.12                                                            |
| 205.1                | 45.0        | 7.10                                                            |
| 200.1                | 50.0        | 7.00                                                            |
| 195.1                | 55.0        | 6.92                                                            |
| 190.1                | 60.0        | 6.91                                                            |
| 185.1                | 65.0        | 6.96                                                            |
| 180.1                | 70.0        | 6.99                                                            |
| 175.1                | 75.0        | 6.97                                                            |
| 170.1                | 80.0        | 6.96                                                            |
| 165.1                | 85.0        | 6.97                                                            |
| 160.1                | 90.0        | 7.01                                                            |
| 155.1                | 95.0        | 6.91                                                            |
| 150.1                | 100.0       | 6.81                                                            |
| 145.1                | 105.0       | 6.80                                                            |
| 140.1                | 110.0       | 6.83                                                            |
| 135.1                | 115.0       | 6.77                                                            |
| 130.1                | 120.0       | 6.70                                                            |
| 125.1                | 125.0       | 6.80                                                            |
| 120.1                | 130.0       | 6.63                                                            |
| 115.1                | 135.0       | 6.62                                                            |
| 105.1                | 145.0       | 6.38                                                            |
| 100.1                | 150.0       | 6.41                                                            |
| 90.1                 | 160.0       | 6.31                                                            |
| 85.1                 | 165.0       | 6.20                                                            |
| 75.1                 | 175.0       | 6.08                                                            |
| 70.1                 | 180.0       | 6.07                                                            |
| 60.1                 | 190.0       | 5.90                                                            |
| 55.1                 | 195.0       | 5.87                                                            |
| 45.1                 | 205.0       | 5.86                                                            |
| 40.1                 | 210.0       | 5.82                                                            |
| 30.1                 | 220.0       | 6.00                                                            |
| 25.1                 | 225.0       | 6.17                                                            |
| 15.1                 | 235.0       | 6.52                                                            |
| 10.1                 | 240.0       | 6.77                                                            |

## Typical Performance Data

| LO<br>(MHz) | LO-RF ISOLATION<br>(dB) |       |       | LO-IF ISOLATION<br>(dB) |       |       |
|-------------|-------------------------|-------|-------|-------------------------|-------|-------|
|             | @LO (dBm)               |       |       | @LO (dBm)               |       |       |
|             | +4                      | +7    | +10   | +4                      | +7    | +10   |
| 40.1        | 57.74                   | 57.75 | 57.94 | 57.96                   | 56.47 | 54.26 |
| 50.4        | 56.55                   | 56.00 | 55.97 | 54.19                   | 54.56 | 53.67 |
| 60.6        | 54.25                   | 54.28 | 54.59 | 50.41                   | 51.33 | 51.91 |
| 70.9        | 54.34                   | 54.43 | 54.73 | 47.30                   | 48.94 | 50.47 |
| 81.1        | 52.21                   | 52.93 | 53.29 | 45.88                   | 47.90 | 49.41 |
| 91.4        | 49.83                   | 49.76 | 50.03 | 43.82                   | 46.55 | 49.38 |
| 101.6       | 50.33                   | 50.18 | 50.20 | 40.93                   | 42.72 | 44.96 |
| 111.9       | 52.14                   | 51.94 | 51.87 | 40.03                   | 41.81 | 43.49 |
| 122.2       | 51.93                   | 52.17 | 51.92 | 39.35                   | 41.39 | 43.52 |
| 132.4       | 49.78                   | 50.81 | 50.93 | 38.78                   | 40.89 | 43.41 |
| 142.7       | 45.28                   | 46.14 | 46.78 | 39.92                   | 42.30 | 44.76 |
| 152.9       | 42.89                   | 43.81 | 44.55 | 38.82                   | 41.77 | 44.44 |
| 163.2       | 41.40                   | 42.38 | 43.11 | 36.11                   | 38.59 | 41.03 |
| 173.4       | 40.66                   | 41.63 | 42.54 | 34.69                   | 36.21 | 37.53 |
| 183.7       | 40.18                   | 41.42 | 42.56 | 33.28                   | 34.11 | 34.96 |
| 193.9       | 40.03                   | 41.30 | 42.27 | 31.85                   | 32.20 | 32.76 |
| 204.2       | 39.88                   | 40.41 | 40.48 | 31.75                   | 32.25 | 32.54 |
| 214.5       | 39.42                   | 39.89 | 39.81 | 31.30                   | 32.18 | 31.85 |
| 224.7       | 39.24                   | 39.91 | 40.16 | 30.47                   | 32.01 | 31.40 |
| 235.0       | 39.14                   | 39.84 | 40.21 | 30.54                   | 31.88 | 32.09 |
| 245.2       | 38.39                   | 38.72 | 38.77 | 30.82                   | 31.80 | 32.38 |
| 255.5       | 37.49                   | 37.51 | 37.24 | 30.88                   | 31.54 | 31.49 |
| 265.7       | 37.21                   | 37.17 | 36.94 | 30.32                   | 30.21 | 29.14 |
| 276.0       | 36.33                   | 35.92 | 35.19 | 29.54                   | 28.42 | 26.56 |
| 286.3       | 35.12                   | 34.06 | 32.89 | 28.63                   | 26.42 | 24.17 |
| 296.5       | 34.17                   | 32.72 | 31.67 | 27.40                   | 24.58 | 22.67 |
| 306.8       | 33.18                   | 31.33 | 30.39 | 25.78                   | 22.97 | 21.53 |
| 317.0       | 31.76                   | 29.68 | 28.69 | 24.33                   | 21.83 | 20.66 |
| 327.3       | 30.38                   | 28.43 | 27.45 | 23.44                   | 21.27 | 20.14 |
| 337.5       | 29.15                   | 27.31 | 26.26 | 22.66                   | 20.66 | 19.48 |
| 347.8       | 28.14                   | 26.12 | 25.01 | 21.98                   | 19.93 | 18.75 |
| 358.0       | 27.11                   | 24.93 | 23.70 | 21.57                   | 19.41 | 18.13 |
| 368.3       | 26.12                   | 23.84 | 22.46 | 20.98                   | 18.82 | 17.44 |
| 378.6       | 25.11                   | 22.74 | 21.37 | 20.37                   | 18.16 | 16.78 |
| 388.8       | 24.38                   | 21.94 | 20.56 | 19.95                   | 17.77 | 16.36 |
| 399.1       | 23.51                   | 21.07 | 19.66 | 19.68                   | 17.58 | 16.19 |
| 409.3       | 22.65                   | 20.32 | 18.84 | 19.44                   | 17.47 | 16.04 |
| 419.6       | 21.81                   | 19.61 | 18.12 | 18.91                   | 17.12 | 15.75 |
| 429.8       | 21.02                   | 18.97 | 17.55 | 18.23                   | 16.62 | 15.32 |
| 440.1       | 20.15                   | 18.24 | 16.85 | 17.71                   | 16.26 | 15.02 |

| RF<br>(IN)<br>(MHz) | LO<br>(MHz) | RF-IF ISOLATION<br>(dB) |       |       |
|---------------------|-------------|-------------------------|-------|-------|
|                     |             | @LO (dBm)               |       |       |
|                     |             | +4                      | +7    | +10   |
| 10.1                | 40.1        | 32.97                   | 31.93 | 31.35 |
| 20.1                | 50.1        | 28.35                   | 28.28 | 28.12 |
| 30.1                | 60.1        | 25.79                   | 25.95 | 26.00 |
| 40.1                | 70.1        | 23.65                   | 23.51 | 23.89 |
| 50.1                | 80.1        | 22.80                   | 22.95 | 22.97 |
| 60.1                | 90.1        | 22.23                   | 22.59 | 22.76 |
| 70.1                | 100.1       | 21.32                   | 21.95 | 22.33 |
| 80.1                | 110.1       | 20.99                   | 21.51 | 21.93 |
| 90.1                | 120.1       | 20.46                   | 20.90 | 21.30 |
| 100.1               | 130.1       | 21.36                   | 21.75 | 22.09 |
| 110.1               | 140.1       | 21.62                   | 21.89 | 22.19 |
| 120.1               | 150.1       | 23.49                   | 24.04 | 24.52 |
| 130.1               | 160.1       | 23.71                   | 24.62 | 25.42 |
| 140.1               | 170.1       | 23.11                   | 24.32 | 25.36 |
| 150.1               | 180.1       | 20.34                   | 20.99 | 21.50 |
| 160.1               | 190.1       | 18.59                   | 19.04 | 19.27 |
| 170.1               | 200.1       | 16.74                   | 17.02 | 17.18 |
| 180.1               | 210.1       | 15.85                   | 16.11 | 16.39 |
| 190.1               | 220.1       | 15.10                   | 15.36 | 15.66 |
| 200.1               | 230.1       | 14.38                   | 14.59 | 15.00 |
| 210.1               | 240.1       | 14.17                   | 14.37 | 14.81 |
| 220.1               | 250.1       | 14.18                   | 14.41 | 14.89 |
| 230.1               | 260.1       | 14.57                   | 14.73 | 15.13 |
| 240.1               | 270.1       | 14.64                   | 14.77 | 15.11 |
| 250.1               | 280.1       | 15.11                   | 15.26 | 15.41 |
| 260.1               | 290.1       | 14.95                   | 14.92 | 14.95 |
| 270.1               | 300.1       | 14.51                   | 14.35 | 14.23 |
| 280.1               | 310.1       | 13.55                   | 13.33 | 13.13 |
| 290.1               | 320.1       | 12.70                   | 12.42 | 12.12 |
| 300.1               | 330.1       | 11.71                   | 11.49 | 11.25 |
| 310.1               | 340.1       | 11.11                   | 10.84 | 10.60 |
| 320.1               | 350.1       | 10.44                   | 10.16 | 9.92  |
| 330.1               | 360.1       | 9.72                    | 9.50  | 9.22  |
| 340.1               | 370.1       | 9.02                    | 8.75  | 8.49  |
| 350.1               | 380.1       | 8.40                    | 8.17  | 7.86  |
| 360.1               | 390.1       | 7.72                    | 7.45  | 7.20  |
| 370.1               | 400.1       | 7.16                    | 6.90  | 6.66  |
| 380.1               | 410.1       | 6.66                    | 6.38  | 6.14  |
| 390.1               | 420.1       | 6.20                    | 5.91  | 5.66  |
| 400.1               | 430.1       | 5.84                    | 5.53  | 5.27  |

## Typical Performance Data

| RF<br>(IN)<br>(MHz) | LO<br>(MHz) | RF VSWR<br>(:1) |      |      | LO<br>(MHz) | LO VSWR<br>(:1) |      |      |       | IF<br>(OUT)<br>(MHz) | IF VSWR<br>@LO=250.1MHz<br>(:1) |      |  |  |
|---------------------|-------------|-----------------|------|------|-------------|-----------------|------|------|-------|----------------------|---------------------------------|------|--|--|
|                     |             | @LO (dBm)       |      |      |             | @LO (dBm)       |      |      |       |                      | @LO (dBm)                       |      |  |  |
|                     |             | +4              | +7   | +10  |             | +4              | +7   | +10  | +4    |                      | +7                              | +10  |  |  |
| 10.1                | 40.1        | 1.54            | 1.32 | 1.36 | 40.1        | 1.75            | 2.52 | 3.52 | 10.0  | 2.18                 | 1.97                            | 1.74 |  |  |
| 20.1                | 50.1        | 1.35            | 1.26 | 1.21 | 50.4        | 1.75            | 2.52 | 3.51 | 15.0  | 2.17                 | 1.96                            | 1.73 |  |  |
| 30.1                | 60.1        | 1.33            | 1.24 | 1.15 | 60.6        | 1.75            | 2.51 | 3.50 | 20.0  | 2.15                 | 1.93                            | 1.70 |  |  |
| 40.1                | 70.1        | 1.32            | 1.21 | 1.14 | 70.9        | 1.76            | 2.49 | 3.47 | 25.0  | 2.14                 | 1.93                            | 1.71 |  |  |
| 50.1                | 80.1        | 1.26            | 1.16 | 1.12 | 81.1        | 1.77            | 2.52 | 3.48 | 30.0  | 2.15                 | 1.95                            | 1.72 |  |  |
| 60.1                | 90.1        | 1.24            | 1.14 | 1.07 | 91.4        | 1.78            | 2.53 | 3.48 | 35.0  | 2.18                 | 1.97                            | 1.75 |  |  |
| 70.1                | 100.1       | 1.21            | 1.11 | 1.05 | 101.6       | 1.81            | 2.56 | 3.50 | 40.0  | 2.19                 | 1.99                            | 1.78 |  |  |
| 80.1                | 110.1       | 1.19            | 1.12 | 1.06 | 111.9       | 1.83            | 2.60 | 3.58 | 45.0  | 2.21                 | 2.02                            | 1.80 |  |  |
| 90.1                | 120.1       | 1.17            | 1.09 | 1.03 | 122.2       | 1.86            | 2.62 | 3.59 | 50.0  | 2.21                 | 2.02                            | 1.81 |  |  |
| 100.1               | 130.1       | 1.15            | 1.06 | 1.03 | 132.4       | 1.86            | 2.60 | 3.50 | 55.0  | 2.21                 | 2.01                            | 1.81 |  |  |
| 110.1               | 140.1       | 1.10            | 1.03 | 1.04 | 142.7       | 1.88            | 2.64 | 3.59 | 60.0  | 2.20                 | 2.00                            | 1.80 |  |  |
| 120.1               | 150.1       | 1.06            | 1.01 | 1.06 | 152.9       | 1.92            | 2.71 | 3.72 | 65.0  | 2.20                 | 2.00                            | 1.79 |  |  |
| 130.1               | 160.1       | 1.03            | 1.06 | 1.11 | 163.2       | 1.95            | 2.72 | 3.73 | 70.0  | 2.18                 | 1.99                            | 1.79 |  |  |
| 140.1               | 170.1       | 1.03            | 1.11 | 1.18 | 173.4       | 1.95            | 2.71 | 3.65 | 75.0  | 2.20                 | 2.01                            | 1.81 |  |  |
| 150.1               | 180.1       | 1.06            | 1.14 | 1.19 | 183.7       | 1.99            | 2.73 | 3.66 | 80.0  | 2.22                 | 2.04                            | 1.84 |  |  |
| 160.1               | 190.1       | 1.09            | 1.15 | 1.20 | 193.9       | 2.06            | 2.81 | 3.79 | 85.0  | 2.22                 | 2.04                            | 1.86 |  |  |
| 170.1               | 200.1       | 1.10            | 1.16 | 1.19 | 204.2       | 2.13            | 2.87 | 3.85 | 90.0  | 2.24                 | 2.06                            | 1.89 |  |  |
| 180.1               | 210.1       | 1.13            | 1.16 | 1.18 | 214.5       | 2.22            | 2.95 | 3.85 | 95.0  | 2.25                 | 2.08                            | 1.91 |  |  |
| 190.1               | 220.1       | 1.17            | 1.14 | 1.14 | 224.7       | 2.28            | 3.07 | 4.02 | 100.0 | 2.23                 | 2.06                            | 1.90 |  |  |
| 200.1               | 230.1       | 1.21            | 1.16 | 1.12 | 235.0       | 2.30            | 3.13 | 4.14 | 105.0 | 2.21                 | 2.04                            | 1.88 |  |  |
| 210.1               | 240.1       | 1.26            | 1.20 | 1.13 | 245.2       | 2.29            | 3.10 | 4.06 | 110.0 | 2.19                 | 2.03                            | 1.87 |  |  |
| 220.1               | 250.1       | 1.34            | 1.27 | 1.20 | 255.5       | 2.28            | 3.10 | 4.06 | 115.0 | 2.15                 | 2.00                            | 1.84 |  |  |
| 230.1               | 260.1       | 1.44            | 1.36 | 1.28 | 265.7       | 2.29            | 3.12 | 4.12 | 120.0 | 2.13                 | 1.98                            | 1.83 |  |  |
| 240.1               | 270.1       | 1.51            | 1.41 | 1.33 | 276.0       | 2.33            | 3.15 | 4.19 | 125.0 | 2.12                 | 1.97                            | 1.82 |  |  |
| 250.1               | 280.1       | 1.64            | 1.54 | 1.46 | 286.3       | 2.30            | 3.08 | 4.07 | 130.0 | 2.13                 | 1.98                            | 1.84 |  |  |
| 260.1               | 290.1       | 1.67            | 1.57 | 1.50 | 296.5       | 2.25            | 2.96 | 3.84 | 135.0 | 2.15                 | 2.00                            | 1.86 |  |  |
| 270.1               | 300.1       | 1.82            | 1.72 | 1.66 | 306.8       | 2.26            | 2.99 | 3.90 | 145.0 | 2.17                 | 2.02                            | 1.88 |  |  |
| 280.1               | 310.1       | 1.79            | 1.71 | 1.67 | 317.0       | 2.30            | 3.06 | 4.05 | 150.0 | 2.16                 | 2.02                            | 1.88 |  |  |
| 290.1               | 320.1       | 1.98            | 1.90 | 1.86 | 327.3       | 2.27            | 2.99 | 3.88 | 160.0 | 2.11                 | 1.97                            | 1.84 |  |  |
| 300.1               | 330.1       | 2.06            | 1.99 | 1.95 | 337.5       | 2.27            | 2.95 | 3.81 | 165.0 | 2.09                 | 1.95                            | 1.82 |  |  |
| 310.1               | 340.1       | 2.17            | 2.10 | 2.05 | 347.8       | 2.32            | 3.00 | 3.88 | 175.0 | 2.08                 | 1.95                            | 1.83 |  |  |
| 320.1               | 350.1       | 2.22            | 2.17 | 2.13 | 358.0       | 2.35            | 2.98 | 3.77 | 180.0 | 2.08                 | 1.95                            | 1.83 |  |  |
| 330.1               | 360.1       | 2.25            | 2.18 | 2.12 | 368.3       | 2.39            | 2.99 | 3.78 | 190.0 | 2.10                 | 1.97                            | 1.84 |  |  |
| 340.1               | 370.1       | 2.32            | 2.24 | 2.18 | 378.6       | 2.51            | 3.12 | 3.92 | 195.0 | 2.09                 | 1.96                            | 1.83 |  |  |
| 350.1               | 380.1       | 2.27            | 2.18 | 2.12 | 388.8       | 2.58            | 3.11 | 3.82 | 205.0 | 2.02                 | 1.88                            | 1.75 |  |  |
| 360.1               | 390.1       | 2.33            | 2.24 | 2.17 | 399.1       | 2.57            | 3.01 | 3.66 | 210.0 | 1.98                 | 1.84                            | 1.71 |  |  |
| 370.1               | 400.1       | 2.29            | 2.20 | 2.13 | 409.3       | 2.68            | 3.08 | 3.70 | 220.0 | 1.98                 | 1.84                            | 1.69 |  |  |
| 380.1               | 410.1       | 2.38            | 2.27 | 2.20 | 419.6       | 2.87            | 3.26 | 3.90 | 225.0 | 2.01                 | 1.86                            | 1.70 |  |  |
| 390.1               | 420.1       | 2.38            | 2.28 | 2.20 | 429.8       | 2.94            | 3.26 | 3.83 | 235.0 | 2.08                 | 1.91                            | 1.73 |  |  |
| 400.1               | 430.1       | 2.42            | 2.30 | 2.22 | 440.1       | 2.92            | 3.16 | 3.59 | 240.0 | 2.09                 | 1.91                            | 1.72 |  |  |

## Harmonics Tables

RF HARMONICS ORDER

|    | (-dBm) | (-dBc) |     |     |     |     |     |     |     |     |     |     |
|----|--------|--------|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|
| 0  | -      | -      | 15  | 19  | 11  | 37  | 17  | 36  | 28  | 51  | 36  | 44  |
| 1  | -      | 20     | +0  | 33  | 12  | 36  | 36  | 60  | 37  | 49  | 31  | 44  |
| 2  | >90    | 52     | 51  | 52  | 54  | 51  | 53  | 62  | 54  | 69  | 67  | >71 |
| 3  | >90    | 65     | 59  | 58  | 61  | 61  | 65  | 70  | 66  | >71 | 60  | >71 |
| 4  | >90    | >71    | >71 | >71 | 66  | >71 | >71 | >71 | >71 | >71 | >71 | >71 |
| 5  | >90    | >71    | >71 | >71 | >71 | >71 | 69  | >71 | >71 | >71 | >71 | >71 |
| 6  | >90    | >71    | >71 | >71 | >71 | >71 | >71 | >71 | >71 | >71 | >71 | >71 |
| 7  | >90    | >71    | >71 | >71 | >71 | >71 | >71 | >71 | >71 | >71 | >71 | >71 |
| 8  | >90    | >71    | >71 | >71 | >71 | >71 | >71 | >71 | >71 | >71 | >71 | >71 |
| 9  | >90    | >71    | >71 | >71 | >71 | >71 | >71 | >71 | 70  | >71 | >71 | >71 |
| 10 | >90    | >71    | >71 | >71 | >71 | >71 | >71 | >71 | >71 | >71 | >71 | >71 |
|    | RF CAL | 0      | 1   | 2   | 3   | 4   | 5   | 6   | 7   | 8   | 9   | 10  |

## LO HARMONICS ORDER

Test conditions:

RF IN: 125.1 MHz; -14.00 dBm.

LO IN: 155.1 MHz; +7.00 dBm

IF OUT: 30 MHz; -19.09 dBm

RF HARMONICS ORDER

|    | (-dBm) | (-dBc) |     |     |     |     |     |     |     |     |     |     |
|----|--------|--------|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|
| 0  | -      | -      | 24  | 31  | 22  | 52  | 28  | 48  | 42  | 67  | 53  | 63  |
| 1  | -      | 20     | +0  | 30  | 12  | 35  | 36  | 51  | 45  | 54  | 39  | 57  |
| 2  | 74     | 48     | 42  | 47  | 42  | 44  | 50  | 54  | 48  | 57  | 69  | 61  |
| 3  | >90    | 50     | 36  | 51  | 40  | 51  | 41  | 53  | 59  | 64  | 49  | 71  |
| 4  | >90    | 68     | 54  | 69  | 60  | 66  | 69  | 60  | 61  | 68  | 70  | 71  |
| 5  | >90    | 71     | 71  | 63  | 53  | 60  | 52  | 55  | 61  | 66  | 68  | 64  |
| 6  | >90    | >81    | >81 | 74  | 68  | 80  | 73  | 70  | 71  | 75  | 76  | 78  |
| 7  | >90    | >81    | >81 | >81 | 72  | 70  | 64  | 67  | 64  | 65  | 75  | 77  |
| 8  | >90    | >81    | >81 | >81 | >81 | >81 | >81 | >81 | 78  | >81 | >81 | >81 |
| 9  | >90    | 79     | >81 | >81 | >81 | >81 | >81 | >81 | >81 | >81 | 76  | >81 |
| 10 | >90    | >81    | >81 | >81 | >81 | >81 | >81 | >81 | >81 | >81 | >81 | >81 |
|    | RF CAL | 0      | 1   | 2   | 3   | 4   | 5   | 6   | 7   | 8   | 9   | 10  |

## LO HARMONICS ORDER

Test conditions:

RF IN: 125.1 MHz; -4.00 dBm.

LO IN: 155.1 MHz; +7.00 dBm

IF OUT: 30 MHz; -9.21 dBm

Notes: 1. All Harmonics are in (dBc) relative to IF OUTPUT.

2. + entry denotes harmonics are in (dBc) above IF OUTPUT.

3. RF Cal represent the Harmonics level of the RF input signal to the mixer.

REV. X2

ADE-6

101013

Page 5 of 5



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS9100 CERTIFIED • RoHS compliant  
P.O. Box 350186, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, instantly • For detailed performance specs & shopping online see






# Frequency Mixer


## Typical Performance Curves

ADE-6


Conversion Loss @ IF=30MHz




Conversion Loss vs. IF @ RF=125.1MHz




Conversion Loss vs. IF @ RF=10MHz




Conversion Loss vs. IF @ RF=250.1MHz



IP3 Input



Compression @ RF IN=+1dBm



REV. X2

ADE-6

101013

Page 1 of 3



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS9100 CERTIFIED • RoHS compliant  
P.O. Box 350186, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661




The Design Engineers Search Engine finds the model you need, instantly • For detailed performance specs & shopping online see






## Typical Performance Curves


LO-RF Isolation




LO-IF Isolation




RF-IF Isolation




RF VSWR



LO VSWR



IF VSWR



REV. X2

ADE-6

101013

Page 2 of 3



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS9100 CERTIFIED • RoHS compliant  
P.O. Box 350186, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4861



The Design Engineers Search Engine finds the model you need, instantly • For detailed performance specs & shopping online see



## Harmonics Tables

RF HARMONICS ORDER

|    | (-dBm) | (-dBc) |     |     |     |     |     |     |     |     |     |     |
|----|--------|--------|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|
| 0  | -      | -      | 15  | 19  | 11  | 37  | 17  | 36  | 28  | 51  | 36  | 44  |
| 1  | -      | 20     | +0  | 33  | 12  | 36  | 36  | 60  | 37  | 49  | 31  | 44  |
| 2  | >90    | 52     | 51  | 52  | 54  | 51  | 53  | 62  | 54  | 69  | 67  | >71 |
| 3  | >90    | 65     | 59  | 58  | 61  | 61  | 65  | 70  | 66  | >71 | 60  | >71 |
| 4  | >90    | >71    | >71 | >71 | 66  | >71 | >71 | >71 | >71 | >71 | >71 | >71 |
| 5  | >90    | >71    | >71 | >71 | >71 | >71 | 69  | >71 | >71 | >71 | >71 | >71 |
| 6  | >90    | >71    | >71 | >71 | >71 | >71 | >71 | >71 | >71 | >71 | >71 | >71 |
| 7  | >90    | >71    | >71 | >71 | >71 | >71 | >71 | >71 | >71 | >71 | >71 | >71 |
| 8  | >90    | >71    | >71 | >71 | >71 | >71 | >71 | >71 | >71 | >71 | >71 | >71 |
| 9  | >90    | >71    | >71 | >71 | >71 | >71 | >71 | >71 | 70  | >71 | >71 | >71 |
| 10 | >90    | >71    | >71 | >71 | >71 | >71 | >71 | >71 | >71 | >71 | >71 | >71 |
|    | RF CAL | 0      | 1   | 2   | 3   | 4   | 5   | 6   | 7   | 8   | 9   | 10  |

### LO HARMONICS ORDER

Test conditions: RF IN: 125.1 MHz; -14.00 dBm.  
LO IN: 155.1 MHz; +7.00 dBm  
IF OUT: 30 MHz; -19.09 dBm

RF HARMONICS ORDER

|    | (-dBm) | (-dBc) |     |     |     |     |     |     |     |     |     |     |
|----|--------|--------|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|
| 0  | -      | -      | 24  | 31  | 22  | 52  | 28  | 48  | 42  | 67  | 53  | 63  |
| 1  | -      | 20     | +0  | 30  | 12  | 35  | 36  | 51  | 45  | 54  | 39  | 57  |
| 2  | 74     | 48     | 42  | 47  | 42  | 44  | 50  | 54  | 48  | 57  | 69  | 61  |
| 3  | >90    | 50     | 36  | 51  | 40  | 51  | 41  | 53  | 59  | 64  | 49  | 71  |
| 4  | >90    | 68     | 54  | 69  | 60  | 66  | 69  | 60  | 61  | 68  | 70  | 71  |
| 5  | >90    | 71     | 71  | 63  | 53  | 60  | 52  | 55  | 61  | 66  | 68  | 64  |
| 6  | >90    | >81    | >81 | 74  | 68  | 80  | 73  | 70  | 71  | 75  | 76  | 78  |
| 7  | >90    | >81    | >81 | >81 | 72  | 70  | 64  | 67  | 64  | 65  | 75  | 77  |
| 8  | >90    | >81    | >81 | >81 | >81 | >81 | >81 | >81 | 78  | >81 | >81 | >81 |
| 9  | >90    | 79     | >81 | >81 | >81 | >81 | >81 | >81 | >81 | >81 | 76  | >81 |
| 10 | >90    | >81    | >81 | >81 | >81 | >81 | >81 | >81 | >81 | >81 | >81 | >81 |
|    | RF CAL | 0      | 1   | 2   | 3   | 4   | 5   | 6   | 7   | 8   | 9   | 10  |

### LO HARMONICS ORDER



Test conditions: RF IN: 125.1 MHz; -4.00 dBm.  
LO IN: 155.1 MHz; +7.00 dBm  
IF OUT: 30 MHz; -9.21 dBm

- Notes: 1. All Harmonics are in (dBc) relative to IF OUTPUT.  
2. + entry denotes harmonics are in (dBc) above IF OUTPUT.  
3. RF Cal represent the Harmonics level of the RF input signal to the mixer.


REV. X2  
ADE-6  
101013  
Page 3 of 3

CD541  
CD542  
CD636  
CD637

## Outline Dimensions



## PCB Land Pattern



Suggested Layout,  
Tolerance to be within  $\pm .002$

| CASE# | A              | B              | C              | D              | E              | F              | G              | H              | J              | K              | L              | WT,<br>GRAM |
|-------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|-------------|
| CD541 |                |                |                |                | .082<br>(2.08) |                |                |                |                |                |                | .15         |
| CD542 | .272<br>(6.91) | .310<br>(7.87) | .220<br>(5.58) | .100<br>(2.54) | .112<br>(2.84) | .055<br>(1.40) | .100<br>(2.54) | .030<br>(0.76) | .026<br>(0.66) | .065<br>(1.65) | .300<br>(7.62) | .20         |
| CD636 |                |                |                |                | .162<br>(4.11) |                |                |                |                |                |                | .25         |
| CD637 |                |                |                |                | .206<br>(5.23) |                |                |                |                |                |                | .40         |

Dimensions are in inches (mm). Tolerances: 2 Pl.  $\pm .01$ ; 3 Pl.  $\pm .005$

### Notes:

- Case material: Plastic.
- Termination finish:  
For RoHS Case Styles: Tin plate over Nickel plate. All models, (+) suffix.  
For RoHS-5 Case Styles: Tin-Lead plate. All models, no (+) suffix.




INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified

# Tape & Reel Packaging TR-F46



| Tape Width,<br>mm | Device Cavity<br>Pitch, mm | Reel Size,<br>inches | Devices per Reel |
|-------------------|----------------------------|----------------------|------------------|
| 16                | 12                         | 13                   | 900              |

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: [www.minicircuits.com/pages/pdfs/tape.pdf](http://www.minicircuits.com/pages/pdfs/tape.pdf)




INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

**Distribution Centers** NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

*Mini-Circuits ISO 9001 & ISO 14001 Certified*


## THIRD ANGLE PROJECTION



## REVISIONS

| REV | ECN No. | DESCRIPTION                                          | DATE     | DR  | AUTH |
|-----|---------|------------------------------------------------------|----------|-----|------|
| A   | M101143 | ADDED "gk" PIN CONNECTION, TT100 CASE STYLE & NOTE 2 | 10/10/05 | MMG | DJ   |
| B   | M102713 | ADDED "...WITH SMOBC"                                | 01/17/06 | MMG | IL   |
| C   | M108637 | REMOVED "PIN 1", ADDED INDEX ON UNIT                 | 12/01/06 | MYG | FL   |


**SUGGESTED MOUNTING CONFIGURATION**  
**FOR BH292, CD541/542/636/637, TT100/240 CASE**  
**STYLES, "gk", "ht", "hu", "nd", "w" PIN CONNECTIONS**



- NOTES:** 1. TRACE WIDTH IS SHOWN FOR ROGERS R04350B WITH DIELECTRIC THICKNESS .030"  $\pm$  .002"; COPPER: 1/2 OZ. EACH SIDE.  
 FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.  
 2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.



DENOTES PCB COPPER LAYOUT WITH SMOBC  
 (SOLDER MASK OVER BARE COPPER)



DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

UNLESS OTHERWISE SPECIFIED

INITIALS

DATE

DIMENSIONS ARE IN INCHES

TOLERANCES ON:

2 PL DECIMALS  $\pm$ 3 PL DECIMALS  $\pm$  .005ANGLES  $\pm$ FRACTIONS  $\pm$ 

DRAWN

MMG

07/17/02

CHECKED

WL

08/02/02

APPROVED

DJ

08/05/02

Mini-Circuits®

THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.

ASHEETA1.DWG REV:A DATE:01/12/95



# Mini-Circuits®

13 Neptune Avenue  
 Brooklyn NY 11235

PL, gk/ht/hu/nd/w, BH292,  
 CD541/542/636/637, TT100/240, TB-03

SIZE

A

CODE IDENT

15542

DRAWING NO:

98-PL-052

REV:

C

FILE: 98PL052


SCALE:

8:1

SHEET:


1 OF 1

## THIRD ANGLE PROJECTION



## REVISIONS

| REV | ECN No. | DESCRIPTION               | DATE  | DR | AUTH |
|-----|---------|---------------------------|-------|----|------|
| E   | M119737 | UPDATED PCB               | 10.08 | MF | AD   |
| F   | M127659 | UPDATED CARR              | 06.10 | SW | SG   |
| G   | M127846 | UPDATED SCHEMATIC DIAGRAM | 06.10 | SW | SG   |
| H   | M131840 | UPDATED DWG               | 05.11 | MF | AD   |

**NOTES:**

1. REFER TO -09 PAGE FOR ITEM DESCRIPTIONS.  
DESIGNATION NUMBERS ON -20 PAGE CORRESPOND TO THE NUMBERS ON -09 PAGE.
2. FOR TEXT HEIGHT & STYLE ON THE LABEL REFER TO: D3-G209.

UNLESS OTHERWISE SPECIFIED

INITIALS

DATE

DIMENSIONS ARE IN INCHES

DRAWN

S.WOLYNSKI

08.29.99

TOLERANCES ON:

CHECKED

SG

07.06.99

2 PL DECIMALS ±

APPROVED

MG

07.10.99

3 PL DECIMALS ±

ANGLES ±

FRACTIONS ±

Mini-Circuits®

THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.

ASHEETA1.DWG REV:A DATE:01/12/95


**Mini-Circuits®** 13 Neptune Avenue  
Brooklyn NY 11235

TB,ADE,CD542/636,06MX01,50

SIZE

A

CODE IDENT

15542

DRAWING NO:

TB-03-20

REV:

H

FILE:

WTB-03

SCALE:


1.5:1

SHEET:


1 OF 2

# Evaluation Board and Circuit

For Pin Connections and DUT Orientation Refer to  
Data Sheet of the DUT



TB-03



Schematic Diagram

## Notes:

1. 50 Ohm SMA Female connectors.
2. PCB Material: Rogers R04350 or equivalent,  
Dielectric Constant=3.5, Thickness=.030 inch.

 **Mini-Circuits®**





All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

| Specification                  | Test/Inspection Condition                                                                                                                                       | Reference/Spec                                                                                       |
|--------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------|------------------------------------------------------------------------------------------------------|
| Operating Temperature          | -40° to 85°C<br>Ambient Environment                                                                                                                             | Individual Model Data Sheet                                                                          |
| Storage Temperature            | -55° to 100° C<br>Ambient Environment                                                                                                                           | Individual Model Data Sheet                                                                          |
| Humidity                       | 90 to 95% RH, 240 hours, 50°C                                                                                                                                   | MIL-STD-202, Method 103, Condition A, Except 50°C and end-point electrical test done within 12 hours |
| Thermal Shock                  | -55° to 100°C, 100 cycles                                                                                                                                       | MIL-STD-202, Method 107, Condition A-3, except +100°C                                                |
| Solder Reflow Heat             | Sn-Pb Eutetic Process: 225°C peak<br>Pb-Free Process 245° - 250°C peak                                                                                          | J-STD-020, Table 4-1, 4-2 and 5-2, Figure 5-1                                                        |
| Solderability                  | 10X Magnification                                                                                                                                               | J-STD-002, 95% Coverage                                                                              |
| Vibration (High Frequency)     | 20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)                                                                             | MIL-STD-202, Method 204, Condition D                                                                 |
| Mechanical Shock               | 50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes                                                                                               | MIL-STD-202, Method 213, Condition A                                                                 |
| Marking Resistance to Solvents | Isopropyl alcohol + mineral spirits at 25°C; terpene defluxer at 25°C;<br>distilled water + proylene glycol monomethyl ether + monoethanolamine at 63°C to 70°C | MIL-STD-202, Method 215                                                                              |