

Surface Mount Frequency Mixer

ADEX-10L+

Level 4 (LO Power +4 dBm) 10 to 1000 MHz


Maximum Ratings

Operating Temperature	-40°C to 85°C
Storage Temperature	-55°C to 100°C
RF Power	50mW
IF Current	40mA
Permanent damage may occur if any of these limits are exceeded.	


Pin Connections

LO	6
RF	3
IF	2
GROUND	1,4,5

Outline Drawing




PCB Land Pattern



Outline Dimensions (inch/mm)

A	B	C	D	E	F	G
.272	.310	.220	.100	.112	.055	.100
6.91	7.87	5.59	2.54	2.84	1.40	2.54
H	J	K	L	wt		
.030	.026	.065	.300	grams		
0.76	0.66	1.65	7.62	0.20		

Demo Board MCL P/N: TB-03 Suggested PCB Layout (PL-052)



- NOTES: 1. TRACE WIDTH IS SHOWN FOR ROGERS RO4350B WITH DIELECTRIC THICKNESS .030" ± .002"; COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.

- DEMOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)
- DEMOTES COPPER LAND PATTERN FREE OF SOLDER MASK

Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

Features

- excellent L-R isolation, 60 dB typ.
- low conversion loss, 7.2 dB typ.
- flat conversion loss ±0.2 dB typ. over entire band
- good VSWR, 1.5:1 typ. for LO & RF, 1.8:1 Typ. for IF
- good performance to 1500 MHz
- aqueous washable
- protected by U.S. Patents 6,133,525 & 6,947,717

Applications

- cellular
- PCN



Generic photo used for illustration purposes only
CASE STYLE: CD542

+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications



Available Tape and Reel
at no extra cost

Reel Size	Devices/Reel
7"	20, 50, 100, 200
13"	500, 1000

Electrical Specifications

FREQUENCY (MHz)		CONVERSION LOSS (dB)				LO-RF ISOLATION (dB)			LO-IF ISOLATION (dB)			IP3 at center band (dBm)						
LO/RF	IF	Mid-Band		Total Range	L	M	U	L	M	U								
f_L - f_U		\bar{X}	σ	Max.	Max.	Typ. Min.	Typ. Min.	Typ. Min.	Typ. Min.	Typ. Min.	Typ. Min.	Typ.						
10-1000	DC-800	7.2	0.10	8.2 [†]	8.8 [†]	75	55	60	40	47	37	40	26	33	20	24	13	16

1 dB COMP: +1 dBm typ.

[†]Conversion loss increases 0.8 dB when IF is above 150 MHz

L = low range [f_L to 10 f_L]

m = mid band [$2f_L$ to $f_U/2$]


M = mid range [$10f_L$ to $f_U/2$]

U = upper range [$f_U/2$ to f_U]

Typical Performance Data

Frequency (MHz)		Conversion Loss (dB)	Isolation L-R (dB)	Isolation L-I (dB)	VSWR RF Port (:1)	VSWR LO Port (:1)
RF	LO	LO +4dBm	LO +4dBm	LO +4dBm	LO +4dBm	LO +4dBm
10.00	40.00	7.30	82.88	58.83	1.54	1.18
25.00	55.00	7.23	82.79	51.06	1.54	1.13
55.00	85.00	7.27	80.30	44.57	1.53	1.12
70.00	100.00	7.31	78.35	42.47	1.53	1.14
100.00	130.00	7.37	75.43	39.36	1.51	1.15
172.00	202.00	7.31	68.52	34.38	1.48	1.21
244.00	274.00	7.21	64.68	31.33	1.46	1.25
316.00	346.00	7.20	61.44	29.83	1.44	1.29
352.00	382.00	7.13	60.51	29.38	1.43	1.28
424.00	454.00	7.19	61.30	28.92	1.43	1.28
460.00	490.00	7.21	61.56	28.63	1.42	1.27
532.00	562.00	7.21	59.88	28.24	1.39	1.27
604.00	634.00	7.46	57.30	27.79	1.40	1.29
640.00	670.00	7.49	55.44	27.54	1.40	1.30
712.00	742.00	7.58	52.02	26.70	1.40	1.34
748.00	778.00	7.46	51.61	25.74	1.40	1.38
820.00	850.00	7.38	51.53	23.84	1.39	1.38
856.00	886.00	7.34	52.51	22.81	1.39	1.42
928.00	958.00	7.43	51.02	21.76	1.35	1.48
1000.00	1030.00	7.65	47.97	21.23	1.27	1.57







Electrical Schematic



Mini-Circuits

www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

REV. E
M158496
ADEX-10L+
DJ/TD/CP/AM
200415
Page 1 of 2



Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



Frequency Mixer

ADEX-10L+

Typical Performance Data

RF (IN) (MHz)	LO (MHz)	CONVERSION LOSS IF FIXED @IF(OUT)=30MHz (dB)			RF (IN) (MHz)	LO (MHz)	IP3 INPUT (dBm)			RF (IN) (MHz)	LO (MHz)	COMPRESSION @RF IN=+1dBm (dB)		
		@LO (dBm)					@LO (dBm)					@LO (dBm)		
		+1	+4	+7			+1	+4	+7			+1	+4	+7
10.1	40.1	7.97	6.71	6.19	10.1	40.1	11.04	15.22	19.06	10.1	40.1	0.61	0.32	0.19
49.9	79.9	8.60	7.41	6.89	49.9	79.9	11.28	15.99	17.34	49.9	79.9	0.69	0.44	0.28
89.7	119.7	8.51	7.39	6.89	89.7	119.7	11.39	16.78	17.01	89.7	119.7	0.72	0.42	0.31
129.5	159.5	8.53	7.39	6.88	129.5	159.5	12.60	14.90	14.89	129.5	159.5	0.72	0.48	0.35
169.3	199.3	8.40	7.30	6.83	169.3	199.3	13.50	14.75	14.93	169.3	199.3	0.73	0.50	0.33
209.0	239.0	8.38	7.26	6.85	209.0	239.0	13.54	13.33	16.92	209.0	239.0	0.73	0.48	0.32
248.8	278.8	8.33	7.23	6.85	248.8	278.8	11.98	13.53	18.83	248.8	278.8	0.76	0.52	0.34
308.5	338.5	8.18	7.24	6.88	308.5	338.5	11.04	15.45	20.54	308.5	338.5	0.77	0.44	0.30
348.3	378.3	8.13	7.24	6.87	348.3	378.3	10.92	14.91	22.37	348.3	378.3	0.82	0.46	0.35
408.0	438.0	8.09	7.26	6.89	408.0	438.0	11.24	15.96	21.82	408.0	438.0	0.80	0.47	0.36
447.8	477.8	8.14	7.31	6.95	447.8	477.8	11.14	16.02	19.45	447.8	477.8	0.79	0.46	0.32
507.5	537.5	8.12	7.29	6.91	507.5	537.5	12.47	16.58	18.34	507.5	537.5	0.80	0.49	0.35
547.3	577.3	8.18	7.35	6.93	547.3	577.3	12.31	18.51	21.89	547.3	577.3	0.81	0.51	0.41
606.9	636.9	8.21	7.40	6.97	606.9	636.9	11.97	15.49	18.92	606.9	636.9	0.85	0.56	0.49
646.7	676.7	8.25	7.50	7.07	646.7	676.7	11.96	14.84	20.53	646.7	676.7	1.06	0.72	0.59
706.4	736.4	8.35	7.58	7.17	706.4	736.4	11.17	13.88	19.87	706.4	736.4	1.11	0.75	0.66
746.2	776.2	8.41	7.58	7.13	746.2	776.2	11.81	14.34	19.27	746.2	776.2	1.18	0.91	0.75
805.9	835.9	8.52	7.50	7.00	805.9	835.9	11.56	18.47	14.80	805.9	835.9	1.25	1.07	0.95
845.7	875.7	8.55	7.49	6.93	845.7	875.7	12.38	13.76	13.65	845.7	875.7	1.34	1.25	1.12
905.4	935.4	8.70	7.57	6.89	905.4	935.4	10.09	11.87	10.34	905.4	935.4	1.39	1.40	1.30
945.2	975.2	8.69	7.58	6.87	945.2	975.2	9.47	10.42	8.82	945.2	975.2	1.40	1.44	1.37
1004.8	1034.8	8.67	7.66	6.95	1004.8	1034.8	8.52	9.25	7.39	1004.8	1034.8	1.52	1.46	1.42
1044.6	1074.6	8.65	7.77	7.08	1044.6	1074.6	7.76	8.47	7.30	1044.6	1074.6	1.52	1.40	1.34
1104.3	1134.3	8.53	7.79	7.23	1104.3	1134.3	7.73	9.29	10.53	1104.3	1134.3	1.70	1.44	1.30
1144.1	1174.1	8.45	7.75	7.23	1144.1	1174.1	7.53	9.70	13.09	1144.1	1174.1	1.84	1.58	1.38
1203.8	1233.8	8.22	7.59	7.16	1203.8	1233.8	8.23	11.48	15.91	1203.8	1233.8	2.02	1.66	1.45
1243.6	1273.6	8.14	7.52	7.13	1243.6	1273.6	8.45	11.95	14.38	1243.6	1273.6	2.08	1.76	1.46
1303.3	1333.3	7.97	7.40	7.07	1303.3	1333.3	9.01	12.38	13.24	1303.3	1333.3	2.17	1.76	1.48
1343.0	1373.0	7.90	7.38	7.09	1343.0	1373.0	9.44	12.70	12.94	1343.0	1373.0	2.16	1.67	1.39
1402.7	1432.7	7.85	7.40	7.22	1402.7	1432.7	9.51	12.53	13.49	1402.7	1432.7	2.14	1.55	1.22
1442.5	1472.5	7.84	7.43	7.27	1442.5	1472.5	9.39	12.45	14.46	1442.5	1472.5	2.11	1.49	1.18
1502.2	1532.2	7.95	7.55	7.38	1502.2	1532.2	9.59	11.96	14.38	1502.2	1532.2	2.12	1.46	1.16
1542.0	1572.0	8.06	7.65	7.49	1542.0	1572.0	9.74	11.69	14.98	1542.0	1572.0	2.03	1.38	1.15
1601.7	1631.7	8.35	7.90	7.73	1601.7	1631.7	9.41	11.67	13.54	1601.7	1631.7	1.98	1.36	1.12
1641.5	1671.5	8.57	8.11	7.92	1641.5	1671.5	9.18	12.07	13.92	1641.5	1671.5	1.94	1.31	1.06
1701.2	1731.2	8.92	8.42	8.22	1701.2	1731.2	8.91	10.96	13.34	1701.2	1731.2	1.90	1.26	1.04
1740.9	1770.9	9.23	8.69	8.47	1740.9	1770.9	8.20	10.70	12.79	1740.9	1770.9	1.84	1.22	0.99
1800.6	1830.6	9.63	9.04	8.80	1800.6	1830.6	8.35	10.24	11.84	1800.6	1830.6	1.67	1.13	0.94
1840.4	1870.4	9.97	9.33	9.06	1840.4	1870.4	8.07	10.71	12.58	1840.4	1870.4	1.65	1.16	0.96
1900.1	1930.1	10.49	9.77	9.46	1900.1	1930.1	8.00	9.11	10.63	1900.1	1930.1	1.57	1.12	0.95

REV. X2
 ADEX-10L+
 100817
 Page 1 of 5



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED • RoHS compliant
 P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see



Frequency Mixer

ADEX-10L+

Typical Performance Data

IF (OUT) (MHz)	LO (MHz)	CONVERSION LOSS VS. IF FREQUENCY @RF(IN)=500.1MHz (dB)	IF (OUT) (MHz)	LO (MHz)	CONVERSION LOSS VS. IF FREQUENCY @RF(IN)=10.1MHz (dB)	IF (OUT) (MHz)	LO (MHz)	CONVERSION LOSS VS. IF FREQUENCY @RF(IN)=1000.1MHz (dB)
		@LO (dBm)			@LO (dBm)			@LO (dBm)
		+4			+4			+4
480.0	20.1	6.82	10.0	20.1	7.12	990.0	10.1	8.30
467.9	32.2	6.85	30.0	40.1	6.98	970.0	30.1	8.20
455.9	44.2	6.83	50.0	60.1	7.03	950.0	50.1	8.13
443.8	56.3	6.79	70.0	80.1	7.01	930.0	70.1	8.06
431.8	68.3	6.80	90.0	100.1	6.99	910.0	90.1	7.97
419.7	80.4	6.79	110.0	120.1	6.99	890.0	110.1	7.86
407.7	92.4	6.76	130.0	140.1	6.96	870.0	130.1	7.80
395.6	104.5	6.73	150.0	160.1	6.97	850.0	150.1	7.79
383.6	116.5	6.69	170.0	180.1	6.97	830.0	170.1	7.73
371.5	128.6	6.64	190.0	200.1	6.95	810.0	190.1	7.68
359.5	140.6	6.63	210.0	220.1	6.95	790.0	210.1	7.64
347.4	152.7	6.64	230.0	240.1	6.92	770.0	230.1	7.62
335.4	164.7	6.64	250.0	260.1	6.96	750.0	250.1	7.56
323.3	176.8	6.63	270.0	280.1	7.02	730.0	270.1	7.55
311.3	188.8	6.63	290.0	300.1	6.97	710.0	290.1	7.52
299.2	200.9	6.62	310.0	320.1	6.99	690.0	310.1	7.49
287.2	212.9	6.62	330.0	340.1	7.05	670.0	330.1	7.45
275.1	225.0	6.59	350.0	360.1	6.99	650.0	350.1	7.44
263.1	237.0	6.58	370.0	380.1	7.11	630.0	370.1	7.41
251.0	249.1	6.57	390.0	400.1	7.11	610.0	390.1	7.38
239.0	261.1	6.61	430.0	440.1	7.51	570.0	430.1	7.36
226.9	273.2	6.61	450.0	460.1	7.26	550.0	450.1	7.36
214.9	285.2	6.61	490.0	500.1	7.29	510.0	490.1	7.36
202.8	297.3	6.59	510.0	520.1	7.30	490.0	510.1	7.38
190.8	309.3	6.60	550.0	560.1	7.40	450.0	550.1	7.36
178.7	321.4	6.59	570.0	580.1	7.47	430.0	570.1	7.44
166.7	333.4	6.59	610.0	620.1	7.63	390.0	610.1	7.40
154.6	345.5	6.58	630.0	640.1	7.68	370.0	630.1	7.42
142.6	357.5	6.59	670.0	680.1	7.90	330.0	670.1	7.51
130.5	369.6	6.62	690.0	700.1	7.94	310.0	690.1	7.48
118.5	381.6	6.65	730.0	740.1	8.02	270.0	730.1	7.45
106.4	393.7	6.64	750.0	760.1	8.04	250.0	750.1	7.43
94.4	405.7	6.61	790.0	800.1	8.00	210.0	790.1	7.33
82.3	417.8	6.61	810.0	820.1	7.96	190.0	810.1	7.28
70.3	429.8	6.64	850.0	860.1	8.03	150.0	850.1	7.24
58.2	441.9	6.66	870.0	880.1	8.03	130.0	870.1	7.19
46.2	453.9	6.62	910.0	920.1	8.08	90.0	910.1	7.18
34.1	466.0	6.65	930.0	940.1	8.15	70.0	930.1	7.30
22.1	478.0	6.68	970.0	980.1	8.27	30.0	970.1	7.41
10.0	490.1	7.07	990.0	1000.1	8.29	10.0	990.1	7.79



Frequency Mixer

ADEX-10L+

Typical Performance Data

LO (MHz)	LO-RF ISOLATION (dB)			LO-IF ISOLATION (dB)		
	@LO (dBm)			@LO (dBm)		
	+1	+4	+7	+1	+4	+7
10.1	59.26	62.18	68.13	47.88	51.52	57.47
49.9	75.20	75.77	71.22	52.10	48.36	46.09
89.7	75.72	68.33	64.67	47.56	43.17	40.51
129.5	73.10	64.29	60.59	43.94	39.78	37.12
169.3	69.77	61.49	58.24	41.16	37.14	34.76
209.0	66.33	59.51	56.38	38.89	35.15	33.28
248.8	64.41	57.59	54.17	37.08	33.68	32.05
308.5	62.61	55.13	51.49	34.86	32.23	30.66
348.3	63.70	54.98	51.02	33.81	31.59	29.90
408.0	65.60	53.80	49.37	32.92	30.73	28.95
447.8	69.51	54.25	49.21	32.41	30.22	28.23
507.5	62.36	57.00	50.09	32.31	30.00	28.01
547.3	57.03	57.60	49.94	32.10	29.51	27.28
606.9	53.38	56.29	48.20	31.76	28.89	26.36
646.7	51.93	55.77	48.27	31.23	28.50	26.13
706.4	51.09	58.57	50.78	30.13	27.77	25.95
746.2	49.59	61.15	54.44	29.28	26.94	25.26
805.9	47.38	55.48	59.66	27.82	25.34	23.64
845.7	45.24	50.15	55.99	26.96	24.40	22.67
905.4	42.38	45.47	49.44	25.79	23.30	21.45
945.2	40.53	43.07	46.79	25.23	22.96	21.00
1004.8	39.00	41.38	45.31	23.97	22.15	20.30
1044.6	37.49	39.51	42.61	23.09	21.63	20.07
1104.3	35.94	38.02	40.77	21.73	20.50	19.27
1144.1	35.00	37.17	39.70	20.94	19.76	18.61
1203.8	33.90	36.31	38.66	19.86	18.74	17.59
1243.6	33.13	35.71	37.79	19.19	18.07	16.89
1303.3	32.08	34.67	36.16	18.15	17.06	15.83
1343.0	31.59	34.12	35.20	17.37	16.28	15.07
1402.7	30.42	32.26	32.32	16.28	15.28	14.22
1442.5	29.58	30.89	30.61	15.61	14.73	13.79
1502.2	28.23	28.92	28.34	14.74	14.00	13.24
1542.0	26.83	27.47	26.94	14.36	13.74	13.05
1601.7	25.28	25.84	25.38	13.87	13.35	12.73
1641.5	24.27	24.92	24.53	13.56	13.12	12.52
1701.2	22.95	23.74	23.51	13.31	12.97	12.41
1740.9	22.15	23.03	22.89	13.20	12.93	12.39
1800.6	20.97	22.05	22.11	12.98	12.93	12.45
1840.4	20.71	21.93	22.10	12.98	13.03	12.58
1900.1	19.46	20.95	21.37	12.79	13.12	12.79

RF (IN) (MHz)	LO (MHz)	RF-IF ISOLATION (dB)		
		@LO (dBm)		
		+1	+4	+7
10.1	40.1	37.75	32.75	38.23
49.9	79.9	34.84	34.94	35.44
89.7	119.7	29.63	30.04	31.22
129.5	159.5	27.35	27.98	27.79
169.3	199.3	25.38	25.93	26.13
209.0	239.0	23.87	24.58	24.67
248.8	278.8	22.76	23.35	23.78
308.5	338.5	21.60	22.34	22.72
348.3	378.3	20.97	21.77	22.25
408.0	438.0	20.31	21.23	21.83
447.8	477.8	19.82	20.74	21.31
507.5	537.5	18.99	19.92	20.60
547.3	577.3	18.58	19.62	20.42
606.9	636.9	18.27	19.45	20.42
646.7	676.7	18.14	19.26	20.10
706.4	736.4	17.65	18.45	18.91
746.2	776.2	17.04	17.49	17.71
805.9	835.9	16.01	16.15	16.22
845.7	875.7	15.54	15.60	15.61
905.4	935.4	15.04	15.12	15.12
945.2	975.2	14.87	15.01	15.11
1004.8	1034.8	14.86	15.07	15.35
1044.6	1074.6	14.95	15.21	15.65
1104.3	1134.3	15.23	15.51	15.93
1144.1	1174.1	15.46	15.66	15.87
1203.8	1233.8	15.76	15.70	15.44
1243.6	1273.6	15.78	15.47	14.92
1303.3	1333.3	15.36	14.65	13.87
1343.0	1373.0	14.79	13.93	13.16
1402.7	1432.7	13.57	12.65	11.99
1442.5	1472.5	12.70	11.81	11.19
1502.2	1532.2	11.57	10.72	10.13
1542.0	1572.0	10.78	9.97	9.40
1601.7	1631.7	9.82	9.07	8.53
1641.5	1671.5	9.22	8.53	8.01
1701.2	1731.2	8.39	7.79	7.32
1740.9	1770.9	7.90	7.37	6.94
1800.6	1830.6	7.17	6.73	6.36
1840.4	1870.4	6.79	6.40	6.07
1900.1	1930.1	6.19	5.88	5.58

Frequency Mixer

ADEX-10L+

Typical Performance Data

RF (IN) (MHz)	LO (MHz)	RF VSWR (:1)		
		@LO (dBm)		
		+1	+4	+7
10.1	40.1	1.93	1.81	1.63
49.9	79.9	1.59	1.43	1.32
89.7	119.7	1.67	1.50	1.39
129.5	159.5	1.61	1.44	1.34
169.3	199.3	1.67	1.49	1.39
209.0	239.0	1.63	1.46	1.38
248.8	278.8	1.61	1.44	1.36
308.5	338.5	1.61	1.46	1.39
348.3	378.3	1.60	1.46	1.39
408.0	438.0	1.57	1.45	1.38
447.8	477.8	1.59	1.47	1.41
507.5	537.5	1.60	1.49	1.43
547.3	577.3	1.57	1.46	1.40
606.9	636.9	1.59	1.49	1.43
646.7	676.7	1.55	1.46	1.41
706.4	736.4	1.57	1.49	1.44
746.2	776.2	1.54	1.45	1.39
805.9	835.9	1.53	1.42	1.35
845.7	875.7	1.54	1.42	1.34
905.4	935.4	1.49	1.37	1.28
945.2	975.2	1.55	1.42	1.32
1004.8	1034.8	1.49	1.36	1.25
1044.6	1074.6	1.53	1.41	1.29
1104.3	1134.3	1.52	1.41	1.29
1144.1	1174.1	1.49	1.39	1.28
1203.8	1233.8	1.49	1.40	1.32
1243.6	1273.6	1.46	1.40	1.34
1303.3	1333.3	1.52	1.48	1.45
1343.0	1373.0	1.57	1.56	1.55
1402.7	1432.7	1.64	1.65	1.65
1442.5	1472.5	1.69	1.70	1.71
1502.2	1532.2	1.76	1.77	1.78
1542.0	1572.0	1.73	1.73	1.74
1601.7	1631.7	1.83	1.83	1.84
1641.5	1671.5	1.77	1.77	1.78
1701.2	1731.2	1.92	1.90	1.90
1740.9	1770.9	1.85	1.84	1.85
1800.6	1830.6	1.93	1.91	1.91
1840.4	1870.4	1.97	1.96	1.97
1900.1	1930.1	1.92	1.90	1.91

LO (MHz)	LO VSWR (:1)		
	@LO (dBm)		
	+1	+4	+7
10.1	1.39	1.06	1.54
49.9	1.45	1.14	1.65
89.7	1.40	1.14	1.65
129.5	1.43	1.18	1.66
169.3	1.41	1.23	1.69
209.0	1.42	1.25	1.68
248.8	1.43	1.29	1.73
308.5	1.44	1.33	1.77
348.3	1.41	1.36	1.84
408.0	1.39	1.39	1.90
447.8	1.37	1.44	1.96
507.5	1.34	1.47	2.02
547.3	1.32	1.52	2.09
606.9	1.29	1.56	2.13
646.7	1.28	1.62	2.22
706.4	1.29	1.68	2.28
746.2	1.29	1.73	2.35
805.9	1.32	1.79	2.40
845.7	1.34	1.83	2.45
905.4	1.43	1.95	2.58
945.2	1.47	2.00	2.64
1004.8	1.56	2.14	2.80
1044.6	1.61	2.19	2.84
1104.3	1.69	2.28	2.95
1144.1	1.75	2.35	3.02
1203.8	1.81	2.38	3.02
1243.6	1.87	2.44	3.08
1303.3	1.91	2.44	3.03
1343.0	1.96	2.47	3.05
1402.7	2.01	2.48	3.04
1442.5	2.07	2.54	3.09
1502.2	2.20	2.64	3.17
1542.0	2.31	2.72	3.24
1601.7	2.48	2.85	3.33
1641.5	2.59	2.94	3.39
1701.2	2.75	3.06	3.45
1740.9	2.84	3.13	3.52
1800.6	2.96	3.21	3.56
1840.4	3.04	3.27	3.60
1900.1	3.08	3.28	3.58

IF (OUT) (MHz)	IF VSWR @LO=1000.1MHz (:1)		
	@LO (dBm)		
	+1	+4	+7
10.0	1.86	1.61	1.16
29.8	1.84	1.36	1.09
49.5	1.74	1.29	1.06
69.3	1.62	1.23	1.02
89.0	1.72	1.29	1.02
108.8	1.73	1.32	1.06
128.5	1.75	1.32	1.06
148.3	1.70	1.30	1.05
168.0	1.72	1.31	1.05
187.8	1.77	1.35	1.08
207.5	1.79	1.38	1.11
227.3	1.78	1.37	1.12
247.0	1.75	1.36	1.11
266.8	1.74	1.35	1.10
286.5	1.76	1.37	1.11
306.3	1.78	1.39	1.14
326.0	1.75	1.38	1.13
345.8	1.74	1.37	1.12
365.5	1.74	1.37	1.12
385.3	1.75	1.39	1.13
405.0	1.77	1.40	1.14
424.8	1.76	1.39	1.14
444.5	1.75	1.39	1.14
464.3	1.77	1.41	1.16
484.0	1.77	1.42	1.16
503.8	1.75	1.40	1.15
523.5	1.74	1.40	1.15
543.3	1.74	1.39	1.15
563.0	1.74	1.40	1.16
582.8	1.75	1.41	1.17
602.5	1.72	1.39	1.15
622.3	1.71	1.38	1.16
642.0	1.73	1.40	1.18
661.8	1.74	1.41	1.19
681.5	1.74	1.41	1.19
701.3	1.71	1.39	1.17
721.0	1.69	1.38	1.17
740.8	1.69	1.39	1.19
780.3	1.70	1.39	1.19
800.0	1.67	1.37	1.17

Harmonics Tables

RF HARMONICS ORDER

	(-dBm)	(-dBc)										
0	-	-	4	19	9	30	21	45	37	58	56	61
1	-	13	0	32	16	33	29	40	46	48	46	61
2	110	64	43	59	43	56	45	59	56	70	64	72
3	117	64	67	67	59	72	57	84	68	85	73	85
4	116	94	87	90	95	88	86	87	82	103	95	93
5	120	103	103	98	91	89	83	99	95	96	104	97
6	114	106	111	110	107	102	101	84	101	107	102	104
7	115	107	118	114	102	109	105	90	83	108	95	103
8	110	102	107	99	104	103	103	98	94	104	96	98
9	114	100	105	109	106	100	103	107	104	95	91	96
10	116	101	98	110	103	105	102	109	100	102	98	95
	RF CAL	0	1	2	3	4	5	6	7	8	9	10

LO HARMONICS ORDER

Test conditions: RF IN: 500.1 MHz; -14.00 dBm.
 LO IN: 530.01 MHz; +4.00 dBm
 IF OUT: 29.91 MHz; -21 dBm

RF HARMONICS ORDER

	(-dBm)	(-dBc)										
0	-	-	13	28	21	44	34	58	50	66	66	78
1	-	13	0	31	16	37	30	45	49	54	55	71
2	95	57	36	64	35	54	38	57	51	68	68	78
3	111	43	49	47	50	58	44	53	66	58	58	66
4	110	91	59	65	56	63	60	62	56	70	67	75
5	114	70	76	66	53	69	53	65	56	69	65	80
6	114	95	84	82	80	79	69	79	66	89	69	89
7	118	98	87	90	78	83	78	77	77	81	94	79
8	114	100	102	99	93	105	86	100	82	101	82	94
9	123	109	112	109	101	100	104	90	88	91	87	90
10	112	109	125	109	109	103	101	105	102	103	100	100
	RF CAL	0	1	2	3	4	5	6	7	8	9	10

LO HARMONICS ORDER

Test conditions: RF IN: 500.1 MHz; -4.00 dBm.
 LO IN: 530.01 MHz; +4.00 dBm
 IF OUT: 29.91 MHz; -10.96 dBm

- Notes: 1. All Harmonics are in (dBc) relative to IF OUTPUT.
 2. + entry denotes harmonics are in (dBc) above IF OUTPUT.
 3. RF Cal represent the Harmonics level of the RF input signal to the mixer.

REV. X2
 ADEX-10L+
 100817
 Page 5 of 5



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED • RoHS compliant
 P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661




The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see minicircuits.com

Frequency Mixer


ADEX-10L+

Typical Performance Curves


Conversion Loss @ IF=30MHz




Conversion Loss vs. IF @ RF=500.1MHz




Conversion Loss vs. IF @ RF=10.1MHz




Conversion Loss vs. IF @ RF=1000.1MHz



IP3 Input




Compression @ RF IN=+1dBm




Typical Performance Curves


LO-RF Isolation




LO-IF Isolation




RF-IF Isolation




RF VSWR



LO VSWR



IF VSWR



Harmonics Tables

RF HARMONICS ORDER

	(-dBm)	(-dBc)										
0	-	-	4	19	9	30	21	45	37	58	56	61
1	-	13	0	32	16	33	29	40	46	48	46	61
2	110	64	43	59	43	56	45	59	56	70	64	72
3	117	64	67	67	59	72	57	84	68	85	73	85
4	116	94	87	90	95	88	86	87	82	103	95	93
5	120	103	103	98	91	89	83	99	95	96	104	97
6	114	106	111	110	107	102	101	84	101	107	102	104
7	115	107	118	114	102	109	105	90	83	108	95	103
8	110	102	107	99	104	103	103	98	94	104	96	98
9	114	100	105	109	106	100	103	107	104	95	91	96
10	116	101	98	110	103	105	102	109	100	102	98	95
	RF CAL	0	1	2	3	4	5	6	7	8	9	10

LO HARMONICS ORDER

Test conditions: RF IN: 500.1 MHz; -14.00 dBm.
 LO IN: 530.01 MHz; +4.00 dBm
 IF OUT: 29.91 MHz; -21 dBm

RF HARMONICS ORDER

	(-dBm)	(-dBc)										
0	-	-	13	28	21	44	34	58	50	66	66	78
1	-	13	0	31	16	37	30	45	49	54	55	71
2	95	57	36	64	35	54	38	57	51	68	68	78
3	111	43	49	47	50	58	44	53	66	58	58	66
4	110	91	59	65	56	63	60	62	56	70	67	75
5	114	70	76	66	53	69	53	65	56	69	65	80
6	114	95	84	82	80	79	69	79	66	89	69	89
7	118	98	87	90	78	83	78	77	77	81	94	79
8	114	100	102	99	93	105	86	100	82	101	82	94
9	123	109	112	109	101	100	104	90	88	91	87	90
10	112	109	125	109	109	103	101	105	102	103	100	100
	RF CAL	0	1	2	3	4	5	6	7	8	9	10

LO HARMONICS ORDER

Test conditions: RF IN: 500.1 MHz; -4.00 dBm.
 LO IN: 530.01 MHz; +4.00 dBm
 IF OUT: 29.91 MHz; -10.96 dBm

- Notes: 1. All Harmonics are in (dBc) relative to IF OUTPUT.
 2. + entry denotes harmonics are in (dBc) above IF OUTPUT.
 3. RF Cal represent the Harmonics level of the RF input signal to the mixer.

REV. X2
 ADEX-10L+
 100817
 Page 3 of 3



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED • RoHS compliant
 P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661




The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see minicircuits.com

Case Style

CD

CD541
CD542
CD636
CD637

Outline Dimensions



PCB Land Pattern



Suggested Layout,
Tolerance to be within $\pm.002$

CASE#	A	B	C	D	E	F	G	H	J	K	L	WT, GRAM
CD541					.082 (2.08)							.15
CD542	.272 (6.91)	.310 (7.87)	.220 (5.58)	.100 (2.54)	.112 (2.84)	.055 (1.40)	.100 (2.54)	.030 (0.76)	.026 (0.66)	.065 (1.65)	.300 (7.62)	.20
CD636					.162 (4.11)							.25
CD637					.206 (5.23)							.40

Dimensions are in inches (mm). Tolerances: 2 Pl. $\pm .01$; 3 Pl. $\pm .005$

Notes:

- Case material: Plastic.
- Termination finish:
 - For RoHS Case Styles: Tin plate over Nickel plate. All models, (+) suffix.
 - For RoHS-5 Case Styles: Tin-Lead plate. All models, no (+) suffix.

Mini-Circuits®

INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified

Tape & Reel Packaging TR-F34



Tape Width, mm	Device Cavity Pitch, mm	Reel Size, inches	Devices per Reel see note	
16	12	7	Small quantity standard (see note)	20
				50
				100
				200
		13	Standard	500
				1000

Note: Availability of small reel quantity varies by model.
Refer to pricing and availability on individual model dashboard.

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: www.minicircuits.com/pages/pdfs/tape.pdf



INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified

THIRD ANGLE PROJECTION



REVISIONS

REV	ECN No.	DESCRIPTION	DATE	DR	AUTH
A	M101143	ADDED "gk" PIN CONNECTION, TT100 CASE STYLE & NOTE 2	10/10/05	MMG	DJ
B	M102713	ADDED "...WITH SMOBC"	01/17/06	MMG	IL
C	M108637	REMOVED "PIN 1", ADDED INDEX ON UNIT	12/01/06	MYG	FL

SUGGESTED MOUNTING CONFIGURATION
FOR BH292, CD541/542/636/637, TT100/240 CASE
STYLES, "gk", "ht", "hu", "nd", "w" PIN CONNECTIONS



- NOTES:** 1. TRACE WIDTH IS SHOWN FOR ROGERS R04350B WITH DIELECTRIC THICKNESS .030" ± .002"; COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
 2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.

- DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)
- DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

UNLESS OTHERWISE SPECIFIED	INITIALS	DATE
DRAWN	MMG	07/17/02
CHECKED	WL	08/02/02
APPROVED	DJ	08/05/02

Mini-Circuits® 13 Neptune Avenue
 Brooklyn NY 11235

PL, gk/ht/hu/nd/w, BH292,
 CD541/542/636/637, TT100/240, TB-03

SIZE A	CODE IDENT 15542	DRAWING NO: 98-PL-052	REV: C
FILE: 98PL052	SCALE: 8:1	SHEET: 1 OF 1	

Mini-Circuits®
 THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.

THIRD ANGLE PROJECTION



REVISIONS

REV	ECN No.	DESCRIPTION	DATE	DR	AUTH
E	M119737	UPDATED PCB	10.08	MF	AD
F	M127659	UPDATED CARR	06.10	SW	SG
G	M127846	UPDATED SCHEMATIC DIAGRAM	06.10	SW	SG
H	M131840	UPDATED DWG	05.11	MF	AD



NOTES:

1. REFER TO -09 PAGE FOR ITEM DESCRIPTIONS.
DESIGNATION NUMBERS ON -20 PAGE CORRESPOND TO THE NUMBERS ON -09 PAGE.
2. FOR TEXT HEIGHT & STYLE ON THE LABEL REFER TO: D3-G209.

UNLESS OTHERWISE SPECIFIED	INITIALS	DATE
DIMENSIONS ARE IN INCHES TOLERANCES ON: 2 PL DECIMALS ± 3 PL DECIMALS ± ANGLES ± FRACTIONS ±	DRAWN	S.WOLYNSKI 06.29.99
	CHECKED	SG 07.06.99
	APPROVED	MG 07.10.99

 **Mini-Circuits®** 13 Neptune Avenue
Brooklyn NY 11235

TB,ADE,CD542/636,06MX01,50

 Mini-Circuits®
THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.

SIZE A	CODE IDENT 15542	DRAWING NO: TB-03-20	REV: H
FILE: WTB-03	SCALE: 1.5:1	SHEET: 1 OF 2	

Evaluation Board and Circuit

For Pin Connections and DUT Orientation Refer to
Data Sheet of the DUT



TB-03



Schematic Diagram

Notes:

1. 50 Ohm SMA Female connectors.
2. PCB Material: Rogers R04350 or equivalent,
Dielectric Constant=3.5, Thickness=.030 inch.

 **Mini-Circuits®**

All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-40° to 85°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Humidity	90 to 95% RH, 240 hours, 50°C	MIL-STD-202, Method 103, Condition A, Except 50°C and end-point electrical test done within 12 hours
Thermal Shock	-55° to 100°C, 100 cycles	MIL-STD-202, Method 107, Condition A-3, except +100°C
Solder Reflow Heat	Sn-Pb Eutetic Process: 225°C peak Pb-Free Process 245° - 250°C peak	J-STD-020, Table 4-1, 4-2 and 5-2, Figure 5-1
Solderability	10X Magnification	J-STD-002, 95% Coverage
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes	MIL-STD-202, Method 213, Condition A
Marking Resistance to Solvents	Isopropyl alcohol + mineral spirits at 25°C; terpene defluxer at 25°C; distilled water + proylene glycol monomethyl ether + monoethanolamine at 63°C to 70°C	MIL-STD-202, Method 215