



Mini-Circuits

WIDEBAND, MICROWAVE

# Monolithic Amplifier


AVA-183A+

50Ω

5 to 18 GHz

## THE BIG DEAL

- Surface Mount Amplifier Up to 18 GHz
- Integrated DC blocks, Bias-Tee & Microwave Bypass Capacitor
- Suitable for Low Phase Noise Applications
- Gain, 13.4 dB Typ. & Flatness,  $\pm 1.2$  dB
- P1dB, Typ. +19.0 dBm
- Output Power, Up to +19.0 dBm Typ.
- Excellent Isolation, 36 dB Typ. at 12 GHz
- Single Positive Supply Voltage, +5 V
- Unconditionally Stable
- Aqueous Washable; 3 mm x 3 mm SMT Package



Generic photo used for illustration purposes only

CASE STYLE: DQ849

**+RoHS Compliant**

The +Suffix identifies RoHS Compliance.  
See our website for methodologies and qualifications

## APPLICATIONS

- Military EW and Radar
- DBS
- Microwave Point-to-Point Radios
- Satellite Systems

## PRODUCT OVERVIEW

The AVA-183A+ is a surface-mount microwave amplifier fabricated using InGaAs pHEMT technology and is a fully integrated gain block up to 18 GHz. It is packaged in Mini-Circuits industry standard 3x3 mm MCLP package, which provides excellent RF and thermal performance. The AVA-183A+ integrates the entire matching network with the majority of the bias circuit inside the package, reducing the need for complicated external circuits. This approach makes the AVA-183A+ extremely flexible and enables simple, straightforward use.

## KEY FEATURES

| Feature                                                        | Advantages                                                                                                                                                                                                                                                         |
|----------------------------------------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Wideband, 5 to 18 GHz                                          | Broad frequency range supports a wide array of applications from microwave radio and radar , to military communications and countermeasures.                                                                                                                       |
| Excellent Gain Flatness                                        | Typical $\pm 1.2$ dB gain flatness across the entire frequency range minimizes the need for external equalizer networks making it a great fit for instrumentation and EW applications.                                                                             |
| High Isolation                                                 | With reverse isolation of 31-42 dB (17-23 dB directivity), the AVA-183A+ is an excellent choice for buffering broadband circuits. It is an ideal LO driver amplifier and provides designers system flexibility and margin when integrating cascaded RF components. |
| Single +5 V Supply                                             | This single-supply implementation is much simpler to use than competing amplifiers with dual supply voltages. No power supply sequencing or complicated bias tee circuits are required, reducing board space and cost.                                             |
| Manufacturability                                              | MSL1 and ESD Class 1A (HBM) ratings minimize special handling on production lines.                                                                                                                                                                                 |
| Low Additive Phase Noise, Typically -151 dBc/Hz @10 KHz Offset | Ideal for low phase noise synthesizer applications                                                                                                                                                                                                                 |

Mini-Circuits

www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

REV. D  
ECO-024424  
AVA-183A+  
MCL NY  
250205

PAGE 1 OF 5



Mini-Circuits®

WIDEBAND, MICROWAVE

## Monolithic Amplifier

AVA-183A+

50Ω 5 to 18 GHz

ELECTRICAL SPECIFICATIONS<sup>1</sup> AT 25°C, Z<sub>0</sub>=50Ω, (REFER TO CHARACTERIZATION CIRCUIT, FIG. 1)

| Parameter                                         | Condition (GHz) | Min.  | Typ.  | Max. | Units  |
|---------------------------------------------------|-----------------|-------|-------|------|--------|
| Frequency Range                                   |                 | 5.0   |       | 18.0 | GHz    |
| DC Voltage (V <sub>D1</sub> , V <sub>D2</sub> )   |                 |       | +5.0  |      | V      |
| DC Current (I <sub>D1</sub> +I <sub>D2</sub> )    |                 | 104   | 131   | 166  | mA     |
| Gain                                              | 5.0             |       | 12.9  |      | dB     |
|                                                   | 8.0             | 12.0  | 14.7  |      |        |
|                                                   | 10.0            | 12.0  | 14.0  |      |        |
|                                                   | 12.0            |       | 13.4  |      |        |
|                                                   | 14.0            |       | 13.1  |      |        |
|                                                   | 16.0            |       | 13.6  |      |        |
|                                                   | 18.0            | 10.8  | 12.4  |      |        |
| Input Return Loss                                 | 5.0             |       | 10.4  |      | dB     |
|                                                   | 8.0             |       | 17.0  |      |        |
|                                                   | 10.0            |       | 11.0  |      |        |
|                                                   | 12.0            |       | 11.0  |      |        |
|                                                   | 14.0            |       | 11.0  |      |        |
|                                                   | 16.0            |       | 11.0  |      |        |
|                                                   | 18.0            |       | 7.5   |      |        |
| Output Return Loss                                | 5.0             |       | 8.0   |      | dB     |
|                                                   | 8.0             |       | 18.0  |      |        |
|                                                   | 10.0            |       | 14.0  |      |        |
|                                                   | 12.0            |       | 11.0  |      |        |
|                                                   | 14.0            |       | 10.6  |      |        |
|                                                   | 16.0            |       | 11.2  |      |        |
|                                                   | 18.0            |       | 11.8  |      |        |
| Output IP3 <sup>2</sup>                           | 5.0             |       | +32.2 |      | dBm    |
|                                                   | 8.0             |       | +29.0 |      |        |
|                                                   | 10.0            |       | +27.7 |      |        |
|                                                   | 12.0            |       | +26.3 |      |        |
|                                                   | 14.0            |       | +25.1 |      |        |
|                                                   | 16.0            |       | +24.3 |      |        |
|                                                   | 18.0            |       | +24.4 |      |        |
| Output Power @ 1 dB Compression                   | 5.0             | +16.0 | +17.6 |      | dBm    |
|                                                   | 8.0             |       | +18.0 |      |        |
|                                                   | 10.0            |       | +19.0 |      |        |
|                                                   | 12.0            |       | +19.0 |      |        |
|                                                   | 14.0            |       | +19.9 |      |        |
|                                                   | 16.0            |       | +19.6 |      |        |
|                                                   | 18.0            |       | +18.7 |      |        |
| Noise Figure                                      | 5.0             |       | 7.4   |      | dB     |
|                                                   | 8.0             |       | 4.3   |      |        |
|                                                   | 10.0            |       | 4.5   |      |        |
|                                                   | 12.0            |       | 4.8   |      |        |
|                                                   | 14.0            |       | 5.1   |      |        |
|                                                   | 16.0            |       | 5.1   |      |        |
|                                                   | 18.0            |       | 6.0   |      |        |
| Additive Phase Noise 5.0 GHz, 10 KHz offset       |                 |       | -151  |      | dBc/Hz |
| Directivity (Isolation-Gain)                      | 12              |       | 23.1  |      | dB     |
| DC Current Variation vs. Temperature <sup>3</sup> |                 |       | 0.046 |      | mA/°C  |
| Thermal Resistance                                |                 |       | 61    |      | °C/W   |

1. Measured on Mini-Circuits Characterization test fixture TB-547-2+. See Characterization Test Circuit (Fig. 1).

2. At P<sub>OUT</sub>=+9 dBm/100 Hz.

3. (Current at +85°C - Current at -45°C) / 130.

ABSOLUTE MAXIMUM RATINGS<sup>4</sup>

| Parameter                          | Ratings         |
|------------------------------------|-----------------|
| Operating Temperature <sup>5</sup> | -40°C to +85°C  |
| Storage Temperature                | -65°C to +150°C |
| Channel Temperature                | +150°C          |
| DC Voltage (Pad 7,8)               | +5.5 V          |
| DC Voltage (Pads 2, 5)             | +10 V           |
| Power Dissipation                  | 980 mW          |
| DC Current (Pad 7+8)               | 180 mA          |
| Input Power (CW)                   | +20 dBm         |

4. Permanent damage may occur if any of these limits are exceeded. These maximum ratings are not intended for continuous normal operation.

5. Defined with reference to ground pad temperature.

Mini-Circuits®

www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

PAGE 2 OF 5



Mini-Circuits

WIDEBAND, MICROWAVE



# Monolithic Amplifier

AVA-183A+



50 $\Omega$

5 to 18 GHz

## INTERMODULATION AND IP3 VS. FREQUENCY AND OUTPUT POWER



## SIMPLIFIED SCHEMATIC AND PAD DESCRIPTION



| Function | Pad Number                               | Description (See Application Circuit, Fig. 2)                  |
|----------|------------------------------------------|----------------------------------------------------------------|
| RF-IN    | 2                                        | RF input pad                                                   |
| RF-OUT   | 5                                        | RF output pad                                                  |
| DC       | 8(V <sub>D1</sub> ), 7(V <sub>D2</sub> ) | DC power supply                                                |
| GND      | Paddle in Center of Bottom               | Connected to ground                                            |
| NOT USED | 1,3,4,6                                  | No internal connection; recommended use: per PCB Layout PL-328 |

Mini-Circuits



Mini-Circuits

WIDEBAND, MICROWAVE


## Monolithic Amplifier

AVA-183A+

50Ω

5 to 18 GHz

## CHARACTERIZATION TEST CIRCUIT



C1=5.6 pF, 0402 (NPO)  
 C2=18 pF, 0402 (NPO)  
 C3=0.001 μF, 0402 (NPO)  
 C4=0.1 μF, 0402 (X7R)  
 L1=3.3 nH, 0805 (wire wound)

ML1-ML7 are short microstrip lines.  
 Refer to 98-PL-328.

Fig 1. Block Diagram of Test Circuit used for characterization. (DUT soldered on Mini-Circuits Characterization Test Board TB-547-2+) Gain, Output Power at 1 dB Compression (P1dB), Noise Figure, Output IP3 (OIP3) are measured using Agilent's N5242A PNA-X microwave network analyzer.

Conditions:

1. Gain:  $P_{IN} = -25$  dBm
2. Output IP3 (OIP3): Two tones, spaced 1 MHz apart, +9 dBm/tone at output.
3.  $V_s$  adjusted for +5.0 V at device ( $V_{D1}$  and  $V_{D2}$ ), compensating loss of bias lines.

## RECOMMENDED APPLICATION CIRCUIT

(Refer to Evaluation Board for PCB Layout and Component Values)




Fig 2. Recommended Application Circuit

C1=5.6 pF, 0402 (NPO)  
 C2=18 pF, 0402 (NPO)  
 C3=0.001 μF, 0402 (NPO)  
 C4=0.1 μF, 0402 (X7R)  
 L1=3.3 nH, 0805 (wire wound)

ML1-ML7 are short microstrip lines.  
 Refer to 98-PL-328.

## PRODUCT MARKING



- Black Body
- Model Family Designation

Marking may contain other features or characters for internal lot control.

Mini-Circuits



Mini-Circuits

WIDEBAND, MICROWAVE

# Monolithic Amplifier

AVA-183A+

50Ω

5 to 18 GHz

ADDITIONAL DETAILED TECHNICAL INFORMATION IS AVAILABLE ON OUR DASHBOARD. TO ACCESS [CLICK HERE](#)

|                                                      |                                                                            |
|------------------------------------------------------|----------------------------------------------------------------------------|
| Performance Data                                     | Data Table<br>Swept Graphs<br>S-Parameter (S2P Files) Data Set (.zip file) |
| Case Style                                           | DQ849 Plastic package, exposed paddle, lead finish: Matte-tin              |
| Tape & Reel<br>Standard Quantities Available on Reel | F104<br>7" reels with 20, 50, 100, 200, 500, 1000 or 2000 devices          |
| Suggested Layout for PCB Design                      | PL-328                                                                     |
| Evaluation Board                                     | TB-547-2+                                                                  |
| Environmental Ratings                                | ENV08T1                                                                    |

## ESD RATING


Human Body Model (HBM): 1A (250 to <500 V) in accordance with ANSI/ESD STM 5.1 - 2001

Machine Model (MM): M1 (25 V) in accordance with ANSI/ESD STM5.2-1999

## MSL RATING

Moisture Sensitivity: MSL1 in accordance with IPC/JEDEC J-STD-020D

## MSL TEST FLOW CHART



### NOTES

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits' standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the standard terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/terms/viewterm.html](http://www.minicircuits.com/terms/viewterm.html)



## Typical Performance Data

NOTE: Use PDF Bookmarks to view DATA at required conditions

## Definitions:

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 5.00V, Id = 132.12mA @ Temperature = 25degC

| FREQ  | Gain  | Isolation | Input<br>Return<br>Loss | Output<br>Return<br>Loss | Stability |         | IP-3<br>Output | 1dB<br>Comp.<br>Output | Noise<br>Figure |
|-------|-------|-----------|-------------------------|--------------------------|-----------|---------|----------------|------------------------|-----------------|
| (GHz) | (dB)  | (dB)      | (dB)                    | (dB)                     | K         | Measure | (dBm)          | (dBm)                  | (dB)            |
| 5.0   | 12.93 | 41.14     | 11.79                   | 7.77                     | 10.13     | 0.88    | 32.66          | 17.23                  | 7.19            |
| 5.2   | 13.37 | 40.17     | 13.87                   | 8.47                     | 9.09      | 0.88    | 29.59          | 17.82                  | 6.52            |
| 5.4   | 13.72 | 39.50     | 16.20                   | 9.25                     | 8.44      | 0.89    | 30.15          | 17.86                  | 5.98            |
| 5.6   | 13.96 | 38.93     | 18.66                   | 9.76                     | 7.88      | 0.90    | 30.59          | 18.15                  | 5.60            |
| 5.8   | 14.15 | 38.57     | 20.99                   | 10.38                    | 7.55      | 0.91    | 31.46          | 17.78                  | 5.28            |
| 6.0   | 14.29 | 38.04     | 22.30                   | 10.85                    | 7.08      | 0.92    | 34.16          | 17.96                  | 5.06            |
| 6.2   | 14.40 | 37.74     | 22.08                   | 11.54                    | 6.84      | 0.93    | 30.07          | 17.91                  | 4.84            |
| 6.4   | 14.50 | 37.46     | 21.65                   | 11.97                    | 6.58      | 0.94    | 28.87          | 18.07                  | 4.69            |
| 6.6   | 14.57 | 37.19     | 21.24                   | 12.52                    | 6.38      | 0.94    | 29.02          | 18.07                  | 4.58            |
| 6.8   | 14.63 | 36.96     | 21.15                   | 13.45                    | 6.24      | 0.96    | 28.88          | 17.92                  | 4.47            |
| 7.0   | 14.69 | 36.89     | 21.97                   | 14.34                    | 6.21      | 0.96    | 29.38          | 17.58                  | 4.45            |
| 7.2   | 14.72 | 36.56     | 22.39                   | 15.65                    | 6.02      | 0.97    | 30.81          | 17.45                  | 4.31            |
| 7.4   | 14.75 | 36.53     | 24.94                   | 16.93                    | 6.03      | 0.98    | 29.25          | 17.80                  | 4.25            |
| 7.6   | 14.76 | 36.40     | 27.93                   | 19.10                    | 5.99      | 0.98    | 28.57          | 16.36                  | 4.20            |
| 7.8   | 14.75 | 36.35     | 33.77                   | 21.29                    | 6.01      | 0.99    | 28.25          | 17.82                  | 4.19            |
| 8.0   | 14.74 | 36.30     | 44.19                   | 25.61                    | 6.01      | 0.99    | 28.00          | 17.58                  | 4.19            |
| 8.2   | 14.69 | 36.39     | 33.39                   | 33.75                    | 6.12      | 0.99    | 27.87          | 17.81                  | 4.18            |
| 8.3   | 14.68 | 36.23     | 29.04                   | 41.01                    | 6.01      | 0.99    | 27.85          | 17.77                  | 4.19            |
| 8.4   | 14.63 | 36.56     | 25.86                   | 34.88                    | 6.26      | 1.00    | 28.06          | 17.76                  | 4.16            |
| 8.8   | 14.50 | 36.38     | 21.05                   | 21.53                    | 6.17      | 0.99    | 27.62          | 18.08                  | 4.24            |
| 8.9   | 14.46 | 36.28     | 20.21                   | 20.07                    | 6.10      | 0.99    | 27.48          | 17.64                  | 4.30            |
| 9.0   | 14.40 | 36.18     | 19.63                   | 18.58                    | 6.04      | 0.99    | 27.39          | 18.02                  | 4.31            |
| 9.1   | 14.36 | 36.30     | 18.94                   | 17.69                    | 6.13      | 0.99    | 27.62          | 18.01                  | 4.28            |
| 9.2   | 14.29 | 36.39     | 17.71                   | 16.70                    | 6.18      | 0.99    | 27.53          | 18.60                  | 4.29            |
| 9.3   | 14.24 | 36.37     | 17.03                   | 15.65                    | 6.15      | 0.98    | 27.64          | 17.95                  | 4.29            |
| 9.6   | 14.05 | 36.76     | 15.97                   | 14.41                    | 6.48      | 0.98    | 27.18          | 18.49                  | 4.42            |
| 9.7   | 13.99 | 36.75     | 15.28                   | 13.87                    | 6.47      | 0.98    | 27.20          | 18.89                  | 4.42            |
| 9.8   | 13.89 | 36.87     | 15.00                   | 13.31                    | 6.58      | 0.97    | 27.41          | 18.20                  | 4.43            |
| 9.9   | 13.90 | 36.74     | 15.13                   | 13.01                    | 6.46      | 0.97    | 27.04          | 18.51                  | 4.45            |
| 10.0  | 13.87 | 36.50     | 14.73                   | 12.80                    | 6.27      | 0.97    | 27.15          | 18.69                  | 4.44            |
| 10.5  | 13.59 | 36.78     | 13.13                   | 11.56                    | 6.48      | 0.96    | 26.88          | 19.10                  | 4.61            |
| 11.0  | 13.37 | 36.62     | 11.81                   | 10.88                    | 6.34      | 0.96    | 26.54          | 19.35                  | 4.75            |
| 11.5  | 13.18 | 36.52     | 10.96                   | 10.41                    | 6.25      | 0.97    | 26.03          | 19.05                  | 4.79            |
| 12.0  | 13.00 | 36.27     | 10.38                   | 10.02                    | 6.07      | 0.97    | 25.66          | 18.74                  | 4.91            |
| 12.5  | 12.89 | 36.15     | 9.93                    | 9.93                     | 5.99      | 0.97    | 25.38          | 19.15                  | 5.01            |
| 13.0  | 12.79 | 35.85     | 9.56                    | 9.77                     | 5.76      | 0.98    | 25.14          | 18.72                  | 5.17            |
| 13.5  | 12.76 | 35.20     | 9.77                    | 9.81                     | 5.39      | 0.98    | 25.11          | 19.45                  | 5.22            |
| 14.0  | 12.86 | 34.98     | 10.37                   | 10.15                    | 5.30      | 0.98    | 27.99          | 19.49                  | 5.25            |
| 14.5  | 13.04 | 34.39     | 11.70                   | 10.43                    | 4.99      | 0.96    | 25.06          | 19.49                  | 5.26            |
| 15.0  | 13.33 | 33.80     | 13.83                   | 11.39                    | 4.73      | 0.96    | 24.26          | 19.97                  | 5.35            |
| 15.5  | 13.54 | 33.05     | 16.50                   | 12.31                    | 4.39      | 0.95    | 26.16          | 20.00                  | 5.23            |
| 16.0  | 13.70 | 32.65     | 17.83                   | 13.31                    | 4.21      | 0.96    | 24.17          | 20.15                  | 5.26            |
| 16.5  | 13.75 | 32.25     | 16.28                   | 15.85                    | 4.07      | 0.98    | 24.06          | 20.21                  | 5.29            |
| 17.0  | 13.56 | 31.98     | 13.43                   | 14.68                    | 3.93      | 0.99    | 23.96          | 19.93                  | 5.33            |
| 17.5  | 13.15 | 31.97     | 10.79                   | 13.29                    | 3.93      | 1.01    | 23.19          | 18.80                  | 5.63            |
| 18.0  | 12.62 | 32.20     | 9.09                    | 11.54                    | 4.02      | 1.02    | 24.16          | 18.21                  | 5.93            |

*Typical Performance Data***Definitions:**

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 4.75V, Id = 131.25mA @ Temperature = 25degC

| FREQ  | Gain  | Isolation | Input<br>Return<br>Loss | Output<br>Return<br>Loss | Stability |         | IP-3<br>Output | 1dB<br>Comp.<br>Output | Noise<br>Figure |
|-------|-------|-----------|-------------------------|--------------------------|-----------|---------|----------------|------------------------|-----------------|
| (GHz) | (dB)  | (dB)      | (dB)                    | (dB)                     | K         | Measure | (dBm)          | (dBm)                  | (dB)            |
| 5.0   | 13.06 | 41.12     | 11.77                   | 7.80                     | 9.96      | 0.88    | 33.38          | 16.71                  | 7.17            |
| 5.2   | 13.50 | 40.11     | 13.84                   | 8.50                     | 8.90      | 0.89    | 30.58          | 17.35                  | 6.48            |
| 5.4   | 13.84 | 39.48     | 16.15                   | 9.30                     | 8.32      | 0.90    | 31.18          | 17.35                  | 5.96            |
| 5.6   | 14.08 | 38.90     | 18.57                   | 9.80                     | 7.76      | 0.90    | 32.19          | 17.62                  | 5.56            |
| 5.8   | 14.26 | 38.53     | 20.96                   | 10.44                    | 7.43      | 0.91    | 37.51          | 17.18                  | 5.26            |
| 6.0   | 14.41 | 38.01     | 22.27                   | 10.92                    | 6.97      | 0.92    | 30.91          | 17.39                  | 5.03            |
| 6.2   | 14.52 | 37.71     | 22.25                   | 11.61                    | 6.73      | 0.93    | 37.74          | 17.30                  | 4.81            |
| 6.4   | 14.62 | 37.46     | 21.75                   | 12.06                    | 6.51      | 0.94    | 29.88          | 17.44                  | 4.65            |
| 6.6   | 14.69 | 37.22     | 21.46                   | 12.61                    | 6.33      | 0.95    | 29.71          | 17.45                  | 4.55            |
| 6.8   | 14.74 | 36.92     | 21.29                   | 13.54                    | 6.14      | 0.96    | 29.94          | 17.29                  | 4.50            |
| 7.0   | 14.80 | 36.89     | 22.09                   | 14.43                    | 6.13      | 0.96    | 33.18          | 16.93                  | 4.51            |
| 7.2   | 14.84 | 36.57     | 22.45                   | 15.79                    | 5.95      | 0.97    | 34.06          | 16.83                  | 4.31            |
| 7.4   | 14.86 | 36.61     | 25.08                   | 17.05                    | 6.02      | 0.98    | 33.14          | 17.16                  | 4.23            |
| 7.6   | 14.88 | 36.38     | 27.88                   | 19.25                    | 5.91      | 0.98    | 30.98          | 16.71                  | 4.20            |
| 7.8   | 14.87 | 36.34     | 33.16                   | 21.44                    | 5.92      | 0.99    | 28.86          | 17.17                  | 4.17            |
| 8.0   | 14.86 | 36.32     | 49.36                   | 25.90                    | 5.94      | 0.99    | 28.52          | 16.94                  | 4.14            |
| 8.2   | 14.81 | 36.44     | 33.89                   | 34.64                    | 6.07      | 0.99    | 28.65          | 17.18                  | 4.17            |
| 8.3   | 14.80 | 36.28     | 29.25                   | 47.90                    | 5.96      | 0.99    | 28.75          | 17.13                  | 4.13            |
| 8.4   | 14.76 | 36.52     | 26.34                   | 35.06                    | 6.15      | 1.00    | 29.59          | 17.14                  | 4.11            |
| 8.8   | 14.63 | 36.37     | 21.28                   | 21.73                    | 6.07      | 0.99    | 28.74          | 17.43                  | 4.20            |
| 8.9   | 14.60 | 36.21     | 20.48                   | 20.15                    | 5.96      | 0.99    | 28.54          | 17.00                  | 4.24            |
| 9.0   | 14.52 | 36.25     | 19.86                   | 18.70                    | 6.01      | 0.99    | 28.03          | 17.36                  | 4.27            |
| 9.1   | 14.50 | 36.24     | 19.09                   | 17.76                    | 5.99      | 0.99    | 28.97          | 17.34                  | 4.26            |
| 9.2   | 14.43 | 36.33     | 17.92                   | 16.78                    | 6.05      | 0.99    | 27.85          | 17.94                  | 4.27            |
| 9.3   | 14.38 | 36.35     | 17.21                   | 15.73                    | 6.06      | 0.98    | 29.09          | 17.30                  | 4.25            |
| 9.6   | 14.20 | 36.65     | 16.08                   | 14.52                    | 6.31      | 0.98    | 27.96          | 17.83                  | 4.37            |
| 9.7   | 14.15 | 36.65     | 15.42                   | 13.94                    | 6.29      | 0.98    | 27.60          | 18.23                  | 4.38            |
| 9.8   | 14.03 | 36.92     | 15.14                   | 13.38                    | 6.52      | 0.97    | 28.81          | 17.53                  | 4.40            |
| 9.9   | 14.06 | 36.61     | 15.27                   | 13.05                    | 6.26      | 0.97    | 27.43          | 17.86                  | 4.40            |
| 10.0  | 14.03 | 36.46     | 14.86                   | 12.93                    | 6.15      | 0.97    | 28.08          | 18.04                  | 4.39            |
| 10.5  | 13.76 | 36.69     | 13.25                   | 11.69                    | 6.32      | 0.96    | 27.56          | 18.46                  | 4.54            |
| 11.0  | 13.55 | 36.62     | 11.95                   | 11.05                    | 6.24      | 0.97    | 26.98          | 18.38                  | 4.69            |
| 11.5  | 13.37 | 36.41     | 11.11                   | 10.50                    | 6.07      | 0.97    | 26.33          | 18.43                  | 4.82            |
| 12.0  | 13.20 | 36.18     | 10.49                   | 10.10                    | 5.91      | 0.97    | 25.88          | 18.11                  | 4.87            |
| 12.5  | 13.10 | 36.00     | 10.05                   | 10.01                    | 5.77      | 0.97    | 25.57          | 18.52                  | 4.94            |
| 13.0  | 13.02 | 35.78     | 9.69                    | 9.82                     | 5.60      | 0.98    | 25.32          | 18.07                  | 5.07            |
| 13.5  | 13.00 | 35.07     | 9.94                    | 9.88                     | 5.20      | 0.97    | 25.36          | 18.82                  | 5.11            |
| 14.0  | 13.11 | 34.96     | 10.51                   | 10.20                    | 5.17      | 0.97    | 27.12          | 18.87                  | 5.23            |
| 14.5  | 13.29 | 34.27     | 11.88                   | 10.49                    | 4.81      | 0.96    | 25.64          | 18.84                  | 5.24            |
| 15.0  | 13.58 | 33.62     | 14.06                   | 11.41                    | 4.52      | 0.96    | 25.07          | 19.37                  | 5.30            |
| 15.5  | 13.80 | 32.79     | 16.78                   | 12.31                    | 4.15      | 0.95    | 25.33          | 19.40                  | 5.21            |
| 16.0  | 13.96 | 32.65     | 18.15                   | 13.44                    | 4.10      | 0.96    | 24.69          | 19.58                  | 5.20            |
| 16.5  | 14.02 | 32.14     | 16.62                   | 16.19                    | 3.91      | 0.98    | 24.44          | 19.65                  | 5.27            |
| 17.0  | 13.84 | 31.94     | 13.64                   | 14.90                    | 3.81      | 0.99    | 24.04          | 19.63                  | 5.30            |
| 17.5  | 13.41 | 31.88     | 10.88                   | 13.27                    | 3.78      | 1.00    | 24.37          | 18.14                  | 5.59            |
| 18.0  | 12.86 | 32.15     | 9.14                    | 11.48                    | 3.90      | 1.01    | 25.06          | 17.54                  | 5.90            |

## Typical Performance Data

## Definitions:

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 5.25V, Id = 132.75mA @ Temperature = 25degC

| FREQ  | Gain  | Isolation | Input<br>Return<br>Loss | Output<br>Return<br>Loss | Stability |         | IP-3<br>Output | 1dB<br>Comp.<br>Output | Noise<br>Figure |
|-------|-------|-----------|-------------------------|--------------------------|-----------|---------|----------------|------------------------|-----------------|
| (GHz) | (dB)  | (dB)      | (dB)                    | (dB)                     | K         | Measure | (dBm)          | (dBm)                  | (dB)            |
| 5.0   | 12.80 | 41.17     | 11.80                   | 7.75                     | 10.30     | 0.88    | 29.67          | 17.64                  | 7.22            |
| 5.2   | 13.25 | 40.19     | 13.88                   | 8.44                     | 9.22      | 0.88    | 29.13          | 18.22                  | 6.54            |
| 5.4   | 13.60 | 39.54     | 16.23                   | 9.21                     | 8.59      | 0.89    | 29.60          | 18.29                  | 6.04            |
| 5.6   | 13.85 | 38.94     | 18.73                   | 9.72                     | 7.99      | 0.90    | 29.91          | 18.58                  | 5.63            |
| 5.8   | 14.04 | 38.57     | 21.00                   | 10.33                    | 7.64      | 0.91    | 29.44          | 18.29                  | 5.33            |
| 6.0   | 14.18 | 38.07     | 22.29                   | 10.80                    | 7.18      | 0.92    | 29.66          | 18.47                  | 5.10            |
| 6.2   | 14.29 | 37.74     | 21.99                   | 11.47                    | 6.91      | 0.93    | 28.52          | 18.44                  | 4.88            |
| 6.4   | 14.40 | 37.48     | 21.57                   | 11.89                    | 6.67      | 0.94    | 28.44          | 18.59                  | 4.72            |
| 6.6   | 14.47 | 37.19     | 21.09                   | 12.44                    | 6.44      | 0.94    | 28.69          | 18.62                  | 4.62            |
| 6.8   | 14.53 | 37.02     | 21.14                   | 13.37                    | 6.35      | 0.95    | 28.49          | 18.47                  | 4.50            |
| 7.0   | 14.59 | 36.88     | 21.91                   | 14.25                    | 6.27      | 0.96    | 28.23          | 18.14                  | 4.40            |
| 7.2   | 14.62 | 36.57     | 22.41                   | 15.57                    | 6.10      | 0.97    | 28.45          | 18.00                  | 4.37            |
| 7.4   | 14.64 | 36.50     | 24.98                   | 16.81                    | 6.09      | 0.98    | 27.91          | 18.36                  | 4.28            |
| 7.6   | 14.66 | 36.40     | 28.09                   | 18.97                    | 6.07      | 0.98    | 27.71          | 17.92                  | 4.22            |
| 7.8   | 14.65 | 36.34     | 34.37                   | 21.12                    | 6.07      | 0.99    | 28.06          | 18.38                  | 4.23            |
| 8.0   | 14.64 | 36.29     | 40.22                   | 25.29                    | 6.07      | 0.99    | 27.82          | 18.14                  | 4.18            |
| 8.2   | 14.58 | 36.43     | 32.75                   | 32.64                    | 6.23      | 0.99    | 27.60          | 18.39                  | 4.19            |
| 8.3   | 14.57 | 36.23     | 28.61                   | 37.16                    | 6.08      | 0.99    | 27.55          | 18.33                  | 4.25            |
| 8.4   | 14.52 | 36.57     | 25.53                   | 34.14                    | 6.35      | 1.00    | 27.51          | 18.35                  | 4.21            |
| 8.8   | 14.38 | 36.39     | 20.89                   | 21.41                    | 6.25      | 0.99    | 27.19          | 18.67                  | 4.25            |
| 8.9   | 14.34 | 36.29     | 19.98                   | 19.93                    | 6.19      | 0.99    | 27.10          | 18.25                  | 4.31            |
| 9.0   | 14.27 | 36.24     | 19.42                   | 18.52                    | 6.17      | 0.99    | 27.14          | 18.61                  | 4.34            |
| 9.1   | 14.23 | 36.37     | 18.73                   | 17.64                    | 6.25      | 0.99    | 27.08          | 18.61                  | 4.30            |
| 9.2   | 14.16 | 36.44     | 17.61                   | 16.67                    | 6.31      | 0.99    | 27.47          | 19.16                  | 4.34            |
| 9.3   | 14.11 | 36.39     | 16.91                   | 15.59                    | 6.26      | 0.98    | 26.99          | 18.54                  | 4.32            |
| 9.6   | 13.92 | 36.82     | 15.80                   | 14.34                    | 6.62      | 0.98    | 26.90          | 19.10                  | 4.44            |
| 9.7   | 13.85 | 36.77     | 15.16                   | 13.79                    | 6.57      | 0.98    | 27.09          | 19.47                  | 4.44            |
| 9.8   | 13.76 | 36.81     | 14.89                   | 13.19                    | 6.62      | 0.97    | 26.76          | 18.80                  | 4.43            |
| 9.9   | 13.76 | 36.79     | 14.96                   | 12.93                    | 6.58      | 0.97    | 26.94          | 19.11                  | 4.47            |
| 10.0  | 13.74 | 36.55     | 14.60                   | 12.71                    | 6.40      | 0.97    | 26.75          | 19.26                  | 4.48            |
| 10.5  | 13.44 | 36.88     | 13.02                   | 11.48                    | 6.64      | 0.96    | 26.63          | 19.65                  | 4.62            |
| 11.0  | 13.21 | 36.66     | 11.73                   | 10.79                    | 6.46      | 0.96    | 26.43          | 19.55                  | 4.72            |
| 11.5  | 13.00 | 36.55     | 10.85                   | 10.34                    | 6.37      | 0.97    | 25.98          | 19.58                  | 4.83            |
| 12.0  | 12.81 | 36.35     | 10.27                   | 9.93                     | 6.23      | 0.97    | 25.67          | 19.30                  | 4.94            |
| 12.5  | 12.69 | 36.23     | 9.78                    | 9.87                     | 6.14      | 0.98    | 25.34          | 19.69                  | 5.02            |
| 13.0  | 12.59 | 35.93     | 9.42                    | 9.72                     | 5.91      | 0.98    | 25.14          | 19.29                  | 5.18            |
| 13.5  | 12.55 | 35.26     | 9.67                    | 9.75                     | 5.54      | 0.98    | 25.06          | 19.94                  | 5.30            |
| 14.0  | 12.65 | 35.04     | 10.28                   | 10.10                    | 5.45      | 0.98    | 25.05          | 19.98                  | 5.29            |
| 14.5  | 12.82 | 34.50     | 11.58                   | 10.36                    | 5.17      | 0.96    | 25.22          | 19.97                  | 5.32            |
| 15.0  | 13.11 | 33.98     | 13.64                   | 11.28                    | 4.93      | 0.96    | 23.97          | 20.41                  | 5.38            |
| 15.5  | 13.32 | 33.22     | 16.23                   | 12.19                    | 4.58      | 0.95    | 25.52          | 20.46                  | 5.29            |
| 16.0  | 13.47 | 32.71     | 17.51                   | 13.13                    | 4.34      | 0.96    | 23.99          | 20.61                  | 5.31            |
| 16.5  | 13.51 | 32.31     | 16.05                   | 15.69                    | 4.20      | 0.98    | 24.10          | 20.65                  | 5.34            |
| 17.0  | 13.32 | 32.05     | 13.31                   | 14.72                    | 4.07      | 0.99    | 26.34          | 20.47                  | 5.40            |
| 17.5  | 12.92 | 32.04     | 10.71                   | 13.39                    | 4.05      | 1.01    | 22.91          | 19.38                  | 5.63            |
| 18.0  | 12.39 | 32.25     | 9.02                    | 11.62                    | 4.14      | 1.02    | 24.05          | 18.79                  | 5.97            |

## Typical Performance Data

## Definitions:

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 5.00V, Id = 126.94mA @ Temperature = -45degC

| FREQ  | Gain  | Isolation | Input<br>Return<br>Loss | Output<br>Return<br>Loss | Stability |         | IP-3<br>Output | 1dB<br>Comp.<br>Output | Noise<br>Figure |
|-------|-------|-----------|-------------------------|--------------------------|-----------|---------|----------------|------------------------|-----------------|
| (GHz) | (dB)  | (dB)      | (dB)                    | (dB)                     | K         | Measure | (dBm)          | (dBm)                  | (dB)            |
| 5.0   | 14.34 | 40.89     | 11.10                   | 7.50                     | 8.19      | 0.87    | 31.49          | 17.17                  | 6.20            |
| 5.2   | 14.74 | 39.99     | 13.00                   | 8.29                     | 7.51      | 0.88    | 32.40          | 17.73                  | 5.54            |
| 5.4   | 15.06 | 39.39     | 15.07                   | 9.14                     | 7.09      | 0.89    | 31.80          | 17.84                  | 5.04            |
| 5.6   | 15.28 | 38.82     | 17.47                   | 9.78                     | 6.67      | 0.90    | 31.17          | 18.09                  | 4.67            |
| 5.8   | 15.44 | 38.51     | 19.60                   | 10.34                    | 6.46      | 0.91    | 32.07          | 17.76                  | 4.35            |
| 6.0   | 15.57 | 38.00     | 21.32                   | 10.93                    | 6.09      | 0.92    | 32.51          | 17.98                  | 4.19            |
| 6.2   | 15.67 | 37.69     | 21.61                   | 11.51                    | 5.88      | 0.93    | 35.90          | 17.97                  | 3.94            |
| 6.4   | 15.78 | 37.48     | 21.78                   | 12.01                    | 5.72      | 0.93    | 34.66          | 18.11                  | 3.77            |
| 6.6   | 15.84 | 37.22     | 21.25                   | 12.64                    | 5.55      | 0.94    | 34.06          | 18.18                  | 3.70            |
| 6.8   | 15.90 | 36.94     | 21.49                   | 13.26                    | 5.39      | 0.95    | 34.38          | 18.00                  | 3.57            |
| 7.0   | 15.96 | 36.87     | 21.73                   | 14.40                    | 5.37      | 0.96    | 34.92          | 17.70                  | 3.49            |
| 7.2   | 16.00 | 36.58     | 22.33                   | 15.24                    | 5.22      | 0.97    | 35.85          | 17.61                  | 3.41            |
| 7.4   | 16.03 | 36.55     | 23.85                   | 16.85                    | 5.23      | 0.97    | 38.98          | 17.95                  | 3.39            |
| 7.6   | 16.06 | 36.44     | 26.18                   | 18.42                    | 5.19      | 0.98    | 39.82          | 17.41                  | 3.33            |
| 7.8   | 16.07 | 36.36     | 29.73                   | 20.90                    | 5.17      | 0.98    | 36.44          | 17.88                  | 3.32            |
| 8.0   | 16.07 | 36.35     | 34.06                   | 24.39                    | 5.19      | 0.99    | 35.88          | 17.63                  | 3.25            |
| 8.2   | 16.04 | 36.39     | 35.75                   | 29.89                    | 5.25      | 0.99    | 36.09          | 17.89                  | 3.27            |
| 8.3   | 16.04 | 36.16     | 34.25                   | 33.36                    | 5.12      | 0.99    | 38.38          | 17.81                  | 3.26            |
| 8.4   | 16.00 | 36.50     | 29.31                   | 31.11                    | 5.33      | 0.99    | 36.85          | 17.68                  | 3.25            |
| 8.8   | 15.89 | 36.47     | 23.35                   | 22.03                    | 5.34      | 0.99    | 38.02          | 17.95                  | 3.34            |
| 8.9   | 15.87 | 36.23     | 21.96                   | 20.51                    | 5.18      | 0.99    | 35.69          | 17.42                  | 3.36            |
| 9.0   | 15.81 | 36.20     | 21.00                   | 19.17                    | 5.18      | 0.99    | 36.26          | 18.01                  | 3.37            |
| 9.1   | 15.81 | 36.16     | 20.57                   | 18.13                    | 5.14      | 0.98    | 37.28          | 18.09                  | 3.34            |
| 9.2   | 15.73 | 36.17     | 19.25                   | 17.11                    | 5.15      | 0.98    | 35.74          | 18.58                  | 3.35            |
| 9.3   | 15.70 | 36.32     | 18.29                   | 16.30                    | 5.23      | 0.98    | 37.51          | 17.96                  | 3.38            |
| 9.6   | 15.55 | 36.53     | 17.01                   | 14.87                    | 5.38      | 0.97    | 36.49          | 18.39                  | 3.45            |
| 9.7   | 15.49 | 36.69     | 16.22                   | 14.51                    | 5.47      | 0.98    | 35.65          | 18.79                  | 3.44            |
| 9.8   | 15.42 | 36.64     | 15.56                   | 13.85                    | 5.44      | 0.97    | 36.01          | 18.25                  | 3.45            |
| 9.9   | 15.42 | 36.47     | 15.54                   | 13.37                    | 5.31      | 0.97    | 35.35          | 18.74                  | 3.51            |
| 10.0  | 15.42 | 36.36     | 15.44                   | 13.12                    | 5.23      | 0.96    | 36.47          | 18.87                  | 3.50            |
| 10.5  | 15.15 | 36.53     | 13.43                   | 11.82                    | 5.32      | 0.96    | 35.28          | 19.24                  | 3.61            |
| 11.0  | 15.04 | 36.47     | 12.04                   | 11.25                    | 5.23      | 0.96    | 33.78          | 18.97                  | 3.70            |
| 11.5  | 14.88 | 36.13     | 10.98                   | 10.51                    | 4.97      | 0.96    | 32.70          | 19.03                  | 3.74            |
| 12.0  | 14.77 | 36.02     | 10.29                   | 10.15                    | 4.86      | 0.96    | 31.75          | 18.65                  | 3.87            |
| 12.5  | 14.72 | 35.78     | 9.84                    | 10.04                    | 4.70      | 0.97    | 30.79          | 19.18                  | 3.94            |
| 13.0  | 14.70 | 35.51     | 9.59                    | 10.02                    | 4.53      | 0.98    | 30.35          | 18.64                  | 4.04            |
| 13.5  | 14.76 | 34.71     | 10.08                   | 10.01                    | 4.15      | 0.96    | 30.15          | 19.36                  | 4.10            |
| 14.0  | 14.88 | 34.50     | 11.22                   | 10.15                    | 4.09      | 0.95    | 30.12          | 19.38                  | 4.13            |
| 14.5  | 15.10 | 33.90     | 13.00                   | 10.30                    | 3.83      | 0.93    | 29.52          | 19.30                  | 4.18            |
| 15.0  | 15.42 | 33.27     | 15.43                   | 11.05                    | 3.56      | 0.93    | 28.43          | 20.01                  | 4.24            |
| 15.5  | 15.66 | 32.48     | 19.32                   | 11.69                    | 3.26      | 0.92    | 28.50          | 20.07                  | 4.13            |
| 16.0  | 15.93 | 31.86     | 21.69                   | 13.19                    | 3.05      | 0.93    | 27.90          | 20.08                  | 4.08            |
| 16.5  | 16.06 | 31.54     | 19.20                   | 14.22                    | 2.92      | 0.94    | 27.76          | 20.33                  | 4.17            |
| 17.0  | 16.01 | 31.20     | 15.37                   | 13.16                    | 2.78      | 0.94    | 26.95          | 19.43                  | 4.23            |
| 17.5  | 15.69 | 31.14     | 11.90                   | 11.76                    | 2.73      | 0.94    | 27.01          | 18.70                  | 4.36            |
| 18.0  | 15.19 | 31.39     | 9.22                    | 9.74                     | 2.72      | 0.95    | 26.95          | 18.28                  | 4.71            |

## Typical Performance Data

### Definitions:

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 4.75V, Id = 124.70mA @ Temperature = -45degC

| FREQ  | Gain  | Isolation | Input Return Loss | Output Return Loss | Stability |         | IP-3 Output | 1dB Comp. Output | Noise Figure |
|-------|-------|-----------|-------------------|--------------------|-----------|---------|-------------|------------------|--------------|
| (GHz) | (dB)  | (dB)      | (dB)              | (dB)               | K         | Measure | (dBm)       | (dBm)            | (dB)         |
| 5.0   | 14.98 | 40.85     | 10.87             | 7.48               | 7.55      | 0.88    | 28.20       | 16.25            | 6.16         |
| 5.2   | 15.36 | 39.97     | 12.66             | 8.27               | 6.95      | 0.88    | 29.12       | 16.89            | 5.49         |
| 5.4   | 15.66 | 39.39     | 14.65             | 9.13               | 6.60      | 0.90    | 28.86       | 16.95            | 4.99         |
| 5.6   | 15.87 | 38.84     | 16.90             | 9.76               | 6.24      | 0.90    | 28.46       | 17.21            | 4.63         |
| 5.8   | 16.02 | 38.57     | 18.97             | 10.35              | 6.08      | 0.91    | 28.33       | 16.80            | 4.31         |
| 6.0   | 16.15 | 38.06     | 20.69             | 10.91              | 5.74      | 0.92    | 28.08       | 17.02            | 4.13         |
| 6.2   | 16.25 | 37.75     | 21.28             | 11.52              | 5.55      | 0.93    | 29.94       | 16.99            | 3.90         |
| 6.4   | 16.35 | 37.58     | 21.51             | 12.01              | 5.42      | 0.93    | 30.04       | 17.13            | 3.75         |
| 6.6   | 16.42 | 37.30     | 21.14             | 12.62              | 5.25      | 0.94    | 29.75       | 17.18            | 3.63         |
| 6.8   | 16.47 | 37.05     | 21.19             | 13.25              | 5.11      | 0.95    | 29.82       | 17.04            | 3.55         |
| 7.0   | 16.54 | 36.94     | 21.46             | 14.33              | 5.07      | 0.96    | 29.55       | 16.71            | 3.43         |
| 7.2   | 16.57 | 36.68     | 21.69             | 15.18              | 4.94      | 0.96    | 29.09       | 16.62            | 3.42         |
| 7.4   | 16.61 | 36.63     | 22.86             | 16.67              | 4.94      | 0.97    | 30.09       | 17.02            | 3.32         |
| 7.6   | 16.64 | 36.50     | 24.42             | 18.28              | 4.89      | 0.98    | 30.49       | 16.49            | 3.30         |
| 7.8   | 16.65 | 36.48     | 26.61             | 20.51              | 4.91      | 0.98    | 30.33       | 16.94            | 3.25         |
| 8.0   | 16.66 | 36.39     | 28.40             | 23.93              | 4.88      | 0.99    | 30.21       | 16.67            | 3.26         |
| 8.2   | 16.63 | 36.46     | 29.53             | 28.62              | 4.94      | 0.99    | 30.39       | 16.89            | 3.24         |
| 8.3   | 16.64 | 36.20     | 29.78             | 31.90              | 4.80      | 0.99    | 30.43       | 16.82            | 3.22         |
| 8.4   | 16.61 | 36.55     | 27.65             | 30.74              | 5.00      | 0.99    | 30.70       | 16.70            | 3.20         |
| 8.8   | 16.50 | 36.56     | 23.16             | 22.52              | 5.03      | 0.99    | 30.34       | 16.88            | 3.25         |
| 8.9   | 16.50 | 36.22     | 22.29             | 20.84              | 4.83      | 0.99    | 30.86       | 16.39            | 3.31         |
| 9.0   | 16.44 | 36.26     | 21.54             | 19.40              | 4.86      | 0.98    | 30.13       | 16.88            | 3.35         |
| 9.1   | 16.43 | 36.19     | 20.96             | 18.45              | 4.81      | 0.98    | 30.78       | 17.01            | 3.31         |
| 9.2   | 16.36 | 36.26     | 19.50             | 17.22              | 4.85      | 0.98    | 30.55       | 17.50            | 3.33         |
| 9.3   | 16.34 | 36.29     | 18.69             | 16.47              | 4.86      | 0.98    | 30.69       | 16.88            | 3.32         |
| 9.6   | 16.19 | 36.51     | 17.40             | 15.09              | 5.00      | 0.97    | 31.10       | 17.28            | 3.41         |
| 9.7   | 16.13 | 36.65     | 16.59             | 14.68              | 5.08      | 0.97    | 30.50       | 17.65            | 3.44         |
| 9.8   | 16.08 | 36.66     | 16.00             | 14.01              | 5.08      | 0.97    | 30.34       | 17.18            | 3.44         |
| 9.9   | 16.08 | 36.46     | 15.96             | 13.51              | 4.94      | 0.96    | 30.44       | 17.71            | 3.45         |
| 10.0  | 16.07 | 36.31     | 15.89             | 13.28              | 4.85      | 0.96    | 30.50       | 17.86            | 3.43         |
| 10.5  | 15.83 | 36.49     | 13.76             | 11.98              | 4.93      | 0.96    | 30.76       | 18.26            | 3.57         |
| 11.0  | 15.74 | 36.37     | 12.42             | 11.34              | 4.81      | 0.96    | 31.59       | 17.97            | 3.66         |
| 11.5  | 15.60 | 36.04     | 11.37             | 10.56              | 4.58      | 0.95    | 30.91       | 18.01            | 3.72         |
| 12.0  | 15.53 | 35.92     | 10.72             | 10.17              | 4.46      | 0.95    | 30.62       | 17.64            | 3.83         |
| 12.5  | 15.51 | 35.59     | 10.30             | 10.04              | 4.26      | 0.96    | 29.42       | 18.14            | 3.89         |
| 13.0  | 15.52 | 35.31     | 10.12             | 9.95               | 4.10      | 0.96    | 29.79       | 17.58            | 4.00         |
| 13.5  | 15.60 | 34.51     | 10.79             | 9.94               | 3.76      | 0.94    | 29.91       | 18.17            | 4.06         |
| 14.0  | 15.73 | 34.16     | 12.14             | 10.11              | 3.65      | 0.93    | 30.26       | 18.17            | 4.05         |
| 14.5  | 15.97 | 33.79     | 14.36             | 10.17              | 3.47      | 0.91    | 30.05       | 17.98            | 4.10         |
| 15.0  | 16.31 | 33.05     | 17.57             | 10.88              | 3.18      | 0.91    | 29.88       | 18.61            | 4.17         |
| 15.5  | 16.59 | 32.21     | 23.45             | 11.47              | 2.88      | 0.91    | 30.66       | 18.72            | 4.12         |
| 16.0  | 16.92 | 31.63     | 28.99             | 12.80              | 2.67      | 0.91    | 30.51       | 18.64            | 4.06         |
| 16.5  | 17.13 | 31.20     | 24.16             | 13.75              | 2.52      | 0.92    | 30.56       | 18.81            | 4.12         |
| 17.0  | 17.16 | 30.77     | 18.52             | 12.53              | 2.36      | 0.90    | 30.37       | 17.82            | 4.10         |
| 17.5  | 16.93 | 30.70     | 13.94             | 11.02              | 2.31      | 0.89    | 30.78       | 17.22            | 4.34         |
| 18.0  | 16.48 | 30.92     | 10.49             | 9.00               | 2.29      | 0.88    | 31.00       | 16.97            | 4.61         |

## Typical Performance Data

## Definitions:

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 5.25V, Id = 128.59mA @ Temperature = -45degC

| FREQ  | Gain  | Isolation | Input<br>Return<br>Loss | Output<br>Return<br>Loss | Stability |         | IP-3<br>Output | 1dB<br>Comp.<br>Output | Noise<br>Figure |
|-------|-------|-----------|-------------------------|--------------------------|-----------|---------|----------------|------------------------|-----------------|
| (GHz) | (dB)  | (dB)      | (dB)                    | (dB)                     | K         | Measure | (dBm)          | (dBm)                  | (dB)            |
| 5.0   | 13.97 | 40.93     | 11.22                   | 7.48                     | 8.60      | 0.87    | 40.30          | 17.72                  | 6.22            |
| 5.2   | 14.38 | 39.95     | 13.16                   | 8.29                     | 7.80      | 0.88    | 39.05          | 18.23                  | 5.59            |
| 5.4   | 14.70 | 39.38     | 15.31                   | 9.12                     | 7.38      | 0.89    | 40.26          | 18.38                  | 5.05            |
| 5.6   | 14.93 | 38.84     | 17.76                   | 9.76                     | 6.97      | 0.90    | 37.28          | 18.65                  | 4.68            |
| 5.8   | 15.09 | 38.50     | 19.95                   | 10.31                    | 6.71      | 0.91    | 37.69          | 18.42                  | 4.37            |
| 6.0   | 15.23 | 38.00     | 21.60                   | 10.90                    | 6.33      | 0.92    | 36.72          | 18.62                  | 4.19            |
| 6.2   | 15.33 | 37.69     | 21.74                   | 11.49                    | 6.10      | 0.93    | 33.92          | 18.64                  | 3.94            |
| 6.4   | 15.44 | 37.48     | 21.87                   | 11.98                    | 5.94      | 0.93    | 35.60          | 18.81                  | 3.80            |
| 6.6   | 15.51 | 37.21     | 21.15                   | 12.62                    | 5.76      | 0.94    | 36.94          | 18.88                  | 3.69            |
| 6.8   | 15.56 | 36.92     | 21.56                   | 13.24                    | 5.58      | 0.95    | 35.10          | 18.70                  | 3.63            |
| 7.0   | 15.63 | 36.83     | 21.79                   | 14.39                    | 5.55      | 0.96    | 33.32          | 17.32                  | 3.50            |
| 7.2   | 15.66 | 36.54     | 22.58                   | 15.21                    | 5.40      | 0.97    | 32.74          | 18.34                  | 3.44            |
| 7.4   | 15.69 | 36.51     | 24.24                   | 16.88                    | 5.41      | 0.97    | 32.22          | 18.67                  | 3.41            |
| 7.6   | 15.72 | 36.40     | 27.11                   | 18.42                    | 5.37      | 0.98    | 32.34          | 18.13                  | 3.33            |
| 7.8   | 15.73 | 36.30     | 31.54                   | 21.02                    | 5.34      | 0.98    | 33.92          | 18.59                  | 3.30            |
| 8.0   | 15.73 | 36.31     | 40.14                   | 24.58                    | 5.37      | 0.99    | 33.01          | 17.40                  | 3.31            |
| 8.2   | 15.68 | 36.39     | 38.83                   | 30.85                    | 5.47      | 0.99    | 32.29          | 18.62                  | 3.30            |
| 8.3   | 15.69 | 36.16     | 34.92                   | 35.32                    | 5.32      | 0.99    | 32.68          | 18.58                  | 3.33            |
| 8.4   | 15.65 | 36.48     | 29.15                   | 32.03                    | 5.53      | 0.99    | 31.39          | 18.43                  | 3.31            |
| 8.8   | 15.52 | 36.51     | 22.86                   | 21.99                    | 5.59      | 0.99    | 31.93          | 18.73                  | 3.36            |
| 8.9   | 15.51 | 36.24     | 21.43                   | 20.41                    | 5.40      | 0.99    | 30.67          | 18.21                  | 3.39            |
| 9.0   | 15.45 | 36.20     | 20.56                   | 19.05                    | 5.39      | 0.99    | 32.15          | 18.80                  | 3.40            |
| 9.1   | 15.44 | 36.19     | 20.19                   | 18.00                    | 5.37      | 0.98    | 30.91          | 18.87                  | 3.38            |
| 9.2   | 15.38 | 36.17     | 18.98                   | 16.99                    | 5.36      | 0.98    | 32.04          | 19.33                  | 3.37            |
| 9.3   | 15.33 | 36.33     | 17.92                   | 16.23                    | 5.45      | 0.98    | 30.71          | 18.74                  | 3.38            |
| 9.6   | 15.16 | 36.52     | 16.69                   | 14.74                    | 5.60      | 0.98    | 30.74          | 19.17                  | 3.50            |
| 9.7   | 15.09 | 36.66     | 15.84                   | 14.43                    | 5.70      | 0.98    | 31.55          | 19.54                  | 3.52            |
| 9.8   | 15.05 | 36.64     | 15.32                   | 13.76                    | 5.66      | 0.97    | 30.13          | 19.02                  | 3.47            |
| 9.9   | 15.03 | 36.52     | 15.21                   | 13.27                    | 5.56      | 0.97    | 31.39          | 19.48                  | 3.50            |
| 10.0  | 15.03 | 36.42     | 15.18                   | 13.01                    | 5.49      | 0.97    | 30.98          | 19.60                  | 3.49            |
| 10.5  | 14.74 | 36.54     | 13.16                   | 11.71                    | 5.56      | 0.96    | 30.69          | 19.90                  | 3.67            |
| 11.0  | 14.61 | 36.54     | 11.76                   | 11.16                    | 5.50      | 0.97    | 29.80          | 19.67                  | 3.76            |
| 11.5  | 14.44 | 36.21     | 10.73                   | 10.44                    | 5.23      | 0.97    | 29.45          | 19.72                  | 3.80            |
| 12.0  | 14.31 | 36.11     | 10.01                   | 10.11                    | 5.13      | 0.97    | 29.02          | 19.41                  | 3.94            |
| 12.5  | 14.24 | 35.84     | 9.56                    | 10.02                    | 4.95      | 0.98    | 28.81          | 20.16                  | 3.97            |
| 13.0  | 14.20 | 35.62     | 9.27                    | 10.02                    | 4.80      | 0.99    | 28.23          | 19.42                  | 4.15            |
| 13.5  | 14.25 | 34.84     | 9.71                    | 10.02                    | 4.42      | 0.98    | 28.05          | 20.12                  | 4.17            |
| 14.0  | 14.35 | 34.60     | 10.74                   | 10.17                    | 4.35      | 0.96    | 27.75          | 20.14                  | 4.13            |
| 14.5  | 14.56 | 34.02     | 12.38                   | 10.31                    | 4.08      | 0.94    | 28.66          | 20.11                  | 4.25            |
| 15.0  | 14.86 | 33.49     | 14.54                   | 11.08                    | 3.86      | 0.94    | 27.74          | 20.68                  | 4.30            |
| 15.5  | 15.08 | 32.54     | 17.88                   | 11.72                    | 3.49      | 0.93    | 26.47          | 20.97                  | 4.22            |
| 16.0  | 15.33 | 32.11     | 19.37                   | 13.31                    | 3.33      | 0.94    | 25.94          | 20.83                  | 4.16            |
| 16.5  | 15.42 | 31.78     | 17.27                   | 14.37                    | 3.20      | 0.95    | 26.68          | 21.20                  | 4.22            |
| 17.0  | 15.32 | 31.42     | 14.06                   | 13.43                    | 3.04      | 0.96    | 25.09          | 20.34                  | 4.27            |
| 17.5  | 14.98 | 31.39     | 11.08                   | 12.15                    | 3.01      | 0.97    | 24.98          | 19.50                  | 4.50            |
| 18.0  | 14.46 | 31.62     | 8.67                    | 10.12                    | 2.98      | 0.98    | 24.97          | 19.02                  | 4.77            |

## Typical Performance Data

## Definitions:

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 5.00V, Id = 132.70mA @ Temperature = 85degC

| FREQ  | Gain  | Isolation | Input<br>Return<br>Loss | Output<br>Return<br>Loss | Stability |         | IP-3<br>Output | 1dB<br>Comp.<br>Output | Noise<br>Figure |
|-------|-------|-----------|-------------------------|--------------------------|-----------|---------|----------------|------------------------|-----------------|
| (GHz) | (dB)  | (dB)      | (dB)                    | (dB)                     | K         | Measure | (dBm)          | (dBm)                  | (dB)            |
| 5.0   | 12.16 | 41.14     | 12.16                   | 7.93                     | 11.19     | 0.88    | 39.08          | 16.96                  | 8.05            |
| 5.2   | 12.60 | 40.27     | 14.22                   | 8.54                     | 10.09     | 0.89    | 30.45          | 17.56                  | 7.37            |
| 5.4   | 12.97 | 39.51     | 16.56                   | 9.31                     | 9.24      | 0.90    | 31.00          | 17.60                  | 6.82            |
| 5.6   | 13.22 | 38.98     | 18.71                   | 9.70                     | 8.61      | 0.90    | 31.76          | 17.86                  | 6.46            |
| 5.8   | 13.43 | 38.47     | 21.15                   | 10.38                    | 8.10      | 0.91    | 33.95          | 17.53                  | 6.08            |
| 6.0   | 13.58 | 38.01     | 22.16                   | 10.81                    | 7.64      | 0.92    | 52.90          | 17.71                  | 5.87            |
| 6.2   | 13.70 | 37.72     | 22.14                   | 11.63                    | 7.39      | 0.93    | 32.24          | 17.64                  | 5.64            |
| 6.4   | 13.80 | 37.38     | 21.25                   | 11.99                    | 7.06      | 0.94    | 29.73          | 17.80                  | 5.49            |
| 6.6   | 13.87 | 37.06     | 21.40                   | 12.58                    | 6.81      | 0.95    | 29.74          | 17.82                  | 5.37            |
| 6.8   | 13.95 | 36.95     | 21.02                   | 13.73                    | 6.75      | 0.96    | 29.70          | 17.68                  | 5.29            |
| 7.0   | 13.99 | 36.76     | 22.11                   | 14.49                    | 6.63      | 0.96    | 30.44          | 17.39                  | 5.70            |
| 7.2   | 14.02 | 36.45     | 22.64                   | 16.18                    | 6.46      | 0.97    | 32.56          | 17.26                  | 5.10            |
| 7.4   | 14.03 | 36.42     | 25.55                   | 17.24                    | 6.48      | 0.98    | 30.75          | 17.58                  | 5.10            |
| 7.6   | 14.04 | 36.29     | 29.03                   | 19.73                    | 6.44      | 0.98    | 29.85          | 17.20                  | 5.02            |
| 7.8   | 14.03 | 36.21     | 36.88                   | 21.93                    | 6.43      | 0.99    | 28.97          | 17.65                  | 5.00            |
| 8.0   | 13.99 | 36.22     | 35.34                   | 26.00                    | 6.48      | 0.99    | 28.68          | 17.44                  | 4.99            |
| 8.2   | 13.93 | 36.42     | 30.38                   | 31.34                    | 6.69      | 0.99    | 28.56          | 17.66                  | 5.01            |
| 8.3   | 13.92 | 36.23     | 27.38                   | 32.16                    | 6.55      | 1.00    | 28.62          | 17.61                  | 5.04            |
| 8.4   | 13.88 | 36.33     | 24.10                   | 28.58                    | 6.64      | 1.00    | 28.80          | 17.69                  | 5.01            |
| 8.8   | 13.71 | 36.42     | 20.58                   | 20.57                    | 6.75      | 0.99    | 28.40          | 17.98                  | 5.08            |
| 8.9   | 13.66 | 36.19     | 19.40                   | 18.84                    | 6.58      | 0.99    | 28.14          | 17.59                  | 5.12            |
| 9.0   | 13.59 | 36.28     | 19.11                   | 17.58                    | 6.66      | 0.99    | 28.04          | 17.84                  | 5.19            |
| 9.1   | 13.54 | 36.34     | 18.46                   | 16.73                    | 6.71      | 0.98    | 28.32          | 17.77                  | 5.11            |
| 9.2   | 13.47 | 36.55     | 17.54                   | 16.08                    | 6.88      | 0.98    | 28.07          | 18.36                  | 5.15            |
| 9.3   | 13.42 | 36.43     | 16.79                   | 14.97                    | 6.77      | 0.98    | 28.35          | 17.80                  | 5.17            |
| 9.6   | 13.24 | 36.60     | 15.95                   | 13.75                    | 6.94      | 0.97    | 27.81          | 18.32                  | 5.31            |
| 9.7   | 13.16 | 36.74     | 15.27                   | 13.34                    | 7.05      | 0.97    | 27.76          | 18.72                  | 5.30            |
| 9.8   | 13.10 | 36.77     | 15.26                   | 12.67                    | 7.08      | 0.96    | 28.02          | 18.04                  | 5.31            |
| 9.9   | 13.07 | 36.77     | 15.41                   | 12.44                    | 7.08      | 0.96    | 27.59          | 18.26                  | 5.34            |
| 10.0  | 13.04 | 36.60     | 14.97                   | 12.46                    | 6.95      | 0.96    | 27.82          | 18.36                  | 5.30            |
| 10.5  | 12.72 | 36.70     | 13.39                   | 11.22                    | 7.06      | 0.96    | 27.50          | 18.79                  | 5.50            |
| 11.0  | 12.47 | 36.73     | 12.23                   | 10.79                    | 7.13      | 0.96    | 27.11          | 18.77                  | 5.63            |
| 11.5  | 12.25 | 36.62     | 11.47                   | 10.46                    | 7.08      | 0.96    | 26.56          | 18.76                  | 5.76            |
| 12.0  | 12.05 | 36.49     | 10.86                   | 10.04                    | 6.99      | 0.96    | 26.16          | 18.51                  | 5.85            |
| 12.5  | 11.89 | 36.25     | 10.33                   | 10.01                    | 6.84      | 0.97    | 25.83          | 18.82                  | 5.99            |
| 13.0  | 11.75 | 36.20     | 9.92                    | 9.69                     | 6.78      | 0.97    | 25.60          | 18.51                  | 6.09            |
| 13.5  | 11.71 | 35.54     | 10.03                   | 9.79                     | 6.33      | 0.97    | 25.64          | 19.03                  | 6.19            |
| 14.0  | 11.79 | 35.06     | 10.46                   | 10.33                    | 6.06      | 0.98    | 24.80          | 19.10                  | 6.26            |
| 14.5  | 11.97 | 34.77     | 11.55                   | 10.54                    | 5.88      | 0.97    | 25.09          | 19.01                  | 6.28            |
| 15.0  | 12.25 | 34.11     | 13.39                   | 11.42                    | 5.51      | 0.97    | 25.40          | 19.35                  | 6.35            |
| 15.5  | 12.45 | 33.37     | 15.62                   | 12.30                    | 5.12      | 0.96    | 24.82          | 19.34                  | 6.31            |
| 16.0  | 12.56 | 33.09     | 17.23                   | 12.48                    | 4.96      | 0.95    | 25.30          | 19.54                  | 6.23            |
| 16.5  | 12.62 | 32.60     | 16.15                   | 16.04                    | 4.80      | 0.99    | 24.08          | 19.48                  | 6.32            |
| 17.0  | 12.41 | 32.37     | 13.68                   | 15.85                    | 4.72      | 1.00    | 23.76          | 19.44                  | 6.37            |
| 17.5  | 11.93 | 32.39     | 11.09                   | 14.85                    | 4.79      | 1.03    | 24.56          | 18.33                  | 6.66            |
| 18.0  | 11.38 | 32.70     | 9.68                    | 13.61                    | 5.07      | 1.04    | 25.81          | 17.74                  | 6.97            |

## Typical Performance Data

## Definitions:

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 4.75V, Id = 132.35mA @ Temperature = 85degC

| FREQ  | Gain  | Isolation | Input Return Loss | Output Return Loss | Stability |         | IP-3 Output | 1dB Comp. Output | Noise Figure |
|-------|-------|-----------|-------------------|--------------------|-----------|---------|-------------|------------------|--------------|
| (GHz) | (dB)  | (dB)      | (dB)              | (dB)               | K         | Measure | (dBm)       | (dBm)            | (dB)         |
| 5.0   | 12.30 | 40.91     | 12.16             | 7.97               | 10.74     | 0.88    | 31.09       | 16.46            | 8.00         |
| 5.2   | 12.74 | 40.11     | 14.22             | 8.63               | 9.79      | 0.89    | 31.26       | 17.09            | 7.32         |
| 5.4   | 13.10 | 39.32     | 16.48             | 9.38               | 8.92      | 0.90    | 31.79       | 17.09            | 6.78         |
| 5.6   | 13.36 | 38.75     | 18.73             | 9.87               | 8.29      | 0.90    | 33.34       | 17.37            | 6.36         |
| 5.8   | 13.55 | 38.32     | 20.99             | 10.49              | 7.88      | 0.91    | 34.86       | 16.95            | 6.07         |
| 6.0   | 13.70 | 37.86     | 22.23             | 11.03              | 7.43      | 0.92    | 29.67       | 17.14            | 5.84         |
| 6.2   | 13.82 | 37.56     | 22.19             | 11.78              | 7.18      | 0.93    | 36.26       | 17.07            | 5.61         |
| 6.4   | 13.92 | 37.23     | 21.69             | 12.22              | 6.87      | 0.94    | 30.90       | 17.22            | 5.40         |
| 6.6   | 13.99 | 36.95     | 21.72             | 12.86              | 6.66      | 0.95    | 30.41       | 17.25            | 5.32         |
| 6.8   | 14.07 | 36.92     | 21.61             | 14.02              | 6.66      | 0.96    | 30.70       | 17.07            | 5.20         |
| 7.0   | 14.11 | 36.68     | 22.48             | 14.89              | 6.51      | 0.97    | 34.56       | 16.79            | 5.12         |
| 7.2   | 14.14 | 36.46     | 23.35             | 16.53              | 6.40      | 0.98    | 32.59       | 16.65            | 5.09         |
| 7.4   | 14.15 | 36.37     | 26.04             | 17.91              | 6.38      | 0.98    | 33.60       | 16.99            | 5.01         |
| 7.6   | 14.16 | 36.23     | 29.78             | 20.32              | 6.32      | 0.99    | 32.47       | 16.59            | 4.95         |
| 7.8   | 14.15 | 36.05     | 37.53             | 23.17              | 6.23      | 0.99    | 29.59       | 17.07            | 4.96         |
| 8.0   | 14.12 | 36.24     | 37.23             | 28.13              | 6.41      | 0.99    | 29.22       | 16.84            | 4.92         |
| 8.2   | 14.07 | 36.29     | 30.35             | 41.19              | 6.49      | 0.99    | 29.33       | 17.05            | 4.94         |
| 8.3   | 14.07 | 36.09     | 27.63             | 36.35              | 6.34      | 1.00    | 29.60       | 17.02            | 4.99         |
| 8.4   | 14.05 | 35.91     | 25.03             | 28.82              | 6.21      | 0.99    | 30.21       | 17.06            | 4.95         |
| 8.8   | 13.88 | 36.17     | 20.83             | 20.23              | 6.43      | 0.99    | 29.61       | 17.32            | 4.99         |
| 8.9   | 13.84 | 36.08     | 19.87             | 18.96              | 6.37      | 0.99    | 29.21       | 16.93            | 5.05         |
| 9.0   | 13.77 | 36.19     | 19.44             | 17.74              | 6.47      | 0.99    | 28.81       | 17.18            | 5.12         |
| 9.1   | 13.72 | 36.26     | 18.73             | 16.72              | 6.52      | 0.98    | 29.68       | 17.13            | 5.06         |
| 9.2   | 13.67 | 36.32     | 17.96             | 15.94              | 6.56      | 0.98    | 28.44       | 17.72            | 5.09         |
| 9.3   | 13.62 | 36.18     | 17.22             | 14.95              | 6.44      | 0.98    | 29.86       | 17.14            | 5.07         |
| 9.6   | 13.46 | 36.34     | 16.31             | 13.73              | 6.58      | 0.97    | 28.67       | 17.66            | 5.22         |
| 9.7   | 13.37 | 36.44     | 15.59             | 13.33              | 6.67      | 0.97    | 28.26       | 18.03            | 5.20         |
| 9.8   | 13.34 | 36.37     | 15.52             | 12.81              | 6.60      | 0.96    | 29.44       | 17.34            | 5.25         |
| 9.9   | 13.30 | 36.50     | 15.55             | 12.66              | 6.71      | 0.96    | 28.09       | 17.58            | 5.26         |
| 10.0  | 13.27 | 36.51     | 15.29             | 12.59              | 6.73      | 0.96    | 28.87       | 17.71            | 5.25         |
| 10.5  | 13.00 | 36.46     | 13.80             | 11.21              | 6.68      | 0.95    | 28.28       | 18.12            | 5.41         |
| 11.0  | 12.79 | 36.51     | 12.61             | 10.80              | 6.75      | 0.95    | 27.70       | 18.13            | 5.55         |
| 11.5  | 12.61 | 36.34     | 11.74             | 10.51              | 6.63      | 0.96    | 26.99       | 18.10            | 5.63         |
| 12.0  | 12.42 | 36.19     | 10.98             | 10.20              | 6.52      | 0.96    | 26.51       | 17.86            | 5.78         |
| 12.5  | 12.29 | 36.01     | 10.40             | 10.18              | 6.40      | 0.97    | 26.12       | 18.16            | 5.86         |
| 13.0  | 12.18 | 35.81     | 9.95              | 9.93               | 6.23      | 0.98    | 25.90       | 17.83            | 6.06         |
| 13.5  | 12.18 | 35.23     | 10.12             | 10.05              | 5.85      | 0.98    | 25.99       | 18.39            | 6.09         |
| 14.0  | 12.29 | 34.98     | 10.52             | 10.56              | 5.72      | 0.98    | 25.12       | 18.44            | 6.14         |
| 14.5  | 12.47 | 34.31     | 11.60             | 10.94              | 5.32      | 0.98    | 25.98       | 18.31            | 6.18         |
| 15.0  | 12.77 | 33.61     | 13.29             | 12.16              | 4.96      | 0.98    | 25.99       | 18.70            | 6.27         |
| 15.5  | 12.97 | 33.05     | 15.27             | 13.13              | 4.69      | 0.97    | 26.38       | 18.68            | 6.20         |
| 16.0  | 13.09 | 32.64     | 16.99             | 13.40              | 4.49      | 0.96    | 25.65       | 18.92            | 6.14         |
| 16.5  | 13.09 | 32.54     | 16.38             | 16.32              | 4.54      | 0.99    | 24.46       | 18.86            | 6.18         |
| 17.0  | 12.82 | 32.25     | 14.01             | 14.73              | 4.43      | 0.99    | 23.96       | 18.75            | 6.26         |
| 17.5  | 12.28 | 32.36     | 11.04             | 14.16              | 4.56      | 1.02    | 25.22       | 17.66            | 6.53         |
| 18.0  | 11.61 | 32.73     | 9.41              | 13.02              | 4.89      | 1.04    | 26.41       | 17.33            | 6.87         |

## Typical Performance Data

## Definitions:

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)









Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)








TEST CONDITIONS: Vd = 5.25V, Id = 133.22mA @ Temperature = 85degC

| FREQ  | Gain  | Isolation | Input<br>Return<br>Loss | Output<br>Return<br>Loss | Stability |         | IP-3<br>Output | 1dB<br>Comp.<br>Output | Noise<br>Figure |
|-------|-------|-----------|-------------------------|--------------------------|-----------|---------|----------------|------------------------|-----------------|
| (GHz) | (dB)  | (dB)      | (dB)                    | (dB)                     | K         | Measure | (dBm)          | (dBm)                  | (dB)            |
| 5.0   | 11.97 | 41.23     | 12.19                   | 7.87                     | 11.53     | 0.88    | 31.84          | 17.38                  | 8.11            |
| 5.2   | 12.42 | 40.37     | 14.31                   | 8.48                     | 10.41     | 0.88    | 30.09          | 17.98                  | 7.41            |
| 5.4   | 12.80 | 39.60     | 16.60                   | 9.19                     | 9.49      | 0.89    | 30.63          | 18.04                  | 6.89            |
| 5.6   | 13.06 | 39.02     | 18.79                   | 9.62                     | 8.80      | 0.90    | 31.14          | 18.32                  | 6.43            |
| 5.8   | 13.27 | 38.50     | 21.06                   | 10.22                    | 8.25      | 0.91    | 31.06          | 18.05                  | 6.17            |
| 6.0   | 13.42 | 38.02     | 21.92                   | 10.68                    | 7.76      | 0.91    | 31.74          | 18.21                  | 5.92            |
| 6.2   | 13.55 | 37.74     | 21.83                   | 11.44                    | 7.52      | 0.93    | 29.88          | 18.16                  | 5.70            |
| 6.4   | 13.65 | 37.39     | 21.14                   | 11.80                    | 7.17      | 0.94    | 29.29          | 18.33                  | 5.53            |
| 6.6   | 13.72 | 37.05     | 21.22                   | 12.42                    | 6.90      | 0.94    | 29.50          | 18.36                  | 5.43            |
| 6.8   | 13.79 | 36.98     | 21.03                   | 13.51                    | 6.88      | 0.96    | 29.31          | 18.24                  | 5.31            |
| 7.0   | 13.84 | 36.79     | 22.06                   | 14.32                    | 6.76      | 0.96    | 29.22          | 17.93                  | 5.78            |
| 7.2   | 13.86 | 36.48     | 22.80                   | 15.88                    | 6.59      | 0.97    | 29.69          | 17.83                  | 5.21            |
| 7.4   | 13.88 | 36.43     | 25.77                   | 17.04                    | 6.60      | 0.98    | 29.03          | 18.15                  | 5.13            |
| 7.6   | 13.88 | 36.34     | 29.22                   | 19.32                    | 6.59      | 0.98    | 28.70          | 17.77                  | 5.06            |
| 7.8   | 13.87 | 36.17     | 37.10                   | 21.46                    | 6.50      | 0.99    | 28.73          | 18.22                  | 5.05            |
| 8.0   | 13.83 | 36.29     | 33.03                   | 25.09                    | 6.65      | 0.99    | 28.49          | 18.01                  | 5.05            |
| 8.2   | 13.77 | 36.34     | 28.98                   | 29.10                    | 6.74      | 0.99    | 28.30          | 18.22                  | 5.08            |
| 8.3   | 13.75 | 36.26     | 26.20                   | 29.48                    | 6.69      | 1.00    | 28.25          | 18.17                  | 5.07            |
| 8.4   | 13.72 | 36.24     | 23.50                   | 26.92                    | 6.69      | 1.00    | 28.22          | 18.25                  | 5.06            |
| 8.8   | 13.53 | 36.48     | 20.08                   | 19.92                    | 6.93      | 0.99    | 27.90          | 18.54                  | 5.17            |
| 8.9   | 13.48 | 36.27     | 19.10                   | 18.55                    | 6.76      | 0.99    | 27.74          | 18.19                  | 5.22            |
| 9.0   | 13.42 | 36.34     | 18.79                   | 17.43                    | 6.83      | 0.99    | 27.72          | 18.42                  | 5.24            |
| 9.1   | 13.36 | 36.42     | 18.20                   | 16.46                    | 6.90      | 0.98    | 27.74          | 18.39                  | 5.21            |
| 9.2   | 13.29 | 36.43     | 17.29                   | 15.63                    | 6.91      | 0.98    | 27.97          | 18.94                  | 5.20            |
| 9.3   | 13.23 | 36.41     | 16.56                   | 14.69                    | 6.87      | 0.98    | 27.72          | 18.42                  | 5.26            |
| 9.6   | 13.04 | 36.65     | 15.73                   | 13.47                    | 7.11      | 0.97    | 27.48          | 18.93                  | 5.36            |
| 9.7   | 12.96 | 36.78     | 15.12                   | 13.06                    | 7.22      | 0.97    | 27.58          | 19.27                  | 5.38            |
| 9.8   | 12.90 | 36.74     | 15.02                   | 12.50                    | 7.18      | 0.96    | 27.34          | 18.65                  | 5.43            |
| 9.9   | 12.86 | 36.79     | 15.10                   | 12.32                    | 7.24      | 0.96    | 27.40          | 18.84                  | 5.37            |
| 10.0  | 12.83 | 36.77     | 14.78                   | 12.28                    | 7.23      | 0.96    | 27.33          | 18.98                  | 5.38            |
| 10.5  | 12.50 | 36.75     | 13.33                   | 10.95                    | 7.23      | 0.95    | 27.17          | 19.32                  | 5.57            |
| 11.0  | 12.23 | 36.83     | 12.16                   | 10.50                    | 7.35      | 0.96    | 26.87          | 19.34                  | 5.68            |
| 11.5  | 12.00 | 36.67     | 11.36                   | 10.21                    | 7.28      | 0.96    | 26.41          | 19.31                  | 5.79            |
| 12.0  | 11.78 | 36.59     | 10.70                   | 9.89                     | 7.24      | 0.96    | 26.05          | 19.09                  | 5.93            |
| 12.5  | 11.61 | 36.45     | 10.14                   | 9.90                     | 7.16      | 0.97    | 25.71          | 19.36                  | 6.04            |
| 13.0  | 11.46 | 36.26     | 9.72                    | 9.63                     | 7.01      | 0.98    | 25.51          | 19.07                  | 6.21            |
| 13.5  | 11.41 | 35.65     | 9.83                    | 9.73                     | 6.59      | 0.98    | 25.50          | 19.55                  | 6.31            |
| 14.0  | 11.48 | 35.36     | 10.25                   | 10.21                    | 6.45      | 0.98    | 24.82          | 19.61                  | 6.36            |
| 14.5  | 11.65 | 34.84     | 11.34                   | 10.50                    | 6.12      | 0.97    | 24.77          | 19.54                  | 6.42            |
| 15.0  | 11.94 | 34.28     | 13.06                   | 11.46                    | 5.79      | 0.97    | 25.24          | 19.86                  | 6.47            |
| 15.5  | 12.14 | 33.40     | 15.23                   | 12.33                    | 5.31      | 0.97    | 24.56          | 19.84                  | 6.38            |
| 16.0  | 12.25 | 33.22     | 16.76                   | 12.55                    | 5.21      | 0.96    | 24.48          | 20.07                  | 6.36            |
| 16.5  | 12.30 | 32.74     | 16.09                   | 15.57                    | 5.04      | 0.99    | 24.06          | 20.00                  | 6.40            |
| 17.0  | 12.09 | 32.50     | 13.78                   | 15.06                    | 4.93      | 1.00    | 23.88          | 20.00                  | 6.52            |
| 17.5  | 11.63 | 32.50     | 11.12                   | 14.36                    | 4.99      | 1.02    | 24.48          | 18.92                  | 6.79            |
| 18.0  | 11.10 | 32.68     | 9.69                    | 13.35                    | 5.21      | 1.04    | 25.73          | 18.35                  | 7.11            |


## Typical Performance Curves




## Typical Performance Curves



### Outline Dimensions



### PCB Land Pattern



Suggested Layout,  
Tolerance to be within  $\pm.002$

| CASE # | A              | B              | C              | D              | E              | F              | G              | H              | J              | K              | L              | M              | N              |
|--------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|
| DQ849  | .118<br>(3.00) | .118<br>(3.00) | .035<br>(0.89) | .008<br>(0.20) | .067<br>(1.70) | .067<br>(1.70) | .012<br>(0.30) | .046<br>(1.17) | .016<br>(0.41) | .026<br>(0.66) | .148<br>(3.76) | .148<br>(3.76) | .067<br>(1.70) |

| CASE # | P              | Q              | R              | S              | T              | WT. GRAM |
|--------|----------------|----------------|----------------|----------------|----------------|----------|
| DQ849  | .012<br>(0.30) | .031<br>(0.79) | .067<br>(1.70) | .061<br>(1.55) | .041<br>(1.04) | .02      |

Dimensions are in inches (mm). Tolerances: 2Pl.  $\pm.01$ ; 3 Pl.  $\pm.004$

### Notes:

- Case material: Plastic.
- Termination finish:  
For RoHS Case Styles: Tin-Silver alloy plate over Nickel barrier or Matte-Tin plated. All models, (+) suffix. See Data sheet.  
For RoHS-5 Case Styles: Tin-Lead plate. All models, no (+) suffix.




INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified

# Tape & Reel Packaging TR-F104



| Tape Width, mm | Device Cavity Pitch, mm | Reel Size, inches | Devices per Reel                    |      |
|----------------|-------------------------|-------------------|-------------------------------------|------|
| 8              | 4                       | 7                 | Small quantity standards (see note) | 20   |
|                |                         |                   |                                     | 50   |
|                |                         |                   |                                     | 100  |
|                |                         |                   |                                     | 200  |
|                |                         |                   |                                     | 500  |
|                |                         |                   |                                     | 1000 |
|                |                         | 7                 | Standard                            | 2000 |

Note: Please Consult individual model data sheet to determine device per reel availability.

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: [www.minicircuits.com/pages/pdfs/tape.pdf](http://www.minicircuits.com/pages/pdfs/tape.pdf)




INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661


Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified



| REVISIONS |         |                              |          |     |      |
|-----------|---------|------------------------------|----------|-----|------|
| REV       | ECN No. | DESCRIPTION                  | DATE     | DR  | AUTH |
| OR        | M125952 | NEW RELEASE                  | 01/08/10 | MMG | RD   |
| A         | M132664 | UPDATED PATTERN & COMPONENTS | 12/16/11 | PW  | DJ   |
| B         | M135298 | UPDATED DESCRIPTION & NOTE 2 | 01/11/12 | AV  | DJ   |

SUGGESTED MOUNTING CONFIGURATION FOR  
DQ849 CASE STYLE, "08AM03" PIN CODE



- NOTES: 1. COPLANAR WAVEGUIDE PARAMETERS ARE SHOWN FOR ROGERS RO4350B WITH DIELECTRIC THICKNESS .010"  $\pm$  .001"; COPPER: 1/2 OZ. EACH SIDE.  
FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
2. 0402 AND 0805 CHIP COMPONENTS FOOTPRINTS ARE SHOWN FOR REFERENCE. VALUE OF COMPONENTS AS PER TB-547-X+.
3. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.



DENOTES PCB COPPER LAYOUT WITH SMOBC  
(SOLDER MASK OVER BARE COPPER)



DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

| UNLESS OTHERWISE SPECIFIED | INITIALS | DATE |
|----------------------------|----------|------|
| DIMENSIONS ARE IN INCHES   | DRAWN    | MMG  |
| TOLERANCES ON:             | CHECKED  | IL   |
| 2 PL DECIMALS $\pm$        | APPROVED | RD   |
| 3 PL DECIMALS $\pm$ .005   |          |      |
| ANGLES $\pm$               |          |      |
| FRACTIONS $\pm$            |          |      |



Mini-Circuits®



13 Neptune Avenue  
Brooklyn NY 11235

PL, 08AM03, DQ849, TB-547-X+

|                                                                                                                                                                                                                                                                                                                                                                                                                                                            |               |
|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|---------------|
| <p>Mini-Circuits®</p> <p>THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.</p> |               |
| ASHEETA1.DWG REV:A                                                                                                                                                                                                                                                                                                                                                                                                                                         | DATE:01/12/95 |

| SIZE  | CODE IDENT | DRAWING NO: | REV:   |
|-------|------------|-------------|--------|
| A     | 15542      | 98-PL-328   | B      |
| FILE: | 98PL328    | SCALE:      | 10:1   |
|       |            | SHEET:      | 1 OF 1 |

# Evaluation Board and Circuit



Schematic Diagram

## NOTES:

1. SMA Female connectors.
2. PCB material: Rogers R04350 or equivalent, dielectric constant=3.5, dielectric thickness=.010 inch.

 **Mini-Circuits®**



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

| Specification                  | Test/Inspection Condition                                                                                  | Reference/Spec                                                  |
|--------------------------------|------------------------------------------------------------------------------------------------------------|-----------------------------------------------------------------|
| Operating Temperature          | -40° to 85° C or -45° to 85° C or -55° to 105° C or -40° to 105° C or -40° to 95° C<br>Ambient Environment | Individual Model Data Sheet                                     |
| Storage Temperature            | -55° to 100° C or -65° to 150°<br>Ambient Environment                                                      | Individual Model Data Sheet                                     |
| HTOL                           | 1000 hours at 125°C                                                                                        | MIL-STD-883, Method 1005, Condition B                           |
| Thermal Shock                  | -55° to 100°C, 100 cycles                                                                                  | MIL-STD-202, Method 107, Condition A-3, except +100°C           |
| Mechanical Shock               | 1.5Kg, 0.5 ms, 5 shock pulses, Y1 direction only                                                           | MIL-STD-883, Method 2002, Condition B, except Y1 direction only |
| Vibration (Variable Frequency) | 50g peak                                                                                                   | MIL-STD-883, Method 2007, Condition B                           |
| Autoclave                      | 15 psig, 100% RH, 121°C, 96 hours                                                                          | JESD22-A102, Condition C                                        |
| HAST                           | 130°C, 85% RH, 96 hours                                                                                    | JESD22-A110                                                     |
| Solderability                  | 10X Magnification                                                                                          | J-STD-002, Para 4.2.5, Test S, 95% Coverage                     |
| Solder Reflow Heat             | Sn-Pb Eutetic Process: 240°C peak<br>Pb-Free Process: 260°C peak                                           | J-STD-020, Table 4-1, 4-2 and 5-2; Figure 5-1                   |
| Moisture Sensitivity: Level 1  | Bake at 125°C for 24 hours<br>Soak at 85°C/85% RH for 168 hours, Reflow 3 cycles at 260°C peak             | J-STD-020                                                       |



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

| Specification                  | Test/Inspection Condition                                                                                                                                       | Reference/Spec          |
|--------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------|-------------------------|
| Marking Resistance to Solvents | Isopropyl alcohol + mineral spirits at 25°C; terpene defluxer at 25°C;<br>distilled water + proylene glycol monomethyl ether + monoethanolamine at 63°C to 70°C | MIL-STD-202, Method 215 |