



MMIC DIE


Wideband Amplifier

AVA-5R183-D+

50Ω 0.5 to 18 GHz

THE BIG DEAL

- Wideband, 0.5 to 18 GHz
- Gain Flatness, ±1.6 dB Typ. up to 18 GHz
- Reverse Isolation, 36 dB Typ.
- P1dB, Typ +18.6 dBm



+RoHS Compliant
 The +Suffix identifies RoHS Compliance.
 See our website for methodologies and qualifications

APPLICATIONS

- 5G MIMO and Back Haul Radio Systems
- Satellite Ka-band Communications
- Test and Measurement Equipment
- Radar, EW, and ECM Defense Systems

SEE ORDERING INFORMATION ON THE LAST PAGE

PRODUCT OVERVIEW

The AVA-5R183-D+ is a GaAs pHEMT MMIC wideband amplifier operating from 0.5 to 18 GHz. The amplifier provides 13.5 dB of Gain, +18 dBm P1dB, and +23 dBm OIP3 typical performance while operating from a +5 V supply with 85 mA current consumption. The amplifier has excellent input and output impedance matches which makes for easy cascading with other devices in multi-chip modules. The Gain flatness along with the other performance characteristics makes AVA-5R183-D+ ideal for use in wideband EW Defense Systems and Test and Measurement Equipment.

KEY FEATURES

Features	Advantages
Wideband: 0.5 to 18 GHz	General purpose wideband amplifier is suitable for wide variety of applications.
Excellent Gain Flatness • 1.6 dB Typ. Up to 18 GHz	Desirable feature for maintaining frequency response within wideband signal chains.
Reverse Isolation, 36 dB Typ.	Isolates adjacent circuitry without need for an external expensive isolator.
Good Input and Output Return Loss	Return Loss enables easy cascading within wideband signal chains.
Unpackaged Die	Suitable for chip and wire hybrid assemblies.

REV. OR
 ECO-014348
 AVA-5R183-D+
 MCL NY
 250904



**MMIC DIE**

Wideband Amplifier

AVA-5R183-D+

Mini-Circuits

50Ω 0.5 to 18 GHz

ELECTRICAL SPECIFICATIONS¹ AT +25°C, V_{DD} = +5 V, I_{DD} = 85 mA & Z_o = 50Ω, UNLESS NOTED OTHERWISE

Parameter	Condition (GHz)	V _{DD} = +5 V			Units
		Min.	Typ.	Max.	
Frequency Range		0.5		18	GHz
Gain	0.5		14.6		dB
	5		12.9		
	10		13.3		
	15		12.5		
	18		13.1		
Input Return Loss	0.5		12		dB
	5		12		
	10		13		
	15		9		
	18		12		
Output Return Loss	0.5		36		dB
	5		25		
	10		34		
	15		16		
	18		17		
Reverse Isolation	0.5-18		36		dB
Output Power at 1 dB Compression	0.5		+19.5		dBm
	5		+19.7		
	10		+18.6		
	15		+17.7		
	18		+16.3		
Output Third-Order Intercept P _{OUT} = 0 dBm/Tone	0.5		+31.3		dBm
	5		+27.4		
	10		+23.3		
	15		+21.7		
	18		+20		
Noise Figure	0.5		4.8		dB
	5		3.3		
	10		2.8		
	15		3.6		
	18		4.4		
Device Operating Voltage (V _{DD})		+4.75	+5	+5.25	V
Device Operating Current (I _{DD})			85		mA
Device Gate Voltage (V _G)			-0.94		V
Device Gate Current (I _G)			0.47		μA
Device Current Variation vs. Temperature ²			264.5		μA/°C
Device Current Variation vs. Voltage ³			0.007		mA/mV
Thermal Resistance, Junction-to-Ground Lead (Θ _{JC})			22.2		°C/W

1. Die is soldered and measured on a die characterization board. See characterization circuit (Fig. 1).

2. Device Current Variation vs. Temperature = (Current in mA at +100°C - Current in mA at -55°C) / +155°C

3. Device Current Variation vs. Voltage = (Current in mA at +5.25 V - Current in mA at +4.75 V) / ((+5.25 V - +4.75 V) * 1000 mA/mV)



MMIC DIE

Wideband Amplifier

AVA-5R183-D+

Mini-Circuits

50Ω 0.5 to 18 GHz

ABSOLUTE MAXIMUM RATINGS⁴

Parameter	Ratings
Operating Temperature (Ground Lead)	-55°C to +100°C
Junction Temperature	+150°C ⁵
Power Dissipation	4.4 W ⁶
Input Power (CW)	+22 dBm
DC Voltage on RF-OUT & V _{DD}	+7 V
DC Voltage on V _G	-0.5 V to -2 V
DC Voltage on RF-IN ⁷	+7 V
Current I _{DD}	250 mA
Current I _G	2 mA


4. Permanent damage may occur if these limits are exceeding. Electrical maximum ratings are not intended for continuous normal operation.

5. $T_j = +85^\circ\text{C} + (V_{DD}) * (I_{DD}) * (\theta_{JC}) = +94^\circ\text{C}$. Keeping T_j below +94°C will ensure MTTF > 100 Years.

6. Derates linearly to 1.57 W at +100°C.


7. DC signal at RF-IN will be blocked by internal blocking capacitor. However, a DC current of 3.5 μA will be present due to the input shunt resistor assuming V_{RF-IN} = +7 V.

SIMPLIFIED SCHEMATIC AND PAD DESCRIPTION



Function	Pad Number	Description
RF-IN	1	RF Input Pad
RF-OUT & V _{DD}	4	RF Output and DC Input Pad
V _G	6	Gate Bias Pad
GROUND	2,3,5,7 & Bottom of Die	The bond pads are connected to backside through vias and do not require any wire-bond connections to ground.

BONDING PAD POSITION



DIMENSIONS IN μm, TYP.

L1	L2	L3	L4
96	2351	2518	2614

H1	H2	H3	H4	H5	H6	H7
99	267	417	1024	1172	1324	1438

Thickness	Die size	Pad size 1,4 & 6	Pad size 2,3,5,7
100	2614x1438	100x100	85x85






MMIC DIE

Wideband Amplifier

AVA-5R183-D+

50Ω 0.5 to 18 GHz

CHARACTERIZATION & APPLICATION CIRCUIT



Component	Size	Value	Part Number	Manufacturer
R1	0402	1K Ohm	FC0402E1001DTT5	Vishay
C1	0402	100 pF	GRM1555C1H101JA01J	Murata
C2	0402	0.1 uF	GRM155R71C104KA88D	Murata
C3	Chip Capacitor	100 pF	MA4M3100	MACOM

Fig 1. Characterization & Application Circuit

Note: This block diagram is used for characterization (Die is attached and wire-bonded on die characterization test board). Gain, Return Loss, Output Power at 1 dB Compression (P1dB), Output IP3 (OIP3) and Noise Figure are measured using Agilent's N5242A PNA- X Microwave Network Analyzer.

Conditions:

1. $V_{DD} = +5\text{ V}$
2. V_G is set to obtain desired I_{DD} as shown in specification table.
3. Gain and Return Loss: $P_{IN} = -25\text{ dBm}$
4. Output IP3 (OIP3): Two Tones, spaced 1 MHz apart, 0 dBm/Tone at output.

Switch ON/OFF sequence:

1. To switch the amplifier ON:
 - a. Set $V_G = -1.1\text{ V}$. Apply V_G .
 - b. Set $V_{DD} = +5\text{ V}$. Apply V_{DD} .
 - c. Increase V_G to obtain desired I_{DD} as shown in specification table.
 - d. Apply RF signal
2. To switch the amplifier OFF:
 - a. Turn OFF RF signal
 - b. Adjust V_G down to -1.1 V .
 - c. Turn off V_{DD} .
 - d. Turn off V_G .



MMIC DIE


Wideband Amplifier

AVA-5R183-D+

Mini-Circuits

50Ω 0.5 to 18 GHz


ASSEMBLY DRAWING



Note: Tested on die characterization board with following bond lengths:

1. Bond length for RF-IN: 330 μm (13 mils)
2. Bond length for RF-OUT + V_{DD} : 330 μm (13 mils)
3. Bond lengths from die, capacitor, and V_G were kept as short as possible

ASSEMBLY PROCEDURE

1. Storage
Die should be stored in a dry nitrogen purged desiccators or equivalent.
2.  ESD
MMIC PHEMT amplifier die are susceptible to electrostatic and mechanical damage. Die are supplied in antistatic protected material, which should be open in clean room conditions at an appropriately grounded anti-static workstation.
3. Die Handling and Attachment
Devices need careful handling using correctly designed collets, it is recommended to handle the chip along the edges with a custom design collet. The die mounting surface must be clean and flat. Using conductive silver filled epoxy, recommended epoxies are Ablestik 84-1 LMISR4 or equivalents. Apply sufficient epoxy to meet required epoxy bond line thickness, epoxy fillet height and epoxy coverage around total periphery. Parts shall be cured in a nitrogen filled atmosphere per manufacturer's cure condition. The surface of the chip has exposed air bridges and should not be touched with vacuum collet, tweezers or fingers.
4. Wire Bonding
Bond pad openings in the surface passivation above the bond pads are provided to allow wire bonding to the die gold bond pads. Thermo-sonic bonding is used with minimized ultrasonic content. Bond force, time, ultrasonic power and temperature are all critical parameters. Suggested wire is pure gold, 1mil diameter. Bonds must be made from the bond pads on the die to the packaged or substrate. All bond wire length and bond wire height should be kept as short as possible unless specified by the Assembly Drawing to minimize performance degradation due to undesirable series inductance.



MMIC DIE


Wideband Amplifier

AVA-5R183-D+


Mini-Circuits

50Ω 0.5 to 18 GHz


GAIN vs. FREQUENCY & TEMPERATURE
INPUT POWER = -25 dBm, VDD = +5V




GAIN vs. FREQUENCY & DEVICE VOLTAGE
INPUT POWER = -25 dBm, Temperature = +25°C




ISOLATION vs. FREQUENCY & TEMPERATURE
INPUT POWER = -25 dBm, VDD = +5V




ISOLATION vs. FREQUENCY & DEVICE VOLTAGE
INPUT POWER = -25 dBm, Temperature = +25°C




INPUT RETURN LOSS vs. FREQ. & TEMP.
INPUT POWER = -25 dBm, VDD = +5V




INPUT RETURN LOSS vs. FREQ. & DEVICE VOLTAGE
INPUT POWER = -25 dBm, Temperature = +25°C



OUTPUT RETURN LOSS vs. FREQ. & TEMP.
INPUT POWER = -25 dBm, VDD = +5V



OUTPUT RETURN LOSS vs. FREQ. & DEVICE VOLTAGE
INPUT POWER = -25 dBm, Temperature = +25°C





MMIC DIE


Wideband Amplifier

AVA-5R183-D+


Mini-Circuits

50Ω 0.5 to 18 GHz


OUTPUT IP3 vs. FREQUENCY & TEMPERATURE
OUTPUT POWER = -5 dBm, VDD = +5V




OUTPUT IP3 vs. FREQUENCY & DEVICE VOLTAGE
OUTPUT POWER = -5 dBm, Temperature = +25°C




P1dB vs. FREQUENCY & TEMPERATURE
VDD = +5V




P1dB vs. FREQUENCY & DEVICE VOLTAGE
Temperature = +25°C




NOISE FIGURE vs. FREQUENCY & TEMPERATURE
VDD = +5V



NOISE FIGURE vs. FREQUENCY & DEVICE VOLTAGE
Temperature = +25°C



GAIN VARIATIONS VS FREQUENCY & TEMPERATURE
INPUT POWER = -25 dBm, VDD = +5V



Mini-Circuits



MMIC DIE

Wideband Amplifier

AVA-5R183-D+

Mini-Circuits

50Ω 0.5 to 18 GHz

ADDITIONAL DETAILED TECHNICAL INFORMATION IS AVAILABLE ON OUR DASHBOARD. [CLICK HERE](#)

Performance Data	Data Table Swept Graphs S-Parameter (S2P Files) Data Set with and without port extension (.zip file)	
Case Style	Die	
Die Ordering and Packaging Information	Quantity, Package Gel - Pak: 5, 10, 50, 100, 200 Medium [†] , Partial wafer: KGD* < 2565 Full Wafer [†] Available upon request contact sales representative Refer to AN-60-067	Model No. AVA-5R183-DG+ AVA-5R183-DP+ AVA-5R183-DF+
Die Marking	EL-AMP-5-2	
Environmental Ratings	ENV80	

* Known Good Die ('KGD') means that the die in question have been subjected to Mini-Circuits DC test performance criteria and measurement instructions and that the parametric data of such die fall within predefined range. While DC testing is not definitive, it does provide a higher degree of confidence that die are capable of meeting typical RF electrical parameters specified by Mini-Circuits.

NOTES

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained there in. For a full statement of the standard. Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/terms/viewterm.html
- D. Mini-Circuits does not warrant the accuracy or completeness of the information, text, graphics and other items contained within this document and same are provided as an accommodation and on an As is basis, with all faults.
- E. Purchasers of this part are solely responsible for proper storing, handling, assembly and processing of Known Good Dice (including, without limitation, proper ESD preventative measures, die preparation, die attach, wire bonding and related assembly and test activities), and Mini-Circuits assumes no responsibility therefor or for environmental effects on Known Good Dice.
- F. Mini-Circuits and the Mini-Circuits logo are registered trademarks of Scientific Components Corporation d/b/a Mini-Circuits. All other third-party trademarks are the property of their respective owners. A reference to any third-party trademark does not constitute or imply any endorsement, affiliation, sponsorship, or recommendation by any such third-party of Mini-Circuits or its products.



Typical Performance Data

Definitions:

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 4.75V, Icc = 84mA @ Temperature = +25°C

FREQ	Gain	Isolation	Input Return Loss	Output Return Loss	Stability		IP-3 Output	1dB Comp. Output	Noise Figure
					K	Measure			
(MHz)	(dB)	(dB)	(dB)	(dB)	K	Measure	(dBm)	(dBm)	(dB)
500	14.77	65.63	11.92	34.45	167.11	1.06	33.19	19.36	4.75
1200	15.29	58.90	17.55	27.55	76.55	1.02	32.33	19.28	4.21
1900	15.85	51.35	13.77	25.14	29.46	1.04	33.13	19.33	3.49
2600	14.06	48.87	8.03	22.50	23.76	1.15	32.28	19.35	3.89
3300	13.06	51.34	8.88	23.12	37.22	1.12	31.99	19.23	4.39
4000	13.18	49.92	10.14	23.98	32.65	1.09	32.47	19.26	4.17
5000	13.44	46.27	11.79	26.15	21.78	1.06	33.14	19.50	3.27
5500	13.58	44.93	12.72	28.85	18.74	1.05	33.01	19.54	3.06
6000	13.72	43.95	13.59	35.28	16.75	1.04	31.85	19.56	2.76
6500	13.81	43.23	14.26	38.91	15.47	1.04	31.53	19.57	2.34
7000	13.86	42.90	14.79	28.52	14.91	1.03	32.39	19.26	2.13
7500	13.89	42.09	15.14	23.98	13.60	1.02	32.31	18.95	2.21
8000	13.93	41.44	15.08	21.25	12.57	1.02	32.31	19.21	2.16
8500	13.99	40.61	14.63	20.03	11.35	1.02	31.31	18.99	2.17
9000	14.06	39.75	14.06	20.00	10.21	1.03	31.73	18.91	2.42
9500	14.12	38.81	13.37	21.01	9.10	1.03	32.85	18.95	2.69
10000	14.14	38.11	12.56	22.57	8.32	1.05	30.97	18.47	2.87
10500	14.15	37.34	11.71	22.39	7.53	1.06	30.47	18.43	3.17
11000	14.11	36.80	10.85	19.60	6.97	1.06	30.81	18.34	3.39
11500	14.04	36.28	10.14	17.00	6.48	1.07	30.19	18.10	3.55
12000	13.94	35.63	9.72	15.10	5.94	1.06	30.14	17.82	3.37
12500	13.84	35.27	9.57	13.83	5.65	1.06	31.55	18.37	3.41
13000	13.75	34.80	9.50	13.20	5.34	1.05	31.23	18.58	3.66
13500	13.67	34.40	9.40	13.29	5.12	1.06	31.16	18.58	3.67
14000	13.60	34.09	9.27	14.02	4.98	1.07	32.00	18.50	3.62
14500	13.54	33.71	9.16	15.53	4.84	1.09	30.93	18.28	3.63
15000	13.46	33.42	8.97	17.53	4.75	1.10	30.36	17.74	3.66
16000	13.47	32.67	8.61	19.38	4.41	1.12	29.02	17.35	3.92
16200	13.51	32.54	8.69	19.46	4.36	1.12	29.27	17.32	3.68
16400	13.56	32.39	8.82	19.45	4.29	1.11	28.20	17.15	3.81
16600	13.64	32.04	8.99	19.50	4.12	1.11	28.21	17.21	3.91
16800	13.72	31.94	9.27	19.77	4.07	1.10	27.47	17.08	3.95
17000	13.83	31.66	9.65	19.95	3.96	1.09	28.53	16.93	4.02
17200	13.93	31.31	10.07	20.07	3.81	1.08	27.46	16.82	4.16
17400	14.04	31.07	10.54	19.69	3.70	1.07	27.27	16.68	4.29
17600	14.10	30.69	11.02	18.84	3.54	1.05	26.63	16.58	4.36
17800	14.13	30.46	11.23	17.33	3.43	1.04	26.59	16.44	4.49
18000	14.10	30.27	11.31	16.18	3.34	1.02	26.52	16.57	4.60

Typical Performance Data

NOTE: Use PDF Bookmarks to view DATA at required conditions

Definitions:

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 5.00V, Icc = 86mA @ Temperature = +25°C

FREQ	Gain	Isolation	Input Return Loss	Output Return Loss	Stability		IP-3 Output	1dB Comp. Output	Noise Figure
					K	Measure			
(MHz)	(dB)	(dB)	(dB)	(dB)	K	Measure	(dBm)	(dBm)	(dB)
500	14.77	60.99	11.92	35.85	97.68	1.06	32.97	19.40	4.79
1200	15.30	58.77	17.51	27.84	75.24	1.02	32.48	19.32	4.20
1900	15.86	51.19	13.73	25.58	28.85	1.04	32.73	19.38	3.46
2600	14.07	49.69	8.01	22.95	26.05	1.15	33.34	19.50	3.87
3300	13.07	52.00	8.86	23.70	40.12	1.12	32.88	19.38	4.34
4000	13.19	50.34	10.13	24.66	34.22	1.09	33.17	19.49	4.16
5000	13.45	46.62	11.77	26.70	22.63	1.06	33.46	19.63	3.28
5500	13.59	45.19	12.68	29.19	19.27	1.05	32.54	19.66	3.05
6000	13.73	44.42	13.55	34.91	17.66	1.04	32.92	19.68	2.79
6500	13.83	43.89	14.21	37.00	16.66	1.04	33.57	19.68	2.39
7000	13.87	43.24	14.73	28.49	15.49	1.03	32.60	19.37	2.19
7500	13.90	42.37	15.10	24.14	14.03	1.03	32.26	18.98	2.25
8000	13.94	41.91	15.04	21.45	13.25	1.02	32.46	19.22	2.20
8500	13.99	40.67	14.59	20.21	11.42	1.02	31.86	19.08	2.18
9000	14.07	40.17	14.00	20.13	10.70	1.03	31.63	18.92	2.41
9500	14.13	39.27	13.31	21.11	9.57	1.03	31.81	18.96	2.73
10000	14.14	38.62	12.51	22.62	8.81	1.05	30.58	18.56	2.85
10500	14.15	37.78	11.65	22.52	7.91	1.06	30.05	18.43	3.18
11000	14.11	36.99	10.81	19.76	7.12	1.06	31.86	18.30	3.39
11500	14.05	36.34	10.11	17.14	6.52	1.07	31.11	17.97	3.54
12000	13.95	35.98	9.67	15.20	6.17	1.07	30.88	17.71	3.38
12500	13.86	35.47	9.53	13.89	5.78	1.06	31.51	18.34	3.43
13000	13.77	35.05	9.46	13.23	5.49	1.06	31.64	18.56	3.64
13500	13.68	34.62	9.37	13.27	5.25	1.06	31.77	18.56	3.62
14000	13.61	34.29	9.24	13.94	5.09	1.07	30.60	18.58	3.59
14500	13.55	33.96	9.15	15.41	4.98	1.09	30.99	18.28	3.66
15000	13.48	33.61	8.97	17.38	4.85	1.10	29.69	17.71	3.62
16000	13.47	32.93	8.62	19.28	4.54	1.12	29.45	17.18	3.91
16200	13.51	32.72	8.72	19.33	4.45	1.12	27.85	17.05	3.67
16400	13.55	32.66	8.85	19.28	4.42	1.11	28.83	16.97	3.79
16600	13.63	32.37	9.02	19.25	4.28	1.11	28.44	16.93	3.88
16800	13.71	32.08	9.31	19.44	4.15	1.10	28.47	16.79	3.98
17000	13.81	31.88	9.68	19.54	4.06	1.09	27.16	16.63	4.06
17200	13.91	31.57	10.11	19.61	3.92	1.08	26.85	16.59	4.17
17400	14.00	31.32	10.56	19.22	3.81	1.07	26.26	16.35	4.33
17600	14.06	31.07	11.02	18.48	3.71	1.05	27.12	16.24	4.37
17800	14.08	30.70	11.21	17.10	3.54	1.04	26.31	16.00	4.48
18000	14.05	30.41	11.26	16.08	3.41	1.02	26.60	16.23	4.55

Typical Performance Data

Definitions:

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 5.25, Icc = 88mA @ Temperature = +25°C

FREQ	Gain	Isolation	Input Return Loss	Output Return Loss	Stability		IP-3 Output	1dB Comp. Output	Noise Figure
					K	Measure			
(MHz)	(dB)	(dB)	(dB)	(dB)			(dBm)	(dBm)	(dB)
500	14.78	64.75	11.91	37.51	388.90	1.06	33.69	19.51	4.79
1200	15.31	61.10	17.47	28.09	273.24	1.01	32.50	19.22	4.22
1900	15.86	52.56	13.69	25.96	104.43	1.03	33.57	19.36	3.49
2600	14.07	49.90	7.99	23.40	96.24	1.14	32.62	19.59	3.86
3300	13.07	53.07	8.84	24.29	269.25	1.12	33.64	19.47	4.45
4000	13.19	51.42	10.10	25.38	85.04	1.09	33.17	19.58	4.20
5000	13.45	47.35	11.73	27.24	43.18	1.06	32.74	19.68	3.33
5500	13.59	45.56	12.64	29.49	34.94	1.04	33.07	19.74	3.09
6000	13.73	44.84	13.49	33.99	31.58	1.03	31.96	19.74	2.77
6500	13.82	44.32	14.16	35.19	32.13	1.03	33.42	19.76	2.31
7000	13.87	43.75	14.69	28.48	29.15	1.03	32.71	19.45	2.19
7500	13.89	43.10	15.05	24.31	25.44	1.03	32.06	19.04	2.29
8000	13.93	42.50	14.99	21.62	21.92	1.03	31.55	19.19	2.14
8500	13.99	41.19	14.55	20.38	19.72	1.03	31.28	19.05	2.15
9000	14.06	40.32	13.96	20.25	16.65	1.04	32.05	18.89	2.42
9500	14.11	39.73	13.26	21.17	15.11	1.05	31.17	18.93	2.72
10000	14.13	38.72	12.45	22.66	13.12	1.06	31.54	18.43	2.84
10500	14.14	38.02	11.61	22.61	11.78	1.07	31.09	18.38	3.16
11000	14.10	37.25	10.76	19.89	10.63	1.08	31.54	18.16	3.40
11500	14.03	36.75	10.07	17.26	9.61	1.09	31.09	17.90	3.55
12000	13.93	36.23	9.64	15.28	9.00	1.08	30.03	17.65	3.38
12500	13.84	35.73	9.49	13.95	8.20	1.07	31.03	18.19	3.49
13000	13.75	35.36	9.43	13.24	7.65	1.05	31.62	18.51	3.63
13500	13.66	34.87	9.33	13.24	7.21	1.04	31.08	18.59	3.63
14000	13.59	34.56	9.22	13.88	6.90	1.05	31.58	18.53	3.59
14500	13.52	34.28	9.12	15.28	6.62	1.06	31.79	18.32	3.72
15000	13.45	33.84	8.96	17.21	6.34	1.08	30.60	17.65	3.61
16000	13.44	33.16	8.65	19.16	5.99	1.13	29.54	16.92	3.83
16200	13.48	32.99	8.74	19.20	5.89	1.13	29.85	16.75	3.67
16400	13.52	32.80	8.88	19.10	5.80	1.13	29.14	16.60	3.76
16600	13.59	32.57	9.05	19.05	5.73	1.12	28.47	16.53	3.85
16800	13.66	32.30	9.35	19.15	5.67	1.12	28.89	16.18	4.00
17000	13.76	32.04	9.72	19.16	5.59	1.11	28.03	16.04	4.06
17200	13.85	31.72	10.14	19.17	5.46	1.10	27.89	15.89	4.14
17400	13.93	31.49	10.59	18.80	5.32	1.09	27.10	15.65	4.27
17600	13.98	31.25	11.03	18.15	5.18	1.08	26.90	15.44	4.38
17800	13.99	30.96	11.19	16.87	5.10	1.07	26.85	15.28	4.47
18000	13.95	30.65	11.21	15.97	4.98	1.06	26.49	15.50	4.58

Typical Performance Data

Definitions:

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 4.75, Icc = 54mA @ Temperature = -55°C

FREQ	Gain	Isolation	Input Return Loss	Output Return Loss	Stability		IP-3 Output	1dB Comp. Output	Noise Figure
					K	Measure			
(MHz)	(dB)	(dB)	(dB)	(dB)			(dBm)	(dBm)	(dB)
500	14.73	66.95	12.05	31.44	219.73	1.06	30.35	18.08	3.87
1200	15.29	69.75	18.31	26.25	299.55	1.01	29.93	17.79	3.41
1900	15.89	60.77	14.97	26.23	97.27	1.03	28.66	17.65	2.74
2600	14.22	59.55	8.41	28.07	89.07	1.14	27.57	17.34	3.12
3300	13.16	74.98	9.18	31.79	620.34	1.12	27.74	17.23	3.68
4000	13.28	56.62	10.50	44.98	76.84	1.09	27.66	17.16	3.48
5000	13.56	51.63	12.28	25.63	43.18	1.06	27.01	17.36	2.74
5500	13.73	49.56	13.24	23.26	33.88	1.04	26.80	17.21	2.48
6000	13.89	49.29	14.07	22.62	32.71	1.03	26.51	17.07	2.17
6500	13.99	49.19	14.67	22.91	32.25	1.03	26.05	16.96	1.90
7000	14.05	48.38	15.10	23.68	29.38	1.03	25.93	16.95	1.63
7500	14.08	47.23	15.34	24.47	25.74	1.03	25.85	16.67	1.66
8000	14.13	46.05	15.17	24.58	22.42	1.03	25.44	16.70	1.53
8500	14.20	44.84	14.51	23.79	19.39	1.03	24.99	16.46	1.42
9000	14.28	43.59	13.71	23.08	16.66	1.04	24.27	16.48	1.46
9500	14.36	42.43	12.77	23.11	14.43	1.05	23.97	16.35	1.62
10000	14.40	41.77	11.87	24.16	13.24	1.06	23.05	16.32	1.56
10500	14.45	40.63	11.15	26.12	11.44	1.07	22.98	16.19	1.76
11000	14.44	40.03	10.51	24.46	10.53	1.08	22.77	16.44	2.03
11500	14.41	39.28	9.97	20.27	9.50	1.09	22.58	16.19	2.03
12000	14.37	38.88	9.61	16.87	8.90	1.08	22.26	15.33	1.96
12500	14.33	38.41	9.48	14.45	8.29	1.07	22.07	15.64	2.03
13000	14.30	37.94	9.49	12.99	7.74	1.05	21.67	15.41	2.35
13500	14.26	37.44	9.47	12.32	7.22	1.04	21.42	15.50	2.47
14000	14.23	37.06	9.38	12.23	6.87	1.05	21.33	15.69	2.37
14500	14.22	36.72	9.21	12.83	6.62	1.06	21.48	15.85	2.42
15000	14.19	36.29	8.85	13.84	6.31	1.08	21.48	15.76	2.45
16000	14.15	35.85	7.95	15.13	5.98	1.12	21.77	14.98	2.65
16200	14.17	35.58	7.89	15.05	5.81	1.13	21.11	15.08	2.46
16400	14.21	35.51	7.86	14.73	5.77	1.12	21.03	14.94	2.52
16600	14.28	35.35	7.86	14.40	5.66	1.12	20.59	15.32	2.52
16800	14.35	35.27	7.96	14.10	5.62	1.12	20.42	15.59	2.65
17000	14.46	35.07	8.14	13.81	5.50	1.11	20.68	15.42	2.43
17200	14.58	34.87	8.39	13.67	5.40	1.10	20.35	15.80	2.54
17400	14.70	34.64	8.73	13.56	5.29	1.09	20.48	15.89	2.51
17600	14.82	34.36	9.19	13.59	5.17	1.08	20.02	16.02	2.51
17800	14.92	34.11	9.59	13.44	5.03	1.06	19.94	15.98	2.47
18000	15.01	33.81	10.07	13.57	4.91	1.05	19.68	16.07	2.56

Typical Performance Data

Definitions:

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 5.00V, Icc = 54mA @ Temperature = -55°C

FREQ	Gain	Isolation	Input Return Loss	Output Return Loss	Stability		IP-3 Output	1dB Comp. Output	Noise Figure
					K	Measure			
(MHz)	(dB)	(dB)	(dB)	(dB)	K	Measure	(dBm)	(dBm)	(dB)
500	14.75	69.93	12.05	31.19	310.69	1.06	30.43	18.51	3.94
1200	15.30	77.20	18.32	26.14	709.12	1.01	30.19	18.33	3.41
1900	15.90	63.24	14.98	26.24	129.56	1.03	28.63	18.19	2.82
2600	14.24	60.34	8.42	28.18	97.82	1.14	28.28	17.99	3.14
3300	13.17	66.36	9.18	31.86	230.41	1.12	27.93	17.99	3.63
4000	13.29	56.13	10.51	44.30	72.81	1.09	27.49	17.82	3.52
5000	13.58	51.87	12.27	25.50	44.50	1.06	27.37	17.92	2.72
5500	13.74	50.11	13.25	23.11	36.17	1.04	26.83	17.76	2.48
6000	13.90	49.68	14.08	22.49	34.26	1.03	26.65	17.74	2.23
6500	14.00	48.65	14.68	22.77	30.33	1.03	26.04	17.63	1.87
7000	14.06	47.82	15.10	23.59	27.58	1.03	26.04	17.52	1.62
7500	14.09	47.03	15.33	24.48	25.18	1.03	25.85	17.24	1.70
8000	14.14	45.85	15.16	24.64	21.92	1.03	25.59	17.26	1.54
8500	14.21	44.67	14.52	23.88	19.02	1.03	25.05	17.13	1.39
9000	14.29	43.72	13.72	23.16	16.93	1.04	24.36	17.04	1.49
9500	14.36	42.62	12.76	23.17	14.77	1.05	23.73	17.02	1.61
10000	14.41	41.58	11.86	24.11	12.96	1.06	23.14	16.78	1.61
10500	14.45	40.79	11.11	26.23	11.66	1.07	23.09	16.64	1.84
11000	14.44	40.13	10.47	24.59	10.66	1.08	22.89	17.00	2.04
11500	14.41	39.36	9.93	20.33	9.59	1.09	22.80	16.54	2.19
12000	14.37	38.94	9.57	16.89	8.96	1.08	22.34	15.90	2.05
12500	14.33	38.44	9.45	14.44	8.32	1.07	22.20	16.20	2.15
13000	14.30	37.99	9.45	12.97	7.78	1.05	21.72	16.10	2.40
13500	14.26	37.63	9.45	12.29	7.39	1.04	21.48	15.86	2.45
14000	14.23	37.10	9.37	12.21	6.92	1.05	21.34	16.36	2.34
14500	14.22	36.78	9.20	12.80	6.67	1.06	21.60	16.42	2.48
15000	14.19	36.40	8.82	13.82	6.40	1.08	21.59	16.42	2.54
16000	14.15	35.87	7.92	15.07	6.01	1.13	21.78	15.76	2.74
16200	14.17	35.68	7.86	14.99	5.89	1.13	21.28	15.63	2.47
16400	14.20	35.57	7.83	14.67	5.82	1.13	21.08	15.70	2.56
16600	14.27	35.52	7.83	14.33	5.78	1.12	20.64	16.09	2.55
16800	14.34	35.35	7.93	14.04	5.68	1.12	20.61	16.14	2.49
17000	14.45	35.14	8.11	13.73	5.56	1.11	20.90	16.08	2.54
17200	14.56	34.88	8.35	13.60	5.42	1.10	20.42	16.35	2.59
17400	14.68	34.80	8.70	13.48	5.40	1.09	20.55	16.43	2.53
17600	14.78	34.41	9.15	13.49	5.21	1.08	20.13	16.54	2.57
17800	14.87	34.27	9.54	13.33	5.14	1.06	19.93	16.62	2.57
18000	14.95	34.01	9.97	13.45	5.02	1.05	19.73	16.61	2.61

Typical Performance Data

Definitions:

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 5.25V, Icc = 54mA @ Temperature = -55°C

FREQ	Gain	Isolation	Input Return Loss	Output Return Loss	Stability		IP-3 Output	1dB Comp. Output	Noise Figure
					K	Measure			
(MHz)	(dB)	(dB)	(dB)	(dB)	K	Measure	(dBm)	(dBm)	(dB)
500	14.78	71.86	12.05	30.82	388.90	1.06	31.03	18.46	3.93
1200	15.33	68.90	18.36	26.11	273.24	1.01	29.56	18.36	3.47
1900	15.93	61.34	15.04	26.26	104.43	1.03	28.43	18.12	2.77
2600	14.26	60.19	8.44	28.30	96.24	1.14	27.76	18.01	3.09
3300	13.20	67.70	9.21	31.86	269.25	1.12	27.79	18.02	3.67
4000	13.32	57.48	10.52	44.04	85.04	1.09	27.63	17.95	3.54
5000	13.60	51.62	12.29	25.33	43.18	1.06	27.18	17.93	2.73
5500	13.76	49.82	13.27	22.98	34.94	1.04	26.83	17.77	2.50
6000	13.92	48.99	14.12	22.33	31.58	1.03	26.45	17.74	2.19
6500	14.02	49.16	14.73	22.67	32.13	1.03	26.26	17.53	1.92
7000	14.08	48.32	15.14	23.52	29.15	1.03	26.01	17.63	1.70
7500	14.11	47.13	15.35	24.45	25.44	1.03	25.56	17.36	1.78
8000	14.16	45.86	15.16	24.69	21.92	1.03	25.33	17.27	1.55
8500	14.22	45.00	14.53	23.96	19.72	1.03	24.74	17.13	1.39
9000	14.30	43.59	13.72	23.15	16.65	1.04	24.31	17.04	1.54
9500	14.38	42.85	12.75	23.18	15.11	1.05	23.73	17.02	1.65
10000	14.42	41.71	11.83	24.08	13.12	1.06	23.01	16.89	1.66
10500	14.46	40.90	11.09	26.18	11.78	1.07	22.92	16.64	1.90
11000	14.45	40.13	10.45	24.72	10.63	1.08	22.65	16.89	2.12
11500	14.42	39.41	9.91	20.40	9.61	1.09	22.53	16.76	2.27
12000	14.38	39.00	9.54	16.88	9.00	1.08	22.26	15.80	2.20
12500	14.34	38.34	9.43	14.38	8.20	1.07	22.07	16.09	2.14
13000	14.31	37.88	9.44	12.91	7.65	1.05	21.69	15.97	2.40
13500	14.27	37.45	9.44	12.23	7.21	1.04	21.34	15.96	2.49
14000	14.24	37.11	9.37	12.12	6.90	1.05	21.36	16.25	2.44
14500	14.23	36.74	9.20	12.74	6.62	1.06	21.54	16.52	2.50
15000	14.20	36.35	8.81	13.77	6.34	1.08	21.41	16.42	2.50
16000	14.16	35.88	7.88	14.96	5.99	1.13	21.66	15.77	2.66
16200	14.18	35.72	7.82	14.90	5.89	1.13	21.09	15.64	2.53
16400	14.21	35.58	7.78	14.57	5.80	1.13	20.99	15.82	2.58
16600	14.27	35.49	7.78	14.22	5.73	1.12	20.43	16.09	2.51
16800	14.34	35.38	7.88	13.93	5.67	1.12	20.43	16.34	2.62
17000	14.44	35.23	8.05	13.62	5.59	1.11	20.75	16.20	2.50
17200	14.55	34.97	8.28	13.48	5.46	1.10	20.30	16.36	2.65
17400	14.66	34.71	8.62	13.36	5.32	1.09	20.27	16.55	2.59
17600	14.76	34.40	9.07	13.39	5.18	1.08	19.95	16.57	2.68
17800	14.84	34.23	9.44	13.22	5.10	1.07	19.81	16.66	2.59
18000	14.90	33.97	9.88	13.34	4.98	1.06	19.64	16.64	2.67

Typical Performance Data

Definitions:

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 4.75V, Icc = 93mA @ Temperature = +100°C

FREQ	Gain	Isolation	Input Return Loss	Output Return Loss	Stability		IP-3 Output	1dB Comp. Output	Noise Figure
					K	Measure			
(MHz)	(dB)	(dB)	(dB)	(dB)	K	Measure	(dBm)	(dBm)	(dB)
500	13.65	65.14	11.96	35.30	157.40	1.06	32.63	18.98	5.51
1200	14.27	57.09	17.61	27.50	62.11	1.02	33.30	18.92	4.83
1900	15.00	50.20	13.53	24.67	25.84	1.04	33.44	19.25	4.06
2600	13.57	48.56	8.08	21.84	23.39	1.15	34.21	19.54	4.58
3300	12.46	50.32	9.02	22.38	33.59	1.12	33.80	19.11	5.10
4000	12.63	49.01	10.36	23.43	29.89	1.09	32.69	19.09	4.77
5000	13.01	45.21	12.09	25.91	19.65	1.06	32.96	19.32	3.82
5500	13.21	44.10	13.00	28.62	17.38	1.05	32.50	19.37	3.63
6000	13.40	43.28	13.84	35.74	15.86	1.04	32.65	19.57	3.21
6500	13.54	42.75	14.54	37.68	14.98	1.03	32.62	19.47	2.96
7000	13.62	42.29	15.14	27.76	14.25	1.03	32.87	19.16	2.75
7500	13.67	41.35	15.41	23.60	12.80	1.02	32.17	18.83	2.81
8000	13.73	40.81	15.14	21.43	11.98	1.02	32.43	19.00	2.74
8500	13.79	39.96	14.56	20.90	10.80	1.02	32.00	18.84	2.76
9000	13.86	39.22	13.95	21.76	9.88	1.03	31.77	18.66	3.04
9500	13.91	38.49	13.28	23.88	9.02	1.04	31.93	18.76	3.33
10000	13.93	37.91	12.55	25.60	8.40	1.05	30.77	18.23	3.54
10500	13.99	37.10	11.81	23.62	7.59	1.06	31.47	18.18	3.82
11000	14.04	36.63	11.05	20.06	7.13	1.06	31.23	18.13	4.15
11500	14.09	36.10	10.36	17.43	6.67	1.06	31.27	17.86	4.21
12000	14.13	35.73	9.90	15.56	6.36	1.06	29.97	17.47	4.05
12500	14.16	35.42	9.73	14.38	6.14	1.06	30.66	17.96	4.16
13000	14.20	35.10	9.71	13.95	5.97	1.06	30.97	18.08	4.35
13500	14.22	34.80	9.70	14.19	5.85	1.06	30.92	18.01	4.44
14000	14.25	34.53	9.62	14.90	5.75	1.07	31.29	17.99	4.42
14500	14.29	34.16	9.53	16.00	5.60	1.08	30.71	17.59	4.28
15000	14.30	33.94	9.40	17.04	5.55	1.09	30.22	17.07	4.39
16000	14.20	33.11	9.58	18.12	5.14	1.09	28.87	16.56	4.74
16200	14.17	32.99	9.78	18.38	5.09	1.09	27.95	16.52	4.59
16400	14.14	32.84	10.04	18.60	5.02	1.08	27.91	16.24	4.73
16600	14.12	32.58	10.29	18.77	4.87	1.08	28.10	16.29	4.77
16800	14.12	32.40	10.59	18.92	4.76	1.07	27.69	16.14	4.86
17000	14.15	32.13	10.90	18.75	4.60	1.06	28.45	15.89	4.88
17200	14.19	31.90	11.11	18.36	4.46	1.06	27.40	16.04	5.07
17400	14.24	31.76	11.18	17.38	4.35	1.05	27.05	15.71	5.12
17600	14.31	31.68	11.07	16.16	4.27	1.04	26.88	15.72	5.29
17800	14.40	31.54	10.65	14.69	4.14	1.03	26.76	15.44	5.28
18000	14.49	31.55	10.17	13.63	4.11	1.03	26.76	15.59	5.55

Typical Performance Data

Definitions:

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 5.00V, Icc = 94mA @ Temperature = +100°C

FREQ	Gain	Isolation	Input Return Loss	Output Return Loss	Stability		IP-3 Output	1dB Comp. Output	Noise Figure
					K	Measure			
(MHz)	(dB)	(dB)	(dB)	(dB)	K	Measure	(dBm)	(dBm)	(dB)
500	13.63	68.29	11.95	37.42	226.09	1.06	33.45	19.28	5.46
1200	14.25	58.25	17.57	27.84	70.88	1.02	33.22	19.22	4.84
1900	14.99	50.80	13.49	25.14	27.67	1.04	32.70	19.57	4.07
2600	13.56	49.25	8.07	22.33	25.28	1.15	33.45	19.94	4.58
3300	12.46	51.41	9.00	22.98	38.06	1.12	32.93	19.44	5.07
4000	12.63	49.54	10.34	24.13	31.76	1.09	34.07	19.33	4.80
5000	13.02	45.95	12.06	26.64	21.36	1.06	32.01	19.54	3.80
5500	13.22	44.62	12.96	29.31	18.42	1.05	33.44	19.68	3.64
6000	13.41	43.82	13.80	36.90	16.85	1.04	33.90	19.79	3.26
6500	13.55	43.24	14.47	38.83	15.81	1.03	32.55	19.70	2.93
7000	13.63	42.45	15.08	28.11	14.48	1.03	32.48	19.46	2.64
7500	13.68	41.77	15.36	23.95	13.40	1.02	33.24	19.05	2.80
8000	13.74	41.21	15.10	21.68	12.53	1.02	31.77	19.21	2.75
8500	13.81	40.48	14.53	21.06	11.46	1.02	33.02	19.14	2.70
9000	13.88	39.56	13.90	21.83	10.25	1.03	32.25	18.96	3.02
9500	13.93	39.04	13.22	23.92	9.60	1.04	31.28	18.98	3.36
10000	13.95	38.07	12.48	25.72	8.55	1.05	31.71	18.44	3.47
10500	14.01	37.46	11.74	23.85	7.90	1.06	32.22	18.38	3.88
11000	14.06	36.93	10.99	20.30	7.38	1.06	31.39	18.25	4.02
11500	14.11	36.34	10.32	17.63	6.84	1.07	30.60	18.07	4.22
12000	14.15	35.98	9.86	15.70	6.53	1.07	30.19	17.85	4.13
12500	14.19	35.72	9.69	14.48	6.34	1.06	31.40	18.25	4.19
13000	14.22	35.50	9.66	14.00	6.23	1.06	31.13	18.37	4.39
13500	14.24	35.12	9.64	14.17	6.04	1.06	29.83	18.31	4.39
14000	14.27	34.81	9.57	14.85	5.92	1.07	30.78	18.21	4.36
14500	14.32	34.42	9.50	15.91	5.76	1.08	31.71	17.89	4.44
15000	14.32	34.14	9.39	16.98	5.66	1.09	29.90	17.28	4.43
16000	14.21	33.45	9.56	17.95	5.33	1.09	29.05	16.65	4.70
16200	14.18	33.22	9.76	18.13	5.22	1.09	28.59	16.59	4.55
16400	14.15	33.10	10.01	18.27	5.16	1.08	28.36	16.23	4.71
16600	14.14	32.93	10.26	18.33	5.06	1.08	28.07	16.27	4.72
16800	14.13	32.67	10.56	18.43	4.90	1.07	27.88	16.11	4.89
17000	14.15	32.43	10.87	18.25	4.76	1.06	27.48	15.77	4.87
17200	14.18	32.21	11.06	17.87	4.62	1.06	27.65	15.73	5.02
17400	14.24	32.15	11.13	17.00	4.55	1.05	26.69	15.58	4.96
17600	14.31	31.98	11.02	15.93	4.42	1.04	26.43	15.61	5.27
17800	14.39	31.87	10.58	14.58	4.31	1.03	26.14	15.41	5.35
18000	14.48	31.93	10.11	13.61	4.30	1.03	26.57	15.55	5.59

Typical Performance Data

Definitions:

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)









Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 5.25V, Icc = 96mA @ Temperature = +100°C


FREQ	Gain	Isolation	Input Return Loss	Output Return Loss	Stability		IP-3 Output	1dB Comp. Output	Noise Figure
					K	Measure			
(MHz)	(dB)	(dB)	(dB)	(dB)			(dBm)	(dBm)	(dB)
500	13.78	62.75	11.95	39.37	119.32	1.06	32.18	19.64	5.56
1200	14.48	58.39	17.54	28.13	72.02	1.02	32.84	19.59	4.87
1900	15.36	50.63	13.46	25.54	27.11	1.04	33.46	19.87	4.12
2600	13.39	49.49	8.05	22.78	26.00	1.15	33.74	20.33	4.50
3300	12.65	51.85	8.99	23.54	40.03	1.12	32.95	19.90	5.07
4000	12.90	50.03	10.33	24.87	33.59	1.09	33.93	19.71	4.79
5000	13.28	46.30	12.04	27.28	22.25	1.06	33.41	19.82	3.85
5500	13.47	44.80	12.94	29.97	18.79	1.05	34.58	20.05	3.54
6000	13.66	44.25	13.75	37.59	17.70	1.04	33.29	20.08	3.30
6500	13.81	43.48	14.45	38.65	16.27	1.03	32.68	20.07	2.98
7000	13.90	42.78	15.04	28.43	15.05	1.03	33.26	19.74	2.73
7500	13.98	42.01	15.32	24.22	13.79	1.02	31.85	19.32	2.77
8000	14.07	41.65	15.06	21.90	13.19	1.02	31.45	19.65	2.73
8500	14.15	40.64	14.48	21.26	11.68	1.02	31.55	19.33	2.75
9000	14.24	39.87	13.84	21.98	10.63	1.03	32.12	19.23	3.00
9500	14.31	39.02	13.16	24.01	9.60	1.04	31.75	19.33	3.42
10000	14.36	38.22	12.44	25.81	8.71	1.05	31.14	18.71	3.50
10500	14.44	37.64	11.71	24.05	8.08	1.06	30.81	18.65	3.86
11000	14.50	37.17	10.97	20.50	7.60	1.06	31.25	18.60	4.06
11500	14.55	36.67	10.29	17.79	7.12	1.07	30.40	18.42	4.24
12000	14.58	36.30	9.83	15.84	6.79	1.07	30.93	18.12	4.13
12500	14.63	35.96	9.66	14.56	6.53	1.06	30.83	18.43	4.15
13000	14.71	35.70	9.65	14.05	6.40	1.06	31.51	18.64	4.39
13500	14.76	35.43	9.63	14.19	6.28	1.06	31.43	18.58	4.43
14000	14.79	35.13	9.58	14.83	6.15	1.07	30.99	18.58	4.34
14500	14.80	34.65	9.50	15.89	5.93	1.08	30.90	18.08	4.39
15000	14.76	34.41	9.39	16.91	5.86	1.09	30.68	17.55	4.39
16000	14.63	33.59	9.59	17.84	5.44	1.09	29.94	16.89	4.77
16200	14.62	33.48	9.80	18.01	5.39	1.09	29.42	16.64	4.56
16400	14.59	33.26	10.06	18.10	5.28	1.08	28.49	16.36	4.64
16600	14.59	33.05	10.30	18.12	5.15	1.08	27.88	16.40	4.70
16800	14.60	32.90	10.62	18.15	5.06	1.07	28.19	16.25	4.76
17000	14.62	32.68	10.90	17.92	4.92	1.06	27.72	16.08	4.94
17200	14.66	32.55	11.10	17.55	4.83	1.05	27.64	15.95	5.10
17400	14.73	32.36	11.13	16.72	4.69	1.05	27.20	15.78	5.09
17600	14.81	32.32	11.00	15.75	4.63	1.04	27.05	15.72	5.37
17800	14.92	32.27	10.54	14.47	4.54	1.03	26.15	15.61	5.41
18000	15.05	32.10	10.06	13.57	4.42	1.03	26.57	15.74	5.55

Typical Performance Curves




Typical Performance Curves


OUTPUT IP3 vs. FREQUENCY & TEMPERATURE
OUTPUT POWER = -5 dBm, VDD = +5V




OUTPUT IP3 vs. FREQUENCY & DEVICE VOLTAGE
OUTPUT POWER = -5 dBm, Temperature = +25°C




P1dB vs. FREQUENCY & TEMPERATURE
VDD = +5V




P1dB vs. FREQUENCY & DEVICE VOLTAGE
Temperature = +25°C




NOISE FIGURE vs. FREQUENCY & TEMPERATURE
VDD = +5V



NOISE FIGURE vs. FREQUENCY & DEVICE VOLTAGE
Temperature = +25°C



GAIN VARIATIONS VS FREQUENCY & TEMPERATURE
INPUT POWER = -25 dBm, VDD = +5V



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-40° to 85° C or -40° to 105° C or -55° to 105° C or -45° to 105° C Ambient Environment	Refer to Individual Model Data Sheet
Storage Environment (Die)	-65° to 150°C	Individual Model Data Sheet
Storage Environment(Packaging)	-40° to 70°C and 40 to 60% humidity (In Factory Shipped Package)	