



MMIC SURFACE MOUNT

X3 Frequency Multiplier

CY3-453+

50Ω Output 20 to 45 GHz

THE BIG DEAL

- Wideband Output From: 20 to 45 GHz
- Outstanding Fundamental and Close-in Harmonic Suppression:
 - F1: 39 dBc Typ.
 - F2: 46 dBc Typ.
 - F4: 40 dBc Typ.
- Input Drive Level: +12 to +17 dBm
- Conversion Loss: 20 dB Typ.
- Tiny Size, 4x4mm 24-Lead, QFN-Style




Generic photo used for illustration purposes only

APPLICATIONS

- 5G MIMO and Back Haul Radio Systems
- Satellite Communications
- Test and Measurement Equipment
- Radar, EW, and ECM Defense Systems

FUNCTIONAL DIAGRAM



PRODUCT OVERVIEW

Mini-Circuits' CY3-453+ is a wideband MMIC Frequency Tripler, converting input frequencies from 6.66 to 15 GHz into output frequencies from 20 to 45 GHz. Its wide output range makes this model suitable for broadband systems as well as a wide variety of narrow-band applications. Utilizing GaAs HBT technology, the CY3-453+ comes housed in a 4x4mm 24-Lead QFN-Style package and offers excellent repeatability, low inductance, and good thermal efficiency.

KEY FEATURES

Features	Advantages
Broadband, 20 to 45 GHz output	With an output frequency range spanning 20 to 45 GHz, this multiplier supports broadband applications.
Excellent Fundamental and Harmonic Suppression <ul style="list-style-type: none"> • F1, 39 dBc Typ. • F2, 46 dBc Typ. • F4, 40 dBc Typ. 	Harmonic and fundamental filtering requirements are dramatically simplified due to the high suppression resulting from internal cancellation within the diode configuration.
Wide input power range +12 to +17 dBm	Wide input power signal range accommodates different input signal levels while still maintain a low conversion loss.





MMIC SURFACE MOUNT

X3 Frequency Multiplier

CY3-453+

50Ω Output 20 to 45 GHz

ELECTRICAL SPECIFICATIONS^{1,3} AT +25°C AND Z₀ = 50Ω, UNLESS NOTED OTHERWISE

Parameter		Input Frequency (GHz)	Min.	Typ.	Max.	Unit
Multiplication Factor			3			
Frequency Range, Input (F1)			6.66		15	GHz
Frequency Range, Output (F3)			20		45	GHz
Input Power			+12	+16	+17	dBm
Conversion Loss (F3)		6.66-8		20.1	22.0	dB
		8-10		19.8	21.6	
		10-12		19.4	21.4	
		12-15		21.0	23.7	
Harmonic Output ^{2,3}	F1	6.66-8		40		dBc
		8-10		43		
		10-12		45		
		12-15		27		
	F2	6.66-8		58		dBc
		8-10		42		
		10-12		49		
		12-15		38		
	F4	6.66-8		30		dBc
		8-10		47		
		10-12		41		
		12-15		43		






1. Measured on Mini-Circuits Characterization Test Board TB-CY3-453C+.

2. Harmonics of input frequency below power of F3.

3. All specifications are measured with RF input power = +16 dBm.




TYPICAL PERFORMANCE GRAPHS






TYPICAL PERFORMANCE GRAPHS


CONVERSION LOSS X3 OUTPUT vs. TEMPERATURE
RF IN = +15dBm




HARMONIC X1 OUTPUT vs. TEMPERATURE
RF IN = +15dBm



HARMONIC X2 OUTPUT vs. TEMPERATURE
RF IN = +15dBm




HARMONIC X4 OUTPUT vs. TEMPERATURE
RF IN = +15dBm






TYPICAL PERFORMANCE GRAPHS


CONVERSION LOSS X3 OUTPUT vs. TEMPERATURE
RF IN = +16dBm




HARMONIC X1 OUTPUT vs. TEMPERATURE
RF IN = +16dBm



HARMONIC X2 OUTPUT vs. TEMPERATURE
RF IN = +16dBm




HARMONIC X4 OUTPUT vs. TEMPERATURE
RF IN = +16dBm






TYPICAL PERFORMANCE GRAPHS


CONVERSION LOSS X3 OUTPUT vs. TEMPERATURE
RF IN = +17dBm




HARMONIC X1 OUTPUT vs. TEMPERATURE
RF IN = +17dBm



HARMONIC X2 OUTPUT vs. TEMPERATURE
RF IN = +17dBm



HARMONIC X4 OUTPUT vs. TEMPERATURE
RF IN = +17dBm





ABSOLUTE MAXIMUM RATINGS⁵

Parameter	Ratings
Operating Temperature (ground lead)	-40°C to +85°C
Storage Temperature	-65°C to +150°C
RF Input Power	+26 dBm (5 minute max) +23 dBm (Continuous)

5. Permanent damage may occur if any of these limits are exceeded. Electrical maximum ratings are not intended for continuous normal operation.

ESD RATING

	Class	Voltage Range	Reference Standard
HBM	1B	500V to < 1000V	ANSI/ESDA/JEDEC JS-001-2017
CDM	C2	500V to < 1000V	JESD22-C101F




ESD HANDLING PRECAUTION: This device is designed to be Class 1B for HBM. Static charges may easily produce potentials higher than this with improper handling and can discharge into DUT and damage it. As a preventive measure Industry standard ESD handling precautions should be used at all times to protect the device from ESD damage.

MSL RATING

Moisture Sensitivity: MSL1 in accordance with IPC/JEDEC J-STD-020E/JEDEC J-STD-033C



FUNCTIONAL DIAGRAM



PAD DESCRIPTION

Function	Pad Number	Description (Refer to Fig 1)
RF-IN	20	RF-IN Pad connects to RF Input Port
RF-OUT	10	RF-OUT Pad connects to RF Output Port
GND	9, 11, & Paddle	Connects to ground
NC	1-8, 12-19, 21-24	Not used internally. Connected to ground on test board

Figure 1. CY3-453+ Functional Diagram

APPLICATION AND CHARACTERIZATION SETUP




Figure 2. Application and Characterization Setup for CY3-453+


Conversion Loss and F1, F2, F4 Harmonic Rejection are measured using N5245A PNA-X microwave network analyzer.

Condition:

1. Conversion Loss and Harmonic Rejection: $P_{IN} = +16$ dBm




CASE STYLE DRAWING



Weight: .04 Grams
Dimensions are in inches [mm]. Tolerances: 2 Pl. ± .01; 3 Pl. ± .005

PRODUCT MARKING



Marking may contain other features or characters for internal lot control



MMIC SURFACE MOUNT

X3 Frequency Multiplier

CY3-453+

 Mini-Circuits

50Ω Output 20 to 45 GHz

ADDITIONAL DETAILED INFORMATION IS AVAILABLE ON OUR DASH BOARD

[CLICK HERE](#)

Performance Data	Data Table Swept Graphs
Case Style	DG1847. Plastic package, exposed paddle, Lead Finish: Matte-Tin
RoHs Status	Compliant
Tape & Reel Standard quantities available on reel	F68 7" reels with 20, 50, 100, 200, 500, 1K or 2K devices
Suggested Layout for PCB Design	PL-732
Evaluation Board	TB-CY3-453C+
Environmental Ratings	ENV08T1

NOTES

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the standard terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/terms/viewterm.html



Typical Performance Data

TEST CONDITION: RF IN = +15dBm

Frequency (GHz)				Temperature = -40°C			
X1 Output	X2 Output	X3 Output	X4 Output	Conversion Loss	Harmonic Output*		
				X3 Output	X1 Output	X2 Output	X4 Output
6.6	13.2	19.8	26.4	18.24	45.85	66.03	30.95
7.0	14.0	21.0	28.0	18.76	44.62	62.13	31.63
7.5	15.0	22.5	30.0	18.99	43.85	62.41	32.10
8.0	16.0	24.0	32.0	18.63	44.27	59.94	36.47
8.5	17.0	25.5	34.0	18.94	44.74	44.79	40.48
9.0	18.0	27.0	36.0	18.62	46.83	42.10	46.42
9.5	19.0	28.5	38.0	18.43	47.61	43.52	49.08
10.0	20.0	30.0	40.0	18.23	49.63	45.71	47.72
10.5	21.0	31.5	42.0	18.48	51.75	47.99	43.37
11.0	22.0	33.0	44.0	18.26	54.08	58.86	42.78
11.5	23.0	34.5	46.0	18.97	43.90	58.09	40.94
12.0	24.0	36.0	48.0	19.08	41.41	59.44	41.67
12.5	25.0	37.5	50.0	19.62	38.65	44.25	43.77
13.0	26.0	39.0	52.0	20.31	32.70	40.70	44.43
13.5	27.0	40.5	54.0	20.35	30.69	36.09	45.93
14.0	28.0	42.0	56.0	20.55	27.09	34.85	52.46
14.5	29.0	43.5	58.0	21.01	25.07	32.26	54.59
15.0	30.0	45.0	60.0	21.31	22.77	30.77	50.65

* Harmonic Output below power level of X3 Output

Frequency (GHz)				Temperature = +25°C			
X1 Output	X2 Output	X3 Output	X4 Output	Conversion Loss	Harmonic Output*		
				X3 Output	X1 Output	X2 Output	X4 Output
6.6	13.2	19.8	26.4	19.33	44.74	64.38	30.96
7.0	14.0	21.0	28.0	19.84	43.67	61.13	31.65
7.5	15.0	22.5	30.0	19.99	43.13	61.99	32.46
8.0	16.0	24.0	32.0	19.66	43.57	57.89	36.98
8.5	17.0	25.5	34.0	19.90	44.24	42.97	41.66
9.0	18.0	27.0	36.0	19.58	46.22	40.25	47.85
9.5	19.0	28.5	38.0	19.40	47.45	42.75	50.34
10.0	20.0	30.0	40.0	19.21	49.29	44.40	48.91
10.5	21.0	31.5	42.0	19.45	50.89	45.81	44.76
11.0	22.0	33.0	44.0	19.24	53.13	52.73	44.59
11.5	23.0	34.5	46.0	19.89	43.07	56.93	41.96
12.0	24.0	36.0	48.0	20.03	40.22	57.63	42.85
12.5	25.0	37.5	50.0	20.52	37.76	46.75	44.74
13.0	26.0	39.0	52.0	21.23	31.78	43.09	45.08
13.5	27.0	40.5	54.0	21.24	29.88	37.84	45.65
14.0	28.0	42.0	56.0	21.52	26.38	36.55	51.77
14.5	29.0	43.5	58.0	22.08	24.50	33.78	58.27
15.0	30.0	45.0	60.0	22.42	22.30	32.29	52.79

* Harmonic Output below power level of X3 Output

Frequency (GHz)				Temperature = +85°C			
X1 Output	X2 Output	X3 Output	X4 Output	Conversion Loss	Harmonic Output*		
				X3 Output	X1 Output	X2 Output	X4 Output
6.6	13.2	19.8	26.4	20.25	43.79	63.35	30.94
7.0	14.0	21.0	28.0	20.73	42.88	60.18	31.68
7.5	15.0	22.5	30.0	20.83	42.51	61.71	32.69
8.0	16.0	24.0	32.0	20.53	42.97	56.18	37.32
8.5	17.0	25.5	34.0	20.71	43.74	41.59	42.73
9.0	18.0	27.0	36.0	20.38	45.79	38.95	49.13
9.5	19.0	28.5	38.0	20.21	47.27	41.99	51.67
10.0	20.0	30.0	40.0	20.01	49.13	43.40	49.68
10.5	21.0	31.5	42.0	20.26	50.03	44.03	46.16
11.0	22.0	33.0	44.0	20.06	51.97	49.11	46.33
11.5	23.0	34.5	46.0	20.64	42.20	52.52	43.01
12.0	24.0	36.0	48.0	20.80	39.21	53.31	43.89
12.5	25.0	37.5	50.0	21.27	36.83	50.69	45.39
13.0	26.0	39.0	52.0	21.95	30.96	46.54	45.13
13.5	27.0	40.5	54.0	21.97	29.21	40.08	44.71
14.0	28.0	42.0	56.0	22.33	25.71	38.48	51.48
14.5	29.0	43.5	58.0	22.95	24.00	35.29	62.86
15.0	30.0	45.0	60.0	23.35	21.95	33.44	54.59

* Harmonic Output below power level of X3 Output

Typical Performance Data

TEST CONDITION: RF IN = +16dBm

Frequency (GHz)				Temperature = -40°C			
X1 Output	X2 Output	X3 Output	X4 Output	Conversion Loss	Harmonic Output*		
				X3 Output	X1 Output	X2 Output	X4 Output
6.6	13.2	19.8	26.4	18.67	45.33	64.34	30.90
7.0	14.0	21.0	28.0	19.29	44.16	61.00	31.68
7.5	15.0	22.5	30.0	19.51	43.59	61.80	33.02
8.0	16.0	24.0	32.0	19.10	44.19	60.92	39.32
8.5	17.0	25.5	34.0	19.29	44.82	44.98	44.64
9.0	18.0	27.0	36.0	18.86	47.06	42.88	56.11
9.5	19.0	28.5	38.0	18.58	47.97	42.40	51.26
10.0	20.0	30.0	40.0	18.31	50.08	43.01	47.46
10.5	21.0	31.5	42.0	18.52	52.05	46.48	43.89
11.0	22.0	33.0	44.0	18.28	54.13	50.37	44.10
11.5	23.0	34.5	46.0	18.79	44.10	51.65	41.21
12.0	24.0	36.0	48.0	18.89	41.49	51.32	41.55
12.5	25.0	37.5	50.0	19.37	38.78	43.25	44.03
13.0	26.0	39.0	52.0	20.06	32.81	40.64	42.85
13.5	27.0	40.5	54.0	20.18	30.83	36.35	40.75
14.0	28.0	42.0	56.0	20.22	27.50	35.13	43.08
14.5	29.0	43.5	58.0	20.79	25.54	33.16	52.60
15.0	30.0	45.0	60.0	21.14	23.34	31.43	58.33

* Harmonic Output below power level of X3 Output

Frequency (GHz)				Temperature = +25°C			
X1 Output	X2 Output	X3 Output	X4 Output	Conversion Loss	Harmonic Output*		
				X3 Output	X1 Output	X2 Output	X4 Output
6.6	13.2	19.8	26.4	19.81	44.18	63.09	30.64
7.0	14.0	21.0	28.0	20.40	43.18	60.01	31.48
7.5	15.0	22.5	30.0	20.54	42.83	61.13	33.05
8.0	16.0	24.0	32.0	20.14	43.45	59.34	39.47
8.5	17.0	25.5	34.0	20.28	44.25	43.56	45.67
9.0	18.0	27.0	36.0	19.87	46.36	41.74	59.62
9.5	19.0	28.5	38.0	19.60	47.73	42.27	50.64
10.0	20.0	30.0	40.0	19.35	49.61	42.60	47.54
10.5	21.0	31.5	42.0	19.57	51.01	46.05	44.79
11.0	22.0	33.0	44.0	19.34	53.04	51.59	45.64
11.5	23.0	34.5	46.0	19.83	43.12	54.95	41.92
12.0	24.0	36.0	48.0	19.94	40.21	56.06	42.38
12.5	25.0	37.5	50.0	20.40	37.77	45.64	44.39
13.0	26.0	39.0	52.0	21.09	31.79	43.21	42.81
13.5	27.0	40.5	54.0	21.16	29.94	38.35	40.74
14.0	28.0	42.0	56.0	21.32	26.67	37.11	44.97
14.5	29.0	43.5	58.0	21.95	24.85	34.77	53.87
15.0	30.0	45.0	60.0	22.32	22.79	32.91	60.92

* Harmonic Output below power level of X3 Output

Frequency (GHz)				Temperature = +85°C			
X1 Output	X2 Output	X3 Output	X4 Output	Conversion Loss	Harmonic Output*		
				X3 Output	X1 Output	X2 Output	X4 Output
6.6	13.2	19.8	26.4	20.77	43.22	61.86	30.48
7.0	14.0	21.0	28.0	21.32	42.37	59.05	31.38
7.5	15.0	22.5	30.0	21.40	42.17	60.63	33.09
8.0	16.0	24.0	32.0	21.04	42.79	57.62	39.62
8.5	17.0	25.5	34.0	21.13	43.71	42.31	46.65
9.0	18.0	27.0	36.0	20.72	45.85	40.68	61.74
9.5	19.0	28.5	38.0	20.47	47.49	41.95	50.13
10.0	20.0	30.0	40.0	20.22	49.40	42.22	47.30
10.5	21.0	31.5	42.0	20.44	50.09	45.35	45.55
11.0	22.0	33.0	44.0	20.23	51.78	51.87	47.05
11.5	23.0	34.5	46.0	20.68	42.15	58.70	42.69
12.0	24.0	36.0	48.0	20.80	39.10	59.35	42.95
12.5	25.0	37.5	50.0	21.25	36.75	49.29	44.21
13.0	26.0	39.0	52.0	21.92	30.88	47.09	42.57
13.5	27.0	40.5	54.0	21.97	29.20	40.99	40.42
14.0	28.0	42.0	56.0	22.24	25.89	39.42	46.41
14.5	29.0	43.5	58.0	22.91	24.24	36.31	55.90
15.0	30.0	45.0	60.0	23.32	22.35	33.89	59.32

* Harmonic Output below power level of X3 Output

Typical Performance Data

TEST CONDITION: RF IN = +17dBm

Frequency (GHz)				Temperature = -40°C			
X1 Output	X2 Output	X3 Output	X4 Output	Conversion Loss	Harmonic Output*		
				X3 Output	X1 Output	X2 Output	X4 Output
6.6	13.2	19.8	26.4	19.22	44.64	62.56	30.38
7.0	14.0	21.0	28.0	19.91	43.56	59.62	31.29
7.5	15.0	22.5	30.0	20.14	43.17	60.29	33.52
8.0	16.0	24.0	32.0	19.67	43.95	62.12	42.67
8.5	17.0	25.5	34.0	19.76	44.73	44.56	46.90
9.0	18.0	27.0	36.0	19.27	47.09	41.77	49.08
9.5	19.0	28.5	38.0	18.92	48.12	39.06	45.78
10.0	20.0	30.0	40.0	18.58	50.32	39.42	44.72
10.5	21.0	31.5	42.0	18.78	52.12	43.12	42.47
11.0	22.0	33.0	44.0	18.56	53.98	44.27	43.40
11.5	23.0	34.5	46.0	18.92	44.00	45.14	40.92
12.0	24.0	36.0	48.0	19.01	41.32	46.11	40.26
12.5	25.0	37.5	50.0	19.43	38.65	42.04	42.70
13.0	26.0	39.0	52.0	20.12	32.65	40.30	40.69
13.5	27.0	40.5	54.0	20.30	30.72	36.73	37.47
14.0	28.0	42.0	56.0	20.23	27.61	35.14	39.18
14.5	29.0	43.5	58.0	20.83	25.74	33.98	47.60
15.0	30.0	45.0	60.0	21.20	23.66	32.14	68.46

* Harmonic Output below power level of X3 Output

Frequency (GHz)				Temperature = +25°C			
X1 Output	X2 Output	X3 Output	X4 Output	Conversion Loss	Harmonic Output*		
				X3 Output	X1 Output	X2 Output	X4 Output
6.6	13.2	19.8	26.4	20.39	43.51	61.36	29.98
7.0	14.0	21.0	28.0	21.04	42.59	58.66	30.98
7.5	15.0	22.5	30.0	21.17	42.40	59.51	33.29
8.0	16.0	24.0	32.0	20.72	43.17	60.80	42.34
8.5	17.0	25.5	34.0	20.78	44.12	43.25	46.51
9.0	18.0	27.0	36.0	20.31	46.35	41.37	48.15
9.5	19.0	28.5	38.0	19.98	47.82	38.78	44.99
10.0	20.0	30.0	40.0	19.67	49.78	39.08	43.95
10.5	21.0	31.5	42.0	19.87	51.02	43.27	42.59
11.0	22.0	33.0	44.0	19.66	52.79	44.99	44.32
11.5	23.0	34.5	46.0	20.03	42.93	46.05	41.20
12.0	24.0	36.0	48.0	20.11	39.97	48.21	40.79
12.5	25.0	37.5	50.0	20.54	37.56	44.09	42.55
13.0	26.0	39.0	52.0	21.22	31.58	43.19	40.52
13.5	27.0	40.5	54.0	21.33	29.79	39.08	37.61
14.0	28.0	42.0	56.0	21.41	26.70	37.57	41.61
14.5	29.0	43.5	58.0	22.06	24.97	35.75	49.53
15.0	30.0	45.0	60.0	22.43	23.05	33.57	66.51

* Harmonic Output below power level of X3 Output

Frequency (GHz)				Temperature = +85°C			
X1 Output	X2 Output	X3 Output	X4 Output	Conversion Loss	Harmonic Output*		
				X3 Output	X1 Output	X2 Output	X4 Output
6.6	13.2	19.8	26.4	21.38	42.53	60.32	29.76
7.0	14.0	21.0	28.0	21.98	41.73	57.68	30.87
7.5	15.0	22.5	30.0	22.05	41.71	58.85	33.20
8.0	16.0	24.0	32.0	21.64	42.46	59.22	42.28
8.5	17.0	25.5	34.0	21.65	43.50	42.09	46.42
9.0	18.0	27.0	36.0	21.20	45.76	40.88	47.10
9.5	19.0	28.5	38.0	20.88	47.52	38.46	44.15
10.0	20.0	30.0	40.0	20.59	49.46	38.78	43.28
10.5	21.0	31.5	42.0	20.80	49.95	43.42	42.65
11.0	22.0	33.0	44.0	20.59	51.43	45.81	44.77
11.5	23.0	34.5	46.0	20.95	41.90	47.11	41.52
12.0	24.0	36.0	48.0	21.04	38.80	50.99	41.15
12.5	25.0	37.5	50.0	21.46	36.48	46.94	42.32
13.0	26.0	39.0	52.0	22.12	30.62	47.69	40.22
13.5	27.0	40.5	54.0	22.21	29.00	42.36	37.60
14.0	28.0	42.0	56.0	22.40	25.84	40.54	43.75
14.5	29.0	43.5	58.0	23.08	24.29	37.50	51.93
15.0	30.0	45.0	60.0	23.48	22.55	34.32	63.24

* Harmonic Output below power level of X3 Output

Typical Performance Data






TEST CONDITION: RF IN = +12 to 14dBm

Frequency (GHz)				Temperature = +25°C		
X1 Output	X2 Output	X3 Output	X4 Output	Conversion Loss		
				12dBm	13dBm	14dBm
6.6	13.2	19.8	26.4	19.21	18.93	19.01
7.0	14.0	21.0	28.0	19.22	19.18	19.42
7.5	15.0	22.5	30.0	19.27	19.29	19.55
8.0	16.0	24.0	32.0	19.27	19.17	19.32
8.5	17.0	25.5	34.0	19.80	19.60	19.65
9.0	18.0	27.0	36.0	19.86	19.50	19.43
9.5	19.0	28.5	38.0	20.15	19.59	19.37
10.0	20.0	30.0	40.0	20.22	19.53	19.24
10.5	21.0	31.5	42.0	20.84	19.96	19.54
11.0	22.0	33.0	44.0	20.90	19.90	19.41
11.5	23.0	34.5	46.0	22.28	20.96	20.23
12.0	24.0	36.0	48.0	22.68	21.24	20.44
12.5	25.0	37.5	50.0	23.51	21.94	20.98
13.0	26.0	39.0	52.0	24.49	22.77	21.73
13.5	27.0	40.5	54.0	24.02	22.59	21.67
14.0	28.0	42.0	56.0	24.72	23.16	22.10
14.5	29.0	43.5	58.0	24.43	23.29	22.50
15.0	30.0	45.0	60.0	24.36	23.43	22.78

* Harmonic Output below power level of X3 Output

Typical Performance Curves


Note: Harmonics data is presented as the harmonic of input frequency below the power of F3




Typical Performance Curves

Note: Harmonics data is presented as the harmonic of input frequency below the power of F3


CONVERSION LOSS X3 OUTPUT vs. TEMPERATURE
RF IN = +15dBm




HARMONIC X1 OUTPUT vs. TEMPERATURE
RF IN = +15dBm



HARMONIC X2 OUTPUT vs. TEMPERATURE
RF IN = +15dBm




HARMONIC X4 OUTPUT vs. TEMPERATURE
RF IN = +15dBm




Typical Performance Curves

Note: Harmonics data is presented as the harmonic of input frequency below the power of F3


CONVERSION LOSS X3 OUTPUT vs. TEMPERATURE
RF IN = +16dBm




HARMONIC X1 OUTPUT vs. TEMPERATURE
RF IN = +16dBm



HARMONIC X2 OUTPUT vs. TEMPERATURE
RF IN = +16dBm




HARMONIC X4 OUTPUT vs. TEMPERATURE
RF IN = +16dBm




Typical Performance Curves

Note: Harmonics data is presented as the harmonic of input frequency below the power of F3


CONVERSION LOSS X3 OUTPUT vs. TEMPERATURE
RF IN = +17dBm




HARMONIC X1 OUTPUT vs. TEMPERATURE
RF IN = +17dBm



HARMONIC X2 OUTPUT vs. TEMPERATURE
RF IN = +17dBm




HARMONIC X4 OUTPUT vs. TEMPERATURE
RF IN = +17dBm



Tape & Reel Packaging TR-F68

DEVICE ORIENTATION IN T&R



Tape Width, mm	Device Cavity Pitch, mm	Reel Size, inches	Devices per Reel see note	
12	8	7	Small quantity standard	20
				50
				100
				200
				500
		7	Standard	1000
		13	Standard	2000
				3000
4000				

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: www.minicircuits.com/pages/pdfs/tape.pdf




INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified


THIRD ANGLE PROJECTION



REVISIONS

REV	ECN No.	DESCRIPTION	DATE	DR	AUTH
OR	ECO-013714	NEW RELEASE	06/13/22	ITG	IL

SUGGESTED MOUNTING CONFIGURATION FOR
DG1847 CASE STYLE



NOTES:

1. TRACE WIDTH AND GAP PARAMETERS ARE SHOWN FOR ROGERS RO4003 WITH DIELECTRIC THICKNESS $.008 \pm .0007$ "; COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH AND GAP MAY NEED TO BE MODIFIED.
2. UNIT FOOT PRINT IS OPTIMIZED FOR PERFORMANCE AND IS DIFFERENT FROM CASE STYLE DG1847 RECOMMENDATIONS.
3. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.



DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER).



DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK.

UNLESS OTHERWISE SPECIFIED	INITIALS		DATE
DIMENSIONS ARE IN INCHES	DRAWN	ITG	06/13/22
TOLERANCES ON:	CHECKED	GF	06/13/22
2 PL DECIMALS ±	APPROVED	IL	06/13/22
3 PL DECIMALS ± .005			
ANGLES ±			
FRACTIONS ±			



Mini-Circuits[®]

13 Neptune Avenue
Brooklyn NY 11235



PL, DG1847, TB-CY3-223(C)+

Mini-Circuits[®]
THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.

SIZE	CODE IDENT	DRAWING NO:	REV:
A	15542	98-PL-732	OR
FILE:	98PL732	SCALE: 8:1	SHEET: 1 OF 1


Evaluation Board and Circuit

SEE DETAIL "A"



INDEX

DETAIL "A"
(SCALE 3:1)



SCHEMATIC DIAGRAM
(SCALE 3:1)

Function	Pad
RF-IN	20
RF-OUT	10
GND	9,11
NC (Ground Externally)	1-8,12-19,21-24

NOTES:

- 1.85mm Female Connectors.
- PCB Material: Roger R04003C or equivalent, Dielectric constant=3.5, Thickness=0.008 inch

 Mini-Circuits®

All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-40° to 85° C or -45° to 85° C or -55° to 105° C or -40° to 105° C or -40° to 95° C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C or -65° to 150° Ambient Environment	Individual Model Data Sheet
HTOL	1000 hours at 125°C	MIL-STD-883, Method 1005, Condition B
Thermal Shock	-55° to 100°C, 100 cycles	MIL-STD-202, Method 107, Condition A-3, except +100°C
Mechanical Shock	1.5Kg, 0.5 ms, 5 shock pulses, Y1 direction only	MIL-STD-883, Method 2002, Condition B, except Y1 direction only
Vibration (Variable Frequency)	50g peak	MIL-STD-883, Method 2007, Condition B
Autoclave	15 psig, 100% RH, 121°C, 96 hours	JESD22-A102, Condition C
HAST	130°C, 85% RH, 96 hours	JESD22-A110
Solderability	10X Magnification	J-STD-002, Para 4.2.5, Test S, 95% Coverage
Solder Reflow Heat	Sn-Pb Eutetic Process: 240°C peak Pb-Free Process: 260°C peak	J-STD-020, Table 4-1, 4-2 and 5-2; Figure 5-1
Moisture Sensitivity: Level 1	Bake at 125°C for 24 hours Soak at 85°C/85% RH for 168 hours, Reflow 3 cycles at 260°C peak	J-STD-020



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Marking Resistance to Solvents	Isopropyl alcohol + mineral spirits at 25°C; terpene defluxer at 25°C; distilled water + proylene glycol monomethyl ether + monoethanolamine at 63°C to 70°C	MIL-STD-202, Method 215