

# Surface Mount Digital Step Attenuator

## DAT-3175A Series

75Ω 0 to 31 dB, 1.0 dB Step 1MHz to 2.5 GHz

### The Big Deal

- Wideband, operates up to 2.5 GHz
- Glitchless attenuation transitions
- High IP3, 52 dBm



CASE STYLE: DG983-2

### Product Overview

The DAT-3175A+ series of 75Ω digital step attenuators provides adjustable attenuation from 0 to 31 dB in 1.0 dB steps. The control is a 5-bit serial/parallel interface, and the attenuators operate with either single positive or dual (positive and negative) supply voltage. DAT-3175A+ series models are produced by a unique CMOS process on silicon, offering the performance of GaAs with the advantages of conventional CMOS devices.

### Key Features

| Feature                                                                                                            | Advantages                                                                                                                                                                                                                      |
|--------------------------------------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Wideband operation, specified from 1MHz to 2.5 GHz                                                                 | Can be used in multiple applications such as various versions of DOCSIS, satellite and defense, reducing part count.                                                                                                            |
| Serial or parallel interface                                                                                       | Models available with serial or parallel interface mode to suit customer demand.                                                                                                                                                |
| Good VSWR, 1.3:1 typ.                                                                                              | Eases interfacing with adjacent components and results in low amplitude ripple.                                                                                                                                                 |
| Single positive supply models:<br>(Model suffixes: -SP+ and -PP+)<br>+2.3 to +3.6V+                                | Use of single positive supply simplifies power supply design. An internal negative voltage generator supplies the desired negative voltage. Single positive supply results in excellent spurious performance, -140 dBm typical. |
| Dual supply models:<br>(Model suffixes: -SN+ and -PN+)<br>+2.7 to +3.6V (Positive) and<br>-3.6 to -3.2V (Negative) | Dual supply provides spurious-free operation. It also allows fast switching up to 1 MHz (vs. 25 kHz for single supply).                                                                                                         |
| Useable over a wide range of supply voltages, +2.3/2.7 to 5.2V                                                     | Wide range of positive operating voltages allows the DAT-3175A+ Series of models to be used in a wide range of applications. See Application Note AN-70-032 for operation above +3.6V                                           |
| Footprint compatible to DAT-3175-XX+ Series (XX=SN/SP/PN/PP)                                                       | Can fit into existing footprint and provide wideband performance, to 2.5 GHz instead of 2.0 GHz.                                                                                                                                |
| Glitchless Attenuation Transitions, 0.26 typical                                                                   | Compared to previous generation of digital attenuators which is a vast improvement.                                                                                                                                             |



# Digital Step Attenuator

75Ω 1-2500 MHz

31 dB, 1.0 dB Step

5 Bit, Serial Control Interface, Dual Supply Voltages

## Product Features

- Dual Supply (Positive & Negative) Voltages
- Immune to latch up
- Glitchless attenuation transitions
- Excellent accuracy, 0.1 dB Typ
- Low Insertion Loss
- High IP3, +55-59 dBm Typ
- Very low DC power consumption
- Excellent return loss, 18 dB Typ
- Small size 4.0 x 4.0 mm

## Typical Applications

- DOCSIS® 3.1
- Portable Wireless
- CATV & DBS
- MMDS & Wireless LAN
- Wireless Local Loop
- UNII & Hiper LAN
- Power amplifier distortion canceling loops



*Generic photo used for illustration purposes only*

## DAT-3175A-SN+

CASE STYLE: DG983-2


### +RoHS Compliant

*The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications*

## General Description

The DAT-3175A-SN+ is a 75Ω RF digital step attenuator that offers an attenuation range up to 31 dB in 1.0 dB steps. The control is a 5-bit serial interface, operating dual (positive and negative) supply voltages. The DAT-3175A-SN+ is produced using a unique CMOS process on silicon, offering the performance of GaAs, with the advantages of conventional CMOS devices.

## Simplified Schematic



[www.minicircuits.com](http://www.minicircuits.com) P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 [sales@minicircuits.com](mailto:sales@minicircuits.com)

REV. OR  
M155582  
DAT-3175A-SN+  
RS/CP/AM  
200513  
Page 2 of 8

RF Electrical Specifications, 1-2500 MHz,  $T_{AMB}=25^{\circ}\text{C}$ ,  $V_{DD}=+3\text{V}$ ,  $V_{SS}=-3.2\text{V}$ ,  $75\Omega$ 

| Parameter                                                      | Freq. Range (GHz) | Min. | Typ.       | Max.       | Units                |
|----------------------------------------------------------------|-------------------|------|------------|------------|----------------------|
| Accuracy @ 1 dB Attenuation Setting                            | 0.001-1.2         | —    | 0.03       | 0.18       | dB                   |
|                                                                | 1.2-2.0           | —    | 0.1        | 0.20       |                      |
|                                                                | 2.0-2.5           | —    | 0.1        | 0.23       |                      |
| Accuracy @ 2 dB Attenuation Setting                            | 0.001-1.2         | —    | 0.07       | 0.21       | dB                   |
|                                                                | 1.2-2.0           | —    | 0.15       | 0.26       |                      |
|                                                                | 2.0-2.5           | —    | 0.15       | 0.31       |                      |
| Accuracy @ 4 dB Attenuation Setting                            | 0.001-1.2         | —    | 0.05       | 0.27       | dB                   |
|                                                                | 1.2-2.0           | —    | 0.15       | 0.36       |                      |
|                                                                | 2.0-2.5           | —    | 0.2        | 0.47       |                      |
| Accuracy @ 8 dB Attenuation Setting                            | 0.001-1.2         | —    | 0.1        | 0.39       | dB                   |
|                                                                | 1.2-2.0           | —    | 0.24       | 0.60       |                      |
|                                                                | 2.0-2.5           | —    | 0.35       | 0.79       |                      |
| Accuracy @ 16 dB Attenuation Setting                           | 0.001-1.2         | —    | 0.23       | 0.63       | dB                   |
|                                                                | 1.2-2.5           | —    | 0.8        | 1.0        |                      |
|                                                                | 2.0-2.5           | —    | 0.8        | 1.43       |                      |
| Insertion Loss <sup>1</sup> @ all attenuator set to 0dB        | 0.001-1.2         | —    | 1.2        | 1.8        | dB                   |
|                                                                | 1.2-2.5           | —    | 1.6        | 1.9        |                      |
| VSWR                                                           | 0.001-1.2         | —    | 1.3        | —          | :1                   |
|                                                                | 1.2-2.5           | —    | 1.4        | —          |                      |
| Input IP3 (at Min. and Max. Attenuation)                       | .005-2.5          | —    | 55-69      | —          | dBm                  |
| Input IP2                                                      | .005-2.5          | —    | See Fig. 1 | —          | dBm                  |
| Input Power @ 0.1dB Compression (at Min. and Max. Attenuation) | 0.030-2.5         | —    | +30        | —          | dBm                  |
| Input Operating Power                                          | 1 MHz to 30 MHz   | —    | —          | See Fig. 2 | dBm                  |
|                                                                | >30 MHz           | —    | —          | +24        |                      |
| Thermal Resistance (Junction to case)                          | —                 | —    | 25         | —          | $^{\circ}\text{C/W}$ |

## DC Electrical Specifications

| Parameter                 | Min. | Typ. | Max.             | Units         |
|---------------------------|------|------|------------------|---------------|
| $V_{DD}$ , Supply Voltage | 2.7  | 3    | 3.6 <sup>2</sup> | V             |
| $I_{DD}$ Supply Current   | —    | —    | 80               | $\mu\text{A}$ |
| Control Input Low         | -0.3 | —    | 0.6 <sup>3</sup> | V             |
| $V_{SS}$ , Supply Voltage | -3.6 | —    | -3.2             | V             |
| $I_{SS}$ , Supply Current | -40  | —    | —                | $\mu\text{A}$ |
| Control Input High        | 1.17 | —    | 3.6              | V             |
| Control Current           | —    | —    | 20               | $\mu\text{A}$ |

1. I. Loss values are de-embedded from test board Loss (test board's Insertion Loss: 0.10dB @ 100MHz, 0.40dB @ 1200MHz, 0.55dB @ 2000MHz, 0.75dB @ 4000MHz).  
 2. For operation above +3.6V see application note, AN-70-032  
 3. 0V during power-up.

Absolute Maximum Ratings<sup>4</sup>

| Parameter             | Ratings                                          |
|-----------------------|--------------------------------------------------|
| Operating Temperature | -40 $^{\circ}\text{C}$ to 105 $^{\circ}\text{C}$ |
| Storage Temperature   | -65 $^{\circ}\text{C}$ to 150 $^{\circ}\text{C}$ |
| $V_{DD}$              | -0.3V Min., 5.5V Max.                            |
| $V_{SS}$              | -3.8V Min.                                       |
| Voltage on any input  | -0.3V Min., 3.6V Max.                            |
| Input Power           | 1-30 MHz Figure 2                                |
|                       | 30-2500MHz +30dBm                                |

4. Permanent damage may occur if any of these limits are exceeded.  
 5. Operation between max operating and absolute max input power will result in reduced reliability.

## Switching Specifications

| Parameter                                                  | Min. | Typ. | Max. | Units           |
|------------------------------------------------------------|------|------|------|-----------------|
| Switching Speed, 50% Control to 0.5dB of Attenuation Value | —    | 0.4  | 0.7  | $\mu\text{Sec}$ |
| Switching Control Frequency                                | —    | 1.0  | —    | MHz             |




Figure 1. IP2 vs. frequency and attenuation


## Pin Description

| Function        | Pin Number | Description                                   |
|-----------------|------------|-----------------------------------------------|
| C16             | 1          | Control for Attenuation bit, 16dB (Notes 4,7) |
| RF in           | 2          | RF in port (Note 1)                           |
| Data            | 3          | Serial Interface data input (Note 3)          |
| Clock           | 4          | Serial Interface clock input                  |
| LE              | 5          | Latch Enable Input (Note 2)                   |
| V <sub>DD</sub> | 6          | Power Supply                                  |
| N/C             | 7          | Not connected                                 |
| N/C             | 8          | Not connected                                 |
| V <sub>DD</sub> | 9          | Power Supply                                  |
| GND             | 10         | Ground connection                             |
| GND             | 11         | Ground connection                             |
| V <sub>SS</sub> | 12         | Negative supply voltage                       |
| V <sub>DD</sub> | 13         | Power Supply                                  |
| RF out          | 14         | RF out port (Note 1)                          |
| C8              | 15         | Control for attenuation bit, 8 dB (Note 4)    |
| C4              | 16         | Control for attenuation bit, 4 dB (Note 4)    |
| C2              | 17         | Control for attenuation bit, 2 dB (Note 4)    |
| GND             | 18         | Ground Connection                             |
| C1              | 19         | Control for attenuation bit, 1 dB (Note 4)    |
| N/C             | 20         | Not connected (Note 7,8)                      |
| GND             | Paddle     | Paddle ground (Note 6)                        |



### Notes:

- Both RF ports must be held at 0VDC or DC blocked with an external series capacitor.
- Latch Enable (LE) has an internal 2M $\Omega$  resistor to V<sub>DD</sub>.
- Place a 10K $\Omega$  resistor in series, as close to pin as possible to avoid freq. resonance.
- Refer to Power-up Control Settings.
- The exposed solder pad on the bottom of the package (See Pin configuration) must be grounded for proper device operation.
- Ground must be less than 80 mil (0.08") from Pin 12 for proper device operation.
- This pin has internal 1M $\Omega$  pull down resistor to ground.
- Place 10K $\Omega$  resistor to ground externally.

## Pin Configuration (Top View)




## Device Marking



Pulsed Power: 5% duty cycle, 4620  $\mu$ S period

## Simplified Schematic



The DAT-3175A-SN+ serial interface consists of 5 control bits that select the desired attenuation state, as shown in Table 1: Truth Table

| Table 1. Truth Table |     |    |    |    |    |
|----------------------|-----|----|----|----|----|
| Attenuation State    | C16 | C8 | C4 | C2 | C1 |
| Reference            | 0   | 0  | 0  | 0  | 0  |
| 1 (dB)               | 0   | 0  | 0  | 0  | 1  |
| 2 (dB)               | 0   | 0  | 0  | 1  | 0  |
| 4 (dB)               | 0   | 0  | 1  | 0  | 0  |
| 8 (dB)               | 0   | 1  | 0  | 0  | 0  |
| 16 (dB)              | 1   | 0  | 0  | 0  | 0  |
| 31 (dB)              | 1   | 1  | 1  | 1  | 1  |

Note: Not all 32 possible combinations of C1 - C16 are shown in table


The serial interface is a 5-bit serial in, parallel-out shift register buffered by a transparent latch.

It is controlled by three CMOS-compatible signals: Data, Clock, and Latch Enable (LE). The Data and Clock inputs allow data to be serially entered into the shift register, a process that is independent of the state of the LE input.

The LE input controls the latch. When LE is HIGH, the latch is transparent and the contents of the serial shift register control the attenuator. When LE is brought LOW, data in the shift register is latched.

The shift register should be loaded while LE is held LOW to prevent the attenuator value from changing as data is entered. The LE input should then be toggled HIGH and brought LOW again, latching the new data. The timing for this operation is defined by **Figure 3** (Serial Interface Timing Diagram) and **Table 2** (Serial Interface AC Characteristics).

**Figure 3: Serial Interface Timing Diagram**



| Table 2. Serial Interface AC Characteristics |                                                  |      |      |       |
|----------------------------------------------|--------------------------------------------------|------|------|-------|
| Symbol                                       | Parameter                                        | Min. | Max. | Units |
| $f_{clk}$                                    | Serial data clock frequency (Note 1)             |      | 10   | MHz   |
| $t_{clkH}$                                   | Serial clock HIGH time                           | 30   |      | ns    |
| $t_{clkL}$                                   | Serial clock LOW time                            | 30   |      | ns    |
| $t_{LESUP}$                                  | LE set-up time after last clock falling edge     | 10   |      | ns    |
| $t_{LEPW}$                                   | LE minimum pulse width                           | 30   |      | ns    |
| $t_{SDSUP}$                                  | Serial data set-up time before clock rising edge | 10   |      | ns    |
| $t_{SDHLD}$                                  | Serial data hold time after clock falling edge   | 10   |      | ns    |

Note 1.  $f_{clk}$  verified during the functional pattern test. Serial programming sections of the functional pattern are clocked at 10MHz to verify  $f_{clk}$  specification.

The DAT-3175A-SN+, uses a common 5-bit serial word format, as shown in Table 3: 5-Bit attenuator Serial Programming Register Map.

The first bit, the MSB, corresponds to the 16-dB Step and B1 bit corresponds to the 1dB step.

| Table 3. 5-Bit attenuator Serial Programming Register Map |    |    |    |    |    |
|-----------------------------------------------------------|----|----|----|----|----|
| B5                                                        | B4 | B3 | B2 | B1 | B0 |
| C16                                                       | C8 | C4 | C2 | C1 | 0  |

↑  
MSB  
(first in)

**Note: The stop bit (B0) must always be low to prevent the attenuator from entering an unknown state.**

↑  
LSB  
(last in)


## Power-up Control Settings

The DAT-3175A-SN+ always assumes a specifiable attenuation setting on power-up, allowing a known attenuation state to be established before an initial serial control word is provided.

When the attenuator powers up, the five control bits are set to whatever data is present on the five data inputs (C1 to C16).

This allows any one of the 32 attenuation settings to be specified as the power-up state.

TB-343 Evaluation Board Schematic Diagram



Note 1: Both RF ports must be held at 0VDC or DC blocked with an external series capacitor.



TB-343

| Bill of Materials         |                                       |
|---------------------------|---------------------------------------|
| N1-N6, N11, N12, N15, N18 | Resistor 0603 10 KOhm +/- 1%          |
| N10, N16, N17, N20        | NPO Capacitor 0603 100pF +/- 5%       |
| N21                       | Tantalum Capacitor 0805 100nF +/- 10% |
| N19                       | Hex Invert Schmitt Trigger MSL1       |

\*\*N12 can be reduced to 0 Ohms

**Additional Detailed Technical Information**

additional information is available on our dash board. To access this information [click here](#)

|                                                                 |                                                                                         |
|-----------------------------------------------------------------|-----------------------------------------------------------------------------------------|
| <b>Performance Data</b>                                         | Data Table                                                                              |
|                                                                 | Swept Graphs                                                                            |
|                                                                 | S-Parameter (S2P Files) Data Set (.zip file)                                            |
| <b>Case Style</b>                                               | DG983-2 Plastic package, exposed paddle, lead finish: NiPdAu                            |
| <b>Tape &amp; Reel</b><br>Standard quantities available on reel | F87<br>7" reels with 20, 50, 100, 200, 500 Or 1000 devices<br>13" reels with 3K devices |
| <b>Suggested Layout for PCB Design</b>                          | PL-194                                                                                  |
| <b>Evaluation Board</b>                                         | TB-343                                                                                  |
| <b>Environmental Ratings</b>                                    | ENV33T1                                                                                 |


**ESD Rating**

Human Body Model (HBM): Class 1C (1000 to <2000V) in accordance with MIL-STD-883 method 3015 (pass 1500V)

Charge Device Model class C2 (500 to <1000V) per JESD22-C101

**MSL Rating**

Moisture Sensitivity: MSL1 in accordance with IPC/JEDEC J-STD-020D

**MSL Test Flow Chart****Additional Notes**

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)



# Digital Step Attenuator

# DAT-3175A-SN+

## Typical Performance Data

TEST CONDITIONS: INPUT POWER=-10dBm, Vdd=+3V, Vss = -3.2V, TEMPERATURE=-45degC

| FREQUENCY<br>(MHz) | STEP ATTENUATION* AT TTL CONTROL STATE<br>(dB) |                 |                 |                 |                 |                |               |
|--------------------|------------------------------------------------|-----------------|-----------------|-----------------|-----------------|----------------|---------------|
|                    | 00000<br>THRU LOSS                             | 00001<br>1.0 dB | 00010<br>2.0 dB | 00100<br>4.0 dB | 01000<br>8.0 dB | 10000<br>16 dB | 11111<br>31dB |
| 10                 | 0.98                                           | 1.04            | 2.05            | 4.11            | 8.17            | 16.17          | 31.20         |
| 50                 | 0.98                                           | 1.05            | 2.05            | 4.11            | 8.17            | 16.20          | 31.35         |
| 100                | 0.99                                           | 1.04            | 2.05            | 4.11            | 8.16            | 16.20          | 31.27         |
| 150                | 1.00                                           | 1.04            | 2.04            | 4.10            | 8.16            | 16.19          | 31.29         |
| 200                | 1.00                                           | 1.05            | 2.05            | 4.10            | 8.16            | 16.20          | 31.23         |
| 250                | 1.01                                           | 1.04            | 2.05            | 4.10            | 8.16            | 16.20          | 31.29         |
| 300                | 1.01                                           | 1.04            | 2.05            | 4.11            | 8.16            | 16.21          | 31.23         |
| 350                | 1.02                                           | 1.04            | 2.05            | 4.11            | 8.17            | 16.21          | 31.31         |
| 400                | 1.02                                           | 1.04            | 2.05            | 4.11            | 8.17            | 16.21          | 31.30         |
| 450                | 1.03                                           | 1.04            | 2.04            | 4.10            | 8.16            | 16.20          | 31.25         |
| 500                | 1.05                                           | 1.04            | 2.04            | 4.10            | 8.15            | 16.19          | 31.30         |
| 550                | 1.07                                           | 1.03            | 2.03            | 4.09            | 8.14            | 16.17          | 31.29         |
| 600                | 1.08                                           | 1.03            | 2.03            | 4.09            | 8.13            | 16.17          | 31.27         |
| 700                | 1.12                                           | 1.03            | 2.03            | 4.07            | 8.11            | 16.14          | 31.24         |
| 800                | 1.17                                           | 1.03            | 2.02            | 4.06            | 8.09            | 16.12          | 31.15         |
| 900                | 1.18                                           | 1.03            | 2.02            | 4.05            | 8.10            | 16.14          | 31.27         |
| 1000               | 1.21                                           | 1.03            | 2.02            | 4.05            | 8.10            | 16.17          | 31.51         |
| 1100               | 1.24                                           | 1.02            | 2.02            | 4.05            | 8.10            | 16.16          | 31.41         |
| 1200               | 1.26                                           | 1.02            | 2.01            | 4.04            | 8.08            | 16.12          | 31.06         |
| 1300               | 1.25                                           | 1.02            | 2.01            | 4.04            | 8.08            | 16.08          | 30.65         |
| 1400               | 1.24                                           | 1.02            | 2.01            | 4.04            | 8.06            | 16.00          | 30.28         |
| 1500               | 1.28                                           | 1.02            | 2.02            | 4.05            | 8.10            | 16.14          | 31.09         |
| 1600               | 1.32                                           | 1.02            | 2.02            | 4.07            | 8.13            | 16.22          | 31.44         |
| 1700               | 1.32                                           | 1.02            | 2.02            | 4.08            | 8.13            | 16.20          | 31.04         |
| 1800               | 1.33                                           | 1.03            | 2.02            | 4.08            | 8.13            | 16.16          | 30.67         |
| 1900               | 1.34                                           | 1.03            | 2.02            | 4.09            | 8.12            | 16.09          | 30.07         |
| 2000               | 1.36                                           | 1.02            | 2.02            | 4.09            | 8.13            | 16.04          | 29.68         |
| 2100               | 1.38                                           | 1.02            | 2.02            | 4.10            | 8.16            | 16.06          | 29.56         |
| 2200               | 1.39                                           | 1.03            | 2.03            | 4.11            | 8.17            | 16.03          | 29.35         |
| 2300               | 1.47                                           | 1.04            | 2.05            | 4.14            | 8.23            | 16.15          | 29.97         |
| 2400               | 1.57                                           | 1.04            | 2.06            | 4.18            | 8.31            | 16.34          | 30.86         |
| 2500               | 1.34                                           | 1.04            | 2.05            | 4.17            | 8.27            | 16.09          | 29.22         |
| 2600               | 1.21                                           | 1.05            | 2.07            | 4.23            | 8.35            | 16.19          | 29.45         |
| 2700               | 1.17                                           | 1.06            | 2.08            | 4.28            | 8.43            | 16.28          | 29.52         |
| 2800               | 1.32                                           | 1.05            | 2.08            | 4.32            | 8.51            | 16.51          | 30.72         |
| 2900               | 1.63                                           | 1.03            | 2.05            | 4.29            | 8.48            | 16.56          | 31.00         |
| 3000               | 2.09                                           | 0.99            | 1.99            | 4.24            | 8.45            | 16.81          | 33.66         |

\* Step Attenuation above Thru Loss (TTL Logic 00000).



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site  
The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: [www.minicircuits.com](http://www.minicircuits.com)



IF/RF MICROWAVE COMPONENTS

REV. OR  
DAT-3175A-SN+  
10/12/2016  
Page 1 of 9

# Digital Step Attenuator

# DAT-3175A-SN+

## Typical Performance Data

TEST CONDITIONS: INPUT POWER=-10dBm, Vdd=+3V, Vss = -3.2V, TEMPERATURE=-45degC

| FREQUENCY<br>(MHz) | INPUT RETURN LOSS AT TTL CONTROL STATE<br>(dB) |                 |                 |                 |                 |                |               |
|--------------------|------------------------------------------------|-----------------|-----------------|-----------------|-----------------|----------------|---------------|
|                    | 00000<br>0 dB                                  | 00001<br>1.0 dB | 00010<br>2.0 dB | 00100<br>4.0 dB | 01000<br>8.0 dB | 10000<br>16 dB | 11111<br>31dB |
| 10                 | 19.90                                          | 22.62           | 24.20           | 37.05           | 29.27           | 24.73          | 23.22         |
| 50                 | 19.52                                          | 22.11           | 23.57           | 40.52           | 30.44           | 25.60          | 23.88         |
| 100                | 19.65                                          | 22.23           | 23.70           | 38.36           | 30.30           | 25.67          | 23.92         |
| 150                | 19.34                                          | 21.78           | 23.12           | 40.42           | 31.89           | 26.66          | 24.74         |
| 200                | 19.48                                          | 21.90           | 23.28           | 40.22           | 31.60           | 26.53          | 24.66         |
| 250                | 19.26                                          | 21.66           | 23.02           | 43.20           | 32.44           | 26.90          | 24.97         |
| 300                | 19.37                                          | 21.88           | 23.30           | 39.35           | 30.95           | 26.16          | 24.38         |
| 350                | 19.23                                          | 21.73           | 23.16           | 38.01           | 30.83           | 26.08          | 24.31         |
| 400                | 19.25                                          | 21.77           | 23.20           | 33.77           | 29.38           | 25.47          | 23.87         |
| 450                | 19.17                                          | 21.61           | 22.99           | 32.66           | 29.41           | 25.68          | 24.05         |
| 500                | 19.16                                          | 21.50           | 22.81           | 30.62           | 28.57           | 25.46          | 23.95         |
| 550                | 19.16                                          | 21.43           | 22.69           | 30.54           | 28.94           | 25.91          | 24.40         |
| 600                | 19.14                                          | 21.35           | 22.51           | 29.56           | 28.48           | 25.91          | 24.46         |
| 700                | 19.27                                          | 21.36           | 22.42           | 29.16           | 28.41           | 26.24          | 24.84         |
| 800                | 19.12                                          | 21.11           | 22.05           | 28.32           | 27.82           | 26.19          | 25.00         |
| 900                | 18.82                                          | 20.72           | 21.58           | 27.30           | 27.00           | 25.87          | 24.88         |
| 1000               | 18.40                                          | 20.24           | 21.06           | 26.63           | 26.55           | 25.80          | 25.00         |
| 1100               | 17.94                                          | 19.68           | 20.46           | 26.06           | 26.39           | 26.26          | 25.64         |
| 1200               | 17.57                                          | 19.22           | 19.95           | 25.76           | 26.48           | 27.05          | 26.78         |
| 1300               | 17.20                                          | 18.79           | 19.46           | 25.71           | 26.97           | 28.63          | 28.90         |
| 1400               | 16.73                                          | 18.25           | 18.88           | 25.36           | 27.13           | 30.04          | 31.54         |
| 1500               | 16.49                                          | 17.99           | 18.62           | 25.55           | 27.98           | 32.73          | 36.17         |
| 1600               | 16.66                                          | 18.15           | 18.77           | 26.34           | 29.76           | 38.44          | 49.76         |
| 1700               | 17.54                                          | 19.01           | 19.55           | 27.63           | 30.95           | 32.98          | 30.94         |
| 1800               | 18.73                                          | 19.99           | 20.44           | 26.58           | 27.79           | 26.51          | 24.95         |
| 1900               | 19.68                                          | 20.59           | 20.92           | 23.77           | 24.17           | 22.85          | 21.64         |
| 2000               | 20.01                                          | 20.45           | 20.78           | 21.21           | 21.36           | 20.23          | 19.26         |
| 2100               | 20.22                                          | 20.16           | 20.43           | 19.17           | 19.12           | 18.12          | 17.29         |
| 2200               | 19.86                                          | 19.50           | 19.72           | 17.81           | 17.64           | 16.75          | 16.04         |
| 2300               | 21.46                                          | 20.95           | 21.07           | 18.03           | 17.47           | 16.44          | 15.72         |
| 2400               | 25.55                                          | 23.45           | 22.70           | 17.70           | 16.57           | 15.48          | 14.81         |
| 2500               | 31.40                                          | 24.90           | 22.83           | 16.81           | 15.37           | 14.32          | 13.79         |
| 2600               | 25.84                                          | 22.87           | 20.87           | 15.62           | 14.01           | 13.06          | 12.64         |
| 2700               | 19.54                                          | 19.43           | 18.47           | 14.69           | 13.10           | 12.25          | 11.91         |
| 2800               | 15.02                                          | 15.81           | 15.75           | 13.73           | 12.46           | 11.80          | 11.53         |
| 2900               | 12.33                                          | 13.33           | 13.68           | 12.92           | 12.09           | 11.62          | 11.42         |
| 3000               | 10.55                                          | 11.66           | 12.21           | 12.36           | 12.01           | 11.82          | 11.71         |



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site  
The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: [www.minicircuits.com](http://www.minicircuits.com)

IF/RF MICROWAVE COMPONENTS

REV. OR  
DAT-3175A-SN+  
10/12/2016  
Page 2 of 9

# Digital Step Attenuator

# DAT-3175A-SN+

## Typical Performance Data

TEST CONDITIONS: INPUT POWER=-10dBm, Vdd=+3V, Vss = -3.2V, TEMPERATURE=-45degC

| FREQUENCY<br>(MHz) | OUTPUT RETURN LOSS AT TTL CONTROL STATE<br>(dB) |                 |                 |                 |                 |                |               |
|--------------------|-------------------------------------------------|-----------------|-----------------|-----------------|-----------------|----------------|---------------|
|                    | 00000<br>0 dB                                   | 00001<br>1.0 dB | 00010<br>2.0 dB | 00100<br>4.0 dB | 01000<br>8.0 dB | 10000<br>16 dB | 11111<br>31dB |
| 10                 | 19.74                                           | 22.14           | 24.03           | 27.77           | 29.67           | 24.76          | 23.29         |
| 50                 | 19.38                                           | 21.61           | 23.41           | 26.75           | 30.95           | 25.66          | 23.90         |
| 100                | 19.33                                           | 21.49           | 23.26           | 26.41           | 31.23           | 25.88          | 24.11         |
| 150                | 18.91                                           | 20.99           | 22.63           | 25.49           | 33.29           | 27.04          | 25.04         |
| 200                | 19.06                                           | 21.15           | 22.83           | 25.78           | 32.89           | 26.80          | 24.85         |
| 250                | 18.99                                           | 21.08           | 22.77           | 25.79           | 33.27           | 26.90          | 24.92         |
| 300                | 19.16                                           | 21.34           | 23.13           | 26.32           | 31.42           | 25.98          | 24.23         |
| 350                | 18.98                                           | 21.14           | 22.94           | 26.04           | 31.33           | 26.06          | 24.26         |
| 400                | 18.87                                           | 21.03           | 22.81           | 25.66           | 29.72           | 25.49          | 23.84         |
| 450                | 18.57                                           | 20.64           | 22.33           | 24.97           | 30.08           | 25.92          | 24.26         |
| 500                | 18.26                                           | 20.21           | 21.81           | 24.14           | 29.53           | 26.06          | 24.48         |
| 550                | 18.15                                           | 20.03           | 21.58           | 23.77           | 30.28           | 26.89          | 25.16         |
| 600                | 18.00                                           | 19.83           | 21.27           | 23.29           | 30.21           | 27.33          | 25.64         |
| 700                | 18.09                                           | 19.85           | 21.24           | 23.11           | 31.09           | 28.40          | 26.56         |
| 800                | 18.38                                           | 20.09           | 21.45           | 23.12           | 31.03           | 28.76          | 26.95         |
| 900                | 19.13                                           | 20.90           | 22.29           | 23.79           | 29.73           | 27.43          | 25.82         |
| 1000               | 19.34                                           | 21.04           | 22.33           | 23.50           | 28.86           | 27.20          | 25.78         |
| 1100               | 18.94                                           | 20.45           | 21.57           | 22.36           | 27.65           | 27.19          | 26.19         |
| 1200               | 18.73                                           | 20.09           | 21.09           | 21.63           | 26.79           | 27.08          | 26.52         |
| 1300               | 18.93                                           | 20.26           | 21.20           | 21.51           | 26.36           | 26.74          | 26.32         |
| 1400               | 19.08                                           | 20.39           | 21.27           | 21.47           | 26.35           | 26.79          | 26.52         |
| 1500               | 18.84                                           | 20.09           | 20.94           | 21.17           | 27.43           | 28.57          | 28.63         |
| 1600               | 17.94                                           | 19.04           | 19.79           | 20.04           | 26.40           | 28.69          | 29.97         |
| 1700               | 17.76                                           | 18.85           | 19.63           | 20.03           | 27.53           | 31.06          | 33.57         |
| 1800               | 17.64                                           | 18.78           | 19.63           | 20.48           | 30.43           | 39.49          | 50.18         |
| 1900               | 17.78                                           | 18.98           | 19.90           | 21.51           | 32.17           | 33.48          | 30.32         |
| 2000               | 17.73                                           | 18.89           | 19.80           | 22.30           | 26.88           | 25.50          | 23.87         |
| 2100               | 17.35                                           | 18.54           | 19.48           | 22.39           | 24.73           | 23.19          | 21.81         |
| 2200               | 18.72                                           | 19.97           | 20.94           | 24.86           | 22.27           | 20.37          | 19.23         |
| 2300               | 20.43                                           | 21.40           | 21.86           | 25.17           | 19.62           | 18.00          | 17.07         |
| 2400               | 23.35                                           | 24.34           | 24.35           | 27.15           | 19.09           | 17.37          | 16.46         |
| 2500               | 32.82                                           | 32.58           | 28.44           | 25.16           | 17.67           | 16.17          | 15.41         |
| 2600               | 33.07                                           | 32.66           | 27.15           | 21.43           | 16.16           | 14.81          | 14.19         |
| 2700               | 21.41                                           | 22.75           | 22.22           | 18.18           | 14.85           | 13.65          | 13.15         |
| 2800               | 15.53                                           | 16.90           | 17.58           | 15.68           | 14.14           | 13.21          | 12.81         |
| 2900               | 11.84                                           | 13.04           | 13.89           | 13.20           | 13.07           | 12.59          | 12.35         |
| 3000               | 9.64                                            | 10.71           | 11.56           | 11.48           | 12.29           | 12.29          | 12.23         |



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site  
The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: [www.minicircuits.com](http://www.minicircuits.com)

IF/RF MICROWAVE COMPONENTS

REV. OR  
DAT-3175A-SN+  
10/12/2016  
Page 3 of 9

# Digital Step Attenuator

# DAT-3175A-SN+

## Typical Performance Data

TEST CONDITIONS: INPUT POWER=-10dBm, Vdd=+3V, Vss= -3.2V, TEMPERATURE=+25degC

| FREQUENCY<br>(MHz) | STEP ATTENUATION* AT TTL CONTROL STATE<br>(dB) |                 |                 |                 |                 |                |               |
|--------------------|------------------------------------------------|-----------------|-----------------|-----------------|-----------------|----------------|---------------|
|                    | 00000<br>THRU LOSS                             | 00001<br>1.0 dB | 00010<br>2.0 dB | 00100<br>4.0 dB | 01000<br>8.0 dB | 10000<br>16 dB | 11111<br>31dB |
| 10                 | 1.10                                           | 1.02            | 2.03            | 4.04            | 8.00            | 16.00          | 30.91         |
| 50                 | 1.11                                           | 1.02            | 2.01            | 4.01            | 8.00            | 15.97          | 30.88         |
| 100                | 1.12                                           | 1.02            | 2.02            | 4.01            | 8.01            | 15.98          | 30.92         |
| 150                | 1.13                                           | 1.01            | 2.02            | 4.02            | 8.00            | 15.98          | 30.89         |
| 200                | 1.14                                           | 1.02            | 2.02            | 4.01            | 8.00            | 15.97          | 30.89         |
| 250                | 1.15                                           | 1.01            | 2.01            | 4.01            | 8.00            | 15.96          | 30.88         |
| 300                | 1.16                                           | 1.01            | 2.01            | 4.01            | 7.99            | 15.96          | 30.90         |
| 350                | 1.18                                           | 1.02            | 2.01            | 4.01            | 8.00            | 15.98          | 30.97         |
| 400                | 1.20                                           | 1.01            | 2.01            | 4.01            | 7.99            | 15.97          | 30.88         |
| 450                | 1.21                                           | 1.01            | 2.01            | 4.00            | 7.98            | 15.96          | 30.88         |
| 500                | 1.22                                           | 1.01            | 2.01            | 4.00            | 7.98            | 15.95          | 30.94         |
| 550                | 1.24                                           | 1.01            | 2.00            | 4.00            | 7.97            | 15.94          | 30.92         |
| 600                | 1.26                                           | 1.01            | 2.00            | 3.99            | 7.97            | 15.94          | 30.93         |
| 700                | 1.29                                           | 1.01            | 2.00            | 3.99            | 7.96            | 15.93          | 30.91         |
| 800                | 1.34                                           | 1.00            | 2.00            | 3.98            | 7.95            | 15.92          | 30.83         |
| 900                | 1.36                                           | 1.00            | 2.00            | 3.98            | 7.96            | 15.94          | 31.00         |
| 1000               | 1.41                                           | 1.00            | 2.00            | 3.97            | 7.96            | 15.96          | 31.15         |
| 1100               | 1.44                                           | 1.00            | 2.00            | 3.97            | 7.96            | 15.96          | 31.06         |
| 1200               | 1.47                                           | 1.00            | 1.99            | 3.97            | 7.95            | 15.93          | 30.76         |
| 1300               | 1.48                                           | 0.99            | 1.99            | 3.96            | 7.94            | 15.87          | 30.30         |
| 1400               | 1.49                                           | 0.99            | 1.99            | 3.96            | 7.93            | 15.82          | 30.14         |
| 1500               | 1.54                                           | 1.00            | 1.99            | 3.98            | 7.97            | 15.97          | 30.94         |
| 1600               | 1.57                                           | 1.00            | 2.00            | 4.00            | 8.00            | 16.03          | 31.10         |
| 1700               | 1.58                                           | 1.00            | 2.00            | 4.00            | 8.00            | 15.99          | 30.69         |
| 1800               | 1.60                                           | 1.00            | 2.00            | 4.01            | 8.01            | 15.99          | 30.34         |
| 1900               | 1.62                                           | 1.00            | 1.99            | 4.01            | 8.01            | 15.91          | 29.85         |
| 2000               | 1.64                                           | 1.00            | 1.99            | 4.01            | 8.00            | 15.86          | 29.54         |
| 2100               | 1.63                                           | 0.99            | 1.99            | 4.01            | 8.02            | 15.88          | 29.48         |
| 2200               | 1.60                                           | 1.00            | 1.99            | 4.02            | 8.04            | 15.86          | 29.25         |
| 2300               | 1.59                                           | 1.00            | 1.99            | 4.04            | 8.09            | 15.97          | 29.88         |
| 2400               | 1.52                                           | 1.00            | 2.00            | 4.07            | 8.15            | 16.07          | 29.97         |
| 2500               | 1.29                                           | 1.00            | 2.00            | 4.08            | 8.12            | 15.88          | 28.90         |
| 2600               | 1.24                                           | 1.00            | 2.01            | 4.12            | 8.19            | 15.96          | 29.05         |
| 2700               | 1.28                                           | 1.01            | 2.02            | 4.15            | 8.24            | 16.03          | 29.30         |
| 2800               | 1.47                                           | 1.00            | 2.01            | 4.16            | 8.28            | 16.19          | 30.32         |
| 2900               | 1.80                                           | 0.98            | 1.98            | 4.14            | 8.25            | 16.27          | 30.82         |
| 3000               | 2.25                                           | 0.95            | 1.94            | 4.11            | 8.24            | 16.51          | 33.27         |

\* Step Attenuation above Thru Loss (TTL Logic 00000).



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site  
The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: [www.minicircuits.com](http://www.minicircuits.com)



IF/RF MICROWAVE COMPONENTS

REV. OR  
DAT-3175A-SN+  
10/12/2016  
Page 4 of 9

# Digital Step Attenuator

# DAT-3175A-SN+

## Typical Performance Data

TEST CONDITIONS: INPUT POWER=-10dBm, Vdd=+3V, Vss= -3.2V, TEMPERATURE=+25degC

| FREQUENCY<br>(MHz) | INPUT RETURN LOSS AT TTL CONTROL STATE<br>(dB) |                 |                 |                 |                 |                |               |
|--------------------|------------------------------------------------|-----------------|-----------------|-----------------|-----------------|----------------|---------------|
|                    | 00000<br>0 dB                                  | 00001<br>1.0 dB | 00010<br>2.0 dB | 00100<br>4.0 dB | 01000<br>8.0 dB | 10000<br>16 dB | 11111<br>31dB |
| 10                 | 18.79                                          | 20.35           | 20.96           | 31.48           | 36.58           | 48.35          | 36.54         |
| 50                 | 18.49                                          | 19.95           | 20.56           | 30.32           | 34.85           | 58.89          | 39.15         |
| 100                | 18.63                                          | 20.14           | 20.79           | 30.94           | 35.85           | 48.82          | 37.48         |
| 150                | 18.34                                          | 19.81           | 20.45           | 29.72           | 33.88           | 46.04          | 39.82         |
| 200                | 18.43                                          | 19.90           | 20.53           | 29.75           | 33.77           | 42.37          | 38.30         |
| 250                | 18.23                                          | 19.65           | 20.28           | 28.90           | 32.38           | 41.03          | 40.71         |
| 300                | 18.27                                          | 19.68           | 20.29           | 28.68           | 31.95           | 38.64          | 38.92         |
| 350                | 18.12                                          | 19.50           | 20.08           | 28.13           | 31.12           | 38.22          | 41.50         |
| 400                | 18.16                                          | 19.54           | 20.11           | 27.99           | 30.78           | 36.94          | 39.38         |
| 450                | 18.18                                          | 19.52           | 20.08           | 27.92           | 30.71           | 37.43          | 42.61         |
| 500                | 18.29                                          | 19.63           | 20.17           | 27.94           | 30.49           | 36.66          | 40.79         |
| 550                | 18.38                                          | 19.73           | 20.22           | 28.05           | 30.62           | 37.47          | 44.41         |
| 600                | 18.49                                          | 19.82           | 20.32           | 28.01           | 30.42           | 36.62          | 41.84         |
| 700                | 18.69                                          | 20.01           | 20.47           | 28.17           | 30.25           | 36.03          | 40.84         |
| 800                | 18.64                                          | 19.93           | 20.36           | 27.56           | 29.26           | 33.80          | 37.26         |
| 900                | 18.43                                          | 19.70           | 20.10           | 26.68           | 27.94           | 31.48          | 33.94         |
| 1000               | 18.00                                          | 19.24           | 19.63           | 25.60           | 26.68           | 29.75          | 32.13         |
| 1100               | 17.36                                          | 18.54           | 18.91           | 24.38           | 25.36           | 28.27          | 30.89         |
| 1200               | 16.72                                          | 17.84           | 18.15           | 23.21           | 24.14           | 26.88          | 29.50         |
| 1300               | 16.19                                          | 17.21           | 17.49           | 22.22           | 23.08           | 25.50          | 27.97         |
| 1400               | 15.82                                          | 16.74           | 16.97           | 21.46           | 22.16           | 24.22          | 26.22         |
| 1500               | 15.77                                          | 16.64           | 16.82           | 21.29           | 21.95           | 23.77          | 25.47         |
| 1600               | 16.09                                          | 16.87           | 17.00           | 21.42           | 22.02           | 23.40          | 24.57         |
| 1700               | 16.76                                          | 17.41           | 17.45           | 21.54           | 21.99           | 22.63          | 23.04         |
| 1800               | 17.43                                          | 17.86           | 17.85           | 21.11           | 21.51           | 21.51          | 21.33         |
| 1900               | 17.92                                          | 18.14           | 18.14           | 20.33           | 20.80           | 20.41          | 19.89         |
| 2000               | 18.14                                          | 18.20           | 18.31           | 19.44           | 20.04           | 19.46          | 18.77         |
| 2100               | 18.40                                          | 18.32           | 18.54           | 18.66           | 19.27           | 18.54          | 17.77         |
| 2200               | 18.43                                          | 18.34           | 18.68           | 18.24           | 18.84           | 18.08          | 17.25         |
| 2300               | 20.19                                          | 20.20           | 20.69           | 19.43           | 19.83           | 18.76          | 17.76         |
| 2400               | 24.65                                          | 24.57           | 25.20           | 20.83           | 20.38           | 18.89          | 17.78         |
| 2500               | 38.26                                          | 34.82           | 31.78           | 20.49           | 18.98           | 17.63          | 16.76         |
| 2600               | 26.93                                          | 27.40           | 25.46           | 18.73           | 16.95           | 15.91          | 15.32         |
| 2700               | 19.83                                          | 20.93           | 20.57           | 17.28           | 15.60           | 14.78          | 14.37         |
| 2800               | 15.55                                          | 16.74           | 16.96           | 15.86           | 14.63           | 14.11          | 13.84         |
| 2900               | 12.92                                          | 14.13           | 14.62           | 14.75           | 14.05           | 13.83          | 13.68         |
| 3000               | 11.10                                          | 12.28           | 12.91           | 13.90           | 13.74           | 13.91          | 13.93         |

# Digital Step Attenuator

# DAT-3175A-SN+

## Typical Performance Data

TEST CONDITIONS: INPUT POWER=-10dBm, Vdd=+3V, Vss= -3.2V, TEMPERATURE=+25degC

| FREQUENCY<br>(MHz) | OUTPUT RETURN LOSS AT TTL CONTROL STATE<br>(dB) |                 |                 |                 |                 |                |               |
|--------------------|-------------------------------------------------|-----------------|-----------------|-----------------|-----------------|----------------|---------------|
|                    | 00000<br>0 dB                                   | 00001<br>1.0 dB | 00010<br>2.0 dB | 00100<br>4.0 dB | 01000<br>8.0 dB | 10000<br>16 dB | 11111<br>31dB |
| 10                 | 18.77                                           | 20.00           | 20.91           | 21.82           | 35.76           | 45.95          | 36.34         |
| 50                 | 18.41                                           | 19.65           | 20.55           | 21.52           | 34.18           | 59.31          | 38.84         |
| 100                | 18.48                                           | 19.73           | 20.65           | 21.68           | 34.69           | 47.71          | 37.58         |
| 150                | 18.14                                           | 19.36           | 20.27           | 21.26           | 32.93           | 45.25          | 40.09         |
| 200                | 18.15                                           | 19.38           | 20.28           | 21.29           | 32.65           | 41.83          | 38.53         |
| 250                | 17.89                                           | 19.08           | 19.98           | 20.92           | 31.42           | 40.95          | 41.58         |
| 300                | 17.86                                           | 19.05           | 19.92           | 20.86           | 30.89           | 38.39          | 39.49         |
| 350                | 17.68                                           | 18.83           | 19.67           | 20.55           | 30.09           | 37.70          | 42.53         |
| 400                | 17.67                                           | 18.81           | 19.67           | 20.54           | 29.81           | 36.54          | 40.08         |
| 450                | 17.60                                           | 18.72           | 19.56           | 20.37           | 29.56           | 36.80          | 44.15         |
| 500                | 17.56                                           | 18.67           | 19.50           | 20.28           | 29.10           | 35.84          | 42.12         |
| 550                | 17.59                                           | 18.67           | 19.50           | 20.22           | 29.05           | 36.03          | 45.82         |
| 600                | 17.56                                           | 18.63           | 19.43           | 20.13           | 28.69           | 35.20          | 43.65         |
| 700                | 17.70                                           | 18.74           | 19.53           | 20.13           | 28.69           | 35.30          | 44.98         |
| 800                | 17.93                                           | 18.97           | 19.73           | 20.22           | 28.69           | 35.20          | 44.70         |
| 900                | 18.46                                           | 19.53           | 20.31           | 20.68           | 29.67           | 37.12          | 48.16         |
| 1000               | 18.61                                           | 19.62           | 20.36           | 20.56           | 29.09           | 35.47          | 43.22         |
| 1100               | 18.36                                           | 19.29           | 19.97           | 19.98           | 27.25           | 31.88          | 36.50         |
| 1200               | 18.04                                           | 18.87           | 19.48           | 19.30           | 25.51           | 29.00          | 32.26         |
| 1300               | 17.88                                           | 18.63           | 19.15           | 18.84           | 24.47           | 27.43          | 30.24         |
| 1400               | 17.89                                           | 18.54           | 18.98           | 18.55           | 24.01           | 26.73          | 29.42         |
| 1500               | 17.63                                           | 18.15           | 18.49           | 18.08           | 23.34           | 25.73          | 28.14         |
| 1600               | 17.09                                           | 17.57           | 17.86           | 17.52           | 22.44           | 24.48          | 26.56         |
| 1700               | 17.06                                           | 17.53           | 17.86           | 17.66           | 22.83           | 24.80          | 26.60         |
| 1800               | 16.99                                           | 17.49           | 17.85           | 17.96           | 23.12           | 24.75          | 25.72         |
| 1900               | 17.12                                           | 17.66           | 18.10           | 18.63           | 23.43           | 24.24          | 24.17         |
| 2000               | 17.14                                           | 17.66           | 18.08           | 19.20           | 22.53           | 22.42          | 21.81         |
| 2100               | 17.40                                           | 17.99           | 18.44           | 20.09           | 22.51           | 21.89          | 21.02         |
| 2200               | 18.75                                           | 19.26           | 19.69           | 22.23           | 22.07           | 20.80          | 19.68         |
| 2300               | 19.44                                           | 19.88           | 20.17           | 23.60           | 20.76           | 19.38          | 18.32         |
| 2400               | 21.25                                           | 21.98           | 22.43           | 27.59           | 21.41           | 19.60          | 18.42         |
| 2500               | 25.96                                           | 28.08           | 28.74           | 36.27           | 20.76           | 18.75          | 17.65         |
| 2600               | 27.11                                           | 34.15           | 41.08           | 25.87           | 19.38           | 17.61          | 16.69         |
| 2700               | 20.63                                           | 22.77           | 24.03           | 20.00           | 17.62           | 16.29          | 15.64         |
| 2800               | 15.48                                           | 16.88           | 17.96           | 16.27           | 16.18           | 15.45          | 15.05         |
| 2900               | 12.18                                           | 13.32           | 14.28           | 13.54           | 14.55           | 14.43          | 14.28         |
| 3000               | 10.06                                           | 11.06           | 11.93           | 11.68           | 13.39           | 13.80          | 13.91         |

# Digital Step Attenuator

# DAT-3175A-SN+

## Typical Performance Data

TEST CONDITIONS: INPUT POWER=-10dBm, Vdd=+3V, Vss =-3.2V, TEMPERATURE=+85degC

| FREQUENCY<br>(MHz) | STEP ATTENUATION* AT TTL CONTROL STATE<br>(dB) |                 |                 |                 |                 |                |               |
|--------------------|------------------------------------------------|-----------------|-----------------|-----------------|-----------------|----------------|---------------|
|                    | 00000<br>THRU LOSS                             | 00001<br>1.0 dB | 00010<br>2.0 dB | 00100<br>4.0 dB | 01000<br>8.0 dB | 10000<br>16 dB | 11111<br>31dB |
| 10                 | 1.30                                           | 0.99            | 1.99            | 3.91            | 7.82            | 15.72          | 30.76         |
| 50                 | 1.30                                           | 0.99            | 1.99            | 3.92            | 7.84            | 15.72          | 30.47         |
| 100                | 1.30                                           | 0.99            | 1.99            | 3.92            | 7.84            | 15.74          | 30.46         |
| 150                | 1.30                                           | 0.99            | 1.99            | 3.92            | 7.84            | 15.73          | 30.52         |
| 200                | 1.32                                           | 0.99            | 1.99            | 3.92            | 7.84            | 15.73          | 30.52         |
| 250                | 1.34                                           | 0.99            | 1.99            | 3.92            | 7.84            | 15.72          | 30.50         |
| 300                | 1.37                                           | 0.98            | 1.99            | 3.92            | 7.83            | 15.71          | 30.50         |
| 350                | 1.40                                           | 0.99            | 1.99            | 3.92            | 7.82            | 15.72          | 30.48         |
| 400                | 1.43                                           | 0.99            | 1.98            | 3.91            | 7.82            | 15.72          | 30.49         |
| 450                | 1.45                                           | 0.98            | 1.98            | 3.91            | 7.81            | 15.70          | 30.54         |
| 500                | 1.46                                           | 0.99            | 1.98            | 3.91            | 7.81            | 15.71          | 30.53         |
| 550                | 1.48                                           | 0.98            | 1.98            | 3.91            | 7.81            | 15.71          | 30.52         |
| 600                | 1.49                                           | 0.98            | 1.98            | 3.91            | 7.82            | 15.70          | 30.52         |
| 700                | 1.52                                           | 0.98            | 1.98            | 3.91            | 7.82            | 15.71          | 30.43         |
| 800                | 1.57                                           | 0.98            | 1.98            | 3.90            | 7.82            | 15.71          | 30.50         |
| 900                | 1.60                                           | 0.98            | 1.98            | 3.91            | 7.83            | 15.74          | 30.62         |
| 1000               | 1.65                                           | 0.98            | 1.98            | 3.90            | 7.83            | 15.77          | 30.82         |
| 1100               | 1.70                                           | 0.97            | 1.98            | 3.90            | 7.83            | 15.76          | 30.67         |
| 1200               | 1.74                                           | 0.97            | 1.97            | 3.90            | 7.82            | 15.71          | 30.39         |
| 1300               | 1.76                                           | 0.97            | 1.97            | 3.89            | 7.81            | 15.66          | 29.93         |
| 1400               | 1.78                                           | 0.97            | 1.97            | 3.90            | 7.81            | 15.66          | 29.95         |
| 1500               | 1.84                                           | 0.98            | 1.98            | 3.91            | 7.85            | 15.78          | 30.66         |
| 1600               | 1.86                                           | 0.98            | 1.98            | 3.93            | 7.87            | 15.82          | 30.71         |
| 1700               | 1.86                                           | 0.98            | 1.98            | 3.94            | 7.88            | 15.78          | 30.26         |
| 1800               | 1.85                                           | 0.98            | 1.98            | 3.94            | 7.89            | 15.75          | 29.83         |
| 1900               | 1.83                                           | 0.98            | 1.98            | 3.94            | 7.90            | 15.75          | 29.68         |
| 2000               | 1.82                                           | 0.98            | 1.98            | 3.95            | 7.91            | 15.72          | 29.47         |
| 2100               | 1.76                                           | 0.97            | 1.98            | 3.96            | 7.93            | 15.74          | 29.39         |
| 2200               | 1.72                                           | 0.97            | 1.97            | 3.96            | 7.95            | 15.74          | 29.26         |
| 2300               | 1.69                                           | 0.97            | 1.97            | 3.99            | 8.01            | 15.88          | 29.97         |
| 2400               | 1.54                                           | 0.97            | 1.96            | 4.00            | 8.00            | 15.75          | 29.03         |
| 2500               | 1.42                                           | 0.97            | 1.96            | 4.00            | 8.00            | 15.67          | 28.64         |
| 2600               | 1.42                                           | 0.96            | 1.96            | 4.01            | 8.02            | 15.72          | 28.85         |
| 2700               | 1.51                                           | 0.95            | 1.95            | 4.02            | 8.05            | 15.80          | 29.22         |
| 2800               | 1.72                                           | 0.94            | 1.94            | 4.03            | 8.07            | 15.89          | 29.90         |
| 2900               | 2.06                                           | 0.92            | 1.91            | 4.01            | 8.05            | 16.00          | 30.69         |
| 3000               | 2.48                                           | 0.90            | 1.89            | 3.99            | 8.05            | 16.21          | 32.93         |

\* Step Attenuation above Thru Loss (TTL Logic 00000).



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site  
The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: [www.minicircuits.com](http://www.minicircuits.com)



IF/RF MICROWAVE COMPONENTS

REV. OR  
DAT-3175A-SN+  
10/12/2016  
Page 7 of 9



# Digital Step Attenuator

# DAT-3175A-SN+

## Typical Performance Data

TEST CONDITIONS: INPUT POWER=-10dBm, Vdd=+3V, Vss =-3.2V, TEMPERATURE=+85degC

| FREQUENCY<br>(MHz) | INPUT RETURN LOSS AT TTL CONTROL STATE<br>(dB) |                 |                 |                 |                 |                |               |
|--------------------|------------------------------------------------|-----------------|-----------------|-----------------|-----------------|----------------|---------------|
|                    | 00000<br>0 dB                                  | 00001<br>1.0 dB | 00010<br>2.0 dB | 00100<br>4.0 dB | 01000<br>8.0 dB | 10000<br>16 dB | 11111<br>31dB |
| 10                 | 17.47                                          | 18.18           | 18.17           | 22.85           | 22.90           | 24.57          | 26.13         |
| 50                 | 17.26                                          | 17.88           | 17.94           | 22.47           | 22.63           | 24.19          | 25.76         |
| 100                | 17.37                                          | 18.03           | 18.13           | 22.86           | 23.12           | 24.84          | 26.51         |
| 150                | 17.14                                          | 17.82           | 17.94           | 22.54           | 22.89           | 24.58          | 26.24         |
| 200                | 17.20                                          | 17.91           | 18.03           | 22.69           | 23.05           | 24.82          | 26.53         |
| 250                | 17.01                                          | 17.69           | 17.80           | 22.23           | 22.52           | 24.13          | 25.71         |
| 300                | 17.02                                          | 17.67           | 17.76           | 22.05           | 22.28           | 23.84          | 25.30         |
| 350                | 16.88                                          | 17.48           | 17.53           | 21.61           | 21.71           | 23.08          | 24.43         |
| 400                | 16.91                                          | 17.50           | 17.50           | 21.47           | 21.51           | 22.79          | 24.08         |
| 450                | 16.95                                          | 17.47           | 17.45           | 21.32           | 21.23           | 22.39          | 23.56         |
| 500                | 17.10                                          | 17.59           | 17.53           | 21.40           | 21.25           | 22.35          | 23.49         |
| 550                | 17.22                                          | 17.68           | 17.60           | 21.44           | 21.23           | 22.25          | 23.34         |
| 600                | 17.39                                          | 17.86           | 17.75           | 21.66           | 21.44           | 22.45          | 23.54         |
| 700                | 17.79                                          | 18.26           | 18.15           | 22.30           | 22.04           | 23.08          | 24.24         |
| 800                | 18.02                                          | 18.57           | 18.48           | 22.95           | 22.73           | 23.97          | 25.28         |
| 900                | 18.00                                          | 18.62           | 18.57           | 23.25           | 23.11           | 24.61          | 26.22         |
| 1000               | 17.52                                          | 18.22           | 18.22           | 22.75           | 22.72           | 24.35          | 26.07         |
| 1100               | 16.75                                          | 17.44           | 17.47           | 21.62           | 21.65           | 23.17          | 24.74         |
| 1200               | 15.93                                          | 16.59           | 16.62           | 20.36           | 20.40           | 21.73          | 23.08         |
| 1300               | 15.29                                          | 15.89           | 15.88           | 19.25           | 19.20           | 20.26          | 21.34         |
| 1400               | 14.96                                          | 15.45           | 15.37           | 18.45           | 18.27           | 19.08          | 19.95         |
| 1500               | 14.96                                          | 15.35           | 15.20           | 18.08           | 17.78           | 18.36          | 19.05         |
| 1600               | 15.33                                          | 15.55           | 15.31           | 17.96           | 17.55           | 17.84          | 18.33         |
| 1700               | 15.87                                          | 15.92           | 15.58           | 17.86           | 17.41           | 17.45          | 17.69         |
| 1800               | 16.35                                          | 16.21           | 15.86           | 17.68           | 17.37           | 17.16          | 17.20         |
| 1900               | 16.63                                          | 16.38           | 16.12           | 17.44           | 17.40           | 17.04          | 16.87         |
| 2000               | 16.85                                          | 16.58           | 16.46           | 17.34           | 17.62           | 17.16          | 16.80         |
| 2100               | 17.25                                          | 16.98           | 17.01           | 17.41           | 17.99           | 17.41          | 16.85         |
| 2200               | 17.80                                          | 17.59           | 17.78           | 17.94           | 18.79           | 18.09          | 17.38         |
| 2300               | 19.86                                          | 19.78           | 20.13           | 20.03           | 21.16           | 20.02          | 18.92         |
| 2400               | 24.16                                          | 24.56           | 25.29           | 23.78           | 24.83           | 22.58          | 20.83         |
| 2500               | 28.95                                          | 34.08           | 37.73           | 25.19           | 24.04           | 21.98          | 20.47         |
| 2600               | 24.72                                          | 28.31           | 28.40           | 23.27           | 21.28           | 20.08          | 19.17         |
| 2700               | 19.46                                          | 21.43           | 21.75           | 21.02           | 19.23           | 18.65          | 18.16         |
| 2800               | 15.93                                          | 17.48           | 17.97           | 18.89           | 17.76           | 17.67          | 17.47         |
| 2900               | 13.48                                          | 14.84           | 15.43           | 17.17           | 16.69           | 17.08          | 17.16         |
| 3000               | 11.63                                          | 12.88           | 13.50           | 15.74           | 15.89           | 16.79          | 17.21         |



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site  
The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: [www.minicircuits.com](http://www.minicircuits.com)

IF/RF MICROWAVE COMPONENTS

REV. OR  
DAT-3175A-SN+  
10/12/2016  
Page 8 of 9



# Digital Step Attenuator

# DAT-3175A-SN+

## Typical Performance Data

TEST CONDITIONS: INPUT POWER=-10dBm, Vdd=+3V, Vss =-3.2V, TEMPERATURE=+85degC


| FREQUENCY<br>(MHz) | OUTPUT RETURN LOSS AT TTL CONTROL STATE<br>(dB) |                 |                 |                 |                 |                |               |
|--------------------|-------------------------------------------------|-----------------|-----------------|-----------------|-----------------|----------------|---------------|
|                    | 00000<br>0 dB                                   | 00001<br>1.0 dB | 00010<br>2.0 dB | 00100<br>4.0 dB | 01000<br>8.0 dB | 10000<br>16 dB | 11111<br>31dB |
| 10                 | 17.48                                           | 17.82           | 18.10           | 17.95           | 22.77           | 24.68          | 26.30         |
| 50                 | 17.25                                           | 17.68           | 17.95           | 17.78           | 22.52           | 24.32          | 25.93         |
| 100                | 17.43                                           | 17.89           | 18.21           | 18.08           | 23.07           | 25.04          | 26.83         |
| 150                | 17.23                                           | 17.73           | 18.07           | 17.98           | 22.92           | 24.90          | 26.65         |
| 200                | 17.18                                           | 17.69           | 18.05           | 17.98           | 22.94           | 24.98          | 26.78         |
| 250                | 16.80                                           | 17.29           | 17.64           | 17.58           | 22.22           | 24.07          | 25.65         |
| 300                | 16.58                                           | 17.06           | 17.38           | 17.32           | 21.72           | 23.47          | 24.98         |
| 350                | 16.32                                           | 16.74           | 17.05           | 16.92           | 21.06           | 22.61          | 23.92         |
| 400                | 16.30                                           | 16.70           | 16.99           | 16.83           | 20.85           | 22.33          | 23.59         |
| 450                | 16.30                                           | 16.68           | 16.93           | 16.73           | 20.62           | 21.94          | 23.10         |
| 500                | 16.42                                           | 16.78           | 16.99           | 16.78           | 20.63           | 21.93          | 23.06         |
| 550                | 16.61                                           | 16.94           | 17.14           | 16.89           | 20.69           | 21.88          | 22.97         |
| 600                | 16.81                                           | 17.11           | 17.30           | 17.01           | 20.88           | 22.05          | 23.12         |
| 700                | 17.19                                           | 17.50           | 17.67           | 17.35           | 21.38           | 22.54          | 23.59         |
| 800                | 17.53                                           | 17.87           | 18.07           | 17.71           | 22.02           | 23.28          | 24.45         |
| 900                | 17.96                                           | 18.35           | 18.58           | 18.13           | 22.86           | 24.33          | 25.63         |
| 1000               | 17.92                                           | 18.33           | 18.56           | 18.05           | 22.89           | 24.48          | 25.96         |
| 1100               | 17.47                                           | 17.88           | 18.14           | 17.55           | 22.18           | 23.84          | 25.46         |
| 1200               | 16.90                                           | 17.29           | 17.53           | 16.88           | 21.14           | 22.69          | 24.22         |
| 1300               | 16.48                                           | 16.79           | 16.99           | 16.27           | 20.15           | 21.47          | 22.84         |
| 1400               | 16.26                                           | 16.47           | 16.57           | 15.80           | 19.31           | 20.35          | 21.48         |
| 1500               | 15.92                                           | 15.98           | 15.98           | 15.21           | 18.27           | 19.00          | 19.86         |
| 1600               | 15.85                                           | 15.80           | 15.74           | 14.97           | 17.81           | 18.39          | 19.11         |
| 1700               | 16.12                                           | 16.00           | 15.88           | 15.18           | 17.85           | 18.24          | 18.77         |
| 1800               | 16.40                                           | 16.23           | 16.10           | 15.58           | 18.04           | 18.22          | 18.52         |
| 1900               | 16.58                                           | 16.42           | 16.31           | 16.15           | 18.26           | 18.20          | 18.25         |
| 2000               | 16.31                                           | 16.24           | 16.22           | 16.55           | 18.18           | 17.98          | 17.81         |
| 2100               | 16.51                                           | 16.57           | 16.66           | 17.55           | 18.89           | 18.51          | 18.08         |
| 2200               | 17.00                                           | 17.15           | 17.33           | 18.94           | 19.43           | 18.79          | 18.08         |
| 2300               | 17.51                                           | 17.76           | 18.00           | 20.29           | 19.95           | 19.03          | 18.15         |
| 2400               | 19.38                                           | 19.87           | 20.27           | 23.48           | 22.51           | 20.84          | 19.51         |
| 2500               | 22.28                                           | 23.48           | 24.50           | 29.92           | 24.88           | 21.90          | 20.17         |
| 2600               | 23.17                                           | 25.87           | 29.40           | 27.04           | 25.15           | 22.02          | 20.31         |
| 2700               | 19.49                                           | 21.50           | 23.68           | 20.74           | 22.30           | 20.81          | 19.66         |
| 2800               | 15.50                                           | 16.88           | 18.23           | 16.68           | 19.27           | 19.12          | 18.65         |
| 2900               | 12.63                                           | 13.73           | 14.79           | 13.93           | 16.73           | 17.39          | 17.46         |
| 3000               | 10.60                                           | 11.54           | 12.45           | 12.00           | 14.91           | 16.07          | 16.53         |

# Digital Step Attenuator


## Typical Performance Curves

**DAT-3175A-SN+**


**Thru Loss**




**Step Attenuation (1dB)**




**Step Attenuation (2dB)**




**Step Attenuation (4dB)**




**Step Attenuation (8dB)**



**Step Attenuation (16dB)**



**Step Attenuation (31dB)**




# Digital Step Attenuator


## Typical Performance Curves

**DAT-3175A-SN+**


Input Return Loss (0dB)




Input Return Loss (1dB)




Input Return Loss (2dB)




Input Return Loss (4dB)




Input Return Loss (8dB)



Input Return Loss (16dB)



Input Return Loss (31dB)




# Digital Step Attenuator


## Typical Performance Curves

**DAT-3175A-SN+**


Output Return Loss (0dB)




Output Return Loss (1dB)




Output Return Loss (2dB)




Output Return Loss (4dB)




Output Return Loss(8dB)




Output Return Loss(16dB)




Output Return Loss (31dB)



### Outline Dimensions



### PCB Land Pattern



Suggested Layout,  
Tolerance to be within  $\pm.002$

| CASE #  | A              | B              | C              | D              | E              | F              | G              | H  | J              | K              |
|---------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|----|----------------|----------------|
| DG983-2 | .157<br>(4.00) | .157<br>(4.00) | .033<br>(0.85) | .008<br>(0.20) | .085<br>(2.15) | .085<br>(2.15) | .009<br>(0.23) | -- | .022<br>(0.55) | .020<br>(0.50) |

| CASE #  | L              | M              | N              | P              | Q              | R              | WT. GRAM |
|---------|----------------|----------------|----------------|----------------|----------------|----------------|----------|
| DG983-2 | .177<br>(4.50) | .177<br>(4.50) | .081<br>(2.06) | .010<br>(0.25) | .032<br>(0.81) | .081<br>(2.06) | .04      |

Dimensions are in inches (mm). Tolerances: 2 Pl.  $\pm .01$ ; 3 Pl.  $\pm .005$

#### Notes:


- Case material: Plastic.
- Termination finish:

For RoHS Case Styles: 0.2  $\mu$ inches of Gold (Au) over 0.1  $\mu$ inched of Palladium (Pd) over 10  $\mu$ inches of Nickel (Ni). All models, (+) suffix.

For RoHS-5 Case Styles: Tin-Lead plate. All models, no (+) suffix.



# Tape & Reel Packaging TR-F87



| Tape Width, mm | Device Cavity Pitch, mm | Reel Size, inches | Devices per Reel                    |      |
|----------------|-------------------------|-------------------|-------------------------------------|------|
| 12             | 8                       | 7                 | Small quantity standards (see note) | 20   |
|                |                         |                   |                                     | 50   |
|                |                         |                   |                                     | 100  |
|                |                         |                   |                                     | 200  |
|                |                         |                   |                                     | 500  |
|                |                         |                   |                                     | 1000 |
|                |                         | 13                | Standard                            | 3000 |

**Note : Please Consult individual model data sheet to determine device per reel availability**

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: [www.minicircuits.com/pages/pdfs/tape.pdf](http://www.minicircuits.com/pages/pdfs/tape.pdf)




**Distribution Centers** NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified

INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

## THIRD ANGLE PROJECTION




## REVISIONS

| REV | ECN No. | DESCRIPTION                                   | DATE  | DR | AUTH |
|-----|---------|-----------------------------------------------|-------|----|------|
| OR  | M97254  | NEW RELEASE (FROM RAVON)                      | 03/05 | DK | HH   |
| A   | M102713 | MODIFIED HATCH, NOTES & ADDED "...WITH SMOBC" | 01/06 | GT | IL   |
| B   | M103510 | ADD R7 & CHANGE LOCATION DESIGNATORS          | 07/09 | EM | KN   |
| B   | R63339  | ADD R7 & CHANGE LOCATION DESIGNATORS          | 07/09 | EM | KN   |

## SUGGESTED MOUNTING CONFIGURATION

FOR DG983-1 CASE STYLE, qj PIN CONNECTIONS, 75 Ω.

KEEP-OUT ZONE,  
.025 X.025, AVOID  
TRACES IN THIS AREA  
TO PREVENT SHORT TO  
METAL INDEX ON BOTTOM  
SIDE OF COMPONENT



## NOTES:

- TRACE WIDTH IS SHOWN FOR FR4 WITH DIELECTRIC THICKNESS .025"±.002". COPPER: 1/2 OZ. EACH SIDE.  
FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
- 0603 SIZE CHIP FOOT PRINTS SHOWN FOR REFERENCE,  
VALUES OF RESISTORS WILL VARY BASED ON APPLICATION.
- BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.



DENOTES PCB COPPER LAYOUT WITH SMOBC  
(SOLDER MASK OVER BARE COPPER)



DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

UNLESS OTHERWISE SPECIFIED

INITIALS

DATE

DIMENSIONS ARE IN INCHES

TOLERANCES ON:

2 PL DECIMALS ±

3 PL DECIMALS ± .005

ANGLES ±

FRACTIONS ±

DRAWN

DK (RAVON)

08 MAR 05

CHECKED

RZ (RAVON)

08 MAR 05

APPROVED

HH (RAVON)

08 MAR 05

Mini-Circuits®

THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS.  
EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE  
AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY  
DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO.  
THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE  
PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.

ASHEETA1.DWG REV:A DATE:01/12/95



Mini-Circuits®

13 Neptune Avenue  
Brooklyn NY 11235

PL, qj, DG983-1  
TB-343 (75 Ω)

SIZE

A

CODE IDENT

15542

DRAWING NO:

98-PL-194

REV:

B

FILE:

98PL194

SCALE:


7:1

SHEET:

1 OF 1



# Evaluation Board and Circuit



TB-343

## Notes:

1. N-Type Female connectors.
2. PCB Material: FR4 Grade IT 180TC (ITEQ Corporation) or equivalent, Dielectric Constant=4.7, Thickness=.025 inch.

 **Mini-Circuits®**





All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

| Specification                  | Test/Inspection Condition                               | Reference/Spec                                        |
|--------------------------------|---------------------------------------------------------|-------------------------------------------------------|
| Operating Temperature          | -40° to 85° C or -40° to 105° C<br>Ambient Environment  | Refer to Individual Model Data Sheet                  |
| Storage Temperature            | -55° to 100° C or -65° to 150° C<br>Ambient Environment | Refer to Individual Model Data Sheet                  |
| Temperature Humidity Bias      | 85°C, 85% RH, 96 hours                                  | JESD22-A101B                                          |
| Thermal Shock                  | -55° to 100°C, 100 cycles                               | MIL-STD-202, Method 107, Condition A-3, except +100°C |
| Solder Reflow Heat             | Pb-Free Process: 260°C peak                             | J-STD-020, Table 4-1, 4-2 and 5-2; Figure 5-1         |
| Solderability                  | 10X magnification, 95% coverage                         | JESD22-B102, Method 1: Dip and Look Test              |
| Marking Resistance to Solvents | Laser marked, visual observation                        | Mini-Circuits D4-Q4T0-04                              |