

Surface Mount

# Frequency Mixer

## JMS-1H

Level 17 (LO Power +17 dBm) 2 to 500 MHz



Generic photo used for illustration purposes only

CASE STYLE: BH292

### Maximum Ratings

Operating Temperature	-40°C to 85°C
Storage Temperature	-55°C to 100°C
RF Power	200mW
IF Current	40mA
Permanent damage may occur if any of these limits are exceeded.	

### Pin Connections

LO	6
RF	3
IF	2
GROUND	1,4,5


### Features

- low conversion loss, 5.90 dB typ.
- excellent L-R isolation, up to 60 dB typ.
- miniature surface mount
- J-leads for strain relief and excellent solderability

### Applications

- up & down converters for receivers & transmitters
- VHF/UHF


### Outline Drawing



### Outline Dimensions (inch/mm)

A	B	C	D	E	F	G		
.280	.310	--	.100	.225	.055	.100		
7.11	7.87	--	2.54	5.72	1.40	2.54		
H	J	K	L				wt	
.047	.065	.065	.300				grams	
1.19	1.65	1.65	7.62				0.45	

### Demo Board MCL P/N: TB-03 Suggested PCB Layout (PL-052)



- NOTES: 1. TRACE WIDTH IS SHOWN FOR ROGERS RO4350B WITH DIELECTRIC THICKNESS .030" ± .002"; COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.  
2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.

- DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)
- DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

### Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.  
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.  
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)

### Electrical Specifications

FREQUENCY (MHz)	CONVERSION LOSS (dB)	LO-RF ISOLATION (dB)			LO-IF ISOLATION (dB)			IP3 at center band (dBm)										
		L	M	U	L	M	U											
2-500	DC-500	5.90	.10	7.0	8.5	60	45	50	25	37	22	55	45	50	25	37	22	22


1 dB COMP.: +14 dBm typ.







L = low range [ $f_l$  to  $10 f_l$ ] M = mid range [ $10 f_l$  to  $f_u/2$ ] U = upper range [ $f_u/2$  to  $f_u$ ]  
m = mid band [ $2f_l$  to  $f_u/2$ ]

### Typical Performance Data

Frequency (MHz)		Conversion Loss (dB)	Isolation L-R (dB)	Isolation L-I (dB)	VSWR RF Port (:1)	VSWR LO Port (:1)
RF	LO	LO +17dBm	LO +17dBm	LO +17dBm	LO +17dBm	LO +17dBm
2.00	32.00	6.78	79.29	69.19	1.33	1.77
4.00	34.00	6.60	72.35	63.39	1.20	1.75
5.00	35.00	6.57	71.51	62.98	1.15	1.82
10.00	40.00	6.55	65.84	61.30	1.14	1.82
20.00	50.00	6.48	59.50	58.68	1.13	1.75
35.20	65.20	6.36	51.64	53.67	1.14	1.75
50.00	80.00	6.53	51.61	53.63	1.14	1.76
85.00	55.00	6.47	45.13	48.67	1.15	1.74
100.00	70.00	6.48	44.98	48.52	1.17	1.71
134.80	104.80	6.32	41.19	46.50	1.19	1.69
184.60	154.60	6.35	38.78	44.90	1.22	1.65
200.00	170.00	6.40	38.62	44.42	1.23	1.62
234.40	204.40	6.30	36.44	41.20	1.24	1.63
250.00	220.00	6.22	36.14	41.01	1.26	1.62
284.20	254.20	6.22	35.11	38.57	1.30	1.58
334.00	304.00	6.18	33.38	37.07	1.34	1.54
383.80	353.80	6.11	32.33	33.77	1.39	1.51
433.60	403.60	6.16	32.22	31.10	1.44	1.45
483.40	453.40	6.45	31.29	29.09	1.47	1.41
500.00	470.00	6.45	30.80	28.30	1.49	1.39

### Electrical Schematic





**Notes**

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuit's standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuit's website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)



# Frequency Mixer

# JMS-1H

## Typical Performance Data

RF (IN) (MHz)	LO (MHz)	CONVERSION LOSS IF FIXED @IF(OUT)=30MHz (dB)			RF (IN) (MHz)	LO (MHz)	IP3 INPUT (dBm)			RF (IN) (MHz)	LO (MHz)	COMPRESSION @RF IN=+14dBm (dB)		
		@LO (dBm)					@LO (dBm)					@LO (dBm)		
		+14	+17	+20			+14	+17	+20			+14	+17	+20
2.0	32.0	7.57	6.78	6.41	10.1	40.1	26.94	30.37	34.44	10.1	40.1	0.90	0.53	0.34
5.0	35.0	7.37	6.57	6.17	49.8	79.8	24.72	28.84	30.94	49.8	79.8	0.72	0.44	0.30
10.0	40.0	7.34	6.55	6.16	89.5	119.5	25.01	27.92	28.85	89.5	119.5	0.76	0.40	0.26
49.8	79.8	6.98	6.37	6.07	129.2	159.2	26.59	28.31	28.59	129.2	159.2	0.79	0.42	0.25
89.5	119.5	6.96	6.32	6.04	168.9	198.9	25.94	26.82	28.43	168.9	198.9	0.75	0.39	0.23
168.9	198.9	6.84	6.28	6.09	208.6	238.6	27.31	27.25	33.65	208.6	238.6	0.84	0.41	0.24
208.6	238.6	6.69	6.24	6.06	248.3	278.3	24.49	26.95	33.17	248.3	278.3	0.82	0.43	0.26
248.3	278.3	6.86	6.36	6.17	287.9	317.9	24.59	28.97	27.40	287.9	317.9	0.88	0.41	0.29
287.9	317.9	6.71	6.32	6.14	327.6	357.6	24.64	28.20	29.68	327.6	357.6	0.84	0.40	0.26
327.6	357.6	6.78	6.41	6.25	367.3	397.3	25.22	29.09	31.07	367.3	397.3	0.82	0.47	0.34
367.3	397.3	6.83	6.39	6.17	407.0	437.0	26.61	24.07	24.61	407.0	437.0	0.80	0.43	0.34
407.0	437.0	6.81	6.44	6.19	446.7	476.7	25.29	24.45	23.17	446.7	476.7	0.77	0.35	0.26
446.7	476.7	6.95	6.60	6.38	486.4	516.4	24.37	28.08	26.16	486.4	516.4	0.91	0.41	0.34
486.4	516.4	6.94	6.56	6.31	526.1	556.1	23.10	30.99	27.73	526.1	556.1	1.01	0.53	0.40
526.1	556.1	7.04	6.57	6.27	565.8	595.8	24.26	29.52	27.87	565.8	595.8	1.06	0.71	0.48
565.8	595.8	7.08	6.52	6.23	585.6	615.6	28.16	27.25	28.32	585.6	615.6	0.99	0.68	0.48
585.6	615.6	7.20	6.58	6.27	625.3	655.3	21.03	30.35	28.79	625.3	655.3	1.05	0.75	0.56
625.3	655.3	7.28	6.72	6.38	645.2	675.2	20.51	24.12	28.75	645.2	675.2	1.00	0.70	0.56
645.2	675.2	7.37	6.85	6.47	684.9	714.9	18.64	19.42	23.43	684.9	714.9	0.98	0.69	0.54
684.9	714.9	7.45	6.99	6.63	704.7	734.7	18.22	18.36	21.03	704.7	734.7	1.09	0.77	0.60
704.7	734.7	7.54	7.10	6.76	744.4	774.4	18.02	17.48	18.85	744.4	774.4	1.05	0.73	0.58
764.3	794.3	7.76	7.35	7.03	764.3	794.3	18.21	17.56	18.26	764.3	794.3	1.08	0.81	0.65
803.9	833.9	7.95	7.52	7.16	823.8	853.8	18.94	18.76	19.21	823.8	853.8	1.17	0.84	0.69
823.8	853.8	8.00	7.53	7.15	863.5	893.5	18.93	19.23	20.58	863.5	893.5	1.20	0.90	0.74
863.5	893.5	8.11	7.51	7.07	883.3	913.3	19.36	19.66	21.50	883.3	913.3	1.28	1.00	0.78
883.3	913.3	8.05	7.41	7.01	923.0	953.0	18.98	20.82	23.93	923.0	953.0	1.37	1.05	0.83
923.0	953.0	8.06	7.36	6.99	942.9	972.9	19.21	21.79	24.59	942.9	972.9	1.44	1.07	0.85
942.9	972.9	8.07	7.37	7.03	982.6	1012.6	20.50	24.02	27.90	982.6	1012.6	1.56	1.14	0.91
982.6	1012.6	8.10	7.46	7.12	1002.4	1032.4	21.56	25.95	31.73	1002.4	1032.4	1.55	1.18	0.96
1002.4	1032.4	8.22	7.56	7.23	1042.1	1072.1	24.21	30.15	27.44	1042.1	1072.1	1.61	1.30	1.04
1042.1	1072.1	8.43	7.68	7.34	1061.9	1091.9	24.96	27.80	26.18	1061.9	1091.9	1.51	1.27	1.05
1061.9	1091.9	8.70	7.90	7.50	1101.6	1131.6	22.17	23.67	25.11	1101.6	1131.6	1.41	1.29	1.13
1101.6	1131.6	9.17	8.18	7.70	1121.5	1151.5	20.64	22.95	24.74	1121.5	1151.5	1.32	1.28	1.13
1121.5	1151.5	9.50	8.37	7.83	1161.2	1191.2	18.73	21.92	25.17	1161.2	1191.2	1.18	1.29	1.21
1181.0	1211.0	10.46	8.99	8.28	1181.0	1211.0	17.91	21.54	25.47	1181.0	1211.0	1.04	1.28	1.25
1220.7	1250.7	11.01	9.43	8.65	1220.7	1250.7	17.70	23.20	26.92	1220.7	1250.7	0.94	1.29	1.29
1240.6	1270.6	11.29	9.66	8.87	1240.6	1270.6	17.21	23.95	25.45	1240.6	1270.6	0.88	1.22	1.26
1280.3	1310.3	11.89	10.30	9.50	1280.3	1310.3	17.53	24.46	24.75	1280.3	1310.3	0.77	1.11	1.12
1300.1	1330.1	12.18	10.53	9.76	1300.1	1330.1	17.44	25.14	23.70	1300.1	1330.1	0.81	1.04	1.05



# Frequency Mixer

# JMS-1H

## Typical Performance Data

IF (OUT) (MHz)	LO (MHz)	CONVERSION LOSS VS. IF FREQUENCY @RF(IN)=250.1MHz (dB)	IF (OUT) (MHz)	LO (MHz)	CONVERSION LOSS VS. IF FREQUENCY @RF(IN)=10.1MHz (dB)	IF (OUT) (MHz)	LO (MHz)	CONVERSION LOSS VS. IF FREQUENCY @RF(IN)=500.1MHz (dB)
		@LO (dBm)			@LO (dBm)			@LO (dBm)
		+17			+17			+17
240.0	10.1	6.38	10.0	20.1	6.15	490.0	10.1	6.48
234.1	16.0	6.40	22.3	32.4	6.12	477.7	22.4	6.42
228.2	21.9	6.27	34.6	44.7	6.12	465.4	34.7	6.38
222.3	27.8	6.32	46.9	57.0	6.12	453.1	47.0	6.42
216.4	33.7	6.29	59.2	69.3	6.04	440.8	59.3	6.46
210.5	39.6	6.26	71.5	81.6	6.10	428.5	71.6	6.30
204.6	45.5	6.34	83.8	93.9	6.19	416.2	83.9	6.29
198.7	51.4	6.24	96.2	106.3	6.12	403.8	96.3	6.25
192.8	57.3	6.26	108.5	118.6	6.11	391.5	108.6	6.19
186.9	63.2	6.26	120.8	130.9	6.06	379.2	120.9	6.20
181.0	69.1	6.24	133.1	143.2	6.04	366.9	133.2	6.10
175.1	75.0	6.34	145.4	155.5	6.16	354.6	145.5	6.04
169.2	80.9	6.30	157.7	167.8	6.21	342.3	157.8	6.06
163.3	86.8	6.24	170.0	180.1	6.16	330.0	170.1	6.06
157.4	92.7	6.30	182.3	192.4	6.19	317.7	182.4	6.05
151.5	98.6	6.19	194.6	204.7	6.19	305.4	194.7	6.02
145.6	104.5	6.25	206.9	217.0	6.21	293.1	207.0	5.98
139.7	110.4	6.23	219.2	229.3	6.26	280.8	219.3	5.96
133.8	116.3	6.14	231.5	241.6	6.23	268.5	231.6	6.03
127.9	122.2	6.16	243.8	253.9	6.24	256.2	243.9	6.02
122.1	128.0	6.09	256.2	266.3	6.33	243.8	256.3	6.03
116.2	133.9	6.08	268.5	278.6	6.36	231.5	268.6	6.07
110.3	139.8	6.19	280.8	290.9	6.35	219.2	280.9	6.05
104.4	145.7	6.14	293.1	303.2	6.38	206.9	293.2	6.09
98.5	151.6	6.16	305.4	315.5	6.35	194.6	305.5	6.11
92.6	157.5	6.13	317.7	327.8	6.43	182.3	317.8	6.07
86.7	163.4	6.10	330.0	340.1	6.47	170.0	330.1	6.11
80.8	169.3	6.17	342.3	352.4	6.42	157.7	342.4	6.15
74.9	175.2	6.15	354.6	364.7	6.43	145.4	354.7	6.15
69.0	181.1	6.15	366.9	377.0	6.46	133.1	367.0	6.21
63.1	187.0	6.14	379.2	389.3	6.47	120.8	379.3	6.20
57.2	192.9	6.09	391.5	401.6	6.55	108.5	391.6	6.19
51.3	198.8	6.13	403.8	413.9	6.50	96.2	403.9	6.27
45.4	204.7	6.16	416.2	426.3	6.51	83.8	416.3	6.29
39.5	210.6	6.20	428.5	438.6	6.62	71.5	428.6	6.34
33.6	216.5	6.22	440.8	450.9	6.66	59.2	440.9	6.42
27.7	222.4	6.19	453.1	463.2	6.71	46.9	453.2	6.42
21.8	228.3	6.23	465.4	475.5	6.69	34.6	465.5	6.52
15.9	234.2	6.26	477.7	487.8	6.58	22.3	477.8	6.60
10.0	240.1	6.25	490.0	500.1	6.57	10.0	490.1	6.54

REV. X2  
JMS-1H  
100817

Page 2 of 5



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED • RoHS compliant  
P.O. Box 350166, Brooklyn, New York 11235-0006 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see



# Frequency Mixer

# JMS-1H

## Typical Performance Data

LO (MHz)	LO-RF ISOLATION (dB)			LO-IF ISOLATION (dB)		
	@LO (dBm)			@LO (dBm)		
	+14	+17	+20	+14	+17	+20
2.0	81.98	79.29	82.48	71.18	69.19	68.76
5.0	71.15	71.51	71.45	68.75	62.98	59.64
10.0	65.40	65.84	66.21	67.50	61.30	57.95
49.8	57.76	57.96	58.09	60.52	51.59	48.08
89.5	52.71	52.48	52.55	59.09	48.58	44.72
168.9	45.96	45.94	46.30	54.53	44.41	40.47
208.6	43.79	44.16	44.33	49.72	43.38	39.59
248.3	41.98	42.27	42.33	47.34	42.53	38.58
287.9	40.89	41.12	40.81	41.79	40.70	37.67
327.6	39.63	39.94	39.99	38.80	38.43	36.62
367.3	38.61	38.46	38.63	35.97	35.79	34.92
407.0	38.06	37.52	37.37	33.89	34.41	33.85
446.7	37.11	36.93	36.67	31.81	32.82	32.84
486.4	36.29	36.22	36.28	29.90	31.02	31.72
526.1	35.54	35.77	36.05	28.56	29.62	30.34
565.8	35.14	35.65	35.65	26.81	27.79	28.76
585.6	34.89	35.49	35.53	26.57	27.42	28.37
625.3	34.00	34.46	34.38	25.44	26.55	27.36
645.2	33.60	34.21	34.15	24.98	26.29	27.01
684.9	32.45	33.37	33.59	24.10	25.75	26.84
704.7	31.90	32.79	33.16	23.80	25.46	26.73
764.3	31.03	31.84	32.78	22.97	24.69	26.35
803.9	30.80	31.67	32.84	22.70	24.55	26.23
823.8	30.79	31.72	33.00	22.50	24.40	26.12
863.5	30.87	32.27	34.52	22.09	24.17	25.96
883.3	30.88	32.60	34.97	21.92	24.10	25.76
923.0	31.72	34.25	36.01	21.31	23.37	24.68
942.9	32.22	34.56	35.79	21.17	23.18	24.44
982.6	32.88	33.90	34.30	20.61	22.50	23.65
1002.4	32.62	33.20	33.48	20.43	22.27	23.38
1042.1	31.88	31.78	31.83	19.78	21.63	22.89
1061.9	31.42	31.08	31.13	19.64	21.55	22.90
1101.6	30.13	29.69	29.71	19.02	20.95	22.42
1121.5	29.84	29.19	29.13	18.75	20.80	22.44
1181.0	28.05	27.67	27.65	18.07	20.34	22.43
1220.7	26.87	26.72	26.79	17.43	19.77	22.16
1240.6	26.34	26.39	26.54	17.30	19.70	22.26
1280.3	25.28	25.64	25.85	16.89	19.30	22.02
1300.1	24.56	25.06	25.48	16.77	19.20	22.01

RF (IN) (MHz)	LO (MHz)	RF-IF ISOLATION (dB)		
		@LO (dBm)		
		+14	+17	+20
10.1	40.1	44.10	47.29	41.99
49.8	79.8	33.67	33.76	33.32
89.5	119.5	29.24	29.25	29.29
129.2	159.2	26.54	26.79	26.78
168.9	198.9	24.78	24.98	25.14
208.6	238.6	23.59	23.90	24.05
248.3	278.3	22.76	22.97	23.18
287.9	317.9	22.52	22.73	22.87
327.6	357.6	22.13	22.69	23.04
367.3	397.3	21.72	22.54	23.29
407.0	437.0	21.98	22.58	23.42
446.7	476.7	22.61	22.97	23.31
486.4	516.4	23.40	23.57	23.66
526.1	556.1	23.37	23.72	24.02
565.8	595.8	21.53	22.20	23.02
585.6	615.6	20.39	20.86	21.55
625.3	655.3	18.23	18.56	18.90
645.2	675.2	17.38	17.71	17.98
684.9	714.9	15.86	16.01	16.31
704.7	734.7	15.28	15.36	15.62
744.4	774.4	14.32	14.23	14.36
764.3	794.3	13.92	13.79	13.73
823.8	853.8	13.05	12.66	12.45
863.5	893.5	12.45	12.00	11.87
883.3	913.3	12.13	11.73	11.71
923.0	953.0	11.47	11.33	11.37
942.9	972.9	11.27	11.16	11.25
982.6	1012.6	10.94	10.93	11.03
1002.4	1032.4	10.84	10.86	11.01
1042.1	1072.1	10.60	10.73	10.91
1061.9	1091.9	10.57	10.71	10.93
1101.6	1131.6	10.35	10.58	10.88
1121.5	1151.5	10.18	10.53	10.85
1161.2	1191.2	9.99	10.41	10.83
1181.0	1211.0	9.83	10.35	10.74
1220.7	1250.7	9.57	10.21	10.59
1240.6	1270.6	9.43	10.10	10.44
1280.3	1310.3	9.08	9.77	10.12
1300.1	1330.1	8.87	9.59	9.89

REV. X2  
JMS-1H  
100817  
Page 3 of 5



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED • RoHS compliant  
P.O. Box 350166, Brooklyn, New York 11235-0006 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, instantly • For detailed performance specs & shopping online see



# Frequency Mixer

# JMS-1H

## Typical Performance Data

RF (IN) (MHz)	LO (MHz)	RF VSWR (:1)			LO (MHz)	LO VSWR (:1)			IF (OUT) (MHz)	IF VSWR @LO=500.5MHz (:1)		
		@LO (dBm)				@LO (dBm)				@LO (dBm)		
		+14	+17	+20		+14	+17	+20		+14	+17	+20
2.0	32.0	1.31	1.33	1.37	2.0	1.22	1.77	2.58	2.0	1.02	1.07	1.13
5.0	35.0	1.17	1.20	1.25	5.0	1.15	1.75	2.56	5.0	1.01	1.06	1.12
10.0	40.0	1.11	1.15	1.20	10.0	1.22	1.82	2.67	10.0	1.02	1.04	1.10
49.8	79.8	1.21	1.07	1.02	49.8	1.04	1.66	2.48	22.3	2.07	1.84	1.64
89.5	119.5	1.20	1.07	1.03	89.5	1.01	1.56	2.26	34.5	1.97	1.76	1.58
129.2	159.2	1.18	1.05	1.04	129.2	1.02	1.62	2.42	46.8	2.01	1.80	1.61
168.9	198.9	1.17	1.04	1.05	168.9	1.02	1.58	2.31	59.0	2.04	1.81	1.61
208.6	238.6	1.14	1.02	1.07	208.6	1.04	1.60	2.35	71.3	2.01	1.79	1.59
248.3	278.3	1.16	1.03	1.06	248.3	1.05	1.64	2.40	83.5	2.04	1.81	1.62
287.9	317.9	1.11	1.01	1.09	287.9	1.10	1.63	2.35	95.8	2.06	1.83	1.63
327.6	357.6	1.10	1.03	1.10	327.6	1.12	1.70	2.46	108.0	2.09	1.87	1.66
367.3	397.3	1.09	1.06	1.15	367.3	1.19	1.70	2.41	120.3	2.03	1.81	1.62
407.0	437.0	1.07	1.06	1.16	407.0	1.21	1.75	2.47	132.5	2.04	1.82	1.62
446.7	476.7	1.07	1.07	1.14	446.7	1.26	1.80	2.52	144.8	2.00	1.78	1.59
486.4	516.4	1.08	1.13	1.21	486.4	1.30	1.80	2.50	157.0	2.02	1.79	1.60
526.1	556.1	1.12	1.20	1.29	526.1	1.34	1.84	2.55	169.3	2.03	1.80	1.60
565.8	595.8	1.16	1.27	1.37	565.8	1.43	1.87	2.54	181.5	2.07	1.83	1.64
585.6	615.6	1.18	1.30	1.40	585.6	1.46	1.91	2.58	193.8	2.12	1.88	1.68
625.3	655.3	1.21	1.33	1.45	625.3	1.54	2.03	2.69	206.0	2.07	1.85	1.65
645.2	675.2	1.23	1.32	1.45	645.2	1.55	2.05	2.71	218.3	2.08	1.85	1.65
684.9	714.9	1.26	1.33	1.46	684.9	1.59	2.10	2.77	230.5	2.04	1.80	1.62
704.7	734.7	1.28	1.33	1.44	704.7	1.61	2.15	2.83	242.8	2.03	1.80	1.61
764.3	794.3	1.31	1.34	1.41	764.3	1.65	2.17	2.85	255.0	2.02	1.79	1.61
803.9	833.9	1.33	1.35	1.42	803.9	1.66	2.18	2.87	267.3	2.04	1.81	1.62
823.8	853.8	1.34	1.36	1.43	823.8	1.67	2.18	2.86	291.8	2.08	1.85	1.65
863.5	893.5	1.37	1.40	1.48	863.5	1.67	2.14	2.80	304.0	2.08	1.84	1.65
883.3	913.3	1.40	1.44	1.51	883.3	1.67	2.13	2.80	316.3	2.10	1.86	1.66
923.0	953.0	1.48	1.52	1.58	923.0	1.68	2.12	2.79	328.5	2.04	1.81	1.62
942.9	972.9	1.54	1.58	1.63	942.9	1.69	2.12	2.80	340.8	2.04	1.81	1.62
982.6	1012.6	1.69	1.72	1.76	982.6	1.76	2.18	2.84	353.0	2.04	1.81	1.62
1002.4	1032.4	1.78	1.81	1.84	1002.4	1.83	2.22	2.88	365.3	2.06	1.83	1.64
1042.1	1072.1	1.99	1.99	2.02	1042.1	1.98	2.32	2.95	377.5	2.06	1.83	1.64
1061.9	1091.9	2.13	2.11	2.13	1061.9	2.07	2.38	2.99	389.8	2.06	1.83	1.64
1101.6	1131.6	2.43	2.37	2.35	1101.6	2.26	2.49	3.05	402.0	2.10	1.86	1.66
1121.5	1151.5	2.60	2.52	2.48	1121.5	2.35	2.54	3.09	414.3	2.11	1.87	1.67
1161.2	1191.2	2.93	2.79	2.71	1161.2	2.55	2.66	3.17	426.5	2.09	1.85	1.66
1181.0	1211.0	3.10	2.93	2.83	1181.0	2.64	2.71	3.20	438.8	2.09	1.85	1.65
1220.7	1250.7	3.38	3.19	3.05	1220.7	2.85	2.81	3.25	451.0	2.02	1.80	1.61
1240.6	1270.6	3.49	3.29	3.14	1240.6	2.95	2.87	3.30	463.3	2.03	1.81	1.63
1280.3	1310.3	3.69	3.50	3.37	1280.3	3.15	2.99	3.38	487.8	2.11	1.88	1.70
1300.1	1330.1	3.74	3.57	3.44	1300.1	3.30	3.05	3.40	500.0	1.99	1.78	1.62

REV. X2  
JMS-1H  
100817  
Page 4 of 5



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED RoHS compliant  
P.O. Box 350166, Brooklyn, New York 11235-0006 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see



## Harmonics Tables

RF HARMONICS ORDER

	(-dBm)	(-dBc)										
0	-	-	16	21	11	28	16	29	21	47	27	42
1	-	17	+0	28	14	32	21	34	34	46	30	51
2	88	71	46	64	45	61	44	58	45	56	49	61
3	>100	61	60	66	53	67	50	67	50	64	47	62
4	>100	81	78	79	82	81	73	81	70	91	69	74
5	>100	80	79	85	73	85	71	79	70	81	70	>93
6	>100	>93	>93	>93	>93	>93	>93	>93	90	>93	88	>93
7	>100	>93	>93	>93	>93	>93	89	88	88	>93	90	>93
8	>100	>93	>93	>93	>93	>93	>93	>93	>93	>93	>93	>93
9	>100	>93	>93	>93	>93	>93	>93	>93	>93	71	>93	>93
10	>100	>93	>93	>93	>93	>93	>93	>93	>93	>93	83	>93
	RF CAL	0	1	2	3	4	5	6	7	8	9	10

### LO HARMONICS ORDER

Test conditions: RF IN: 250.1 MHz; -1.00 dBm.  
 LO IN: 280.01 MHz; +17.00 dBm  
 IF OUT: 29.91 MHz; -7.34 dBm

RF HARMONICS ORDER

	(-dBm)	(-dBc)										
0	-	-	25	32	23	43	31	50	41	56	43	61
1	-	17	+0	29	13	35	21	34	31	45	40	66
2	76	56	41	64	39	53	38	50	39	51	43	63
3	>100	45	45	49	56	56	43	49	55	62	42	59
4	>100	69	57	69	56	65	56	62	52	64	53	68
5	>100	61	83	69	57	65	51	58	47	59	47	64
6	>100	72	64	81	64	79	68	78	66	74	62	80
7	>100	73	72	81	68	74	71	75	63	70	62	68
8	>100	82	76	81	76	87	75	85	75	81	71	78
9	>100	85	77	77	75	85	74	85	71	77	70	79
10	>100	96	88	90	>103	85	83	83	80	96	78	90
	RF CAL	0	1	2	3	4	5	6	7	8	9	10

### LO HARMONICS ORDER

Test conditions: RF IN: 250.1 MHz; 9.00 dBm.  
 LO IN: 280.01 MHz; +17.00 dBm  
 IF OUT: 29.91 MHz; 2.61 dBm

- Notes: 1. All Harmonics are in (dBc) relative to IF OUTPUT.  
 2. + entry denotes harmonics are in (dBc) above IF OUTPUT.  
 3. RF Cal represent the Harmonics level of the RF input signal to the mixer.

REV. X2  
 JMS-1H  
 100817

Page 5 of 5



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED • RoHS compliant  
 P.O. Box 350166, Brooklyn, New York 11235-0006 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see [minicircuits.com](http://www.minicircuits.com)




# Frequency Mixer


# JMS-1H

## Typical Performance Curves


### Conversion Loss @ IF=30MHz




### Conversion Loss vs. IF @ RF=250.1MHz




### Conversion Loss vs. IF @ RF=10.1MHz




### Conversion Loss vs. IF @ RF=500.1MHz



### IP3 Input



### Compression @ RF IN=+14dBm



REV. X2

JMS-1H

100817

Page 1 of 3



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED • RoHS compliant  
P.O. Box 350166, Brooklyn, New York 11235-0006 (718) 934-4500 Fax (718) 332-4661




The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see






## Typical Performance Curves


LO-RF Isolation




LO-IF Isolation




RF-IF Isolation




RF VSWR



LO VSWR



IF VSWR



## Harmonics Tables

RF HARMONICS ORDER

	(-dBm)	(-dBc)										
0	-	-	16	21	11	28	16	29	21	47	27	42
1	-	17	+0	28	14	32	21	34	34	46	30	51
2	88	71	46	64	45	61	44	58	45	56	49	61
3	>100	61	60	66	53	67	50	67	50	64	47	62
4	>100	81	78	79	82	81	73	81	70	91	69	74
5	>100	80	79	85	73	85	71	79	70	81	70	>93
6	>100	>93	>93	>93	>93	>93	>93	>93	90	>93	88	>93
7	>100	>93	>93	>93	>93	>93	89	88	88	>93	90	>93
8	>100	>93	>93	>93	>93	>93	>93	>93	>93	>93	>93	>93
9	>100	>93	>93	>93	>93	>93	>93	>93	>93	71	>93	>93
10	>100	>93	>93	>93	>93	>93	>93	>93	>93	>93	83	>93
	RF CAL	0	1	2	3	4	5	6	7	8	9	10

### LO HARMONICS ORDER

Test conditions: RF IN: 250.1 MHz; -1.00 dBm.  
 LO IN: 280.01 MHz; +17.00 dBm  
 IF OUT: 29.91 MHz; -7.34 dBm

RF HARMONICS ORDER

	(-dBm)	(-dBc)										
0	-	-	25	32	23	43	31	50	41	56	43	61
1	-	17	+0	29	13	35	21	34	31	45	40	66
2	76	56	41	64	39	53	38	50	39	51	43	63
3	>100	45	45	49	56	56	43	49	55	62	42	59
4	>100	69	57	69	56	65	56	62	52	64	53	68
5	>100	61	83	69	57	65	51	58	47	59	47	64
6	>100	72	64	81	64	79	68	78	66	74	62	80
7	>100	73	72	81	68	74	71	75	63	70	62	68
8	>100	82	76	81	76	87	75	85	75	81	71	78
9	>100	85	77	77	75	85	74	85	71	77	70	79
10	>100	96	88	90	>103	85	83	83	80	96	78	90
	RF CAL	0	1	2	3	4	5	6	7	8	9	10

### LO HARMONICS ORDER

Test conditions: RF IN: 250.1 MHz; 9.00 dBm.  
 LO IN: 280.01 MHz; +17.00 dBm  
 IF OUT: 29.91 MHz; 2.61 dBm

- Notes: 1. All Harmonics are in (dBc) relative to IF OUTPUT.  
 2. + entry denotes harmonics are in (dBc) above IF OUTPUT.  
 3. RF Cal represent the Harmonics level of the RF input signal to the mixer.

REV. X2  
 JMS-1H  
 100817

Page 3 of 3






IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED • RoHS compliant  
 P.O. Box 350166, Brooklyn, New York 11235-0006 (718) 934-4500 Fax (718) 332-4661




The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see [minicircuits.com](http://www.minicircuits.com)

### Outline Dimensions



### PCB Land Pattern




CASE #	A	B	C	D	E	F	G	H	J	K	L	WT. GRAM
BH292	.280 (7.11)	.310 (7.87)	- -	.100 (2.54)	.225 (5.72)	.055 (1.40)	.100 (2.54)	.047 (1.19)	.065 (1.65)	.065 (1.65)	.300 (7.62)	.45

Dimensions are in inches (mm). Tolerances: 2Pl.  $\pm.01$ ; 3Pl.  $\pm.005$

#### Notes:

- Case material: Ceramic.
- Termination finish:  
 For RoHS Case Styles: Tin plate over Nickel plate. All models, (+) suffix.  
 For RoHS-5 Case Styles: Tin-Lead plate. All models, no (+) suffix.

# Tape & Reel Packaging TR-F24



Tape Width, mm	Device Cavity Pitch, mm	Reel Size, inches	Devices per Reel
16	12	13	500

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: [www.minicircuits.com/pages/pdfs/tape.pdf](http://www.minicircuits.com/pages/pdfs/tape.pdf)



INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified

THIRD ANGLE PROJECTION



REVISIONS

REV	ECN No.	DESCRIPTION	DATE	DR	AUTH
A	M101143	ADDED "gk" PIN CONNECTION, TT100 CASE STYLE & NOTE 2	10/10/05	MMG	DJ
B	M102713	ADDED "...WITH SMOBC"	01/17/06	MMG	IL
C	M108637	REMOVED "PIN 1", ADDED INDEX ON UNIT	12/01/06	MYG	FL

SUGGESTED MOUNTING CONFIGURATION  
FOR BH292, CD541/542/636/637, TT100/240 CASE  
STYLES, "gk", "ht", "hu", "nd", "w" PIN CONNECTIONS



- NOTES:** 1. TRACE WIDTH IS SHOWN FOR ROGERS R04350B WITH DIELECTRIC THICKNESS .030" ± .002"; COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.  
 2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.

- DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)
- DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

UNLESS OTHERWISE SPECIFIED	INITIALS	DATE
DIMENSIONS ARE IN INCHES	MMG	07/17/02
TOLERANCES ON:	WL	08/02/02
2 PL DECIMALS ±	DJ	08/05/02
3 PL DECIMALS ± .005		
ANGLES ±		
FRACTIONS ±		


**Mini-Circuits®** 13 Neptune Avenue  
 Brooklyn NY 11235

PL, gk/ht/hu/nd/w, BH292,  
 CD541/542/636/637, TT100/240, TB-03

SIZE A	CODE IDENT 15542	DRAWING NO: 98-PL-052	REV: C
FILE: 98PL052	SCALE: 8:1	SHEET: 1 OF 1	


Mini-Circuits®  
 THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.

THIRD ANGLE PROJECTION



REVISIONS

REV	ECN No.	DESCRIPTION	DATE	DR	AUTH
E	M119737	UPDATED PCB	10.08	MF	AD
F	M127659	UPDATED CARR	06.10	SW	SG
G	M127846	UPDATED SCHEMATIC DIAGRAM	06.10	SW	SG
H	M131840	UPDATED DWG	05.11	MF	AD




**NOTES:**

1. REFER TO -09 PAGE FOR ITEM DESCRIPTIONS.  
DESIGNATION NUMBERS ON -20 PAGE CORRESPOND TO THE NUMBERS ON -09 PAGE.
2. FOR TEXT HEIGHT & STYLE ON THE LABEL REFER TO: D3-G209.

UNLESS OTHERWISE SPECIFIED	INITIALS	DATE
DIMENSIONS ARE IN INCHES TOLERANCES ON: 2 PL DECIMALS ± 3 PL DECIMALS ± ANGLES ± FRACTIONS ±	DRAWN	S.WOLYNSKI 06.29.99
	CHECKED	SG 07.06.99
	APPROVED	MG 07.10.99

 **Mini-Circuits®** 13 Neptune Avenue  
Brooklyn NY 11235


TB,ADE,CD542/636,06MX01,50

 Mini-Circuits®  
THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.


SIZE A	CODE IDENT 15542	DRAWING NO: TB-03-20	REV: H
FILE: WTB-03	SCALE: 1.5:1	SHEET: 1 OF 2	

# Evaluation Board and Circuit

For Pin Connections and DUT Orientation Refer to  
Data Sheet of the DUT




TB-03



Schematic Diagram

## Notes:

1. 50 Ohm SMA Female connectors.
2. PCB Material: Rogers R04350 or equivalent,  
Dielectric Constant=3.5, Thickness=.030 inch.

 **Mini-Circuits®**



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-40° to 85°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Humidity	90 to 95% RH, 240 hours, 50°C	MIL-STD-202, Method 103, Condition A, Except 50°C and end-point electrical test done within 12 hours
Thermal Shock	-55° to 100°C, 100 cycles	MIL-STD-202, Method 107, Condition A-3, except +100°C
Solder Reflow Heat	Sn-Pb Eutetic Process: 225°C peak Pb-Free Process 245° - 250°C peak	J-STD-020, Table 4-1, 4-2 and 5-2, Figure 5-1
Solderability	10X Magnification	J-STD-002, 95% Coverage
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes	MIL-STD-202, Method 213, Condition A
Marking Resistance to Solvents	Isopropyl alcohol + mineral spirits at 25°C; terpene defluxer at 25°C; distilled water + proylene glycol monomethyl ether + monoethanolamine at 63°C to 70°C	MIL-STD-202, Method 215