

Engineering Development Model

Frequency Synthesizer

KSN-EDR8066

Important Note

This model has been designed, built and tested in our engineering department. Performance data represents model capability. At present it is a non-catalog model. On request, we can supply a final specification sheet, part number and price/delivery information.



Please click "Back", and then click "Contact Us" for Applications support.

CASE STYLE : DK801

ELECTRICAL SPECIFICATIONS 50Ω, over -45°C to +85°C				
Parameter	Min.	Typ.	Max.	Units
Frequency	409		415	MHz
Step size		20		kHz
Settling Time Within ±1kHz		5		msec
Output Power	-4	0	+4	dBm
Phase Noise				
at 100 Hz offset		-78		dBc/Hz
at 1 kHz offset		-79		dBc/Hz
at 10 KHz offset		-111	-106	dBc/Hz
at 100 KHz offset		-140	-134	dBc/Hz
at 1000 kHz offset		-159		dBc/Hz
Integrated SSB Phase Noise		-44		dBc
Reference Spurious Suppression		-102		dBc
Comparison Spurious Suppression		-112		dBc
Non-Harm. Spurious Suppression		-90		dBc
Harmonic Suppression		-19		dBc
Supply voltage VCO		5		V
Supply voltage PLL		5		V
Supply current VCO		19	27	mA
Supply current PLL		13	21	mA
Reference In (External)				
Frequency		10		MHz
Amplitude		1		Vp-p
Impedance		100		kΩ
Ph. N @ 1kHz		-145		dBc/Hz
Input Logic Levels	Logic high	4	5	V
	Logic Low		1	V
Digital Lock Detect	Locked	4.6	5	V
	Unlocked		0.4	V
Frequency Synthesizer PLL	ADF4118			

ABSOLUTE MAXIMUM RATINGS	
Operating Temperature	-45°C to 85°C
Storage Temperature	-55°C to 100°C
VCO Supply Voltage	6V
PLL Supply Voltage	6V
Reference Frequency voltage	5.8Vp-p
Data, Clock & LE levels	5.3V

Power On sequence: Vcc VCO followed by Vcc PLL

Power Off sequence: Vcc PLL followed by Vcc VCO

PIN CONNECTIONS			
RF OUT	7	CLOCK	10
VCC VCO	5	DATA	11
VCC PLL	1	LATCH ENABLE	12
REF IN	3	GROUND	2,4,6,8,13,14
LOCK DETECT	9		

Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuits' standard limited warranty and terms and conditions (collectively, "Standard Terms"). Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCStore/terms.jsp



www.minicircuits.com P.O. Box 350168, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

REV. OR
KSN-EDR8066
150311

Frequency Synthesizer

KSN-EDR8066

Typical Performance Data

FREQ. (MHz)	POWER OUTPUT (dBm)			HARMONICS						VCO CURRENT (mA)			PLL CURRENT (mA)		
				(dBc)											
				F2			F3								
-45 °C	+25°C	+85 °C	-45 °C	+25°C	+85 °C	-45 °C	+25°C	+85 °C	-45 °C	+25°C	+85 °C	-45 °C	+25°C	+85 °C	
404.0	-0.29	-0.10	-0.15	-16.61	-17.27	-18.49	-41.79	-40.51	-40.51	17.56	18.44	18.68	11.95	13.14	14.02
405.6	-0.31	-0.11	-0.17	-16.86	-17.77	-18.82	-41.22	-40.45	-40.45	17.56	18.44	18.71	11.96	13.15	14.03
407.2	-0.32	-0.12	-0.18	-17.02	-18.19	-19.03	-40.59	-40.21	-40.21	17.57	18.46	18.73	11.96	13.15	14.03
408.8	-0.33	-0.13	-0.19	-17.04	-18.48	-19.11	-39.88	-39.87	-39.87	17.57	18.47	18.75	11.96	13.16	14.03
409.0	-0.33	-0.13	-0.19	-17.05	-18.51	-19.11	-39.86	-39.71	-39.71	17.57	18.47	18.75	11.96	13.16	14.04
410.4	-0.34	-0.14	-0.20	-17.01	-18.65	-19.14	-39.33	-39.28	-39.28	17.57	18.48	18.77	11.96	13.16	14.03
412.0	-0.36	-0.15	-0.21	-16.97	-18.70	-19.10	-39.06	-38.67	-38.67	17.57	18.49	18.79	11.97	13.16	14.04
413.6	-0.38	-0.16	-0.23	-16.99	-18.71	-19.15	-39.12	-38.12	-38.12	17.57	18.51	18.81	11.97	13.16	14.04
415.0	-0.39	-0.18	-0.24	-17.14	-18.67	-19.30	-39.22	-37.94	-37.94	17.57	18.52	18.83	11.97	13.16	14.04
415.2	-0.40	-0.18	-0.25	-17.16	-18.67	-19.33	-39.24	-37.92	-37.92	17.57	18.52	18.83	11.97	13.16	14.04
416.8	-0.42	-0.20	-0.27	-17.53	-18.72	-19.67	-39.26	-37.95	-37.95	17.57	18.53	18.85	11.97	13.16	14.04
418.4	-0.44	-0.22	-0.29	-18.04	-18.92	-20.17	-39.11	-38.18	-38.18	17.58	18.55	18.87	11.97	13.16	14.04
420.0	-0.47	-0.24	-0.32	-18.64	-19.28	-20.77	-38.65	-38.42	-38.42	17.58	18.56	18.89	11.97	13.16	14.04

FREQ. (MHz)	PHASE NOISE (dBc/Hz) @ OFFSETS														
	-45 °C					+25 °C					+85 °C				
	100Hz	1kHz	10kHz	100kHz	1MHz	100Hz	1kHz	10kHz	100kHz	1MHz	100Hz	1kHz	10kHz	100kHz	1MHz
404.0	-76.99	-75.47	-110.36	-135.60	-155.58	-80.47	-76.65	-110.71	-137.95	-157.79	-83.17	-76.26	-110.13	-137.45	-158.45
405.6	-79.09	-75.73	-110.35	-135.67	-155.81	-82.01	-77.62	-110.80	-138.06	-160.01	-78.37	-77.30	-110.23	-137.40	-158.42
407.2	-78.36	-75.86	-110.56	-135.84	-156.10	-79.82	-79.77	-111.11	-138.66	-159.82	-78.02	-77.89	-109.96	-137.87	-158.38
408.8	-77.38	-75.90	-110.83	-135.81	-156.54	-79.38	-78.71	-111.45	-139.19	-159.21	-75.62	-77.73	-110.29	-138.07	-159.24
409.0	-77.27	-76.76	-110.95	-136.09	-149.83	-80.64	-78.25	-110.99	-139.56	-151.86	-78.80	-78.66	-110.37	-138.08	-153.96
410.4	-80.18	-76.69	-110.73	-136.14	-156.30	-81.03	-79.14	-111.03	-139.50	-160.10	-75.50	-77.95	-110.48	-138.12	-159.05
412.0	-74.83	-78.54	-111.18	-136.47	-157.05	-77.94	-78.22	-111.67	-139.91	-159.77	-75.67	-77.72	-109.96	-137.69	-159.42
413.6	-74.59	-78.10	-111.28	-136.72	-157.84	-78.13	-79.60	-111.57	-140.14	-159.97	-74.88	-77.71	-110.21	-137.85	-158.11
415.0	-76.78	-79.62	-111.36	-137.00	-157.00	-76.17	-80.64	-111.79	-140.01	-160.21	-74.29	-77.95	-110.34	-137.85	-159.56
415.2	-76.93	-78.93	-111.23	-136.87	-157.78	-75.80	-79.46	-111.57	-139.94	-162.11	-75.26	-78.11	-110.46	-137.69	-159.02
416.8	-76.90	-77.95	-111.91	-137.41	-158.04	-77.23	-78.63	-111.45	-140.36	-160.99	-77.38	-78.46	-110.48	-137.96	-158.76
418.4	-77.01	-76.14	-111.94	-137.64	-158.19	-76.25	-79.94	-111.70	-140.22	-159.72	-75.88	-77.73	-110.80	-137.94	-159.23
420.0	-78.66	-79.40	-111.99	-138.48	-158.82	-77.27	-78.61	-111.57	-140.40	-160.47	-79.81	-78.93	-111.08	-138.06	-159.85

Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
 B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
 C. The parts covered by this specification document are subject to Mini-Circuits' standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCStore/terms.jsp



Frequency Synthesizer

KSN-EDR8066

Typical Performance Data

COMPARISON SPURIOUS ORDER	COMPARISON SPURIOUS @Fcarrier 409 MHz± (n*Fcomparison) (dBc) NOTE 1			COMPARISON SPURIOUS @Fcarrier 412 MHz± (n*Fcomparison) (dBc) NOTE 1			COMPARISON SPURIOUS @Fcarrier 415 MHz± (n*Fcomparison) (dBc) NOTE 1		
	-45 °C	+25°C	+85 °C	-45 °C	+25°C	+85 °C	-45 °C	+25°C	+85 °C
-5	-107.32	-109.65	-108.85	-109.55	-109.53	-109.33	-108.05	-108.99	-108.60
-4	-106.92	-105.95	-107.02	-106.58	-106.84	-106.88	-107.05	-106.76	-105.59
-3	-103.65	-103.69	-104.11	-103.93	-103.67	-100.93	-103.63	-104.12	-103.54
-2	-99.17	-102.12	-98.31	-97.81	-100.40	-100.60	-101.17	-100.63	-95.82
-1	-92.16	-92.02	-87.36	-92.04	-92.54	-86.16	-92.54	-94.29	-83.83
0 ^{note 2}	-	-	-	-	-	-	-	-	-
+1	-92.86	-94.58	-87.15	-93.25	-92.53	-85.30	-92.95	-93.78	-84.30
+2	-100.89	-97.91	-99.43	-99.82	-100.68	-96.99	-100.94	-100.49	-96.58
+3	-103.65	-102.93	-105.29	-104.59	-104.97	-101.32	-104.65	-103.50	-103.09
+4	-107.18	-106.48	-107.80	-107.32	-107.84	-107.59	-106.68	-107.56	-106.84
+5	-108.42	-109.15	-107.87	-107.75	-109.55	-107.40	-108.68	-109.67	-107.22

Note 1: Comparison frequency 20 kHz

Note 2: All spurs are referenced to carrier signal (n=0).

REFERENCE SPURIOUS ORDER	REFERENCE SPURIOUS @Fcarrier 409 MHz± (n*Freference) (dBc) NOTE 3			REFERENCE SPURIOUS @Fcarrier 412 MHz± (n*Freference) (dBc) NOTE 3			REFERENCE SPURIOUS @Fcarrier 415 MHz± (n*Freference) (dBc) NOTE 3		
	-45 °C	+25°C	+85 °C	-45 °C	+25°C	+85 °C	-45 °C	+25°C	+85 °C
-5	-116.66	-118.74	-120.27	-115.07	-114.41	-116.81	-111.75	-114.71	-115.37
-4	-120.33	-117.75	-115.70	-119.31	-116.99	-114.04	-109.36	-113.80	-113.64
-3	-122.24	-118.86	-119.55	-123.21	-118.69	-120.46	-112.64	-114.86	-116.50
-2	-111.55	-107.66	-108.50	-113.73	-107.23	-108.18	-108.61	-107.93	-108.41
-1	-103.62	-101.85	-103.09	-103.67	-101.73	-103.02	-102.43	-101.69	-102.89
0 ^{note 4}	-	-	-	-	-	-	-	-	-
+1	-104.71	-102.89	-104.19	-104.41	-102.86	-104.16	-101.65	-100.84	-102.33
+2	-113.17	-108.16	-109.22	-114.03	-108.64	-109.92	-108.28	-106.06	-107.29
+3	-125.31	-123.59	-122.78	-124.57	-123.92	-123.49	-112.00	-113.03	-115.69
+4	-118.58	-115.57	-113.98	-116.53	-115.38	-114.25	-110.56	-110.41	-110.40
+5	-126.59	-126.79	-126.25	-126.73	-124.17	-124.66	-114.00	-116.09	-117.47

Note 3: Reference frequency 10 MHz

Note 4: All spurs are referenced to carrier signal (n=0).

Notes




- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
 B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
 C. The parts covered by this specification document are subject to Mini-Circuits' standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



Frequency Synthesizer

KSN-EDR8066

Typical Performance Data



Notes






- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
 B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
 C. The parts covered by this specification document are subject to Mini-Circuits' standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCStore/terms.jsp



Frequency Synthesizer

Typical Performance Data

KSN-EDR8066



Notes







- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
 B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
 C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCStore/terms.jsp



Frequency Synthesizer

Typical Performance Data

KSN-EDR8066




Notes


- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
 B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
 C. The parts covered by this specification document are subject to Mini-Circuits' standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCStore/terms.jsp



Outline Dimensions



Suggested PCB Land Pattern



 METALLIZATION
 SOLDER RESIST

CASE#	A	B	C	D	E	F	G	H	J	K	L	M	N	P	Q	WT. GRAM
DK801	.584 (14.83)	.800 (20.32)	.154 (3.91)	.079 (2.01)	.203 (5.16)	.040 (1.02)	.040 (1.02)	.291 (7.39)	.039 (1.0)	.624 (15.85)	.840 (21.34)	.060 (1.52)	.193 (4.90)	.170 (4.32)	.060 (1.52)	1.6

Dimensions are in inches (mm). Tolerances: 2PL. +/- .03; 3PL. +/- .015


Notes:

- Case material: Nickel-Silver alloy.
- Base: Printed wiring laminate.
- Termination finish:

For RoHS Case Styles: 2-5 μ inch (.05-.13 microns) Gold over 120-240 μ inch (3.05-6.10 microns) Nickel plate.
All models, (+) suffix.

Tape & Reel Packaging TR-F28

DEVICE ORIENTATION IN T&R



Tape Width, mm	Device Cavity Pitch, mm	Reel Size, inches	Devices per Reel	
32	20	13	Small quantity standards (see note)	20
				50
				100
				200
			Standard	500

Note: Please consult individual model data sheet to determine device per reel availability.

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: www.minicircuits.com/pages/pdfs/tape.pdf




INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified


THIRD ANGLE PROJECTION



REVISIONS

REV	ECN No.	DESCRIPTION	DATE	DR	AUTH
OR	M108069	NEW RELEASE	11/06	DK	HH
A	M110535	MODIFY GROUND PADS	03/07	DK	HH
B	M126537	DELETE CHIP COMP. & TABLE OF VALUES	03/10	DK	HH
B	R78979	DELETE CHIP COMP. & TABLE OF VALUES	03/10	DK	HH

SUGGESTED MOUNTING CONFIGURATION

FOR DK801/DK1042 CASE STYLE, rs PIN CONNECTION, 50 Ω . ϕ .020 PTH. TYP.
FOR GROUND

NOTES:

- TRACE WIDTH IS SHOWN FOR FR4 WITH DIELECTRIC THICKNESS. .025"±.002". COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
- BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.

DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)

DENOTES COPPER LAND PATTERN FREE OF SOLDERMASK

UNLESS OTHERWISE SPECIFIED

INITIALS

DATE

DIMENSIONS ARE IN INCHES

TOLERANCES ON:

2 PL DECIMALS ±

3 PL DECIMALS ± .005

ANGLES ±

FRACTIONS ±

DRAWN

DK (RAVON)

27 MAR 07

CHECKED

RZ (RAVON)

27 MAR 07

APPROVED

HH (RAVON)

27 MAR 07

Mini-Circuits®

THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.

ASHEETA1.DWG REV:A DATE:01/12/95



Mini-Circuits®

13 Neptune Avenue
Brooklyn NY 11235PL, rs ,DK801/DK1042, KSN
TB-567+ (50 Ω)SIZE
ACODE IDENT
15542DRAWING NO:
98-PL-249REV:
B


FILE: 98PL249

SCALE: 5:1


SHEET: 1 OF 1

ELECTRICAL SCHEME-GENERAL


(TB for KSN)




DC PROTECTIONS




MAIN REGULATOR




VCC VCO REGULATOR




VCC PLL REGULATOR




SCHMITT TRIGGER REGULATOR




VCC PLL FILTERING




VCC VCO FILTERING




SCHMITT TRIGGER FILTERING




SCHMITT TRIGGER




USB CONTROLER



LD REGULATOR SCHMITT TRIGGER AND LED



Evaluation Board and Circuit



TB-567+

NOTES:

1. SMA F JACK CONNECTORS.
2. PCB MATERIAL: FR4 OR EQUIVALENT, DIALECTRIC CONSTANT=4.7, DIALECTRIC THICKNESS=.059 INCH.



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-45° to 85°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Humidity	90 to 95% RH, 240 hours, 50°C	MIL-STD-202, Method 103, Condition A, Except 50°C and end-point electrical test done within 12 hours
Thermal Shock	-55° to 100°C, 100 cycles	MIL-STD-202, Method 107, Condition A-3, except +100°C
Solder Reflow Heat	Sn-Pb Eutectic Process: 225°C peak Pb-Free Process, 245°C peak	J-STD-020, Table 4-1, 4-2 and 5-2, Figure 5-1
Solderability	10X Magnification	J-STD-002, Para 4.2.5, Test S, 95% Coverage
Vibration (High Frequency)	20g peak, 20-2000 Hz, 4 times in each of three axes (total 12)	MIL-STD-883, Method 2007.3, Condition A
Mechanical Shock	50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes	MIL-STD-202, Method 213, Condition A
Marking Resistance to Solvents	Isopropyl alcohol + mineral spirits at 25°C; terpene defluxer at 25°C; distilled water + proylene glycol monomethyl ether + monoethanolamine at 63°C to 70°C	MIL-STD-202, Method 215