

Engineering Development Model

Frequency Synthesizer

KSN-EDR10453ME

Important Note

This model has been designed, built and tested in our engineering department. Performance data represents model capability. At present it is a non-catalog model. On request, we can supply a final specification sheet, part number and price/delivery information.



Please click "Back", and then click "Contact Us" for Applications support.

CASE STYLE : DK1042

ELECTRICAL SPECIFICATIONS 50Ω, over -20°C to +80°C				
Parameter	Min.	Typ.	Max.	Units
Frequency	1870		1885	MHz
Step size		200		kHz
Settling Time Within ±50Hz		1		msec
Output Power	0	+4	+8	dBm
Phase Noise				
at 100 Hz offset		-86		dBc/Hz
at 1 kHz offset		-85		dBc/Hz
at 10 KHz offset		-91	-85	dBc/Hz
at 100 KHz offset		-121	-115	dBc/Hz
at 1000 kHz offset		-143	-137	dBc/Hz
Integrated SSB Phase Noise		-43		dBc
Reference Spurious Suppression		-97		dBc
Comparison Spurious Suppression		-116		dBc
Non-Harm. Spurious Suppression		-90		dBc
Harmonic Suppression		-49		dBc
Supply voltage VCO		5		V
Supply voltage PLL		3.3		V
Supply current VCO		27	35	V
Supply current PLL		10	19	V
Reference In (External)				
Frequency		26		MHz
Amplitude		1		Vp-p
Impedance		100		kΩ
Ph. N @ 1kHz		-145		dBc/Hz
Input Logic Levels	Logic high	1.4	3.3	V
Logic Low			0.6	
Digital Lock Detect	Locked	2.9	3.3	V
Unlocked			0.4	
Frequency Synthesizer PLL	ADF4106			

ABSOLUTE MAXIMUM RATINGS	
Operating Temperature	-45°C to 85°C
Storage Temperature	-55°C to 100°C
VCO Supply Voltage	6V
PLL Supply Voltage	4.3V
Reference Frequency voltage	3.6Vp-p
Data, Clock & LE levels	3.6V

Power On sequence: Vcc VCO followed by Vcc PLL
Power Off sequence: Vcc PLL followed by Vcc VCO

PIN CONNECTIONS			
RF OUT	7	CLOCK	10
VCC VCO	5	DATA	11
VCC PLL	1	LATCH ENABLE	12
REF IN	3	GROUND	2,4,6,8,13,14
LOCK DETECT	9		

Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuits' standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCStore/terms.jsp



www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

REV. OR
KSN-EDR10453ME
150122

Frequency Synthesizer

KSN-EDR10453ME

Typical Performance Data

FREQ. (MHz)	POWER OUTPUT (dBm)			HARMONICS (dBc)						VCO CURRENT (mA)			PLL CURRENT (mA)		
				F2			F3								
	-20 °C	+25°C	+80 °C	-20 °C	+25°C	+80 °C	-20 °C	+25°C	+80 °C	-20 °C	+25°C	+80 °C	-20 °C	+25°C	+80 °C
1865	4.08	3.94	3.87	-55.28	-49.74	-62.83	-53.75	-45.80	-58.29	26.07	26.63	27.25	9.01	10.20	11.92
1867	4.08	3.93	3.87	-55.13	-49.83	-62.23	-54.88	-45.49	-57.44	26.07	26.64	27.25	9.01	10.25	11.97
1868	4.08	3.93	3.87	-54.98	-49.57	-61.51	-53.30	-45.27	-57.39	26.08	26.64	27.26	9.01	10.26	12.01
1870	4.07	3.93	3.87	-54.85	-49.78	-61.65	-53.14	-45.30	-56.37	26.09	26.65	27.26	9.00	10.25	12.01
1870	4.07	3.93	3.87	-54.98	-49.99	-61.45	-53.40	-45.05	-61.31	26.09	26.65	27.26	9.01	10.26	12.02
1871	4.09	3.94	3.87	-55.21	-49.80	-60.53	-53.26	-45.06	-60.94	26.10	26.66	27.25	9.01	10.26	12.03
1873	4.09	3.93	3.87	-54.90	-49.72	-60.39	-53.24	-45.12	-60.65	26.11	26.67	27.26	9.02	10.27	12.04
1875	4.05	3.93	3.87	-55.32	-49.83	-60.42	-52.28	-45.04	-61.28	26.12	26.68	27.27	9.02	10.28	12.05
1876	4.10	3.93	3.88	-54.99	-49.59	-60.55	-52.15	-44.95	-61.65	26.13	26.68	27.27	9.01	10.27	12.04
1878	4.11	3.94	3.89	-56.23	-49.82	-60.26	-52.04	-44.75	-60.97	26.13	26.69	27.28	9.01	10.27	12.05
1879	4.11	3.94	3.89	-56.57	-49.66	-60.25	-51.93	-44.63	-61.47	26.15	26.70	27.29	9.01	10.28	12.06
1881	4.12	3.94	3.89	-56.82	-49.71	-59.26	-52.10	-44.75	-61.01	26.15	26.71	27.29	9.02	10.28	12.07
1883	4.13	3.94	3.90	-56.38	-49.74	-59.38	-52.84	-44.72	-61.26	26.16	26.72	27.29	9.01	10.27	12.05
1884	4.14	3.95	3.91	-56.05	-49.73	-59.33	-53.63	-44.47	-61.65	26.17	26.72	27.30	9.01	10.27	12.06
1885	4.15	3.96	3.91	-55.39	-49.71	-59.66	-53.59	-44.49	-61.08	26.18	26.73	27.30	9.02	10.28	12.07
1886	4.15	3.96	3.91	-55.77	-49.56	-59.60	-52.31	-44.42	-60.90	26.18	26.74	27.31	9.02	10.28	12.07
1887	4.16	3.97	3.92	-55.91	-49.65	-59.70	-53.19	-43.90	-61.35	26.20	26.74	27.32	9.02	10.29	12.08
1890	4.17	3.98	3.93	-55.60	-49.75	-59.83	-53.15	-43.93	-61.21	26.21	26.76	27.33	9.01	10.28	12.07

FREQ. (MHz)	PHASE NOISE (dBc/Hz)														
	@ OFFSETS														
	-20 °C					+25°C					+80 °C				
	100Hz	1kHz	10kHz	100kHz	1MHz	100Hz	1kHz	10kHz	100kHz	1MHz	100Hz	1kHz	10kHz	100kHz	1MHz
1865	-85.82	-86.73	-90.21	-121.58	-145.75	-87.48	-86.83	-91.01	-120.92	-143.21	-87.66	-85.39	-90.37	-119.33	-140.63
1867	-84.41	-85.13	-91.06	-121.53	-144.86	-85.30	-84.69	-90.84	-120.75	-143.39	-84.42	-86.13	-90.99	-119.37	-140.07
1868	-84.78	-86.52	-90.57	-121.56	-145.06	-84.68	-83.39	-90.65	-120.72	-143.42	-83.02	-85.56	-91.38	-119.36	-140.07
1870	-83.52	-84.14	-90.47	-121.54	-145.40	-85.90	-84.74	-90.39	-120.71	-143.47	-86.38	-84.45	-92.03	-119.32	-140.76
1870	-84.91	-84.67	-90.18	-121.55	-145.50	-86.24	-84.63	-90.94	-120.73	-143.55	-84.76	-83.15	-91.08	-119.21	-140.71
1871	-83.35	-84.65	-90.69	-121.59	-144.92	-85.12	-85.59	-90.55	-120.84	-143.40	-85.66	-85.21	-91.35	-119.33	-140.50
1873	-84.71	-84.97	-90.81	-121.65	-145.41	-87.70	-83.04	-90.88	-120.71	-143.58	-85.19	-85.67	-91.11	-119.29	-141.17
1875	-85.15	-84.03	-90.50	-121.61	-144.97	-85.88	-84.47	-90.85	-120.71	-142.91	-83.40	-85.96	-90.94	-119.42	-140.57
1876	-84.73	-84.45	-91.01	-121.61	-145.39	-84.90	-84.52	-90.95	-120.68	-143.44	-85.41	-86.33	-91.09	-119.35	-141.11
1878	-84.74	-85.06	-90.68	-121.50	-145.34	-86.40	-85.23	-91.19	-120.57	-143.03	-83.48	-86.31	-91.42	-119.34	-140.93
1879	-87.41	-85.77	-90.67	-121.49	-145.33	-84.74	-86.26	-91.03	-120.69	-142.87	-85.63	-86.93	-91.60	-119.23	-140.79
1881	-84.87	-85.61	-90.14	-121.48	-145.11	-86.47	-86.59	-90.90	-120.78	-142.10	-86.42	-83.33	-91.52	-119.15	-141.00
1883	-85.13	-87.02	-90.77	-121.46	-145.57	-84.81	-87.38	-90.72	-120.94	-143.61	-85.44	-84.72	-91.61	-119.36	-140.70
1884	-85.48	-84.57	-90.65	-121.65	-145.53	-84.69	-86.58	-90.61	-120.68	-143.23	-84.12	-84.58	-91.57	-119.43	-140.46
1885	-84.89	-83.73	-90.79	-121.45	-145.36	-90.39	-83.19	-91.45	-120.91	-143.02	-88.12	-83.31	-92.25	-119.32	-140.48
1886	-84.11	-86.22	-90.95	-121.51	-145.31	-86.65	-84.06	-91.19	-120.88	-142.77	-84.09	-85.05	-91.88	-119.38	-140.38
1887	-84.32	-83.32	-90.53	-121.68	-145.43	-85.43	-83.98	-91.01	-120.76	-142.42	-84.73	-84.59	-92.44	-119.44	-140.45
1890	-85.38	-83.27	-90.72	-121.71	-145.14	-85.37	-86.02	-91.22	-121.01	-143.38	-87.12	-86.00	-91.95	-119.41	-139.74

Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"). Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCStore/terms.jsp



Frequency Synthesizer

KSN-EDR10453ME

Typical Performance Data

COMPARISON SPURIOUS ORDER	COMPARISON SPURIOUS @F _{carrier} 1870 MHz± (n*F _{comparison}) (dBc) NOTE 1			COMPARISON SPURIOUS @F _{carrier} 1878 MHz± (n*F _{comparison}) (dBc) NOTE 1			COMPARISON SPURIOUS @F _{carrier} 1885 MHz± (n*F _{comparison}) (dBc) NOTE 1		
	-20 °C	+25°C	+80 °C	-20 °C	+25°C	+80 °C	-20 °C	+25°C	+80 °C
-5	-106.86	-114.17	-104.46	-110.33	-116.64	-98.51	-113.54	-107.96	-99.18
-4	-106.55	-110.68	-101.38	-108.74	-109.29	-95.66	-105.99	-107.49	-93.48
-3	-101.63	-108.26	-98.76	-106.70	-101.61	-92.10	-106.33	-101.13	-92.11
-2	-99.16	-99.99	-92.39	-99.16	-99.49	-88.02	-98.67	-98.40	-87.98
-1	-83.96	-87.48	-79.94	-86.20	-85.82	-77.22	-87.26	-86.40	-76.39
0 ^{note 2}	-	-	-	-	-	-	-	-	-
+1	-85.64	-87.79	-83.50	-88.78	-89.66	-77.66	-89.92	-89.68	-77.29
+2	-98.96	-101.46	-93.15	-103.42	-102.89	-87.66	-102.03	-97.08	-86.39
+3	-104.40	-108.93	-95.67	-107.11	-102.19	-92.58	-110.72	-102.87	-92.20
+4	-106.98	-110.67	-100.71	-104.18	-109.50	-96.02	-104.00	-107.25	-92.94
+5	-109.39	-115.29	-102.57	-110.21	-114.07	-97.83	-114.78	-108.08	-97.97

Note 1: Comparison frequency 200 kHz

Note 2: All spurs are referenced to carrier signal (n=0).

REFERENCE SPURIOUS ORDER	REFERENCE SPURIOUS @F _{carrier} 1870 MHz± (n*F _{reference}) (dBc) NOTE 3			REFERENCE SPURIOUS @F _{carrier} 1878 MHz± (n*F _{reference}) (dBc) NOTE 3			REFERENCE SPURIOUS @F _{carrier} 1885 MHz± (n*F _{reference}) (dBc) NOTE 3		
	-20 °C	+25°C	+80 °C	-20 °C	+25°C	+80 °C	-20 °C	+25°C	+80 °C
-5	-120.31	-119.72	-122.04	-119.36	-121.21	-118.62	-121.77	-120.93	-117.95
-4	-125.74	-126.55	-117.06	-126.12	-125.14	-118.04	-123.57	-121.07	-118.30
-3	-112.86	-121.34	-125.44	-113.94	-121.06	-119.38	-118.39	-126.74	-124.07
-2	-114.66	-120.17	-122.40	-114.57	-119.49	-123.02	-115.84	-120.11	-126.63
-1	-101.77	-95.07	-106.43	-100.43	-94.58	-107.82	-100.58	-94.96	-108.30
0 ^{note 4}	-	-	-	-	-	-	-	-	-
+1	-99.36	-101.06	-114.48	-99.94	-102.70	-107.69	-105.07	-104.65	-108.60
+2	-116.97	-119.15	-118.14	-116.35	-117.32	-115.86	-114.99	-114.35	-119.00
+3	-117.10	-117.76	-123.09	-119.56	-118.30	-122.44	-121.99	-125.14	-123.02
+4	-115.81	-114.03	-117.33	-116.34	-113.50	-117.74	-114.10	-112.33	-117.75
+5	-117.44	-116.54	-121.30	-118.01	-115.01	-121.85	-120.21	-118.48	-123.49

Note 3: Reference frequency 26 MHz

Note 4: All spurs are referenced to carrier signal (n=0).

Notes




- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
 B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
 C. The parts covered by this specification document are subject to Mini-Circuit's standard limited warranty and terms and conditions (collectively, "Standard Terms"). Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuit's website at www.minicircuits.com/MCStore/terms.jsp



Frequency Synthesizer

Typical Performance Data

KSN-EDR10453ME



Notes






- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"). Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCStore/terms.jsp



Frequency Synthesizer

Typical Performance Data

KSN-EDR10453ME



Notes







- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
 B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
 C. The parts covered by this specification document are subject to Mini-Circuit's standard limited warranty and terms and conditions (collectively, "Standard Terms"). Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuit's website at www.minicircuits.com/MCStore/terms.jsp



Frequency Synthesizer

Typical Performance Data

KSN-EDR10453ME




Notes



- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
 B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
 C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"). Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCStore/terms.jsp



Outline Dimensions



Suggested PCB Land Pattern



CASE#	A	B	C	D	E	F	G	H	J	K	L	M	N	P	Q	WT. GRAM
DK1042	.584 (14.83)	.800 (20.32)	.154 (3.91)	.079 (2.01)	.203 (5.16)	.060 (1.52)	.045 (1.14)	.291 (7.39)	.039 (1.0)	.624 (15.85)	.840 (21.34)	.065 (1.65)	.193 (4.90)	.170 (4.32)	.060 (1.52)	1.6


Dimensions are in inches (mm). Tolerances: 2PL. +/- .03; 3PL. +/- .015

Notes:

- Case material: Nickel-Silver alloy.
- Base: Printed wiring laminate.
- Termination finish:
For RoHS Case Styles: 2-5 μ inch (.05-.13 microns) Gold over 120-240 μ inch (3.05-6.10 microns) Nickel plate.
All models, (+) suffix.

Tape & Reel Packaging TR-F28

DEVICE ORIENTATION IN T&R



Tape Width, mm	Device Cavity Pitch, mm	Reel Size, inches	Devices per Reel	
32	20	13	Small	20
			quantity	50
			standards	100
			(see note)	200
			Standard	500

Note: Please consult individual model data sheet to determine device per reel availability.

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: www.minicircuits.com/pages/pdfs/tape.pdf




INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified


THIRD ANGLE PROJECTION



REVISIONS

REV	ECN No.	DESCRIPTION	DATE	DR	AUTH
OR	M108069	NEW RELEASE	11/06	DK	HH
A	M110535	MODIFY GROUND PADS	03/07	DK	HH
B	M126537	DELETE CHIP COMP. & TABLE OF VALUES	03/10	DK	HH
B	R78979	DELETE CHIP COMP. & TABLE OF VALUES	03/10	DK	HH

SUGGESTED MOUNTING CONFIGURATION

FOR DK801/DK1042 CASE STYLE, rs PIN CONNECTION, 50 Ω . ϕ .020 PTH. TYP.
FOR GROUND

NOTES:

- TRACE WIDTH IS SHOWN FOR FR4 WITH DIELECTRIC THICKNESS. .025"±.002". COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
- BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.

 DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)

 DENOTES COPPER LAND PATTERN FREE OF SOLDERMASK

UNLESS OTHERWISE SPECIFIED

INITIALS

DATE

DIMENSIONS ARE IN INCHES

TOLERANCES ON:

2 PL DECIMALS ±

3 PL DECIMALS ± .005

ANGLES ±

FRACTIONS ±

DRAWN

DK (RAVON)

27 MAR 07

CHECKED

RZ (RAVON)

27 MAR 07

APPROVED

HH (RAVON)

27 MAR 07

 Mini-Circuits®

THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.

ASHEETA1.DWG REV:A DATE:01/12/95



Mini-Circuits®

13 Neptune Avenue
Brooklyn NY 11235PL, rs ,DK801/DK1042, KSN
TB-567+ (50 Ω)SIZE
ACODE IDENT
15542DRAWING NO:
98-PL-249REV:
B


FILE: 98PL249

SCALE: 5:1


SHEET: 1 OF 1

ELECTRICAL SCHEME-GENERAL


(TB for KSN)




DC PROTECTIONS




MAIN REGULATOR




VCC VCO REGULATOR




VCC PLL REGULATOR




SCHMITT TRIGGER REGULATOR




VCC VCO FILTERING




VCC PLL FILTERING




SCHMITT TRIGGER FILTERING




SCHMITT TRIGGER




USB CONTROLER




LD REGULATOR SCHMITT TRIGGER AND LED



Evaluation Board and Circuit



TB-567-1+



NOTES:

1. SMA F JACK CONNECTORS.
2. PCB MATERIAL: FR4 OR EQUIVALENT, DIALECTRIC CONSTANT=4.7, DIALECTRIC THICKNESS=.059 INCH.



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-45° to 85°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Humidity	90 to 95% RH, 240 hours, 50°C	MIL-STD-202, Method 103, Condition A, Except 50°C and end-point electrical test done within 12 hours
Thermal Shock	-55° to 100°C, 100 cycles	MIL-STD-202, Method 107, Condition A-3, except +100°C
Solder Reflow Heat	Sn-Pb Eutectic Process: 225°C peak Pb-Free Process, 245°C peak	J-STD-020, Table 4-1, 4-2 and 5-2, Figure 5-1
Solderability	10X Magnification	J-STD-002, Para 4.2.5, Test S, 95% Coverage
Vibration (High Frequency)	20g peak, 20-2000 Hz, 4 times in each of three axes (total 12)	MIL-STD-883, Method 2007.3, Condition A
Mechanical Shock	50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes	MIL-STD-202, Method 213, Condition A
Marking Resistance to Solvents	Isopropyl alcohol + mineral spirits at 25°C; terpene defluxer at 25°C; distilled water + proylene glycol monomethyl ether + monoethanolamine at 63°C to 70°C	MIL-STD-202, Method 215