



Mini-Circuits

ULTRA HIGH DYNAMIC RANGE

Monolithic Amplifier

LHA-1H+

50Ω 0.05 to 6 GHz

THE BIG DEAL

- High IP3, +41 dBm typ. at 2 GHz, +5V
- Gain, 13.9 dB typ. at 2 GHz, +5V
- High Pout, P1dB +22.5 dBm typ. at 2 GHz, +5V
- Low noise figure, 2.1 dB @ 2 GHz, +5V
- Usable to +4.0V



Generic photo used for illustration purposes only

CASE STYLE: FG873

+RoHS Compliant

The +Suffix identifies RoHS Compliance.

See our website for methodologies and qualifications

APPLICATIONS

- Base station infrastructure
- Portable Wireless
- CATV & DBS
- MMDS & Wireless LAN
- LTE

PRODUCT OVERVIEW

LHA-1H+ (RoHS compliant) is an advanced wideband amplifier fabricated using E-PHEMT technology and offers extremely high dynamic range over a broad frequency range and with low noise figure. In addition, the LHA-1H+, unlike competitive models, is well matched (input and output) over a broad frequency range without the need for external matching components. It is enclosed in a 3x3 mm MCLP package for low parasitic interface.

KEY FEATURES

Feature	Advantages
Broad Band: 0.05 to 6.0 GHz	Broadband covering primary wireless communications bands: Cellular, PCS, LTE, WiMAX
Extremely High IP3 versus DC power Consumption +41 dBm typical at 2 GHz	The LHA-1H+ matches industry leading IP3 performance relative to device size and power consumption. The combination of the design and E-PHEMT Structure provides enhanced linearity over a broad frequency range as evidence in the IP3 being typically 17 dB above the P 1dB point. This feature makes this amplifier ideal for use in: <ul style="list-style-type: none"> • Driver amplifiers for complex waveform up converter paths • Drivers in linearized transmit systems • Secondary amplifiers in ultra High Dynamic range receivers
No External Matching Components Required	LHA-1H+ provides Input and Output Return Loss of 10-22 dB up to 4 GHz without the need for any external matching components
Low Noise Figure: 2.7 dB typ. up to 4 GHz 3.3 dB typ. up to 6 GHz	A unique feature of the LHA-1H+ which separates this design from all competitors is the low noise figure performance in combination with the high dynamic range.
Low Junction Temperature: T _j =115°C at +85°C lead temperature and +135°C at +105°C lead temperature	Results in excellent reliability up to +105°C

REV. A
ECO-011665
LHA-1H+
MCL NY
240725



Mini-Circuits

ULTRA HIGH DYNAMIC RANGE

Monolithic Amplifier

LHA-1H+

50Ω 0.05 to 6 GHz

ELECTRICAL SPECIFICATIONS¹ AT +25°C, UNLESS NOTED OTHERWISE

Parameter	Condition (GHz)	Vd=+5.0V			Vd=+4.5V	Vd=+4.0V	Units
		Min.	Typ.	Max.	Typ.	Typ.	
Frequency Range		0.05-6			0.05-6	0.05-6	GHz
Gain	0.05	16.0	17.7	19.6	17.6	17.3	dB
	0.8	14.4	15.9	17.6	15.7	15.5	
	2.0	—	13.9	—	13.8	13.5	
	3.0	—	12.2	—	12.0	11.7	
	4.0	9.8	10.8	12.0	10.5	10.3	
	6.0	—	8.7	—	8.5	8.2	
Input Return Loss	0.05	—	11.5	—	11.2	10.9	dB
	0.8	13.0	16.2	—	16.0	15.4	
	2.0	—	11.4	—	11.2	10.9	
	3.0	—	10.1	—	10.0	9.7	
	4.0	—	9.7	—	9.8	9.6	
	6.0	—	8.7	—	8.8	8.6	
Output Return Loss	0.05	—	14.6	—	14.5	14.3	dB
	0.8	13.0	22.3	—	22.4	22.0	
	2.0	—	20.1	—	19.4	17.8	
	3.0	—	18.1	—	17.6	16.3	
	4.0	—	16.4	—	16.3	15.5	
	6.0	—	15.4	—	15.0	14.2	
Reverse Isolation	2.0	—	19.2	—	19.1	18.9	dB
Output Power @1 dB compression	0.05	+20.0	+22.7	—	+21.4	+19.9	dBm
	0.8	+20.0	+22.6	—	+21.4	+19.9	
	2.0	+20.0	+22.5	—	+21.3	+19.8	
	3.0	—	+22.7	—	+21.5	+19.9	
	4.0	—	+22.9	—	+21.7	+20.0	
	6.0	—	+22.2	—	+21.1	+19.7	
Output IP3	0.05	—	+40.3	—	+38.5	+35.6	dBm
	0.8	+38.0	+41.2	—	+39.6	+35.4	
	2.0	—	+41.4	—	+36.3	+32.9	
	3.0	—	+40.9	—	+35.8	+32.3	
	4.0	—	+41.0	—	+35.8	+32.4	
	6.0	—	+38.6	—	+34.5	+31.4	
Noise Figure	0.05	—	1.6	—	1.5	1.5	dB
	0.8	—	1.9	—	1.8	1.8	
	2.0	—	2.1	—	2.0	2.0	
	3.0	—	2.5	—	2.3	2.2	
	4.0	—	2.7	—	2.4	2.3	
	6.0	—	3.3	—	3.1	2.8	
Device Operating Voltage		+4.8	+5.0	+5.2	+4.5	+4.0	V
Device Operating Current			145	165	116	88	mA
Device Current Variation vs. Temperature ²			109		141	154	µA/°C
Device Current Variation vs Voltage			0.058		0.057	0.055	mA/mV
Thermal Resistance, junction-to-ground lead			36		36	36	°C/W

1. Measured on Mini-Circuits Characterization test board TB-784+. See Characterization Test Circuit (Fig. 1)

2. (Current at 85°C — Current at -45°C)/130

ABSOLUTE MAXIMUM RATINGS³

Parameter	Ratings
Operating Temperature (ground lead)	-40°C to +105°C
Storage Temperature	-65°C to +150°C
Operating Current at 5V	210 mA
Power Dissipation	1 W
Input Power (CW)	+24 dBm
DC Voltage on Pad 3	+6 V

3. Permanent damage may occur if any of these limits are exceeded.

Electrical maximum ratings are not intended for continuous normal operation.

Mini-Circuits®

www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

PAGE 2 OF 5



ULTRA HIGH DYNAMIC RANGE


Monolithic Amplifier

LHA-1H+

Mini-Circuits®


50Ω 0.05 to 6 GHz

SIMPLIFIED SCHEMATIC AND PAD DESCRIPTION




Function	Pad Number	Description
RF-IN	1	RF input pin. This pin requires the use of an external DC blocking capacitor chosen for the frequency of operation.
RF-OUT and DC-IN	3	RF output and bias pin. DC voltage is present on this pin; therefore a DC blocking capacitor is necessary for proper operation. An RF choke is needed to feed DC bias without loss of RF signal due to the bias connection, as shown in "Recommended Application Circuit", Fig. 2
GND	2,4	Connections to ground. Use via holes as shown in "Suggested Layout for PCB Design" to reduce ground path inductance for best performance.


Histogram of OIP3 at 900MHz



Histogram of OIP3 at 2400MHz



Histogram of OIP3 at 3500MHz



Mini-Circuits®

www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

PAGE 3 OF 5



ULTRA HIGH DYNAMIC RANGE

Monolithic Amplifier

LHA-1H+

Mini-Circuits®

50Ω 0.05 to 6 GHz

CHARACTERIZATION TEST CIRCUIT




Fig 1. Block Diagram of Test Circuit used for characterization. (DUT soldered on Mini-Circuits Characterization test board TB-819-1H+) Gain, Return loss, Output power at 1dB compression ($P_{1\text{ dB}}$), output IP3 (OIP3) and noise figure measured using Agilent's N5242A PNA-X microwave network analyzer.

Conditions:

1. Gain and Return loss: $P_{\text{IN}} = -25\text{dBm}$
2. Output IP3 (OIP3): Two tones, spaced 1 MHz apart, 5 dBm/tone at output.

RECOMMENDED APPLICATION CIRCUIT





Fig 2. Test Board includes case, connectors, and components soldered to PCB.

PRODUCT MARKING



Marking may contain other features or characters for internal lot control

Mini-Circuits®

www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

PAGE 4 OF 5



Mini-Circuits

ULTRA HIGH DYNAMIC RANGE

Monolithic Amplifier

LHA-1H+

50Ω 0.05 to 6 GHz

ADDITIONAL DETAILED TECHNICAL INFORMATION IS AVAILABLE ON OUR DASHBOARD. [CLICK HERE](#)

Performance Data	Data Table Swept Graphs S-Parameter (S2P Files) Data Set (.zip file)
Case Style	FG873 (3x3 mm MCLP) Plastic package, exposed paddle lead finish: matte-tin
Tape & Reel Standard quantities available on reel	F68 7" reels with 20, 50, 100, 200, 500, 1K, 2K or 3K devices 13" Reels with 2K, 3K, 4K devices
Suggested Layout for PCB Design	PL-443
Evaluation Board	TB-819-1H+
Environmental Ratings	ENV08T1

ESD RATING

Human Body Model (HBM): Class 1B (500 to <1000V) in accordance with ANSI/ESD STM 5.1 - 2001

Machine Model (MM): Class M1 (>25V) in accordance with ANSI/ESD STM5.2-1999

MSL RATING

Moisture Sensitivity: MSL1 in accordance with IPC/JEDEC J-STD-020D

NOTES

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the standard terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/terms/viewterm.html

www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

PAGE 5 OF 5

Monolithic Amplifier

LHA-1H+

Typical Performance Data

NOTE: Use PDF Bookmarks to view DATA at required conditions

Definitions:

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 5.00V, Id = 144.67mA @ Temperature = +25°C

FREQ (MHz)	Gain (dB)	Isolation (dB)	Input Return Loss (dB)	Output Return Loss (dB)	Stability		IP-3 Output (dBm)	1dB Comp. Output (dBm)	Noise Figure (dB)
20	19.71	23.78	7.20	9.89	0.88	0.69	40.34	21.55	1.62
100	16.98	20.84	16.41	18.41	1.06	0.62	40.67	22.45	1.68
200	16.63	20.67	19.76	21.39	1.09	0.62	41.01	22.54	1.70
300	16.51	20.63	20.34	22.28	1.10	0.62	40.82	22.62	1.73
400	16.42	20.60	19.94	22.61	1.10	0.63	40.03	22.50	1.67
500	16.33	20.57	19.31	22.81	1.10	0.64	41.12	22.71	1.77
600	16.23	20.53	18.54	22.81	1.10	0.65	40.65	22.63	1.77
700	16.12	20.49	17.78	22.95	1.10	0.65	40.50	22.65	1.75
800	16.00	20.44	17.02	22.96	1.11	0.66	40.74	22.72	1.81
900	15.88	20.38	16.34	22.99	1.11	0.67	39.92	22.52	1.81
1000	15.74	20.32	15.69	22.98	1.11	0.68	41.21	22.77	1.86
1200	15.45	20.18	14.60	22.84	1.11	0.71	40.52	22.62	1.89
1400	15.14	20.01	13.69	22.68	1.11	0.73	40.37	22.58	1.95
1600	14.81	19.83	12.94	22.46	1.11	0.75	40.82	22.68	2.06
1800	14.46	19.64	12.35	22.17	1.11	0.77	42.24	22.77	2.03
2000	14.12	19.43	11.86	21.82	1.11	0.79	42.12	22.72	2.06
2200	13.77	19.20	11.48	21.40	1.11	0.80	40.57	22.40	2.06
2400	13.44	18.96	11.15	20.94	1.11	0.82	41.88	22.64	2.12
2600	13.11	18.72	10.87	20.39	1.10	0.83	44.47	23.14	2.16
2800	12.77	18.47	10.66	19.96	1.10	0.84	44.99	23.07	2.29
3000	12.46	18.21	10.48	19.46	1.10	0.85	42.82	23.20	2.17
3200	12.15	17.94	10.37	19.01	1.09	0.85	42.72	22.90	2.24
3400	11.86	17.67	10.28	18.56	1.09	0.85	43.89	23.12	2.23
3600	11.59	17.39	10.23	18.07	1.09	0.86	43.98	23.24	2.25
3800	11.32	17.10	10.26	17.64	1.08	0.85	43.78	23.42	2.40
4000	11.08	16.81	10.31	17.23	1.08	0.85	43.00	23.16	2.32
4200	10.85	16.51	10.38	16.82	1.07	0.84	43.02	23.09	2.42
4400	10.64	16.19	10.50	16.43	1.07	0.83	43.03	23.09	2.43
4600	10.44	15.90	10.66	16.24	1.06	0.82	44.15	23.18	2.51
4800	10.26	15.57	10.80	16.08	1.05	0.81	42.76	22.99	2.53
5000	10.08	15.27	10.98	16.10	1.05	0.80	43.28	23.54	2.57
5200	9.92	14.95	11.07	16.06	1.04	0.79	42.45	22.99	2.54
5400	9.76	14.64	11.09	16.14	1.03	0.78	41.31	22.35	2.73
5600	9.59	14.35	11.00	16.31	1.02	0.77	42.93	22.76	2.76
5800	9.41	14.08	10.85	16.42	1.02	0.77	43.70	23.07	2.78
6000	9.26	13.80	10.49	16.16	1.01	0.76	42.18	22.90	2.83
6200	9.07	13.54	10.05	15.83	0.99	0.76	41.05	22.50	2.90
6400	8.87	13.32	9.54	15.29	0.99	0.76	41.75	22.35	3.03
6600	8.68	13.10	8.97	14.57	0.97	0.76	43.50	22.65	3.16
6800	8.46	12.91	8.30	13.69	0.96	0.76	41.66	22.52	3.22
7000	8.22	12.74	7.64	12.79	0.95	0.77	41.05	22.28	3.43



ISO 9001 ISO 14001 AS 9100 CERTIFIED

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com



IF/RF MICROWAVE COMPONENTS

REV. OR

LHA-1H+

7/25/2016

Page 1 of 20

Monolithic Amplifier

LHA-1H+

Typical Performance Data

Definitions:

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 4.75V, Id = 130.12mA @ Temperature = +25°C

FREQ (MHz)	Gain (dB)	Isolation (dB)	Input Return Loss (dB)	Output Return Loss (dB)	Stability		IP-3 Output (dBm)	1dB Comp. Output (dBm)	Noise Figure (dB)
					K	Measure			
20	19.65	23.76	7.20	9.87	0.88	0.70	39.34	21.02	1.57
100	16.92	20.81	16.32	18.42	1.05	0.62	41.11	21.86	1.65
200	16.57	20.64	19.58	21.44	1.09	0.62	42.14	21.94	1.69
300	16.45	20.60	20.15	22.34	1.10	0.63	42.01	22.02	1.67
400	16.36	20.57	19.76	22.65	1.10	0.63	40.82	21.91	1.62
500	16.27	20.53	19.15	22.80	1.10	0.64	42.20	22.12	1.73
600	16.17	20.49	18.38	22.75	1.10	0.65	41.51	22.05	1.72
700	16.06	20.44	17.63	22.83	1.10	0.66	41.11	22.07	1.73
800	15.94	20.39	16.88	22.78	1.11	0.67	41.42	22.14	1.76
900	15.81	20.34	16.21	22.74	1.11	0.68	40.19	21.95	1.75
1000	15.68	20.27	15.57	22.66	1.11	0.69	41.00	22.19	1.86
1200	15.38	20.13	14.50	22.40	1.11	0.71	40.07	22.05	1.84
1400	15.07	19.96	13.59	22.15	1.11	0.73	39.92	22.01	1.93
1600	14.73	19.77	12.84	21.85	1.11	0.75	39.99	22.10	1.99
1800	14.39	19.58	12.27	21.53	1.11	0.77	40.60	22.19	1.99
2000	14.04	19.36	11.78	21.17	1.10	0.79	39.93	22.14	2.05
2200	13.70	19.13	11.41	20.77	1.10	0.80	38.65	21.84	2.02
2400	13.36	18.90	11.08	20.36	1.10	0.82	39.77	22.08	2.07
2600	13.02	18.65	10.81	19.86	1.10	0.83	41.13	22.53	2.13
2800	12.69	18.40	10.60	19.50	1.10	0.84	41.25	22.47	2.26
3000	12.38	18.14	10.43	19.07	1.09	0.85	40.03	22.59	2.15
3200	12.07	17.87	10.32	18.68	1.09	0.85	39.87	22.33	2.30
3400	11.78	17.60	10.23	18.30	1.09	0.86	40.43	22.53	2.16
3600	11.51	17.31	10.19	17.87	1.09	0.86	40.54	22.65	2.26
3800	11.24	17.03	10.23	17.50	1.08	0.85	40.51	22.83	2.35
4000	11.00	16.74	10.28	17.14	1.08	0.85	39.78	22.59	2.36
4200	10.77	16.44	10.34	16.77	1.07	0.84	39.70	22.54	2.39
4400	10.56	16.12	10.49	16.42	1.06	0.83	39.50	22.53	2.36
4600	10.36	15.83	10.65	16.25	1.06	0.82	40.30	22.62	2.48
4800	10.18	15.50	10.78	16.10	1.05	0.81	39.53	22.44	2.49
5000	10.00	15.20	10.98	16.12	1.05	0.80	40.42	22.95	2.51
5200	9.84	14.88	11.06	16.08	1.04	0.79	39.22	22.44	2.47
5400	9.68	14.57	11.09	16.13	1.03	0.78	38.21	21.84	2.61
5600	9.51	14.29	11.00	16.27	1.02	0.77	39.58	22.22	2.71
5800	9.33	14.02	10.84	16.32	1.02	0.76	40.19	22.53	2.72
6000	9.18	13.74	10.50	16.03	1.01	0.76	39.19	22.36	2.81
6200	8.99	13.48	10.04	15.63	1.00	0.76	38.23	21.98	2.84
6400	8.79	13.26	9.55	15.04	0.99	0.76	38.44	21.86	2.90
6600	8.59	13.05	8.97	14.29	0.98	0.76	39.69	22.13	3.07
6800	8.37	12.87	8.30	13.41	0.97	0.76	38.74	22.00	3.19
7000	8.12	12.71	7.64	12.52	0.95	0.76	38.08	21.77	3.30



ISO 9001 ISO 14001 AS 9100 CERTIFIED

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com



IF/RF MICROWAVE COMPONENTS

REV. OR

LHA-1H+

7/25/2016

Page 2 of 20

Monolithic Amplifier

LHA-1H+

Typical Performance Data

Definitions:

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 5.25V, Id = 159.70mA @ Temperature = +25°C

FREQ (MHz)	Gain (dB)	Isolation (dB)	Input Return Loss (dB)	Output Return Loss (dB)	Stability		IP-3 Output (dBm)	1dB Comp. Output (dBm)	Noise Figure (dB)
					K	Measure			
20	19.73	23.79	7.36	9.95	0.89	0.69	40.41	22.06	1.75
100	17.04	20.91	16.55	18.62	1.06	0.62	40.30	22.97	1.74
200	16.70	20.74	19.82	21.72	1.09	0.62	40.28	23.06	1.75
300	16.59	20.70	20.37	22.68	1.10	0.62	40.40	23.14	1.75
400	16.50	20.67	19.97	23.06	1.10	0.63	39.77	23.01	1.71
500	16.40	20.64	19.31	23.27	1.10	0.64	40.76	23.22	1.78
600	16.31	20.60	18.54	23.31	1.10	0.64	40.26	23.13	1.84
700	16.20	20.56	17.76	23.47	1.11	0.65	40.08	23.14	1.83
800	16.08	20.51	17.01	23.51	1.11	0.66	40.55	23.22	1.87
900	15.95	20.45	16.32	23.56	1.11	0.67	39.86	23.01	1.83
1000	15.82	20.39	15.66	23.55	1.11	0.68	40.87	23.28	1.91
1200	15.53	20.25	14.59	23.43	1.11	0.71	40.63	23.11	1.95
1400	15.21	20.09	13.67	23.27	1.11	0.73	40.31	23.07	2.00
1600	14.88	19.92	12.91	23.02	1.11	0.75	41.26	23.18	2.06
1800	14.54	19.72	12.32	22.67	1.11	0.77	43.11	23.28	2.07
2000	14.19	19.51	11.83	22.24	1.11	0.79	43.75	23.24	2.16
2200	13.84	19.29	11.44	21.73	1.11	0.80	41.93	22.90	2.09
2400	13.50	19.05	11.12	21.20	1.11	0.82	42.98	23.15	2.18
2600	13.17	18.80	10.83	20.56	1.10	0.83	46.79	23.68	2.28
2800	12.84	18.56	10.62	20.06	1.10	0.84	47.79	23.61	2.35
3000	12.52	18.30	10.44	19.49	1.10	0.85	47.49	23.74	2.30
3200	12.21	18.03	10.32	18.97	1.10	0.85	46.05	23.41	2.32
3400	11.92	17.76	10.21	18.47	1.09	0.86	50.17	23.65	2.28
3600	11.64	17.47	10.17	17.94	1.09	0.86	54.63	23.76	2.43
3800	11.38	17.19	10.19	17.48	1.08	0.85	49.99	23.96	2.47
4000	11.13	16.90	10.24	17.04	1.08	0.85	49.49	23.67	2.45
4200	10.90	16.59	10.30	16.61	1.07	0.84	50.15	23.59	2.53
4400	10.70	16.27	10.43	16.22	1.06	0.83	50.87	23.58	2.54
4600	10.49	15.98	10.59	16.03	1.06	0.82	50.18	23.67	2.60
4800	10.31	15.64	10.72	15.86	1.05	0.81	48.06	23.47	2.61
5000	10.13	15.34	10.89	15.88	1.05	0.80	45.49	24.04	2.72
5200	9.97	15.02	10.98	15.85	1.04	0.79	46.01	23.48	2.69
5400	9.81	14.70	10.99	15.95	1.03	0.78	45.55	22.82	2.80
5600	9.64	14.41	10.89	16.15	1.02	0.77	46.47	23.24	2.93
5800	9.47	14.14	10.73	16.29	1.01	0.77	46.45	23.56	2.93
6000	9.31	13.85	10.38	16.11	1.00	0.76	44.88	23.38	3.00
6200	9.13	13.59	9.95	15.82	0.99	0.76	43.89	22.97	3.05
6400	8.93	13.36	9.44	15.34	0.98	0.76	44.38	22.82	3.21
6600	8.73	13.14	8.87	14.65	0.97	0.76	45.03	23.13	3.32
6800	8.51	12.94	8.22	13.79	0.96	0.77	43.54	23.00	3.43
7000	8.27	12.77	7.56	12.91	0.95	0.77	43.19	22.76	3.58



ISO 9001 ISO 14001 AS 9100 CERTIFIED

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com



IF/RF MICROWAVE COMPONENTS

REV. OR

LHA-1H+

7/25/2016

Page 3 of 20

Monolithic Amplifier

LHA-1H+

Typical Performance Data

Definitions:

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 5.00V, Id = 133.10mA @ Temperature = -45°C

FREQ (MHz)	Gain (dB)	Isolation (dB)	Input Return Loss (dB)	Output Return Loss (dB)	Stability		IP-3 Output (dBm)	1dB Comp. Output (dBm)	Noise Figure (dB)
					K	Measure			
20	19.80	23.72	6.80	9.35	0.85	0.69	41.97	21.48	1.60
100	16.62	20.37	15.74	16.61	1.04	0.61	37.46	22.37	1.35
200	16.18	20.15	19.75	19.16	1.08	0.61	36.86	22.46	1.38
300	16.04	20.11	20.73	19.40	1.09	0.61	36.68	22.55	1.44
400	15.95	20.08	20.52	19.38	1.10	0.61	36.12	22.46	1.36
500	15.87	20.05	20.08	19.43	1.10	0.62	36.83	22.66	1.46
600	15.78	20.03	19.36	19.37	1.10	0.62	36.54	22.60	1.43
700	15.69	19.99	18.74	19.62	1.10	0.63	36.40	22.64	1.43
800	15.60	19.95	18.13	19.89	1.11	0.64	36.75	22.71	1.49
900	15.49	19.90	17.42	20.22	1.11	0.65	36.16	22.54	1.45
1000	15.39	19.85	16.87	20.81	1.11	0.66	37.38	22.75	1.55
1200	15.15	19.73	15.82	22.00	1.11	0.68	36.90	22.69	1.52
1400	14.89	19.59	14.93	22.58	1.11	0.69	36.74	22.64	1.56
1600	14.62	19.44	14.08	23.21	1.11	0.71	37.28	22.70	1.61
1800	14.33	19.27	13.43	23.40	1.12	0.73	38.27	22.76	1.64
2000	14.03	19.09	12.97	23.50	1.12	0.74	38.68	22.70	1.64
2200	13.72	18.90	12.61	23.09	1.12	0.76	37.42	22.41	1.60
2400	13.42	18.70	12.26	22.55	1.12	0.77	37.98	22.58	1.66
2600	13.11	18.49	11.92	22.17	1.12	0.79	40.19	23.05	1.74
2800	12.82	18.27	11.62	22.13	1.11	0.80	40.73	22.99	1.75
3000	12.53	18.03	11.43	22.01	1.11	0.81	40.93	23.16	1.67
3200	12.27	17.77	11.40	21.36	1.11	0.81	39.64	22.89	1.85
3400	12.00	17.52	11.25	20.92	1.11	0.81	41.11	23.12	1.72
3600	11.75	17.26	11.17	20.27	1.10	0.81	41.78	23.20	1.84
3800	11.49	17.01	11.02	19.71	1.09	0.82	42.83	23.39	1.95
4000	11.24	16.75	11.03	18.83	1.09	0.82	41.71	23.12	1.89
4200	11.02	16.47	11.11	17.84	1.08	0.81	41.59	23.10	1.92
4400	10.82	16.18	11.22	17.01	1.07	0.80	41.93	23.17	1.88
4600	10.63	15.90	11.40	16.67	1.07	0.79	43.56	23.24	1.95
4800	10.49	15.56	11.70	16.39	1.06	0.77	43.70	23.16	2.00
5000	10.34	15.25	11.69	17.16	1.06	0.76	48.33	23.75	2.02
5200	10.17	14.95	11.37	18.20	1.05	0.76	44.37	23.22	1.99
5400	10.00	14.68	11.34	18.08	1.04	0.76	42.92	22.54	2.19
5600	9.84	14.40	11.61	17.45	1.03	0.74	44.30	22.85	2.21
5800	9.68	14.13	11.27	17.72	1.02	0.74	46.30	23.13	2.25
6000	9.52	13.86	10.88	17.45	1.01	0.74	46.45	23.09	2.29
6200	9.35	13.62	10.40	17.00	1.00	0.73	45.00	22.70	2.30
6400	9.17	13.40	10.18	16.33	0.99	0.73	44.96	22.41	2.39
6600	9.01	13.15	9.66	15.60	0.98	0.72	44.28	22.54	2.50
6800	8.81	12.96	9.08	14.58	0.97	0.72	47.50	22.56	2.59
7000	8.58	12.79	8.38	13.72	0.96	0.73	46.51	22.36	2.70



ISO 9001 ISO 14001 AS 9100 CERTIFIED

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com



IF/RF MICROWAVE COMPONENTS

REV. OR

LHA-1H+

7/25/2016

Page 4 of 20

Monolithic Amplifier

LHA-1H+

Typical Performance Data

Definitions:

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 4.75V, Id = 118.21mA @ Temperature = -45°C

FREQ (MHz)	Gain (dB)	Isolation (dB)	Input Return Loss (dB)	Output Return Loss (dB)	Stability		IP-3 Output (dBm)	1dB Comp. Output (dBm)	Noise Figure (dB)
20	19.72	23.66	6.82	9.26	0.85	0.69	41.14	20.89	1.45
100	16.55	20.31	15.72	16.70	1.04	0.61	37.68	21.71	1.29
200	16.11	20.09	19.73	19.41	1.08	0.61	37.30	21.81	1.35
300	15.97	20.05	20.75	19.72	1.09	0.61	37.15	21.90	1.35
400	15.88	20.02	20.55	19.71	1.10	0.61	36.47	21.82	1.33
500	15.80	19.99	20.11	19.75	1.10	0.62	37.44	22.01	1.42
600	15.71	19.97	19.39	19.69	1.10	0.63	37.00	21.96	1.41
700	15.63	19.93	18.75	19.93	1.10	0.63	36.80	22.00	1.39
800	15.53	19.89	18.15	20.20	1.11	0.64	37.25	22.07	1.45
900	15.43	19.85	17.43	20.52	1.11	0.65	36.48	21.90	1.46
1000	15.32	19.80	16.86	21.10	1.11	0.66	38.10	22.11	1.55
1200	15.09	19.68	15.79	22.28	1.11	0.68	37.17	22.02	1.48
1400	14.83	19.55	14.90	22.81	1.11	0.70	37.06	21.99	1.54
1600	14.56	19.39	14.04	23.38	1.11	0.71	37.58	22.04	1.60
1800	14.27	19.23	13.40	23.50	1.12	0.73	38.55	22.10	1.58
2000	13.97	19.05	12.93	23.49	1.12	0.75	38.63	22.03	1.61
2200	13.67	18.87	12.57	23.00	1.12	0.76	37.44	21.76	1.57
2400	13.37	18.67	12.21	22.39	1.12	0.77	37.94	21.93	1.64
2600	13.06	18.47	11.87	21.93	1.12	0.79	40.25	22.38	1.71
2800	12.76	18.25	11.56	21.82	1.11	0.80	40.46	22.33	1.78
3000	12.48	18.02	11.35	21.65	1.11	0.81	40.27	22.48	1.66
3200	12.22	17.76	11.34	21.02	1.11	0.81	39.32	22.24	1.80
3400	11.95	17.51	11.18	20.59	1.11	0.82	40.52	22.45	1.73
3600	11.70	17.25	11.10	19.97	1.10	0.82	40.93	22.53	1.82
3800	11.44	17.00	10.96	19.45	1.10	0.82	41.53	22.71	1.86
4000	11.20	16.75	10.96	18.59	1.09	0.82	40.16	22.46	1.87
4200	10.98	16.47	11.04	17.63	1.08	0.81	40.12	22.45	1.91
4400	10.77	16.18	11.14	16.85	1.08	0.80	40.52	22.52	1.90
4600	10.59	15.91	11.32	16.53	1.07	0.79	41.48	22.60	1.90
4800	10.45	15.56	11.62	16.27	1.06	0.77	41.25	22.51	1.95
5000	10.29	15.25	11.63	17.04	1.06	0.76	43.04	23.07	2.02
5200	10.14	14.96	11.30	18.05	1.05	0.77	41.16	22.56	2.05
5400	9.96	14.68	11.27	17.93	1.04	0.76	40.18	21.94	2.10
5600	9.81	14.41	11.53	17.31	1.03	0.75	41.29	22.25	2.19
5800	9.64	14.14	11.21	17.57	1.03	0.74	42.26	22.51	2.20
6000	9.49	13.87	10.81	17.30	1.01	0.74	41.66	22.46	2.21
6200	9.31	13.63	10.35	16.85	1.00	0.74	41.02	22.10	2.26
6400	9.13	13.41	10.14	16.21	1.00	0.73	41.31	21.85	2.32
6600	8.97	13.16	9.62	15.48	0.98	0.73	42.11	21.97	2.51
6800	8.77	12.97	9.05	14.49	0.98	0.73	42.76	22.01	2.53
7000	8.55	12.80	8.36	13.63	0.96	0.73	41.76	21.81	2.64



ISO 9001 ISO 14001 AS 9100 CERTIFIED

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com



IF/RF MICROWAVE COMPONENTS

REV. OR

LHA-1H+

7/25/2016

Page 5 of 20

Monolithic Amplifier

LHA-1H+

Typical Performance Data

Definitions:

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 5.25V, Id = 148.74mA @ Temperature = -45°C

FREQ (MHz)	Gain (dB)	Isolation (dB)	Input Return Loss (dB)	Output Return Loss (dB)	Stability		IP-3 Output (dBm)	1dB Comp. Output (dBm)	Noise Figure (dB)
					K	Measure			
20	19.86	23.76	6.95	9.46	0.85	0.69	43.21	22.05	1.74
100	16.71	20.46	15.89	16.70	1.04	0.61	37.24	22.97	1.39
200	16.28	20.25	19.87	19.18	1.08	0.61	36.70	23.06	1.45
300	16.14	20.20	20.79	19.40	1.09	0.61	36.52	23.14	1.41
400	16.05	20.17	20.57	19.38	1.10	0.61	35.97	23.04	1.39
500	15.97	20.15	20.08	19.42	1.10	0.62	36.64	23.24	1.49
600	15.89	20.12	19.35	19.37	1.10	0.62	36.32	23.17	1.47
700	15.80	20.08	18.72	19.62	1.10	0.63	36.24	23.21	1.47
800	15.70	20.04	18.11	19.90	1.11	0.64	36.54	23.29	1.52
900	15.59	19.99	17.39	20.24	1.11	0.65	36.04	23.11	1.52
1000	15.49	19.94	16.85	20.83	1.11	0.66	37.12	23.35	1.58
1200	15.25	19.81	15.77	22.05	1.11	0.68	36.75	23.27	1.54
1400	14.98	19.67	14.88	22.66	1.11	0.69	36.58	23.22	1.59
1600	14.71	19.51	14.03	23.31	1.11	0.71	37.22	23.28	1.66
1800	14.41	19.34	13.40	23.53	1.11	0.73	38.18	23.35	1.68
2000	14.11	19.15	12.93	23.64	1.12	0.74	38.62	23.29	1.72
2200	13.80	18.96	12.58	23.25	1.12	0.76	37.57	22.98	1.70
2400	13.50	18.75	12.23	22.72	1.12	0.77	37.90	23.17	1.70
2600	13.18	18.54	11.89	22.32	1.11	0.79	40.00	23.65	1.75
2800	12.88	18.32	11.58	22.28	1.11	0.80	40.33	23.59	1.87
3000	12.60	18.07	11.39	22.13	1.11	0.81	41.15	23.77	1.74
3200	12.33	17.81	11.38	21.45	1.11	0.81	39.57	23.46	1.85
3400	12.06	17.55	11.23	20.98	1.10	0.81	40.83	23.70	1.81
3600	11.81	17.29	11.15	20.35	1.10	0.81	41.31	23.79	1.91
3800	11.55	17.03	11.01	19.76	1.09	0.82	42.45	24.00	1.98
4000	11.30	16.78	11.02	18.87	1.09	0.81	42.05	23.69	1.89
4200	11.07	16.49	11.10	17.84	1.08	0.81	41.57	23.68	2.01
4400	10.87	16.20	11.20	17.00	1.07	0.80	41.78	23.74	1.99
4600	10.68	15.92	11.39	16.62	1.07	0.78	42.66	23.81	2.02
4800	10.54	15.56	11.69	16.36	1.06	0.77	42.87	23.72	2.04
5000	10.38	15.26	11.68	17.13	1.05	0.76	44.38	24.35	2.11
5200	10.22	14.96	11.35	18.17	1.04	0.76	43.77	23.78	2.13
5400	10.04	14.68	11.31	18.06	1.04	0.75	42.49	23.06	2.20
5600	9.89	14.40	11.57	17.44	1.03	0.74	43.03	23.39	2.26
5800	9.72	14.14	11.24	17.75	1.02	0.74	43.00	23.67	2.34
6000	9.57	13.86	10.83	17.47	1.01	0.73	44.03	23.65	2.36
6200	9.38	13.64	10.37	17.13	1.00	0.73	43.12	23.23	2.43
6400	9.20	13.38	10.14	16.32	0.99	0.72	42.03	22.92	2.50
6600	9.04	13.15	9.63	15.64	0.98	0.72	41.33	23.04	2.58
6800	8.84	12.96	9.04	14.63	0.97	0.72	41.80	23.07	2.62
7000	8.62	12.78	8.36	13.75	0.96	0.73	41.80	22.86	2.78



ISO 9001 ISO 14001 AS 9100 CERTIFIED

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com



IF/RF MICROWAVE COMPONENTS

REV. OR

LHA-1H+

7/25/2016

Page 6 of 20

Monolithic Amplifier

LHA-1H+

Typical Performance Data

Definitions:

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 5.00V, Id = 148.60mA @ Temperature = +85°C

FREQ (MHz)	Gain (dB)	Isolation (dB)	Input Return Loss (dB)	Output Return Loss (dB)	Stability		IP-3 Output (dBm)	1dB Comp. Output (dBm)	Noise Figure (dB)
					K	Measure			
20	19.41	23.78	7.85	10.27	0.93	0.69	38.10	21.62	2.18
100	17.11	21.19	16.64	20.24	1.08	0.64	42.69	22.47	2.16
200	16.84	21.05	18.87	24.13	1.10	0.64	48.37	22.55	2.23
300	16.73	21.01	18.87	25.39	1.10	0.64	48.35	22.63	2.28
400	16.63	20.98	18.33	25.56	1.11	0.65	50.56	22.48	2.20
500	16.53	20.94	17.64	25.41	1.11	0.66	45.29	22.71	2.29
600	16.42	20.89	16.96	25.06	1.11	0.67	47.39	22.60	2.32
700	16.30	20.84	16.22	24.84	1.11	0.68	45.93	22.61	2.29
800	16.16	20.78	15.56	24.40	1.11	0.69	45.75	22.70	2.33
900	16.02	20.71	14.96	23.99	1.11	0.70	45.36	22.48	2.37
1000	15.87	20.63	14.38	23.56	1.11	0.71	43.49	22.77	2.39
1200	15.54	20.46	13.43	22.50	1.10	0.74	42.94	22.61	2.39
1400	15.19	20.27	12.65	21.59	1.10	0.76	43.32	22.59	2.50
1600	14.84	20.05	12.00	20.82	1.10	0.78	42.54	22.71	2.56
1800	14.47	19.82	11.48	20.21	1.10	0.80	41.67	22.84	2.56
2000	14.10	19.58	11.06	19.66	1.10	0.82	40.95	22.82	2.66
2200	13.72	19.35	10.69	19.14	1.09	0.83	40.50	22.51	2.61
2400	13.35	19.09	10.38	18.68	1.09	0.85	42.07	22.74	2.67
2600	12.99	18.84	10.13	18.20	1.09	0.86	41.40	23.21	2.81
2800	12.64	18.57	9.93	17.87	1.09	0.87	41.79	23.16	2.92
3000	12.31	18.30	9.77	17.49	1.08	0.88	40.61	23.24	2.85
3200	11.99	18.02	9.69	17.10	1.08	0.88	41.27	22.98	2.97
3400	11.68	17.75	9.63	16.71	1.08	0.89	41.04	23.18	2.93
3600	11.38	17.45	9.64	16.31	1.08	0.89	40.85	23.26	3.05
3800	11.11	17.16	9.64	16.07	1.07	0.88	40.67	23.38	3.13
4000	10.86	16.85	9.70	15.88	1.07	0.88	40.63	23.12	3.12
4200	10.62	16.54	9.79	15.74	1.07	0.87	40.71	23.04	3.24
4400	10.40	16.21	9.92	15.43	1.06	0.86	40.51	23.00	3.18
4600	10.17	15.93	10.10	15.27	1.06	0.85	40.94	23.07	3.29
4800	9.99	15.59	10.21	15.18	1.05	0.84	40.33	22.85	3.34
5000	9.81	15.27	10.36	15.23	1.04	0.83	40.10	23.29	3.39
5200	9.63	14.95	10.55	15.26	1.04	0.82	39.71	22.82	3.40
5400	9.46	14.64	10.64	15.19	1.03	0.81	39.23	22.28	3.51
5600	9.29	14.35	10.57	15.22	1.02	0.80	40.03	22.68	3.65
5800	9.12	14.07	10.41	15.32	1.01	0.80	40.33	22.97	3.68
6000	8.95	13.79	10.12	15.20	1.00	0.79	39.41	22.75	3.76
6200	8.78	13.52	9.66	14.93	0.99	0.79	38.70	22.42	3.82
6400	8.56	13.30	9.09	14.50	0.98	0.79	39.17	22.36	3.93
6600	8.35	13.09	8.40	13.88	0.97	0.80	39.94	22.66	4.08
6800	8.10	12.93	7.80	13.07	0.96	0.81	38.84	22.48	4.19
7000	7.83	12.77	7.11	12.09	0.94	0.81	38.30	22.24	4.37



ISO 9001 ISO 14001 AS 9100 CERTIFIED

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com



IF/RF MICROWAVE COMPONENTS

REV. OR

LHA-1H+

7/25/2016

Page 7 of 20

Monolithic Amplifier

LHA-1H+

Typical Performance Data

Definitions:

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 4.75V, Id = 135.57mA @ Temperature = +85°C

FREQ (MHz)	Gain (dB)	Isolation (dB)	Input Return Loss (dB)	Output Return Loss (dB)	Stability		IP-3 Output (dBm)	1dB Comp. Output (dBm)	Noise Figure (dB)
20	19.40	23.77	7.69	10.22	0.92	0.69	37.46	21.10	2.09
100	17.08	21.14	16.45	20.11	1.07	0.64	42.40	21.94	2.13
200	16.81	21.00	18.73	23.88	1.10	0.64	46.31	22.02	2.17
300	16.69	20.96	18.72	25.07	1.10	0.64	47.84	22.09	2.25
400	16.60	20.93	18.21	25.22	1.11	0.65	46.87	21.96	2.16
500	16.49	20.88	17.54	25.05	1.11	0.66	43.73	22.18	2.30
600	16.38	20.84	16.87	24.70	1.11	0.67	44.03	22.08	2.27
700	16.26	20.78	16.13	24.46	1.11	0.68	43.46	22.10	2.26
800	16.12	20.72	15.48	24.02	1.11	0.69	43.13	22.18	2.31
900	15.98	20.65	14.91	23.60	1.10	0.70	42.45	21.97	2.34
1000	15.83	20.57	14.33	23.19	1.10	0.71	41.66	22.24	2.40
1200	15.50	20.40	13.37	22.16	1.10	0.74	40.82	22.09	2.37
1400	15.15	20.20	12.61	21.28	1.10	0.76	40.90	22.07	2.46
1600	14.79	19.98	11.97	20.54	1.09	0.78	40.46	22.18	2.50
1800	14.42	19.75	11.45	19.96	1.09	0.80	40.31	22.30	2.51
2000	14.05	19.51	11.03	19.43	1.09	0.81	39.43	22.27	2.58
2200	13.67	19.27	10.68	18.94	1.09	0.83	38.63	21.97	2.61
2400	13.31	19.02	10.37	18.51	1.09	0.84	39.94	22.20	2.67
2600	12.94	18.76	10.12	18.06	1.09	0.86	40.08	22.65	2.76
2800	12.60	18.50	9.93	17.77	1.08	0.87	40.17	22.59	2.86
3000	12.26	18.23	9.77	17.41	1.08	0.88	39.15	22.69	2.83
3200	11.94	17.95	9.69	17.06	1.08	0.88	39.36	22.44	2.93
3400	11.63	17.67	9.63	16.71	1.08	0.88	39.51	22.63	2.84
3600	11.34	17.38	9.64	16.33	1.07	0.88	39.46	22.73	2.99
3800	11.07	17.09	9.65	16.11	1.07	0.88	39.42	22.84	3.07
4000	10.82	16.78	9.71	15.93	1.07	0.88	39.06	22.61	3.05
4200	10.58	16.47	9.80	15.82	1.06	0.87	38.97	22.53	3.17
4400	10.36	16.15	9.93	15.52	1.06	0.86	38.85	22.49	3.16
4600	10.13	15.87	10.12	15.36	1.06	0.85	39.39	22.57	3.24
4800	9.95	15.53	10.23	15.27	1.05	0.84	38.69	22.35	3.26
5000	9.77	15.21	10.39	15.31	1.04	0.83	38.99	22.79	3.35
5200	9.60	14.89	10.57	15.33	1.04	0.82	38.37	22.32	3.29
5400	9.42	14.58	10.68	15.24	1.03	0.81	37.65	21.79	3.52
5600	9.25	14.30	10.62	15.23	1.02	0.80	38.59	22.19	3.59
5800	9.08	14.02	10.45	15.32	1.01	0.79	38.99	22.48	3.54
6000	8.92	13.74	10.17	15.15	1.01	0.79	38.13	22.27	3.66
6200	8.74	13.47	9.72	14.86	0.99	0.78	37.31	21.93	3.74
6400	8.53	13.25	9.14	14.39	0.98	0.79	37.66	21.87	3.84
6600	8.31	13.05	8.45	13.74	0.97	0.79	38.46	22.18	3.97
6800	8.05	12.89	7.85	12.92	0.96	0.80	37.51	21.99	4.10
7000	7.79	12.73	7.14	11.93	0.95	0.80	36.99	21.75	4.23



ISO 9001 ISO 14001 AS 9100 CERTIFIED

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com



IF/RF MICROWAVE COMPONENTS

REV. OR

LHA-1H+

7/25/2016

Page 8 of 20

Monolithic Amplifier

LHA-1H+

Typical Performance Data

Definitions:

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 5.25V, Id = 161.18mA @ Temperature = +85°C

FREQ (MHz)	Gain (dB)	Isolation (dB)	Input Return Loss (dB)	Output Return Loss (dB)	Stability		IP-3 Output (dBm)	1dB Comp. Output (dBm)	Noise Figure (dB)
					K	Measure			
20	19.41	23.77	8.01	10.25	0.93	0.68	37.75	22.05	2.35
100	17.13	21.21	16.84	20.35	1.08	0.64	42.80	22.93	2.29
200	16.87	21.07	19.11	24.46	1.10	0.64	47.52	23.01	2.33
300	16.76	21.04	19.08	25.89	1.11	0.64	46.63	23.10	2.44
400	16.66	21.01	18.52	26.16	1.11	0.65	47.44	22.94	2.28
500	16.56	20.97	17.80	26.07	1.11	0.66	45.61	23.17	2.44
600	16.45	20.93	17.12	25.78	1.11	0.67	49.12	23.05	2.42
700	16.33	20.88	16.36	25.59	1.11	0.68	48.64	23.05	2.43
800	16.20	20.82	15.69	25.15	1.11	0.69	47.79	23.15	2.46
900	16.06	20.76	15.10	24.73	1.11	0.70	50.48	22.92	2.49
1000	15.91	20.69	14.49	24.28	1.11	0.71	44.63	23.22	2.57
1200	15.58	20.53	13.52	23.14	1.11	0.74	46.02	23.04	2.55
1400	15.24	20.34	12.73	22.16	1.11	0.76	46.30	23.02	2.63
1600	14.89	20.13	12.07	21.33	1.10	0.78	44.30	23.15	2.70
1800	14.52	19.91	11.53	20.65	1.10	0.80	42.75	23.29	2.69
2000	14.15	19.69	11.09	20.03	1.10	0.82	42.22	23.27	2.76
2200	13.77	19.45	10.72	19.46	1.10	0.83	42.39	22.94	2.75
2400	13.42	19.21	10.40	18.93	1.10	0.85	44.02	23.18	2.85
2600	13.05	18.96	10.14	18.39	1.09	0.86	42.22	23.67	2.93
2800	12.70	18.70	9.93	17.99	1.09	0.87	42.33	23.62	3.03
3000	12.37	18.43	9.77	17.55	1.09	0.88	41.27	23.70	3.01
3200	12.05	18.16	9.67	17.10	1.09	0.89	42.43	23.43	3.16
3400	11.74	17.88	9.60	16.66	1.08	0.89	41.84	23.62	3.00
3600	11.45	17.59	9.59	16.21	1.08	0.89	41.80	23.70	3.19
3800	11.17	17.30	9.58	15.93	1.08	0.89	41.27	23.81	3.30
4000	10.92	16.99	9.63	15.70	1.07	0.88	41.59	23.54	3.22
4200	10.68	16.68	9.71	15.52	1.07	0.87	41.72	23.45	3.35
4400	10.46	16.35	9.84	15.19	1.06	0.86	41.54	23.40	3.37
4600	10.23	16.07	10.01	15.01	1.06	0.86	41.54	23.48	3.44
4800	10.05	15.72	10.11	14.92	1.05	0.85	41.26	23.25	3.47
5000	9.87	15.40	10.26	14.96	1.04	0.83	40.71	23.70	3.55
5200	9.69	15.08	10.44	14.99	1.04	0.82	40.65	23.21	3.59
5400	9.53	14.76	10.52	14.95	1.03	0.81	40.56	22.67	3.68
5600	9.35	14.47	10.46	15.00	1.02	0.81	40.92	23.09	3.79
5800	9.19	14.18	10.30	15.17	1.01	0.80	40.95	23.38	3.85
6000	9.02	13.88	10.02	15.11	1.00	0.80	40.19	23.15	3.89
6200	8.85	13.61	9.57	14.95	0.99	0.80	39.63	22.80	4.01
6400	8.64	13.38	9.00	14.61	0.98	0.80	40.12	22.76	4.13
6600	8.43	13.16	8.32	14.06	0.96	0.81	40.73	23.09	4.28
6800	8.17	12.99	7.71	13.31	0.95	0.81	39.71	22.88	4.41
7000	7.91	12.82	7.02	12.34	0.94	0.82	39.32	22.64	4.56



ISO 9001 ISO 14001 AS 9100 CERTIFIED

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com



IF/RF MICROWAVE COMPONENTS

REV. OR

LHA-1H+

7/25/2016

Page 9 of 20

Monolithic Amplifier

LHA-1H+

Typical Performance Data

Definitions:

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 5.00V, Id = 146.66mA @ Temperature = +105°C

FREQ (MHz)	Gain (dB)	Isolation (dB)	Input Return Loss (dB)	Output Return Loss (dB)	Stability		IP-3 Output (dBm)	1dB Comp. Output (dBm)	Noise Figure (dB)
					K	Measure			
20	19.27	23.75	8.05	10.34	0.94	0.69	36.49	21.53	2.42
100	17.12	21.28	16.66	20.65	1.08	0.64	41.41	22.34	2.36
200	16.88	21.15	18.61	24.82	1.10	0.64	42.84	22.41	2.39
300	16.76	21.11	18.46	25.99	1.11	0.65	42.54	22.48	2.41
400	16.66	21.08	17.79	25.86	1.11	0.66	42.86	22.34	2.37
500	16.56	21.04	17.11	25.42	1.11	0.67	42.05	22.56	2.47
600	16.44	20.99	16.45	24.89	1.11	0.68	42.91	22.45	2.47
700	16.31	20.93	15.71	24.46	1.11	0.69	42.83	22.46	2.46
800	16.17	20.87	15.07	23.84	1.11	0.70	42.33	22.55	2.53
900	16.02	20.80	14.51	23.26	1.11	0.71	42.48	22.34	2.54
1000	15.86	20.72	13.95	22.71	1.11	0.72	41.48	22.62	2.59
1200	15.53	20.54	13.04	21.57	1.10	0.75	41.26	22.46	2.60
1400	15.17	20.34	12.31	20.62	1.10	0.77	41.61	22.46	2.69
1600	14.81	20.11	11.71	19.88	1.10	0.79	40.79	22.58	2.73
1800	14.43	19.87	11.23	19.29	1.09	0.81	40.14	22.72	2.76
2000	14.05	19.63	10.82	18.81	1.09	0.83	39.65	22.68	2.85
2200	13.67	19.38	10.49	18.38	1.09	0.84	39.35	22.37	2.86
2400	13.30	19.12	10.19	17.99	1.09	0.86	40.36	22.62	2.93
2600	12.93	18.86	9.94	17.57	1.09	0.87	40.06	23.05	3.03
2800	12.58	18.59	9.75	17.29	1.08	0.88	40.31	23.01	3.12
3000	12.24	18.32	9.60	16.96	1.08	0.89	39.17	23.06	3.06
3200	11.91	18.04	9.50	16.64	1.08	0.89	39.80	22.82	3.15
3400	11.60	17.76	9.43	16.32	1.08	0.90	39.69	22.98	3.08
3600	11.30	17.47	9.42	15.98	1.07	0.90	39.60	23.05	3.25
3800	11.02	17.18	9.42	15.77	1.07	0.90	39.35	23.12	3.35
4000	10.76	16.88	9.46	15.61	1.07	0.89	39.33	22.90	3.27
4200	10.51	16.57	9.55	15.47	1.06	0.88	39.42	22.81	3.41
4400	10.29	16.25	9.66	15.18	1.06	0.88	39.20	22.75	3.37
4600	10.06	15.96	9.82	15.00	1.06	0.87	39.62	22.85	3.48
4800	9.87	15.63	9.95	14.89	1.05	0.86	38.98	22.62	3.50
5000	9.68	15.31	10.13	14.90	1.04	0.85	38.91	22.97	3.62
5200	9.51	14.98	10.31	14.86	1.04	0.83	38.53	22.54	3.57
5400	9.34	14.67	10.42	14.77	1.03	0.82	38.20	22.09	3.74
5600	9.17	14.38	10.39	14.80	1.02	0.82	39.03	22.50	3.80
5800	9.00	14.09	10.30	14.90	1.01	0.81	39.12	22.76	3.85
6000	8.84	13.79	10.02	14.80	1.00	0.80	38.24	22.49	3.92
6200	8.66	13.52	9.61	14.62	0.99	0.80	37.69	22.19	4.00
6400	8.46	13.29	9.05	14.27	0.98	0.80	38.14	22.21	4.15
6600	8.24	13.08	8.33	13.72	0.96	0.81	38.75	22.53	4.31
6800	7.98	12.92	7.69	12.97	0.96	0.82	37.83	22.27	4.45
7000	7.71	12.76	6.97	12.00	0.94	0.82	37.27	22.04	4.63



ISO 9001 ISO 14001 AS 9100 CERTIFIED

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com



REV. OR
LHA-1H+

7/25/2016

Page 10 of 20

IF/RF MICROWAVE COMPONENTS

Monolithic Amplifier

LHA-1H+

Typical Performance Data

Definitions:

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 4.75V, Id = 134.58mA @ Temperature = +105°C

FREQ	Gain	Isolation	Input Return Loss	Output Return Loss	Stability		IP-3 Output	1dB Comp. Output	Noise Figure
(MHz)	(dB)	(dB)	(dB)	(dB)	K	Measure	(dBm)	(dBm)	(dB)
20	19.29	23.76	7.76	10.31	0.94	0.70	36.70	21.01	2.18
100	17.10	21.24	16.36	20.54	1.08	0.64	41.23	21.81	2.21
200	16.85	21.10	18.45	24.51	1.10	0.64	42.61	21.88	2.22
300	16.73	21.07	18.28	25.59	1.11	0.65	42.64	21.95	2.25
400	16.63	21.03	17.61	25.48	1.11	0.66	43.02	21.81	2.22
500	16.53	20.99	16.98	25.03	1.11	0.67	41.32	22.03	2.35
600	16.41	20.94	16.31	24.50	1.11	0.68	41.99	21.93	2.33
700	16.28	20.88	15.59	24.06	1.11	0.69	41.60	21.94	2.30
800	16.14	20.81	14.97	23.45	1.11	0.70	41.23	22.02	2.39
900	15.99	20.74	14.41	22.88	1.10	0.71	41.14	21.82	2.39
1000	15.83	20.66	13.88	22.35	1.10	0.72	40.47	22.09	2.48
1200	15.49	20.47	12.98	21.26	1.10	0.75	39.82	21.95	2.43
1400	15.13	20.26	12.26	20.35	1.10	0.77	40.02	21.94	2.53
1600	14.76	20.03	11.67	19.64	1.09	0.79	39.49	22.05	2.58
1800	14.39	19.79	11.20	19.07	1.09	0.81	39.11	22.18	2.64
2000	14.01	19.54	10.80	18.62	1.09	0.82	38.44	22.14	2.68
2200	13.62	19.29	10.47	18.21	1.08	0.84	38.00	21.85	2.67
2400	13.26	19.02	10.18	17.84	1.08	0.85	38.87	22.09	2.77
2600	12.89	18.76	9.93	17.45	1.08	0.87	39.11	22.50	2.86
2800	12.54	18.49	9.74	17.19	1.08	0.88	39.13	22.47	2.93
3000	12.20	18.22	9.59	16.89	1.07	0.88	38.29	22.52	2.88
3200	11.87	17.94	9.51	16.61	1.07	0.89	38.47	22.29	3.01
3400	11.55	17.66	9.44	16.32	1.07	0.89	38.62	22.46	2.95
3600	11.25	17.37	9.43	16.01	1.07	0.89	38.63	22.53	3.05
3800	10.97	17.08	9.44	15.83	1.07	0.89	38.44	22.61	3.17
4000	10.72	16.77	9.49	15.68	1.06	0.89	38.15	22.40	3.13
4200	10.47	16.47	9.57	15.56	1.06	0.88	38.14	22.32	3.26
4400	10.25	16.14	9.69	15.30	1.05	0.87	37.94	22.27	3.19
4600	10.02	15.86	9.86	15.13	1.05	0.86	38.59	22.37	3.29
4800	9.83	15.53	9.99	15.02	1.04	0.85	37.93	22.15	3.36
5000	9.64	15.21	10.18	15.02	1.04	0.84	38.01	22.49	3.42
5200	9.47	14.89	10.36	14.97	1.03	0.83	37.50	22.07	3.41
5400	9.30	14.57	10.47	14.86	1.03	0.82	36.97	21.62	3.55
5600	9.13	14.29	10.45	14.86	1.02	0.81	37.83	22.03	3.59
5800	8.96	14.00	10.36	14.93	1.01	0.80	38.10	22.29	3.68
6000	8.80	13.71	10.08	14.77	1.00	0.80	37.26	22.03	3.76
6200	8.62	13.44	9.67	14.55	0.99	0.79	36.58	21.73	3.83
6400	8.42	13.22	9.12	14.13	0.98	0.79	37.04	21.75	3.92
6600	8.19	13.01	8.41	13.54	0.97	0.80	37.67	22.06	4.11
6800	7.93	12.86	7.75	12.77	0.96	0.81	36.79	21.81	4.20
7000	7.67	12.70	7.03	11.79	0.94	0.81	36.21	21.57	4.35



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits LHA-1H+ [minicircuits.com](http://www.minicircuits.com)

REV. OR

LHA-1H+

7/25/2016

Page 11 of 20

Monolithic Amplifier

LHA-1H+

Typical Performance Data

Definitions:

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 5.25V, Id = 158.65mA @ Temperature = +105°C

FREQ	Gain	Isolation	Input Return Loss	Output Return Loss	Stability		IP-3 Output	1dB Comp. Output	Noise Figure
(MHz)	(dB)	(dB)	(dB)	(dB)	K	Measure	(dBm)	(dBm)	(dB)
20	19.26	23.75	8.14	10.33	0.95	0.68	36.05	21.96	2.52
100	17.13	21.29	16.85	20.74	1.09	0.64	41.08	22.78	2.44
200	16.88	21.17	18.90	25.10	1.11	0.64	42.23	22.85	2.46
300	16.77	21.13	18.71	26.40	1.11	0.65	41.79	22.93	2.53
400	16.67	21.11	18.01	26.33	1.11	0.66	41.80	22.78	2.44
500	16.57	21.07	17.33	25.90	1.11	0.67	41.52	23.00	2.61
600	16.45	21.02	16.63	25.42	1.11	0.68	42.57	22.87	2.51
700	16.33	20.97	15.88	24.98	1.11	0.69	42.58	22.88	2.53
800	16.19	20.91	15.23	24.35	1.11	0.70	42.17	22.98	2.62
900	16.04	20.84	14.65	23.75	1.11	0.71	42.52	22.75	2.59
1000	15.89	20.77	14.08	23.17	1.11	0.72	42.08	23.04	2.63
1200	15.55	20.60	13.15	21.99	1.11	0.75	41.80	22.88	2.67
1400	15.20	20.41	12.41	21.00	1.11	0.77	42.39	22.87	2.77
1600	14.84	20.19	11.79	20.22	1.10	0.79	41.19	23.00	2.84
1800	14.46	19.96	11.30	19.58	1.10	0.81	40.23	23.14	2.83
2000	14.09	19.73	10.88	19.07	1.10	0.83	39.78	23.11	2.92
2200	13.71	19.49	10.53	18.60	1.10	0.84	40.05	22.79	2.90
2400	13.35	19.23	10.22	18.17	1.09	0.86	40.88	23.04	2.99
2600	12.98	18.97	9.96	17.70	1.09	0.87	40.05	23.48	3.09
2800	12.63	18.71	9.76	17.37	1.09	0.88	40.36	23.44	3.16
3000	12.29	18.44	9.60	17.00	1.09	0.89	39.54	23.48	3.12
3200	11.96	18.16	9.49	16.64	1.08	0.90	40.24	23.24	3.25
3400	11.64	17.89	9.41	16.28	1.08	0.90	40.03	23.40	3.16
3600	11.34	17.60	9.39	15.90	1.08	0.90	39.83	23.45	3.34
3800	11.06	17.31	9.38	15.65	1.07	0.90	39.68	23.51	3.42
4000	10.81	17.00	9.42	15.44	1.07	0.90	39.77	23.28	3.37
4200	10.56	16.70	9.49	15.27	1.07	0.89	39.85	23.18	3.46
4400	10.34	16.37	9.60	14.97	1.06	0.88	39.70	23.13	3.46
4600	10.11	16.09	9.75	14.79	1.06	0.87	39.87	23.22	3.58
4800	9.92	15.74	9.86	14.67	1.05	0.86	39.37	23.00	3.60
5000	9.73	15.43	10.05	14.66	1.04	0.85	39.11	23.34	3.64
5200	9.56	15.10	10.21	14.62	1.03	0.84	38.99	22.92	3.67
5400	9.40	14.77	10.31	14.56	1.02	0.83	38.86	22.46	3.81
5600	9.22	14.48	10.29	14.61	1.02	0.82	39.40	22.88	3.89
5800	9.06	14.18	10.20	14.74	1.01	0.81	39.28	23.14	3.94
6000	8.90	13.88	9.91	14.69	1.00	0.81	38.70	22.85	4.02
6200	8.73	13.59	9.51	14.59	0.98	0.81	38.27	22.55	4.10
6400	8.52	13.36	8.97	14.33	0.97	0.81	38.71	22.59	4.22
6600	8.30	13.14	8.27	13.86	0.96	0.82	39.05	22.91	4.39
6800	8.05	12.97	7.61	13.17	0.95	0.83	38.30	22.63	4.54
7000	7.78	12.80	6.90	12.22	0.93	0.84	37.90	22.40	4.73



ISO 9001 ISO 14001 AS 9100 CERTIFIED

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

minicircuits.com



REV. OR

LHA-1H+

7/25/2016

Page 12 of 20

IF/RF MICROWAVE COMPONENTS

Monolithic Amplifier

LHA-1H+

Typical Performance Data

Definitions:

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 4.00V, Id = 85.81mA @ Temperature = +25°C

FREQ (MHz)	Gain (dB)	Isolation (dB)	Input Return Loss (dB)	Output Return Loss (dB)	Stability		IP-3 Output (dBm)	1dB Comp. Output (dBm)	Noise Figure (dB)
					K	Measure			
20	19.27	23.63	6.80	9.59	0.88	0.72	35.06	18.92	1.45
100	16.55	20.56	15.66	18.38	1.06	0.64	36.11	19.63	1.55
200	16.19	20.38	18.69	21.77	1.09	0.64	37.04	19.72	1.63
300	16.07	20.33	19.22	22.76	1.10	0.64	37.36	19.80	1.59
400	15.97	20.29	18.87	22.93	1.10	0.65	38.02	19.72	1.59
500	15.88	20.25	18.29	22.84	1.10	0.65	36.28	19.89	1.62
600	15.77	20.20	17.59	22.52	1.10	0.66	36.19	19.84	1.69
700	15.66	20.15	16.90	22.29	1.10	0.67	35.79	19.85	1.64
800	15.54	20.09	16.20	21.97	1.10	0.68	35.64	19.90	1.71
900	15.41	20.02	15.56	21.64	1.10	0.69	35.37	19.74	1.72
1000	15.27	19.95	14.96	21.29	1.10	0.70	34.60	19.91	1.78
1200	14.97	19.79	13.93	20.60	1.10	0.72	34.19	19.79	1.78
1400	14.64	19.61	13.08	20.02	1.10	0.74	34.33	19.77	1.82
1600	14.30	19.41	12.38	19.51	1.09	0.76	34.09	19.82	1.92
1800	13.95	19.20	11.81	19.07	1.09	0.78	33.96	19.90	1.92
2000	13.60	18.98	11.36	18.69	1.09	0.80	33.23	19.82	1.96
2200	13.25	18.75	11.02	18.34	1.09	0.81	32.65	19.61	1.96
2400	12.91	18.51	10.71	18.02	1.09	0.83	33.36	19.82	2.00
2600	12.58	18.25	10.46	17.68	1.08	0.84	33.67	20.10	2.08
2800	12.25	18.00	10.28	17.47	1.08	0.85	33.72	20.10	2.12
3000	11.94	17.74	10.13	17.23	1.08	0.86	33.07	20.15	2.03
3200	11.63	17.48	10.04	17.05	1.08	0.86	33.12	20.03	2.11
3400	11.34	17.21	9.96	16.89	1.08	0.87	33.37	20.16	2.03
3600	11.07	16.93	9.95	16.67	1.07	0.87	33.45	20.27	2.17
3800	10.81	16.65	10.01	16.51	1.07	0.86	33.46	20.36	2.26
4000	10.57	16.36	10.07	16.33	1.07	0.86	33.11	20.25	2.18
4200	10.35	16.06	10.16	16.14	1.06	0.85	33.04	20.22	2.29
4400	10.15	15.75	10.30	15.92	1.06	0.84	32.96	20.22	2.25
4600	9.95	15.47	10.49	15.84	1.05	0.83	33.44	20.32	2.31
4800	9.78	15.14	10.64	15.74	1.05	0.82	33.05	20.18	2.29
5000	9.60	14.85	10.85	15.77	1.04	0.81	33.48	20.52	2.35
5200	9.44	14.55	10.93	15.71	1.04	0.79	32.94	20.20	2.30
5400	9.28	14.25	10.95	15.65	1.03	0.78	32.21	19.82	2.43
5600	9.11	13.98	10.86	15.63	1.03	0.78	32.98	20.12	2.51
5800	8.93	13.73	10.72	15.50	1.02	0.77	33.37	20.37	2.49
6000	8.77	13.46	10.37	15.03	1.01	0.76	32.89	20.23	2.56
6200	8.58	13.23	9.93	14.50	1.00	0.76	32.18	19.97	2.58
6400	8.37	13.03	9.43	13.81	0.99	0.75	32.29	19.90	2.67
6600	8.16	12.84	8.88	13.06	0.98	0.75	32.90	20.13	2.80
6800	7.92	12.68	8.23	12.22	0.98	0.75	32.45	20.02	2.91
7000	7.67	12.54	7.59	11.40	0.96	0.75	32.02	19.84	3.03



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site [minicircuits.com](http://www.minicircuits.com)



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

IF/RF MICROWAVE COMPONENTS

minicircuits.com



REV. OR

LHA-1H+

7/25/2016

Page 13 of 20

Monolithic Amplifier

LHA-1H+

Typical Performance Data

Definitions:

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 4.50V, Id = 115.25mA @ Temperature = +25°C

FREQ	Gain	Isolation	Input Return Loss	Output Return Loss	Stability		IP-3 Output	1dB Comp. Output	Noise Figure
(MHz)	(dB)	(dB)	(dB)	(dB)	K	Measure	(dBm)	(dBm)	(dB)
20	19.57	23.74	7.08	9.82	0.88	0.70	37.73	20.41	1.52
100	16.82	20.74	16.15	18.34	1.06	0.63	40.78	21.20	1.60
200	16.47	20.57	19.39	21.37	1.09	0.63	45.05	21.29	1.60
300	16.35	20.52	19.97	22.25	1.10	0.63	48.21	21.37	1.69
400	16.26	20.49	19.59	22.51	1.10	0.64	42.93	21.27	1.60
500	16.16	20.46	19.00	22.61	1.10	0.64	43.86	21.48	1.69
600	16.06	20.41	18.25	22.50	1.10	0.65	42.08	21.42	1.69
700	15.95	20.37	17.49	22.51	1.10	0.66	40.85	21.44	1.71
800	15.83	20.31	16.76	22.40	1.11	0.67	41.11	21.50	1.77
900	15.71	20.25	16.09	22.29	1.11	0.68	39.64	21.32	1.74
1000	15.57	20.18	15.45	22.15	1.11	0.69	39.79	21.54	1.81
1200	15.27	20.04	14.39	21.79	1.10	0.71	38.61	21.41	1.83
1400	14.96	19.86	13.49	21.45	1.10	0.73	38.56	21.38	1.89
1600	14.62	19.68	12.76	21.11	1.10	0.75	38.35	21.46	1.94
1800	14.28	19.47	12.17	20.77	1.10	0.77	38.55	21.54	1.94
2000	13.93	19.26	11.71	20.44	1.10	0.79	37.62	21.48	2.01
2200	13.58	19.03	11.34	20.08	1.10	0.80	36.64	21.22	1.96
2400	13.24	18.79	11.02	19.71	1.10	0.82	37.58	21.44	2.04
2600	12.91	18.54	10.75	19.29	1.10	0.83	38.44	21.85	2.10
2800	12.58	18.29	10.56	19.00	1.10	0.84	38.57	21.80	2.18
3000	12.27	18.02	10.39	18.63	1.09	0.85	37.68	21.91	2.12
3200	11.96	17.76	10.29	18.33	1.09	0.85	37.46	21.68	2.16
3400	11.67	17.49	10.19	18.03	1.09	0.86	37.84	21.88	2.13
3600	11.40	17.20	10.17	17.67	1.08	0.86	37.97	21.99	2.19
3800	11.13	16.92	10.21	17.37	1.08	0.85	38.07	22.15	2.30
4000	10.89	16.63	10.27	17.06	1.08	0.85	37.48	21.94	2.29
4200	10.67	16.32	10.34	16.73	1.07	0.84	37.25	21.90	2.31
4400	10.46	16.01	10.49	16.42	1.06	0.83	37.26	21.90	2.26
4600	10.26	15.72	10.65	16.27	1.06	0.82	37.92	21.98	2.35
4800	10.08	15.39	10.80	16.13	1.05	0.81	37.24	21.81	2.38
5000	9.90	15.10	11.00	16.16	1.05	0.80	37.91	22.27	2.42
5200	9.74	14.78	11.09	16.11	1.04	0.79	37.10	21.82	2.42
5400	9.58	14.47	11.11	16.12	1.03	0.78	35.97	21.27	2.58
5600	9.41	14.20	11.02	16.20	1.03	0.77	37.09	21.63	2.64
5800	9.23	13.93	10.86	16.19	1.02	0.76	37.68	21.92	2.66
6000	9.07	13.66	10.52	15.82	1.01	0.76	37.00	21.76	2.73
6200	8.89	13.41	10.07	15.37	1.00	0.75	36.07	21.42	2.75
6400	8.69	13.19	9.55	14.74	0.99	0.75	36.24	21.29	2.84
6600	8.48	12.99	8.98	13.97	0.98	0.75	37.11	21.55	2.94
6800	8.26	12.81	8.33	13.08	0.97	0.75	36.49	21.44	3.03
7000	8.01	12.65	7.66	12.20	0.96	0.76	35.86	21.23	3.14



ISO 9001 ISO 14001 AS 9100 CERTIFIED

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

minicircuits.com



REV. OR

LHA-1H+

7/25/2016

Page 14 of 20

IF/RF MICROWAVE COMPONENTS

Monolithic Amplifier

LHA-1H+

Typical Performance Data

Definitions:

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 4.00V, Id = 73.78mA @ Temperature = -45°C

FREQ	Gain	Isolation	Input Return Loss	Output Return Loss	Stability		IP-3 Output	1dB Comp. Output	Noise Figure
(MHz)	(dB)	(dB)	(dB)	(dB)	K	Measure	(dBm)	(dBm)	(dB)
20	19.23	23.45	6.50	8.71	0.84	0.69	33.42	18.32	1.17
100	16.12	19.95	15.20	17.02	1.04	0.63	33.43	19.13	1.26
200	15.67	19.72	19.24	20.89	1.09	0.62	34.20	19.26	1.33
300	15.54	19.67	20.47	21.81	1.10	0.62	34.89	19.34	1.34
400	15.45	19.64	20.40	21.92	1.10	0.63	36.78	19.33	1.28
500	15.37	19.62	19.99	21.95	1.10	0.63	34.44	19.43	1.36
600	15.29	19.60	19.27	21.79	1.11	0.64	34.91	19.40	1.41
700	15.20	19.57	18.60	21.94	1.11	0.65	34.87	19.40	1.40
800	15.11	19.53	17.95	22.08	1.11	0.66	34.62	19.44	1.40
900	15.00	19.50	17.20	22.29	1.11	0.66	35.40	19.33	1.39
1000	14.90	19.45	16.58	22.66	1.11	0.67	32.81	19.36	1.47
1200	14.67	19.35	15.45	23.39	1.11	0.69	33.72	19.33	1.41
1400	14.42	19.23	14.54	23.36	1.11	0.71	34.43	19.35	1.51
1600	14.15	19.10	13.69	23.43	1.11	0.73	34.24	19.35	1.59
1800	13.87	18.95	13.06	22.99	1.12	0.75	33.93	19.41	1.53
2000	13.58	18.80	12.58	22.48	1.12	0.76	32.88	19.27	1.59
2200	13.28	18.63	12.23	21.62	1.12	0.78	32.96	19.11	1.55
2400	12.99	18.46	11.86	20.75	1.12	0.80	34.18	19.32	1.61
2600	12.68	18.28	11.50	20.01	1.12	0.81	33.21	19.55	1.67
2800	12.39	18.09	11.16	19.64	1.11	0.82	33.35	19.55	1.69
3000	12.11	17.88	10.94	19.37	1.11	0.83	32.50	19.58	1.59
3200	11.86	17.64	10.90	18.88	1.11	0.84	33.67	19.55	1.76
3400	11.60	17.41	10.74	18.56	1.11	0.84	33.60	19.70	1.65
3600	11.36	17.17	10.66	18.09	1.10	0.84	33.70	19.77	1.72
3800	11.10	16.94	10.52	17.71	1.10	0.85	33.31	19.85	1.81
4000	10.87	16.70	10.50	17.05	1.09	0.85	33.47	19.72	1.81
4200	10.65	16.43	10.56	16.33	1.08	0.84	33.66	19.70	1.84
4400	10.46	16.16	10.64	15.77	1.08	0.83	33.79	19.78	1.82
4600	10.28	15.89	10.80	15.58	1.07	0.82	34.51	19.92	1.87
4800	10.16	15.54	11.09	15.39	1.06	0.80	34.20	19.85	1.85
5000	10.01	15.24	11.12	16.12	1.06	0.79	33.71	20.27	1.89
5200	9.86	14.95	10.84	16.94	1.05	0.80	34.11	19.92	1.88
5400	9.69	14.68	10.83	16.79	1.04	0.79	34.00	19.52	2.02
5600	9.55	14.41	11.10	16.23	1.03	0.78	34.94	19.82	2.04
5800	9.39	14.14	10.82	16.41	1.02	0.77	35.25	20.07	2.00
6000	9.24	13.88	10.43	16.13	1.01	0.77	34.45	20.03	2.08
6200	9.06	13.64	10.03	15.72	1.00	0.77	34.08	19.76	2.14
6400	8.88	13.42	9.84	15.15	0.99	0.76	34.68	19.67	2.19
6600	8.72	13.18	9.35	14.50	0.98	0.76	35.62	19.84	2.28
6800	8.52	12.99	8.81	13.63	0.97	0.75	35.00	19.87	2.35
7000	8.30	12.83	8.16	12.86	0.96	0.76	34.45	19.72	2.49



ISO 9001 ISO 14001 AS 9100 CERTIFIED

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

minicircuits.com



REV. OR

LHA-1H+

7/25/2016

Page 15 of 20

IF/RF MICROWAVE COMPONENTS

Monolithic Amplifier

LHA-1H+

Typical Performance Data

Definitions:

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 4.50V, Id = 102.88mA @ Temperature = -45°C

FREQ (MHz)	Gain (dB)	Isolation (dB)	Input Return Loss (dB)	Output Return Loss (dB)	Stability		IP-3 Output (dBm)	1dB Comp. Output (dBm)	Noise Figure (dB)
20	19.61	23.63	6.71	9.12	0.84	0.69	38.81	20.20	1.34
100	16.45	20.21	15.57	16.75	1.03	0.62	37.95	20.98	1.29
200	16.00	19.99	19.66	19.69	1.08	0.61	38.68	21.10	1.36
300	15.86	19.95	20.74	20.09	1.09	0.61	38.40	21.18	1.32
400	15.77	19.92	20.58	20.10	1.10	0.62	37.37	21.12	1.31
500	15.69	19.89	20.12	20.14	1.10	0.62	39.00	21.30	1.43
600	15.61	19.87	19.41	20.07	1.10	0.63	38.34	21.25	1.42
700	15.52	19.83	18.78	20.30	1.11	0.64	38.01	21.28	1.40
800	15.43	19.79	18.14	20.55	1.11	0.64	38.34	21.34	1.44
900	15.32	19.75	17.41	20.86	1.11	0.65	37.38	21.18	1.44
1000	15.22	19.70	16.85	21.42	1.11	0.66	39.56	21.35	1.54
1200	14.98	19.59	15.75	22.55	1.11	0.68	37.91	21.28	1.44
1400	14.73	19.46	14.85	23.00	1.11	0.70	37.89	21.26	1.51
1600	14.46	19.32	14.00	23.50	1.12	0.72	38.36	21.30	1.57
1800	14.17	19.16	13.36	23.50	1.12	0.73	39.18	21.36	1.58
2000	13.88	18.98	12.87	23.39	1.12	0.75	38.74	21.27	1.63
2200	13.57	18.80	12.52	22.80	1.12	0.76	37.40	21.03	1.56
2400	13.28	18.61	12.17	22.11	1.12	0.78	38.21	21.21	1.64
2600	12.97	18.42	11.81	21.57	1.12	0.79	40.18	21.61	1.70
2800	12.68	18.21	11.50	21.39	1.11	0.81	40.38	21.57	1.82
3000	12.40	17.98	11.29	21.19	1.11	0.81	39.13	21.70	1.63
3200	12.14	17.73	11.27	20.60	1.11	0.82	38.98	21.50	1.76
3400	11.87	17.48	11.11	20.20	1.11	0.82	39.81	21.70	1.64
3600	11.62	17.23	11.04	19.61	1.10	0.82	40.04	21.78	1.79
3800	11.36	16.99	10.89	19.12	1.10	0.83	40.08	21.93	1.90
4000	11.12	16.74	10.89	18.30	1.09	0.83	38.96	21.70	1.81
4200	10.90	16.46	10.96	17.40	1.09	0.82	39.03	21.70	1.90
4400	10.70	16.17	11.05	16.66	1.08	0.81	39.38	21.77	1.87
4600	10.52	15.90	11.23	16.37	1.08	0.80	40.28	21.86	1.90
4800	10.38	15.55	11.53	16.13	1.06	0.78	39.67	21.76	1.92
5000	10.23	15.25	11.55	16.89	1.06	0.77	40.55	22.28	1.96
5200	10.07	14.96	11.22	17.87	1.05	0.77	39.50	21.81	1.90
5400	9.90	14.68	11.20	17.74	1.04	0.77	38.57	21.26	2.00
5600	9.75	14.41	11.47	17.13	1.03	0.75	39.66	21.55	2.08
5800	9.59	14.14	11.15	17.38	1.03	0.75	40.64	21.80	2.11
6000	9.44	13.87	10.76	17.10	1.01	0.75	39.73	21.75	2.14
6200	9.26	13.63	10.31	16.66	1.00	0.74	39.04	21.43	2.21
6400	9.08	13.41	10.08	16.04	1.00	0.74	39.50	21.22	2.26
6600	8.92	13.17	9.59	15.32	0.98	0.73	40.58	21.36	2.41
6800	8.72	12.98	9.02	14.35	0.98	0.73	40.26	21.40	2.45
7000	8.50	12.81	8.34	13.51	0.96	0.74	39.62	21.21	2.54



ISO 9001 ISO 14001 AS 9100 CERTIFIED

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

minicircuits.com



REV. OR

LHA-1H+

7/25/2016

Page 16 of 20

IF/RF MICROWAVE COMPONENTS

Monolithic Amplifier

LHA-1H+

Typical Performance Data

Definitions:

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 4.00V, Id = 94.74mA @ Temperature = +85°C

FREQ (MHz)	Gain (dB)	Isolation (dB)	Input Return Loss (dB)	Output Return Loss (dB)	Stability		IP-3 Output (dBm)	1dB Comp. Output (dBm)	Noise Figure (dB)
					K	Measure			
20	19.13	23.72	7.30	10.08	0.92	0.71	35.89	19.20	1.82
100	16.79	20.97	15.67	19.78	1.07	0.65	37.54	19.93	1.94
200	16.51	20.82	17.74	23.36	1.10	0.65	38.11	20.01	2.01
300	16.39	20.77	17.77	24.21	1.10	0.66	38.14	20.08	2.01
400	16.29	20.73	17.29	23.97	1.11	0.66	38.55	20.00	1.95
500	16.18	20.67	16.67	23.46	1.11	0.67	37.14	20.19	2.08
600	16.07	20.61	16.07	22.87	1.10	0.68	37.07	20.12	2.07
700	15.93	20.54	15.39	22.40	1.10	0.69	36.73	20.14	2.07
800	15.80	20.47	14.80	21.82	1.10	0.70	36.56	20.20	2.12
900	15.65	20.38	14.27	21.31	1.10	0.71	36.28	20.03	2.18
1000	15.49	20.29	13.72	20.82	1.09	0.72	35.82	20.25	2.22
1200	15.14	20.08	12.84	19.81	1.09	0.75	35.36	20.13	2.18
1400	14.78	19.86	12.12	18.99	1.08	0.77	35.46	20.11	2.28
1600	14.42	19.61	11.52	18.34	1.08	0.79	35.26	20.21	2.31
1800	14.04	19.35	11.05	17.84	1.07	0.80	35.11	20.31	2.30
2000	13.66	19.10	10.67	17.43	1.07	0.82	34.48	20.27	2.41
2200	13.27	18.84	10.35	17.06	1.07	0.84	33.89	20.05	2.37
2400	12.90	18.58	10.08	16.76	1.07	0.85	34.58	20.24	2.46
2600	12.54	18.31	9.86	16.47	1.06	0.86	34.90	20.57	2.56
2800	12.19	18.05	9.69	16.33	1.06	0.87	34.99	20.55	2.64
3000	11.85	17.77	9.56	16.13	1.06	0.88	34.33	20.63	2.59
3200	11.53	17.49	9.51	15.96	1.06	0.88	34.34	20.46	2.67
3400	11.23	17.21	9.48	15.80	1.06	0.89	34.59	20.61	2.64
3600	10.94	16.92	9.51	15.60	1.06	0.88	34.66	20.71	2.73
3800	10.66	16.63	9.55	15.53	1.06	0.88	34.66	20.79	2.84
4000	10.42	16.32	9.63	15.48	1.05	0.88	34.30	20.64	2.80
4200	10.18	16.01	9.73	15.52	1.05	0.87	34.20	20.60	2.89
4400	9.97	15.70	9.90	15.34	1.05	0.86	34.09	20.57	2.91
4600	9.74	15.42	10.10	15.25	1.05	0.85	34.56	20.65	2.95
4800	9.56	15.09	10.24	15.17	1.04	0.84	34.07	20.48	3.00
5000	9.38	14.79	10.41	15.20	1.04	0.83	34.49	20.82	3.06
5200	9.21	14.48	10.60	15.19	1.03	0.81	33.89	20.47	3.02
5400	9.03	14.19	10.70	14.99	1.03	0.80	33.17	20.05	3.16
5600	8.86	13.92	10.63	14.85	1.02	0.79	34.01	20.38	3.22
5800	8.68	13.66	10.48	14.74	1.02	0.78	34.34	20.64	3.22
6000	8.51	13.40	10.18	14.37	1.01	0.78	33.72	20.46	3.27
6200	8.32	13.15	9.72	13.89	1.00	0.77	33.02	20.19	3.32
6400	8.10	12.96	9.14	13.26	0.99	0.77	33.24	20.13	3.47
6600	7.87	12.78	8.46	12.53	0.98	0.77	33.87	20.38	3.60
6800	7.61	12.65	7.87	11.71	0.98	0.77	33.27	20.22	3.68
7000	7.33	12.53	7.18	10.79	0.96	0.78	32.73	20.01	3.84



ISO 9001 ISO 14001 AS 9100 CERTIFIED

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

minicircuits.com



REV. OR

LHA-1H+

7/25/2016

Page 17 of 20

IF/RF MICROWAVE COMPONENTS

Monolithic Amplifier

LHA-1H+

Typical Performance Data

Definitions:

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 4.50V, Id = 122.32mA @ Temperature = +85°C

FREQ	Gain	Isolation	Input Return Loss	Output Return Loss	Stability		IP-3 Output	1dB Comp. Output	Noise Figure
(MHz)	(dB)	(dB)	(dB)	(dB)	K	Measure	(dBm)	(dBm)	(dB)
20	19.36	23.76	7.54	10.19	0.92	0.70	37.47	20.53	1.99
100	17.01	21.10	16.26	19.97	1.07	0.64	41.46	21.34	2.08
200	16.73	20.95	18.49	23.60	1.10	0.64	43.92	21.43	2.11
300	16.62	20.91	18.53	24.66	1.10	0.65	43.93	21.49	2.15
400	16.52	20.87	18.01	24.72	1.11	0.65	44.14	21.37	2.11
500	16.42	20.83	17.35	24.48	1.11	0.66	41.99	21.59	2.21
600	16.31	20.77	16.70	24.07	1.11	0.67	41.72	21.51	2.21
700	16.18	20.72	15.99	23.78	1.10	0.68	41.09	21.52	2.20
800	16.04	20.65	15.34	23.31	1.10	0.69	40.87	21.59	2.24
900	15.90	20.57	14.77	22.88	1.10	0.70	40.34	21.40	2.27
1000	15.74	20.50	14.20	22.46	1.10	0.71	39.82	21.66	2.32
1200	15.41	20.31	13.27	21.47	1.10	0.74	39.01	21.52	2.29
1400	15.06	20.11	12.51	20.62	1.09	0.76	38.99	21.50	2.41
1600	14.70	19.88	11.88	19.93	1.09	0.78	38.63	21.61	2.44
1800	14.33	19.64	11.37	19.38	1.09	0.80	38.53	21.72	2.42
2000	13.96	19.39	10.97	18.91	1.08	0.81	37.77	21.68	2.51
2200	13.57	19.15	10.61	18.46	1.08	0.83	37.01	21.41	2.50
2400	13.21	18.89	10.32	18.08	1.08	0.85	37.93	21.63	2.61
2600	12.85	18.63	10.08	17.69	1.08	0.86	38.28	22.04	2.68
2800	12.50	18.37	9.89	17.46	1.08	0.87	38.51	22.00	2.80
3000	12.16	18.09	9.75	17.16	1.07	0.88	37.61	22.09	2.77
3200	11.84	17.82	9.67	16.87	1.07	0.88	37.62	21.86	2.83
3400	11.54	17.53	9.62	16.58	1.07	0.88	37.86	22.04	2.76
3600	11.24	17.24	9.64	16.26	1.07	0.88	37.97	22.14	2.93
3800	10.97	16.95	9.66	16.09	1.07	0.88	37.86	22.26	3.02
4000	10.73	16.64	9.72	15.94	1.06	0.87	37.44	22.04	2.99
4200	10.48	16.33	9.82	15.88	1.06	0.87	37.33	21.98	3.07
4400	10.27	16.01	9.97	15.60	1.05	0.86	37.21	21.94	3.04
4600	10.04	15.73	10.15	15.46	1.05	0.85	37.74	22.02	3.18
4800	9.85	15.39	10.28	15.37	1.05	0.84	37.16	21.81	3.16
5000	9.68	15.08	10.44	15.41	1.04	0.83	37.57	22.23	3.26
5200	9.50	14.77	10.63	15.42	1.04	0.81	36.89	21.79	3.21
5400	9.33	14.46	10.73	15.30	1.03	0.80	36.07	21.28	3.39
5600	9.16	14.18	10.67	15.25	1.02	0.79	37.00	21.66	3.46
5800	8.99	13.91	10.51	15.27	1.02	0.79	37.39	21.95	3.48
6000	8.82	13.63	10.22	15.02	1.01	0.78	36.70	21.75	3.55
6200	8.64	13.37	9.76	14.66	1.00	0.78	35.89	21.42	3.62
6400	8.42	13.16	9.18	14.12	0.99	0.78	36.17	21.36	3.67
6600	8.20	12.97	8.50	13.42	0.97	0.78	36.94	21.65	3.87
6800	7.95	12.82	7.89	12.59	0.97	0.79	36.19	21.47	3.99
7000	7.68	12.67	7.19	11.61	0.95	0.79	35.55	21.24	4.07



ISO 9001 ISO 14001 AS 9100 CERTIFIED

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

minicircuits.com



REV. OR

LHA-1H+

7/25/2016

Page 18 of 20

IF/RF MICROWAVE COMPONENTS

Monolithic Amplifier

LHA-1H+

Typical Performance Data

Definitions:

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 4.00V, Id = 95.21mA @ Temperature = +105°C

FREQ (MHz)	Gain (dB)	Isolation (dB)	Input Return Loss (dB)	Output Return Loss (dB)	Stability		IP-3 Output (dBm)	1dB Comp. Output (dBm)	Noise Figure (dB)
					K	Measure			
20	19.05	23.70	7.33	10.18	0.93	0.72	35.45	19.09	1.87
100	16.84	21.08	15.49	20.14	1.08	0.65	37.03	19.80	2.00
200	16.58	20.93	17.35	23.76	1.10	0.66	37.56	19.88	2.08
300	16.46	20.89	17.20	24.42	1.11	0.66	37.51	19.94	2.12
400	16.35	20.84	16.63	23.92	1.11	0.67	37.68	19.84	2.02
500	16.24	20.78	16.07	23.22	1.11	0.68	36.70	20.05	2.13
600	16.12	20.72	15.48	22.52	1.10	0.69	36.58	19.98	2.12
700	15.98	20.64	14.82	21.95	1.10	0.70	36.31	19.99	2.16
800	15.83	20.56	14.25	21.28	1.10	0.71	36.17	20.05	2.20
900	15.68	20.47	13.74	20.69	1.09	0.72	35.94	19.89	2.21
1000	15.51	20.36	13.25	20.16	1.09	0.73	35.49	20.12	2.28
1200	15.15	20.15	12.42	19.14	1.08	0.76	35.10	20.00	2.28
1400	14.78	19.90	11.75	18.32	1.08	0.78	35.16	19.99	2.35
1600	14.41	19.64	11.22	17.71	1.07	0.80	35.04	20.09	2.37
1800	14.02	19.38	10.78	17.23	1.06	0.81	34.88	20.20	2.40
2000	13.63	19.11	10.43	16.87	1.06	0.83	34.24	20.17	2.47
2200	13.23	18.84	10.14	16.55	1.06	0.84	33.74	19.94	2.46
2400	12.87	18.56	9.88	16.28	1.06	0.86	34.43	20.14	2.53
2600	12.49	18.29	9.67	16.02	1.06	0.87	34.68	20.46	2.66
2800	12.14	18.02	9.51	15.88	1.05	0.88	34.77	20.45	2.73
3000	11.79	17.74	9.39	15.71	1.05	0.89	34.13	20.51	2.63
3200	11.46	17.46	9.33	15.57	1.05	0.89	34.18	20.35	2.76
3400	11.15	17.18	9.29	15.44	1.05	0.89	34.39	20.48	2.65
3600	10.85	16.89	9.31	15.28	1.05	0.89	34.46	20.56	2.82
3800	10.58	16.60	9.34	15.24	1.05	0.89	34.41	20.62	2.94
4000	10.32	16.30	9.41	15.21	1.05	0.89	34.10	20.49	2.90
4200	10.08	16.00	9.52	15.24	1.05	0.88	34.00	20.45	2.95
4400	9.86	15.68	9.66	15.07	1.04	0.87	33.90	20.41	3.00
4600	9.63	15.41	9.85	14.98	1.04	0.86	34.35	20.49	3.04
4800	9.44	15.08	10.00	14.89	1.04	0.85	33.85	20.32	3.08
5000	9.26	14.78	10.20	14.90	1.04	0.84	34.19	20.58	3.14
5200	9.09	14.47	10.40	14.85	1.03	0.82	33.65	20.28	3.11
5400	8.91	14.17	10.52	14.64	1.03	0.81	33.06	19.90	3.25
5600	8.74	13.90	10.49	14.54	1.02	0.80	33.84	20.25	3.23
5800	8.56	13.63	10.40	14.44	1.02	0.79	34.09	20.48	3.34
6000	8.40	13.36	10.12	14.11	1.01	0.78	33.45	20.26	3.38
6200	8.21	13.11	9.71	13.69	1.00	0.78	32.85	20.02	3.42
6400	7.99	12.92	9.14	13.09	0.99	0.78	33.12	20.03	3.56
6600	7.76	12.74	8.43	12.39	0.98	0.78	33.70	20.29	3.66
6800	7.49	12.62	7.79	11.59	0.97	0.78	33.06	20.07	3.80
7000	7.21	12.49	7.08	10.66	0.96	0.78	32.53	19.86	3.95



ISO 9001 ISO 14001 AS 9100 CERTIFIED

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

minicircuits.com



REV. OR

LHA-1H+

7/25/2016

Page 19 of 20

IF/RF MICROWAVE COMPONENTS

Monolithic Amplifier

LHA-1H+

Typical Performance Data

Definitions:

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 4.50V, Id = 122.20mA @ Temperature = +105°C

FREQ	Gain	Isolation	Input Return Loss	Output Return Loss	Stability		IP-3 Output	1dB Comp. Output	Noise Figure
(MHz)	(dB)	(dB)	(dB)	(dB)	K	Measure	(dBm)	(dBm)	(dB)
20	19.26	23.76	7.63	10.29	0.93	0.70	36.57	20.45	2.06
100	17.05	21.19	16.16	20.41	1.08	0.64	40.37	21.24	2.13
200	16.79	21.06	18.19	24.19	1.10	0.65	41.63	21.31	2.16
300	16.67	21.02	18.02	25.13	1.11	0.65	41.51	21.37	2.13
400	16.57	20.98	17.40	24.97	1.11	0.66	41.64	21.25	2.14
500	16.46	20.93	16.78	24.48	1.11	0.67	40.21	21.46	2.23
600	16.35	20.88	16.13	23.92	1.11	0.68	40.55	21.37	2.21
700	16.21	20.82	15.43	23.47	1.10	0.69	39.94	21.39	2.25
800	16.07	20.74	14.82	22.85	1.10	0.70	39.82	21.47	2.29
900	15.92	20.66	14.28	22.29	1.10	0.71	39.52	21.27	2.30
1000	15.76	20.58	13.75	21.77	1.10	0.73	38.92	21.53	2.40
1200	15.42	20.38	12.87	20.72	1.09	0.75	38.34	21.40	2.38
1400	15.05	20.17	12.16	19.85	1.09	0.77	38.48	21.39	2.46
1600	14.68	19.93	11.58	19.17	1.08	0.79	38.16	21.50	2.51
1800	14.30	19.68	11.12	18.64	1.08	0.81	37.86	21.61	2.54
2000	13.92	19.42	10.73	18.22	1.08	0.82	37.26	21.58	2.60
2200	13.54	19.17	10.42	17.84	1.08	0.84	36.55	21.30	2.60
2400	13.17	18.90	10.13	17.50	1.07	0.85	37.46	21.53	2.66
2600	12.80	18.63	9.89	17.15	1.07	0.87	37.76	21.93	2.76
2800	12.45	18.36	9.71	16.94	1.07	0.88	37.88	21.88	2.84
3000	12.11	18.08	9.57	16.68	1.07	0.88	37.03	21.96	2.78
3200	11.78	17.80	9.49	16.44	1.07	0.89	37.14	21.74	2.93
3400	11.46	17.52	9.43	16.20	1.07	0.89	37.35	21.90	2.85
3600	11.17	17.23	9.43	15.93	1.06	0.89	37.35	21.98	2.93
3800	10.88	16.94	9.45	15.79	1.06	0.89	37.30	22.06	3.11
4000	10.63	16.63	9.51	15.68	1.06	0.89	36.96	21.87	3.03
4200	10.38	16.33	9.60	15.61	1.06	0.88	36.84	21.80	3.17
4400	10.16	16.01	9.72	15.37	1.05	0.87	36.72	21.75	3.15
4600	9.93	15.73	9.90	15.22	1.05	0.86	37.25	21.85	3.21
4800	9.74	15.39	10.04	15.10	1.04	0.85	36.61	21.64	3.23
5000	9.56	15.08	10.23	15.11	1.04	0.84	36.91	21.97	3.28
5200	9.39	14.76	10.42	15.06	1.03	0.82	36.37	21.57	3.26
5400	9.22	14.45	10.53	14.92	1.03	0.81	35.69	21.12	3.46
5600	9.04	14.17	10.51	14.89	1.02	0.81	36.64	21.52	3.53
5800	8.87	13.89	10.41	14.90	1.02	0.80	36.85	21.78	3.54
6000	8.71	13.60	10.14	14.68	1.00	0.79	36.12	21.53	3.67
6200	8.53	13.34	9.73	14.38	0.99	0.78	35.42	21.24	3.64
6400	8.32	13.13	9.18	13.90	0.99	0.79	35.75	21.25	3.83
6600	8.10	12.93	8.46	13.25	0.97	0.79	36.51	21.56	3.95
6800	7.84	12.78	7.80	12.45	0.97	0.79	35.60	21.31	4.09
7000	7.56	12.63	7.08	11.48	0.95	0.80	35.11	21.09	4.23



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com



REV. OR

LHA-1H+









7/25/2016

Page 20 of 20


Monolithic Amplifier

LHA-1H+

Typical Performance Curves



 **Mini-Circuits®**
ISO 9001 ISO 14001 AS 9100 CERTIFIED

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site
 minicircuits.com

IF/RF MICROWAVE COMPONENTS










REV. OR
LHA-1H+
7/25/2016
Page 1 of 5

Monolithic Amplifier

LHA-1H+









Typical Performance Curves



Monolithic Amplifier

LHA-1H+

Typical Performance Curves



 **Mini-Circuits®**
ISO 9001 ISO 14001 AS 9100 CERTIFIED

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site
 The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

IF/RF MICROWAVE COMPONENTS







minicircuits.com

REV. OR
LHA-1H+
7/25/2016
Page 3 of 5

Monolithic Amplifier

LHA-1H+








Typical Performance Curves



Monolithic Amplifier

LHA-1H+

Typical Performance Curves




Case Style


FG

FG873

Outline Dimensions



PCB Land Pattern



Suggested Layout,
Tolerance to be within $\pm .002$

CASE #	A	B	C	D	E	F	G	H	J	K	L	M	N	P
FG873	.118 (3.00)	.118 (3.00)	.035 (0.89)	.008 (0.20)	.07 (1.78)	.024 (0.60)	.017 (0.43)	.018 (0.46)	.021 (0.52)	.024 (0.61)	.061 (1.55)	.186 (4.72)	.186 (4.72)	.032 (0.81)

CASE #	Q	R	S	T	WT. GRAM
FG873	.064 (1.63)	.032 (0.81)	.064 (1.63)	.050 (1.27)	.02

Dimensions are in inches (mm). Tolerances: 2 Pl. $\pm .01$; 3Pl. $\pm .004$

Notes:

1. Case material: Plastic.
2. Termination finish:

For RoHS Case Styles: Tin-Silver alloy plate over Nickel barrier or Matte-Tin per Data Sheet.

All models, (+) suffix.

For RoHS-5 Case Styles: Tin-Lead plate. All models, no (+) suffix.

 **Mini-Circuits®**
ISO 9001 ISO 14001 CERTIFIED

ALL NEW
minicircuits.com

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site




The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

RF/IF MICROWAVE COMPONENTS

Tape & Reel Packaging TR-F68

DEVICE ORIENTATION IN T&R



DIRECTION OF FEED



Tape Width, mm	Device Cavity Pitch, mm	Reel Size, inches	Devices per Reel see note	
12	8	7	Small quantity standard	20 50 100 200
			500	500
			Standard	1000
			Standard	2000
		13	Standard	3000
			Standard	4000

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: www.minicircuits.com/pages/pdfs/tape.pdf




Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Mini-Circuits ISO 9001 & ISO 14001 Certified


THIRD ANGLE PROJECTION



REVISIOnS

REV	ECN No.	DESCRIPTION	DATE	DR	AUTH
OR	M148938	NEW RELEASE	11/17/14	ITG	MM

SUGGESTED MOUNTING CONFIGURATION
FOR FG873 CASE STYLE, "04AM05" PIN CODE

NOTES:

1. TRACE WIDTH PARAMETERS ARE SHOWN FOR ROGERS R04350B WITH DIELECTRIC THICKNESS $.010'' \pm .001''$. COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.



DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER).



DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK.

UNLESS OTHERWISE SPECIFIED

DIMENSIONS ARE IN INCHES

TOLERANCES ON:

2 PL DECIMALS $\pm .005$ 3 PL DECIMALS $\pm .001$ ANGLES $\pm .5^\circ$ FRACTIONS $\pm .005$

INITIALS

DRAWN

CHECKED

APPROVED

DATE

ITG

GF

MM



Mini-Circuits®

13 Neptune Avenue
Brooklyn NY 11235

PL, 04AM05, FG873, TB-819+

SIZE CODE IDENT DRAWING NO. REV:


A 15542 98-PL-443 OR

FILE: 98PL443 SCALE: 16:1 SHEET: 1 OF 1


THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS.
EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE
AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY
DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO.
THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE
PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.

ASHEET1.DWG REV:A DATE:01/12/95

Evaluation Board and Circuit




TB-819-1H+



Schematic Diagram

COMPONENT	VALUE	SIZE
DUT	LHA-1H+	3X3 MM
C1	0.001 uF	
C2	1 nF	0805
D1	Zener Diode 5.6V ONSEMI MMSZ4690T1G	SOD123
R1	62 Ohm	0402
Q1	Transistor ONSEMI FET NTS4101P	SOT323
BIAS TEE	Mini-Circuits TCBT-14+	-



Stack-Up Diagram

NOTES:

1. Vs voltage: +5±0.2V.
2. SMA Female connectors.
3. PCB material: Rogers R04350 or equivalent,
dielectric constant=3.5,
Total Finished Thickness - .026"±10%.

Mini-Circuits®



Environmental Specifications

ENV08T1

All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-40° to 85° C or -45° to 85° C or -55° to 105° C or -40° to 105° C or -40° to 95° C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C or -65° to 150° Ambient Environment	Individual Model Data Sheet
HTOL	1000 hours at 125°C	MIL-STD-883, Method 1005, Condition B
Thermal Shock	-55° to 100°C, 100 cycles	MIL-STD-202, Method 107, Condition A-3, except +100°C
Mechanical Shock	1.5Kg, 0.5 ms, 5 shock pulses, Y1 direction only	MIL-STD-883, Method 2002, Condition B, except Y1 direction only
Vibration (Variable Frequency)	50g peak	MIL-STD-883, Method 2007, Condition B
Autoclave	15 psig, 100% RH, 121°C, 96 hours	JESD22-A102, Condition C
HAST	130°C, 85% RH, 96 hours	JESD22-A110
Solderability	10X Magnification	J-STD-002, Para 4.2.5, Test S, 95% Coverage
Solder Reflow Heat	Sn-Pb Eutetic Process: 240°C peak Pb-Free Process: 260°C peak	J-STD-020, Table 4-1, 4-2 and 5-2; Figure 5-1
Moisture Sensitivity: Level 1	Bake at 125°C for 24 hours Soak at 85°C/85% RH for 168 hours, Reflow 3 cycles at 260°C peak	J-STD-020



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Marking Resistance to Solvents	Isopropyl alcohol + mineral spirits at 25°C; terpene defluxer at 25°C; distilled water + propylene glycol monomethyl ether + monoethanolamine at 63°C to 70°C	MIL-STD-202, Method 215