



MMIC WIDEBAND, LOW NOISE


Monolithic Amplifier

PMA3-14LN+

50Ω 0.05 to 10 GHz

THE BIG DEAL

- Flat Gain, 22.6±0.75 dB Up to 10 GHz
- P1dB, +22 dBm Typ. vs. OIP3, +30.7 dBm Typ.
- Low Noise Figure, 1.1 dB Typ.
- Patent Pending



Generic photo used for illustration purposes only

CASE STYLE: DQ1225

+RoHS Compliant

The +Suffix identifies RoHS Compliance.
See our website for methodologies and qualifications

APPLICATIONS

- Wi-Fi
- WLAN
- LTE/WCDMA/EDGE
- L, S and C-Band Radar
- C-Band Satcom

PRODUCT OVERVIEW

The PMA3-14LN+ is a GaAs pHEMT based wideband, low noise MMIC amplifier with a unique combination of low noise, high OIP3, and high output power, over a wideband making it ideal for sensitive, high-dynamic range receiver applications. This design operates on a single supply of +6 V, is well matched for 50Ω and comes in a tiny, low profile package (3x3 mm-12 lead), accommodating dense circuit board layouts.

KEY FEATURES

Feature	Advantages
Low Noise, 1.1 dB Typical	Enables lower system noise figure performance.
High Dynamic Range • OIP3 +30.7 dBm Typ. • P1dB +22 dBm Typ.	The PMA3-14LN+ matches industry leading OIP3 performance relative to device size and power consumption. The combination of the design and pHEMT structure provides enhanced linearity over a board frequency range as evidence in the OIP3 being approximately 9-11 dB above the P1dB point. This feature makes this amplifier ideal for use in: • Driver Amplifiers for complex waveform upconverter paths • Drivers in linearized transmit systems • Secondary amplifiers in ultra-high dynamic range receivers
3x3 mm 12-Lead MCLP Package	Tiny footprint saves space in dense layouts while providing low inductance, repeatable transitions, and excellent thermal contact to the PCB.
Wide Bandwidth with Flat Gain, ±0.75 dB	Enables a single amplifier to be used in many wideband applications including defense, instrumentation and more.





MMIC WIDEBAND, LOW NOISE

Monolithic Amplifier

PMA3-14LN+

50Ω 0.05 to 10 GHz

ELECTRICAL SPECIFICATIONS¹ AT +25°C AND +6 V, UNLESS NOTED OTHERWISE

Parameter	Condition (MHz)	V _{DD} = +6 V			Units
		Min.	Typ.	Max.	
Frequency Range		50		10000	MHz
Gain	50	20.0	22.4	24.3	dB
	2000	20.0	22.6	24.4	
	4000	20.0	22.6	24.3	
	8000	20.3	23.1	24.9	
	10000		21.6		
Input Return Loss	50		20		dB
	2000		16		
	4000		14		
	8000		20		
	10000		13		
Output Return Loss	50		17		dB
	2000		20		
	4000		18		
	8000		16		
	10000		18		
P1dB	50		+22.0		dBm
	2000		+22.9		
	4000		+22.0		
	8000		+19.8		
	10000		+16.6		
OIP3 P _{OUT} = -5 dBm/Tone	50		+31.2		dBm
	2000		+31.8		
	4000		+30.7		
	8000		+28.7		
	10000		+26.0		
Low Noise Figure	50		1.8		dB
	2000		1.0		
	4000		1.1		
	8000		1.2		
	10000		2.1		
Device Operating Voltage		+5.75	+6	+6.25	V
Device Operating Current			67	90	mA
Device Current Variation vs. Temperature ²			-23.1		uA/°C
Device Current Variation vs. Voltage ³			0.0115		mA/mV
Thermal Resistance, Junction-to-Ground Lead, at +85°C Stage Temperature			53.9		°C/W

1. Measured on Mini-Circuits Characterization Test Board TB-PMA3-14LN+. See Characterization Test & Application Circuit (Fig. 1).

2. Device Current Variation vs. Temperature = (Current in mA at +85°C - Current in mA at -45°C)/+130°C

3. Device Current Variation vs. Voltage = (Current in mA at +6.25 V - Current in mA at +5.75 V) / ((+6.25 V - +5.75 V) * 1000 mA/mV)

ABSOLUTE MAXIMUM RATINGS⁴

Parameter	Ratings
Operating Temperature (Ground Lead)	-45°C to +85°C
Storage Temperature	-65°C to +150°C
Junction Temperature	+150°C
Total Power Dissipation	1.2 W
Input Power (CW)	+25 dBm (5 minutes max.) +12 dBm (continuous)
DC Voltage at V _{DD}	+8 V

4. Permanent damage may occur if any of those limits are exceeded. Electrical maximum ratings are not intended for continuous normal operation.






MMIC WIDEBAND, LOW NOISE

Monolithic Amplifier

PMA3-14LN+

50Ω 0.05 to 10 GHz

SIMPLIFIED SCHEMATIC & PAD DESCRIPTION



Function	Pad Number	Description (See Figure 1)
Current Mirror	1	Current Mirror Pad. Feedback to RF-IN via L1. See details in Figure 1.
RF-IN	2	RF Input Pad
RF-OUT & V _{DD}	8	RF Output Pad & DC Pad
NC	10	No connection to ground on test board. Pin 10 can be grounded similar to Pins 3-7, 9 & 11-12 or left open.
NC	3-7,9,11 & 12	No Connection, Grounded on Test Board
GND	Paddle, Index	Ground

CHARACTERIZATION TEST AND APPLICATION CIRCUIT




Fig 1. Application and Characterization Circuit

Note: This block diagram is used for characterization.


(DUT is soldered on Mini-Circuits Characterization test board TB-PMA3-14LN+) Gain, Return Loss, Output Power at 1 dB Compression (P_{1dB}), Output IP3 (OIP3) and Noise Figure measured using Agilent's N5242A PNA-X microwave network analyzer.

Conditions:

1. V_{DD} = +6 V
2. Gain and Return Loss: P_{IN} = -25 dBm
3. Output IP3 (OIP3): Two tones, spaced 1 MHz apart, -5 dBm/tone at output.

Component	Size	Value	Part Number	Manufacturer
C1 & C2	0402	0.01 uF	GRM155R71H103KA88D	Murata
C3	0402	0.2 pF	GJM1555C1HR20WB01D	Murata
C4	0402	0.1 pF	GJM1555C1HR10WB01D	Murata
C5 & C6	0402	100 pF	GRM1555C1H101JA01D	Murata
C7 & C8	0402	0.1 uF	GRM155R71H104KE14J	Murata
L1 & L2	0402	900 nH	0402DF-901XJRU	Coilcraft
R1	0402	510Ω	RK73H1ETTP5100F	KOA

PRODUCT MARKING



Marking may contain other features or characters for internal lot control.





MMIC WIDEBAND, LOW NOISE

Monolithic Amplifier

PMA3-14LN+

50Ω 0.05 to 10 GHz

ADDITIONAL DETAILED TECHNICAL INFORMATION IS AVAILABLE ON OUR DASHBOARD. TO ACCESS [CLICK HERE](#)

Performance Data	Data Table
	Swept Graphs
	S-Parameter (S2P Files) Data Set (.zip file)
Case Style	DQ1225 Plastic package, exposed paddle, Lead Finish: Matte Tin
Tape & Reel	F66
Standard Quantities Available on Reel	7" Reels with 20, 50, 100, 200, 500, 1000, 2000, or 3000 devices
Suggested Layout for PCB Design	PL-725
Evaluation Board	TB-PMA3-14LN+
Environmental Ratings	ENV08T1


ESD RATING

Human Body Model (HBM): Class 1B(500 V) in accordance with ANSI/ESD STM 5.1 - 2001

MSL RATING

Moisture Sensitivity: MSL1 in accordance with IPC/JEDEC J-STD-020D

MSL TEST FLOW CHART



NOTES

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the standard terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/terms/viewterm.html



*Typical Performance Data***Definitions:**

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 5.75V, Id = 64mA @ Temperature = +25°C

FREQ	Gain	Isolation	Input Return Loss	Output Return Loss	Stability		IP-3 Output	1dB Comp. Output	Noise Figure
(MHz)	(dB)	(dB)	(dB)	(dB)	K	Measure	(dBm)	(dBm)	(dB)
10	20.46	27.17	9.18	14.25	1.15	0.87	25.43	19.41	8.92
100	22.20	25.13	22.46	21.95	1.05	0.50	30.65	22.45	1.37
200	22.28	25.07	23.42	23.85	1.04	0.48	28.68	22.50	1.06
300	22.29	25.08	23.27	24.74	1.05	0.49	29.17	22.55	1.02
400	22.29	25.15	22.98	25.12	1.05	0.50	27.58	22.54	0.97
500	22.29	25.19	22.58	25.57	1.05	0.50	29.99	22.55	0.96
1000	22.28	25.22	19.66	27.67	1.05	0.52	29.94	22.67	0.94
1200	22.28	25.25	18.42	27.51	1.05	0.52	31.22	22.78	0.96
1400	22.27	25.35	17.29	26.20	1.06	0.54	29.62	22.80	0.91
1600	22.26	25.42	16.20	24.55	1.06	0.55	29.97	22.83	0.94
1800	22.25	25.45	15.30	22.84	1.06	0.55	31.54	22.80	0.96
2000	22.23	25.55	14.44	21.32	1.06	0.57	32.31	22.68	0.97
2200	22.21	25.62	13.69	20.06	1.07	0.58	33.26	22.75	0.93
2400	22.18	25.67	13.06	19.05	1.07	0.58	29.73	22.78	1.07
2600	22.17	25.86	12.58	18.29	1.08	0.60	28.43	22.65	0.98
2800	22.16	25.88	12.19	17.80	1.08	0.61	30.87	22.38	1.05
3000	22.16	25.94	11.94	17.47	1.08	0.62	29.72	22.10	0.99
3200	22.16	26.04	11.74	17.30	1.08	0.63	28.81	21.77	1.06
3400	22.16	26.12	11.63	17.22	1.09	0.64	28.42	21.40	1.04
3600	22.16	26.20	11.60	17.21	1.09	0.64	28.39	21.13	1.06
3800	22.18	26.24	11.60	17.36	1.09	0.65	28.66	21.56	1.05
4000	22.20	26.27	11.70	17.64	1.09	0.65	29.25	21.51	1.16
4200	22.22	26.35	11.87	18.05	1.10	0.66	30.11	21.70	1.14
4400	22.24	26.42	12.10	18.50	1.10	0.67	28.80	21.74	1.19
4600	22.27	26.45	12.36	19.04	1.10	0.67	29.16	21.61	1.14
4800	22.32	26.55	12.67	19.61	1.11	0.68	29.37	21.83	1.19
5000	22.37	26.55	13.02	20.26	1.11	0.68	30.08	21.69	1.21
5200	22.43	26.66	13.44	20.86	1.12	0.69	28.61	21.57	1.22
5400	22.48	26.67	13.87	21.44	1.12	0.68	29.58	21.33	1.27
5600	22.55	26.67	14.42	21.98	1.12	0.68	28.42	21.15	1.23
5800	22.61	26.80	15.06	22.61	1.12	0.69	29.99	21.12	1.22
6000	22.66	26.85	15.80	23.09	1.13	0.69	28.20	21.28	1.22
6200	22.73	26.92	16.75	23.01	1.13	0.69	28.94	21.09	1.10
6400	22.77	26.98	17.74	22.66	1.14	0.69	29.82	21.04	1.20
6600	22.81	27.06	19.02	21.83	1.15	0.69	30.01	21.24	1.14
6800	22.86	27.19	20.71	20.64	1.16	0.70	29.50	21.05	1.15
7000	22.91	27.25	22.82	19.57	1.16	0.70	28.62	20.90	1.17
7200	22.94	27.35	24.91	18.68	1.17	0.70	29.79	20.90	1.14
7400	22.94	27.41	26.72	17.99	1.18	0.70	28.14	20.60	1.16
7600	22.93	27.57	26.69	17.33	1.20	0.71	30.13	20.20	1.15
7800	22.92	27.73	25.02	16.70	1.22	0.72	28.81	20.10	1.19
8000	22.89	27.96	23.01	16.34	1.25	0.74	29.42	19.59	1.23
8200	22.84	28.11	20.99	16.14	1.27	0.75	28.14	19.10	1.23
8400	22.78	28.34	19.42	16.02	1.30	0.77	28.40	18.78	1.23
8600	22.70	28.59	18.18	16.27	1.34	0.79	27.50	18.22	1.25
8800	22.59	28.83	17.09	16.71	1.39	0.82	27.89	18.12	1.33
9000	22.46	29.19	16.24	17.37	1.45	0.84	28.51	18.14	1.45
9200	22.31	29.42	15.50	18.23	1.51	0.87	28.63	17.44	1.59
9400	22.13	29.81	14.75	19.22	1.60	0.89	27.39	17.01	1.65
9600	21.89	30.15	14.06	20.07	1.69	0.92	28.06	16.83	1.83
9800	21.59	30.58	13.41	20.21	1.80	0.94	26.04	16.17	2.00
10000	21.25	31.03	12.70	19.46	1.94	0.96	27.73	16.12	2.14

*Typical Performance Data***Definitions:**

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 6.00V, Id = 73mA @ Temperature = +25°C

FREQ	Gain	Isolation	Input Return Loss	Output Return Loss	Stability		IP-3 Output	1dB Comp. Output	Noise Figure
(MHz)	(dB)	(dB)	(dB)	(dB)	K	Measure	(dBm)	(dBm)	(dB)
10	20.89	27.66	9.92	14.72	1.16	0.87	24.88	19.95	8.89
100	22.53	25.52	26.78	19.12	1.05	0.49	32.71	22.79	1.40
200	22.61	25.47	28.52	20.23	1.05	0.48	32.00	22.83	1.07
300	22.62	25.39	28.32	20.81	1.04	0.47	28.43	22.87	1.00
400	22.62	25.46	27.58	21.06	1.05	0.49	30.39	22.86	0.96
500	22.62	25.45	26.99	21.32	1.05	0.49	30.91	22.87	0.96
1000	22.63	25.58	22.54	23.32	1.05	0.51	33.73	22.92	0.90
1200	22.63	25.59	20.87	24.16	1.05	0.52	33.97	23.00	0.92
1400	22.63	25.62	19.43	24.41	1.06	0.52	30.98	23.00	0.89
1600	22.62	25.68	18.05	24.10	1.06	0.54	32.38	22.95	0.94
1800	22.61	25.75	16.93	23.22	1.06	0.55	31.99	22.92	0.98
2000	22.60	25.84	15.88	22.03	1.06	0.56	33.50	22.86	0.96
2200	22.59	25.88	14.99	20.91	1.06	0.57	32.07	22.94	1.00
2400	22.57	25.97	14.25	19.87	1.07	0.58	28.97	22.79	0.99
2600	22.55	26.10	13.68	19.10	1.07	0.59	29.22	22.50	0.97
2800	22.55	26.16	13.24	18.54	1.07	0.60	31.43	22.36	1.03
3000	22.54	26.25	12.94	18.14	1.08	0.61	31.52	21.92	0.99
3200	22.54	26.29	12.70	17.92	1.08	0.61	29.87	21.69	1.06
3400	22.54	26.34	12.57	17.77	1.08	0.62	30.20	21.49	1.04
3600	22.53	26.47	12.53	17.70	1.09	0.63	31.03	21.37	1.03
3800	22.54	26.52	12.52	17.77	1.09	0.64	29.60	21.90	1.11
4000	22.55	26.60	12.64	17.97	1.09	0.65	31.64	21.79	1.13
4200	22.56	26.64	12.81	18.27	1.10	0.66	30.33	21.91	1.08
4400	22.57	26.66	13.07	18.59	1.10	0.66	30.28	21.97	1.14
4600	22.60	26.76	13.34	19.01	1.11	0.67	30.77	21.83	1.15
4800	22.63	26.76	13.69	19.35	1.11	0.67	30.89	22.05	1.21
5000	22.68	26.87	14.07	19.72	1.11	0.68	29.24	21.93	1.16
5200	22.72	26.91	14.51	20.03	1.11	0.68	29.97	21.86	1.23
5400	22.77	26.95	14.99	20.26	1.12	0.68	29.29	21.62	1.16
5600	22.82	26.99	15.59	20.43	1.12	0.68	29.23	21.43	1.22
5800	22.87	27.12	16.29	20.59	1.13	0.69	28.08	21.43	1.19
6000	22.91	27.15	17.12	20.67	1.13	0.69	28.84	21.59	1.16
6200	22.96	27.21	18.22	20.40	1.14	0.69	29.49	21.42	1.13
6400	23.00	27.29	19.35	20.07	1.14	0.69	28.29	21.37	1.15
6600	23.03	27.33	20.91	19.43	1.15	0.69	31.02	21.56	1.20
6800	23.07	27.42	23.06	18.62	1.16	0.69	31.03	21.38	1.14
7000	23.10	27.52	26.02	17.86	1.17	0.69	28.56	21.24	1.09
7200	23.13	27.58	29.47	17.22	1.17	0.69	29.56	21.23	1.14
7400	23.12	27.73	32.61	16.76	1.19	0.70	28.31	20.95	1.17
7600	23.10	27.88	30.41	16.31	1.21	0.71	30.40	20.55	1.11
7800	23.08	28.05	26.39	15.83	1.23	0.72	28.20	20.47	1.21
8000	23.05	28.21	23.62	15.56	1.25	0.74	29.02	19.97	1.19
8200	23.00	28.41	21.35	15.43	1.28	0.75	27.16	19.46	1.17
8400	22.94	28.65	19.60	15.34	1.32	0.77	27.01	19.14	1.20
8600	22.85	28.86	18.37	15.61	1.35	0.79	27.92	18.58	1.24
8800	22.75	29.19	17.29	16.02	1.41	0.82	27.46	18.48	1.36
9000	22.63	29.47	16.42	16.61	1.47	0.84	27.06	18.51	1.41
9200	22.49	29.74	15.72	17.39	1.53	0.86	26.86	17.80	1.56
9400	22.31	30.04	14.99	18.35	1.60	0.89	26.79	17.37	1.73
9600	22.09	30.44	14.31	19.15	1.70	0.91	27.46	17.19	1.83
9800	21.81	30.88	13.66	19.56	1.82	0.94	25.57	16.53	1.92
10000	21.48	31.29	12.98	19.18	1.95	0.96	26.56	16.48	2.13

Typical Performance Data

Definitions:

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 6.25V, Id = 82mA @ Temperature = +25°C

FREQ	Gain	Isolation	Input Return Loss	Output Return Loss	Stability		IP-3 Output	1dB Comp. Output	Noise Figure
(MHz)	(dB)	(dB)	(dB)	(dB)	K	Measure	(dBm)	(dBm)	(dB)
10	21.19	27.68	10.44	14.65	1.14	0.86	29.15	20.47	8.86
100	22.77	25.75	31.56	17.49	1.05	0.48	32.57	23.19	1.39
200	22.84	25.71	34.55	18.33	1.05	0.47	29.47	23.25	1.04
300	22.85	25.68	34.35	18.78	1.04	0.47	30.81	23.28	1.01
400	22.86	25.67	33.07	19.02	1.04	0.47	31.73	23.27	0.99
500	22.86	25.68	32.09	19.15	1.05	0.48	30.72	23.27	0.93
1000	22.87	25.77	25.40	20.85	1.05	0.50	35.34	23.30	0.92
1200	22.88	25.81	23.22	21.68	1.05	0.51	32.63	23.34	0.95
1400	22.88	25.86	21.35	22.22	1.06	0.52	32.51	23.32	0.92
1600	22.88	25.94	19.69	22.43	1.06	0.53	30.94	23.26	0.92
1800	22.87	25.97	18.33	22.16	1.06	0.54	30.77	23.24	0.94
2000	22.87	26.03	17.14	21.55	1.06	0.55	31.18	23.18	0.97
2200	22.85	26.15	16.10	20.74	1.07	0.56	34.08	23.28	0.97
2400	22.84	26.20	15.24	19.89	1.07	0.57	31.38	23.04	1.00
2600	22.82	26.25	14.61	19.16	1.07	0.58	29.96	22.77	0.97
2800	22.82	26.34	14.08	18.63	1.07	0.59	29.95	22.70	1.03
3000	22.81	26.40	13.73	18.20	1.07	0.60	30.20	22.28	1.01
3200	22.81	26.49	13.48	17.98	1.08	0.61	31.69	22.12	0.99
3400	22.80	26.55	13.33	17.78	1.08	0.61	30.03	22.05	1.06
3600	22.79	26.60	13.27	17.66	1.08	0.62	30.66	22.03	1.05
3800	22.80	26.67	13.27	17.68	1.09	0.63	30.11	22.49	1.11
4000	22.80	26.76	13.38	17.79	1.09	0.64	31.10	22.43	1.09
4200	22.81	26.85	13.54	18.00	1.10	0.65	31.04	22.55	1.11
4400	22.81	26.86	13.83	18.20	1.10	0.65	29.49	22.49	1.13
4600	22.83	26.92	14.11	18.47	1.10	0.66	29.56	22.34	1.12
4800	22.86	26.98	14.47	18.69	1.11	0.66	30.55	22.51	1.20
5000	22.89	27.07	14.88	18.89	1.11	0.67	30.80	22.34	1.17
5200	22.94	27.10	15.35	19.01	1.11	0.67	29.21	22.27	1.15
5400	22.97	27.18	15.86	19.08	1.12	0.68	29.97	21.98	1.17
5600	23.02	27.21	16.51	19.10	1.12	0.68	29.46	21.77	1.22
5800	23.06	27.28	17.26	19.12	1.12	0.68	29.21	21.77	1.18
6000	23.10	27.31	18.16	19.10	1.13	0.68	30.09	21.90	1.16
6200	23.14	27.38	19.31	18.79	1.13	0.68	29.37	21.74	1.12
6400	23.17	27.50	20.56	18.54	1.14	0.69	29.64	21.70	1.13
6600	23.19	27.61	22.28	18.03	1.15	0.69	29.02	21.88	1.19
6800	23.22	27.65	24.93	17.40	1.16	0.69	30.14	21.72	1.21
7000	23.26	27.78	28.78	16.77	1.17	0.69	27.84	21.59	1.11
7200	23.27	27.81	34.48	16.29	1.18	0.69	28.84	21.59	1.16
7400	23.26	27.91	40.72	15.94	1.19	0.70	28.92	21.34	1.07
7600	23.24	28.03	31.93	15.58	1.21	0.71	28.65	20.95	1.16
7800	23.22	28.25	26.68	15.21	1.23	0.72	29.03	20.87	1.17
8000	23.18	28.46	23.63	15.00	1.26	0.74	27.72	20.39	1.17
8200	23.12	28.62	21.35	14.94	1.29	0.75	27.41	19.86	1.18
8400	23.07	28.91	19.63	14.85	1.33	0.77	28.00	19.54	1.24
8600	22.99	29.11	18.42	15.10	1.37	0.79	27.38	18.94	1.35
8800	22.89	29.30	17.36	15.49	1.41	0.81	27.06	18.86	1.33
9000	22.78	29.65	16.51	16.06	1.47	0.84	26.56	18.91	1.49
9200	22.64	29.89	15.84	16.76	1.53	0.86	26.75	18.18	1.59
9400	22.47	30.20	15.13	17.61	1.60	0.88	26.77	17.75	1.75
9600	22.26	30.61	14.45	18.36	1.70	0.91	25.97	17.57	1.87
9800	21.99	31.02	13.82	18.81	1.81	0.93	25.38	16.90	1.99
10000	21.68	31.37	13.16	18.63	1.93	0.95	25.97	16.87	2.10

*Typical Performance Data***Definitions:**

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 5.75V, Id = 73mA @ Temperature = -45°C

FREQ	Gain	Isolation	Input Return Loss	Output Return Loss	Stability		IP-3 Output	1dB Comp. Output	Noise Figure
(MHz)	(dB)	(dB)	(dB)	(dB)	K	Measure	(dBm)	(dBm)	(dB)
10	21.43	27.97	10.37	14.21	1.13	0.86	27.48	18.56	8.41
100	23.03	26.02	31.19	15.66	1.04	0.47	29.11	21.26	0.93
200	23.14	25.83	34.00	16.68	1.04	0.44	32.57	21.28	0.71
300	23.17	25.90	35.38	17.12	1.04	0.45	33.38	21.29	0.70
400	23.18	25.71	34.52	17.25	1.03	0.43	32.67	21.30	0.69
500	23.17	25.82	34.35	17.39	1.04	0.45	27.90	21.32	0.67
1000	23.20	25.90	28.31	18.87	1.04	0.47	31.67	21.32	0.72
1200	23.21	25.95	25.68	19.83	1.04	0.48	32.24	21.31	0.68
1400	23.22	25.99	23.52	20.82	1.05	0.49	32.21	21.26	0.56
1600	23.23	25.96	21.39	21.67	1.04	0.49	29.78	21.08	0.58
1800	23.24	26.06	19.77	22.21	1.05	0.50	33.22	21.03	0.60
2000	23.24	26.11	18.38	22.02	1.05	0.51	35.44	20.94	0.64
2200	23.23	26.13	17.24	21.39	1.05	0.52	30.29	20.98	0.60
2400	23.22	26.21	16.43	20.56	1.05	0.53	30.60	20.71	0.67
2600	23.22	26.28	15.82	19.80	1.05	0.54	31.11	20.31	0.65
2800	23.23	26.34	15.32	19.25	1.05	0.54	30.14	20.18	0.61
3000	23.23	26.39	14.95	18.68	1.06	0.55	30.50	19.67	0.63
3200	23.24	26.48	14.68	18.41	1.06	0.56	30.60	19.29	0.69
3400	23.24	26.54	14.58	18.16	1.06	0.56	30.34	18.96	0.61
3600	23.25	26.58	14.46	17.96	1.06	0.57	28.39	18.84	0.68
3800	23.25	26.67	14.43	17.85	1.06	0.58	29.35	19.51	0.68
4000	23.27	26.74	14.49	17.82	1.07	0.59	30.75	19.38	0.74
4200	23.27	26.77	14.65	17.98	1.07	0.59	29.50	19.56	0.74
4400	23.28	26.78	14.96	18.08	1.07	0.59	30.51	19.56	0.74
4600	23.30	26.91	15.27	18.24	1.07	0.61	28.36	19.67	0.74
4800	23.34	26.95	15.59	18.28	1.07	0.61	29.10	20.10	0.78
5000	23.39	26.99	15.92	18.37	1.07	0.61	28.24	20.12	0.74
5200	23.43	27.02	16.41	18.31	1.07	0.61	28.37	20.46	0.74
5400	23.49	27.13	16.79	18.27	1.08	0.62	28.47	20.16	0.76
5600	23.54	27.14	17.29	18.16	1.07	0.62	27.89	20.07	0.79
5800	23.59	27.21	17.87	17.97	1.08	0.62	28.58	20.31	0.75
6000	23.65	27.21	18.44	17.66	1.07	0.62	28.50	20.59	0.79
6200	23.72	27.28	19.26	17.13	1.07	0.62	28.50	20.31	0.62
6400	23.77	27.31	19.84	16.79	1.07	0.61	28.52	20.22	0.64
6600	23.81	27.39	20.93	16.25	1.08	0.62	28.77	20.44	0.68
6800	23.85	27.47	22.13	15.51	1.08	0.61	27.62	20.15	0.66
7000	23.90	27.51	23.20	14.76	1.08	0.60	28.66	19.96	0.71
7200	23.95	27.61	23.62	14.10	1.08	0.60	26.90	19.97	0.66
7400	23.97	27.72	23.70	13.57	1.09	0.60	28.00	19.74	0.64
7600	23.99	27.82	23.16	13.03	1.10	0.60	26.92	19.41	0.65
7800	24.04	27.98	21.81	12.46	1.11	0.60	27.76	19.40	0.65
8000	24.06	28.02	20.78	12.14	1.11	0.60	27.44	19.03	0.65
8200	24.05	28.19	20.42	12.13	1.13	0.61	26.78	18.63	0.63
8400	24.07	28.29	19.69	12.01	1.14	0.62	26.52	18.45	0.70
8600	24.09	28.36	19.16	12.13	1.15	0.62	26.06	18.00	0.74
8800	24.11	28.54	18.43	12.21	1.16	0.64	26.50	17.99	0.76
9000	24.10	28.73	17.86	12.39	1.19	0.66	26.44	18.12	0.80
9200	24.10	28.91	17.22	12.61	1.21	0.68	25.95	17.51	0.94
9400	24.09	29.19	16.66	12.84	1.24	0.70	26.09	17.14	0.99
9600	24.05	29.50	16.26	13.17	1.27	0.73	25.45	16.98	1.06
9800	23.98	29.72	15.85	13.62	1.31	0.76	24.21	16.34	1.17
10000	23.89	29.93	15.24	14.19	1.35	0.78	24.86	16.26	1.32

Typical Performance Data

Definitions:

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 6.00V, Id = 81mA Temperature = -45°C

FREQ	Gain	Isolation	Input Return Loss	Output Return Loss	Stability		IP-3 Output	1dB Comp. Output	Noise Figure
(MHz)	(dB)	(dB)	(dB)	(dB)	K	Measure	(dBm)	(dBm)	(dB)
10	21.68	28.13	10.89	13.85	1.12	0.85	26.60	19.21	8.37
100	23.24	26.29	31.41	14.54	1.04	0.47	29.94	21.92	0.99
200	23.35	26.09	31.05	15.43	1.03	0.44	32.75	21.95	0.76
300	23.38	26.08	31.58	15.79	1.04	0.44	33.31	21.95	0.72
400	23.38	26.04	31.48	15.89	1.03	0.43	28.26	21.96	0.67
500	23.39	26.09	31.60	16.00	1.04	0.44	32.15	21.97	0.65
1000	23.41	26.16	31.16	17.25	1.04	0.46	31.53	21.94	0.62
1200	23.43	26.17	28.82	18.06	1.04	0.47	36.84	21.91	0.66
1400	23.45	26.18	26.28	18.90	1.04	0.48	31.09	21.84	0.56
1600	23.46	26.22	23.61	19.71	1.04	0.48	32.96	21.67	0.58
1800	23.47	26.27	21.66	20.34	1.05	0.50	32.68	21.61	0.67
2000	23.47	26.32	19.96	20.53	1.05	0.50	30.55	21.54	0.59
2200	23.47	26.39	18.63	20.35	1.05	0.52	30.33	21.62	0.64
2400	23.46	26.44	17.63	19.78	1.05	0.52	30.10	21.31	0.69
2600	23.46	26.52	16.94	19.26	1.05	0.53	29.77	20.98	0.61
2800	23.47	26.56	16.37	18.83	1.05	0.54	31.23	20.86	0.69
3000	23.46	26.63	15.93	18.30	1.06	0.54	29.21	20.42	0.70
3200	23.47	26.65	15.64	18.06	1.06	0.55	31.91	20.18	0.66
3400	23.47	26.72	15.48	17.79	1.06	0.55	30.13	19.99	0.68
3600	23.47	26.78	15.35	17.59	1.06	0.56	30.41	19.99	0.65
3800	23.48	26.88	15.31	17.41	1.06	0.57	29.90	20.53	0.73
4000	23.48	26.92	15.35	17.34	1.06	0.58	31.53	20.46	0.72
4200	23.48	26.98	15.52	17.42	1.07	0.59	29.13	20.66	0.72
4400	23.48	27.00	15.85	17.38	1.07	0.59	30.16	20.62	0.70
4600	23.50	27.05	16.21	17.44	1.07	0.60	28.10	20.69	0.72
4800	23.53	27.15	16.50	17.40	1.07	0.61	30.12	21.09	0.75
5000	23.57	27.20	16.89	17.42	1.07	0.61	29.46	21.04	0.73
5200	23.61	27.27	17.43	17.27	1.07	0.61	29.46	21.31	0.73
5400	23.66	27.24	17.79	17.18	1.07	0.61	29.24	20.98	0.75
5600	23.70	27.33	18.31	17.04	1.07	0.62	28.36	20.76	0.84
5800	23.74	27.40	18.89	16.83	1.07	0.62	28.73	20.93	0.77
6000	23.80	27.35	19.46	16.53	1.07	0.61	28.69	21.15	0.71
6200	23.86	27.43	20.21	16.09	1.07	0.61	28.24	20.83	0.60
6400	23.91	27.53	20.70	15.79	1.07	0.62	29.29	20.69	0.68
6600	23.93	27.58	21.63	15.36	1.08	0.61	27.95	20.90	0.67
6800	23.97	27.66	22.50	14.75	1.08	0.61	27.66	20.60	0.68
7000	24.01	27.75	23.09	14.07	1.08	0.61	29.86	20.41	0.64
7200	24.05	27.80	22.88	13.53	1.09	0.60	27.81	20.39	0.64
7400	24.07	27.88	22.48	13.05	1.09	0.60	28.00	20.17	0.62
7600	24.08	28.01	21.76	12.59	1.10	0.60	27.27	19.85	0.66
7800	24.12	28.13	20.44	12.06	1.11	0.60	28.73	19.83	0.71
8000	24.14	28.22	19.61	11.81	1.11	0.60	25.98	19.48	0.68
8200	24.12	28.28	19.31	11.83	1.13	0.61	27.06	19.08	0.66
8400	24.14	28.50	18.68	11.73	1.14	0.62	26.17	18.89	0.68
8600	24.16	28.53	18.27	11.87	1.15	0.63	25.99	18.44	0.64
8800	24.17	28.76	17.62	11.97	1.17	0.65	26.32	18.44	0.75
9000	24.16	28.94	17.17	12.17	1.19	0.67	25.88	18.58	0.84
9200	24.16	29.12	16.59	12.39	1.22	0.68	24.94	17.96	0.90
9400	24.14	29.33	16.09	12.64	1.24	0.71	24.80	17.61	0.96
9600	24.10	29.66	15.74	12.97	1.28	0.74	24.89	17.46	1.11
9800	24.02	29.83	15.38	13.40	1.31	0.76	24.34	16.80	1.16
10000	23.93	30.14	14.83	14.02	1.36	0.79	24.17	16.74	1.34

Typical Performance Data

Definitions:

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 6.25V, Id = 89mA @ Temperature = -45°C

FREQ	Gain	Isolation	Input Return Loss	Output Return Loss	Stability		IP-3 Output	1dB Comp. Output	Noise Figure
(MHz)	(dB)	(dB)	(dB)	(dB)	K	Measure	(dBm)	(dBm)	(dB)
10	21.87	27.96	11.20	13.62	1.10	0.83	26.74	19.86	8.39
100	23.40	26.43	29.08	13.82	1.04	0.46	31.35	22.54	0.95
200	23.51	26.32	27.69	14.56	1.04	0.44	30.27	22.55	0.76
300	23.53	26.25	27.89	14.89	1.03	0.43	32.28	22.56	0.68
400	23.55	26.21	27.90	15.00	1.03	0.43	32.74	22.57	0.68
500	23.54	26.25	28.09	15.07	1.04	0.43	32.89	22.60	0.67
1000	23.58	26.30	30.50	16.19	1.04	0.45	35.24	22.56	0.67
1200	23.60	26.33	30.31	16.93	1.04	0.46	30.96	22.52	0.63
1400	23.61	26.36	28.31	17.68	1.04	0.47	35.63	22.44	0.57
1600	23.63	26.40	25.42	18.47	1.04	0.48	32.49	22.27	0.62
1800	23.64	26.43	23.23	19.13	1.05	0.49	30.76	22.24	0.65
2000	23.65	26.45	21.25	19.45	1.05	0.49	33.32	22.20	0.60
2200	23.65	26.54	19.76	19.43	1.05	0.51	30.89	22.27	0.64
2400	23.64	26.58	18.67	19.01	1.05	0.51	31.79	21.93	0.59
2600	23.64	26.64	17.88	18.64	1.05	0.52	29.92	21.60	0.59
2800	23.64	26.72	17.24	18.24	1.05	0.53	35.14	21.54	0.66
3000	23.64	26.76	16.75	17.77	1.05	0.54	31.62	21.16	0.59
3200	23.65	26.77	16.42	17.56	1.05	0.54	30.69	21.00	0.64
3400	23.65	26.86	16.23	17.27	1.06	0.55	30.72	20.88	0.67
3600	23.64	26.88	16.10	17.07	1.06	0.55	30.72	20.93	0.62
3800	23.64	26.97	16.03	16.90	1.06	0.56	29.10	21.41	0.68
4000	23.65	27.05	16.07	16.77	1.06	0.57	30.31	21.39	0.72
4200	23.64	27.12	16.27	16.80	1.07	0.58	29.51	21.61	0.72
4400	23.64	27.21	16.59	16.72	1.07	0.59	29.83	21.59	0.68
4600	23.65	27.19	16.96	16.72	1.07	0.59	29.99	21.61	0.73
4800	23.68	27.29	17.27	16.64	1.07	0.60	29.30	21.94	0.80
5000	23.71	27.33	17.65	16.58	1.07	0.60	29.02	21.86	0.74
5200	23.75	27.38	18.19	16.44	1.07	0.61	28.60	22.06	0.76
5400	23.79	27.40	18.56	16.34	1.07	0.61	29.00	21.68	0.77
5600	23.83	27.43	19.07	16.19	1.07	0.61	29.01	21.40	0.83
5800	23.87	27.51	19.60	15.98	1.07	0.61	28.28	21.54	0.74
6000	23.92	27.56	20.16	15.73	1.07	0.61	27.41	21.68	0.73
6200	23.97	27.63	20.82	15.32	1.07	0.61	28.28	21.36	0.76
6400	24.02	27.67	21.25	15.10	1.07	0.61	27.91	21.19	0.65
6600	24.04	27.70	22.05	14.71	1.07	0.61	28.63	21.36	0.71
6800	24.07	27.79	22.69	14.17	1.08	0.61	27.50	21.05	0.68
7000	24.11	27.89	22.89	13.59	1.08	0.61	28.29	20.84	0.72
7200	24.14	27.96	22.41	13.10	1.09	0.60	27.17	20.81	0.68
7400	24.15	27.99	21.80	12.70	1.09	0.60	28.11	20.59	0.69
7600	24.15	28.13	20.99	12.29	1.10	0.60	27.45	20.26	0.63
7800	24.19	28.31	19.76	11.82	1.11	0.60	26.51	20.25	0.69
8000	24.21	28.34	18.94	11.59	1.12	0.60	26.88	19.89	0.69
8200	24.18	28.40	18.66	11.62	1.13	0.61	25.99	19.49	0.67
8400	24.20	28.61	18.08	11.55	1.15	0.62	26.12	19.30	0.63
8600	24.21	28.67	17.69	11.71	1.16	0.63	25.60	18.84	0.72
8800	24.22	28.82	17.09	11.81	1.17	0.64	26.22	18.85	0.76
9000	24.21	29.10	16.69	12.04	1.20	0.67	25.43	19.00	0.79
9200	24.20	29.32	16.15	12.24	1.22	0.69	24.70	18.39	0.93
9400	24.18	29.57	15.67	12.48	1.25	0.72	24.74	18.04	0.98
9600	24.14	29.79	15.33	12.82	1.29	0.74	24.42	17.88	1.08
9800	24.06	30.08	15.01	13.25	1.33	0.77	23.08	17.24	1.24
10000	23.96	30.27	14.48	13.82	1.37	0.79	23.58	17.17	1.35

Typical Performance Data

Definitions:

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 5.75V, Id = 60mA @ Temperature = +85°C

FREQ	Gain	Isolation	Input Return Loss	Output Return Loss	Stability		IP-3 Output	1dB Comp. Output	Noise Figure
(MHz)	(dB)	(dB)	(dB)	(dB)	K	Measure	(dBm)	(dBm)	(dB)
10	19.99	26.69	8.62	13.26	1.14	0.86	24.80	18.03	9.37
100	21.73	24.58	18.36	26.72	1.04	0.50	28.73	21.34	1.81
200	21.78	24.52	18.81	31.01	1.04	0.49	31.82	21.54	1.45
300	21.79	24.55	18.67	33.59	1.04	0.49	30.85	21.71	1.39
400	21.79	24.62	18.33	35.38	1.05	0.50	31.77	21.74	1.27
500	21.79	24.59	18.07	35.87	1.05	0.50	31.64	21.76	1.30
1000	21.76	24.71	16.10	28.03	1.05	0.53	30.00	21.72	1.26
1200	21.74	24.78	15.27	25.06	1.05	0.54	30.33	21.65	1.28
1400	21.72	24.87	14.50	22.77	1.06	0.55	29.20	21.61	1.19
1600	21.70	24.97	13.76	20.87	1.06	0.56	29.33	21.41	1.29
1800	21.67	25.03	13.13	19.39	1.07	0.57	28.69	21.38	1.29
2000	21.66	25.13	12.55	18.14	1.07	0.58	28.65	21.37	1.35
2200	21.63	25.24	12.01	17.11	1.07	0.59	30.66	21.49	1.38
2400	21.61	25.34	11.57	16.34	1.08	0.60	30.46	21.27	1.26
2600	21.59	25.42	11.24	15.75	1.08	0.61	27.92	20.95	1.36
2800	21.58	25.50	10.99	15.37	1.08	0.62	28.39	20.86	1.36
3000	21.58	25.60	10.83	15.15	1.09	0.63	27.60	20.26	1.37
3200	21.59	25.69	10.72	15.06	1.09	0.64	28.49	19.94	1.43
3400	21.60	25.75	10.72	15.09	1.09	0.64	28.19	19.60	1.44
3600	21.61	25.82	10.77	15.22	1.10	0.65	28.26	19.35	1.43
3800	21.64	25.89	10.85	15.50	1.10	0.66	28.74	20.00	1.52
4000	21.67	25.92	11.00	15.90	1.10	0.66	27.78	19.71	1.51
4200	21.69	25.99	11.18	16.43	1.11	0.67	29.01	19.71	1.59
4400	21.72	26.06	11.40	17.00	1.11	0.68	27.37	19.69	1.51
4600	21.75	26.16	11.56	17.65	1.12	0.69	26.92	19.62	1.55
4800	21.80	26.22	11.73	18.28	1.12	0.70	28.39	20.00	1.59
5000	21.84	26.27	11.89	19.01	1.13	0.71	28.56	20.01	1.58
5200	21.89	26.32	12.06	19.76	1.13	0.71	28.64	20.13	1.59
5400	21.94	26.37	12.24	20.50	1.13	0.72	28.05	20.04	1.68
5600	21.99	26.48	12.48	21.32	1.14	0.73	27.39	20.00	1.64
5800	22.04	26.49	12.78	22.43	1.14	0.73	27.54	20.12	1.65
6000	22.09	26.63	13.15	23.68	1.15	0.74	28.53	20.25	1.63
6200	22.15	26.67	13.67	25.08	1.16	0.74	29.09	20.18	1.59
6400	22.19	26.79	14.17	26.49	1.17	0.75	28.72	20.22	1.59
6600	22.21	26.91	14.82	27.60	1.18	0.75	29.06	20.34	1.63
6800	22.25	26.97	15.60	27.32	1.19	0.76	29.16	20.26	1.62
7000	22.28	27.16	16.51	26.58	1.22	0.77	28.93	20.19	1.65
7200	22.28	27.30	17.24	25.52	1.24	0.78	29.47	20.21	1.66
7400	22.26	27.46	17.88	24.77	1.26	0.79	29.89	20.06	1.74
7600	22.24	27.62	18.16	24.30	1.29	0.80	28.67	19.83	1.69
7800	22.25	27.85	18.17	23.86	1.32	0.81	29.16	19.77	1.74
8000	22.28	27.94	17.98	23.60	1.34	0.82	29.36	19.41	1.68
8200	22.23	28.11	17.68	22.96	1.38	0.83	29.85	18.97	1.67
8400	22.22	28.39	16.77	23.18	1.42	0.85	29.22	18.70	1.72
8600	22.24	28.51	15.71	23.57	1.44	0.86	29.14	18.24	1.68
8800	22.15	28.69	14.90	23.54	1.48	0.88	28.81	18.16	1.75
9000	21.99	28.99	14.29	23.72	1.54	0.90	29.60	18.11	1.88
9200	21.79	29.28	13.64	23.59	1.61	0.92	28.55	17.35	1.93
9400	21.56	29.59	12.84	22.77	1.68	0.94	30.81	16.95	2.05
9600	21.26	29.96	12.06	20.99	1.77	0.96	28.40	16.69	2.21
9800	20.89	30.39	11.26	18.65	1.88	0.98	27.82	16.03	2.35
10000	20.45	30.97	10.41	16.47	2.03	1.00	27.88	16.00	2.57

Typical Performance Data

Definitions:

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 6.00V, Id = 67mA @ Temperature = +85°C

FREQ	Gain	Isolation	Input Return Loss	Output Return Loss	Stability		IP-3 Output	1dB Comp. Output	Noise Figure
(MHz)	(dB)	(dB)	(dB)	(dB)	K	Measure	(dBm)	(dBm)	(dB)
10	20.38	27.05	9.21	13.86	1.15	0.86	25.43	18.44	9.33
100	22.04	24.88	20.60	23.55	1.04	0.49	30.13	21.67	1.78
200	22.10	24.83	21.22	25.66	1.04	0.48	30.19	21.87	1.46
300	22.10	24.77	21.02	26.86	1.04	0.48	30.77	22.02	1.35
400	22.10	24.86	20.61	27.75	1.04	0.49	30.56	22.07	1.27
500	22.10	24.91	20.21	28.57	1.05	0.50	30.16	22.09	1.26
1000	22.08	25.02	17.72	31.05	1.05	0.52	31.69	22.00	1.24
1200	22.07	25.05	16.71	28.45	1.05	0.53	31.84	21.89	1.27
1400	22.06	25.10	15.80	25.62	1.06	0.54	30.72	21.83	1.18
1600	22.05	25.20	14.92	23.21	1.06	0.55	29.54	21.61	1.30
1800	22.02	25.28	14.22	21.29	1.06	0.56	30.85	21.60	1.28
2000	22.01	25.38	13.53	19.74	1.07	0.57	30.35	21.61	1.29
2200	21.99	25.46	12.92	18.48	1.07	0.58	29.92	21.73	1.30
2400	21.97	25.58	12.42	17.53	1.08	0.59	28.62	21.40	1.29
2600	21.95	25.69	12.05	16.80	1.08	0.60	29.63	21.01	1.35
2800	21.94	25.72	11.76	16.32	1.08	0.61	29.41	20.99	1.37
3000	21.93	25.84	11.58	16.01	1.09	0.62	29.73	20.40	1.37
3200	21.94	25.88	11.47	15.86	1.09	0.62	29.44	20.21	1.37
3400	21.95	26.00	11.46	15.82	1.09	0.64	28.54	20.05	1.43
3600	21.96	26.05	11.50	15.90	1.10	0.64	28.87	19.94	1.44
3800	21.98	26.13	11.58	16.11	1.10	0.65	29.82	20.57	1.47
4000	22.00	26.21	11.74	16.45	1.10	0.66	28.03	20.31	1.50
4200	22.02	26.19	11.95	16.92	1.10	0.66	29.58	20.32	1.50
4400	22.04	26.28	12.17	17.40	1.11	0.68	28.02	20.30	1.51
4600	22.06	26.38	12.34	18.00	1.12	0.69	29.87	20.15	1.54
4800	22.10	26.43	12.52	18.57	1.12	0.69	28.85	20.49	1.57
5000	22.14	26.50	12.68	19.17	1.12	0.70	28.50	20.47	1.55
5200	22.18	26.56	12.86	19.82	1.13	0.71	29.38	20.56	1.59
5400	22.22	26.64	13.05	20.41	1.13	0.71	28.65	20.43	1.60
5600	22.26	26.68	13.31	21.05	1.14	0.72	28.78	20.34	1.62
5800	22.30	26.78	13.64	21.84	1.15	0.72	29.51	20.45	1.65
6000	22.34	26.85	14.06	22.72	1.15	0.73	29.16	20.54	1.64
6200	22.39	26.96	14.61	23.37	1.16	0.74	30.40	20.49	1.59
6400	22.41	27.09	15.17	24.04	1.18	0.74	30.25	20.53	1.57
6600	22.43	27.14	15.89	24.21	1.19	0.75	30.02	20.64	1.61
6800	22.45	27.26	16.79	23.74	1.20	0.75	29.30	20.58	1.61
7000	22.47	27.44	17.78	23.22	1.23	0.76	29.11	20.52	1.61
7200	22.46	27.52	18.62	22.63	1.24	0.77	28.97	20.54	1.66
7400	22.44	27.77	19.33	22.23	1.28	0.79	31.01	20.41	1.71
7600	22.41	27.92	19.58	22.04	1.31	0.80	29.32	20.18	1.71
7800	22.42	28.06	19.49	21.86	1.33	0.81	31.51	20.14	1.78
8000	22.45	28.22	19.14	21.70	1.36	0.82	30.43	19.83	1.69
8200	22.39	28.48	18.66	21.33	1.41	0.84	28.74	19.41	1.71
8400	22.39	28.66	17.49	21.63	1.44	0.85	29.69	19.18	1.71
8600	22.41	28.76	16.25	22.03	1.45	0.86	28.08	18.74	1.69
8800	22.31	29.00	15.34	22.02	1.50	0.88	29.87	18.66	1.70
9000	22.16	29.38	14.64	22.24	1.57	0.90	29.64	18.62	1.82
9200	21.97	29.61	13.95	22.34	1.64	0.92	28.58	17.84	1.97
9400	21.75	29.92	13.13	22.01	1.71	0.94	29.29	17.44	2.07
9600	21.46	30.28	12.32	20.72	1.80	0.96	28.72	17.18	2.23
9800	21.11	30.63	11.52	18.73	1.90	0.98	27.34	16.51	2.33
10000	20.69	31.12	10.67	16.68	2.03	0.99	28.18	16.49	2.52

Typical Performance Data

Definitions:

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)









Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)








TEST CONDITIONS: Vd = 6.25V, Id = 75mA @ Temperature = +85°C

FREQ	Gain	Isolation	Input Return Loss	Output Return Loss	Stability		IP-3 Output	1dB Comp. Output	Noise Figure
(MHz)	(dB)	(dB)	(dB)	(dB)	K	Measure	(dBm)	(dBm)	(dB)
10	20.68	26.96	9.63	14.19	1.12	0.84	25.28	18.79	9.29
100	22.29	25.10	23.01	21.20	1.04	0.48	29.55	21.98	1.84
200	22.35	25.12	23.80	22.47	1.04	0.48	30.16	22.18	1.48
300	22.35	25.06	23.49	23.19	1.04	0.48	30.79	22.32	1.30
400	22.35	25.13	22.95	23.80	1.04	0.49	29.96	22.37	1.27
500	22.35	25.08	22.44	24.34	1.04	0.49	30.28	22.39	1.30
1000	22.34	25.25	19.28	28.13	1.05	0.52	30.66	22.28	1.27
1200	22.33	25.28	18.07	28.36	1.05	0.53	31.06	22.16	1.26
1400	22.32	25.35	17.03	26.72	1.06	0.54	33.02	22.10	1.18
1600	22.31	25.43	16.02	24.54	1.06	0.55	31.62	21.86	1.29
1800	22.29	25.53	15.18	22.54	1.06	0.56	31.24	21.86	1.28
2000	22.28	25.58	14.42	20.86	1.07	0.57	31.03	21.89	1.23
2200	22.26	25.67	13.75	19.44	1.07	0.58	32.01	22.01	1.27
2400	22.25	25.75	13.18	18.33	1.07	0.59	30.07	21.66	1.29
2600	22.23	25.87	12.77	17.53	1.08	0.60	29.83	21.28	1.30
2800	22.22	25.92	12.44	16.96	1.08	0.60	31.20	21.29	1.40
3000	22.21	25.99	12.23	16.55	1.08	0.61	32.76	20.76	1.34
3200	22.22	26.09	12.11	16.34	1.09	0.62	29.31	20.65	1.37
3400	22.22	26.15	12.08	16.23	1.09	0.63	30.23	20.62	1.39
3600	22.22	26.22	12.13	16.24	1.09	0.64	28.89	20.60	1.42
3800	22.24	26.27	12.21	16.37	1.09	0.64	29.57	21.13	1.45
4000	22.26	26.36	12.39	16.63	1.10	0.65	29.45	20.92	1.49
4200	22.27	26.46	12.59	17.01	1.11	0.66	29.37	20.92	1.53
4400	22.28	26.47	12.83	17.41	1.11	0.67	28.08	20.86	1.47
4600	22.31	26.51	13.02	17.87	1.11	0.68	29.08	20.69	1.53
4800	22.34	26.61	13.20	18.37	1.12	0.69	29.90	20.96	1.52
5000	22.37	26.69	13.36	18.83	1.12	0.69	30.19	20.90	1.59
5200	22.40	26.74	13.53	19.34	1.13	0.70	30.06	20.96	1.54
5400	22.43	26.80	13.74	19.76	1.13	0.70	30.65	20.79	1.57
5600	22.47	26.91	14.01	20.24	1.14	0.71	28.92	20.65	1.65
5800	22.51	27.00	14.36	20.75	1.15	0.72	30.82	20.75	1.68
6000	22.54	27.09	14.78	21.34	1.16	0.73	28.84	20.80	1.61
6200	22.58	27.14	15.39	21.67	1.16	0.73	29.36	20.76	1.54
6400	22.59	27.25	16.00	21.93	1.18	0.74	29.95	20.81	1.56
6600	22.60	27.41	16.79	21.98	1.20	0.75	30.19	20.91	1.57
6800	22.61	27.49	17.80	21.61	1.21	0.75	28.92	20.86	1.61
7000	22.63	27.65	18.91	21.20	1.23	0.76	29.54	20.82	1.65
7200	22.61	27.78	19.85	20.80	1.25	0.77	28.27	20.84	1.67
7400	22.58	27.98	20.66	20.63	1.29	0.78	29.64	20.74	1.63
7600	22.55	28.16	20.89	20.54	1.32	0.80	28.69	20.50	1.73
7800	22.57	28.36	20.66	20.47	1.35	0.81	29.31	20.47	1.75
8000	22.59	28.45	20.16	20.36	1.37	0.82	28.60	20.21	1.75
8200	22.52	28.74	19.47	20.12	1.42	0.83	28.13	19.84	1.69
8400	22.54	28.89	18.06	20.55	1.45	0.85	28.41	19.64	1.76
8600	22.56	29.01	16.67	20.86	1.47	0.86	28.34	19.23	1.65
8800	22.46	29.26	15.66	20.89	1.52	0.88	28.53	19.14	1.74
9000	22.31	29.57	14.89	21.13	1.58	0.90	28.52	19.12	1.80
9200	22.13	29.84	14.18	21.30	1.65	0.91	26.87	18.36	1.96
9400	21.92	30.07	13.34	21.17	1.71	0.93	27.33	17.95	2.10
9600	21.64	30.46	12.51	20.27	1.80	0.95	27.04	17.70	2.21
9800	21.30	30.82	11.71	18.56	1.90	0.97	27.46	17.00	2.38
10000	20.89	31.21	10.84	16.70	2.01	0.99	26.75	17.01	2.47


Typical Performance Curves




Typical Performance Curves



Outline Dimensions



PCB Land Pattern



SUGGESTED LAYOUT,
TOLERANCE TO BE WITHIN ± 0.002

Weight: .02 Grams

Dimensions are in inches (mm). Tolerances: 2Pl. $\pm .01$; 3 Pl. $\pm .004$

Notes:

- Case material: Plastic.
- Termination finish:
 - For RoHS Case Styles: Tin-Silver alloy plate over Nickel barrier or Matte-Tin. All models, (+) suffix. See Data sheet.
 - For RoHS-5 Case Styles: Tin-Lead plate. All models, no (+) suffix.




INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified

Tape & Reel Packaging TR-F66



Tape Width, mm	Device Cavity Pitch, mm	Reel Size, inches	Devices per Reel see note	
8	4	7	Small quantity standard	20
				50
				100
				200
				500
		7	Standard	1000, 2000, 3000

Note: Please consult individual model data sheet to determine device per reel availability.


Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: www.minicircuits.com/pages/pdfs/tape.pdf



INTERNET <http://www.minicircuits.com>
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661
Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010
Mini-Circuits ISO 9001 & ISO 14001 Certified

THIRD ANGLE PROJECTION




REVISIONS

REV	ECN No.	DESCRIPTION	DATE	DR	AUTH
OR	ECO-011385	NEW RELEASE	01/14/22	ITG	IL
A	ECO-018630	ADDED INDEX PIN	07/24/23	ITG	CT
B	ECO-019376	ADDED KEEP-OUT ZONE	09/29/23	ITG	IL

SUGGESTED MOUNTING CONFIGURATION FOR DQ1225 CASE STYLE


KEEP-OUT ZONE, .030X.030,
AVOID TRACES IN THIS AREA
TO PREVENT SHORT TO METAL
INDEX ON BOTTOM SIDE OF
COMPONENT



3 LAYER STACK-UP DIAGRAM

COMPONENT	SIZE
C1...C8	0402
L1,L2	0402
R1	0402


.090"±.002"
[2.30±0.05]mm



SOLDER MASK (SM1)
IMMERSION GOLD (0.025um-0.075um)
ELECTROLESS NICKEL (3um-6um)
L1 COPPER: 0.5 OZ (0.7mil)
BASE: RO4350B (10mil)
L2 COPPER: 0.5 OZ (0.7mil)
BASE: FR4 (2.0mm)
L3 COPPER: 0.5 OZ (0.7mil)
ELECTROLESS NICKEL (3um-6um)
IMMERSION GOLD (0.025um-0.075um)
SOLDER MASK (SM2)

NOTES:

1. PCB IS MULTILAYER PCB, SEE STACK-UP DIAGRAM.
2. TRACE WIDTH & GAP PARAMETERS ARE SHOWN FOR ROGERS RO4350B WITH DIELECTRIC THICKNESS .010"±.001"; COPPER: 1/2 OZ. FOR OTHER MATERIALS TRACE WIDTH AND GAP MAY NEED TO BE MODIFIED.
3. CHIP COMPONENT FOOT PRINTS SHOWN FOR REFERENCE. FOR COMPONENT VALUES REFER TO TB-PMA3-14LN+ OR TB-TSS-14LN+.
4. COPPER LAYERS L2 & L3 OF THE PCB ARE CONTINUOUS GROUND PLANES.



DENOTES PCB COPPER LAYOUT WITH SMOBC
(SOLDER MASK OVER BARE COPPER)

DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

UNLESS OTHERWISE SPECIFIED

DIMENSIONS ARE IN INCHES

TOLERANCES ON:
2 PL DECIMALS ±
3 PL DECIMALS ± .005
ANGLES ±
FRACTIONS ±

INITIALS

DATE

DRAWN

ITG

01/13/22

CHECKED

GF

01/13/22

APPROVED

IL

01/13/22



Mini-Circuits®

13 Neptune Avenue
Brooklyn NY 11235

PL, DQ1225, TB-PMA3(TSS)-14LN+

SIZE

A

CODE IDENT

15542

DRAWING NO:

98-PL-725

REV:

B

FILE:

98PL725

SCALE:

8:1

SHEET:





1 OF 1

Mini-Circuits®

THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.

ASHEETA1.DWG REV:A DATE:01/12/95


Evaluation Board and Circuit



COMPONENTS	SIZE	VALUE	MANUFACTURER	PART NUMBER
C1,C2,C9,C10	0402	0.01 μ F	Murata	GRM155R71H103KA88D
C3		0.2 pF		GJM1555C1HR20WB01D
C4		0.1 pF		GJM1555C1HR10WB01D
C5,C6		100 pF		GRM1555C1H101JA01D
C7,C8		0.1 μ F		GRM155R71H104KE14J
L1,L2		900 nH	Coilcraft	0402DF-901XJRU
R1		510 Ω	KOA Speer	RK73H1ETTP5100F

Notes:

1. 50 Ohm SMA Female Connectors.
2. PCB Material: Roger R04350B or equivalent,
Dielectric constant=3.5, Thickness=0.010 inch





All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-40° to 85° C or -45° to 85° C or -55° to 105° C or -40° to 105° C or -40° to 95° C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C or -65° to 150° Ambient Environment	Individual Model Data Sheet
HTOL	1000 hours at 125°C	MIL-STD-883, Method 1005, Condition B
Thermal Shock	-55° to 100°C, 100 cycles	MIL-STD-202, Method 107, Condition A-3, except +100°C
Mechanical Shock	1.5Kg, 0.5 ms, 5 shock pulses, Y1 direction only	MIL-STD-883, Method 2002, Condition B, except Y1 direction only
Vibration (Variable Frequency)	50g peak	MIL-STD-883, Method 2007, Condition B
Autoclave	15 psig, 100% RH, 121°C, 96 hours	JESD22-A102, Condition C
HAST	130°C, 85% RH, 96 hours	JESD22-A110
Solderability	10X Magnification	J-STD-002, Para 4.2.5, Test S, 95% Coverage
Solder Reflow Heat	Sn-Pb Eutetic Process: 240°C peak Pb-Free Process: 260°C peak	J-STD-020, Table 4-1, 4-2 and 5-2; Figure 5-1
Moisture Sensitivity: Level 1	Bake at 125°C for 24 hours Soak at 85°C/85% RH for 168 hours, Reflow 3 cycles at 260°C peak	J-STD-020



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Marking Resistance to Solvents	Isopropyl alcohol + mineral spirits at 25°C; terpene defluxer at 25°C; distilled water + proylene glycol monomethyl ether + monoethanolamine at 63°C to 70°C	MIL-STD-202, Method 215