



MMIC SURFACE MOUNT

# Low Noise Amplifier


## PMA3-14LV+

Mini-Circuits

50Ω 0.05 to 10 GHz Wideband Amplifier

### THE BIG DEAL

- Low Noise Figure, Typ. 1.1 dB
- High OIP3, Typ. +29.1 dBm
- High P1dB, Typ. +19.8 dBm
- Single Supply Voltage, +5 V at 59 mA
- 3x3 mm 12-Lead QFN-Style Package




Generic photo used for illustration purposes only

### APPLICATIONS

- Test and Measurement Equipment
- 5G MIMO and Back Haul Radio
- Satellite Communication
- Radar, EW, and ECM Defense Systems

### FUNCTIONAL DIAGRAM



### PRODUCT OVERVIEW

The PMA3-14LV+ is a GaAs pHEMT-based low noise MMIC amplifier with high IP3 and flat gain. Operating from 0.05 to 10 GHz, this amplifier features high dynamic range with typical 1.1 dB noise figure, 22.0 dB gain, +19.8 dBm P1dB, and +29.1 dBm OIP3. This combination of performance makes it ideal for sensitive high dynamic range receiver applications. PMA3-14LV+ operates from a single +5 V supply, is well matched to 50Ω, and comes in a very small, low profile 3x3 mm QFN-style package for easy integration into dense circuit board layouts.

### KEY FEATURES

Feature	Advantages
Low Noise Figure, Typ. 1.1 dB	A 50Ω matched low noise MMIC device enables low system noise figure performance without the need for complicated discrete-based solutions.
Low Power Consumption, Typ. +5 V at 59 mA	At only 59 mA, this amplifier is ideal for applications with limited available power or densely packed applications where thermal and power management is critical.
3x3 mm 12-Lead QFN-Style Package	Very small footprint saves space in dense PCB layouts while providing low inductance, repeatable transitions, and excellent thermal contact with the PCB. Industry standard packaging allows for easy assembly in high volume manufacturing processes.





MMIC SURFACE MOUNT

## Low Noise Amplifier

PMA3-14LV+

Mini-Circuits

50Ω 0.05 to 10 GHz Wideband Amplifier

ELECTRICAL SPECIFICATIONS<sup>1</sup> AT +25°C, V<sub>DD</sub> = +5 V, Z<sub>0</sub> = 50Ω, UNLESS NOTED OTHERWISE

Parameter	Condition (GHz)	Min.	Typ.	Max.	Units
Frequency Range		0.05		10	GHz
Gain	0.05	19.9	21.8		dB
	2	20.4	22.0		
	4	20.4	22.0		
	8	20.9	23.3		
	10	18.1	21.5		
Input Return Loss	0.05		19		dB
	2		15		
	4		12		
	8		21		
	10		10		
Output Return Loss	0.05		21		dB
	2		19		
	4		14		
	8		14		
	10		11		
Isolation	0.05-10		25		dB
Output Power at 1 dB Compression (P1dB)	0.05		+19.3		dBm
	2		+21.1		
	4		+19.8		
	8		+18.3		
	10		+15.5		
Output Third-Order Intercept (P <sub>OUT</sub> = -5 dBm/Tone)	0.05		+27.4		dBm
	2		+30.0		
	4		+29.1		
	8		+27.8		
	10		+26.4		
Noise Figure	0.05		1.6		dB
	2		1.0		
	4		1.1		
	8		1.3		
	10		2.3		
Device Operating Voltage (V <sub>DD</sub> )		+4.75	+5.0	+5.25	V
Device Operating Current (I <sub>DD</sub> ) <sup>2</sup>			59		mA
DC Current Variation vs. Temperature <sup>3</sup>			-16.7		μA/°C
DC Current Variation vs. Voltage <sup>4</sup>			0.028		mA/mV

1. Tested on Mini-Circuits Characterization Test Board TB-PMA3-14LVC+. See Figure 2. Board loss de-embedded to the device.

2. Current at P<sub>IN</sub> = -25 dBm. Increases to 80 mA at P1dB.







3. (Current at +105°C - Current at -45°C) / (+105°C - -45°C)

4. (Current at +5.25 V - Current at +4.75 V) / (+5.25 V - +4.75 V)






### TYPICAL PERFORMANCE GRAPHS






### TYPICAL PERFORMANCE GRAPHS


ISOLATION vs. TEMPERATURE,  
 $P_{IN} = -25 \text{ dBm}$ ,  $V_{DD} = +5 \text{ V}$




ISOLATION vs. VOLTAGE,  
TEMPERATURE = +25°C




P1dB vs. TEMPERATURE,  
 $V_{DD} = +5 \text{ V}$




P1dB vs. VOLTAGE,  
TEMPERATURE = +25°C



OUTPUT IP3 vs. TEMPERATURE,  
 $P_{OUT} = -5 \text{ dBm/TONE}$ ,  $V_{DD} = +5 \text{ V}$






OUTPUT IP3 vs. VOLTAGE,  
 $P_{OUT} = -5 \text{ dBm/TONE}$ , TEMPERATURE = +25°C





### TYPICAL PERFORMANCE GRAPHS





MMIC SURFACE MOUNT

# Low Noise Amplifier

## PMA3-14LV+

Mini-Circuits

50Ω 0.05 to 10 GHz Wideband Amplifier

### ABSOLUTE MAXIMUM RATINGS<sup>5</sup>

Parameter	Ratings
Operating Temperature	-45°C to +105°C
Storage Temperature	-65°C to +150°C
Junction Temperature <sup>6</sup>	+150°C
Total Power Dissipation	0.83 W
Input Power (CW), $V_{DD} = +5 V$	+25 dBm
DC Voltage at RF-OUT & $V_{DD}$	+8 V
DC Current $I_{DD}$	130 mA

5. Permanent damage may occur if any of these limits are exceeded. Maximum ratings are not intended for continuous normal operation.

6. Peak temperature on top of Die.

### THERMAL RESISTANCE

Parameter	Ratings
Thermal Resistance ( $\Theta_{JC}$ ) <sup>7</sup>	53.9°C/W

7.  $\Theta_{JC}$  = (Hot Spot Temperature on Die - Temperature at Ground Lead) / Dissipated Power

### ESD RATING

	Class	Voltage Range	Reference Standard
HBM	1B	500 V to < 1000 V	ANSI/ESD STM 5.1 - 2001
CDM	C3	≥ 1000 V	ANSI/ESDA/JEDEC JS-002-2022



ESD HANDLING PRECAUTION: This device is designed to be Class 1B for HBM. Static charges may easily produce potentials higher than this with improper handling and can discharge into DUT and damage it. As a preventive measure Industry standard ESD handling precautions should be used at all times to protect the device from ESD damage.

### MSL RATING

Moisture Sensitivity: MSL1 in accordance with IPC/JEDEC J-STD-020D /JEDEC J-STD-033C





### FUNCTIONAL DIAGRAM




Figure 1. PMA3-14LV+ Functional Diagram

### PAD DESCRIPTION

Function	Pad Number	Description (Refer to Figure 2)
RF-IN	2	RF-IN Pad connects to RF Input port.
RF-OUT & V <sub>DD</sub>	8	RF-OUT Pad connects to RF Output port. V <sub>DD</sub> is applied via external bias tee.
CURRENT MIRROR <sup>8</sup>	1	Current Mirror Pad. Supplies gate voltage to RF-IN via L1. See details in Figure 2.
NC	3-7, 9, 11-12	Connects to ground on the test board.
NC	10	No connection to ground on the test board. Pin 10 can be grounded similar to Pins 3-7, 9 & 11-12 or left open.
GND	PADDLE & INDEX	Connects to ground.

8. To achieve the specified performance, follow the current mirror circuit described in Figure 2. For the part to operate, a DC feedback loop to RF-IN must be present.

### CHARACTERIZATION TEST BOARD




Figure 2. PMA3-14LV+ Characterization and Application Circuit

#### Electrical Parameters and Conditions

Gain, Return Loss, Output Power at 1 dB Compression (P1dB), Output IP3 (OIP3), and Noise Figure measured using N5242A PNA-X microwave network analyzer.

#### Conditions:

1. Gain and Return Loss: P<sub>IN</sub> = -25 dBm
2. Output IP3 (OIP3): Two tones, spaced 1 MHz apart, +5 dBm/Tone at output.
3. V<sub>DD</sub> = +5 V

Component	Value	Size	Part Number	Manufacturer
C1, C2	0.01 μF	0402	GRM155R71H103KA88D	Murata
C3	0.2 pF	0402	GJM1555C1HR20WB01D	Murata
C4	0.1 pF	0402	GJM1555C1HR10WB01D	Murata
C5, C6	100 pF	0402	GRM1555C1H101JA01D	Murata
C7, C8	0.1 μF	0402	GRM155R71H104KE14J	Murata
L1, L2	900 nH	0402	0402DF-901XJRU	Coilcraft
R1	5.6k Ω	0402	RK73H1ETTP5601F	KOA Speer



MMIC SURFACE MOUNT

# Low Noise Amplifier



## PMA3-14LV+

Mini-Circuits

50Ω 0.05 to 10 GHz Wideband Amplifier

### CASE STYLE DRAWING

### PCB Land Pattern




SUGGESTED LAYOUT,  
TOLERANCE TO BE WITHIN ±.002

Weight: .02 Grams

Dimensions are in inches [mm]. Tolerances in inches: 2 Pl. ±.01; 3 Pl. ±.004 inches

### PRODUCT MARKING



Marking may contain other features or characters for internal lot control.



MMIC SURFACE MOUNT

# Low Noise Amplifier

## PMA3-14LV+

Mini-Circuits

50Ω 0.05 to 10 GHz Wideband Amplifier

ADDITIONAL DETAILED INFORMATION IS AVAILABLE ON OUR DASHBOARD [CLICK HERE](#)

Performance Data & Graphs	Data
	Graphs
	S-Parameter (S2P Files) Data Set (.zip file)
Case Style	DQ1225 Plastic package, exposed paddle, Lead Finish: Matte-Tin
RoHs Status	Compliant
Tape & Reel	F66
Standard Quantities Available on Reel	7" Reels with 20, 50, 100, 200, 500, 1000, 2000, or 3000 devices
Suggested Layout for PCB Design	PL-820
Evaluation Board	TB-PMA3-14LVC+
	Gerber File
Environmental Ratings	ENV08T1

### NOTES

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the standard terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/terms/viewterm.html](http://www.minicircuits.com/terms/viewterm.html)



## Typical Performance Data

### Definitions:

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS:  $V_{DD} = +4.75\text{ V}$ ,  $I_{DD} = 47\text{ mA}$  @ Temperature = +25°C

FREQ	Gain	Isolation	Input Return Loss	Output Return Loss	Stability		Noise Figure	FREQ	IP-3 Output		1dB Comp. Output
					K	Measure			POUT = 0 dBm/Tone	POUT = +5 dBm/Tone	
(GHz)	(dB)	(dB)	(dB)	(dB)	K	Measure	(dB)	(GHz)	(dBm)	(dBm)	(dBm)
0.05	20.9	24.4	14.8	22.7	1.05	0.58	1.76	0.01	25.2	26.6	15.9
0.1	21.1	24.2	16.0	26.2	1.04	0.52	1.33	0.05	28.3	29.0	19.1
0.3	21.2	24.0	16.5	29.7	1.04	0.50	1.08	0.10	28.5	28.9	20.3
0.5	21.2	24.1	16.3	29.3	1.04	0.50	1.03	0.40	28.8	29.1	20.6
0.7	21.2	24.1	16.0	27.7	1.05	0.51	1.08	0.50	29.6	30.2	20.8
1.0	21.1	24.2	15.3	25.4	1.05	0.53	0.99	1.00	28.3	28.6	21.3
1.2	21.1	24.3	14.9	23.8	1.06	0.54	1.10	1.50	29.0	29.4	20.9
1.4	21.1	24.3	14.4	22.5	1.06	0.55	1.12	2.00	28.5	28.9	21.1
1.6	21.1	24.4	13.8	21.1	1.06	0.56	1.07	2.50	27.6	27.9	21.3
1.8	21.0	24.5	13.3	20.0	1.07	0.57	1.08	3.00	27.5	27.6	20.7
2.0	21.0	24.6	12.8	18.9	1.07	0.58	1.01	3.50	27.1	27.0	20.4
2.2	21.0	24.7	12.3	18.0	1.07	0.59	1.01	4.00	26.2	25.9	20.1
2.4	20.9	24.8	11.9	17.4	1.08	0.60	1.06	4.50	25.9	25.5	20.5
2.6	20.9	24.9	11.5	16.7	1.08	0.61	1.09	5.00	25.2	24.7	20.1
2.8	20.9	24.9	11.2	16.3	1.08	0.62	1.13	5.50	26.3	25.9	19.3
3.0	20.9	25.0	10.9	15.9	1.09	0.63	1.12	6.00	25.9	25.6	19.4
3.2	20.9	25.1	10.7	15.6	1.09	0.64	1.07	6.50	27.1	26.8	19.2
3.4	20.9	25.2	10.5	15.4	1.09	0.65	1.12	7.00	27.9	27.6	19.1
3.6	20.9	25.3	10.4	15.4	1.10	0.65	1.15	7.50	28.5	28.1	18.8
3.8	20.9	25.3	10.4	15.4	1.10	0.66	1.15	8.00	28.2	28.0	18.2
4.0	20.9	25.4	10.4	15.6	1.10	0.67	1.21	8.50	28.8	28.4	17.2
4.2	21.0	25.5	10.5	16.0	1.11	0.68	1.19	9.00	28.1	28.0	16.1
4.4	21.0	25.5	10.7	16.5	1.11	0.69	1.20	9.50	28.2	28.1	15.6
4.6	21.0	25.6	10.9	17.2	1.11	0.69	1.18	10.00	27.7	28.2	14.7
4.8	21.1	25.6	11.2	18.1	1.12	0.70	1.20				
5.0	21.2	25.7	11.5	19.2	1.12	0.70	1.22				
5.2	21.2	25.7	11.8	20.8	1.12	0.70	1.25				
5.4	21.3	25.8	12.3	22.6	1.12	0.71	1.21				
5.6	21.4	25.8	12.8	25.5	1.12	0.71	1.21				
5.8	21.5	25.8	13.5	31.4	1.13	0.71	1.23				
6.0	21.6	25.9	14.2	34.9	1.13	0.70	1.21				
6.2	21.7	25.9	15.1	33.0	1.13	0.70	1.23				
6.4	21.8	26.0	16.2	28.8	1.13	0.70	1.21				
6.6	21.9	26.1	17.5	24.5	1.14	0.70	1.20				
6.8	21.9	26.1	19.1	21.7	1.14	0.69	1.17				
7.0	22.0	26.2	21.0	19.7	1.15	0.69	1.21				
7.2	22.0	26.3	22.9	18.1	1.16	0.69	1.25				
7.4	22.0	26.4	24.5	17.1	1.17	0.70	1.25				
7.6	22.0	26.6	24.7	16.4	1.18	0.70	1.30				
7.8	22.0	26.8	23.5	15.9	1.20	0.72	1.34				
8.0	22.0	26.9	21.9	15.7	1.22	0.73	1.37				
8.2	21.9	27.1	20.3	15.6	1.24	0.75	1.42				
8.4	21.8	27.4	18.9	15.9	1.28	0.77	1.50				
8.6	21.7	27.6	17.9	16.4	1.31	0.80	1.59				
8.8	21.6	27.9	16.9	17.2	1.36	0.82	1.66				
9.0	21.5	28.1	16.1	18.3	1.41	0.85	1.73				
9.2	21.3	28.4	15.5	20.2	1.47	0.87	1.83				
9.4	21.1	28.8	14.8	22.7	1.54	0.90	1.91				
9.6	20.9	29.1	14.1	23.3	1.62	0.92	2.05				
9.8	20.6	29.5	13.3	21.2	1.71	0.94	2.18				
10.0	20.3	30.0	12.5	20.0	1.83	0.96	2.27				

*Typical Performance Data*

**NOTE: Use PDF Bookmarks to view DATA at required conditions**

**Definitions:**

- Input Return Loss = -S11 (dB)
- Gain(Power Gain) = S21 (dB)
- Reverse Isolation = -S12 (dB)
- Output Return Loss = -S22 (dB)

TEST CONDITIONS: V<sub>DD</sub> = +5 V, I<sub>DD</sub> = 55 mA @ Temperature = +25°C

FREQ	Gain	Isolation	Input Return Loss	Output Return Loss	Stability		Noise Figure	FREQ	IP-3 Output		1dB Comp. Output
					K	Measure			POUT = 0 dBm/Tone	POUT = +5 dBm/Tone	
(GHz)	(dB)	(dB)	(dB)	(dB)	K	Measure	(dB)	(GHz)	(dBm)	(dBm)	(dBm)
0.1	21.4	24.9	17.2	20.9	1.05	0.56	1.75	0.01	27.1	27.6	16.6
0.1	21.6	24.6	18.9	24.4	1.04	0.51	1.31	0.05	29.0	29.8	19.7
0.3	21.7	24.5	19.6	29.0	1.04	0.49	1.07	0.10	29.7	30.0	20.8
0.5	21.7	24.5	19.4	29.9	1.04	0.49	1.02	0.40	29.7	30.1	21.1
0.7	21.7	24.6	18.9	30.6	1.05	0.50	1.04	0.50	31.2	31.3	21.2
1.0	21.7	24.7	17.9	29.9	1.05	0.52	0.97	1.00	29.3	29.7	21.6
1.2	21.7	24.7	17.3	28.3	1.05	0.53	1.03	1.50	30.5	30.6	21.3
1.4	21.7	24.8	16.6	26.5	1.06	0.54	1.04	2.00	29.7	30.0	21.5
1.6	21.6	24.9	15.9	24.7	1.06	0.55	1.02	2.50	28.9	28.9	21.6
1.8	21.6	24.9	15.2	23.2	1.06	0.56	1.02	3.00	29.0	28.9	21.0
2.0	21.6	25.0	14.5	21.8	1.07	0.57	1.01	3.50	28.9	28.6	20.5
2.2	21.6	25.1	13.9	20.7	1.07	0.58	0.99	4.00	27.9	27.7	20.3
2.4	21.5	25.2	13.4	19.8	1.07	0.59	1.05	4.50	27.8	27.5	20.6
2.6	21.5	25.3	12.9	18.9	1.08	0.60	1.05	5.00	27.0	26.7	20.2
2.8	21.5	25.4	12.5	18.3	1.08	0.61	1.12	5.50	27.9	27.7	19.8
3.0	21.5	25.4	12.2	17.8	1.09	0.62	1.09	6.00	27.7	27.3	19.8
3.2	21.5	25.5	11.9	17.4	1.09	0.63	1.09	6.50	28.5	28.2	19.6
3.4	21.5	25.6	11.7	17.1	1.09	0.64	1.06	7.00	29.2	28.8	19.6
3.6	21.5	25.7	11.6	17.0	1.10	0.65	1.15	7.50	29.3	29.0	19.2
3.8	21.5	25.7	11.6	17.0	1.10	0.65	1.14	8.00	28.9	28.7	18.6
4.0	21.5	25.8	11.6	17.2	1.10	0.66	1.14	8.50	29.1	28.6	17.6
4.2	21.5	25.9	11.7	17.5	1.11	0.67	1.17	9.00	28.2	28.0	16.5
4.4	21.5	25.9	11.9	18.0	1.11	0.68	1.18	9.50	28.0	28.0	16.0
4.6	21.6	26.0	12.1	18.6	1.12	0.68	1.16	10.00	27.4	28.1	15.2
4.8	21.6	26.0	12.5	19.5	1.12	0.69	1.19				
5.0	21.7	26.1	12.9	20.4	1.12	0.69	1.21				
5.2	21.7	26.1	13.3	21.8	1.12	0.70	1.29				
5.4	21.8	26.2	13.9	23.2	1.13	0.70	1.17				
5.6	21.9	26.3	14.4	24.9	1.13	0.70	1.19				
5.8	21.9	26.3	15.2	26.8	1.13	0.70	1.18				
6.0	22.0	26.3	16.2	28.6	1.14	0.70	1.18				
6.2	22.1	26.4	17.2	27.3	1.14	0.70	1.20				
6.4	22.2	26.5	18.6	24.7	1.15	0.70	1.21				
6.6	22.2	26.6	20.3	22.0	1.15	0.70	1.17				
6.8	22.3	26.6	22.6	20.1	1.16	0.70	1.17				
7.0	22.3	26.8	25.6	18.6	1.17	0.70	1.24				
7.2	22.3	26.9	29.3	17.4	1.18	0.70	1.24				
7.4	22.3	27.0	31.9	16.5	1.19	0.70	1.25				
7.6	22.3	27.2	28.9	15.8	1.21	0.71	1.31				
7.8	22.3	27.3	24.8	15.4	1.23	0.72	1.32				
8.0	22.2	27.5	22.3	15.2	1.25	0.74	1.37				
8.2	22.1	27.7	20.4	15.2	1.28	0.76	1.43				
8.4	22.0	27.9	18.9	15.4	1.32	0.78	1.53				
8.6	21.9	28.2	17.9	15.8	1.36	0.80	1.59				
8.8	21.8	28.4	17.0	16.5	1.40	0.83	1.66				
9.0	21.7	28.7	16.3	17.6	1.45	0.85	1.75				
9.2	21.6	29.0	15.8	19.3	1.52	0.87	1.85				
9.4	21.4	29.3	15.1	21.9	1.58	0.89	1.95				
9.6	21.2	29.6	14.6	24.4	1.67	0.92	2.06				
9.8	20.9	30.0	13.9	21.2	1.75	0.94	2.21				
10.0	20.7	30.4	13.0	19.8	1.87	0.96	2.27				

## Typical Performance Data

### Definitions:

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS:  $V_{DD} = +5.25\text{ V}$ ,  $I_{DD} = 62\text{ mA}$  @ Temperature = +25°C

FREQ	Gain	Isolation	Input Return Loss	Output Return Loss	Stability		Noise Figure	FREQ	IP-3 Output		1dB Comp. Output
					K	Measure			POUT = 0 dBm/Tone	POUT = +5 dBm/Tone	
(GHz)	(dB)	(dB)	(dB)	(dB)	K	Measure	(dB)	(GHz)	(dBm)	(dBm)	(dBm)
0.05	21.8	25.3	19.8	18.5	1.05	0.55	1.75	0.01	27.9	29.3	17.3
0.1	22.1	25.0	22.3	20.7	1.04	0.49	1.31	0.05	30.7	31.0	20.3
0.3	22.1	24.9	23.4	22.8	1.04	0.48	1.06	0.10	31.0	31.4	21.3
0.5	22.1	24.9	22.9	23.2	1.04	0.48	1.02	0.40	31.1	31.5	21.6
0.7	22.1	25.0	22.2	23.9	1.05	0.49	1.04	0.50	31.9	32.8	21.7
1.0	22.1	25.0	20.7	24.8	1.05	0.51	0.98	1.00	30.9	31.0	21.9
1.2	22.1	25.1	19.8	25.3	1.05	0.52	1.07	1.50	32.0	32.0	21.7
1.4	22.1	25.2	18.8	25.2	1.06	0.53	1.05	2.00	31.1	31.4	21.8
1.6	22.1	25.2	17.9	24.6	1.06	0.54	0.99	2.50	30.3	30.2	21.8
1.8	22.1	25.3	17.0	23.6	1.06	0.55	0.97	3.00	30.6	30.3	21.2
2.0	22.0	25.4	16.2	22.5	1.07	0.56	0.99	3.50	30.3	30.1	20.7
2.2	22.0	25.4	15.5	21.7	1.07	0.57	0.96	4.00	29.6	29.3	20.7
2.4	22.0	25.5	14.8	20.9	1.07	0.58	1.05	4.50	29.3	29.0	21.0
2.6	22.0	25.6	14.3	20.0	1.08	0.59	1.05	5.00	28.8	28.3	20.6
2.8	22.0	25.7	13.8	19.4	1.08	0.60	1.10	5.50	29.3	28.9	20.3
3.0	22.0	25.8	13.4	18.8	1.08	0.61	1.09	6.00	28.8	28.6	20.2
3.2	21.9	25.8	13.1	18.4	1.09	0.62	1.07	6.50	29.5	29.2	20.0
3.4	22.0	25.9	12.9	18.1	1.09	0.63	1.10	7.00	29.6	29.4	20.0
3.6	21.9	26.0	12.7	17.9	1.09	0.63	1.11	7.50	29.6	29.4	19.6
3.8	21.9	26.1	12.7	17.8	1.10	0.64	1.13	8.00	29.2	29.1	19.1
4.0	21.9	26.1	12.7	17.9	1.10	0.65	1.16	8.50	28.6	28.6	18.0
4.2	21.9	26.2	12.8	18.1	1.11	0.66	1.17	9.00	27.7	27.9	16.9
4.4	22.0	26.3	13.1	18.4	1.11	0.67	1.16	9.50	27.3	27.7	16.4
4.6	22.0	26.3	13.3	18.9	1.12	0.68	1.15	10.00	26.8	27.6	15.6
4.8	22.0	26.4	13.7	19.5	1.12	0.68	1.18				
5.0	22.1	26.5	14.1	20.1	1.12	0.69	1.18				
5.2	22.1	26.5	14.6	20.9	1.13	0.69	1.25				
5.4	22.2	26.6	15.3	21.6	1.13	0.69	1.17				
5.6	22.2	26.6	15.9	22.4	1.13	0.70	1.17				
5.8	22.3	26.7	16.8	23.1	1.14	0.70	1.16				
6.0	22.3	26.7	17.9	23.1	1.14	0.70	1.19				
6.2	22.4	26.8	19.1	22.3	1.15	0.70	1.19				
6.4	22.4	26.9	20.7	21.2	1.15	0.70	1.19				
6.6	22.5	27.0	22.8	19.8	1.16	0.70	1.16				
6.8	22.5	27.1	25.8	18.5	1.17	0.70	1.17				
7.0	22.5	27.1	30.1	17.5	1.18	0.70	1.19				
7.2	22.5	27.3	31.8	16.5	1.19	0.70	1.23				
7.4	22.5	27.4	31.8	15.8	1.21	0.71	1.26				
7.6	22.5	27.6	27.1	15.3	1.23	0.72	1.30				
7.8	22.4	27.8	23.7	14.9	1.25	0.73	1.31				
8.0	22.4	27.9	21.5	14.8	1.28	0.74	1.37				
8.2	22.3	28.1	19.9	14.7	1.30	0.76	1.43				
8.4	22.2	28.4	18.6	15.0	1.34	0.78	1.52				
8.6	22.1	28.6	17.7	15.3	1.38	0.80	1.61				
8.8	22.0	28.8	16.9	16.0	1.43	0.83	1.68				
9.0	21.9	29.1	16.3	16.9	1.48	0.85	1.75				
9.2	21.8	29.4	15.8	18.5	1.54	0.87	1.86				
9.4	21.6	29.6	15.2	21.0	1.60	0.89	1.95				
9.6	21.4	30.0	14.8	27.0	1.69	0.91	2.09				
9.8	21.2	30.3	14.2	21.2	1.77	0.93	2.22				
10.0	20.9	30.7	13.4	19.5	1.88	0.95	2.31				

*Typical Performance Data*

**Definitions:**

Input Return Loss = -S11 (dB)  
 Gain(Power Gain) = S21 (dB)  
 Reverse Isolation = -S12 (dB)  
 Output Return Loss = -S22 (dB)

TEST CONDITIONS: V<sub>DD</sub> = +5 V, I<sub>DD</sub> = 58 mA @ Temperature = +105°C

FREQ	Gain	Isolation	Input Return Loss	Output Return Loss	Stability		Noise Figure	FREQ	IP-3 Output		1dB Comp. Output
					K	Measure			POUT = 0 dBm/Tone	POUT = +5 dBm/Tone	
(GHz)	(dB)	(dB)	(dB)	(dB)	K	Measure	(dB)	(GHz)	(dBm)	(dBm)	(dBm)
0.05	21.1	24.6	17.1	21.9	1.06	0.57	2.36	0.01	27.3	27.3	15.5
0.1	21.3	24.4	18.6	25.6	1.05	0.52	1.80	0.05	29.5	29.8	18.6
0.3	21.3	24.4	19.1	30.2	1.05	0.52	1.52	0.10	30.3	30.1	19.7
0.5	21.3	24.4	18.6	31.9	1.05	0.52	1.47	0.40	29.9	30.4	20.3
0.7	21.3	24.4	18.0	32.5	1.06	0.54	1.54	0.50	31.6	31.6	20.4
1.0	21.2	24.5	16.8	29.5	1.06	0.55	1.44	1.00	30.0	30.0	20.0
1.2	21.2	24.6	16.1	26.6	1.07	0.57	1.58	1.50	30.7	30.7	20.2
1.4	21.1	24.7	15.3	24.2	1.07	0.58	1.55	2.00	29.6	30.1	19.9
1.6	21.1	24.8	14.6	22.3	1.08	0.59	1.53	2.50	29.0	29.1	19.7
1.8	21.1	24.9	14.0	20.5	1.08	0.60	1.52	3.00	29.6	29.3	19.3
2.0	21.0	25.0	13.4	19.3	1.09	0.61	1.52	3.50	29.3	29.3	19.0
2.2	21.0	25.0	13.1	18.2	1.09	0.62	1.56	4.00	28.8	28.5	18.9
2.4	21.0	25.1	12.8	17.5	1.10	0.63	1.56	4.50	28.8	28.4	19.0
2.6	21.0	25.2	12.5	16.9	1.10	0.64	1.59	5.00	28.1	27.7	18.6
2.8	20.9	25.3	12.4	16.4	1.11	0.64	1.64	5.50	29.0	28.6	18.6
3.0	20.9	25.4	12.2	16.3	1.11	0.65	1.65	6.00	28.8	28.2	18.6
3.2	20.9	25.5	12.2	16.2	1.12	0.66	1.65	6.50	29.2	29.0	18.6
3.4	20.9	25.6	12.2	16.2	1.13	0.67	1.65	7.00	29.9	29.6	18.8
3.6	20.9	25.6	12.2	16.5	1.13	0.68	1.72	7.50	29.6	29.7	18.7
3.8	20.9	25.7	12.4	16.7	1.14	0.68	1.68	8.00	30.1	29.7	18.6
4.0	21.0	25.8	12.6	17.2	1.14	0.69	1.66	8.50	29.6	29.5	17.8
4.2	21.0	25.8	12.8	17.8	1.15	0.70	1.75	9.00	28.9	28.9	16.6
4.4	21.0	25.9	13.1	18.7	1.15	0.71	1.72	9.50	29.2	28.9	15.9
4.6	21.0	26.0	13.3	19.7	1.16	0.72	1.74	10.00	28.7	29.2	15.1
4.8	21.0	26.0	13.6	20.8	1.16	0.73	1.76				
5.0	21.1	26.1	13.9	22.1	1.17	0.74	1.77				
5.2	21.1	26.1	14.0	24.0	1.17	0.74	1.85				
5.4	21.1	26.2	14.4	26.1	1.18	0.75	1.80				
5.6	21.2	26.3	14.5	28.4	1.19	0.76	1.81				
5.8	21.2	26.4	14.9	32.0	1.20	0.77	1.88				
6.0	21.2	26.5	15.4	34.4	1.20	0.77	1.84				
6.2	21.2	26.6	15.6	35.7	1.21	0.78	1.89				
6.4	21.3	26.7	16.2	36.0	1.23	0.78	1.95				
6.6	21.3	26.8	16.6	34.6	1.25	0.79	1.93				
6.8	21.3	27.0	17.2	33.3	1.27	0.80	1.95				
7.0	21.3	27.1	18.0	32.7	1.28	0.80	2.00				
7.2	21.3	27.2	18.7	31.2	1.29	0.80	2.03				
7.4	21.3	27.3	20.3	29.4	1.32	0.81	2.05				
7.6	21.3	27.4	20.9	27.2	1.34	0.82	2.11				
7.8	21.3	27.6	20.8	25.3	1.36	0.82	2.09				
8.0	21.3	27.7	20.3	24.1	1.38	0.83	2.14				
8.2	21.2	27.9	19.5	21.9	1.41	0.84	2.19				
8.4	21.1	28.1	18.2	21.0	1.45	0.85	2.31				
8.6	20.9	28.3	17.2	20.6	1.51	0.87	2.37				
8.8	20.8	28.6	16.2	20.6	1.57	0.89	2.47				
9.0	20.6	28.8	15.3	21.3	1.62	0.90	2.54				
9.2	20.5	29.1	14.6	22.7	1.69	0.92	2.64				
9.4	20.3	29.4	13.7	24.6	1.75	0.94	2.71				
9.6	20.1	29.7	12.9	26.2	1.84	0.97	2.84				
9.8	19.9	30.1	12.2	26.3	1.94	0.99	2.94				
10.0	19.6	30.5	11.2	23.3	2.06	1.01	3.03				

*Typical Performance Data*

**Definitions:**







Input Return Loss = -S11 (dB)  
 Gain(Power Gain) = S21 (dB)  
 Reverse Isolation = -S12 (dB)  
 Output Return Loss = -S22 (dB)

TEST CONDITIONS: V<sub>DD</sub> = +5 V, I<sub>DD</sub> = 55 mA @ Temperature = -45°C

FREQ	Gain	Isolation	Input Return Loss	Output Return Loss	Stability		Noise Figure
					K	Measure	
(GHz)	(dB)	(dB)	(dB)	(dB)	K	Measure	(dB)
0.05	21.8	25.3	20.6	17.5	1.05	0.55	1.16
0.1	22.0	25.0	23.3	19.6	1.04	0.49	0.96
0.3	22.1	24.8	25.2	21.8	1.04	0.46	0.78
0.5	22.2	24.8	24.8	22.4	1.04	0.46	0.76
0.7	22.2	24.9	23.9	23.1	1.04	0.47	0.83
1.0	22.1	24.9	22.1	24.6	1.04	0.49	0.69
1.2	22.1	25.0	21.0	25.2	1.05	0.49	0.79
1.4	22.1	25.0	19.8	25.5	1.05	0.50	0.87
1.6	22.1	25.1	18.6	25.2	1.05	0.51	0.84
1.8	22.1	25.1	17.6	23.7	1.05	0.52	0.84
2.0	22.1	25.2	16.6	22.5	1.06	0.53	0.78
2.2	22.1	25.3	15.8	21.3	1.06	0.54	0.72
2.4	22.1	25.3	15.1	20.2	1.06	0.55	0.79
2.6	22.1	25.4	14.5	19.3	1.07	0.56	0.79
2.8	22.1	25.5	14.2	18.5	1.07	0.56	0.84
3.0	22.1	25.6	13.8	18.1	1.07	0.57	0.88
3.2	22.1	25.6	13.6	17.7	1.07	0.57	0.77
3.4	22.1	25.7	13.6	17.5	1.07	0.58	0.77
3.6	22.1	25.7	13.5	17.5	1.07	0.59	0.80
3.8	22.2	25.8	13.7	17.6	1.08	0.59	0.78
4.0	22.2	25.9	13.8	17.8	1.08	0.60	0.81
4.2	22.2	25.9	14.1	18.2	1.08	0.61	0.80
4.4	22.2	26.0	14.5	18.6	1.09	0.62	0.79
4.6	22.3	26.0	14.7	19.2	1.09	0.62	0.75
4.8	22.3	26.1	15.2	19.8	1.09	0.62	0.74
5.0	22.4	26.1	15.5	20.2	1.08	0.63	0.79
5.2	22.5	26.2	15.8	20.9	1.08	0.63	0.80
5.4	22.6	26.2	16.2	21.4	1.09	0.64	0.74
5.6	22.7	26.3	16.4	21.6	1.08	0.64	0.74
5.8	22.7	26.3	17.2	21.5	1.08	0.63	0.69
6.0	22.9	26.4	17.6	21.0	1.08	0.63	0.77
6.2	23.0	26.4	18.1	20.0	1.08	0.63	0.73
6.4	23.0	26.5	18.9	18.9	1.08	0.62	0.71
6.6	23.1	26.5	19.3	17.7	1.08	0.62	0.70
6.8	23.2	26.6	20.2	16.6	1.08	0.61	0.65
7.0	23.3	26.7	20.6	15.7	1.08	0.61	0.72
7.2	23.4	26.7	21.0	14.8	1.09	0.60	0.67
7.4	23.5	26.9	21.1	14.1	1.09	0.59	0.65
7.6	23.5	26.9	20.9	13.7	1.09	0.59	0.71
7.8	23.6	27.0	21.0	13.3	1.10	0.59	0.72
8.0	23.6	27.1	20.6	13.0	1.11	0.59	0.71
8.2	23.7	27.2	20.4	12.7	1.11	0.59	0.71
8.4	23.7	27.3	20.2	12.6	1.12	0.60	0.82
8.6	23.8	27.5	19.9	12.5	1.13	0.61	0.86
8.8	23.8	27.7	19.7	12.5	1.15	0.62	0.93
9.0	23.8	27.9	19.2	12.4	1.16	0.64	0.96
9.2	23.8	28.0	18.9	12.5	1.17	0.65	1.04
9.4	23.8	28.2	18.3	12.3	1.19	0.66	1.10
9.6	23.8	28.5	17.8	12.4	1.22	0.69	1.22
9.8	23.7	28.7	17.7	12.8	1.24	0.71	1.38
10.0	23.6	28.9	17.3	13.3	1.28	0.73	1.49


FREQ	IP-3 Output		1dB Comp. Output
	POUT = 0 dBm/Tone	POUT = +5 dBm/Tone	
(GHz)	(dBm)	(dBm)	(dBm)
0.01	27.3	26.6	16.5
0.05	29.0	30.9	19.3
0.10	29.8	30.3	20.4
0.40	29.7	29.9	20.7
0.50	30.8	31.3	20.8
1.00	29.1	29.4	21.2
1.50	30.1	30.3	20.9
2.00	29.1	29.5	21.1
2.50	28.6	28.4	21.3
3.00	28.5	28.5	20.5
3.50	28.3	28.3	19.5
4.00	27.5	27.5	19.4
4.50	27.5	27.3	19.7
5.00	26.0	26.1	19.4
5.50	26.8	26.6	19.4
6.00	26.6	26.7	19.5
6.50	27.7	27.8	19.5
7.00	27.8	28.1	19.6
7.50	27.9	28.2	19.3
8.00	27.6	27.9	18.7
8.50	27.5	28.0	17.9
9.00	26.6	27.5	16.9
9.50	26.3	27.3	16.4
10.00	25.4	26.9	15.4

## Typical Performance Curves




## Typical Performance Curves


**ISOLATION vs. TEMPERATURE,**  
 $P_{IN} = -25 \text{ dBm}$ ,  $V_{DD} = +5 \text{ V}$




**ISOLATION vs. VOLTAGE,**  
 TEMPERATURE = +25°C




**P1dB vs. TEMPERATURE,**  
 $V_{DD} = +5 \text{ V}$




**P1dB vs. VOLTAGE,**  
 TEMPERATURE = +25°C






**OUTPUT IP3 vs. TEMPERATURE,**  
 $P_{OUT} = +5 \text{ dBm/TONE}$ ,  $V_{DD} = +5 \text{ V}$




**OUTPUT IP3 vs. VOLTAGE,**  
 $P_{OUT} = +5 \text{ dBm/TONE}$ , TEMPERATURE = +25°C




## Typical Performance Curves



### Outline Dimensions



### PCB Land Pattern



SUGGESTED LAYOUT,  
TOLERANCE TO BE WITHIN  $\pm .002$

**Weight: .02 Grams**

**Dimensions are in inches (mm). Tolerances: 2Pl.  $\pm .01$ ; 3 Pl.  $\pm .004$**

#### Notes:

1. Case material: Plastic.
2. Termination finish:
  - For RoHS Case Styles: Tin-Silver alloy plate over Nickel barrier or Matte-Tin. All models, (+) suffix. See Data sheet.
  - For RoHS-5 Case Styles: Tin-Lead plate. All models, no (+) suffix.




INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified

# Tape & Reel Packaging TR-F66



Tape Width, mm	Device Cavity Pitch, mm	Reel Size, inches	Devices per Reel see note	
8	4	7	Small quantity standard	20
				50
				100
				200
				500
		7	Standard	1000, 2000, 3000

Note: Please consult individual model data sheet to determine device per reel availability.

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: [www.minicircuits.com/pages/pdfs/tape.pdf](http://www.minicircuits.com/pages/pdfs/tape.pdf)

**Mini-Circuits®**


INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified


THIRD ANGLE PROJECTION



REVISIONS


REV	ECN No.	DESCRIPTION	DATE	DR	AUTH
OR	ECO-025145	NEW RELEASE	04/08/25	ITG	IL

SUGGESTED MOUNTING CONFIGURATION FOR  
DQ1225 CASE STYLE




COMPONENT	SIZE
C1-C8	0402
L1,L2	0402
R1	0402

3 LAYER STACK-UP DIAGRAM



NOTES:

1. PCB IS MULTILAYER PCB, SEE STACK-UP DIAGRAM.
2. TRACE WIDTH & GAP ARE SHOWN FOR ROGERS R04350B WITH DIELECTRIC THICKNESS .010".  
COPPER: 1/2 OZ. EACH LAYER. FOR OTHER MATERIALS TRACE WIDTH & GAP MAY NEED TO BE MODIFIED.
3. CHIP COMPONENT FOOT PRINTS SHOWN FOR REFERENCE, FOR COMPONENT VALUES REFER TO TB-PMA3-14LVC+.
4. LAYERS 2 & 3 OF PCB ARE CONTINUOUS GROUND PLANE.



DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)

DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

UNLESS OTHERWISE SPECIFIED	INITIALS	DATE
DIMENSIONS ARE IN INCHES	ITG	04/08/25
TOLERANCES ON:	GF	04/08/25
2 PL DECIMALS ±	IL	04/08/25
3 PL DECIMALS ± .005		
ANGLES ±		
FRACTIONS ±		



Mini-Circuits®

13 Neptune Avenue  
Brooklyn NY 11235





PL, DQ1225, TB-PMA3-14LVC+

SIZE	CODE IDENT	DRAWING NO:	REV:
A	15542	98-PL-820	OR
FILE:	98PL820	SCALE: 8:1	SHEET: 1 OF 1

Mini-Circuits®

THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.

# Evaluation Board and Circuit



## Schematic Diagram

COMPONENTS	SIZE	VALUE	MANUFACTURER	PART NUMBER
C1,C2,C9,C10	0402	0.01uF	Murata	GRM155R71H103KA88D
C3		0.2 pF		GJM1555C1HR20WB01D
C4		0.1 pF		GJM1555C1HR10WB01D
C5,C6		100 pF		GRM1555C1H101JA01D
C7,C8		0.1 uF		GRM155R71H104KE14J
L1,L2		900 nH		Coilcraft
R1		5.6 kΩ	KOA Speer	RK73H1ETTP5601F

### NOTES:

1. 50 Ohm SMA Female Connectors.
2. PCB Material: Roger RO4350B or equivalent, Dielectric constant=3.5, Thickness=0.010 inch

**Mini-Circuits®**

All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-40° to 85° C or -45° to 85° C or -55° to 105° C or -40° to 105° C or -40° to 95° C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C or -65° to 150° Ambient Environment	Individual Model Data Sheet
HTOL	1000 hours at 125°C	MIL-STD-883, Method 1005, Condition B
Thermal Shock	-55° to 100°C, 100 cycles	MIL-STD-202, Method 107, Condition A-3, except +100°C
Mechanical Shock	1.5Kg, 0.5 ms, 5 shock pulses, Y1 direction only	MIL-STD-883, Method 2002, Condition B, except Y1 direction only
Vibration (Variable Frequency)	50g peak	MIL-STD-883, Method 2007, Condition B
Autoclave	15 psig, 100% RH, 121°C, 96 hours	JESD22-A102, Condition C
HAST	130°C, 85% RH, 96 hours	JESD22-A110
Solderability	10X Magnification	J-STD-002, Para 4.2.5, Test S, 95% Coverage
Solder Reflow Heat	Sn-Pb Eutetic Process: 240°C peak Pb-Free Process: 260°C peak	J-STD-020, Table 4-1, 4-2 and 5-2; Figure 5-1
Moisture Sensitivity: Level 1	Bake at 125°C for 24 hours Soak at 85°C/85% RH for 168 hours, Reflow 3 cycles at 260°C peak	J-STD-020

All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

<b>Specification</b>	<b>Test/Inspection Condition</b>	<b>Reference/Spec</b>
Marking Resistance to Solvents	Isopropyl alcohol + mineral spirits at 25°C; terpene defluxer at 25°C; distilled water + proylene glycol monomethyl ether + monoethanolamine at 63°C to 70°C	MIL-STD-202, Method 215