




WIDEBAND, HIGH GAIN, LOW NOISE

Monolithic Amplifier PMA3-34GLN+

50Ω 10 to 30 GHz

THE BIG DEAL

- Wideband, 10 to 30 GHz
- Usable down to 9 GHz
- High Gain, 25.5 dB typ. at 20 GHz
- Low NF, 1.6 dB typ. at 20 GHz
- P1dB, +10 dBm typ. at 20 GHz
- OIP3, +22 dBm typ. at 20 GHz
- Built-in Bias Tee and DC Blocks
- Patent Pending



Generic photo used for illustration purposes only

CASE STYLE: DQ1225

+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our website for methodologies and qualifications

APPLICATIONS

- 5G
- Fixed Satellite
- Mobile

PRODUCT OVERVIEW

The PMA3-34GLN+ is a PHEMT based wideband, low noise MMIC amplifier with a unique combination of high gain and low noise figure over a very broad bandwidth making it ideal for using as the first stage driver amplifier of receiver applications. This design operates on a single 4V supply, is matched to 50 Ohm and comes in a tiny plastic package (3 x 3 x 0.89mm), accommodating dense circuit board layouts.

KEY FEATURES

Feature	Advantages
Low noise, 1.6 dB at 20 GHz	Enables lower system noise figure performance
High Gain, 25.5 dB at 20 GHz	Enables signal amplification without the need for multiple gain stage, minimizing the effect of subsequent stages on noise figure
Built-in Bias Tee & DC Blocks	Minimizes the external component count & PC board space, making it less expensive and user friendly for system designers
3 x 3mm 12-lead MCLP package	Tiny footprint saves space in dense layouts while providing low inductance, repeatable transitions, and excellent thermal contact to the PCB

REV. C
ECO-011519
PMA3-34GLN+
GY/RS/CP/AM
240401





WIDEBAND, HIGH GAIN, LOW NOISE

Monolithic Amplifier PMA3-34GLN+

Mini-Circuits

50Ω 10 to 30 GHz

ELECTRICAL SPECIFICATIONS¹ AT +25°C, V_s = +4V AND R₁=18Ω, UNLESS NOTED OTHERWISE

Parameter	Condition (GHz)	V _s = +4 V			Units
		Min.	Typ.	Max.	
Frequency Range	—	10		30	GHz
Noise Figure	10	—	1.9	—	dB
	15	—	1.8	—	
	20	—	1.6	—	
	30	—	2.4	—	
Gain	10	22.5	25.3	29.2	dB
	15	24.7	27.9	31.5	
	20	22.2	25.5	31.1	
	30	—	18.2	—	
Input Return Loss	10		13		dB
	15		13		
	20		21		
	30		8		
Output Return Loss	10		12		dB
	15		10		
	20		10		
	30		9		
Output Power @ 1 dB compression	10		+8.5		dBm
	15		+9.5		
	20		+10		
	30		+11		
Output IP3	10		+18.6		dBm
	15		+22.1		
	20		+22		
	30		+23.4		
Supply Voltage (V _s)		+3.75	+4.0	+4.25	V
Device Operating Current (I _{DD})			68	112	mA
Device Current Variation vs. Temperature ²			-50		μA/°C
Device Current Variation vs. Voltage			0.02		mA/mV
Thermal Resistance, junction-to-ground lead			106		°C/W

1. Measured on Mini-Circuits Characterization test board TB-PMA3-34GLN+ with thru-line loss being deducted. See Characterization Test Circuit (Fig. 1)

2. Device Current Variation vs. Temperature = (Current at 85°C - Current at -45°C)/130°C

ABSOLUTE MAXIMUM RATINGS³

Parameter	Ratings
Operating Temperature (ground lead)	-40°C to +85°C
Storage Temperature	-65°C to +150°C
Junction Temperature	+146°C
Total Power Dissipation	0.65W
Input Power (CW), V _s = +4 V	+23 dBm (5 minutes max.) +13 dBm (continuous)
DC Voltage at Port 2 & 8	+2 V
DC Voltage (V _s)	+6 V

3. Permanent damage may occur if any of these limits are exceeded. Electrical maximum ratings are not intended for continuous normal operation.







WIDEBAND, HIGH GAIN, LOW NOISE

Monolithic Amplifier PMA3-34GLN+

50Ω 10 to 30 GHz

SIMPLIFIED SCHEMATIC AND PAD DESCRIPTION



Function	Pad Number	Description (Fig. 1)
RF-IN	2	RF Input Pad. Connects to RF input
RF-OUT	8	RF Output Pad. Connects to RF output
V _{DD}	6	DC Power Supply Pad. Connects to Voltage Source Vs via R1
Ground	1,3,7,9 & Paddle	Connects to ground
No Connection	4,5,10,11& 12	Not used internally. Connected to ground on test board

RECOMMENDED APPLICATION AND CHARACTERIZATION TEST CIRCUIT




Fig 1. Application and Characterization Circuit


Note: This block diagram is used for characterization. (DUT is soldered on Mini-Circuits Characterization test board TB-PMA3-34GLN+) Gain, Return loss, Output power at 1dB compression (P1 dB), output IP3 (OIP3) and noise figure measured using Agilent's N5245A microwave network analyzer.

Conditions:

1. Gain and Return loss: Pin= -25dBm
2. Output IP3 (OIP3): Two tones, spaced 1 MHz apart, -5dBm/tone at output.

Component	Size	Value	Part Number	Manufacturer
R1	0402	18 Ohm	RK73G1ETTP18ROF	KOA
C1	0402	5 pF	GJM1555C1H5R0CB01D	Murata
C2	0402	0.1 uF	GRM155R71C104KA88D	Murata

PRODUCT MARKING



Marking may contain other features or characters for internal lot control





WIDEBAND, HIGH GAIN, LOW NOISE

Monolithic Amplifier PMA3-34GLN+

50Ω 10 to 30 GHz

ADDITIONAL DETAILED TECHNICAL INFORMATION IS AVAILABLE ON OUR DASH BOARD. TO ACCESS [CLICK HERE](#)

Performance Data	Data Table graphs, s-parameter data set (.zip file)
Case Style	DQ1225 Plastic package, exposed paddle, lead finish: Matte Tin
Tape & Reel Standard quantities available on reel	F66 7" reels with 20, 50, 100, 200, 500, 1K, 2K or 3K devices
Suggested Layout for PCB Design	PL-674
Evaluation Board	TB-PMA3-34GLN+ (Without connectors) TB-PMA3-34GLNC+ (With connectors)
Environmental Ratings	ENV08T1


ESD RATING

Human Body Model (HBM): Class 1A (250 to <500V) in accordance with ANSI/ESD STM 5.1 - 2001

MSL RATING

Moisture Sensitivity: MSL1 in accordance with IPC/JEDEC J-STD-020D

MSL TEST FLOW CHART



- NOTES**
- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
 - B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
 - C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the standard. Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



Typical Performance Data

Definitions:

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 4.00V, Id = 68mA @ Temperature = +25°C

FREQ	Gain	Isolation	Input Return Loss	Output Return Loss	Stability		IP-3 Output	1dB Comp. Output	Noise Figure
					K	Measure			
(MHz)	(dB)	(dB)	(dB)	(dB)	K	Measure	(dBm)	(dBm)	(dB)
9000	22.92	67.81	10.44	11.99	81.23	1.02	17.62	6.34	2.23
9500	24.29	61.86	11.60	12.18	36.15	1.00	18.40	7.53	1.98
10000	25.39	60.57	12.03	12.15	27.79	1.00	18.22	8.15	1.81
10500	26.29	58.61	11.50	12.20	19.88	1.00	19.40	8.27	1.74
11000	27.02	60.08	10.36	12.65	21.27	1.03	19.26	8.11	1.70
11500	27.67	58.37	9.23	13.76	15.91	1.07	19.05	8.31	1.76
12000	28.20	61.13	8.44	15.64	20.35	1.11	18.58	8.65	1.77
12500	28.57	62.69	8.19	17.99	23.43	1.13	19.43	8.41	1.85
13000	28.77	59.85	8.41	17.94	16.68	1.13	19.02	8.68	1.83
13500	28.83	57.77	9.24	14.86	13.23	1.08	19.46	8.87	1.87
14000	28.70	56.31	10.46	12.54	11.52	1.03	19.73	8.62	1.79
14500	28.48	54.57	12.06	11.09	9.81	0.98	20.70	9.21	1.77
15000	28.20	54.41	13.69	10.53	10.07	0.95	20.49	9.15	1.69
15500	27.95	52.00	15.27	10.49	7.99	0.93	20.96	9.33	1.67
16000	27.68	51.56	16.58	10.77	7.96	0.93	21.06	9.41	1.61
16500	27.40	49.69	16.74	11.23	6.71	0.94	21.46	9.19	1.59
17000	27.13	50.77	16.15	11.78	7.88	0.95	21.38	9.21	1.56
17500	26.86	50.52	15.33	12.15	7.91	0.96	20.50	8.97	1.51
18000	26.59	49.29	14.63	12.22	7.08	0.96	20.90	8.94	1.57
18500	26.35	49.17	14.32	11.99	7.16	0.96	20.44	9.19	1.48
19000	26.11	48.93	14.29	11.55	7.14	0.96	19.54	8.68	1.55
19500	25.92	48.77	14.58	11.16	7.18	0.95	21.40	8.76	1.52
20000	25.73	47.20	15.35	10.87	6.16	0.93	20.34	9.44	1.59
20500	25.50	46.80	16.35	10.62	6.06	0.92	20.62	9.52	1.48
21000	25.16	46.32	16.74	10.38	5.95	0.92	19.21	9.91	1.51
21500	24.58	46.31	16.10	9.81	6.25	0.91	20.99	10.61	1.57
22000	24.01	46.70	14.76	9.21	6.80	0.90	20.96	10.65	1.54
22500	23.59	46.96	13.50	8.90	7.20	0.90	21.56	10.79	1.60
23000	23.23	47.32	12.27	8.81	7.69	0.91	22.11	10.48	1.59
23500	22.86	47.23	11.29	8.76	7.82	0.92	21.99	10.93	1.58
24000	22.43	47.48	10.86	8.69	8.39	0.92	21.63	11.05	1.65
24500	21.98	47.51	10.47	8.50	8.73	0.93	20.84	11.25	1.68
25000	21.65	48.14	10.30	8.35	9.66	0.92	22.93	11.19	1.59
25500	21.29	47.66	9.87	8.02	9.34	0.92	22.40	11.07	1.73
26000	20.86	48.38	9.42	7.72	10.38	0.92	21.22	11.06	1.81
26500	20.41	47.88	8.93	7.40	10.01	0.92	21.31	11.14	1.83
27000	19.97	48.01	8.52	7.20	10.41	0.92	21.83	11.15	1.99
27500	19.57	47.41	8.21	7.12	10.01	0.92	20.69	10.94	2.07
28000	19.25	46.14	7.97	7.34	8.98	0.95	22.33	11.16	2.16
28500	19.02	46.31	7.90	7.67	9.50	0.97	20.96	10.91	2.18
29000	18.76	45.49	7.85	8.18	9.10	0.99	21.06	10.91	2.18
29500	18.54	45.24	8.01	8.78	9.32	1.01	22.17	10.81	2.23
30000	18.34	45.90	8.17	9.27	10.56	1.02	20.56	11.16	2.27
31000	17.84	46.16	8.32	9.90	11.87	1.04	21.01	10.99	2.40

Typical Performance Data

Definitions:

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 3.75V, Id = 63mA @ Temperature = +25°C

FREQ	Gain	Isolation	Input Return Loss	Output Return Loss	Stability		IP-3 Output	1dB Comp. Output	Noise Figure
					K	Measure			
(MHz)	(dB)	(dB)	(dB)	(dB)	K	Measure	(dBm)	(dBm)	(dB)
9000	22.62	69.03	10.61	12.09	97.34	1.02	16.77	5.68	2.29
9500	23.98	63.57	11.73	12.29	45.72	1.00	17.71	6.89	2.01
10000	25.07	58.79	12.08	12.24	23.53	1.00	17.26	7.51	1.79
10500	25.97	61.72	11.43	12.26	29.46	1.01	18.68	7.76	1.82
11000	26.69	60.80	10.21	12.69	23.91	1.04	18.50	7.58	1.81
11500	27.33	59.90	9.02	13.80	19.58	1.08	18.21	7.91	1.80
12000	27.87	61.71	8.21	15.65	22.40	1.12	18.09	8.12	1.84
12500	28.24	60.56	7.95	18.12	18.86	1.14	18.30	7.76	1.91
13000	28.47	57.87	8.16	18.25	13.64	1.14	18.55	8.06	1.93
13500	28.55	57.74	8.96	15.14	13.53	1.09	19.12	8.38	1.92
14000	28.43	54.72	10.16	12.70	9.85	1.04	19.01	8.14	1.85
14500	28.22	53.46	11.74	11.23	8.86	0.98	19.91	8.75	1.78
15000	27.95	52.49	13.35	10.63	8.31	0.95	19.76	8.69	1.75
15500	27.70	51.88	14.90	10.56	8.10	0.94	20.65	8.73	1.64
16000	27.42	51.84	16.15	10.85	8.46	0.93	20.52	8.81	1.63
16500	27.13	50.57	16.35	11.32	7.64	0.94	20.88	8.72	1.60
17000	26.86	49.85	15.83	11.89	7.31	0.95	20.86	8.73	1.61
17500	26.59	49.13	15.05	12.22	6.96	0.96	20.51	8.36	1.61
18000	26.32	48.56	14.38	12.32	6.72	0.97	20.19	8.45	1.59
18500	26.08	48.74	14.12	12.06	7.03	0.97	20.07	8.71	1.59
19000	25.83	48.32	14.04	11.64	6.88	0.96	19.62	8.19	1.58
19500	25.64	47.76	14.32	11.26	6.60	0.95	20.67	8.28	1.53
20000	25.46	46.87	15.08	10.96	6.12	0.94	19.09	8.83	1.55
20500	25.23	46.84	16.10	10.72	6.28	0.93	19.41	8.91	1.53
21000	24.91	46.06	16.61	10.48	5.95	0.92	19.04	9.31	1.54
21500	24.35	46.39	16.11	9.90	6.49	0.91	20.51	10.03	1.55
22000	23.79	46.98	14.85	9.31	7.23	0.90	20.51	10.07	1.49
22500	23.38	46.88	13.56	9.01	7.35	0.90	20.98	10.20	1.58
23000	23.02	47.30	12.32	8.90	7.89	0.91	21.02	9.90	1.56
23500	22.65	47.13	11.34	8.85	7.95	0.92	20.82	10.35	1.61
24000	22.22	47.73	10.87	8.78	8.86	0.93	21.33	10.47	1.65
24500	21.77	47.15	10.48	8.58	8.60	0.93	20.20	10.67	1.73
25000	21.45	48.31	10.29	8.43	10.11	0.93	22.13	10.61	1.69
25500	21.08	48.15	9.85	8.08	10.11	0.92	21.54	10.50	1.74
26000	20.65	47.95	9.39	7.79	10.13	0.92	20.99	10.49	1.80
26500	20.21	47.15	8.90	7.45	9.45	0.92	21.77	10.57	1.87
27000	19.77	46.74	8.51	7.24	9.25	0.92	21.02	10.58	1.95
27500	19.37	46.81	8.19	7.16	9.58	0.93	21.77	10.38	2.07
28000	19.04	47.45	7.94	7.35	10.68	0.95	20.85	10.59	2.18
28500	18.81	45.90	7.85	7.72	9.30	0.97	23.86	10.34	2.17
29000	18.55	45.02	7.78	8.20	8.79	1.00	21.39	10.33	2.14
29500	18.33	45.46	7.93	8.79	9.78	1.01	21.76	10.21	2.23
30000	18.13	45.16	8.08	9.29	9.91	1.03	20.69	10.58	2.25
31000	17.62	46.59	8.21	9.90	12.74	1.04	21.48	10.41	2.43

Typical Performance Data

Definitions:

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 4.25V, Id = 73mA @ Temperature = +25°C

FREQ	Gain	Isolation	Input Return Loss	Output Return Loss	Stability		IP-3 Output	1dB Comp. Output	Noise Figure
					K	Measure			
(MHz)	(dB)	(dB)	(dB)	(dB)	K	Measure	(dBm)	(dBm)	(dB)
9000	23.16	63.93	10.31	11.90	50.30	1.02	18.43	6.94	2.24
9500	24.54	64.38	11.49	12.10	46.76	1.00	19.23	8.13	1.96
10000	25.64	64.95	11.98	12.07	44.52	1.00	18.54	8.62	1.80
10500	26.56	58.53	11.56	12.16	19.11	1.00	19.57	8.73	1.75
11000	27.30	59.77	10.49	12.61	19.91	1.03	19.54	8.58	1.75
11500	27.95	61.35	9.38	13.77	21.83	1.07	19.38	8.91	1.78
12000	28.48	63.04	8.63	15.65	24.72	1.11	19.37	9.24	1.80
12500	28.84	62.69	8.40	17.92	22.91	1.13	19.59	8.88	1.82
13000	29.02	60.77	8.65	17.67	18.17	1.12	19.69	9.13	1.88
13500	29.07	57.64	9.48	14.66	12.75	1.08	19.85	9.30	1.86
14000	28.92	56.45	10.72	12.39	11.46	1.02	20.17	9.04	1.79
14500	28.69	53.71	12.35	10.98	8.69	0.97	21.19	9.75	1.78
15000	28.41	54.31	13.99	10.46	9.74	0.94	21.39	9.69	1.73
15500	28.17	53.60	15.60	10.41	9.36	0.93	22.01	9.75	1.62
16000	27.89	51.75	16.96	10.71	7.95	0.93	21.65	9.83	1.65
16500	27.61	51.28	17.07	11.17	7.84	0.94	21.32	9.75	1.59
17000	27.35	50.42	16.43	11.71	7.38	0.95	22.03	9.77	1.54
17500	27.09	49.63	15.56	12.06	6.97	0.96	21.34	9.40	1.57
18000	26.82	49.92	14.84	12.16	7.41	0.96	21.20	9.51	1.57
18500	26.58	49.19	14.52	11.90	7.00	0.96	20.72	9.75	1.61
19000	26.33	48.70	14.49	11.48	6.79	0.95	21.13	9.12	1.58
19500	26.14	48.71	14.82	11.08	6.95	0.94	21.09	9.33	1.52
20000	25.95	47.19	15.60	10.79	6.00	0.93	20.60	9.86	1.59
20500	25.71	47.43	16.58	10.54	6.35	0.92	21.01	10.07	1.50
21000	25.37	47.13	16.84	10.28	6.36	0.91	20.01	10.32	1.57
21500	24.77	46.86	16.07	9.70	6.49	0.90	21.70	11.02	1.57
22000	24.19	46.84	14.70	9.12	6.75	0.90	21.01	11.05	1.50
22500	23.77	47.39	13.44	8.81	7.38	0.90	22.15	11.19	1.53
23000	23.41	47.58	12.22	8.73	7.74	0.91	23.43	10.87	1.53
23500	23.03	47.85	11.27	8.68	8.20	0.92	21.87	11.45	1.63
24000	22.60	47.81	10.85	8.61	8.51	0.92	21.75	11.57	1.62
24500	22.14	47.27	10.46	8.42	8.31	0.92	21.32	11.77	1.72
25000	21.81	47.98	10.32	8.28	9.30	0.92	22.88	11.71	1.70
25500	21.45	48.00	9.88	7.94	9.49	0.92	23.04	11.59	1.75
26000	21.02	48.09	9.44	7.65	9.84	0.91	21.31	11.59	1.82
26500	20.57	47.97	8.94	7.34	9.92	0.91	21.23	11.66	1.84
27000	20.13	47.29	8.55	7.14	9.44	0.91	22.38	11.68	1.92
27500	19.72	46.64	8.24	7.07	9.00	0.92	22.76	11.48	2.11
28000	19.42	46.74	8.00	7.28	9.42	0.94	22.08	11.68	2.15
28500	19.18	45.80	7.95	7.64	8.83	0.96	21.36	11.54	2.24
29000	18.93	45.56	7.90	8.17	9.00	0.99	21.89	11.45	2.21
29500	18.72	45.82	8.07	8.77	9.80	1.01	22.39	11.34	2.29
30000	18.52	45.42	8.24	9.26	9.82	1.02	21.58	11.60	2.31
31000	18.03	45.92	8.38	9.90	11.33	1.03	21.78	11.51	2.44

Typical Performance Data

Definitions:

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 4.00V, Id = 73.00mA @ Temperature = -45°C

FREQ	Gain	Isolation	Input Return Loss	Output Return Loss	Stability		IP-3 Output	1dB Comp. Output	Noise Figure
					K	Measure			
(MHz)	(dB)	(dB)	(dB)	(dB)	K	Measure	(dBm)	(dBm)	(dB)
9000	24.56	67.03	9.90	11.46	59.59	1.02	18.84	7.31	1.54
9500	25.87	62.49	11.18	11.61	31.52	1.00	19.52	8.32	1.29
10000	26.93	62.18	11.82	11.41	27.32	0.99	19.29	8.88	1.23
10500	27.80	62.33	11.54	11.21	25.01	0.99	20.33	8.94	1.18
11000	28.52	61.71	10.54	11.47	21.10	1.01	20.38	8.80	1.14
11500	29.15	60.70	9.34	12.37	17.13	1.05	20.09	9.14	1.21
12000	29.70	66.80	8.43	14.11	32.12	1.10	19.93	9.35	1.24
12500	30.07	63.48	8.05	16.41	21.05	1.13	20.04	9.13	1.22
13000	30.29	60.25	8.29	16.70	14.35	1.13	20.42	9.25	1.28
13500	30.36	57.29	9.18	13.88	10.26	1.08	20.68	9.60	1.30
14000	30.20	58.82	10.50	11.68	12.64	1.02	21.19	9.30	1.19
14500	29.98	54.64	12.10	10.38	8.12	0.96	21.70	9.90	1.15
15000	29.67	54.55	13.79	9.83	8.41	0.93	21.85	9.85	1.08
15500	29.41	52.79	15.26	9.79	7.18	0.92	22.17	10.02	1.01
16000	29.13	52.65	16.32	9.99	7.39	0.91	22.34	10.12	1.08
16500	28.84	51.27	17.01	10.29	6.60	0.92	22.91	9.87	1.00
17000	28.60	50.00	16.97	10.79	5.95	0.93	22.88	9.89	0.96
17500	28.36	50.34	16.35	11.26	6.39	0.94	22.12	9.55	0.96
18000	28.11	49.46	15.20	11.50	5.94	0.95	21.67	9.48	1.00
18500	27.88	49.57	14.10	11.51	6.16	0.95	21.25	9.75	0.95
19000	27.65	49.10	13.66	11.32	5.97	0.95	21.09	9.29	0.94
19500	27.48	48.56	13.62	11.10	5.73	0.95	21.14	9.26	0.97
20000	27.35	47.67	14.29	10.73	5.28	0.93	21.71	9.99	0.94
20500	27.18	46.76	16.16	10.32	4.89	0.91	21.33	10.08	0.94
21000	26.90	46.07	17.57	9.94	4.66	0.90	20.88	10.36	0.96
21500	26.27	46.58	16.71	9.23	5.17	0.88	21.75	11.05	0.92
22000	25.60	46.68	14.32	8.55	5.44	0.88	21.78	11.06	0.94
22500	25.14	47.14	12.34	8.28	5.85	0.88	22.17	11.21	0.98
23000	24.87	47.51	11.79	8.49	6.30	0.90	23.13	10.86	0.97
23500	24.57	47.07	11.07	8.64	6.17	0.91	22.41	11.38	0.98
24000	24.15	48.08	11.19	8.57	7.27	0.91	23.02	11.52	1.07
24500	23.66	47.40	10.76	8.07	6.93	0.90	22.44	11.62	1.10
25000	23.33	47.68	10.61	7.62	7.28	0.88	23.14	11.52	1.02
25500	22.84	47.50	9.43	7.09	7.14	0.88	23.03	11.34	1.12
26000	22.38	48.14	8.65	6.88	7.80	0.89	21.96	11.30	1.18
26500	21.98	47.51	8.31	6.76	7.45	0.90	23.35	11.43	1.25
27000	21.64	48.26	8.11	6.84	8.41	0.91	21.46	11.54	1.31
27500	21.33	47.56	8.30	6.77	8.03	0.90	21.90	11.33	1.37
28000	21.06	47.02	8.46	6.91	7.90	0.91	22.06	11.54	1.37
28500	20.67	45.89	8.16	6.82	7.13	0.91	22.98	11.25	1.46
29000	20.24	45.57	7.77	6.88	7.07	0.93	22.12	11.21	1.53
29500	19.91	45.60	7.62	7.38	7.48	0.97	25.21	11.07	1.64
30000	19.73	45.30	7.57	8.25	7.66	1.01	21.93	11.47	1.69
31000	19.49	45.56	8.29	9.81	8.91	1.04	22.22	11.46	1.66

Typical Performance Data

Definitions:

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 3.75V, Id = 68mA @ Temperature = -45°C

FREQ	Gain	Isolation	Input Return Loss	Output Return Loss	Stability		IP-3 Output	1dB Comp. Output	Noise Figure
					K	Measure			
(MHz)	(dB)	(dB)	(dB)	(dB)	K	Measure	(dBm)	(dBm)	(dB)
9000	24.29	68.38	10.06	11.57	72.23	1.02	18.06	6.53	1.60
9500	25.60	63.80	11.31	11.71	38.02	1.00	19.06	7.67	1.25
10000	26.64	60.10	11.91	11.49	22.32	0.99	18.48	8.37	1.20
10500	27.50	58.31	11.51	11.33	16.34	0.99	19.99	8.43	1.14
11000	28.22	60.24	10.42	11.54	18.42	1.01	19.43	8.15	1.13
11500	28.85	62.25	9.18	12.40	21.11	1.06	19.65	8.61	1.20
12000	29.39	63.00	8.24	14.12	21.33	1.11	19.81	8.81	1.25
12500	29.77	61.08	7.85	16.49	16.40	1.14	19.72	8.48	1.27
13000	30.00	61.84	8.06	16.95	17.67	1.13	19.66	8.74	1.32
13500	30.09	59.07	8.93	14.10	12.92	1.09	20.26	9.10	1.32
14000	29.94	57.13	10.18	11.83	10.67	1.02	20.48	8.82	1.15
14500	29.73	55.13	11.81	10.49	8.80	0.97	21.83	9.43	1.17
15000	29.43	54.66	13.49	9.90	8.73	0.93	20.82	9.38	1.14
15500	29.17	52.70	14.98	9.86	7.30	0.92	21.96	9.42	1.11
16000	28.89	52.91	16.03	10.06	7.82	0.92	21.78	9.65	1.03
16500	28.61	51.16	16.63	10.38	6.70	0.92	21.85	9.40	1.04
17000	28.35	50.53	16.52	10.85	6.48	0.93	22.93	9.28	0.98
17500	28.11	49.78	15.94	11.34	6.16	0.94	21.68	9.05	1.00
18000	27.86	49.51	14.94	11.58	6.15	0.95	21.57	8.87	1.01
18500	27.62	49.05	13.96	11.57	5.97	0.96	21.36	9.14	1.00
19000	27.39	48.48	13.51	11.39	5.72	0.96	21.92	8.65	0.99
19500	27.23	48.67	13.54	11.17	5.97	0.95	22.48	8.76	0.94
20000	27.10	47.24	14.16	10.80	5.18	0.93	21.76	9.36	1.00
20500	26.93	46.64	15.81	10.41	4.96	0.92	21.53	9.47	0.93
21000	26.66	46.22	17.15	10.05	4.87	0.90	20.23	9.75	1.00
21500	26.05	46.53	16.74	9.35	5.29	0.89	21.85	10.45	0.96
22000	25.40	46.51	14.49	8.68	5.48	0.88	21.22	10.47	0.94
22500	24.95	46.79	12.53	8.39	5.79	0.89	21.95	10.62	0.98
23000	24.67	47.37	11.86	8.57	6.37	0.90	24.75	10.28	0.98
23500	24.37	46.74	11.08	8.72	6.10	0.92	21.69	10.79	0.96
24000	23.95	47.39	11.16	8.64	6.88	0.92	21.00	10.93	0.97
24500	23.46	47.10	10.76	8.17	6.87	0.90	21.53	11.03	1.06
25000	23.14	47.71	10.54	7.71	7.46	0.89	23.96	10.94	1.02
25500	22.66	47.59	9.51	7.18	7.41	0.89	23.16	10.74	1.14
26000	22.21	47.45	8.75	6.96	7.41	0.89	22.02	10.70	1.16
26500	21.79	47.16	8.34	6.82	7.34	0.90	22.56	10.82	1.30
27000	21.45	46.18	8.11	6.89	6.78	0.91	23.52	10.86	1.27
27500	21.13	46.14	8.21	6.79	7.00	0.90	22.36	10.76	1.34
28000	20.84	45.81	8.32	6.96	7.03	0.91	20.85	10.96	1.29
28500	20.47	45.23	8.08	6.86	6.72	0.92	22.49	10.67	1.51
29000	20.05	45.43	7.78	6.95	7.13	0.94	22.12	10.53	1.54
29500	19.73	44.42	7.63	7.43	6.67	0.97	22.44	10.48	1.63
30000	19.54	45.04	7.59	8.26	7.60	1.01	21.37	10.77	1.68
31000	19.27	45.55	8.21	9.81	9.09	1.04	23.11	10.76	1.67

Typical Performance Data

Definitions:

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 4.25V, Id = 78mA @ Temperature = -45°C

FREQ	Gain	Isolation	Input Return Loss	Output Return Loss	Stability		IP-3 Output	1dB Comp. Output	Noise Figure
					K	Measure			
(MHz)	(dB)	(dB)	(dB)	(dB)	K	Measure	(dBm)	(dBm)	(dB)
9000	24.79	64.81	9.78	11.38	44.71	1.03	19.35	7.92	1.50
9500	26.11	64.92	11.05	11.54	40.43	1.00	20.01	8.91	1.31
10000	27.17	63.81	11.76	11.31	31.96	0.99	19.73	9.47	1.19
10500	28.05	60.06	11.56	11.16	18.74	0.98	21.32	9.53	1.14
11000	28.78	60.47	10.63	11.42	17.78	1.01	20.56	9.27	1.15
11500	29.42	62.26	9.47	12.34	19.94	1.05	20.58	9.62	1.17
12000	29.97	62.74	8.59	14.13	19.61	1.10	20.93	9.95	1.20
12500	30.34	65.22	8.24	16.37	25.16	1.12	21.19	9.61	1.19
13000	30.54	60.98	8.51	16.49	15.28	1.12	20.71	9.71	1.31
13500	30.59	60.46	9.45	13.67	14.51	1.07	21.80	10.04	1.23
14000	30.42	58.50	10.77	11.55	11.92	1.01	21.53	9.86	1.22
14500	30.18	55.21	12.39	10.29	8.48	0.95	22.39	10.45	1.15
15000	29.87	54.38	14.08	9.77	8.07	0.92	22.01	10.39	1.02
15500	29.61	52.51	15.57	9.76	6.81	0.91	22.48	10.44	1.00
16000	29.33	52.34	16.62	9.92	6.97	0.91	23.27	10.68	0.97
16500	29.06	51.95	17.37	10.25	6.96	0.91	23.82	10.43	0.98
17000	28.81	50.54	17.37	10.71	6.17	0.92	24.00	10.45	0.97
17500	28.58	49.96	16.67	11.18	5.97	0.93	22.94	10.11	0.97
18000	28.33	50.69	15.51	11.41	6.65	0.95	22.47	10.05	0.95
18500	28.10	49.67	14.29	11.43	6.07	0.95	22.25	10.33	0.99
19000	27.87	48.97	13.82	11.26	5.73	0.95	22.71	9.87	0.92
19500	27.71	48.19	13.74	11.05	5.35	0.94	22.14	9.84	0.91
20000	27.57	47.98	14.47	10.66	5.33	0.93	22.16	10.56	0.95
20500	27.39	47.05	16.48	10.23	4.93	0.91	22.03	10.65	0.87
21000	27.10	46.51	17.91	9.84	4.78	0.89	20.92	10.91	0.97
21500	26.45	47.06	16.60	9.10	5.32	0.88	22.03	11.59	0.91
22000	25.78	46.48	14.19	8.46	5.19	0.87	22.57	11.60	1.00
22500	25.31	47.50	12.21	8.20	5.95	0.88	22.37	11.77	0.99
23000	25.04	47.75	11.75	8.42	6.33	0.90	23.01	11.41	0.93
23500	24.75	48.04	11.05	8.58	6.73	0.91	22.33	11.92	0.99
24000	24.33	48.46	11.22	8.50	7.42	0.91	23.31	12.08	1.01
24500	23.83	47.47	10.75	7.99	6.84	0.90	22.93	12.15	1.08
25000	23.50	48.05	10.62	7.53	7.41	0.88	23.44	12.06	1.05
25500	22.99	47.43	9.37	7.02	6.94	0.88	23.20	11.88	1.20
26000	22.54	47.91	8.61	6.82	7.43	0.89	22.55	11.93	1.21
26500	22.15	47.63	8.29	6.72	7.39	0.89	23.96	11.97	1.28
27000	21.82	47.56	8.12	6.81	7.59	0.90	24.06	12.07	1.31
27500	21.51	45.27	8.35	6.74	6.08	0.90	23.37	11.86	1.38
28000	21.24	46.60	8.54	6.88	7.38	0.90	21.35	12.08	1.37
28500	20.84	45.74	8.21	6.75	6.83	0.91	22.56	11.78	1.44
29000	20.41	46.14	7.82	6.85	7.41	0.93	21.46	11.74	1.57
29500	20.08	45.38	7.63	7.36	7.15	0.96	21.07	11.60	1.66
30000	19.91	45.36	7.59	8.26	7.57	1.01	21.55	12.03	1.70
31000	19.69	45.60	8.37	9.85	8.78	1.04	22.83	12.01	1.80

Typical Performance Data

Definitions:

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 4.00V, Id = 65mA @ Temperature = +85°C

FREQ	Gain	Isolation	Input Return Loss	Output Return Loss	Stability		IP-3 Output	1dB Comp. Output	Noise Figure
					K	Measure			
(MHz)	(dB)	(dB)	(dB)	(dB)	K	Measure	(dBm)	(dBm)	(dB)
9000	21.52	75.40	11.12	12.64	236.03	1.02	16.60	5.42	2.88
9500	22.94	63.90	12.20	12.86	54.77	1.00	17.52	6.66	2.56
10000	24.07	59.56	12.40	12.85	29.39	1.00	17.28	7.31	2.45
10500	24.98	58.23	11.47	12.98	22.48	1.02	18.39	7.44	2.29
11000	25.72	61.37	10.18	13.58	29.03	1.05	18.27	7.30	2.35
11500	26.39	60.91	8.97	14.82	24.92	1.09	18.14	7.65	2.34
12000	26.90	60.85	8.28	17.42	23.16	1.13	17.77	7.97	2.40
12500	27.27	61.64	8.06	20.29	24.36	1.15	18.72	7.63	2.37
13000	27.53	60.61	8.37	18.92	21.25	1.13	18.35	7.92	2.43
13500	27.59	58.01	9.28	15.34	15.93	1.09	18.97	8.23	2.40
14000	27.47	55.28	10.61	12.90	11.99	1.03	18.99	8.00	2.39
14500	27.30	54.80	11.97	11.77	11.76	0.99	19.98	8.61	2.33
15000	27.04	53.77	13.45	11.28	10.92	0.96	19.84	8.58	2.28
15500	26.79	52.04	14.97	11.32	9.38	0.95	20.64	8.63	2.29
16000	26.52	50.76	16.04	11.61	8.47	0.95	20.83	8.72	2.22
16500	26.23	51.12	16.20	11.95	9.20	0.95	20.85	8.63	2.15
17000	25.97	49.89	15.67	12.36	8.27	0.96	20.53	8.63	2.13
17500	25.67	49.89	14.96	12.66	8.57	0.97	19.95	8.38	2.08
18000	25.40	49.14	14.37	12.69	8.11	0.97	19.84	8.34	2.12
18500	25.14	49.29	14.11	12.42	8.48	0.97	19.75	8.70	2.11
19000	24.89	49.32	14.15	11.94	8.74	0.97	19.63	8.19	2.12
19500	24.68	48.47	14.68	11.47	8.13	0.95	20.09	8.27	2.10
20000	24.45	47.38	15.95	11.01	7.41	0.94	19.94	8.91	2.07
20500	24.19	46.95	17.16	10.66	7.27	0.92	19.67	8.97	2.10
21000	23.79	46.20	16.88	10.24	6.92	0.91	19.06	9.31	2.12
21500	23.22	46.09	15.43	9.82	7.18	0.91	20.81	10.02	2.11
22000	22.70	46.97	14.28	9.39	8.26	0.91	20.55	10.11	2.11
22500	22.32	47.23	13.29	9.34	8.79	0.92	21.62	10.15	2.17
23000	22.00	47.54	12.40	9.47	9.40	0.93	21.72	9.84	2.15
23500	21.65	47.56	11.73	9.57	9.76	0.94	21.21	10.31	2.15
24000	21.25	48.18	11.40	9.51	10.92	0.95	21.30	10.58	2.22
24500	20.78	47.29	11.03	9.15	10.24	0.94	21.00	10.77	2.25
25000	20.38	48.17	10.77	8.73	11.66	0.93	22.23	10.67	2.28
25500	20.00	47.96	10.18	8.29	11.56	0.93	21.98	10.56	2.32
26000	19.56	47.81	9.55	7.96	11.64	0.93	20.93	10.55	2.41
26500	19.13	48.14	8.95	7.73	12.34	0.93	21.96	10.65	2.52
27000	18.70	46.85	8.46	7.63	10.94	0.94	21.61	10.66	2.58
27500	18.31	46.55	8.05	7.62	10.86	0.95	21.31	10.55	2.70
28000	18.01	46.53	7.86	7.87	11.23	0.97	20.05	10.85	2.59
28500	17.75	46.33	7.75	8.21	11.41	0.99	21.88	10.50	2.85
29000	17.55	46.11	7.87	8.72	11.68	1.01	20.28	10.40	2.83
29500	17.36	45.54	7.88	9.45	11.47	1.04	20.81	10.32	2.98
30000	17.16	45.65	8.06	10.21	12.27	1.05	21.26	10.71	3.00
31000	16.76	46.09	8.55	11.18	14.17	1.06	21.29	10.70	3.15

Typical Performance Data

Definitions:

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 3.75V, Id = 60mA @ Temperature = +85°C

FREQ	Gain	Isolation	Input Return Loss	Output Return Loss	Stability		IP-3 Output	1dB Comp. Output	Noise Figure
					K	Measure			
(MHz)	(dB)	(dB)	(dB)	(dB)	K	Measure	(dBm)	(dBm)	(dB)
9000	21.22	66.65	11.27	12.74	89.59	1.02	16.30	4.77	2.99
9500	22.63	63.04	12.32	12.98	51.53	1.00	16.87	6.15	2.59
10000	23.76	61.99	12.42	12.92	40.37	1.00	16.60	6.81	2.44
10500	24.65	58.80	11.37	13.06	24.90	1.02	18.22	6.94	2.40
11000	25.39	59.15	10.02	13.63	23.26	1.05	17.66	6.79	2.31
11500	26.06	62.13	8.78	14.83	29.63	1.10	17.54	7.14	2.34
12000	26.57	60.81	8.07	17.37	23.73	1.14	17.52	7.47	2.46
12500	26.96	60.39	7.82	20.43	21.64	1.16	17.65	7.26	2.38
13000	27.23	59.82	8.12	19.31	19.89	1.14	17.75	7.44	2.51
13500	27.31	56.99	9.00	15.67	14.50	1.10	18.38	7.77	2.46
14000	27.21	54.43	10.31	13.10	11.15	1.04	18.31	7.55	2.39
14500	27.05	54.37	11.65	11.89	11.47	1.00	19.39	8.17	2.36
15000	26.80	53.32	13.11	11.38	10.64	0.97	19.27	8.15	2.28
15500	26.55	51.56	14.60	11.39	9.12	0.96	19.84	8.19	2.18
16000	26.27	50.97	15.64	11.67	8.93	0.95	19.73	8.28	2.23
16500	25.98	50.45	15.87	12.04	8.77	0.96	19.82	8.17	2.15
17000	25.71	50.01	15.38	12.46	8.64	0.97	19.92	8.18	2.13
17500	25.40	49.15	14.71	12.77	8.11	0.97	19.66	7.93	2.13
18000	25.14	49.07	14.15	12.81	8.28	0.98	19.38	7.89	2.13
18500	24.88	49.33	13.89	12.52	8.78	0.98	19.52	8.24	2.04
19000	24.62	48.33	13.91	12.05	8.04	0.97	19.10	7.61	2.13
19500	24.42	48.04	14.42	11.55	7.97	0.96	19.93	7.81	2.04
20000	24.20	47.16	15.66	11.11	7.44	0.94	19.14	8.33	2.17
20500	23.95	46.88	16.89	10.76	7.42	0.93	19.39	8.53	2.05
21000	23.56	45.86	16.78	10.37	6.86	0.92	18.58	8.87	2.13
21500	23.01	46.22	15.46	9.93	7.49	0.91	20.22	9.46	2.12
22000	22.50	46.44	14.36	9.51	7.99	0.91	19.61	9.55	2.17
22500	22.12	46.86	13.36	9.45	8.66	0.92	20.37	9.71	2.15
23000	21.80	47.22	12.41	9.57	9.30	0.93	20.32	9.29	2.10
23500	21.45	47.19	11.76	9.65	9.60	0.94	20.19	9.75	2.24
24000	21.05	47.08	11.43	9.59	9.89	0.95	20.69	10.03	2.43
24500	20.59	47.46	11.03	9.24	10.70	0.94	20.78	10.23	2.32
25000	20.20	47.98	10.75	8.83	11.68	0.94	21.96	10.13	2.31
25500	19.82	48.01	10.17	8.37	11.92	0.93	21.90	10.02	2.40
26000	19.37	48.10	9.54	8.04	12.31	0.93	20.58	10.01	2.42
26500	18.95	48.31	8.94	7.79	12.88	0.94	20.60	10.10	2.54
27000	18.52	47.54	8.46	7.67	12.11	0.94	21.61	10.21	2.57
27500	18.13	48.37	8.03	7.66	13.67	0.96	20.67	10.00	2.66
28000	17.82	46.91	7.84	7.91	12.01	0.98	22.38	10.19	2.78
28500	17.56	46.47	7.71	8.25	11.87	1.00	20.72	9.94	2.83
29000	17.35	46.67	7.81	8.76	12.74	1.02	20.48	9.85	2.90
29500	17.16	45.42	7.80	9.44	11.52	1.04	21.26	9.75	2.93
30000	16.96	46.38	7.97	10.18	13.61	1.05	20.09	10.15	2.99
31000	16.55	46.88	8.44	11.12	15.81	1.06	20.55	10.13	3.10

Typical Performance Data

Definitions:

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)









Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)








TEST CONDITIONS: Vd = 4.25V, Id = 69mA @ Temperature = +85°C

FREQ	Gain	Isolation	Input Return Loss	Output Return Loss	Stability		IP-3 Output	1dB Comp. Output	Noise Figure
					K	Measure			
(MHz)	(dB)	(dB)	(dB)	(dB)	K	Measure	(dBm)	(dBm)	(dB)
9000	21.77	64.96	10.97	12.54	68.57	1.02	17.19	6.02	2.88
9500	23.20	63.83	12.09	12.78	52.61	1.01	17.87	7.24	2.58
10000	24.34	60.01	12.38	12.74	29.97	1.00	17.64	7.76	2.45
10500	25.25	59.37	11.54	12.93	24.84	1.01	18.78	7.88	2.35
11000	26.00	59.24	10.31	13.57	22.07	1.05	18.85	7.75	2.30
11500	26.67	61.05	9.14	14.84	24.67	1.09	18.92	8.11	2.34
12000	27.17	60.87	8.48	17.46	22.65	1.12	18.67	8.42	2.36
12500	27.54	60.80	8.26	20.19	21.63	1.14	18.72	8.07	2.40
13000	27.78	59.41	8.59	18.63	18.12	1.12	18.94	8.34	2.40
13500	27.82	58.23	9.53	15.11	16.00	1.08	19.50	8.63	2.46
14000	27.68	56.75	10.90	12.77	13.93	1.02	19.55	8.39	2.39
14500	27.51	54.46	12.27	11.66	11.06	0.99	20.08	8.99	2.31
15000	27.25	54.19	13.76	11.20	11.20	0.96	20.41	8.85	2.31
15500	27.00	52.67	15.30	11.24	9.85	0.95	20.81	9.03	2.23
16000	26.73	51.64	16.37	11.52	9.16	0.95	21.41	9.11	2.22
16500	26.44	51.28	16.50	11.88	9.15	0.95	21.48	9.03	2.17
17000	26.18	49.83	15.93	12.27	8.02	0.96	21.46	9.02	2.14
17500	25.88	50.13	15.20	12.58	8.60	0.97	20.68	8.79	2.07
18000	25.62	49.53	14.59	12.60	8.27	0.97	20.71	8.87	2.13
18500	25.36	49.86	14.32	12.33	8.83	0.97	20.25	9.10	2.10
19000	25.10	48.88	14.34	11.87	8.11	0.96	20.66	8.60	2.11
19500	24.89	48.29	14.92	11.40	7.79	0.95	20.80	8.68	2.09
20000	24.65	47.36	16.21	10.92	7.21	0.93	20.34	9.31	2.15
20500	24.39	48.08	17.39	10.57	8.07	0.92	20.07	9.37	2.06
21000	23.98	46.71	16.94	10.15	7.17	0.91	19.57	9.69	2.08
21500	23.39	46.42	15.37	9.72	7.29	0.91	21.28	10.39	2.12
22000	22.87	47.27	14.20	9.30	8.35	0.91	20.77	10.48	2.03
22500	22.48	47.52	13.21	9.27	8.89	0.91	21.58	10.65	2.11
23000	22.17	47.40	12.34	9.40	9.06	0.93	22.55	10.20	2.12
23500	21.81	47.46	11.72	9.49	9.45	0.94	21.26	10.80	2.15
24000	21.40	48.18	11.40	9.45	10.71	0.94	21.17	11.08	2.23
24500	20.93	48.19	11.03	9.08	11.13	0.94	21.25	11.27	2.27
25000	20.53	48.09	10.79	8.66	11.34	0.93	22.24	11.17	2.27
25500	20.15	48.33	10.20	8.23	11.86	0.92	21.78	11.06	2.30
26000	19.71	48.71	9.57	7.90	12.66	0.92	20.98	11.06	2.44
26500	19.28	48.52	8.97	7.69	12.67	0.93	21.04	11.25	2.54
27000	18.85	47.80	8.51	7.60	11.98	0.94	22.78	11.26	2.61
27500	18.47	47.06	8.08	7.57	11.33	0.95	22.64	11.05	2.70
28000	18.17	45.80	7.88	7.83	10.11	0.97	22.39	11.26	2.91
28500	17.90	46.70	7.81	8.18	11.73	0.99	22.51	11.01	2.88
29000	17.70	46.56	7.95	8.71	12.14	1.01	20.95	10.91	2.90
29500	17.53	46.47	7.95	9.44	12.58	1.03	22.14	10.82	2.98
30000	17.32	46.93	8.13	10.21	14.01	1.05	21.13	11.21	2.93
31000	16.93	47.55	8.61	11.18	16.49	1.06	21.34	11.20	2.96


Typical Performance Curves




Typical Performance Curves



Outline Dimensions



PCB Land Pattern



SUGGESTED LAYOUT,
TOLERANCE TO BE WITHIN $\pm .002$

Weight: .02 Grams

Dimensions are in inches (mm). Tolerances: 2Pl. $\pm .01$; 3 Pl. $\pm .004$

Notes:

1. Case material: Plastic.
2. Termination finish:
 - For RoHS Case Styles: Tin-Silver alloy plate over Nickel barrier or Matte-Tin. All models, (+) suffix. See Data sheet.
 - For RoHS-5 Case Styles: Tin-Lead plate. All models, no (+) suffix.

Mini-Circuits®


Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified

INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Tape & Reel Packaging TR-F66



Tape Width, mm	Device Cavity Pitch, mm	Reel Size, inches	Devices per Reel see note	
8	4	7	Small quantity standard	20
				50
				100
				200
				500
		7	Standard	1000, 2000, 3000

Note: Please consult individual model data sheet to determine device per reel availability.

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: www.minicircuits.com/pages/pdfs/tape.pdf

Mini-Circuits®


INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified


THIRD ANGLE PROJECTION



REVISIONS

REV	ECN No.	DESCRIPTION	DATE	DR	AUTH
OR	ECO-002696	NEW RELEASE	05/27/20	ITG	CC
A	ECO-011382	UPDATED LAYOUT AND NEW R1 SIZE	01/12/22	ITG	IL

SUGGESTED MOUNTING CONFIGURATION
FOR DQ1225 CASE STYLE



COMPONENT	SIZE
R1	0603
C2,C2	0402

NOTES:

1. TRACE WIDTH & GAP PARAMETERS ARE SHOWN FOR ROGERS R04350B WITH DIELECTRIC THICKNESS $.0066" \pm .0007"$. COPPER: 1 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH & GAP MAY NEED TO BE MODIFIED.
2. CHIP COMPONENT FOOT PRINTS SHOWN FOR REFERENCE. FOR COMPONENT VALUES REFER TO TB-PMA3-223GLNC+; TB-PMA3-313GLNC+; TB-PMA3-346GLNC+.
3. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.

- DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER).
- DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK.

UNLESS OTHERWISE SPECIFIED	INITIALS	DATE
DIMENSIONS ARE IN INCHES	DRAWN ITG	05/27/20
TOLERANCES ON:	CHECKED GF	05/27/20
2 PL DECIMALS \pm	APPROVED CC	05/27/20
3 PL DECIMALS \pm .005		
ANGLES \pm		
FRACTIONS \pm		

Mini-Circuits[®] 13 Neptune Avenue
Brooklyn NY 11235

PL. DQ1225, TB-PMA3-XXXGLNC+



SIZE	CODE IDENT	DRAWING NO:	REV:
A	15542	98-PL-674	A
FILE:	98PL674	SCALE: 8:1	SHEET: 1 OF 1

Mini-Circuits[®]


THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.

Evaluation Board and Circuit

SEE DETAIL "A"



DETAIL "A"
(SCALE 3:1)



SCHEMATIC DIAGRAM

Component	Size	Value	Part Number	Manufacturer
R1	0603	180hm	SG73G1JTTD18R0C	Koa Speer
C1	0402	5pF	GJM1555C1H5R0CB01D	Murata
C2	0402	0.1uF	GRM155R71C104KA88D	Murata



Notes:

- 2.4mm Female Connectors,
- PCB Material: Roger R04350B or equivalent,
Dielectric constant=3.5, Thickness=0.0066 inch


 **Mini-Circuits®**

Evaluation Board and Circuit

SEE DETAIL "A"



DETAIL "A"
(SCALE 3:1)



SCHEMATIC DIAGRAM

Component	Size	Value	Part Number	Manufacturer
R1	0603	180hm	SG73G1JTTD18R0C	Koa Speer
C1	0402	5pF	GJM1555C1H5R0CB01D	Murata
C2	0402	0.1uF	GRM155R71C104KA88D	Murata

Notes:

- 2.4mm Female Connectors,
- PCB Material: Roger RO4350B or equivalent,
Dielectric constant=3.5, Thickness=0.0066 inch.

 Mini-Circuits®

All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-40° to 85°C or -45° to 85°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C or -65° to 150° Ambient Environment	Individual Model Data Sheet
Thermal Shock	-55° to 100°C, 100 cycles	MIL-STD-202, Method 107, Condition A-3, except +100°C
Mechanical Shock	1.5Kg, 0.5 ms, 5 shock pulses, Y1 direction only	MIL-STD-883, Method 2002, Condition B, except Y1 direction only
Vibration (Variable Frequency)	50g peak	MIL-STD-883, Method 2007, Condition B
Autoclave	15 psig, 100% RH, 121°C, 96 hours	JESD22-A102, Condition C
HAST	130°C, 85% RH, 96 hours	JESD22-A110
Solderability	10X Magnification	J-STD-002, Para 4.2.5, Test S, 95% Coverage
Solder Reflow Heat	Sn-Pb Eutetic Process: 240°C peak Pb-Free Process: 260°C peak	J-STD-020, Table 4-1, 4-2 and 5-2; Figure 5-1
Moisture Sensitivity: Level 1	Bake at 125°C for 24 hours Soak at 85°C/85% RH for 168 hours, Reflow 3 cycles at 260°C peak	J-STD-020
Marking Resistance to Solvents	Isopropyl alcohol + mineral spirits at 25°C; terpene defluxer at 25°C; distilled water + proylene glycol monomethyl ether +	MIL-STD-202, Method 215



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
	monoethanolamine at 63°C to 70°C	