

Surface Mount Frequency Mixer

RMS-1MH+

Level 13 (LO Power +13 dBm) 2 to 500 MHz



Generic photo used for illustration purposes only

CASE STYLE: TT240

+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

Maximum Ratings

Operating Temperature	-40°C to 85°C
Storage Temperature	-55°C to 100°C
RF Power	200mW
IF Current	40mA
Permanent damage may occur if any of these limits are exceeded.	

Pin Connections

LO	1
RF	4
IF	5
GROUND	2,3,6


Features

- excellent L-R isolation, 44 dB typ.
- conversion loss, 5.65 dB typ.
- small size, 0.25"x0.31"x0.2"

Applications

- HF & VHF communications
- intermediate frequency for down converters


Outline Drawing



Outline Dimensions (inch)

A	B	C	D	E	F
.250	.31	.20	.100	.050	.055
6.35	7.87	5.08	2.54	1.27	1.40
G	H	J	K	wt	
.040	.070	.270	.050	grams	
1.02	1.78	6.86	1.27	0.50	

Demo Board MCL P/N: TB-03 Suggested PCB Layout (PL-052)



- NOTES: 1. TRACE WIDTH IS SHOWN FOR ROGERS R04350B WITH DIELECTRIC THICKNESS .030" ± .002"; COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.

- DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)
- DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuit's standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuit's website at www.minicircuits.com/MCLStore/terms.jsp

Electrical Specifications

FREQUENCY (MHz)	CONVERSION LOSS (dB)	LO-RF ISOLATION (dB)						LO-IF ISOLATION (dB)						IP3 at center band (dBm)
		L		M		U		L		M		U		
$f_L - f_U$	\bar{X} σ Max.	Typ.	Min.	Typ.	Min.	Typ.	Min.	Typ.	Min.	Typ.	Min.	Typ.	Min.	Typ.
2-500 DC-500	6.07 .16 7.0 8.0	58	45	44	25	30	20	55	40	36	25	28	17	26

1 dB COMP: +9 dBm typ.
For phase detection, DC output positive with in-phase RF & LO.


L = low range [f_L to 10 f_L]
m = mid band [2 f_L to $f_U/2$]

M = mid range [10 f_L to $f_U/2$] U = upper range [$f_U/2$ to f_U]

Typical Performance Data

Frequency (MHz)		Conversion Loss (dB)	VSWR RF Port (:1)	Frequency (MHz)	Isolation L-R (dB)	Isolation L-I (dB)	VSWR LO Port (:1)
RF	LO	LO +13dBm	LO +13dBm		LO +13dBm	LO +13dBm	LO +13dBm
2.10	32.10	6.68	2.42	10.50	95.44	63.71	1.79
4.10	34.10	6.36	2.54	14.50	90.48	60.97	1.80
6.10	36.10	6.32	2.59	20.50	85.55	57.99	1.78
10.10	40.10	6.28	2.60	24.50	81.96	56.51	1.78
14.10	44.10	6.27	2.57	30.50	79.59	54.62	1.78
18.10	48.10	6.26	2.53	35.00	77.37	53.48	1.79
20.10	50.10	6.22	2.52	40.10	75.20	52.34	1.79
25.10	55.10	6.20	2.48	50.10	71.74	50.40	1.79
50.10	80.10	6.14	2.29	80.10	64.50	46.30	1.78
100.10	130.10	6.13	1.89	105.10	60.46	43.60	1.77
125.10	155.10	6.11	1.71	155.10	55.39	40.81	1.80
150.10	180.10	6.07	1.56	205.10	51.72	39.49	1.79
175.10	205.10	6.16	1.45	255.10	49.15	38.65	1.84
200.10	230.10	6.18	1.41	305.10	46.78	37.95	1.88
250.10	280.10	6.16	1.39	330.10	46.50	37.64	1.91
300.10	330.10	6.24	1.41	355.10	45.71	37.18	1.90
350.10	380.10	6.31	1.41	405.10	43.38	35.68	1.95
400.10	430.10	6.37	1.42	430.10	42.53	34.62	1.96
425.10	455.10	6.50	1.44	455.10	41.47	33.69	1.93
500.00	470.00	6.51	1.70	470.00	40.85	33.01	1.96







Electrical Schematic



Mini-Circuits

www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

REV. E
M154339
RMS-1MH+
200815
Page 1 of 2



Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



Frequency Mixer

RMS-1MH+

Typical Performance Data

RF (IN) (MHz)	LO (MHz)	CONVERSION LOSS IF FIXED @IF(OUT)=30MHz (dB)			RF (IN) (MHz)	LO (MHz)	IP3 INPUT (dBm)			RF (IN) (MHz)	LO (MHz)	COMPRESSION @RF IN=+9dBm (dB)		
		@LO (dBm)					@LO (dBm)					@LO (dBm)		
		+10	+13	+16			+10	+13	+16			+10	+13	+16
2.0	32.0	7.33	6.87	6.69	10.1	40.1	22.39	34.79	28.91	10.1	40.1	1.04	0.72	0.48
5.0	35.0	6.39	5.99	5.81	49.6	79.6	22.93	25.90	29.33	49.6	79.6	1.03	0.83	0.62
10.0	40.0	6.66	6.21	6.01	89.0	119.0	21.97	27.40	28.52	89.0	119.0	1.05	0.84	0.61
49.6	79.6	6.44	6.06	5.78	128.5	158.5	25.21	28.49	23.49	128.5	158.5	1.17	0.86	0.61
89.0	119.0	6.43	6.02	5.77	167.9	197.9	26.81	22.67	22.94	167.9	197.9	1.11	0.79	0.55
128.5	158.5	6.39	6.06	5.85	207.4	237.4	25.28	21.49	24.90	207.4	237.4	1.25	0.85	0.62
167.9	197.9	6.34	6.06	5.85	246.8	276.8	22.46	21.30	26.77	246.8	276.8	1.19	0.84	0.61
207.4	237.4	6.31	6.05	5.86	286.3	316.3	20.21	21.42	26.73	286.3	316.3	1.23	0.88	0.66
246.8	276.8	6.35	6.11	5.91	325.7	355.7	20.21	24.17	23.32	325.7	355.7	1.19	0.84	0.63
286.3	316.3	6.36	6.11	5.92	365.2	395.2	20.16	22.91	22.51	365.2	395.2	1.17	0.86	0.64
325.7	355.7	6.40	6.18	5.98	404.6	434.6	22.00	22.54	21.63	404.6	434.6	1.16	0.83	0.69
365.2	395.2	6.41	6.18	5.98	444.1	474.1	22.98	20.89	18.86	444.1	474.1	1.15	0.80	0.66
404.6	434.6	6.46	6.22	5.98	483.5	513.5	20.17	24.35	19.76	483.5	513.5	1.28	0.94	0.75
444.1	474.1	6.50	6.28	6.08	523.0	553.0	21.07	28.76	20.09	523.0	553.0	1.17	0.94	0.78
483.5	513.5	6.56	6.28	6.07	562.4	592.4	21.87	20.04	21.12	562.4	592.4	1.22	0.97	0.87
523.0	553.0	6.64	6.31	6.00	601.9	631.9	19.44	18.00	18.29	601.9	631.9	1.41	1.05	0.92
562.4	592.4	6.69	6.40	6.04	641.3	671.3	18.39	17.17	17.00	641.3	671.3	1.56	1.09	0.98
601.9	631.9	6.74	6.49	6.17	680.8	710.8	16.57	15.09	15.04	680.8	710.8	1.73	1.23	1.10
641.3	671.3	6.84	6.57	6.31	720.2	750.2	16.00	14.15	15.89	720.2	750.2	1.92	1.42	1.21
680.8	710.8	6.94	6.64	6.37	759.7	789.7	15.96	14.84	18.44	759.7	789.7	2.03	1.64	1.34
720.2	750.2	7.15	6.74	6.43	799.1	829.1	14.38	16.33	19.80	799.1	829.1	1.90	1.72	1.42
759.7	789.7	7.32	6.79	6.42	838.6	868.6	12.03	15.41	19.69	838.6	868.6	1.78	1.77	1.59
799.1	829.1	7.70	6.98	6.49	878.0	908.0	11.01	13.27	18.70	878.0	908.0	1.62	1.61	1.63
838.6	868.6	8.08	7.28	6.59	917.5	947.5	11.75	14.19	16.41	917.5	947.5	1.53	1.56	1.57
878.0	908.0	8.39	7.58	6.77	956.9	986.9	13.20	15.70	16.45	956.9	986.9	1.59	1.56	1.58
956.9	986.9	8.58	7.87	7.22	996.4	1026.4	15.55	18.19	17.20	996.4	1026.4	1.56	1.48	1.47
996.4	1026.4	8.64	8.00	7.51	1035.9	1065.9	19.12	20.36	20.51	1035.9	1065.9	1.60	1.41	1.33
1035.9	1065.9	8.68	8.15	7.79	1075.3	1105.3	22.57	26.16	26.05	1075.3	1105.3	1.55	1.24	1.15
1075.3	1105.3	8.83	8.37	8.00	1114.8	1144.8	24.50	19.63	21.85	1114.8	1144.8	1.66	1.25	1.18
1154.2	1184.2	8.78	8.31	7.96	1154.2	1184.2	18.64	15.76	18.78	1154.2	1184.2	1.76	1.28	1.16
1193.7	1223.7	8.73	8.29	8.02	1193.7	1223.7	14.63	14.07	17.72	1193.7	1223.7	1.89	1.36	1.16
1213.4	1243.4	8.75	8.31	8.05	1213.4	1243.4	13.70	13.68	16.83	1213.4	1243.4	1.90	1.38	1.15
1252.8	1282.8	8.81	8.44	8.24	1252.8	1282.8	13.04	13.54	16.32	1252.8	1282.8	2.41	1.67	1.27
1272.6	1302.6	8.90	8.55	8.36	1272.6	1302.6	13.04	13.63	15.97	1272.6	1302.6	2.19	1.41	1.07
1312.0	1342.0	9.09	8.83	8.69	1312.0	1342.0	13.22	13.79	15.89	1312.0	1342.0	2.34	1.41	0.97
1331.7	1361.7	9.28	9.02	8.87	1331.7	1361.7	13.45	13.87	15.94	1331.7	1361.7	2.35	1.35	0.90
1371.2	1401.2	9.70	9.47	9.33	1371.2	1401.2	14.17	14.54	16.26	1371.2	1401.2	2.66	1.39	0.90
1390.9	1420.9	9.88	9.67	9.56	1390.9	1420.9	14.58	15.31	16.99	1390.9	1420.9	2.76	1.39	0.90
1430.4	1460.4	10.34	10.06	9.98	1430.4	1460.4	14.49	16.90	18.28	1430.4	1460.4	3.09	1.63	1.14
1450.1	1480.1	10.62	10.28	10.19	1450.1	1480.1	13.76	16.68	18.19	1450.1	1480.1	3.21	1.78	1.30



Frequency Mixer

RMS-1MH+

Typical Performance Data

IF (OUT) (MHz)	LO (MHz)	CONVERSION LOSS VS. IF FREQUENCY @RF(IN)=250.1MHz (dB)	IF (OUT) (MHz)	LO (MHz)	CONVERSION LOSS VS. IF FREQUENCY @RF(IN)=10.1MHz (dB)	IF (OUT) (MHz)	LO (MHz)	CONVERSION LOSS VS. IF FREQUENCY @RF(IN)=500.1MHz (dB)
		@LO (dBm)			@LO (dBm)			@LO (dBm)
		+13			+13			+13
240.0	10.1	6.17	10.0	20.1	6.04	490.0	10.1	6.32
234.1	16.0	6.16	22.3	32.4	5.95	477.7	22.4	6.31
228.2	21.9	6.13	34.6	44.7	5.95	465.4	34.7	6.27
222.3	27.8	6.12	46.9	57.0	5.99	453.1	47.0	6.25
216.4	33.7	6.12	59.2	69.3	5.97	440.8	59.3	6.25
210.5	39.6	6.11	71.5	81.6	6.01	428.5	71.6	6.15
204.6	45.5	6.11	83.8	93.9	6.03	416.2	83.9	6.12
198.7	51.4	6.08	96.2	106.3	6.01	403.8	96.3	6.09
192.8	57.3	6.07	108.5	118.6	6.02	391.5	108.6	6.03
186.9	63.2	6.05	120.8	130.9	6.01	379.2	120.9	6.02
181.0	69.1	6.06	133.1	143.2	6.01	366.9	133.2	5.98
175.1	75.0	6.08	145.4	155.5	6.06	354.6	145.5	5.94
169.2	80.9	6.05	157.7	167.8	6.08	342.3	157.8	5.94
163.3	86.8	6.04	170.0	180.1	6.09	330.0	170.1	5.94
157.4	92.7	6.05	182.3	192.4	6.12	317.7	182.4	5.93
151.5	98.6	5.99	194.6	204.7	6.11	305.4	194.7	5.93
145.6	104.5	5.99	206.9	217.0	6.13	293.1	207.0	5.90
139.7	110.4	5.98	219.2	229.3	6.16	280.8	219.3	5.90
133.8	116.3	5.94	231.5	241.6	6.15	268.5	231.6	5.92
127.9	122.2	5.89	243.8	253.9	6.19	256.2	243.9	5.92
122.1	128.0	5.87	256.2	266.3	6.24	243.8	256.3	5.93
116.2	133.9	5.89	268.5	278.6	6.26	231.5	268.6	5.95
110.3	139.8	5.93	280.8	290.9	6.28	219.2	280.9	5.93
104.4	145.7	5.92	293.1	303.2	6.27	206.9	293.2	5.96
98.5	151.6	5.92	305.4	315.5	6.27	194.6	305.5	5.97
92.6	157.5	5.91	317.7	327.8	6.32	182.3	317.8	5.97
86.7	163.4	5.90	330.0	340.1	6.34	170.0	330.1	5.99
80.8	169.3	5.91	342.3	352.4	6.34	157.7	342.4	6.01
74.9	175.2	5.92	354.6	364.7	6.37	145.4	354.7	6.03
69.0	181.1	5.91	366.9	377.0	6.40	133.1	367.0	6.07
63.1	187.0	5.89	379.2	389.3	6.40	120.8	379.3	6.06
57.2	192.9	5.88	391.5	401.6	6.41	108.5	391.6	6.06
51.3	198.8	5.88	403.8	413.9	6.38	96.2	403.9	6.09
45.4	204.7	5.92	416.2	426.3	6.42	83.8	416.3	6.09
39.5	210.6	5.93	428.5	438.6	6.48	71.5	428.6	6.13
33.6	216.5	5.93	440.8	450.9	6.54	59.2	440.9	6.16
27.7	222.4	5.93	453.1	463.2	6.54	46.9	453.2	6.16
21.8	228.3	5.93	465.4	475.5	6.50	34.6	465.5	6.19
15.9	234.2	5.96	477.7	487.8	6.47	22.3	477.8	6.20
10.0	240.1	6.04	490.0	500.1	6.46	10.0	490.1	6.27

Frequency Mixer

RMS-1MH+

Typical Performance Data

LO (MHz)	LO-RF ISOLATION (dB)			LO-IF ISOLATION (dB)		
	@LO (dBm)			@LO (dBm)		
	+10	+13	+16	+10	+13	+16
2.0	76.01	74.51	74.01	68.31	65.71	64.46
5.0	69.66	68.76	68.46	63.66	61.00	59.73
10.0	64.01	63.07	62.89	58.52	55.80	54.50
49.6	54.33	53.63	52.79	49.70	47.81	45.81
89.0	50.16	49.16	48.70	45.12	43.24	41.30
128.5	47.19	47.06	46.34	42.25	40.50	39.15
167.9	46.04	45.92	44.93	40.13	39.13	37.72
207.4	45.19	44.64	43.19	39.41	38.43	36.48
246.8	44.85	43.76	42.15	39.33	37.86	35.67
286.3	43.36	42.24	40.78	39.11	37.44	35.00
325.7	42.08	40.77	39.15	38.71	36.74	34.05
365.2	41.21	39.83	38.15	37.72	35.83	33.13
404.6	39.91	38.64	37.03	36.60	34.66	32.17
444.1	38.03	37.19	35.95	35.27	33.60	30.91
483.5	35.56	35.22	34.37	33.08	32.39	30.62
523.0	33.76	33.21	32.33	31.24	30.29	28.93
562.4	32.72	31.85	31.01	31.04	28.85	27.02
601.9	31.90	31.05	30.16	31.50	29.09	26.27
641.3	31.42	30.41	29.25	30.40	28.69	26.05
680.8	30.91	29.62	28.33	28.72	27.68	25.47
720.2	30.23	28.93	27.42	26.63	26.26	24.26
759.7	29.44	27.90	26.37	24.96	24.93	23.06
799.1	28.61	27.22	25.63	23.18	23.37	21.97
838.6	27.59	26.49	25.08	21.68	21.48	20.53
878.0	26.88	25.88	24.63	21.50	20.40	19.29
956.9	26.06	25.09	23.97	20.80	19.72	17.78
996.4	25.77	24.97	24.07	20.24	19.40	17.48
1035.9	25.37	24.61	24.01	19.47	18.75	16.82
1075.3	25.04	24.59	24.24	18.82	18.37	16.42
1154.2	24.49	24.28	24.37	16.89	16.82	14.95
1193.7	24.47	24.53	24.85	15.85	16.04	14.60
1213.4	24.33	24.35	24.81	15.26	15.61	14.07
1252.8	24.46	24.73	25.25	14.18	14.70	13.37
1272.6	24.63	25.00	25.40	13.61	14.22	12.98
1312.0	25.50	25.71	25.48	12.52	13.23	12.16
1331.7	25.89	25.74	25.13	12.03	12.63	11.71
1371.2	27.23	26.36	24.91	11.36	11.89	11.14
1390.9	27.71	26.42	24.68	11.05	11.52	10.84
1430.4	27.67	25.77	23.75	11.02	11.24	10.52
1450.1	27.46	25.32	23.35	11.06	11.20	10.38

RF (IN) (MHz)	LO (MHz)	RF-IF ISOLATION (dB)		
		@LO (dBm)		
		+10	+13	+16
10.1	40.1	45.18	45.77	45.93
49.6	79.6	33.63	33.29	32.78
89.0	119.0	28.91	28.87	28.71
128.5	158.5	26.40	26.34	26.29
167.9	197.9	24.66	24.67	24.63
207.4	237.4	23.54	23.59	23.59
246.8	276.8	22.76	22.77	22.86
286.3	316.3	22.43	22.46	22.53
325.7	355.7	22.21	22.42	22.55
365.2	395.2	22.16	22.45	22.75
404.6	434.6	22.40	22.69	22.96
444.1	474.1	22.81	23.06	23.13
483.5	513.5	23.13	23.39	23.55
523.0	553.0	23.22	23.46	24.04
562.4	592.4	22.52	22.62	23.07
601.9	631.9	20.89	20.87	20.98
641.3	671.3	18.93	18.83	18.83
680.8	710.8	17.12	16.95	17.08
720.2	750.2	15.46	15.37	15.51
759.7	789.7	14.16	14.10	14.13
799.1	829.1	13.22	13.12	13.10
838.6	868.6	12.55	12.52	12.56
878.0	908.0	11.95	11.98	12.21
917.5	947.5	11.42	11.37	11.86
956.9	986.9	10.96	10.90	11.41
996.4	1026.4	10.58	10.62	11.11
1035.9	1065.9	10.33	10.52	10.97
1075.3	1105.3	10.08	10.36	10.85
1114.8	1144.8	9.93	10.33	10.92
1154.2	1184.2	9.83	10.36	11.08
1193.7	1223.7	9.81	10.50	11.33
1213.4	1243.4	9.80	10.61	11.35
1252.8	1282.8	9.91	10.62	11.09
1272.6	1302.6	9.88	10.48	10.79
1312.0	1342.0	9.56	9.94	9.94
1331.7	1361.7	9.27	9.55	9.47
1371.2	1401.2	8.50	8.62	8.51
1390.9	1420.9	8.13	8.16	8.04
1430.4	1460.4	7.47	7.41	7.33
1450.1	1480.1	7.09	7.09	7.02

Frequency Mixer

RMS-1MH+

Typical Performance Data

RF (IN) (MHz)	LO (MHz)	RF VSWR (:1)			LO (MHz)	LO VSWR (:1)			IF (OUT) (MHz)	IF VSWR @LO=500.1MHz (:1)		
		@LO (dBm)				@LO (dBm)				@LO (dBm)		
		+10	+13	+16		+10	+13	+16		+10	+13	+16
5.0	35.0	1.16	1.13	1.15	5.0	1.38	2.10	3.07	5.0	1.41	1.24	1.14
10.0	40.0	1.12	1.06	1.09	10.0	1.33	2.01	2.91	10.0	1.42	1.25	1.14
49.6	79.6	1.11	1.03	1.07	49.6	1.09	1.42	2.42	22.4	1.82	1.65	1.47
89.0	119.0	1.12	1.02	1.07	89.0	1.09	1.41	2.33	34.7	1.79	1.62	1.45
128.5	158.5	1.10	1.02	1.07	128.5	1.11	1.44	2.40	47.0	1.81	1.65	1.48
167.9	197.9	1.08	1.02	1.08	167.9	1.12	1.43	2.35	59.3	1.84	1.68	1.52
207.4	237.4	1.07	1.03	1.10	207.4	1.12	1.46	2.40	71.6	1.86	1.70	1.53
246.8	276.8	1.07	1.03	1.10	246.8	1.13	1.47	2.41	83.9	1.85	1.68	1.52
286.3	316.3	1.06	1.04	1.11	286.3	1.14	1.49	2.40	96.3	1.85	1.68	1.51
325.7	355.7	1.04	1.04	1.12	325.7	1.17	1.52	2.47	108.6	1.84	1.67	1.50
365.2	395.2	1.03	1.06	1.14	365.2	1.18	1.54	2.45	120.9	1.84	1.67	1.50
404.6	434.6	1.02	1.07	1.16	404.6	1.21	1.58	2.50	133.2	1.85	1.68	1.50
444.1	474.1	1.02	1.08	1.15	444.1	1.24	1.61	2.53	145.5	1.85	1.68	1.51
483.5	513.5	1.02	1.10	1.17	483.5	1.27	1.64	2.55	157.8	1.85	1.68	1.52
523.0	553.0	1.04	1.11	1.22	523.0	1.31	1.68	2.59	170.1	1.85	1.69	1.52
562.4	592.4	1.05	1.12	1.23	562.4	1.35	1.73	2.61	182.4	1.87	1.71	1.53
601.9	631.9	1.08	1.14	1.23	601.9	1.40	1.78	2.68	194.7	1.89	1.72	1.54
641.3	671.3	1.10	1.17	1.25	641.3	1.43	1.82	2.70	207.0	1.89	1.73	1.54
680.8	710.8	1.12	1.20	1.28	680.8	1.48	1.87	2.74	219.3	1.90	1.72	1.54
720.2	750.2	1.13	1.22	1.29	720.2	1.52	1.91	2.75	231.6	1.89	1.72	1.54
759.7	789.7	1.13	1.21	1.28	759.7	1.57	1.96	2.78	243.9	1.88	1.71	1.54
799.1	829.1	1.15	1.21	1.28	799.1	1.64	2.01	2.82	256.3	1.89	1.72	1.54
838.6	868.6	1.20	1.22	1.29	838.6	1.69	2.07	2.84	268.6	1.89	1.72	1.54
878.0	908.0	1.27	1.27	1.32	878.0	1.75	2.14	2.92	280.9	1.89	1.72	1.54
917.5	947.5	1.33	1.33	1.37	917.5	1.80	2.20	2.94	293.2	1.88	1.70	1.53
956.9	986.9	1.39	1.41	1.44	956.9	1.85	2.27	2.99	305.5	1.87	1.69	1.51
996.4	1026.4	1.48	1.51	1.54	996.4	1.91	2.34	3.04	317.8	1.86	1.69	1.51
1035.9	1065.9	1.58	1.61	1.66	1035.9	1.97	2.40	3.06	330.1	1.86	1.69	1.51
1075.3	1105.3	1.66	1.70	1.76	1075.3	2.03	2.47	3.12	342.4	1.86	1.69	1.51
1114.8	1144.8	1.73	1.78	1.86	1114.8	2.08	2.51	3.11	354.7	1.86	1.68	1.51
1154.2	1184.2	1.81	1.88	1.97	1154.2	2.15	2.58	3.15	367.0	1.85	1.68	1.50
1193.7	1223.7	1.91	2.00	2.09	1193.7	2.20	2.63	3.15	379.3	1.85	1.67	1.50
1213.4	1243.4	1.96	2.05	2.15	1213.4	2.23	2.64	3.14	391.6	1.86	1.68	1.51
1252.8	1282.8	2.07	2.17	2.25	1252.8	2.29	2.69	3.15	403.9	1.88	1.70	1.52
1272.6	1302.6	2.13	2.23	2.31	1272.6	2.31	2.72	3.15	416.3	1.89	1.70	1.52
1312.0	1342.0	2.23	2.33	2.40	1312.0	2.35	2.72	3.10	428.6	1.87	1.69	1.51
1331.7	1361.7	2.29	2.39	2.45	1331.7	2.37	2.73	3.10	440.9	1.85	1.67	1.50
1371.2	1401.2	2.34	2.46	2.53	1371.2	2.43	2.77	3.12	453.2	1.85	1.67	1.50
1390.9	1420.9	2.35	2.47	2.54	1390.9	2.44	2.77	3.09	465.5	1.86	1.69	1.51
1430.4	1460.4	2.34	2.44	2.53	1430.4	2.52	2.80	3.08	477.8	1.88	1.70	1.53
1450.1	1480.1	2.33	2.41	2.50	1450.1	2.56	2.84	3.10	490.1	1.89	1.71	1.54

Harmonics Tables

RF HARMONICS ORDER

	(-dBm)	(-dBc)										
0	-	-	11	17	12	21	13	29	20	41	31	47
1	-	17	+0	27	13	31	19	32	30	49	36	44
2	>100	59	41	53	42	49	41	50	42	58	53	67
3	>100	73	63	68	57	62	51	73	53	66	53	65
4	>100	76	64	79	67	70	69	68	64	71	71	78
5	>100	83	>88	83	78	80	73	81	70	88	72	82
6	>100	>88	>88	>88	88	87	>88	84	87	86	84	>88
7	>100	>88	>88	>88	>88	>88	>88	84	86	>88	87	>88
8	>100	>88	>88	>88	>88	>88	>88	>88	>88	>88	>88	>88
9	>100	>88	>88	>88	>88	>88	>88	>88	>88	72	>88	>88
10	>100	>88	>88	>88	>88	>88	>88	>88	>88	>88	80	>88
	RF CAL	0	1	2	3	4	5	6	7	8	9	10

LO HARMONICS ORDER

Test conditions: RF IN: 250.1 MHz; -6.00 dBm.
 LO IN: 280.01 MHz; +13.00 dBm
 IF OUT: 29.91 MHz; -12.06 dBm

RF HARMONICS ORDER

	(-dBm)	(-dBc)										
0	-	-	20	26	25	35	27	48	35	60	43	63
1	-	17	+0	27	12	32	19	34	30	73	41	52
2	88	51	38	56	38	49	38	46	39	55	46	61
3	>100	44	45	50	56	53	45	47	44	50	50	57
4	>100	77	57	61	56	58	56	53	51	54	50	62
5	>100	57	57	58	56	60	52	57	49	59	48	65
6	>100	73	63	80	64	72	68	67	68	61	60	62
7	>100	80	69	75	69	70	81	69	66	66	62	69
8	>100	74	72	66	64	66	65	77	74	82	81	73
9	>100	82	83	80	72	76	69	73	78	74	77	74
10	>100	88	84	84	84	75	77	72	75	79	71	86
	RF CAL	0	1	2	3	4	5	6	7	8	9	10

LO HARMONICS ORDER

Test conditions: RF IN: 250.1 MHz; 4.00 dBm.
 LO IN: 280.01 MHz; +13.00 dBm
 IF OUT: 29.91 MHz; -2.13 dBm

- Notes: 1. All Harmonics are in (dBc) relative to IF OUTPUT.
 2. + entry denotes harmonics are in (dBc) above IF OUTPUT.
 3. RF Cal represent the Harmonics level of the RF input signal to the mixer.

REV. X2
 RMS-1MH+
 100817
 Page 5 of 5



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED • RoHS compliant
 P.O. Box 350166, Brooklyn, New York 11235-0006 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see




Frequency Mixer


RMS-1MH+

Typical Performance Curves


Conversion Loss @ IF=30MHz




Conversion Loss vs. IF @ RF=250.1MHz




Conversion Loss vs. IF @ RF=10.1MHz




Conversion Loss vs. IF @ RF=500.1MHz



IP3 Input




Compression @ RF IN=+9dBm




Typical Performance Curves


LO-RF Isolation




LO-IF Isolation




RF-IF Isolation




RF VSWR



LO VSWR



IF VSWR



Harmonics Tables

RF HARMONICS ORDER

	(-dBm)	(-dBc)										
0	-	-	11	17	12	21	13	29	20	41	31	47
1	-	17	+0	27	13	31	19	32	30	49	36	44
2	>100	59	41	53	42	49	41	50	42	58	53	67
3	>100	73	63	68	57	62	51	73	53	66	53	65
4	>100	76	64	79	67	70	69	68	64	71	71	78
5	>100	83	>88	83	78	80	73	81	70	88	72	82
6	>100	>88	>88	>88	88	87	>88	84	87	86	84	>88
7	>100	>88	>88	>88	>88	>88	>88	84	86	>88	87	>88
8	>100	>88	>88	>88	>88	>88	>88	>88	>88	>88	>88	>88
9	>100	>88	>88	>88	>88	>88	>88	>88	>88	72	>88	>88
10	>100	>88	>88	>88	>88	>88	>88	>88	>88	>88	80	>88
	RF CAL	0	1	2	3	4	5	6	7	8	9	10

LO HARMONICS ORDER

Test conditions: RF IN: 250.1 MHz; -6.00 dBm.
 LO IN: 280.01 MHz; +13.00 dBm
 IF OUT: 29.91 MHz; -12.06 dBm

RF HARMONICS ORDER

	(-dBm)	(-dBc)										
0	-	-	20	26	25	35	27	48	35	60	43	63
1	-	17	+0	27	12	32	19	34	30	73	41	52
2	88	51	38	56	38	49	38	46	39	55	46	61
3	>100	44	45	50	56	53	45	47	44	50	50	57
4	>100	77	57	61	56	58	56	53	51	54	50	62
5	>100	57	57	58	56	60	52	57	49	59	48	65
6	>100	73	63	80	64	72	68	67	68	61	60	62
7	>100	80	69	75	69	70	81	69	66	66	62	69
8	>100	74	72	66	64	66	65	77	74	82	81	73
9	>100	82	83	80	72	76	69	73	78	74	77	74
10	>100	88	84	84	84	75	77	72	75	79	71	86
	RF CAL	0	1	2	3	4	5	6	7	8	9	10

LO HARMONICS ORDER

Test conditions: RF IN: 250.1 MHz; 4.00 dBm.
 LO IN: 280.01 MHz; +13.00 dBm
 IF OUT: 29.91 MHz; -2.13 dBm

- Notes: 1. All Harmonics are in (dBc) relative to IF OUTPUT.
 2. + entry denotes harmonics are in (dBc) above IF OUTPUT.
 3. RF Cal represent the Harmonics level of the RF input signal to the mixer.

REV. X2
 RMS-1MH+
 100817
 Page 3 of 3




IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED • RoHS compliant
 P.O. Box 350166, Brooklyn, New York 11235-0006 (718) 934-4500 Fax (718) 332-4661




The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see minicircuits.com

Outline Dimensions



PCB Land Pattern



Suggested Layout,
Tolerance to be within $\pm .002$

CASE #	A	B	C	D	E	F	G	H	J	K	WT. GRAM
TT240	.250 (6.35)	.31 (7.87)	.20 (5.08)	.100 (2.54)	.050 (1.27)	.055 (1.40)	.040 (1.02)	.070 (1.78)	.270 (6.86)	.050 (1.27)	.50

Dimensions are in inches (mm). Tolerances: 2Pl. $\pm .01$; 3 Pl. $\pm .005$

Notes:

- Case material: Ceramic.
- Termination finish:
 - For RoHS Case Styles: 2-10 μ inch (.05-.25 microns) Gold plate over 100-300 μ inch (2.54-7.62 microns) Nickel plate. All models, (+) suffix.
 - For RoHS-5 Case Styles: Tin-Lead plate. All models, no (+) suffix.




P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

RF/IF MICROWAVE COMPONENTS

Tape & Reel Packaging TR-F2



Tape Width, mm	Device Cavity Pitch, mm	Reel Size, inches	Devices per Reel See note
16	12	7	10
			20
			50
			100
			200
		13	500

Note: Please consult individual model data sheet to determine device per reel availability

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: www.minicircuits.com/pages/pdfs/tape.pdf



INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified

THIRD ANGLE PROJECTION



REVISIONS

REV	ECN No.	DESCRIPTION	DATE	DR	AUTH
A	M101143	ADDED "gk" PIN CONNECTION, TT100 CASE STYLE & NOTE 2	10/10/05	MMG	DJ
B	M102713	ADDED "...WITH SMOBC"	01/17/06	MMG	IL
C	M108637	REMOVED "PIN 1", ADDED INDEX ON UNIT	12/01/06	MYG	FL

SUGGESTED MOUNTING CONFIGURATION
FOR BH292, CD541/542/636/637, TT100/240 CASE
STYLES, "gk", "ht", "hu", "nd", "w" PIN CONNECTIONS



- NOTES:** 1. TRACE WIDTH IS SHOWN FOR ROGERS R04350B WITH DIELECTRIC THICKNESS .030" ± .002"; COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
 2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.

- DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)
- DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

UNLESS OTHERWISE SPECIFIED	INITIALS	DATE
DIMENSIONS ARE IN INCHES	MMG	07/17/02
TOLERANCES ON:	WL	08/02/02
2 PL DECIMALS ±	DJ	08/05/02
3 PL DECIMALS ± .005		
ANGLES ±		
FRACTIONS ±		

Mini-Circuits® 13 Neptune Avenue
Brooklyn NY 11235

PL, gk/ht/hu/nd/w, BH292,
CD541/542/636/637, TT100/240, TB-03

SIZE A	CODE IDENT 15542	DRAWING NO: 98-PL-052	REV: C
FILE: 98PL052	SCALE: 8:1	SHEET: 1 OF 1	

Mini-Circuits®
 THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.

THIRD ANGLE PROJECTION



REVISIONS

REV	ECN No.	DESCRIPTION	DATE	DR	AUTH
E	M119737	UPDATED PCB	10.08	MF	AD
F	M127659	UPDATED CARR	06.10	SW	SG
G	M127846	UPDATED SCHEMATIC DIAGRAM	06.10	SW	SG
H	M131840	UPDATED DWG	05.11	MF	AD



NOTES:

1. REFER TO -09 PAGE FOR ITEM DESCRIPTIONS.
DESIGNATION NUMBERS ON -20 PAGE CORRESPOND TO THE NUMBERS ON -09 PAGE.
2. FOR TEXT HEIGHT & STYLE ON THE LABEL REFER TO: D3-G209.

UNLESS OTHERWISE SPECIFIED	INITIALS	DATE
DIMENSIONS ARE IN INCHES TOLERANCES ON: 2 PL DECIMALS ± 3 PL DECIMALS ± ANGLES ± FRACTIONS ±	DRAWN	S.WOLYNSKI 06.29.99
	CHECKED	SG 07.06.99
	APPROVED	MG 07.10.99

 **Mini-Circuits®** 13 Neptune Avenue
Brooklyn NY 11235

TB,ADE,CD542/636,06MX01,50

 Mini-Circuits®
THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.

SIZE A	CODE IDENT 15542	DRAWING NO: TB-03-20	REV: H
FILE: WTB-03	SCALE: 1.5:1	SHEET: 1 OF 2	

Evaluation Board and Circuit

For Pin Connections and DUT Orientation Refer to
Data Sheet of the DUT



TB-03



Schematic Diagram

Notes:

1. 50 Ohm SMA Female connectors.
2. PCB Material: Rogers R04350 or equivalent,
Dielectric Constant=3.5, Thickness=.030 inch.

 **Mini-Circuits®**



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-40° to 85°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Humidity	90 to 95% RH, 240 hours, 50°C	MIL-STD-202, Method 103, Condition A, Except 50°C and end-point electrical test done within 12 hours
Thermal Shock	-55° to 100°C, 100 cycles	MIL-STD-202, Method 107, Condition A-3, except +100°C
Solder Reflow Heat	Sn-Pb Eutetic Process: 225°C peak Pb-Free Process 245° - 250°C peak	J-STD-020, Table 4-1, 4-2 and 5-2, Figure 5-1
Solderability	10X Magnification	J-STD-002, 95% Coverage
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes	MIL-STD-202, Method 213, Condition A
Marking Resistance to Solvents	Isopropyl alcohol + mineral spirits at 25°C; terpene defluxer at 25°C; distilled water + proylene glycol monomethyl ether + monoethanolamine at 63°C to 70°C	MIL-STD-202, Method 215