

Low Noise, Medium Power
E-PHEMT

TAV2-501+

50Ω 0.4 to 3.9 GHz

The Big Deal

- Low Noise Figure, 0.6 dB typ. at 0.9 GHz, 4.5V
- High OIP3, +42.9 dBm typ. at 2 GHz, 4.5V
- Footprint compatible with ATF-501P8^{a,b}



CASE STYLE: MC1631-1

Product Overview

TAV2-501+ is an ultra-low noise, high IP3 transistor device, manufactured using E-PHEMT* technology enabling it to work with a single positive supply voltage. It has outstanding Noise Figure, particularly below 2.5 GHz, and when combining this noise figure with high IP3 performance in a single device it makes it an ideal amplifier for demanding base station applications.

Key Features

Feature	Advantages
Wideband, 0.4 to 3.9 GHz	A single device covers many wireless communications bands including cellular, ISM, GSM, WCDMA, WiMax, WLAN, and more.
High IP3 vs. DC power consumption <ul style="list-style-type: none">• +42.9 dBm at 0.9 GHz, 4.5V• +42.9 dBm at 2 GHz, 4.5V• +43.9 dBm at 3.9 GHz, 4.5V For additional data, see Tables 1-4 on Page 5	The TAV2-501+ matches industry leading IP3 performance relative to device size and power consumption. Enhanced linearity over a broad frequency range makes the device ideal for use in: <ul style="list-style-type: none">• Driver amplifiers for complex waveform up converter paths• Drivers in linearized transmit systems
High P1dB <ul style="list-style-type: none">• +30.6 dBm at 0.9 GHz, 4.5V• +27.7 dBm at 2 GHz, 4.5V• +30.0 dBm at 3.9 GHz, 4.5V For additional data, see Tables 1-4 on Page 5	Results in a very dynamic range preventing amplifier saturation under strong interfering signals.
Combines high gain (16.4 dB) with very low Noise Figure (0.7 dB)	The unique combination of high gain and low Noise Figure results in lower overall system noise.
2 x 2mm 8-lead MCLP package	Tiny footprint saves space in dense layouts while providing low inductance, repeatable transitions, and excellent thermal contact to the PCB.

* Enhancement mode Pseudomorphic High Electron Mobility Transistor.

a. Suitability for model replacement within a particular system must be determined by and is solely the responsibility of the customer based on, among other things, electrical performance criteria, stimulus conditions, application, compatibility with other components and environmental conditions and stresses.

b. The ATF-501P8 part number is used for identification and comparison purposes only.



Low Noise, Medium Power
E-PHEMT

0.4-3.9GHz

Product Features

- Single Positive Supply Voltage
- Low Noise Figure, 0.6 dB at 0.9 GHz
- Gain, 15 dB at 2 GHz
- High Output IP3, 42.9 dBm at 2 GHz
- P1dB, 30.6 dBm at 0.9 GHz, 27.7 dBm at 2 GHz
- External biasing and matching required
- Footprint compatible with ATF-501P8^{a,b}



Generic photo used for illustration purposes only

TAV2-501+

CASE STYLE: MC1631-1

Typical Applications

- Cellular
- ISM
- GSM
- WCDMA
- WiMax
- WLAN



+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

General Description

TAV2-501+ is an ultra-low noise, high IP3 transistor device, manufactured using E-PHEMT* technology enabling it to work with a single positive supply voltage. It has outstanding Noise Figure, particularly below 2.5 GHz, and when combining this noise figure with high IP3 performance in a single device it makes it an ideal amplifier for demanding base station applications.

simplified schematic and pad description



Function	Pad Number	Description
Source	1,4 & paddle	Source terminal, normally connected to ground
Gate	2	Gate used for RF input
Drain	7	Drain used for RF output
NC	3,5,6,8	No connection, connected to ground externally

Notes:

- a. Suitability for model replacement within a particular system must be determined by and is solely the responsibility of the customer based on, among other things, electrical performance criteria, stimulus conditions, application, compatibility with other components and environmental conditions and stresses.
- b. The ATF-501P8 part number is used for identification and comparison purposes only.

Electrical Specifications at $T_{AMB}=25^{\circ}\text{C}$, Frequency 0.4 to 3.9 GHz

Symbol	Parameter	Condition	Min.	Typ.	Max.	Units
DC Specifications						
VGS	Operational Gate Voltage	$V_{DS} = 4.5 \text{ V}$, $I_{DS} = 280 \text{ mA}$	0.39	0.52	0.65	V
VTH	Threshold Voltage	$V_{DS} = 4.5 \text{ V}$, $I_{DS} = 28 \text{ mA}$		0.38		V
IDSS	Saturated Drain Current	$V_{DS} = 4.5 \text{ V}$, $VGS = 0 \text{ V}$		0.5		μA
GM	Transconductance	$V_{DS} = 4.5 \text{ V}$, $G_M = \Delta I_{DS}/\Delta V_{GS}$ $\Delta V_{GS} = V_{GS1} - V_{GS2}$ $V_{GS1} = V_{GS}$, typ - 0.05 V $V_{GS2} = V_{GS}$, typ + 0.05 V		2600		mS
IGSS	Gate Leakage Current	$V_{GD} = V_{GS} = -6.7 \text{ V}$		65		μA
RF Specifications, $Z_0 = 50 \text{ Ohms}$						
NF ⁽¹⁾	Noise Figure	$V_{DS} = 4.5 \text{ V}$, $I_{DS} = 280 \text{ mA}$	$f = 0.9 \text{ GHz}$ $f = 2.0 \text{ GHz}$		0.6 1.3	dB
Gain ^(1,5)	Gain	$V_{DS} = 4.5 \text{ V}$, $I_{DS} = 280 \text{ mA}$	$f = 0.9 \text{ GHz}$ $f = 2.0 \text{ GHz}$	13.6	23.5 15.1	16.7
OIP3 ^(1,6)	Output IP3	$V_{DS} = 4.5 \text{ V}$, $I_{DS} = 280 \text{ mA}$	$f = 0.9 \text{ GHz}$ $f = 2.0 \text{ GHz}$	40	42.9 42.9	dBm
P1dB ^(1,5)	Power Output at 1 dB Compression	$V_{DS} = 4.5 \text{ V}$, $I_{DS} = 280 \text{ mA}$	$f = 0.9 \text{ GHz}$ $f = 2.0 \text{ GHz}$	25.5	30.6 27.7	dBm
PAE ^(1,5)	Power Added Efficiency	$V_{DS} = 4.5 \text{ V}$, $I_{DS} = 280 \text{ mA}$	$f = 0.9 \text{ GHz}$ $f = 2.0 \text{ GHz}$	33	45 45	%

Absolute Maximum Ratings⁽³⁾

Symbol	Parameter	Max.	Units
$V_{DS}^{(3)}$	Drain-Source Voltage	7	V
$V_{GS}^{(3)}$	Gate-Source Voltage	-5 to +0.8	V
$V_{GD}^{(3)}$	Gate-Drain Voltage	-5 to +0.8	V
$I_{DS}^{(3)}$	Drain Current	500	mA
I_{GS}	Gate Current	60	μA
P_{DISS}	Total Dissipated Power	2.4	W
$P_{IN}^{(4)}$	RF Input Power	28	dBm
T_{CH}	Channel Temperature	150	$^{\circ}\text{C}$
T_{OP}	Operating Temperature	-40 to 85	$^{\circ}\text{C}$
T_{STD}	Storage Temperature	-65 to 150	$^{\circ}\text{C}$
Θ_{JC}	Thermal Resistance	23	$^{\circ}\text{C}/\text{W}$

Notes:

- (1) Measurements at 0.9 GHz obtained on Mini-Circuits characterization test board TB-TAV2-501+ with load and source pull test (Fig. 1), while measurements at 2 GHz tested on Mini-Circuits matching circuit test board TB-TAV2-501M+ (Fig. 2).
- (2) Operation of this device above any one of these parameters may cause permanent damage.
- (3) Assumes DC quiescent conditions.
- (4) I_{GS} is limited to 60 μA during test.
- (5) Measurements at 0.9 GHz obtained for optimized P1dB.
- (6) Measurements at 0.9 GHz obtained for optimized IP3.






Fig 1. Block Diagram of Test Circuit used for characterization. (DUT soldered on Mini-Circuits Test Board TB-TAV2-501+) Gain, Output power at 1dB compression (P1 dB) and output IP3 (OIP3) are measured using Keysight Network Analyzer N5424A PNAx and Maury automated tuner.

Conditions (Optimized IP3):

1. Drain voltage (with reference to source, VDS) = 4.5V as shown.
2. Gate Voltage (with reference to source, VGS) is set to obtain desired Drain-Source current (IDS) as shown in specification table or load and source pull tables.
3. Gain: Pin= -25dBm
4. Pin for IP3: -10 dBm at 0.9 GHz, -5 dBm at 2.0 GHz, -1 dBm at 2.4 GHz, 0 dBm at 3.9 GHz.

Conditions (Optimized P1dB):

1. Drain voltage (with reference to source, VDS) = 4.5V as shown.
2. Gate Voltage (with reference to source, VGS) is set to obtain desired Drain-Source current (IDS) as shown in specification table or load and source pull tables.
3. Gain: Pin= -25dBm
4. Pin for IP3: -10 dBm at 0.9 GHz, -5 dBm at 2.0 GHz and 2.4 GHz, -2 dBm at 3.9 GHz.

Recommended Application Circuit




Fig 2. Recommended Application Circuit used for characterization. (DUT soldered on Mini-Circuits Matching Circuit Test Board TB-TAV2-501M+)

Table 1: Optimum OIP3 at 4.5 V, 280 mA

Freq (GHz)	OIP3 (dBm)	Gain (dB)	P1dB (dBm)	PAE (%)	Γ_{source}	Γ_{load}
0.9	45.11	19.98	29.85	49.66	$0.694 \angle -114.29^\circ$	$0.693 \angle -91.12^\circ$
2.0	46.32	14.22	28.68	48.82	$0.842 \angle 29.84^\circ$	$0.715 \angle 35.13^\circ$
2.4	44.64	11.23	27.44	42.12	$0.724 \angle 123.43^\circ$	$0.638 \angle 75.56^\circ$
3.9	43.89	11.00	27.83	42.76	$0.884 \angle -108.07^\circ$	$0.679 \angle -114.78^\circ$

Table 2: Optimum P1dB at 4.5 V, 280 mA

Freq (GHz)	OIP3 (dBm)	Gain (dB)	P1dB (dBm)	PAE (%)	Γ_{source}	Γ_{load}
0.9	40.18	22.77	30.03	52.30	$0.658 \angle -87.51^\circ$	$0.690 \angle -73.64^\circ$
2.0	41.52	17.02	30.23	56.73	$0.743 \angle 39.55^\circ$	$0.715 \angle 43.14^\circ$
2.4	41.11	15.10	30.52	53.56	$0.742 \angle 92.52^\circ$	$0.720 \angle 93.56^\circ$
3.9	39.53	11.72	29.95	46.67	$0.759 \angle -95.66^\circ$	$0.687 \angle -96.87^\circ$


Table 3: Optimum OIP3 at 4.5 V, 400 mA

Freq (GHz)	OIP3 (dBm)	Gain (dB)	P1dB (dBm)	PAE (%)	Γ_{source}	Γ_{load}
0.9	47.67	16.84	29.54	50.28	$0.645 \angle -138.14^\circ$	$0.602 \angle -69.95^\circ$
2.0	45.77	15.97	29.23	50.14	$0.649 \angle 40.96^\circ$	$0.613 \angle 40.33^\circ$
2.4	48.05	13.40	29.66	48.74	$0.803 \angle 112.01^\circ$	$0.619 \angle 92.12^\circ$
3.9	46.32	11.40	29.57	46.28	$0.884 \angle -108.07^\circ$	$0.684 \angle -105.84^\circ$

Table 4: Optimum P1dB at 4.5 V, 400 mA

Freq (GHz)	OIP3 (dBm)	Gain (dB)	P1dB (dBm)	PAE (%)	Γ_{source}	Γ_{load}
0.9	42.99	23.04	30.01	45.83	$0.658 \angle -87.51^\circ$	$0.785 \angle -87.47^\circ$
2.0	42.01	18.53	30.68	48.45	$0.833 \angle 43.23^\circ$	$0.827 \angle 42.17^\circ$
2.4	44.45	17.26	30.16	55.62	$0.874 \angle 94.67^\circ$	$0.726 \angle 86.88^\circ$
3.9	43.13	12.90	30.83	49.36	$0.875 \angle -101.14^\circ$	$0.784 \angle -99.28^\circ$

Product Marking



Additional Detailed Technical Information

additional information is available on our dash board. To access this information [click here](#)

Performance Data	Data Table
	Swept Graphs
	S-Parameter (S2P Files) Data Set (.zip file)
Case Style	MC1631-1 Plastic low profile 2mm x 2mm, lead finish: matte-tin
Tape & Reel	F66
Standard quantities available on reel	7" reels with 20, 50, 100, 200, 500, 1K or 2K devices
Suggested Layout for PCB Design	PL-685, PL-688
Test Board	TB-TAV2-501+
Evaluation Board (2GHz)	TB-TAV2-501M+
Environmental Ratings	ENV08T2


ESD Rating

Human Body Model (HBM): Class 1B (500V to < 1000V) in accordance with ANSI/ESD STM 5.1 - 2001

MSL Rating

Moisture Sensitivity: MSL1 in accordance with IPC/JEDECJ-STD-020D

MSL Test Flow Chart



Additional Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

Typical Performance Data

VDS (V)	IDS (mA)				
	@ VGS =				
	0.40 V	0.50 V	0.60 V	0.70 V	0.80 V
0.00	0.16	0.33	0.41	0.34	0.67
0.20	27.52	113.78	205.30	247.06	262.64
0.40	30.52	132.94	315.00	451.22	505.78
0.60	32.81	140.92	340.26	564.70	706.02
0.80	34.71	147.72	352.64	597.72	827.84
1.00	36.21	153.76	362.96	613.36	871.08
1.20	37.44	159.22	372.16	626.06	890.00
1.40	38.59	164.06	380.58	637.66	905.24
1.60	39.70	168.96	388.90	649.10	918.82
1.80	41.05	169.88	397.98	662.06	930.96
2.00	42.45	178.96	407.42	672.94	943.62
2.20	43.86	186.16	417.00	684.04	952.32
2.40	45.27	192.22	426.70	695.06	960.20
2.60	46.69	197.76	436.18	706.00	966.88
2.80	48.10	203.12	445.70	716.78	972.02
3.00	49.49	208.40	455.12	727.24	975.44
3.20	50.88	213.58	464.68	737.18	976.68
3.40	52.30	218.82	474.30	747.60	975.60
3.60	53.70	224.12	484.14	755.82	971.46
3.80	55.23	229.52	494.06	763.14	966.00
4.00	56.77	235.06	504.52	769.52	958.54
4.20	58.36	240.82	514.46	774.56	949.34
4.40	60.24	246.78	524.54	778.24	939.00
4.50	61.03	249.76	529.44	779.58	933.44
4.60	61.86	252.90	534.36	780.44	927.54
4.80	63.63	259.34	544.18	781.22	915.58
5.00	65.40	266.02	553.90	780.56	902.74
5.20	67.26	273.10	563.42	778.62	889.62
5.40	69.24	280.50	572.52	775.02	876.28
5.60	71.73	288.74	582.54	770.92	862.82
5.80	73.64	296.40	589.36	765.86	849.32
6.00	75.75	304.80	595.76	760.08	836.06
6.20	77.93	313.52	601.34	753.68	823.20
6.40	80.19	322.58	606.14	746.78	811.66
6.60	82.52	332.08	609.86	739.48	802.38
6.80	84.97	342.00	612.68	731.90	793.12
7.00	87.67	352.34	614.62	724.16	782.40


Mini-Circuits®

ISO 9001 ISO 14001 AS 9100 CERTIFIED

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site
 The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

IF/RF MICROWAVE COMPONENTS



REV. A

TAV2-501+

12/15/2020

Page 1 of 7

MMIC Amplifier

TAV2-501+

Typical Performance Data

Definitions:

Input Return Loss = -S11 (dB)
Gain(Power Gain) = S21 (dB)
Reverse Isolation = -S12 (dB)
Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 4.50V, Id = 281mA @ Temperature = +25°C

FREQ (MHz)	Gain (dB)	Isolation (dB)	Input Return Loss (dB)	Output Return Loss (dB)	Stability	
					K	Measure
400	20.17	37.00	0.50	2.30	0.20	0.76
450	19.15	37.03	0.51	2.31	0.25	0.76
500	18.22	37.28	0.53	2.31	0.29	0.76
550	17.39	37.25	0.53	2.31	0.32	0.76
600	16.64	36.94	0.54	2.32	0.34	0.76
650	15.94	37.14	0.56	2.32	0.37	0.76
700	15.29	37.05	0.58	2.33	0.41	0.76
750	14.69	36.86	0.57	2.36	0.44	0.77
800	14.13	37.09	0.59	2.36	0.48	0.77
850	13.62	37.13	0.59	2.34	0.51	0.77
900	13.12	37.25	0.59	2.38	0.56	0.77
950	12.65	36.96	0.60	2.38	0.57	0.77
1000	12.21	37.07	0.61	2.38	0.61	0.77
1050	11.78	36.84	0.62	2.38	0.61	0.78
1100	11.37	36.96	0.63	2.39	0.69	0.78
1150	11.00	36.77	0.63	2.41	0.70	0.78
1200	10.62	36.58	0.64	2.42	0.72	0.78
1250	10.28	36.66	0.64	2.42	0.76	0.78
1300	9.95	36.73	0.65	2.42	0.80	0.78
1350	9.61	36.53	0.66	2.44	0.84	0.78
1400	9.31	36.78	0.65	2.44	0.88	0.79
1450	9.01	36.37	0.66	2.45	0.88	0.79
1500	8.73	36.55	0.67	2.46	0.95	0.79
1550	8.46	36.17	0.67	2.46	0.93	0.79
1600	8.20	36.29	0.67	2.46	0.95	0.79
1650	7.95	36.63	0.68	2.47	1.04	0.79
1700	7.71	36.23	0.68	2.47	1.03	0.79
1750	7.46	36.06	0.67	2.47	1.05	0.79
1800	7.24	36.24	0.68	2.47	1.07	0.79
1850	7.02	36.19	0.68	2.48	1.11	0.79
1900	6.80	35.80	0.68	2.48	1.09	0.79
1950	6.60	35.94	0.68	2.49	1.14	0.79
2000	6.40	35.77	0.68	2.48	1.13	0.79
2050	6.21	35.77	0.68	2.48	1.15	0.79
2100	6.02	35.66	0.68	2.50	1.16	0.80
2150	5.84	35.65	0.68	2.48	1.20	0.79
2200	5.67	35.40	0.67	2.49	1.16	0.80
2250	5.49	35.32	0.67	2.50	1.20	0.80
2300	5.32	35.46	0.66	2.50	1.21	0.80
2350	5.15	35.16	0.67	2.50	1.21	0.80
2400	5.00	35.23	0.66	2.49	1.24	0.80
2450	4.84	35.31	0.66	2.51	1.27	0.80
2500	4.70	35.05	0.66	2.49	1.26	0.80
2550	4.54	35.10	0.65	2.49	1.28	0.80
2600	4.41	35.01	0.65	2.49	1.28	0.80
2650	4.25	34.84	0.65	2.49	1.28	0.80
2700	4.11	34.86	0.66	2.50	1.33	0.80
2750	3.99	34.93	0.65	2.50	1.34	0.80
2800	3.84	34.73	0.65	2.49	1.33	0.80
2850	3.71	34.52	0.65	2.49	1.34	0.79
2900	3.58	34.46	0.65	2.50	1.33	0.80
2950	3.45	34.48	0.64	2.49	1.34	0.80
3000	3.32	34.42	0.66	2.48	1.35	0.80
3050	3.19	34.48	0.64	2.50	1.38	0.80
3100	3.06	34.38	0.65	2.49	1.40	0.80
3150	2.96	34.12	0.64	2.50	1.36	0.80
3200	2.82	34.07	0.65	2.50	1.40	0.80
3250	2.69	34.13	0.66	2.51	1.44	0.80
3300	2.58	34.03	0.65	2.51	1.44	0.80
3350	2.45	33.98	0.67	2.50	1.49	0.80
3400	2.33	33.91	0.66	2.52	1.47	0.80
3450	2.22	33.80	0.66	2.51	1.48	0.80
3500	2.08	33.82	0.68	2.52	1.54	0.80
3550	1.96	33.66	0.69	2.53	1.54	0.80
3600	1.86	33.61	0.68	2.52	1.55	0.80
3650	1.72	33.82	0.71	2.53	1.65	0.80
3700	1.62	33.57	0.69	2.54	1.61	0.80
3750	1.49	33.44	0.71	2.55	1.63	0.80
3800	1.39	33.41	0.71	2.55	1.67	0.80
3850	1.27	33.57	0.72	2.55	1.71	0.81
3900	1.14	33.34	0.73	2.56	1.72	0.81
3950	1.03	33.40	0.74	2.57	1.77	0.81
4000	0.91	33.26	0.75	2.56	1.81	0.80



ISO 9001 ISO 14001 AS 9100 CERTIFIED

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

IF/RF MICROWAVE COMPONENTS



MMIC Amplifier

TAV2-501+

Typical Performance Data

Definitions:

Input Return Loss = -S11 (dB)
Gain(Power Gain) = S21 (dB)
Reverse Isolation = -S12 (dB)
Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 4.50V, Id = 227mA @ Temperature = -45°C

FREQ (MHz)	Gain (dB)	Isolation (dB)	Input Return Loss (dB)	Output Return Loss (dB)	Stability	
					K	Measure
400	20.43	37.02	0.49	2.41	0.21	0.79
450	19.42	36.84	0.50	2.41	0.25	0.78
500	18.49	36.91	0.52	2.41	0.26	0.79
550	17.67	36.98	0.53	2.41	0.30	0.79
600	16.92	36.95	0.53	2.42	0.32	0.79
650	16.21	36.96	0.55	2.42	0.33	0.80
700	15.57	37.01	0.57	2.43	0.40	0.79
750	14.97	36.75	0.56	2.45	0.41	0.80
800	14.41	36.66	0.58	2.46	0.45	0.79
850	13.90	36.84	0.57	2.44	0.48	0.79
900	13.39	36.69	0.58	2.47	0.49	0.80
950	12.93	36.64	0.58	2.48	0.52	0.80
1000	12.48	36.46	0.60	2.47	0.56	0.80
1050	12.06	36.63	0.61	2.48	0.60	0.80
1100	11.65	36.70	0.62	2.49	0.62	0.80
1150	11.27	36.48	0.62	2.50	0.66	0.80
1200	10.90	36.47	0.63	2.51	0.68	0.81
1250	10.55	36.51	0.63	2.51	0.70	0.81
1300	10.22	36.42	0.64	2.52	0.75	0.81
1350	9.88	36.19	0.65	2.53	0.78	0.81
1400	9.58	36.59	0.64	2.54	0.83	0.81
1450	9.28	36.25	0.65	2.55	0.84	0.81
1500	9.00	36.29	0.66	2.55	0.86	0.81
1550	8.73	36.19	0.66	2.54	0.91	0.81
1600	8.47	36.18	0.66	2.55	0.92	0.81
1650	8.21	35.83	0.67	2.56	0.93	0.81
1700	7.97	36.13	0.67	2.56	0.96	0.82
1750	7.73	35.88	0.66	2.56	0.96	0.82
1800	7.50	35.96	0.67	2.56	1.00	0.82
1850	7.28	35.82	0.67	2.57	1.02	0.82
1900	7.06	35.95	0.66	2.57	1.04	0.82
1950	6.86	35.85	0.67	2.58	1.06	0.82
2000	6.66	35.61	0.67	2.57	1.06	0.82
2050	6.47	35.59	0.66	2.56	1.09	0.82
2100	6.28	35.60	0.66	2.59	1.11	0.82
2150	6.09	35.55	0.66	2.56	1.12	0.82
2200	5.93	35.45	0.66	2.58	1.14	0.82
2250	5.75	35.26	0.66	2.59	1.15	0.82
2300	5.58	35.37	0.65	2.59	1.17	0.82
2350	5.41	35.23	0.66	2.58	1.17	0.82
2400	5.26	34.84	0.65	2.58	1.15	0.82
2450	5.10	35.10	0.65	2.59	1.19	0.82
2500	4.95	34.88	0.64	2.58	1.19	0.82
2550	4.80	35.01	0.64	2.57	1.22	0.82
2600	4.66	34.82	0.63	2.58	1.20	0.82
2650	4.52	34.74	0.63	2.57	1.21	0.82
2700	4.37	34.65	0.64	2.58	1.23	0.82
2750	4.24	34.60	0.63	2.58	1.25	0.82
2800	4.10	34.70	0.63	2.57	1.27	0.82
2850	3.97	34.46	0.64	2.57	1.26	0.82
2900	3.84	34.55	0.63	2.57	1.28	0.82
2950	3.71	34.35	0.62	2.57	1.26	0.82
3000	3.58	34.24	0.63	2.56	1.28	0.82
3050	3.45	34.24	0.62	2.58	1.28	0.82
3100	3.32	34.16	0.63	2.58	1.30	0.82
3150	3.21	34.12	0.61	2.58	1.30	0.82
3200	3.07	34.05	0.62	2.58	1.33	0.82
3250	2.95	34.00	0.64	2.59	1.36	0.82
3300	2.84	33.93	0.63	2.59	1.35	0.82
3350	2.70	33.90	0.64	2.58	1.39	0.82
3400	2.59	33.82	0.64	2.59	1.39	0.82
3450	2.48	33.74	0.63	2.58	1.39	0.82
3500	2.34	33.77	0.65	2.59	1.43	0.82
3550	2.23	33.65	0.66	2.61	1.46	0.82
3600	2.11	33.46	0.66	2.59	1.45	0.82
3650	1.98	33.58	0.67	2.61	1.52	0.82
3700	1.88	33.53	0.67	2.62	1.52	0.83
3750	1.75	33.41	0.68	2.61	1.54	0.82
3800	1.64	33.56	0.69	2.62	1.60	0.82
3850	1.53	33.30	0.68	2.63	1.58	0.83
3900	1.40	33.36	0.69	2.64	1.61	0.83
3950	1.29	33.14	0.70	2.63	1.63	0.83
4000	1.17	33.19	0.72	2.64	1.67	0.83



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

IF/RF MICROWAVE COMPONENTS



REV. A

TAV2-501+

12/15/2020

Page 3 of 7

Typical Performance Data

Definitions:

Input Return Loss = -S11 (dB)
 Gain(Power Gain) = S21 (dB)
 Reverse Isolation = -S12 (dB)
 Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 4.50V, Id = 309mA @ Temperature = +85°C

FREQ (MHz)	Gain (dB)	Isolation (dB)	Input Return Loss (dB)	Output Return Loss (dB)	Stability	
					K	Measure
400	19.97	37.02	0.49	2.41	0.23	0.75
450	18.95	36.84	0.50	2.41	0.26	0.75
500	18.02	37.51	0.54	2.26	0.31	0.75
550	17.19	37.20	0.55	2.27	0.35	0.74
600	16.44	37.56	0.55	2.27	0.37	0.75
650	15.74	37.14	0.57	2.27	0.39	0.75
700	15.09	37.20	0.58	2.29	0.45	0.75
750	14.49	37.33	0.58	2.31	0.48	0.76
800	13.93	37.26	0.60	2.32	0.49	0.76
850	13.42	37.28	0.60	2.30	0.53	0.76
900	12.92	37.18	0.60	2.33	0.57	0.76
950	12.45	37.03	0.61	2.34	0.58	0.77
1000	12.01	36.97	0.62	2.33	0.63	0.76
1050	11.59	37.15	0.63	2.34	0.67	0.76
1100	11.18	36.93	0.64	2.35	0.69	0.76
1150	10.81	36.82	0.64	2.37	0.72	0.77
1200	10.43	36.93	0.65	2.38	0.77	0.77
1250	10.09	36.87	0.65	2.38	0.80	0.77
1300	9.76	36.82	0.66	2.38	0.84	0.77
1350	9.42	36.90	0.67	2.40	0.88	0.78
1400	9.13	36.65	0.66	2.40	0.90	0.77
1450	8.83	36.55	0.67	2.41	0.92	0.78
1500	8.54	36.45	0.68	2.42	0.96	0.78
1550	8.27	36.40	0.68	2.42	0.98	0.78
1600	8.02	36.60	0.68	2.42	1.01	0.78
1650	7.76	36.56	0.69	2.43	1.06	0.78
1700	7.52	36.38	0.69	2.43	1.08	0.78
1750	7.28	36.43	0.69	2.44	1.11	0.78
1800	7.06	36.21	0.69	2.44	1.12	0.78
1850	6.84	36.14	0.69	2.45	1.14	0.78
1900	6.62	36.23	0.69	2.44	1.16	0.78
1950	6.42	35.76	0.70	2.46	1.14	0.79
2000	6.22	35.70	0.69	2.44	1.17	0.78
2050	6.03	35.97	0.69	2.46	1.23	0.79
2100	5.84	35.83	0.69	2.47	1.24	0.79
2150	5.65	35.72	0.69	2.45	1.24	0.79
2200	5.49	35.49	0.69	2.46	1.24	0.79
2250	5.31	35.75	0.69	2.47	1.31	0.79
2300	5.14	35.53	0.68	2.47	1.27	0.79
2350	4.97	35.39	0.69	2.47	1.31	0.79
2400	4.82	35.36	0.69	2.47	1.30	0.79
2450	4.66	35.17	0.68	2.48	1.33	0.79
2500	4.52	35.14	0.68	2.48	1.32	0.79
2550	4.36	35.00	0.68	2.47	1.34	0.79
2600	4.23	34.91	0.67	2.47	1.31	0.79
2650	4.07	34.99	0.67	2.47	1.36	0.79
2700	3.92	34.85	0.68	2.48	1.38	0.79
2750	3.80	35.01	0.67	2.48	1.39	0.79
2800	3.65	34.74	0.68	2.47	1.41	0.79
2850	3.52	34.57	0.68	2.47	1.41	0.79
2900	3.39	34.75	0.68	2.48	1.45	0.79
2950	3.26	34.35	0.67	2.47	1.40	0.79
3000	3.13	34.41	0.69	2.47	1.44	0.79
3050	3.00	34.23	0.67	2.49	1.43	0.79
3100	2.87	34.30	0.68	2.49	1.48	0.79
3150	2.76	34.37	0.67	2.48	1.47	0.79
3200	2.62	34.11	0.68	2.49	1.48	0.79
3250	2.49	34.06	0.69	2.50	1.51	0.79
3300	2.38	34.08	0.69	2.50	1.53	0.80
3350	2.25	34.12	0.71	2.49	1.58	0.79
3400	2.13	33.86	0.70	2.50	1.57	0.80
3450	2.02	33.83	0.70	2.50	1.58	0.79
3500	1.88	33.87	0.72	2.50	1.64	0.79
3550	1.76	33.62	0.73	2.52	1.65	0.80
3600	1.65	33.56	0.73	2.51	1.65	0.79
3650	1.51	33.86	0.75	2.53	1.76	0.80
3700	1.41	33.61	0.74	2.54	1.73	0.80
3750	1.28	33.55	0.76	2.53	1.78	0.80
3800	1.17	33.48	0.76	2.55	1.80	0.80
3850	1.06	33.23	0.76	2.55	1.79	0.80
3900	0.93	33.44	0.77	2.56	1.86	0.80
3950	0.81	33.39	0.78	2.57	1.90	0.80
4000	0.69	33.45	0.80	2.57	1.97	0.80



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site
www.minicircuits.com



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

IF/RF MICROWAVE COMPONENTS



MMIC Amplifier

TAV2-501+

Typical Performance Data

Definitions:

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 4.50V, Id = 281mA @ Temperature = +25°C

FREQ (MHz)	Gain (dB)	Isolation (dB)	Input Return Loss (dB)	Output Return Loss (dB)	Stability		IP-3 Output (dBm)	1dB Comp. Output (dBm)	Noise Figure (dB)
					K	Measure			
400	-44.12	84.21	0.08	0.09	481.91	0.04	-	-	-
450	-40.62	72.55	0.09	0.10	110.82	0.05	-	-	-
500	-37.67	70.71	0.10	0.11	69.97	0.05	-6.66	-22.23	32.89
550	-35.20	69.75	0.11	0.11	55.55	0.05	-6.82	-19.75	30.95
600	-32.58	73.58	0.10	0.11	63.04	0.05	3.28	-17.95	30.96
650	-30.16	74.62	0.08	0.11	43.32	0.05	2.33	-14.46	21.88
700	-28.16	70.71	0.12	0.16	42.43	0.07	5.73	-12.60	21.49
750	-25.80	73.08	0.13	0.17	47.36	0.07	9.86	-10.81	20.33
800	-23.62	72.22	0.13	0.19	38.61	0.08	15.74	-8.09	15.64
850	-21.52	70.39	0.14	0.21	29.31	0.09	15.84	-5.89	12.94
900	-19.44	72.17	0.15	0.24	34.66	0.10	19.37	-4.29	12.65
950	-17.39	70.16	0.16	0.27	24.87	0.12	19.53	-3.92	11.87
1000	-15.34	60.39	0.17	0.30	7.90	0.13	23.07	-2.94	8.36
1050	-13.32	61.69	0.18	0.36	9.28	0.16	27.97	0.58	7.79
1100	-11.29	59.78	0.21	0.44	7.91	0.19	27.46	3.72	7.78
1150	-9.23	56.36	0.24	0.53	5.54	0.22	30.72	4.27	6.20
1200	-7.17	54.32	0.27	0.66	4.54	0.27	32.56	4.46	5.89
1250	-5.08	52.22	0.33	0.82	4.06	0.33	34.74	6.94	5.75
1300	-2.94	50.15	0.38	1.04	3.64	0.41	35.48	9.00	5.37
1350	-0.78	47.35	0.47	1.34	2.85	0.51	34.76	11.80	5.48
1400	1.39	44.43	0.59	1.75	2.38	0.63	35.52	14.49	5.02
1450	3.56	41.57	0.76	2.30	2.03	0.77	34.62	15.34	4.18
1500	5.73	39.20	0.99	3.04	1.83	0.93	34.40	16.43	3.63
1550	7.80	37.09	1.32	4.02	1.78	1.09	35.97	18.56	3.13
1600	9.79	34.49	1.75	5.17	1.56	1.21	37.88	22.87	2.78
1650	11.66	32.24	2.34	6.37	1.45	1.27	37.55	24.95	2.37
1700	13.39	30.25	3.18	7.52	1.38	1.25	37.42	26.06	2.06
1750	14.98	28.35	4.43	8.63	1.31	1.16	38.41	27.11	1.96
1800	16.30	26.76	6.33	10.38	1.28	1.05	37.16	28.00	1.63
1850	17.16	25.51	8.29	14.51	1.23	0.99	40.89	28.57	1.56
1900	17.26	25.10	7.47	34.61	1.21	1.02	39.45	29.36	1.29
1950	16.50	25.61	4.90	15.44	1.20	1.10	39.89	29.07	1.27
2000	15.19	26.59	3.07	9.68	1.19	1.14	40.86	27.63	1.24
2050	13.66	27.80	2.02	7.02	1.19	1.14	37.72	27.10	1.31
2100	12.15	29.07	1.43	5.51	1.19	1.10	40.02	26.63	1.24
2150	10.73	30.18	1.08	4.54	1.20	1.04	40.44	26.11	1.62
2200	9.44	31.22	0.86	3.90	1.21	0.99	38.15	25.45	1.36
2250	8.28	32.06	0.71	3.43	1.21	0.94	36.71	24.49	1.38
2300	7.21	33.02	0.62	3.08	1.25	0.89	36.71	24.16	1.56
2350	6.26	33.43	0.54	2.80	1.22	0.84	36.69	22.31	1.64
2400	5.40	34.28	0.49	2.59	1.26	0.81	34.74	20.82	2.44
2450	4.60	34.66	0.45	2.43	1.26	0.78	33.46	19.87	2.61
2500	3.89	35.17	0.42	2.27	1.29	0.74	37.15	18.72	2.34
2550	3.25	35.33	0.39	2.15	1.26	0.72	35.09	17.75	2.28
2600	2.64	35.94	0.37	2.07	1.30	0.70	33.57	16.71	2.64
2650	2.08	36.56	0.34	1.98	1.32	0.68	33.45	16.07	3.19
2700	1.58	36.45	0.34	1.91	1.33	0.66	35.94	15.70	2.99
2750	1.12	36.88	0.33	1.84	1.39	0.65	32.23	15.28	3.02
2800	0.67	36.65	0.32	1.80	1.35	0.63	36.72	15.39	3.48
2850	0.27	37.15	0.32	1.74	1.39	0.62	33.20	15.69	3.66
2900	-0.09	37.11	0.31	1.70	1.39	0.61	34.43	15.35	3.57
2950	-0.44	37.20	0.30	1.67	1.40	0.60	34.10	13.86	3.79
3000	-0.77	37.49	0.30	1.66	1.44	0.60	34.46	13.81	4.27
3050	-1.04	37.42	0.29	1.62	1.42	0.59	34.09	12.99	3.98
3100	-1.31	37.47	0.30	1.61	1.44	0.59	32.87	11.98	4.25
3150	-1.57	37.79	0.30	1.58	1.51	0.58	36.11	12.28	4.05
3200	-1.82	37.32	0.30	1.58	1.49	0.58	34.35	11.14	4.75
3250	-2.02	37.95	0.30	1.55	1.54	0.57	33.64	17.38	4.12
3300	-2.22	37.50	0.31	1.54	1.54	0.56	33.75	17.65	5.43
3350	-2.40	37.45	0.31	1.56	1.57	0.57	33.46	17.11	4.74
3400	-2.59	37.50	0.32	1.55	1.64	0.57	33.52	17.28	5.27
3450	-2.71	37.61	0.31	1.54	1.61	0.57	33.97	17.05	5.12
3500	-2.87	37.40	0.32	1.53	1.63	0.56	32.31	17.13	5.07
3550	-3.00	37.34	0.33	1.55	1.68	0.57	33.55	16.61	4.69
3600	-3.13	37.17	0.33	1.55	1.67	0.57	33.74	16.97	5.88
3650	-3.22	37.30	0.34	1.55	1.70	0.57	33.85	16.48	5.83
3700	-3.32	37.09	0.35	1.55	1.72	0.57	32.27	15.85	5.44
3750	-3.39	37.12	0.35	1.56	1.75	0.57	33.99	16.64	5.09
3800	-3.46	37.16	0.35	1.57	1.76	0.58	34.07	15.77	6.13
3850	-3.53	36.29	0.38	1.58	1.76	0.57	31.88	15.60	5.12
3900	-3.58	36.70	0.37	1.59	1.81	0.58	33.94	16.53	5.33
3950	-3.61	36.44	0.38	1.59	1.79	0.58	31.98	15.84	5.89
4000	-3.64	36.39	0.39	1.62	1.83	0.59	33.61	16.32	5.25



ISO 9001 ISO 14001 AS 9100 CERTIFIED

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site
 The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

IF/RF MICROWAVE COMPONENTS



MMIC Amplifier

Typical Performance Data

TAV2-501+

Definitions:

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 4.50V, Id = 182mA @ Temperature = -45°C

FREQ (MHz)	Gain (dB)	Isolation (dB)	Input Return Loss (dB)	Output Return Loss (dB)	Stability		IP-3 Output (dBm)	1dB Comp. Output (dBm)	Noise Figure (dB)
400	-43.29	84.21	0.08	0.09	75.94	0.04	-	-	-
450	-40.80	72.55	0.09	0.10	68.09	0.05	-	-	-
500	-37.54	73.45	0.09	0.11	91.30	0.05	-8.56	-22.57	30.85
550	-34.82	83.03	0.11	0.12	257.32	0.05	-3.81	-19.09	28.87
600	-32.33	65.81	0.10	0.12	26.12	0.05	-2.49	-19.09	28.89
650	-29.98	79.24	0.10	0.13	99.59	0.06	2.45	-14.10	20.53
700	-27.71	66.59	0.12	0.16	25.30	0.07	4.92	-11.95	20.23
750	-25.43	68.40	0.13	0.16	26.52	0.07	7.80	-11.10	17.95
800	-23.27	62.34	0.12	0.16	9.84	0.07	13.00	-8.46	17.50
850	-21.17	68.25	0.14	0.21	21.16	0.09	13.90	-5.80	14.09
900	-19.11	72.43	0.14	0.22	30.44	0.10	24.54	-4.79	13.51
950	-17.06	68.83	0.15	0.25	18.36	0.11	20.82	-4.25	12.80
1000	-15.09	66.93	0.18	0.31	16.44	0.13	24.37	-4.42	11.30
1050	-13.05	62.78	0.18	0.35	9.62	0.15	24.71	0.81	8.19
1100	-11.01	58.53	0.20	0.42	5.93	0.18	27.15	3.40	8.00
1150	-8.99	55.45	0.24	0.50	4.58	0.21	28.82	4.55	7.21
1200	-6.92	53.85	0.26	0.63	3.80	0.26	31.09	5.11	5.57
1250	-4.85	50.82	0.30	0.79	2.89	0.32	34.16	6.82	5.37
1300	-2.73	48.35	0.35	0.99	2.25	0.39	34.46	8.90	4.64
1350	-0.61	46.43	0.45	1.28	2.21	0.49	33.29	11.84	4.26
1400	1.52	44.35	0.56	1.69	2.06	0.62	32.91	13.39	3.45
1450	3.64	41.79	0.73	2.22	1.87	0.76	31.34	15.37	3.19
1500	5.75	39.38	0.93	2.92	1.66	0.91	31.69	16.65	2.87
1550	7.80	37.03	1.21	3.80	1.50	1.06	30.81	17.85	2.40
1600	9.76	34.44	1.61	4.80	1.35	1.18	33.24	20.91	2.00
1650	11.63	32.13	2.12	5.82	1.23	1.24	32.28	21.74	1.77
1700	13.37	30.23	2.85	6.75	1.20	1.23	33.53	23.42	1.48
1750	14.99	28.23	3.93	7.65	1.15	1.15	34.60	25.00	1.36
1800	16.43	26.48	5.51	9.04	1.11	1.05	34.47	28.28	1.31
1850	17.47	25.15	7.31	12.25	1.09	0.98	36.31	29.70	1.14
1900	17.73	24.61	6.99	22.58	1.08	1.01	36.08	30.22	0.85
1950	17.08	24.88	4.73	17.87	1.06	1.10	40.59	29.53	0.78
2000	15.78	25.92	2.93	10.53	1.06	1.16	40.85	25.83	0.80
2050	14.23	27.25	1.90	7.48	1.07	1.16	40.06	27.25	0.82
2100	12.66	28.47	1.33	5.79	1.07	1.13	38.96	26.39	0.77
2150	11.22	29.66	1.01	4.75	1.09	1.07	37.20	25.50	1.00
2200	9.90	30.77	0.81	4.06	1.11	1.01	36.50	24.70	0.94
2250	8.69	31.57	0.67	3.57	1.11	0.96	38.51	23.42	0.98
2300	7.62	32.50	0.59	3.21	1.14	0.91	36.08	21.84	1.04
2350	6.67	33.04	0.52	2.93	1.15	0.87	36.20	22.09	1.26
2400	5.77	33.70	0.48	2.71	1.17	0.83	33.64	21.59	1.50
2450	5.00	34.26	0.43	2.52	1.16	0.80	33.93	19.60	1.91
2500	4.27	35.02	0.40	2.37	1.23	0.77	36.67	18.61	1.75
2550	3.60	35.24	0.40	2.23	1.25	0.74	34.92	17.50	1.69
2600	3.01	35.80	0.37	2.13	1.27	0.72	33.69	16.50	2.10
2650	2.44	35.96	0.35	2.05	1.27	0.70	35.49	16.27	2.37
2700	1.94	36.18	0.35	1.98	1.31	0.68	32.23	15.76	2.42
2750	1.48	36.55	0.34	1.91	1.33	0.66	34.08	16.65	2.71
2800	1.03	36.86	0.33	1.86	1.33	0.65	33.31	16.47	2.56
2850	0.63	36.84	0.32	1.81	1.34	0.64	33.98	16.39	3.15
2900	0.27	36.95	0.32	1.76	1.34	0.63	34.15	15.53	3.04
2950	-0.08	37.37	0.31	1.73	1.40	0.62	34.58	13.76	3.22
3000	-0.39	37.08	0.32	1.69	1.38	0.61	35.15	13.96	3.59
3050	-0.68	37.41	0.31	1.66	1.42	0.60	33.36	13.82	2.88
3100	-0.95	37.56	0.30	1.64	1.43	0.60	35.15	13.54	3.08
3150	-1.20	37.70	0.30	1.63	1.44	0.59	34.75	12.47	2.85
3200	-1.44	37.67	0.30	1.62	1.49	0.59	32.28	11.53	2.80
3250	-1.65	37.27	0.30	1.60	1.46	0.58	32.73	18.09	3.60
3300	-1.85	37.90	0.31	1.59	1.53	0.58	32.85	17.95	2.97
3350	-2.03	37.38	0.31	1.57	1.47	0.58	34.33	17.44	4.13
3400	-2.19	37.24	0.31	1.57	1.50	0.58	32.96	17.28	4.02
3450	-2.35	37.38	0.32	1.56	1.54	0.57	33.11	16.04	4.12
3500	-2.48	37.28	0.32	1.56	1.51	0.57	33.86	16.45	3.37
3550	-2.62	37.31	0.32	1.57	1.58	0.58	33.70	16.61	3.73
3600	-2.73	37.18	0.33	1.58	1.56	0.58	34.29	16.06	3.86
3650	-2.86	36.79	0.34	1.57	1.58	0.58	33.39	16.33	4.56
3700	-2.94	37.36	0.34	1.57	1.66	0.57	33.44	16.25	3.71
3750	-3.03	36.84	0.37	1.58	1.69	0.57	32.92	16.01	4.24
3800	-3.10	36.67	0.35	1.59	1.65	0.58	34.16	15.69	4.76
3850	-3.16	36.79	0.37	1.59	1.69	0.58	32.19	15.57	4.85
3900	-3.22	36.50	0.37	1.61	1.64	0.59	32.55	16.15	4.21
3950	-3.28	36.43	0.37	1.61	1.69	0.58	34.61	16.51	4.94
4000	-3.33	36.08	0.39	1.64	1.71	0.59	32.21	16.03	3.87



ISO 9001 ISO 14001 AS 9100 CERTIFIED



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

IF/RF MICROWAVE COMPONENTS

REV. A

TAV2-501+

12/15/2020

Page 6 of 7

Typical Performance Data

Definitions:

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 4.50V, Id = 364mA @ Temperature = +85°C

FREQ (MHz)	Gain (dB)	Isolation (dB)	Input Return Loss (dB)	Output Return Loss (dB)	Stability		IP-3 Output (dBm)	1dB Comp. Output (dBm)	Noise Figure (dB)
					K	Measure			
400	-43.41	84.21	0.08	0.09	172.22	0.06	-	-	-
450	-40.86	72.55	0.09	0.10	170.18	0.07	-	-	-
500	-37.66	75.86	0.12	0.16	240.94	0.07	-10.29	-22.91	32.56
550	-35.17	78.84	0.14	0.18	312.75	0.08	-2.66	-19.51	29.87
600	-32.65	69.97	0.14	0.18	87.75	0.08	4.71	-19.51	30.40
650	-30.35	77.65	0.14	0.19	170.88	0.08	-1.21	-14.52	22.22
700	-28.08	69.00	0.16	0.22	61.50	0.10	9.11	-12.36	21.72
750	-25.82	64.94	0.17	0.23	33.69	0.10	8.60	-11.51	18.58
800	-23.70	67.16	0.16	0.23	33.79	0.10	10.38	-8.85	18.45
850	-21.56	68.03	0.18	0.28	37.59	0.12	14.16	-6.17	14.97
900	-19.51	66.06	0.19	0.30	26.44	0.13	19.60	-5.16	14.66
950	-17.44	76.95	0.20	0.32	84.24	0.14	22.42	-4.61	13.57
1000	-15.43	65.40	0.22	0.39	22.88	0.17	25.07	-4.77	13.27
1050	-13.38	64.45	0.23	0.44	19.57	0.19	30.13	0.48	11.71
1100	-11.36	61.93	0.25	0.52	13.99	0.22	29.47	3.11	8.46
1150	-9.30	56.76	0.29	0.60	8.00	0.25	29.68	4.27	8.36
1200	-7.22	53.77	0.32	0.73	5.69	0.30	31.81	4.84	8.14
1250	-5.12	51.66	0.36	0.90	4.74	0.36	37.31	6.58	7.83
1300	-2.98	49.69	0.42	1.11	3.95	0.43	38.70	8.71	6.99
1350	-0.83	47.08	0.52	1.42	3.36	0.53	35.58	11.72	6.36
1400	1.33	44.50	0.65	1.84	2.85	0.65	37.23	13.34	5.47
1450	3.50	41.70	0.83	2.41	2.43	0.79	36.02	15.45	4.97
1500	5.65	39.50	1.06	3.16	2.19	0.94	36.29	16.79	4.40
1550	7.73	36.99	1.38	4.13	1.91	1.10	36.74	18.14	3.81
1600	9.72	34.65	1.84	5.28	1.75	1.21	37.00	21.54	3.34
1650	11.59	32.40	2.47	6.48	1.59	1.26	37.84	24.59	2.86
1700	13.31	30.56	3.39	7.62	1.54	1.23	37.41	26.22	2.51
1750	14.85	28.61	4.79	8.78	1.45	1.14	39.30	26.91	2.48
1800	16.12	26.96	6.89	10.65	1.38	1.03	43.08	27.85	2.08
1850	16.90	25.82	8.95	15.13	1.33	0.98	39.87	29.15	1.70
1900	16.90	25.56	7.72	34.68	1.31	1.03	39.82	29.43	1.63
1950	16.08	26.15	4.96	14.97	1.31	1.12	40.87	28.75	1.59
2000	14.75	27.03	3.13	9.64	1.29	1.16	37.92	27.16	1.61
2050	13.25	28.22	2.10	7.05	1.29	1.15	39.77	26.99	1.67
2100	11.75	29.51	1.50	5.56	1.30	1.11	40.26	26.35	1.70
2150	10.36	30.40	1.15	4.62	1.29	1.05	37.43	25.82	2.00
2200	9.09	31.54	0.94	3.98	1.33	1.00	39.64	24.54	2.00
2250	7.91	32.47	0.79	3.52	1.36	0.95	36.80	23.07	2.14
2300	6.88	33.04	0.69	3.17	1.37	0.90	37.26	21.50	2.25
2350	5.94	33.71	0.61	2.91	1.38	0.86	36.44	21.81	2.52
2400	5.07	34.43	0.57	2.69	1.43	0.83	35.33	21.30	2.90
2450	4.31	34.90	0.52	2.52	1.44	0.79	34.10	19.22	3.19
2500	3.60	35.52	0.49	2.37	1.48	0.77	37.56	18.15	2.84
2550	2.93	36.19	0.47	2.26	1.55	0.74	35.99	17.02	3.77
2600	2.36	36.30	0.45	2.16	1.54	0.72	34.33	15.98	3.75
2650	1.80	36.70	0.43	2.07	1.58	0.70	35.64	15.77	4.23
2700	1.30	36.69	0.42	1.99	1.57	0.68	32.51	15.25	4.27
2750	0.84	36.84	0.41	1.94	1.61	0.67	35.27	16.18	4.51
2800	0.40	37.21	0.40	1.88	1.65	0.65	33.92	16.00	4.52
2850	0.01	37.31	0.39	1.84	1.65	0.65	36.57	15.92	4.91
2900	-0.35	37.30	0.39	1.80	1.70	0.63	34.49	15.03	4.94
2950	-0.69	37.37	0.38	1.77	1.71	0.63	35.31	13.22	5.08
3000	-1.00	37.60	0.38	1.74	1.75	0.62	35.53	13.42	5.54
3050	-1.29	37.57	0.38	1.71	1.75	0.61	34.16	13.27	5.11
3100	-1.55	37.59	0.36	1.69	1.76	0.61	36.54	12.99	5.44
3150	-1.81	37.94	0.37	1.69	1.83	0.61	35.26	11.91	5.24
3200	-2.03	37.66	0.38	1.67	1.84	0.60	32.58	10.95	5.15
3250	-2.24	37.80	0.37	1.66	1.86	0.60	35.11	17.75	5.74
3300	-2.44	37.56	0.37	1.64	1.86	0.59	33.84	17.60	5.53
3350	-2.61	37.77	0.38	1.64	1.91	0.59	36.66	17.07	6.27
3400	-2.78	37.53	0.38	1.64	1.93	0.59	33.59	16.90	6.41
3450	-2.93	37.65	0.40	1.63	1.98	0.59	33.08	15.62	6.39
3500	-3.07	37.27	0.39	1.63	1.96	0.59	35.25	16.04	5.77
3550	-3.19	37.60	0.40	1.65	2.04	0.59	33.92	16.21	6.09
3600	-3.30	37.40	0.40	1.66	2.05	0.60	34.70	15.65	6.11
3650	-3.42	37.25	0.42	1.66	2.07	0.60	33.70	15.93	6.76
3700	-3.49	37.02	0.42	1.66	2.08	0.59	35.55	15.86	6.40
3750	-3.58	36.58	0.44	1.68	2.08	0.60	32.27	15.61	6.61
3800	-3.64	36.87	0.43	1.68	2.11	0.60	35.39	15.28	7.31
3850	-3.69	36.65	0.45	1.69	2.13	0.60	33.86	15.17	7.18
3900	-3.74	36.45	0.45	1.70	2.13	0.61	32.55	15.77	6.63
3950	-3.78	36.54	0.46	1.72	2.19	0.61	36.71	16.14	7.31
4000	-3.83	36.09	0.48	1.75	2.21	0.62	33.61	15.66	6.75



ISO 9001 ISO 14001 AS 9100 CERTIFIED



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site

The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

IF/RF MICROWAVE COMPONENTS









REV. A

TAV2-501+

12/15/2020

Page 7 of 7

Typical Performance Curves



Mini-Circuits®

ISO 9001 ISO 14001 AS 9100 CERTIFIED

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site
minicircuits.com



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com









IF/RF MICROWAVE COMPONENTS

minicircuits.com



REV. A
TAV2-501+
12/15/2020
Page 1 of 3

Typical Performance Curves



Mini-Circuits®

ISO 9001 ISO 14001 AS 9100 CERTIFIED

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site
minicircuits.com











IF/RF MICROWAVE COMPONENTS

minicircuits.com

REV. A
TAV2-501+
12/15/2020
Page 2 of 3

Typical Performance Curves





Case Style

MC

MC1631-1

Outline Dimensions

PCB Land Pattern



Suggested Layout,
Tolerance to be within $\pm .002$

SE #.	A	B	C	D	E	F	G	H	J	K	L	M	N	P
MC1631-1	.079 (2.00)	.079 (2.00)	.039 (1.00)	.047 (1.20)	.024 (.60)	.009 (.23)	.014 (.35)	.020 (.50)	.008 (.20)	.002 (.05)	.106 (2.70)	.049 (1.25)	.026 (.65)	.031 (.80)

CASE #.	Q	R	WT, GRAM
MC1631-1	.010 (.25)	.012 (.30)	.006

Dimensions are in inches (mm). Tolerances: 2 Pl. $\pm .01$; 3 Pl. $\pm .005$

Notes:

1. Case material: Plastic.
2. Termination finish:

For RoHS Case Styles: Tin-Silver over Nickel plated or Matte-Tin Plated (See Data sheet).
All models, (+) suffix.

3. Lead #1 identifier shall be located in the cross-hatched area shown.
Identifier may be either a molded or marked feature.

 **Mini-Circuits®**
ISO 9001 ISO 14001 CERTIFIED

ALL NEW
minicircuits.com

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site




The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

RF/I/F MICROWAVE COMPONENTS

Tape & Reel Packaging TR-F66

DEVICE ORIENTATION IN T&R



Tape Width, mm	Device Cavity Pitch, mm	Reel Size, inches	Devices per Reel see note	
8	4	7	Small quantity standard	20
				50
				100
				200
				500
		7	Standard	1000, 2000, 3000

Note: Please consult individual model data sheet to determine device per reel availability.

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: www.minicircuits.com/pages/pdfs/tape.pdf



Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Mini-Circuits ISO 9001 & ISO 14001 Certified


THIRD ANGLE PROJECTION



REVISIONS

REV	ECN No.	DESCRIPTION	DATE	DR	AUTH
OR	ECO-003375	NEW RELEASE	07/22/20	ITG	CM

SUGGESTED MOUNTING CONFIGURATION
FOR MC1631-1 CASE STYLE



NOTES:

1. LINE WIDTH & GAP PARAMETERS ARE SHOWN FOR ROGERS RO4350B WITH DIELECTRIC THICKNESS $.010 \pm .001$. COPPER: 1/2 OZ. EACH SIDE.
FOR OTHER MATERIALS LINE WIDTH & GAP MAY NEED TO BE MODIFIED.
3. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.



DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER).



DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK.

UNLESS OTHERWISE SPECIFIED

DIMENSIONS ARE IN INCHES

TOLERANCES ON:

2 PL DECIMALS $\pm .005$ 3 PL DECIMALS $\pm .005$ ANGLES $\pm .5^\circ$ FRACTIONS $\pm .005$ 

INITIALS

DATE

DRAWN ITG 07/22/20

CHECKED GF 07/22/20

APPROVED CM 07/22/20



Mini-Circuits®

13 Neptune Avenue
Brooklyn NY 11235



PL, MC1631-1, TB-TAV2-501+

SIZE A CODE IDENT 15542 DRAWING NO: 98-PL-685 REV: OR

FILE: 98PL685 SCALE: 12:1 SHEET: 1 OF 1

THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS.
EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE
AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY
DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO.
THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE
PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.

Evaluation Board and Circuit



Schematic Diagram

Notes:

1. 50 Ohm SMA Female connectors.
2. PCB Material: RO4350 or equivalent,
Dielectric Constant=3.5, Thickness=.010 inch.

 Mini-Circuits®



Environmental Specifications

ENV08T2

All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-45° to 85°C or -40° to 85°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-65° to 150° C Ambient Environment	Individual Model Data Sheet
Thermal Shock	-55° to 100°C, 100 cycles	MIL-STD-202, Method 107, Condition A-3, except +100°C
Mechanical Shock	1.5Kg, 0.5 ms, 5 shock pulses, Y1 direction only	MIL-STD-883, Method 2002, Condition B, except Y1 direction only
Vibration (Variable Frequency)	50g peak	MIL-STD-883, Method 2007, Condition B
Autoclave	15 psig, 100% RH, 121°C, 96 hours	JESD22-A102, Condition C
HAST	130°C, 85% RH, 96 hours	JESD22-A110
Solderability	10X Magnification	J-STD-002, Para 4.2.5, Test S, 95% Coverage
Solder Reflow Heat	Sn-Pb Eutetic Process: 240°C peak Pb-Free Process: 260°C peak	J-STD-020, Table 4-1, 4-2 and 5-2; Figure 5-1
Moisture Sensitivity: Level 1	Bake at 125°C for 24 hours Soak at 85°C/85% RH for 168 hours, Reflow 3 cycles at 260°C peak	J-STD-020
Marking Resistance to Solvents	Isopropyl alcohol + mineral spirits at 25°C; terpene defluxer at 25°C; distilled water + propylene glycol monomethyl ether +	MIL-STD-202, Method 215



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
	monoethanolamine at 63°C to 70°C	