

Solid state


SPI RF SP8T Switch

SPI-SP8T-6G

50Ω 1 to 6000 MHz

The Big Deal

- Daisy Chain SPI Control
- High Isolation (80 dB typ)
- High speed switching (6 μs typ)
- High power handling (+27 dBm max)
- SMP snap-on RF connectors



Generic photo used for illustration purposes only

Case Style: PM2656

Product Overview

Mini-Circuits' SPI-SP8T-6G is a low cost, high speed solid state RF SP8T absorptive switch, with control and power via a Hirose DF11 connector. The model contains an electronic, high speed (6 μs typ switching time), high linearity (IP3 50 dBm typ), SP8T switch. The RF switch is operated using a 3-wire SPI interface compatible with TTL and LVTTTL voltages and allows connecting up to 50 units in series to the same control line in a 'Daisy Chain' configuration. The RF switch operates over a wide frequency band from 1 to 6000 MHz with high isolation (80 dB typical) making the switch perfectly suitable for a wide variety of RF applications.

The SPI-SP8T-6G is constructed in a compact, rugged metal case (3.68" x 3.27" x 0.40") with 9 SMP(M) connectors (COM, and J1 to J8), and two Hirose DF11 connectors providing SPI control and power, one for input and one for output when connecting multiple units in series.

Key Features

Feature	Advantages
Daisy chain SPI control	Allows connecting up to 50 units in series to a single power supply and 3 wire SPI control.
RF SP8T absorptive switch	Wideband (1 to 6000 MHz) with high isolation (80 dB typ.), and high power rating (+27 dBm through path).
High Linearity (IP3 +50 dBm typ.)	Results in little or negligible inter-modulation generation, meeting requirements for digital communications signals
Solid state switch	Provides high speed (6 μs typ) switching with no wear on the switch as with electro-mechanical designs
DC Blocking	No need for external DC blocking circuitry
SMP connectors	Snap on RF connectors allow quick assembly and disassembly and the small size of SMP connectors makes tighter assemblies possible



Solid state

SPI RF SP8T Switch

SPI-SP8T-6G

50Ω 1 to 6000 MHz

Features

- High speed switching (6 μ s typ)
- 1 to 6000 MHz SP8T absorptive RF switch
- High power handling, +27 dBm
- High linearity (IP3 +50 dBm)
- High isolation (80 dB typ)
- SPI control
- Daisy-chain up to 50 switches to control through a single interface (see pages 4-5)
- Easy installation and operation



Generic photo used for illustration purposes only
Case Style: PM2656


Applications

- R&D
- Automated Test equipment
- Controlling RF signal paths

RoHS Compliant

See our web site for RoHS Compliance methodologies and qualifications

Block Diagram



RF Electrical Specifications @ +25°C

Parameter	Port	Conditions	Min.	Typ.	Max.	Units
Operating Frequency			1		6000	MHz
Insertion Loss	COM to active ports 1-8	1 to 3000 MHz	–	3.2	5.0	dB
		3000 to 6000 MHz	–	4.7	6.5	
Isolation	Between any two ports of J1 to J8	1 to 3000 MHz	70	95	–	dB
		3000 to 6000 MHz	65	90	–	
	COM to any terminated port	1 to 3000 MHz	65	90	–	
		3000 to 6000 MHz	60	85	–	
VSWR	COM port	1 to 3000 MHz	–	1.25	–	:1
		3000 to 6000 MHz	–	1.40	–	
	Any port connected to COM	1 to 3000 MHz	–	1.25	–	
		3000 to 6000 MHz	–	1.45	–	
	Any terminated port	1 to 3000 MHz	–	1.10	–	
		3000 to 6000 MHz	–	1.25	–	
Power Input @ 1 dB Compression ^{1,2}	COM to any active port	1 to 6000 MHz	30	–	–	dBm
IP3 ³	COM to any active port	10 to 6000 MHz	–	50	–	dBm
Switching time ⁴	–	1 to 6000 MHz	–	6	–	µs
Operating RF Input Power	COM to any active port	Hot Switching	–	–	+17	dBm
	Any terminated port	–	–	–	+17	
	COM to any active port	Through path ¹	–	–	+27	
Control	Control is via SPI in at Control In port. Control Out can be used to connect multiple units in a 'Daisy chain' without additional controls					

¹ Max operating power degrades linearly below 10 MHz to +22 dBm at 1 MHz.

² Note absolute maximum ratings in table below

³ Tested with 1 MHz span between signals, +5 dBm per tone.

⁴ Tested Latch Enable(LE) signal to 90% RF signal at RF port

Connections

RF Switch (J1 to J8, COM)	(SMP male)
Power & Control in (Control in)*	(Hirose DF11 10 pin Connector) ⁵
Power & Control out (Control out)**	(Hirose DF11 10 pin Connector) ⁵

⁵ Mating connector is Hirose DF11-10DS-2C(20)

* Control in Pin Connections

Pin Number	Function
1 - 3	Vcc In
4 - 6	GND
7	Data In
8	Clock In
9	LE In
10	Lock in

** Control out Pin Connections

Pin Number	Function
1 - 3	Vcc out
4 - 6	GND
7	Data Out
8	Clock Out
9	LE Out
10	Lock Out

Absolute Maximum Ratings

Operating Temperature	0°C to 50°C
Storage Temperature	-20°C to 60°C
DC supply voltage max.	26V
Control input line max.	6V
Max supply current per pin	800 mA
RF power @ into inactive (internal termination) port	+20 dBm
RF power @ 1 -10 MHz into COM or active port	+25 dBm
RF power @ 10 -6000 MHz into COM or active port	+30 dBm
DC voltage @ RF Ports	16V

Permanent damage may occur if any of these limits are exceeded. Operating in the range between operating power limits and absolute maximum ratings for extended periods of time may result in reduced life and reliability.

DC Electrical Specifications

Parameter	Min.	Typ.	Max.	Units
Vcc, Supply Voltage	5	—	24	V
Load on Vcc between In and Out ports	—	0.05	—	Ω
Icc, Supply Current	@24V	7	—	mA
	@5V	7	—	
Control Input Low	-0.3	—	+0.6	V
Control Input High	2.0	—	5.5	V
Control Current	—	400	—	µA

Control Interface

The SPI-SP8T-6G serial interface consists of 4 control bits per unit that select the desired switch state, as shown in Table 1: Switch Logic Table.

Table 1: Switch Logic Table				
A0	A1	A2	A3	Switch State
1	0	1	0	Com<->J1
1	0	1	1	Com<->J2
1	0	0	1	Com<->J3
1	0	0	0	Com<->J4
0	0	1	0	Com<->J5
0	0	1	1	Com<->J6
0	0	0	1	Com<->J7
0	0	0	0	Com<->J8

The serial interface is a 4-bit serial in, parallel-out shift register buffered by a transparent latch. It is controlled by three-wire SPI protocol using Data, Clock, and Latch Enable (LE) and an additional Lock for added noise immunity and increased flexibility in controlling the units. All signal voltages are compatible with TTL and LVTTTL. The Data and Clock inputs allow data to be serially entered into the shift register, a process that is independent of the state of the LE input.

The LE input controls the latch. When LE is HIGH, the latch is transparent and the contents of the serial shift register control the switch. When LE is brought LOW, data in the shift register is latched.

Lock is used to lock the current state of the switch regardless of LE state or shift register, while allowing the LE to pass to other switches in the chain. If Lock is at logic HIGH the switch will respond to LE normally, when Lock is at logic LOW the switch will not respond to LE. If Lock is not required it can be kept constantly at logic high.

The shift register should be loaded while LE is held LOW to prevent the switch state from changing as data is entered. If multiple units are connected in series, data for all units should be entered before raising the LE to prevent switches assuming unanticipated states. Thus for example if three units are connected in daisy chain all 12 bits of control should be entered before raising the LE (see figures 2-4 for connecting units in daisy chain).

The LE input should then be toggled HIGH and brought LOW again, latching the new data. The timing for this operation is defined by Figure 1: Serial Interface Timing Diagram and Table 2: Serial Interface AC Characteristics.

Note:

1. LE is connected in parallel to all units in a daisy chain using the switches internal buffers to prevent control current from increasing as more units are connected.

Figure 1: Serial Interface Timing Diagram




Table 2. Serial Interface AC Characteristics				
Symbol	Parameter	Min.	Max.	Units
f_{clk}	Serial data clock frequency		20	MHz
t_{clkH}	Serial clock HIGH time	8		ns
t_{clkL}	Serial clock LOW time	14		ns
t_{LESUP}	LE set-up time after last clock rising edge	8		ns
t_{LEPW}	LE minimum pulse width	8		ns
t_{SDSUP}	Serial data set-up time before clock rising edge	8		ns
t_{SDHLD}	Serial data hold time after clock falling edge	1		ns

Control Interface (Daisy Chain)

Figure 2: Connection diagram for multiple units in series




Figure 3: Serial Interface Timing Diagram for 3 units in series






Figure 4: Example of command for 3 switches in series




Typical Performance Curves


Insertion Loss over Temperature




Insertion Loss at Ports J1-J8 vs. Frequency




Active Port VSWR over Temp.



Common Port VSWR over Temp.




Internal Term. VSWR over Temp.




Typical Performance Curves (Continued)


Isolation Com to Port J1 with J2 active over Temp.




Isolation Com to Port J1-J8 vs. Frequency




Isolation Port 2 to Port 1 Isolation over temp.







Isolation Port to Port vs. Frequency



Input IP3



Outline Drawing (PM2656)



Outline Dimensions (inch mm)

A	B	C	D	E	F	G	H	J	K	WT. GRAMS
3.270 83.06	3.680 93.47	0.400 10.16	0.205 5.21	0.450 11.43	0.190 4.83	0.500 12.70	2.560 65.02	0.060 1.52	0.100 2.54	180


Recommended Accessories

Several optional cable accessories with and without interface connector are available with the SPI-SP8T-6G.

Cable P/N	Cable Length	Wire Gauge	Cable connectors	Recommended use
CBL-DF11-3FFD+	3 ft (0.91 m)	30 AWG	Hirose DF11-10DS-2C(20) on each end	Connect between switches in series
CBL-DF11-3FPD+	3 ft (0.91 m)	30 AWG	Hirose DF11-10DS-2C(20) on one end, pigtail (bare wires) on the other	Connect SPI-SP8T-6G switch to customer control board and power


All cables are shielded and can handle the power draw of up to 50 switches in series.

CBL-DF11-3FPD+ Control Cable



Pin Number	Function	Description	Pigtail Wire Color
1	Vcc	Supply Voltage	WHITE
2	Vcc	Supply Voltage	BLACK
3	Vcc	Supply Voltage	RED
4	GND	Ground connection	GREEN
5	GND	Ground connection	YELLOW
6	GND	Ground connection	BLUE
7	Data	Data for SPI	BROWN
8	Clock	Clock for SPI	ORANGE
9	LE	Latch Enable for SPI	GRAY
10	Lock	Lock for SPI	VIOLET

CBL-DF11-3FFD+ Control Cable



J1 Pin Number	J2 Pin Number	Function	Description
1	1	Vcc	Supply Voltage
2	2	Vcc	Supply Voltage
3	3	Vcc	Supply Voltage
4	4	GND	Ground connection
5	5	GND	Ground connection
6	6	GND	Ground connection
7	7	Data	Data for SPI
8	8	Clock	Clock for SPI
9	9	LE	Latch Enable for SPI
10	10	Lock	Lock for SPI

Ordering, Pricing & Availability Information see our web site

Model	Description
SPI-SP8T-6G	SPI RF SP8T Switch

Optional Accessories	Description
CBL-DF11-3FFD+	3 ft. Hirose DF11 (female-female) cable assembly (SPI)
CBL-DF11-3FPD+	3 ft. Hirose DF11 (female-pigtail) cable assembly (SPI)
SMPF-SF50+	SMP Female to SMA Female Adapter

Additional Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



Solid State SPI RF SP8T Switch

SPI-SP8T-6G

Typical Performance Data

TEST CONDITIONS: @Temperature = +25°C, Power in=0 dBm

FREQUENCY (MHz)	INSERTION LOSS							
	(dB)							
	COM-J1	COM-J2	COM-J3	COM-J4	COM-J5	COM-J6	COM-J7	COM-J8
1	2.04	2.04	1.98	2.06	2.12	2.10	2.08	2.06
20	2.06	2.05	2.00	2.08	2.14	2.12	2.09	2.08
40	2.07	2.07	2.02	2.10	2.15	2.13	2.11	2.09
70	2.10	2.09	2.04	2.12	2.17	2.15	2.13	2.12
100	2.12	2.11	2.06	2.14	2.20	2.17	2.15	2.14
200	2.19	2.17	2.12	2.21	2.27	2.24	2.21	2.21
300	2.26	2.24	2.19	2.29	2.35	2.31	2.28	2.29
400	2.35	2.32	2.26	2.38	2.43	2.39	2.36	2.38
500	2.45	2.40	2.34	2.48	2.53	2.48	2.44	2.47
600	2.54	2.49	2.43	2.57	2.61	2.56	2.52	2.57
700	2.62	2.57	2.51	2.66	2.70	2.64	2.60	2.66
800	2.69	2.64	2.58	2.73	2.76	2.71	2.67	2.72
900	2.75	2.70	2.64	2.78	2.82	2.77	2.73	2.78
1000	2.79	2.75	2.69	2.83	2.86	2.81	2.78	2.82
1100	2.83	2.80	2.73	2.87	2.91	2.85	2.82	2.86
1200	2.86	2.83	2.77	2.90	2.94	2.89	2.85	2.89
1300	2.90	2.87	2.80	2.93	2.98	2.92	2.89	2.93
1400	2.94	2.90	2.84	2.97	3.02	2.95	2.92	2.98
1500	2.99	2.94	2.88	3.02	3.07	2.98	2.96	3.02
1600	3.04	2.98	2.92	3.06	3.11	3.02	3.00	3.06
1700	3.09	3.03	2.97	3.12	3.16	3.07	3.05	3.10
1800	3.15	3.09	3.03	3.17	3.21	3.13	3.10	3.14
1900	3.20	3.15	3.09	3.22	3.26	3.19	3.15	3.19
2000	3.24	3.21	3.16	3.27	3.31	3.27	3.22	3.26
2100	3.30	3.28	3.22	3.32	3.37	3.34	3.28	3.33
2200	3.36	3.34	3.29	3.37	3.42	3.42	3.34	3.40
2300	3.41	3.39	3.34	3.42	3.48	3.48	3.40	3.48
2400	3.46	3.44	3.39	3.46	3.52	3.53	3.45	3.54
2600	3.53	3.52	3.46	3.52	3.60	3.60	3.53	3.63
2800	3.59	3.60	3.53	3.57	3.66	3.66	3.60	3.68
2900	3.63	3.64	3.56	3.61	3.70	3.68	3.65	3.71
3000	3.68	3.68	3.60	3.67	3.75	3.72	3.69	3.77
3100	3.75	3.73	3.64	3.76	3.83	3.75	3.74	3.85
3200	3.86	3.77	3.69	3.87	3.94	3.80	3.80	3.95
3300	3.97	3.82	3.74	4.00	4.06	3.85	3.86	4.06
3400	4.09	3.87	3.80	4.11	4.17	3.93	3.92	4.17
3500	4.17	3.93	3.85	4.19	4.24	4.00	3.98	4.23
3600	4.21	3.98	3.91	4.22	4.28	4.07	4.03	4.25
3700	4.22	4.03	3.95	4.22	4.28	4.11	4.07	4.24
3800	4.21	4.07	3.98	4.20	4.26	4.14	4.10	4.22
3900	4.20	4.08	4.00	4.20	4.26	4.15	4.10	4.22
4000	4.21	4.08	4.00	4.21	4.28	4.14	4.10	4.25
4100	4.25	4.08	4.01	4.25	4.34	4.14	4.10	4.29
4200	4.31	4.09	4.03	4.30	4.42	4.15	4.12	4.34
4300	4.35	4.12	4.06	4.33	4.48	4.17	4.15	4.37
4400	4.37	4.16	4.10	4.35	4.52	4.20	4.19	4.39
4600	4.38	4.21	4.16	4.37	4.54	4.25	4.24	4.40
4800	4.40	4.24	4.20	4.41	4.56	4.27	4.27	4.45
5000	4.47	4.33	4.28	4.47	4.63	4.38	4.38	4.56
5200	4.58	4.54	4.44	4.56	4.72	4.63	4.60	4.77
5400	4.73	4.79	4.63	4.76	4.88	4.90	4.85	4.97
5600	4.93	4.96	4.80	4.99	5.13	5.06	5.01	5.15
5800	5.12	5.03	4.92	5.22	5.30	5.09	5.07	5.30
6000	5.21	5.08	5.00	5.30	5.36	5.13	5.11	5.41

Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
 B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
 C. The parts covered by this specification document are subject to Mini-Circuits' standard limited warranty and terms and conditions (collectively, "Standard Terms"). Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCStore/terms.jsp



Solid State SPI RF SP8T Switch

SPI-SP8T-6G

Typical Performance Data

TEST CONDITIONS: @Temperature = +25°C, Power in=0 dBm

FREQUENCY (MHz)	Isolation (COM to terminated port)							
	(dB)							
	COM-J1	COM-J2	COM-J3	COM-J4	COM-J5	COM-J6	COM-J7	COM-J8
1	87.36	93.70	94.41	96.47	96.67	89.18	90.97	95.81
20	99.55	107.36	104.02	105.73	105.40	107.87	87.83	96.21
40	101.20	109.54	103.82	106.27	105.73	108.55	86.34	96.14
70	104.83	109.75	105.60	108.40	106.04	109.57	84.82	95.91
100	105.49	110.18	105.74	110.80	106.57	112.25	83.84	95.18
200	107.14	109.37	105.05	109.56	112.63	112.29	81.29	91.55
300	103.31	109.75	104.26	110.76	108.78	111.88	78.56	90.76
400	104.90	112.13	102.20	112.14	110.90	114.32	77.29	89.95
500	104.87	109.91	106.23	107.35	108.01	111.01	77.85	89.94
600	104.39	111.05	100.55	109.38	106.63	110.57	79.15	88.83
700	104.75	112.29	102.83	108.25	106.15	112.06	78.39	88.38
800	103.98	109.96	105.85	108.26	112.29	109.02	76.70	87.70
900	103.75	108.84	105.43	111.22	108.96	109.93	75.28	87.80
1000	102.49	109.14	104.68	110.30	109.84	109.95	75.30	87.46
1100	102.56	107.11	101.47	108.05	108.17	109.17	75.98	87.15
1200	103.29	108.25	103.71	107.87	105.43	105.97	78.51	86.58
1300	102.95	106.74	104.22	112.13	107.85	110.51	79.01	86.97
1400	102.69	112.57	101.86	111.10	106.44	111.59	79.15	86.75
1500	106.04	108.81	101.47	108.45	108.03	108.80	80.91	86.52
1600	105.79	107.03	102.28	103.70	107.91	107.58	81.85	86.54
1700	102.12	110.42	100.55	109.22	110.57	105.75	81.43	86.22
1800	102.56	106.86	100.59	105.81	107.42	105.98	81.26	85.98
1900	104.15	107.92	98.44	111.93	112.45	105.89	81.26	86.04
2000	103.19	106.17	98.69	107.56	108.45	104.56	81.77	85.52
2100	102.00	105.54	97.68	106.45	105.30	108.04	81.95	85.92
2200	102.68	105.77	96.45	106.73	105.63	105.31	81.84	85.17
2300	105.51	104.46	97.47	108.12	106.43	104.21	81.26	84.95
2400	102.62	103.91	97.28	108.15	107.29	104.35	80.96	84.40
2600	101.85	103.31	93.17	108.19	105.09	104.12	80.45	84.12
2800	102.60	107.58	91.67	109.94	105.16	102.89	80.33	85.12
2900	102.98	105.26	92.25	105.90	107.80	106.46	78.94	85.22
3000	101.37	102.95	91.01	107.73	102.28	110.72	78.33	85.23
3100	101.55	106.56	90.16	111.65	101.10	107.34	78.96	85.82
3200	101.80	102.51	90.06	106.84	101.56	105.59	79.50	85.05
3300	98.40	105.97	89.61	107.56	102.97	103.23	79.36	84.93
3400	100.88	103.25	88.47	107.66	100.42	107.11	78.76	84.35
3500	102.83	101.06	88.77	103.46	98.88	105.21	78.72	84.56
3600	98.11	107.73	88.24	105.18	98.69	103.68	77.93	84.76
3700	96.53	107.90	87.75	106.61	99.05	101.48	77.10	83.80
3800	98.63	108.60	87.43	105.83	97.21	107.85	76.34	83.57
3900	97.46	107.29	86.70	108.58	96.76	103.67	75.56	83.58
4000	95.69	107.74	86.30	107.85	96.47	104.13	75.73	83.21
4100	97.26	104.17	85.87	106.48	96.46	102.68	75.30	82.93
4200	96.28	101.78	85.63	106.37	98.71	101.30	75.27	83.07
4300	96.93	102.59	85.35	107.85	94.31	101.40	75.08	83.01
4400	98.57	103.79	85.16	106.21	94.85	100.93	74.86	82.53
4600	95.76	103.89	84.42	113.93	93.46	101.20	74.19	82.19
4800	94.79	103.55	83.22	104.96	92.68	101.63	73.38	81.85
5000	92.44	102.04	82.62	108.04	91.29	100.32	72.83	81.47
5200	90.78	103.64	81.82	105.72	90.64	100.60	72.05	80.69
5400	89.21	103.40	81.44	105.57	89.35	104.48	71.71	80.74
5600	88.89	102.02	81.13	107.44	88.97	103.62	71.76	79.31
5800	87.96	101.05	80.60	106.46	88.20	101.46	71.35	78.55
6000	86.20	99.85	80.04	110.99	86.55	101.41	70.41	77.79

Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
 B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
 C. The parts covered by this specification document are subject to Mini-Circuits' standard limited warranty and terms and conditions (collectively, "Standard Terms"). Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCStore/terms.jsp



Solid State SPI RF SP8T Switch

SPI-SP8T-6G

Typical Performance Data

TEST CONDITIONS: @Temperature = +25°C, Power in=0 dBm

FREQUENCY (MHz)	Isolation (port to port)						
	(dB)						
	J1-J2	J2-J3	J3-J4	J4-J5	J5-J6	J6-J7	J7-J8
1	85.05	89.27	89.16	93.83	92.68	84.82	95.65
20	96.51	101.06	103.16	101.48	103.46	100.38	91.18
40	98.73	103.47	104.36	103.34	101.22	104.08	90.63
70	101.22	105.50	106.02	103.46	104.23	107.91	88.51
100	105.12	106.67	107.13	102.99	103.60	109.78	87.54
200	100.50	104.86	101.04	106.47	104.03	104.12	84.94
300	100.08	104.79	103.96	108.03	104.41	104.26	81.57
400	104.03	103.39	99.61	103.61	100.58	106.71	82.76
500	99.91	102.26	102.05	104.17	103.28	102.90	80.73
600	99.33	103.21	98.46	104.08	105.70	104.67	78.49
700	97.36	102.92	96.20	103.64	103.04	107.31	81.06
800	100.17	101.92	95.88	101.19	103.09	104.28	79.59
900	99.77	102.65	100.22	102.89	106.51	103.28	77.90
1000	99.50	100.45	97.46	106.19	101.87	101.87	76.83
1100	100.51	103.74	97.40	103.24	107.89	104.62	76.32
1200	98.43	100.13	97.56	99.47	105.02	102.19	76.23
1300	99.18	101.86	96.69	101.00	98.31	101.52	75.54
1400	97.93	102.57	97.20	101.34	104.75	103.05	74.58
1500	98.53	100.82	98.32	102.50	102.01	98.32	76.54
1600	97.37	103.17	98.05	101.33	96.52	102.12	76.47
1700	99.80	99.30	98.12	102.61	98.41	101.14	75.86
1800	95.87	98.75	100.24	101.42	100.82	101.57	74.93
1900	101.45	100.30	104.36	101.06	101.30	99.04	75.34
2000	97.29	100.70	100.94	100.47	102.29	100.20	75.46
2100	98.16	98.50	102.89	98.72	96.44	96.56	76.18
2200	97.30	97.89	100.74	98.49	100.75	98.82	75.53
2300	98.13	101.18	96.59	100.45	101.57	98.64	74.85
2400	97.04	99.06	96.51	97.82	98.52	100.37	74.84
2600	97.10	98.80	92.87	101.91	99.01	99.46	76.46
2800	100.32	97.95	90.25	99.86	98.65	99.67	75.53
2900	92.58	97.72	88.52	99.00	98.00	96.00	74.58
3000	93.21	98.61	88.74	99.36	98.31	97.73	77.38
3100	92.45	98.38	87.41	100.33	95.09	96.24	79.04
3200	94.29	97.40	86.60	100.62	98.43	93.93	77.67
3300	92.05	96.29	86.62	98.69	95.74	96.66	77.72
3400	89.90	96.44	87.24	98.12	95.18	97.00	76.80
3500	90.12	93.15	88.22	96.74	96.98	93.90	75.99
3600	89.80	94.45	87.83	99.56	98.60	96.38	75.92
3700	86.02	92.79	88.85	98.39	97.10	92.61	77.81
3800	86.20	95.75	90.73	98.54	93.66	93.28	79.35
3900	85.35	94.56	91.74	99.95	93.45	93.92	80.33
4000	83.92	92.25	92.49	98.00	97.22	90.71	81.16
4100	84.64	90.98	91.70	98.53	94.48	95.53	80.13
4200	84.24	90.64	94.95	98.28	92.73	94.27	79.33
4300	84.05	90.60	94.53	96.71	97.80	91.29	78.71
4400	85.49	90.35	93.80	98.47	94.78	91.23	78.47
4600	84.77	91.23	92.10	98.07	94.35	92.64	77.85
4800	88.48	88.03	89.16	96.00	93.42	89.33	78.06
5000	90.97	88.87	87.91	98.79	94.72	88.66	76.80
5200	95.14	89.38	88.27	99.31	95.05	87.70	76.57
5400	95.60	87.75	87.73	97.14	91.52	86.50	76.46
5600	93.25	87.08	85.68	96.07	91.84	87.15	75.11
5800	89.50	85.54	85.93	98.25	90.10	86.05	76.80
6000	87.39	86.98	90.39	89.81	88.61	80.92	76.63

Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
 B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
 C. The parts covered by this specification document are subject to Mini-Circuits' standard limited warranty and terms and conditions (collectively, "Standard Terms"). Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCStore/terms.jsp



Solid State SPI RF SP8T Switch

SPI-SP8T-6G

Typical Performance Data

TEST CONDITIONS: @Temperature = 0/+25/+50°C, Power in=0 dBm

FREQUENCY (MHz)	INSERTION LOSS			VSWR (Active Port)			VSWR (Com port)			VSWR (Terminated port)		
	(dB)			(:1)			(:1)			(:1)		
	@0°C	@+25°C	@+50°C	@0°C	@+25°C	@+50°C	@0°C	@+25°C	@+50°C	@0°C	@+25°C	@+50°C
1	2.01	2.04	2.07	1.46	1.47	1.47	1.47	1.47	1.49	1.06	1.05	1.04
20	2.03	2.06	2.09	1.45	1.46	1.47	1.47	1.47	1.48	1.05	1.04	1.01
40	2.05	2.07	2.10	1.45	1.46	1.47	1.47	1.47	1.48	1.05	1.03	1.01
70	2.07	2.10	2.12	1.45	1.46	1.47	1.47	1.48	1.48	1.04	1.03	1.01
100	2.10	2.12	2.14	1.44	1.46	1.46	1.47	1.48	1.48	1.04	1.03	1.01
200	2.17	2.19	2.20	1.42	1.42	1.43	1.44	1.45	1.46	1.04	1.03	1.01
300	2.24	2.26	2.28	1.37	1.37	1.38	1.38	1.40	1.41	1.05	1.03	1.01
400	2.32	2.35	2.36	1.31	1.31	1.32	1.32	1.32	1.33	1.05	1.04	1.02
500	2.40	2.45	2.45	1.25	1.25	1.26	1.24	1.23	1.24	1.05	1.04	1.02
600	2.49	2.54	2.53	1.20	1.20	1.20	1.14	1.14	1.15	1.05	1.04	1.02
700	2.58	2.62	2.61	1.16	1.17	1.16	1.06	1.06	1.07	1.05	1.04	1.02
800	2.67	2.69	2.68	1.12	1.14	1.13	1.03	1.03	1.03	1.05	1.04	1.02
900	2.72	2.75	2.74	1.09	1.10	1.10	1.07	1.08	1.07	1.05	1.04	1.02
1000	2.77	2.79	2.79	1.06	1.06	1.06	1.12	1.13	1.12	1.05	1.04	1.03
1100	2.82	2.83	2.82	1.02	1.02	1.01	1.17	1.16	1.17	1.06	1.04	1.03
1200	2.86	2.86	2.85	1.02	1.03	1.03	1.20	1.18	1.19	1.05	1.04	1.03
1300	2.92	2.90	2.89	1.07	1.08	1.08	1.20	1.17	1.19	1.05	1.04	1.03
1400	2.97	2.94	2.93	1.11	1.13	1.12	1.16	1.15	1.17	1.06	1.04	1.03
1500	3.01	2.99	2.98	1.15	1.17	1.17	1.11	1.12	1.13	1.05	1.04	1.03
1600	3.06	3.04	3.02	1.21	1.20	1.21	1.08	1.10	1.11	1.05	1.03	1.03
1700	3.11	3.09	3.05	1.25	1.23	1.25	1.10	1.11	1.11	1.05	1.03	1.03
1800	3.17	3.15	3.10	1.28	1.25	1.26	1.17	1.16	1.17	1.05	1.03	1.04
1900	3.21	3.20	3.17	1.30	1.28	1.29	1.28	1.25	1.26	1.05	1.02	1.04
2000	3.26	3.24	3.21	1.34	1.30	1.32	1.38	1.36	1.38	1.05	1.02	1.04
2100	3.31	3.30	3.26	1.38	1.34	1.36	1.45	1.45	1.47	1.05	1.02	1.04
2200	3.36	3.36	3.31	1.40	1.38	1.40	1.50	1.52	1.54	1.05	1.03	1.05
2300	3.41	3.41	3.35	1.42	1.41	1.42	1.53	1.56	1.57	1.06	1.03	1.05
2400	3.47	3.46	3.38	1.42	1.42	1.43	1.53	1.57	1.58	1.06	1.04	1.05
2600	3.55	3.53	3.44	1.39	1.41	1.43	1.50	1.53	1.55	1.07	1.05	1.06
2800	3.65	3.59	3.52	1.35	1.36	1.37	1.44	1.46	1.48	1.08	1.07	1.06
2900	3.71	3.63	3.57	1.31	1.34	1.35	1.40	1.41	1.41	1.08	1.08	1.07
3000	3.76	3.68	3.63	1.32	1.34	1.36	1.33	1.32	1.33	1.09	1.09	1.07
3100	3.83	3.75	3.71	1.37	1.37	1.39	1.22	1.23	1.23	1.09	1.10	1.08
3200	3.94	3.86	3.82	1.46	1.42	1.44	1.07	1.12	1.12	1.09	1.11	1.08
3300	4.07	3.97	3.94	1.53	1.48	1.50	1.03	1.04	1.03	1.10	1.12	1.09
3400	4.17	4.09	4.05	1.56	1.51	1.52	1.11	1.11	1.09	1.11	1.12	1.09
3500	4.24	4.17	4.12	1.53	1.49	1.51	1.17	1.21	1.19	1.11	1.13	1.09
3600	4.26	4.21	4.16	1.46	1.44	1.45	1.24	1.27	1.27	1.11	1.13	1.09
3700	4.26	4.22	4.17	1.37	1.35	1.36	1.30	1.31	1.29	1.12	1.14	1.10
3800	4.24	4.21	4.15	1.24	1.23	1.23	1.29	1.29	1.28	1.12	1.15	1.10
3900	4.23	4.20	4.15	1.11	1.11	1.12	1.25	1.24	1.24	1.13	1.16	1.11
4000	4.25	4.21	4.16	1.12	1.09	1.12	1.22	1.20	1.19	1.13	1.16	1.11
4100	4.31	4.25	4.20	1.24	1.18	1.22	1.22	1.20	1.20	1.14	1.17	1.11
4200	4.36	4.31	4.26	1.33	1.27	1.31	1.26	1.22	1.24	1.13	1.17	1.11
4300	4.41	4.35	4.30	1.36	1.34	1.36	1.28	1.26	1.28	1.14	1.17	1.12
4400	4.46	4.37	4.33	1.36	1.36	1.37	1.28	1.29	1.32	1.14	1.18	1.12
4600	4.52	4.38	4.34	1.25	1.29	1.27	1.27	1.30	1.30	1.14	1.18	1.12
4800	4.56	4.40	4.37	1.13	1.18	1.15	1.34	1.33	1.32	1.15	1.18	1.13
5000	4.63	4.47	4.44	1.18	1.16	1.16	1.40	1.40	1.43	1.14	1.18	1.13
5200	4.76	4.58	4.59	1.35	1.26	1.31	1.43	1.48	1.52	1.16	1.19	1.13
5400	4.85	4.73	4.75	1.48	1.40	1.47	1.39	1.47	1.44	1.17	1.18	1.14
5600	4.98	4.93	4.95	1.64	1.58	1.63	1.21	1.24	1.26	1.19	1.18	1.14
5800	5.11	5.12	5.12	1.62	1.66	1.65	1.07	1.09	1.12	1.19	1.19	1.15
6000	5.15	5.21	5.17	1.40	1.51	1.44	1.07	1.07	1.05	1.17	1.16	1.14

Notes




- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
 B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
 C. The parts covered by this specification document are subject to Mini-Circuits' standard limited warranty and terms and conditions (collectively, "Standard Terms"). Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCStore/terms.jsp



Solid State SPI RF SP8T Switch

SPI-SP8T-6G

Typical Performance Curves



Notes





- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits' standard limited warranty and terms and conditions (collectively, "Standard Terms"). Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCStore/terms.jsp



Solid State SPI RF SP8T Switch

SPI-SP8T-6G





Typical Performance Curves



Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuit's standard limited warranty and terms and conditions (collectively, "Standard Terms"). Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuit's website at www.minicircuits.com/MCStore/terms.jsp





A

CASE#	A	B	C	D	E	F	G	H	J	K	WT.
PM2656	3.270 (83.06)	3.680 (93.47)	.400 (10.16)	.205 (5.21)	.450 (11.43)	.190 (4.83)	.500 (12.70)	2.560 (65.02)	.060 (1.52)	.100 (2.54)	180

Dimensions are in inches (mm). Tolerances: 2PL. +/- .03; 3PL. +/- .015

Notes:

1. Case material: Aluminum alloy.
2. Case finish for RoHS Case Styles: Clear chemical conversion coating, non-chrome or trivalent chrome based.



INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified



Environmental Specifications ENV55

All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-0° to 50° C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-20° to 60° C Ambient Environment	Individual Model Data Sheet
Operating and Storage Humidity	5% to 85% RH (non-condensing)	Ambient
Bench Handling Test	Bench Top Tip 45° & Drop	MIL-PRF-28800F
Transit Drop Test	Free Fall Drop, 20 cm (7.9 inches)	MIL-PRF-28800F Class 3