USB & ETHERNET & DAISY-CHAIN

Signal Generator

SSG-5N9G-RC

50Ω 5000 to 9000 MHz -55 dBm to +23 dBm SMA Female

THE BIG DEAL

- Cost effective C-band / ISM signal generator
- High output power, +23 dBm
- Good harmonics & phase noise
- CW, pulsed, AM, FM & chirp outputs
- Compact design for bench top use
- Power over Ethernet (PoE) enabled
- Daisy-chain for multi-module dynamic control

Generic photo used for illustration purposes only

APPLICATIONS

- Semiconductor high power burn-in & life testing
- Benchtop signal generator
- Automated production test systems
- C-band / ISM testing
- Quantum computing

PRODUCT OVERVIEW

Mini-Circuits' SSG-5N9G-RC is a wide-band signal generator operating from 5000 to 9000 MHz. With up to +23 dBm typical output power, it is an ideal signal source for characterization of millimeter wave components and systems at high power. Configure CW / single-tone outputs, flexible pulse sequences, AM, FM and Chirp modulations, or automated frequency / power sweep & hop sequences.

SSG-5N9G-RC has been developed in a compact package with powerful software control and automation to provide a cost effective C-band / ISM signal generator and LO source for any bench or production test application. This is a high quality, repeatable and reliable signal source with low phase noise and excellent harmonic rejection.

The generator can be controlled via USB or Ethernet (supporting SSH, HTTP & Telnet protocols). A USB cable with screw lock fastens the cable securely to the module. Full software support is provided, including our user-friendly GUI application for Windows, flexible API and programming instructions for Windows and Linux environments. The daisy-chain control interface with "dynamic addressing" simplifies control integration and allows multiple units to be combined into a multi-channel signal source with control through a single software interface.

KEY FEATURES

Feature	Advantages
High quality signal source	Outstanding combination of fine frequency and power resolution, low phase noise and excellent harmonic rejection, and low spurious signals in a compact package; suited to a wide range of test applications.
Flexible pulse, AM, FM and Chirp modulation	Configure various analog modulations according to your needs.
Sweep & Hop sequences	Configure custom CW output frequency and power sequences to run unaided for high speed, automated test applications.
USB & Ethernet control	USB HID and Ethernet (HTTP / Telnet / SSH) interfaces provide easy compatibility with a wide range of software setups and programming environments.
Dynamic daisy-chain control	Simplify control software and interconnections and develop low-cost, multi-channel signal generator systems by daisy-chaining multiple units with control through a single interface.

Trademarks:
Windows is a registered trademark of Microsoft Corporation in the United States and other countries ; Linux is a registered trademark of Linus Torvalds ; Pentium is a registered trademark of Intel Corporation. Neither Mini-Circuits nor the Mini-Circuits products are affiliated with or endorsed by the owners of the referenced trademarks. Mini-Circuits and the Mini-Circuits logo are registered trademarks of Scientific Components Corporation.

www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

Signal Generator

SSG-5N9G-RC

50Ω 5000 to 9000 MHz -55 dBm to +23 dBm SMA Female

ELECTRICAL SPECIFICATIONS [1], +25°C

Parameter	Condition (MHz)		Min.	Typ.	Max.	Unit
Output Frequency	–		5000	–	9000	MHz
Frequency Resolution [2]	5000 - 9000		–	1	–	Hz
Frequency Accuracy	Using internal reference		–	±1	–	ppm
Return Loss	5000 - 9000		–	-10	–	dB
Output Power Max	5000 - 9000		+20	+23	–	dBm
Output Power Min	5000 - 9000		–	-55	-50	dBm
Power Resolution (nominal)	5000 - 9000		–	0.1	–	dB
Output Power Accuracy	5000 - 9000	-50 to +20 dBm	–	±0.5	±1.0	dB
RF Output Leakage	5000 - 9000	RF off	–	-80	–	dBm
Harmonics [3]	5000 - 7000	-50 to +20 dBm	–	-15	–	dBc
	7000 - 9000		–	-30	–	
Non-Harmonic Spurious	Offsets 100 kHz to 150 MHz	0 dBm to Max Power	–	-70	-60	dBc
Boundary Spurs	5000 - 9000		–	-40	–	
Settling Time [4, 5]	Hop mode [6]	5000 - 9000	–	0.12	0.20	ms
	Frequency sweep	5000 - 9000	–	0.15	0.22	
	Power transition (at set frequency)		–	0.015	–	
	PC (external) control		–	2	–	
Dwell Time (nominal) [5, 7]	–		0.01	–	10,000	ms
Phase Offset Range	–		0	–	359	deg
Phase Offset Resolution	–		–	1	–	

1. Specifications are after 15 minutes warm-up time.
2. Frequency Resolution is tested with 10 MHz external reference.
3. It is recommended using Mini-Circuits' VLF-8400+ filter together with the SSG-5N9G-RC to improve SSG harmonics at lower frequencies.
4. Settling Time - transition time between 2 output states. During the transition, RF output is turned off to avoid transient outputs.
5. Generator response time is Dwell Time + Settling Time.
6. For hop sequences pre-loaded into internal memory (high-speed mode).
7. Dwell Time - duration of each signal point in a Sweep or Hop sequence set by user. Default is minimum dwell time.

MODULATION SPECIFICATIONS [8], +25°C

Parameter		Condition		Min.	Typ.	Max.	Unit
Modulation types		AM, FM, Chirp, Pulse (Rising, Falling and bi-directional)					
Max modulation freq		3 dB point		–	–	5	kHz
FM Max deviation		–		–	50	–	MHz
AM Modulation depth [9]		–		0	–	100	%
Chirp rate		Nominal value		0.0015	–	20	MHz/µs
Pulse Width Resolution		Nominal value		0.05	–	–	µs
Pulse Width [10, 11]		Measured at the 50% of pulse level	Internal Pulse Modulation	5	–	10e6	µs
			External Pulse Modulation	5	–	10e6	
Pulse Period (regular mode)		Measured at the 50% of pulse level	Internal Pulse Modulation	10	–	10e6	µs
			External Pulse Modulation	10	–	10e6	
Pulse interval [12]	Fixed freq. & Power	Measured at the 50% of pulse level		7	–	4e6	µs
	Varying freq. & Power			150	–	4e6	
Pulse Rise / Fall Time [13, 14]		Measured between 10% and 90% of pulse level		–	60 / 30	–	ns
Pulse Width Accuracy [15]		Measured at 50% of pulse level	Internal pulse modulation	–	±10	–	%
			External pulse modulation	–	±10	–	
External pulse modulation input threshold		External pulse modulation		3	–	–	V
Trigger Response Delay		Trigger edge to 50% of pulse level	Internal pulse modulation	–	1	–	µs
			External pulse modulation	–	2	–	
Pulse Power Ratio		PWR_{OUT} = +20 dBm, $FREQ_{OUT}$ = 5000 MHz		–	70	–	dB
		PWR_{OUT} = +20 dBm, $FREQ_{OUT}$ = 9000 MHz		–	70	–	

8. Regular pulse mode has fixed frequency and power supporting internal and external modulation and input / output trigger options. Dynamic mode allows for flexible RF pulse sequences with varying frequency, power pulse width and pulse repetition interval (PRI).
9. In AM modulation, ensure there is sufficient margin between the carrier power and Generator's Min/Max power spec to allow generating the modulated signal without distortions. For example a modulation depth of 50% translates to power of +1.76 dB to -3.01 dB from the carrier.
10. Pulse Width in normal mode must be less than pulse period by at least 0.5 µs with Internal pulse modulation and by 2 µs in external pulse modulation.
11. Pulse Widths below 0.5 µs can be set, however performance is only guaranteed for the ranges noted in the table.
12. In dynamic mode.
13. Pulse rise time will increase with pulse interval under 3 µs.
14. For signals at same power & frequency.
15. Pulse Width Accuracy is 3% of pulse width, or ±100 ns, whichever is greater.

PHASE NOISE (SSB), +25°C

Frequency Offset (kHz)	Carrier Frequency (MHz)					
	5000		7000		9000	
	Typ.	Max	Typ.	Max	Typ.	Max
1	-98.5	-96.0	-95.5	-93.0	-93.5	-91.0
10	-109.5	-107.0	-106.5	-104.5	-104.5	-102.0
100	-117.0	-115.0	-114.5	-112.0	-112.0	-109.5
1,000	-125.0	-122.5	-119.0	-115.5	-120.0	-117.5
10,000	-145.5	-142.5	-145.0	-142.0	-145.0	-142.0
Noise Floor	-150.0	-146.0	-150.0	-146.0	-150.0	-146.0

Signal Generator

SSG-5N9G-RC

50Ω 5000 to 9000 MHz -55 dBm to +23 dBm SMA Female

REFERENCE, TRIGGER & DC POWER, +25°C

Parameter	Condition		Min.	Typ.	Max.	Unit
Aging	Using internal reference		–	2	–	ppm/yr
Reference In	Frequency	–	–	10	–	MHz
	Power	–	-3.5	–	+12.5	dBm
	Phase noise	10 kHz Offset	–	-135	–	dBc/Hz
Reference Out	Frequency	–	–	10	–	MHz
	Frequency accuracy	Using internal reference	–	±1	–	ppm
	Power	–	–	+10	–	dBm
	Phase noise	10 kHz Offset	–	-140	–	dBc/Hz
Trigger Out [16]	Low		0	–	0.4	V
	High		3.0	–	5.0	
	Pulse width		–	100	–	µs
Trigger In	Low		0	–	0.4	V
	High		3.0	–	5.0	
	Pulse width		–	1	–	µs
Supply Voltage (V_{DC})	DC Input port [17]		5.7	6.0	6.3	V_{DC}
Supply Current (I_{DC})			–	2.2	2.8	A
Supply Current (I_{DC})	USB port [17]		–	20	–	mA
Supply Voltage (V_{DC})	LAN port [17, 18]		50	53	57	V_{DC}
Supply Current (I_{DC})			–	300	450	mA

16. Trigger out voltage specified with impedance load of 10 kΩ minimum.
17. Power must be provided via the 2.1 mm DC Input or LAN port (using PoE systems) before connecting the unit to USB. The same is true in reverse, disconnect unit from USB beofre disconnecting power supply.
18. Compliant with IEEE 802.3at mode A and mode B.

ABSOLUTE MAXIMUM RATINGS

Operating Temperature	0°C to 50°C
Storage Temperature	-20°C to 60°C
Power in @ Reference in	+15 dBm
Reverse Voltage (DC) @ Reference out	8 V_{DC}
Reverse Voltage (DC) @ RF out	15 V_{DC}
Reverse Power (RF) @ RF out	+24 dBm
Voltage input to trigger ports	-0.3V_{DC} to +5.5V_{DC}

Permanent damage may occur if any of these limits are exceeded. Operating in the range between operating power limits and absolute maximum ratings for extended periods of time may result in reduced life and reliability.

Signal Generator

SSG-5N9G-RC

50Ω 5000 to 9000 MHz -55 dBm to +23 dBm SMA Female

TYPICAL PERFORMANCE GRAPHS

Power Accuracy vs. Output Frequency



Power Accuracy vs. Output Power



Phase Noise vs. Output Frequency



Phase Noise vs. Offset Frequency



Max Power vs. Output Frequency



Spurious vs. Output Frequency (Offsets 100 kHz to 150 MHz @ +5 dBm)



TYPICAL PERFORMANCE GRAPHS (CONTINUED)

Harmonics vs. Output Frequency @ +20 dBm



Harmonics vs. Output Frequency @ 0 dBm



Harmonics vs. Output Frequency @ -20 dBm



Harmonics vs. Output Frequency @ -40 dBm



Harmonics vs. Output Frequency @ -50 dBm



CONTROL INTERFACES

Ethernet Control	Supported Protocols	TCP / IP, HTTP, Telnet, SSH, DHCP, UDP (limited)
	Max Data Rate	1 Gbps (1000 Base-T Full Duplex)
USB Control	Supported Protocols	HID (Human Interface Device) - High-speed
	Min Communication Time [19]	400 µs typ (full transmit/receive cycle)

19. USB Min Communication Time is based on the polling interval of the USB HID protocol (125 µs polling interval, 64 bytes per packet), medium CPU load and no other high-speed USB devices using the USB bus.

SOFTWARE & DOCUMENTATION

Mini-Circuits' full software and support package including user guide, Windows GUI, API, programming manual and examples can be downloaded free of charge (refer to the last page for the download path).

A comprehensive set of software control options is provided:

- GUI for Windows – Simple software interface for control via Ethernet and USB.
- Programming / automation via Ethernet:
  - Complete set of control commands which can be sent via any supported protocol.
  - Simple to implement in the majority of modern programming environments.
- Programming / automation via USB:
  - DLL files provide a full API for Windows with a set of intuitive functions which can be implemented in any programming environment supporting .Net Framework or ActiveX.
  - Direct USB programming is possible in any other environment (not supporting .Net or ActiveX).

Please contact testsolutions@minicircuits.com for support.

MINIMUM SYSTEM REQUIREMENTS

GUI	Windows 7 or later
USB API DLL	Windows 7 or later and programming environment with ActiveX or .NET support
USB Direct Programming	Linux, Windows 7 or later
HTTP, Telnet or SSH	Any computer with a network port and Ethernet-TCP/IP (HTTP, Telnet or SSH protocols) support
Hardware	Intel i3 (or equivalent) or later

Signal Generator

SSG-5N9G-RC

50Ω 5000 to 9000 MHz -55 dBm to +23 dBm SMA Female

GRAPHICAL USER INTERFACE (GUI) FOR WINDOWS - KEY FEATURES

- Connect via USB or Ethernet
- Password protected access for safe remote usage over Ethernet



- Configure output power, frequency, pulse modulation
- Program timed signal output sequences (linear sweep and frequency hop)
- Control timed sequences in multiple generators simultaneously
- Track unit operation time since last calibration and setup calibration reminders



Signal Generator

SSG-5N9G-RC

50Ω 5000 to 9000 MHz -55 dBm to +23 dBm SMA Female

AUTOMATED SWEEP / HOP SEQUENCES

- Sweep across a frequency band at a fixed output power.
- Sweep output power levels at a fixed frequency.
- Hop through a list of pre-defined frequency / power settings.
- Set dwell times down to 10 µs in high speed mode.
- Run on demand or in response to external triggers.
- Produce triggers to signal switching points or completing a run.



MODULATION

- Select AM,FM, Chirp or Pulse modulation
- In the individual screens for each modulation specify the parameters for the modulated signal



Signal Generator

SSG-5N9G-RC

50Ω 5000 to 9000 MHz -55 dBm to +23 dBm SMA Female

DYNAMIC PULSE MODULATION

- Configure repetitive pulsed output sequences.
- Define custom pulse lists with a different frequency, power, width & interval at each step.
- Set pulse widths down to 0.5 us.
- Run continuously or for a preset number of cycles.



Pulse #	RF Freq (MHz)	RF Power (dBm)	P.Width (usec)	Interval (usec)
1	5100	0	45000	500
2	5150	-5	5000	500
3	5590	-10	1	500
4	6990	-19	0.5	500
5	7050	-19	1	500
6	7000	-19	1	500
7	9000	-25	5	900
8	7555	5	5	900
9	8000.0001	5	10	900
10	8400	5	55	900
11	8500	10	5	900
12	8300	10	2	900
13	8400	10	1	900

FREQUENCY MODULATION (FM)

- Set carrier power and frequency.
- Set modulating signal frequency.
- Set desired FM deviation.
- Select Sine or triangle wave modulating signal.





CONNECTING MULTIPLE MODULES (DAISY CHAIN)

The model is designed to connect up to 25 modules in series (daisy chain) using dynamic addressing, meaning there is no need to specifically set the address of the modules. The addresses will be set automatically as part of establishing the communications with the computer. The module connected to the computer's USB port or Ethernet connection will be assigned address 0 (master), the first module connected to it will get address 1 (slave) and subsequent modules incrementing up to address 24 (slave).



Connections between modules will be made using the serial in/out ports with the module connected to the PC act as a master and all other as slave modules. All control will be through the master module (address 0) which is the only one communicating with the PC or computer network. Serial control out port of each module should be connected to the serial control in port of the next module.

Power must be supplied to each module separately via their individual power supplies.

The serial master/slave bus allows connecting modules of different types to the same daisy chain as long as all support Mini-Circuits Dynamic addressing setup. To add a new module to the setup, simply connect the module and refresh the address listing, no need to reset any of the existing modules or assign addresses manually.

Signal Generator

SSG-5N9G-RC

50Ω 5000 to 9000 MHz -55 dBm to +23 dBm SMA Female

BLOCK DIAGRAM



CONNECTIONS

Port Name	Connector Type
RF output	SMA-Female
Reference in	J4 SMB-Male
Reference out	J5 SMB-Male
Trigger in	J3 SMB-Male
Trigger out	J2 SMB-Male
Power in [20]	2.1 mm DC socket
USB port	USB type C female
Network (Ethernet/LAN)	RJ45 socket
Serial Out (Digital Control 1 port)	Digital Snap Fit Connector [21]
Serial In (Digital Control 2 port)	Digital Snap Fit Connector [21]

20. No power On/Off switch - SSG will power on as soon as power is connected, starting at the specified startup condition (factory default set to 9 GHz, -50 dBm, RF Off).
21. Mating connector is Hirose ST40X-10S-CV(30)

Signal Generator

SSG-5N9G-RC

50Ω 5000 to 9000 MHz -55 dBm to +23 dBm SMA Female

OUTLINE DRAWING (SL3643)



NOTES:

1. Case material: Aluminum alloy.
2. Case Finish: Nickel Plate.
3. Dimensions are in inches [mm]. Tolerances 2 Pl. ±.03 inch; 3 Pl. ±.015 inches.
4. Weight: 500 grams
5. Marking may contain other features or characters for internal lot control.

Signal Generator

SSG-5N9G-RC

50Ω 5000 to 9000 MHz -55 dBm to +23 dBm SMA Female

DETAILED MODEL INFORMATION IS AVAILABLE ON OUR WEBSITE

CLICK HERE

Performance Data & Graphs	**Data** **Graphs**
Case Style	**SL3643**
Environmental Rating	**ENV55**
Software, User Guide & Programming Manual	https://www.minicircuits.com/softwaredownload/sg.html
Regulatory Compliance	Refer to user guide for compliance information CE UKCA https://www.minicircuits.com/app/AN49-003.pdf
Support	testsolutions@minicircuits.com

INCLUDED ACCESSORIES [22]

	Part No.	Description	Qty.
	AC/DC-6-3W	AC/DC Grounded Power adapter, 0°C to +40°C AC Input: 100-240 V, 50/60 Hz, I_{Max}= 1.2A DC Output 6±0.3 V, I_{Max}= 3A	1
(See images below)	CBL-3W-xx	AC Power Cord (Select one power cord from below with each unit)	1
	USB-CBL-AC-7SC+	6.5 ft (2.0 m) USB Cable: USB type A (Male) to USB type C (Male) Includes a screw lock to securely fasten the USB cable to the module	1
	CBL-5FT-BMSMB+	5.0 ft (1.5 m) Trigger cable: BNC (Male) to SMB (Female)	2

22. Additional quantities are available for purchase as optional accessories.

AC POWER CORD OPTIONS [23]

United States	Europe	United Kingdom	Australia and China	Israel
CBL-3W-US	CBL-3W-EU	CBL-3W-UK	CBL-3W-AU	CBL-3W-IL

23. Select one option from the list with each unit. Please contact testsolutions@minicircuits.com if your region is not listed.

Signal Generator

SSG-5N9G-RC

50Ω 5000 to 9000 MHz -55 dBm to +23 dBm SMA Female

OPTIONAL ACCESSORIES

	Part No.	Description
	CBL-RJ45-MM-5+	5.0 ft (1.5 m) Ethernet cable: RJ45 (Male) to RJ45 (Male) Cat 5E cable
	CBL-5FT-MMD+	5.0 ft (1.5 m) Cable assembly for serial control daisy chain with snap fit connectors
	CBL-1.5FT-MMD+	1.5 ft (0.45 m) Cable assembly for serial control daisy chain with snap fit connectors
	VLF-8400+	LTCC Filter: Low pass filter (50Ω), providing good harmonics at DC - 8400 MHz

CALIBRATION

Part No.	Description
CALSSG-5N9G-RC	Calibration Service for SSG-5N9G-RC CLICK HERE

NOTES:

A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.

B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.

C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at https://www.minicircuits.com/terms/viewterm.html

USB / Ethernet / Daisy Chain

Signal Generator

SSG-5N9G-RC

Typical Performance Data

Test Conditions: @ Temperature = 0°C.

Freq. (MHz)	Power deviation from nominal vs. Output Frequency (dB)									
	-50 dBm	-45 dBm	-40 dBm	-30 dBm	-20 dBm	-10 dBm	0 dBm	+10 dBm	+15 dBm	+20 dBm
5000	0.01	-0.18	-0.17	-0.25	-0.18	-0.10	-0.20	0.04	0.03	0.27
5050	-0.05	-0.20	-0.13	-0.12	-0.07	0.01	-0.12	0.09	0.10	0.30
5100	-0.10	-0.22	-0.09	0.01	0.03	0.11	-0.04	0.15	0.17	0.32
5150	-0.15	-0.22	-0.09	-0.09	-0.07	0.03	-0.10	0.15	0.20	0.29
5200	-0.19	-0.22	-0.09	-0.19	-0.16	-0.05	-0.16	0.15	0.23	0.26
5300	-0.05	-0.14	-0.06	-0.04	-0.01	-0.02	-0.02	0.14	0.18	0.32
5400	-0.04	-0.22	-0.12	-0.16	-0.10	-0.03	-0.22	0.08	0.08	0.30
5500	-0.15	-0.17	-0.16	-0.07	-0.03	-0.12	-0.20	-0.05	0.10	0.27
5600	-0.11	-0.11	-0.22	-0.25	-0.07	0.01	-0.14	0.15	0.19	0.37
5700	0.01	0.14	0.06	0.19	0.23	0.25	-0.04	0.19	0.27	0.28
5800	-0.81	-0.61	-0.52	-0.41	-0.27	-0.32	-0.20	0.18	0.19	0.18
5900	-0.41	-0.29	-0.19	-0.25	-0.15	-0.15	-0.34	0.04	0.11	0.16
6000	0.13	-0.02	-0.15	-0.20	-0.07	-0.10	-0.08	0.19	0.19	0.38
6100	-0.18	-0.23	-0.22	-0.22	-0.14	-0.05	-0.13	0.25	0.34	0.37
6200	-0.63	-0.56	-0.44	-0.31	-0.27	0.02	-0.12	0.07	0.26	0.29
6300	-0.32	-0.17	-0.07	-0.12	-0.22	-0.05	-0.06	0.14	0.19	0.14
6400	-0.12	-0.21	-0.32	-0.29	-0.28	-0.05	-0.13	0.19	0.27	0.39
6500	-0.23	-0.42	-0.37	-0.36	-0.24	-0.12	-0.15	0.09	0.08	0.25
6600	-0.26	-0.35	-0.29	-0.28	-0.18	0.16	-0.04	0.15	0.17	0.29
6700	-0.30	-0.37	-0.18	-0.25	-0.12	-0.02	-0.06	0.28	0.25	0.34
6800	-0.51	-0.43	-0.30	-0.19	-0.05	0.10	0.03	0.24	0.35	0.28
6900	-0.09	0.01	-0.03	0.00	0.00	0.21	0.08	0.15	0.19	0.22
7000	-0.24	-0.22	-0.27	-0.07	-0.04	0.37	0.14	0.33	0.43	0.39
7100	0.26	0.07	-0.01	-0.03	-0.03	0.25	0.12	0.34	0.33	0.33
7200	-0.13	-0.26	-0.19	-0.16	0.01	0.31	0.09	0.27	0.30	0.33
7300	-0.19	-0.25	-0.22	-0.31	-0.24	0.10	0.00	0.23	0.18	0.12
7400	-0.05	-0.08	-0.04	-0.07	-0.13	0.01	-0.06	0.15	0.18	0.27
7500	0.14	0.02	-0.01	-0.05	0.02	0.12	0.05	0.32	0.27	0.17
7600	-0.32	-0.19	-0.24	-0.02	0.05	0.07	0.01	0.27	0.28	0.30
7700	-0.15	-0.27	-0.13	-0.11	0.04	-0.06	-0.10	0.14	0.10	0.20
7800	-0.20	-0.33	-0.29	-0.09	0.02	-0.05	0.00	0.17	0.19	0.26
7900	-0.54	-0.46	-0.25	-0.13	-0.15	-0.11	-0.14	0.08	0.19	0.18
8000	-0.52	-0.28	-0.27	-0.15	-0.06	-0.12	-0.03	0.14	0.19	0.12
8100	-0.11	-0.20	-0.24	-0.19	-0.13	-0.11	-0.11	0.18	0.08	0.05
8200	-0.15	-0.36	-0.44	-0.43	-0.41	-0.31	-0.16	0.02	-0.06	-0.02
8300	-0.06	-0.29	-0.29	-0.21	-0.15	-0.11	-0.14	0.04	0.10	0.09
8400	-0.13	-0.30	-0.28	-0.10	-0.02	0.06	-0.03	0.13	0.17	0.18
8500	-0.43	-0.53	-0.25	-0.18	-0.04	0.00	-0.13	0.07	0.21	0.14
8600	-0.84	-0.34	-0.28	-0.04	-0.01	0.15	0.08	0.25	0.32	0.26
8700	0.16	0.03	0.10	-0.09	-0.10	0.01	-0.02	0.09	0.16	0.07
8750	0.20	0.00	0.02	-0.09	-0.07	0.07	0.03	0.13	0.20	0.13
8800	0.24	-0.03	-0.06	-0.09	-0.05	0.14	0.08	0.17	0.24	0.19
8850	0.13	-0.03	-0.03	-0.14	-0.10	0.04	0.03	0.16	0.20	0.17
8900	0.02	-0.02	0.00	-0.18	-0.15	-0.05	-0.02	0.15	0.15	0.15
8950	0.01	-0.12	-0.07	-0.15	-0.08	0.02	0.02	0.25	0.22	0.21
9000	0.00	-0.23	-0.14	-0.11	-0.02	0.08	0.07	0.35	0.29	0.28

Signal Generator

Typical Performance Data

Test Conditions: @ Temperature = 0°C.

Power (dBm)	Power deviation from nominal vs. Output Power (dB)								
	5.0 GHz	5.5 GHz	6.0 GHz	6.5 GHz	7.0 GHz	7.5 GHz	8.0 GHz	8.5 GHz	9.0 GHz
-50	0.01	-0.15	0.13	-0.23	-0.24	0.14	-0.52	-0.43	0.00
-49	-0.03	-0.15	0.10	-0.27	-0.23	0.12	-0.47	-0.45	-0.05
-48	-0.07	-0.16	0.07	-0.31	-0.23	0.09	-0.42	-0.47	-0.09
-47	-0.10	-0.16	0.04	-0.34	-0.22	0.07	-0.37	-0.49	-0.14
-46	-0.14	-0.17	0.01	-0.38	-0.22	0.04	-0.33	-0.51	-0.18
-45	-0.18	-0.17	-0.02	-0.42	-0.22	0.02	-0.28	-0.53	-0.23
-44	-0.18	-0.17	-0.04	-0.41	-0.23	0.01	-0.28	-0.48	-0.21
-43	-0.17	-0.17	-0.07	-0.40	-0.24	0.01	-0.28	-0.42	-0.19
-42	-0.17	-0.16	-0.09	-0.39	-0.25	0.00	-0.27	-0.36	-0.17
-41	-0.17	-0.16	-0.12	-0.38	-0.26	0.00	-0.27	-0.30	-0.16
-40	-0.17	-0.16	-0.15	-0.37	-0.27	-0.01	-0.27	-0.25	-0.14
-38	-0.19	-0.16	-0.16	-0.35	-0.23	0.00	-0.27	-0.19	-0.14
-36	-0.21	-0.15	-0.17	-0.33	-0.19	0.01	-0.26	-0.13	-0.14
-34	-0.22	-0.13	-0.18	-0.33	-0.15	0.00	-0.24	-0.12	-0.14
-32	-0.24	-0.10	-0.19	-0.34	-0.11	-0.02	-0.19	-0.15	-0.13
-30	-0.25	-0.07	-0.20	-0.36	-0.07	-0.05	-0.15	-0.18	-0.11
-28	-0.21	-0.09	-0.18	-0.33	-0.05	-0.06	-0.12	-0.13	-0.09
-26	-0.16	-0.12	-0.16	-0.30	-0.04	-0.07	-0.10	-0.09	-0.07
-24	-0.15	-0.11	-0.14	-0.28	-0.03	-0.06	-0.08	-0.06	-0.05
-22	-0.16	-0.07	-0.10	-0.26	-0.04	-0.02	-0.07	-0.05	-0.03
-20	-0.18	-0.03	-0.07	-0.24	-0.04	0.02	-0.06	-0.04	-0.02
-18	-0.17	-0.03	-0.08	-0.24	0.13	0.08	-0.06	-0.03	0.07
-16	-0.17	-0.03	-0.09	-0.24	0.29	0.13	-0.06	-0.03	0.15
-14	-0.16	-0.04	-0.09	-0.22	0.38	0.16	-0.08	-0.02	0.17
-12	-0.13	-0.08	-0.10	-0.17	0.37	0.14	-0.10	-0.01	0.12
-10	-0.10	-0.12	-0.10	-0.12	0.37	0.12	-0.12	0.00	0.08
-8	-0.09	-0.18	-0.09	-0.14	0.32	0.10	-0.10	-0.02	0.10
-6	-0.09	-0.25	-0.08	-0.16	0.27	0.07	-0.08	-0.04	0.12
-4	-0.11	-0.27	-0.08	-0.17	0.23	0.06	-0.06	-0.07	0.11
-2	-0.15	-0.23	-0.08	-0.16	0.19	0.05	-0.05	-0.10	0.09
0	-0.20	-0.20	-0.08	-0.15	0.14	0.05	-0.03	-0.13	0.07
+2	-0.14	-0.15	0.00	-0.10	0.24	0.15	0.01	-0.05	0.17
+4	-0.09	-0.09	0.08	-0.05	0.34	0.24	0.06	0.04	0.28
+6	-0.04	-0.06	0.14	0.00	0.38	0.30	0.09	0.08	0.34
+8	0.00	-0.05	0.16	0.05	0.35	0.31	0.12	0.07	0.34
+10	0.04	-0.05	0.19	0.09	0.33	0.32	0.14	0.07	0.35
+11	0.04	-0.02	0.19	0.09	0.35	0.31	0.15	0.09	0.34
+12	0.04	0.01	0.19	0.09	0.37	0.30	0.16	0.12	0.32
+13	0.03	0.04	0.19	0.08	0.39	0.29	0.17	0.15	0.31
+14	0.03	0.07	0.19	0.08	0.41	0.28	0.18	0.18	0.30
+15	0.03	0.10	0.19	0.08	0.43	0.27	0.19	0.21	0.29
+16	0.08	0.14	0.23	0.11	0.42	0.25	0.18	0.19	0.29
+17	0.12	0.17	0.26	0.15	0.41	0.23	0.16	0.18	0.28
+18	0.17	0.21	0.30	0.18	0.40	0.21	0.15	0.17	0.28
+19	0.22	0.24	0.34	0.22	0.39	0.19	0.13	0.15	0.28
+20	0.27	0.27	0.38	0.25	0.39	0.17	0.12	0.14	0.28

Signal Generator

Typical Performance Data

Test Conditions: @ Temperature = 0°C.

Freq. (MHz)	Harmonics levels vs. Output Frequency (dBc)									
	F2					F3				
	-50 dBm	-40 dBm	-20 dBm	0 dBm	+20 dBm	-50 dBm	-40 dBm	-20 dBm	0 dBm	+20 dBm
5000	-15.00	-16.83	-19.11	-14.04	-17.45	-32.83	-37.05	-38.98	-46.83	-31.30
5050	-15.77	-17.20	-19.59	-14.60	-17.86	-34.86	-37.78	-42.55	-53.38	-34.20
5100	-16.55	-17.56	-20.06	-15.16	-18.28	-36.88	-38.52	-46.13	-59.93	-37.10
5150	-16.05	-17.54	-19.99	-15.30	-18.46	-37.51	-37.58	-49.33	-61.41	-40.65
5200	-15.54	-17.52	-19.91	-15.43	-18.65	-38.13	-36.65	-52.53	-62.89	-44.20
5300	-14.07	-16.41	-18.99	-15.12	-18.29	-46.50	-43.35	-58.81	-73.47	-53.77
5400	-15.03	-16.32	-18.31	-14.86	-18.42	-56.31	-39.50	-60.46	-73.85	-62.39
5500	-16.14	-16.36	-17.85	-14.98	-18.76	-51.90	-35.14	-57.13	-69.53	-58.98
5600	-12.10	-14.97	-17.92	-15.09	-18.78	-47.74	-39.40	-59.90	-69.98	-55.65
5700	-12.37	-15.34	-17.85	-15.34	-19.48	-52.22	-40.19	-55.05	-70.07	-56.09
5800	-11.07	-15.23	-18.53	-16.03	-21.01	-50.03	-38.66	-62.31	-67.10	-55.97
5900	-15.10	-17.40	-18.77	-15.44	-19.21	-50.11	-40.12	-59.67	-65.50	-53.93
6000	-13.51	-19.22	-19.91	-15.71	-19.16	-49.89	-39.30	-60.96	-62.37	-54.02
6100	-15.89	-17.38	-19.27	-15.83	-18.91	-49.62	-34.95	-56.08	-61.57	-53.70
6200	-19.06	-19.00	-19.75	-15.72	-18.57	-48.62	-38.05	-57.98	-59.14	-53.79
6300	-18.77	-19.42	-20.28	-15.92	-19.00	-54.06	-32.90	-55.00	-57.76	-53.69
6400	-12.65	-16.10	-19.46	-16.12	-19.34	-48.62	-39.55	-60.32	-61.08	-54.95
6500	-14.43	-17.95	-19.20	-16.16	-19.20	-51.90	-38.81	-59.56	-59.58	-54.18
6600	-24.81	-19.72	-18.73	-16.78	-19.27	-52.58	-36.68	-57.82	-56.79	-53.13
6700	-17.46	-17.16	-17.58	-16.42	-18.63	-47.25	-35.25	-59.54	-65.82	-52.84
6800	-12.83	-15.12	-16.66	-16.06	-18.71	-52.13	-39.11	-60.94	-58.87	-52.78
6900	-12.54	-14.75	-16.08	-15.73	-18.59	-49.82	-38.50	-54.65	-63.26	-54.71
7000	-21.43	-16.63	-15.19	-15.11	-18.05	-45.76	-38.49	-55.72	-67.27	-55.09
7100	-14.98	-17.27	-18.65	-19.43	-22.25	-45.95	-37.03	-56.76	-67.52	-56.35
7200	-11.70	-15.16	-18.01	-19.28	-22.78	-47.81	-34.40	-56.57	-71.09	-60.35
7300	-13.49	-16.92	-18.79	-19.39	-23.59	-46.90	-37.71	-54.01	-68.53	-59.94
7400	-20.07	-21.89	-22.33	-22.06	-27.23	-48.95	-34.16	-54.61	-67.23	-62.87
7500	-25.86	-27.46	-26.84	-25.49	-32.73	-47.84	-36.83	-54.16	-69.05	-66.57
7600	-27.26	-33.69	-31.28	-28.99	-37.62	-48.42	-33.78	-56.10	-72.16	-72.18
7700	-25.05	-31.78	-34.52	-33.71	-43.53	-48.15	-36.52	-55.39	-75.08	-79.28
7800	-31.20	-34.05	-38.32	-38.54	-49.28	-45.44	-35.47	-54.81	-73.19	-81.92
7900	-31.08	-36.27	-44.41	-44.62	-55.95	-50.70	-33.64	-53.76	-78.11	-82.62
8000	-39.07	-39.71	-52.56	-52.43	-61.86	-45.24	-32.24	-52.43	-78.79	-81.75
8100	-42.03	-43.61	-57.29	-58.12	-66.82	-44.72	-32.13	-49.60	-72.11	-84.08
8200	-44.42	-36.95	-53.21	-56.57	-63.65	-44.22	-34.62	-55.46	-71.56	-84.10
8300	-40.97	-37.68	-50.49	-54.26	-60.00	-43.81	-31.87	-54.30	-73.29	-81.58
8400	-51.28	-37.70	-52.77	-51.52	-58.61	-42.16	-32.69	-48.31	-73.26	-83.77
8500	-43.52	-37.00	-51.41	-51.96	-60.45	-45.95	-33.32	-52.85	-73.03	-86.33
8600	-44.45	-38.47	-53.08	-50.69	-62.90	-46.89	-33.49	-48.27	-69.18	-88.11
8700	-54.24	-38.95	-51.15	-50.21	-67.02	-44.74	-37.42	-54.16	-72.49	-87.81
8750	-49.22	-37.21	-50.79	-49.63	-68.15	-44.57	-32.55	-54.28	-72.44	-88.06
8800	-44.21	-35.47	-50.43	-49.05	-69.28	-44.40	-27.67	-54.40	-72.40	-88.31
8850	-43.89	-36.10	-51.28	-49.09	-68.18	--	--	--	--	--
8900	-43.57	-36.73	-52.14	-49.13	-67.07	--	--	--	--	--
8950	-44.37	-37.39	-51.36	-48.97	-64.92	--	--	--	--	--
9000	-45.16	-38.05	-50.59	-48.80	-62.76	--	--	--	--	--

Signal Generator

SSG-5N9G-RC

Typical Performance Data

Test Conditions: @ Temperature = 0°C.

Freq. (MHz)	Phase Noise vs. Output Frequency (dBc / Hz)				
	1 kHz	10 kHz	100 kHz	1 MHz	10 MHz
5000	-98.62	-109.15	-117.58	-125.29	-135.21
5050	-98.76	-109.01	-117.40	-124.89	-135.27
5100	-98.89	-108.86	-117.22	-124.49	-135.32
5150	-98.61	-108.74	-117.23	-124.47	-134.91
5200	-98.33	-108.62	-117.24	-124.44	-134.50
5300	-97.77	-108.59	-116.97	-123.86	-135.30
5400	-97.90	-108.21	-116.65	-123.09	-135.28
5500	-97.60	-108.13	-116.76	-123.52	-135.58
5600	-97.73	-108.32	-116.48	-122.33	-135.30
5700	-97.30	-107.86	-116.28	-122.16	-135.57
5800	-97.42	-107.75	-116.33	-121.13	-135.63
5900	-97.03	-107.78	-115.90	-121.29	-135.28
6000	-96.96	-107.79	-116.23	-119.83	-135.06
6100	-96.85	-107.13	-115.79	-119.19	-135.46
6200	-96.63	-107.23	-116.02	-117.31	-135.90
6300	-96.66	-106.99	-116.01	-117.03	-136.36
6400	-96.27	-107.02	-115.44	-116.36	-136.21
6500	-96.21	-106.92	-115.48	-119.34	-136.21
6600	-95.98	-106.58	-115.31	-119.29	-136.04
6700	-95.83	-106.61	-114.84	-118.18	-135.56
6800	-95.49	-106.38	-114.88	-117.27	-135.64
6900	-95.46	-106.35	-114.83	-117.82	-135.73
7000	-95.62	-106.06	-114.47	-118.14	-135.91
7100	-95.36	-105.63	-114.54	-117.33	-135.17
7200	-95.50	-105.83	-114.24	-118.46	-135.69
7300	-95.24	-105.69	-114.17	-117.52	-135.68
7400	-94.73	-105.67	-114.21	-116.69	-135.30
7500	-95.31	-105.57	-113.80	-123.53	-135.45
7600	-94.84	-105.55	-113.44	-122.13	-136.08
7700	-94.72	-105.31	-113.63	-121.90	-136.72
7800	-94.65	-105.29	-113.69	-120.25	-135.94
7900	-94.81	-105.08	-113.37	-121.33	-136.19
8000	-94.28	-105.11	-113.42	-120.78	-136.15
8100	-94.32	-104.95	-113.61	-119.59	-135.76
8200	-93.93	-105.01	-113.22	-120.69	-135.83
8300	-94.48	-104.86	-113.32	-119.97	-135.52
8400	-94.17	-104.61	-112.80	-118.88	-136.10
8500	-93.84	-104.51	-112.65	-121.80	-135.29
8600	-93.99	-104.35	-112.54	-121.41	-135.73
8700	-93.93	-104.19	-112.70	-121.43	-135.07
8750	-93.84	-104.23	-112.72	-121.34	-135.20
8800	-93.74	-104.27	-112.73	-121.24	-135.32
8850	-93.78	-104.28	-112.58	-120.87	-135.21
8900	-93.81	-104.28	-112.42	-120.50	-135.10
8950	-93.64	-104.15	-112.32	-120.08	-135.35
9000	-93.46	-104.02	-112.21	-119.65	-135.60

Freq. (MHz)	Power (dBM) Max
5000	24.17
5050	24.29
5100	24.42
5150	24.50
5200	24.58
5300	24.42
5400	24.14
5500	23.99
5600	23.68
5700	23.34
5800	23.13
5900	22.90
6000	22.67
6100	22.57
6200	22.49
6300	22.48
6400	22.58
6500	22.80
6600	23.11
6700	23.50
6800	23.79
6900	23.97
7000	24.26
7100	24.51
7200	24.61
7300	24.68
7400	24.76
7500	24.74
7600	24.53
7700	24.32
7800	24.10
7900	24.03
8000	23.89
8100	23.84
8200	23.83
8300	23.64
8400	23.50
8500	23.56
8600	23.48
8700	23.43
8750	23.47
8800	23.51
8850	23.55
8900	23.60
8950	23.64
9000	23.68

Signal Generator

SSG-5N9G-RC

Typical Performance Data

Test Conditions: @ Temperature = 0°C.

Freq. Offsets (kHz)	Phase Noise vs. Offset Frequency (dBc / Hz)				
	5.0 GHz	6.0 GHz	7.0 GHz	8.0 GHz	9.0 GHz
1	-98.62	-96.96	-95.62	-94.28	-93.46
10	-109.15	-107.79	-106.06	-105.11	-104.02
100	-117.58	-116.23	-114.47	-113.42	-112.21
1000	-125.29	-119.83	-118.14	-120.78	-119.65
10000	-135.21	-135.06	-135.91	-136.15	-135.60

Freq. (MHz)	Spurious (dBc)
5000	-65.93
5050	-66.06
5100	-66.19
5150	-66.32
5200	-66.44
5300	-66.50
5400	-66.34
5500	-66.19
5600	-66.38
5700	-66.57
5800	-66.54
5900	-66.28
6000	-66.03
6100	-65.94
6200	-65.85
6300	-66.10
6400	-66.71
6500	-67.32
6600	-66.35
6700	-65.38
6800	-65.17
6900	-65.71
7000	-66.25
7100	-65.70
7200	-65.15
7300	-65.06
7400	-65.43
7500	-65.81
7600	-65.74
7700	-65.67
7800	-65.60
7900	-65.54
8000	-65.49
8100	-65.65
8200	-65.81
8300	-65.67
8400	-65.25
8500	-64.82
8600	-65.56
8700	-66.29
8750	-66.66
8800	-66.14
8850	-65.62
8900	-65.10
8950	-64.58
9000	-64.06

Note: Spurious was measured in offsets of 100 kHz to 150 MHz.

Signal Generator

SSG-5N9G-RC

Typical Performance Data

Test Conditions: @ Temperature = 25°C.

Freq. (MHz)	Power deviation from nominal vs. Output Frequency (dB)									
	-50 dBm	-45 dBm	-40 dBm	-30 dBm	-20 dBm	-10 dBm	0 dBm	+10 dBm	+15 dBm	+20 dBm
5000	0.26	0.22	0.24	0.21	0.24	0.25	0.16	0.43	0.55	0.37
5050	0.26	0.23	0.26	0.30	0.31	0.30	0.20	0.47	0.57	0.42
5100	0.25	0.23	0.28	0.38	0.37	0.36	0.24	0.51	0.60	0.46
5150	0.16	0.21	0.25	0.29	0.31	0.31	0.23	0.49	0.58	0.46
5200	0.07	0.18	0.23	0.20	0.24	0.25	0.22	0.47	0.57	0.46
5300	0.25	0.23	0.29	0.33	0.37	0.33	0.29	0.47	0.58	0.43
5400	0.34	0.28	0.31	0.28	0.32	0.37	0.26	0.47	0.55	0.57
5500	0.17	0.23	0.29	0.37	0.39	0.33	0.23	0.44	0.51	0.57
5600	0.29	0.26	0.31	0.29	0.30	0.36	0.28	0.46	0.52	0.65
5700	0.31	0.33	0.35	0.44	0.46	0.25	0.25	0.47	0.49	0.61
5800	0.01	0.15	0.14	0.20	0.23	0.25	0.27	0.47	0.58	0.58
5900	0.19	0.22	0.25	0.27	0.32	0.21	0.23	0.47	0.57	0.44
6000	0.31	0.17	0.24	0.21	0.24	0.30	0.29	0.54	0.60	0.61
6100	0.09	0.15	0.21	0.18	0.28	0.24	0.20	0.45	0.55	0.60
6200	-0.05	-0.02	0.09	0.12	0.16	0.29	0.25	0.54	0.55	0.60
6300	0.04	0.12	0.18	0.17	0.22	0.22	0.25	0.43	0.52	0.45
6400	0.12	0.10	0.07	0.11	0.18	0.28	0.30	0.57	0.70	0.59
6500	0.10	0.10	0.12	0.16	0.15	0.23	0.24	0.48	0.56	0.54
6600	0.09	0.10	0.11	0.14	0.21	0.32	0.30	0.50	0.61	0.57
6700	0.11	0.17	0.21	0.18	0.20	0.24	0.26	0.56	0.61	0.56
6800	0.24	0.17	0.26	0.16	0.33	0.36	0.31	0.62	0.62	0.56
6900	0.32	0.32	0.41	0.29	0.42	0.27	0.26	0.47	0.51	0.43
7000	0.16	0.15	0.24	0.16	0.33	0.37	0.30	0.59	0.59	0.50
7100	0.36	0.34	0.37	0.23	0.45	0.29	0.31	0.54	0.62	0.49
7200	0.25	0.29	0.32	0.24	0.46	0.36	0.35	0.53	0.65	0.52
7300	0.17	0.20	0.26	0.12	0.25	0.29	0.26	0.47	0.59	0.46
7400	0.17	0.28	0.31	0.28	0.32	0.33	0.30	0.55	0.61	0.53
7500	0.23	0.25	0.28	0.17	0.33	0.27	0.30	0.50	0.61	0.46
7600	0.14	0.20	0.18	0.24	0.33	0.33	0.30	0.53	0.61	0.49
7700	0.25	0.30	0.27	0.18	0.33	0.26	0.25	0.42	0.54	0.46
7800	0.14	0.24	0.18	0.22	0.34	0.33	0.27	0.51	0.64	0.50
7900	0.10	0.20	0.25	0.20	0.29	0.27	0.26	0.52	0.58	0.46
8000	0.17	0.26	0.22	0.21	0.36	0.27	0.29	0.57	0.61	0.47
8100	0.22	0.26	0.25	0.19	0.28	0.24	0.26	0.44	0.56	0.39
8200	0.15	0.16	0.18	0.14	0.23	0.30	0.33	0.58	0.59	0.47
8300	0.29	0.21	0.28	0.15	0.34	0.25	0.24	0.48	0.46	0.42
8400	0.18	0.19	0.25	0.25	0.39	0.34	0.32	0.54	0.53	0.45
8500	0.24	0.33	0.36	0.21	0.36	0.26	0.25	0.51	0.50	0.45
8600	0.12	0.16	0.24	0.29	0.46	0.32	0.35	0.59	0.64	0.56
8700	0.35	0.38	0.39	0.20	0.27	0.27	0.21	0.43	0.51	0.39
8750	0.27	0.29	0.31	0.20	0.36	0.34	0.30	0.49	0.57	0.46
8800	0.20	0.19	0.23	0.20	0.45	0.40	0.39	0.55	0.63	0.52
8850	0.27	0.30	0.27	0.16	0.36	0.31	0.32	0.50	0.59	0.46
8900	0.34	0.41	0.32	0.11	0.27	0.21	0.25	0.45	0.55	0.40
8950	0.21	0.26	0.23	0.13	0.36	0.29	0.29	0.49	0.59	0.44
9000	0.08	0.12	0.14	0.14	0.44	0.37	0.32	0.53	0.63	0.48

Signal Generator

Typical Performance Data

Test Conditions: @ Temperature = 25°C.

Power (dBm)	Power deviation from nominal vs. Output Power (dB)								
	5.0 GHz	5.5 GHz	6.0 GHz	6.5 GHz	7.0 GHz	7.5 GHz	8.0 GHz	8.5 GHz	9.0 GHz
-50	0.26	0.17	0.31	0.10	0.16	0.23	0.17	0.24	0.08
-49	0.25	0.18	0.28	0.10	0.16	0.24	0.19	0.26	0.09
-48	0.25	0.20	0.25	0.10	0.16	0.24	0.21	0.28	0.10
-47	0.24	0.21	0.22	0.10	0.16	0.24	0.22	0.29	0.10
-46	0.23	0.22	0.20	0.10	0.15	0.25	0.24	0.31	0.11
-45	0.22	0.23	0.17	0.10	0.15	0.25	0.26	0.33	0.12
-44	0.22	0.24	0.18	0.11	0.17	0.26	0.25	0.33	0.12
-43	0.23	0.25	0.20	0.11	0.18	0.27	0.24	0.34	0.13
-42	0.23	0.26	0.21	0.11	0.20	0.27	0.24	0.34	0.13
-41	0.24	0.28	0.23	0.12	0.22	0.28	0.23	0.35	0.13
-40	0.24	0.29	0.24	0.12	0.24	0.28	0.22	0.36	0.14
-38	0.25	0.31	0.26	0.14	0.25	0.30	0.24	0.37	0.15
-36	0.27	0.32	0.27	0.15	0.27	0.31	0.25	0.38	0.16
-34	0.26	0.34	0.27	0.16	0.25	0.28	0.25	0.35	0.16
-32	0.23	0.35	0.24	0.16	0.21	0.23	0.23	0.28	0.15
-30	0.21	0.37	0.21	0.16	0.16	0.17	0.21	0.21	0.14
-28	0.20	0.35	0.20	0.15	0.20	0.19	0.25	0.24	0.17
-26	0.20	0.32	0.18	0.13	0.23	0.21	0.29	0.26	0.20
-24	0.20	0.33	0.19	0.13	0.27	0.24	0.32	0.29	0.26
-22	0.22	0.36	0.21	0.14	0.30	0.29	0.34	0.33	0.35
-20	0.24	0.39	0.24	0.15	0.33	0.33	0.36	0.36	0.44
-18	0.26	0.41	0.24	0.19	0.34	0.29	0.36	0.31	0.40
-16	0.28	0.43	0.23	0.23	0.35	0.26	0.36	0.25	0.36
-14	0.28	0.42	0.24	0.24	0.36	0.25	0.34	0.23	0.35
-12	0.26	0.38	0.27	0.24	0.36	0.26	0.30	0.25	0.36
-10	0.25	0.33	0.30	0.23	0.37	0.27	0.27	0.26	0.37
-8	0.24	0.31	0.31	0.22	0.36	0.28	0.30	0.27	0.38
-6	0.23	0.29	0.32	0.22	0.36	0.29	0.33	0.27	0.39
-4	0.22	0.27	0.31	0.22	0.35	0.30	0.34	0.27	0.38
-2	0.19	0.25	0.30	0.23	0.33	0.30	0.31	0.26	0.35
0	0.16	0.23	0.29	0.24	0.30	0.30	0.29	0.25	0.32
+2	0.24	0.30	0.36	0.32	0.41	0.35	0.36	0.34	0.41
+4	0.32	0.37	0.44	0.40	0.51	0.40	0.44	0.42	0.50
+6	0.37	0.41	0.49	0.45	0.57	0.44	0.50	0.47	0.55
+8	0.40	0.42	0.51	0.47	0.58	0.47	0.53	0.49	0.54
+10	0.43	0.44	0.54	0.48	0.59	0.50	0.57	0.51	0.53
+11	0.46	0.45	0.55	0.50	0.59	0.52	0.58	0.50	0.55
+12	0.48	0.47	0.56	0.52	0.59	0.54	0.59	0.50	0.57
+13	0.50	0.48	0.57	0.53	0.59	0.56	0.60	0.50	0.59
+14	0.52	0.50	0.58	0.55	0.59	0.59	0.60	0.50	0.61
+15	0.55	0.51	0.60	0.56	0.59	0.61	0.61	0.50	0.63
+16	0.51	0.52	0.60	0.56	0.57	0.58	0.58	0.49	0.60
+17	0.48	0.54	0.60	0.55	0.56	0.55	0.56	0.48	0.57
+18	0.44	0.55	0.60	0.55	0.54	0.52	0.53	0.47	0.54
+19	0.41	0.56	0.60	0.54	0.52	0.49	0.50	0.46	0.51
+20	0.37	0.57	0.61	0.54	0.50	0.46	0.47	0.45	0.48

Signal Generator

Typical Performance Data

Test Conditions: @ Temperature = 25°C.

Freq. (MHz)	Harmonics levels vs. Output Frequency (dBc)									
	F2					F3				
	-50 dBm	-40 dBm	-20 dBm	0 dBm	+20 dBm	-50 dBm	-40 dBm	-20 dBm	0 dBm	+20 dBm
5000	-14.81	-16.45	-18.96	-13.96	-17.96	-34.61	-36.28	-40.67	-49.06	-31.99
5050	-15.50	-16.94	-19.44	-14.52	-18.33	-35.80	-38.33	-43.85	-54.94	-35.00
5100	-16.20	-17.42	-19.92	-15.09	-18.69	-36.99	-40.38	-47.03	-60.82	-38.02
5150	-15.53	-17.16	-19.75	-15.13	-18.82	-39.34	-38.54	-50.82	-63.38	-41.78
5200	-14.86	-16.90	-19.59	-15.17	-18.94	-41.68	-36.70	-54.60	-65.93	-45.54
5300	-14.74	-16.74	-18.91	-15.00	-18.64	-49.09	-40.26	-59.28	-68.26	-55.02
5400	-16.06	-16.30	-18.37	-14.96	-19.17	-55.08	-38.74	-62.06	-73.73	-63.04
5500	-13.84	-15.42	-17.87	-15.08	-19.53	-50.87	-38.50	-56.08	-71.82	-59.30
5600	-13.14	-15.46	-18.13	-15.34	-19.73	-49.96	-35.88	-57.66	-67.96	-56.61
5700	-11.69	-14.70	-17.85	-15.42	-19.93	-53.35	-35.71	-58.55	-66.55	-56.29
5800	-11.53	-15.73	-18.59	-16.11	-21.15	-48.25	-39.32	-60.53	-67.31	-56.18
5900	-14.87	-17.39	-19.00	-15.67	-19.73	-46.33	-38.43	-54.77	-65.30	-54.48
6000	-18.48	-21.16	-20.25	-16.04	-19.71	-47.10	-40.99	-57.07	-62.52	-54.72
6100	-15.95	-17.66	-19.36	-15.88	-19.40	-50.57	-34.58	-55.64	-60.64	-54.33
6200	-19.68	-18.62	-19.45	-15.74	-19.08	-51.66	-37.34	-57.63	-60.54	-54.09
6300	-16.41	-17.45	-19.28	-15.89	-19.39	-50.68	-39.32	-55.11	-59.34	-54.15
6400	-12.58	-15.94	-18.70	-16.02	-19.75	-50.09	-38.24	-56.37	-61.34	-55.11
6500	-16.85	-18.08	-18.57	-16.12	-19.80	-51.41	-38.35	-58.91	-60.58	-54.35
6600	-21.33	-18.84	-18.28	-16.68	-20.00	-55.66	-38.43	-60.44	-56.75	-53.23
6700	-16.13	-16.58	-17.32	-16.25	-19.33	-50.63	-37.95	-56.97	-69.08	-53.12
6800	-13.18	-14.95	-16.61	-15.96	-19.76	-51.08	-37.24	-56.91	-60.17	-53.64
6900	-12.90	-15.07	-15.78	-15.58	-19.48	-50.36	-38.81	-56.27	-63.54	-54.90
7000	-18.91	-16.03	-15.58	-15.43	-19.32	-49.51	-36.96	-57.34	-69.53	-55.40
7100	-14.25	-17.10	-19.09	-20.04	-23.60	-48.81	-34.32	-55.71	-66.52	-56.73
7200	-12.49	-15.86	-18.64	-19.72	-24.04	-48.66	-34.07	-57.61	-69.82	-60.84
7300	-15.92	-18.81	-19.75	-20.17	-25.12	-48.60	-34.08	-55.43	-70.19	-60.42
7400	-23.88	-23.71	-23.24	-23.18	-28.99	-50.35	-34.63	-53.82	-69.86	-63.75
7500	-26.43	-26.43	-28.05	-26.83	-34.63	-49.47	-34.92	-58.45	-70.42	-67.44
7600	-36.19	-37.27	-32.75	-30.35	-39.27	-51.75	-36.18	-52.69	-74.98	-74.41
7700	-26.80	-31.96	-36.02	-35.39	-45.33	-49.64	-32.66	-58.61	-72.87	-81.36
7800	-31.27	-33.29	-39.51	-40.10	-51.07	-48.35	-33.11	-54.43	-74.53	-82.04
7900	-34.65	-36.34	-46.52	-46.78	-56.98	-49.21	-34.24	-54.54	-74.63	-83.88
8000	-43.83	-40.10	-55.85	-54.58	-63.03	-46.50	-36.90	-56.94	-71.78	-80.73
8100	-50.61	-38.57	-54.62	-59.05	-66.31	-46.94	-32.25	-51.32	-73.98	-82.73
8200	-46.57	-39.81	-51.46	-56.32	-63.00	-45.53	-36.01	-56.20	-75.43	-83.02
8300	-42.71	-40.21	-51.60	-53.86	-60.60	-44.29	-32.03	-50.43	-75.50	-83.33
8400	-49.55	-36.33	-54.26	-52.37	-60.22	-45.46	-31.27	-50.86	-74.92	-82.47
8500	-42.56	-36.88	-52.16	-52.48	-61.61	-44.55	-29.54	-48.85	-71.32	-82.84
8600	-44.32	-35.62	-51.67	-51.39	-63.02	-44.16	-30.28	-51.18	-71.32	-87.77
8700	-52.22	-38.48	-53.53	-50.87	-65.99	-45.62	-30.66	-54.07	-71.81	-90.66
8750	-46.68	-37.51	-52.17	-50.47	-65.73	-44.40	-31.59	-53.49	-71.30	-90.17
8800	-41.15	-36.55	-50.81	-50.08	-65.47	-43.19	-32.52	-52.92	-70.80	-89.69
8850	-43.04	-38.37	-51.26	-50.33	-64.52	--	--	--	--	--
8900	-44.92	-40.19	-51.71	-50.58	-63.57	--	--	--	--	--
8950	-44.60	-37.74	-51.27	-50.21	-62.63	--	--	--	--	--
9000	-44.27	-35.29	-50.83	-49.84	-61.70	--	--	--	--	--

Signal Generator

SSG-5N9G-RC

Typical Performance Data

Test Conditions: @ Temperature = 25°C.

Freq. (MHz)	Phase Noise vs. Output Frequency (dBc / Hz)				
	1 kHz	10 kHz	100 kHz	1 MHz	10 MHz
5000	-98.23	-109.48	-117.17	-125.04	-135.28
5050	-98.15	-109.25	-117.10	-124.98	-135.34
5100	-98.07	-109.01	-117.03	-124.92	-135.40
5150	-98.15	-108.98	-117.02	-124.63	-135.36
5200	-98.23	-108.95	-117.00	-124.34	-135.32
5300	-98.23	-108.89	-116.75	-123.86	-135.74
5400	-97.77	-108.72	-116.37	-123.74	-135.60
5500	-97.70	-108.35	-116.36	-122.42	-135.76
5600	-97.50	-108.29	-116.10	-123.34	-135.21
5700	-97.10	-108.52	-115.97	-121.94	-136.29
5800	-97.37	-108.26	-115.84	-121.01	-135.98
5900	-96.72	-107.46	-116.12	-122.30	-136.00
6000	-96.81	-107.57	-115.90	-119.70	-135.62
6100	-96.88	-107.41	-115.31	-118.73	-135.50
6200	-96.55	-107.52	-115.80	-119.20	-135.28
6300	-96.57	-107.24	-115.28	-118.79	-136.31
6400	-96.39	-107.22	-115.42	-117.22	-136.18
6500	-96.15	-106.95	-115.00	-119.02	-136.90
6600	-96.11	-106.52	-114.89	-118.30	-137.04
6700	-95.96	-106.54	-114.58	-117.96	-136.40
6800	-95.84	-106.86	-114.54	-118.09	-136.17
6900	-95.70	-106.23	-114.71	-118.36	-136.34
7000	-95.91	-106.43	-114.45	-118.38	-136.13
7100	-95.40	-106.00	-114.04	-118.86	-136.02
7200	-95.75	-105.95	-113.98	-118.20	-136.01
7300	-94.95	-106.00	-114.09	-117.77	-136.59
7400	-94.94	-105.89	-113.95	-117.30	-136.24
7500	-95.09	-106.04	-113.71	-122.75	-136.42
7600	-94.70	-105.59	-113.45	-123.45	-137.28
7700	-95.11	-105.66	-113.31	-121.86	-136.75
7800	-95.11	-105.36	-113.31	-120.70	-135.17
7900	-95.03	-105.29	-113.69	-119.45	-136.47
8000	-94.61	-105.22	-113.29	-119.76	-136.15
8100	-94.31	-104.79	-112.94	-119.73	-136.60
8200	-94.23	-104.91	-113.04	-119.66	-136.74
8300	-93.90	-104.77	-112.70	-119.56	-136.84
8400	-94.28	-104.71	-113.01	-118.94	-136.21
8500	-93.98	-104.72	-112.63	-122.45	-136.39
8600	-93.38	-104.45	-112.58	-120.45	-136.26
8700	-93.43	-104.05	-112.09	-118.85	-135.98
8750	-93.46	-104.19	-112.09	-119.50	-136.17
8800	-93.49	-104.33	-112.09	-120.14	-136.36
8850	-93.43	-104.27	-111.98	-120.72	-136.29
8900	-93.37	-104.21	-111.86	-121.30	-136.22
8950	-93.17	-104.09	-111.84	-120.49	-136.29
9000	-92.96	-103.96	-111.81	-119.67	-136.35

Freq. (MHz)	Power (dBM) Max
5000	24.29
5050	24.41
5100	24.53
5150	24.59
5200	24.65
5300	24.49
5400	24.22
5500	24.10
5600	23.80
5700	23.48
5800	23.29
5900	23.07
6000	22.90
6100	22.84
6200	22.78
6300	22.78
6400	22.90
6500	23.10
6600	23.34
6700	23.68
6800	24.00
6900	24.19
7000	24.32
7100	24.47
7200	24.51
7300	24.54
7400	24.57
7500	24.58
7600	24.35
7700	24.12
7800	23.96
7900	23.85
8000	23.74
8100	23.71
8200	23.67
8300	23.51
8400	23.42
8500	23.39
8600	23.37
8700	23.32
8750	23.37
8800	23.42
8850	23.46
8900	23.50
8950	23.53
9000	23.56

Signal Generator

SSG-5N9G-RC

Typical Performance Data

Test Conditions: @ Temperature = 25°C.

Freq. Offsets (kHz)	Phase Noise vs. Offset Frequency (dBc / Hz)				
	5.0 GHz	6.0 GHz	7.0 GHz	8.0 GHz	9.0 GHz
1	-98.23	-96.81	-95.91	-94.61	-92.96
10	-109.48	-107.57	-106.43	-105.22	-103.96
100	-117.17	-115.90	-114.45	-113.29	-111.81
1000	-125.04	-119.70	-118.38	-119.76	-119.67
10000	-135.28	-135.62	-136.13	-136.15	-136.35

Freq. (MHz)	Spurious (dBc)
5000	-65.56
5050	-65.70
5100	-65.83
5150	-65.97
5200	-66.10
5300	-66.35
5400	-66.58
5500	-66.81
5600	-66.93
5700	-67.05
5800	-66.99
5900	-66.75
6000	-66.51
6100	-66.35
6200	-66.20
6300	-66.13
6400	-66.16
6500	-66.19
6600	-65.98
6700	-65.77
6800	-65.92
6900	-66.44
7000	-66.96
7100	-66.38
7200	-65.79
7300	-65.76
7400	-66.27
7500	-66.78
7600	-65.94
7700	-65.09
7800	-64.93
7900	-65.43
8000	-65.94
8100	-65.90
8200	-65.87
8300	-65.69
8400	-65.39
8500	-65.08
8600	-65.53
8700	-65.99
8750	-66.21
8800	-66.04
8850	-65.86
8900	-65.69
8950	-65.51
9000	-65.34

Note: Spurious was measured in offsets of 100 kHz to 150 MHz.

Signal Generator

SSG-5N9G-RC

Typical Performance Data

Test Conditions: @ Temperature = 50°C.

Freq. (MHz)	Power deviation from nominal vs. Output Frequency (dB)									
	-50 dBm	-45 dBm	-40 dBm	-30 dBm	-20 dBm	-10 dBm	0 dBm	+10 dBm	+15 dBm	+20 dBm
5000	0.16	0.13	0.15	0.10	0.08	-0.06	-0.06	0.27	0.45	0.41
5050	0.18	0.10	0.15	0.17	0.13	-0.04	0.05	0.33	0.47	0.47
5100	0.19	0.08	0.15	0.23	0.18	-0.02	0.15	0.39	0.48	0.52
5150	0.09	0.05	0.08	0.19	0.09	0.01	0.14	0.34	0.45	0.52
5200	-0.01	0.03	0.02	0.14	0.00	0.04	0.12	0.30	0.41	0.51
5300	0.13	0.10	0.10	0.25	0.18	0.12	0.23	0.37	0.50	0.52
5400	0.08	0.11	0.09	0.18	0.09	-0.01	0.12	0.37	0.51	0.49
5500	0.09	0.13	0.13	0.25	0.22	0.01	0.12	0.37	0.47	0.50
5600	0.19	0.20	0.21	0.22	0.13	0.12	0.22	0.39	0.52	0.56
5700	0.26	0.35	0.30	0.43	0.34	0.29	0.26	0.43	0.52	0.65
5800	-0.22	-0.11	-0.06	0.04	-0.11	0.11	0.23	0.49	0.47	0.62
5900	-0.04	0.09	0.05	0.18	0.05	0.04	0.13	0.43	0.39	0.55
6000	-0.01	0.04	0.02	0.12	0.04	0.24	0.26	0.47	0.57	0.54
6100	0.09	0.02	0.05	0.13	0.02	0.12	0.16	0.50	0.58	0.59
6200	-0.04	-0.01	-0.10	-0.02	-0.12	0.07	0.24	0.50	0.58	0.63
6300	-0.11	-0.15	-0.07	0.03	0.05	0.05	0.19	0.45	0.49	0.52
6400	-0.05	-0.10	-0.13	0.01	0.00	0.11	0.18	0.48	0.55	0.61
6500	0.00	0.00	-0.05	0.04	-0.08	0.02	0.14	0.42	0.45	0.46
6600	-0.06	-0.07	-0.05	0.04	0.02	0.21	0.28	0.47	0.56	0.63
6700	0.00	0.10	0.04	0.07	-0.03	0.06	0.22	0.52	0.62	0.62
6800	0.08	0.00	0.02	0.11	0.08	0.06	0.17	0.52	0.62	0.59
6900	0.26	0.24	0.29	0.30	0.19	0.07	0.16	0.42	0.55	0.53
7000	0.17	0.17	0.12	0.19	0.16	0.02	0.22	0.53	0.57	0.56
7100	0.21	0.14	0.12	0.26	0.16	-0.01	0.13	0.52	0.54	0.53
7200	0.00	0.17	0.13	0.31	0.08	0.03	0.21	0.53	0.69	0.65
7300	-0.23	-0.13	-0.02	0.02	-0.11	0.02	0.08	0.44	0.46	0.50
7400	-0.03	0.05	0.05	0.17	0.02	0.05	0.20	0.38	0.52	0.50
7500	0.04	0.03	0.08	0.11	0.07	0.05	0.23	0.46	0.42	0.45
7600	0.32	0.13	0.08	0.23	0.13	0.18	0.24	0.45	0.49	0.52
7700	0.29	0.20	0.18	0.18	0.09	0.08	0.23	0.40	0.49	0.46
7800	0.16	0.13	0.14	0.27	0.16	0.24	0.29	0.53	0.55	0.53
7900	0.18	0.19	0.22	0.24	0.17	0.30	0.34	0.58	0.57	0.57
8000	0.12	0.09	0.06	0.21	0.18	0.28	0.25	0.53	0.58	0.55
8100	0.13	0.10	0.15	0.24	0.17	0.21	0.34	0.53	0.58	0.54
8200	-0.04	0.05	-0.02	0.15	0.17	0.20	0.28	0.47	0.55	0.50
8300	0.19	0.11	0.19	0.19	0.02	0.20	0.27	0.42	0.51	0.41
8400	0.18	0.20	0.19	0.32	0.14	0.27	0.34	0.54	0.49	0.52
8500	0.49	0.43	0.35	0.29	0.01	0.09	0.21	0.45	0.51	0.48
8600	-0.01	0.03	0.07	0.33	0.13	0.23	0.34	0.56	0.52	0.57
8700	-0.01	0.13	0.19	0.23	0.01	0.25	0.30	0.48	0.45	0.52
8750	-0.01	0.08	0.14	0.23	0.08	0.27	0.33	0.53	0.47	0.55
8800	-0.02	0.02	0.10	0.22	0.15	0.29	0.36	0.58	0.50	0.59
8850	0.07	0.15	0.11	0.15	0.07	0.20	0.27	0.49	0.44	0.50
8900	0.16	0.28	0.13	0.07	0.00	0.11	0.17	0.40	0.38	0.41
8950	0.03	0.12	0.04	0.10	0.07	0.12	0.19	0.41	0.40	0.42
9000	-0.10	-0.04	-0.04	0.13	0.15	0.14	0.21	0.42	0.43	0.43

Signal Generator

Typical Performance Data

Test Conditions: @ Temperature = 50°C.

Power (dBm)	Power deviation from nominal vs. Output Power (dB)								
	5.0 GHz	5.5 GHz	6.0 GHz	6.5 GHz	7.0 GHz	7.5 GHz	8.0 GHz	8.5 GHz	9.0 GHz
-50	0.16	0.09	-0.01	0.00	0.17	0.04	0.12	0.49	-0.10
-49	0.15	0.09	0.00	0.00	0.17	0.04	0.11	0.48	-0.09
-48	0.15	0.10	0.01	0.00	0.17	0.03	0.11	0.47	-0.08
-47	0.14	0.11	0.02	0.00	0.17	0.03	0.10	0.45	-0.06
-46	0.13	0.12	0.03	0.00	0.17	0.03	0.09	0.44	-0.05
-45	0.13	0.13	0.04	0.00	0.17	0.03	0.09	0.43	-0.04
-44	0.13	0.13	0.03	-0.01	0.16	0.04	0.08	0.42	-0.04
-43	0.14	0.13	0.03	-0.02	0.15	0.05	0.08	0.40	-0.04
-42	0.14	0.13	0.02	-0.03	0.14	0.06	0.07	0.39	-0.04
-41	0.15	0.13	0.02	-0.04	0.13	0.07	0.07	0.37	-0.04
-40	0.15	0.13	0.02	-0.05	0.12	0.08	0.06	0.35	-0.04
-38	0.13	0.13	0.02	-0.03	0.12	0.09	0.07	0.34	-0.01
-36	0.10	0.13	0.03	-0.01	0.13	0.10	0.08	0.33	0.02
-34	0.09	0.16	0.06	0.01	0.15	0.10	0.11	0.32	0.06
-32	0.10	0.21	0.09	0.03	0.17	0.11	0.16	0.30	0.09
-30	0.10	0.25	0.12	0.04	0.19	0.11	0.21	0.29	0.13
-28	0.12	0.27	0.12	-0.02	0.18	0.09	0.19	0.24	0.10
-26	0.15	0.28	0.12	-0.08	0.16	0.06	0.17	0.19	0.07
-24	0.14	0.27	0.10	-0.11	0.15	0.05	0.17	0.14	0.08
-22	0.11	0.24	0.07	-0.10	0.16	0.06	0.17	0.07	0.11
-20	0.08	0.22	0.04	-0.08	0.16	0.07	0.18	0.01	0.15
-18	0.08	0.22	0.06	-0.07	0.09	0.04	0.16	0.02	0.12
-16	0.08	0.22	0.09	-0.06	0.02	0.01	0.15	0.02	0.09
-14	0.05	0.18	0.13	-0.04	-0.01	0.01	0.17	0.04	0.09
-12	0.00	0.10	0.18	-0.01	0.00	0.03	0.22	0.07	0.12
-10	-0.06	0.01	0.24	0.02	0.02	0.05	0.28	0.09	0.14
-8	-0.01	0.06	0.23	0.03	0.05	0.10	0.28	0.13	0.15
-6	0.04	0.10	0.22	0.04	0.09	0.16	0.29	0.17	0.16
-4	0.04	0.12	0.22	0.07	0.13	0.19	0.28	0.19	0.18
-2	-0.01	0.12	0.24	0.11	0.17	0.21	0.26	0.20	0.19
0	-0.06	0.12	0.26	0.14	0.22	0.23	0.25	0.21	0.21
+2	0.03	0.18	0.31	0.23	0.30	0.28	0.34	0.28	0.29
+4	0.13	0.25	0.36	0.33	0.39	0.33	0.43	0.36	0.37
+6	0.19	0.30	0.40	0.38	0.45	0.37	0.49	0.41	0.41
+8	0.23	0.33	0.43	0.40	0.49	0.42	0.51	0.43	0.41
+10	0.27	0.37	0.47	0.42	0.53	0.46	0.53	0.45	0.42
+11	0.31	0.39	0.49	0.43	0.54	0.45	0.54	0.46	0.42
+12	0.34	0.41	0.51	0.43	0.55	0.44	0.55	0.47	0.42
+13	0.38	0.43	0.53	0.44	0.55	0.44	0.56	0.49	0.42
+14	0.42	0.45	0.55	0.45	0.56	0.43	0.57	0.50	0.43
+15	0.45	0.47	0.57	0.45	0.57	0.42	0.58	0.51	0.43
+16	0.45	0.48	0.57	0.46	0.56	0.43	0.57	0.50	0.43
+17	0.44	0.48	0.56	0.46	0.56	0.43	0.57	0.50	0.43
+18	0.43	0.49	0.55	0.46	0.56	0.44	0.56	0.49	0.43
+19	0.42	0.49	0.54	0.46	0.56	0.45	0.56	0.49	0.43
+20	0.41	0.50	0.54	0.46	0.56	0.45	0.55	0.48	0.43

Signal Generator

Typical Performance Data

Test Conditions: @ Temperature = 50°C.

Freq. (MHz)	Harmonics levels vs. Output Frequency (dBc)									
	F2					F3				
	-50 dBm	-40 dBm	-20 dBm	0 dBm	+20 dBm	-50 dBm	-40 dBm	-20 dBm	0 dBm	+20 dBm
5000	-14.82	-16.75	-19.00	-14.10	-18.72	-37.81	-36.21	-42.41	-52.50	-32.85
5050	-15.46	-17.16	-19.47	-14.61	-19.08	-37.64	-37.06	-45.72	-57.83	-36.07
5100	-16.11	-17.57	-19.93	-15.12	-19.44	-37.47	-37.91	-49.02	-63.16	-39.29
5150	-15.50	-17.24	-19.76	-15.21	-19.47	-40.67	-37.97	-52.06	-64.59	-43.10
5200	-14.90	-16.90	-19.60	-15.30	-19.50	-43.87	-38.04	-55.10	-66.02	-46.90
5300	-15.86	-17.06	-19.09	-15.26	-19.18	-53.88	-39.37	-60.79	-70.26	-56.64
5400	-16.06	-16.34	-18.63	-15.33	-19.64	-54.19	-40.29	-59.86	-77.44	-62.95
5500	-13.64	-15.58	-18.09	-15.37	-20.05	-53.42	-39.84	-57.31	-72.04	-59.26
5600	-14.07	-15.71	-18.19	-15.44	-20.30	-52.32	-37.82	-54.97	-67.54	-57.06
5700	-11.45	-14.66	-17.91	-15.71	-20.72	-51.77	-37.77	-55.11	-68.79	-56.78
5800	-12.80	-16.16	-18.88	-16.50	-21.60	-52.13	-39.84	-61.02	-66.80	-56.66
5900	-15.21	-17.55	-19.23	-16.14	-20.20	-50.25	-36.93	-54.02	-64.47	-55.14
6000	-19.65	-20.11	-20.16	-16.34	-20.05	-51.18	-37.19	-57.21	-61.48	-55.22
6100	-16.23	-17.86	-19.34	-15.97	-19.95	-53.39	-39.77	-57.53	-59.91	-54.85
6200	-19.96	-18.41	-19.10	-15.82	-19.81	-50.94	-36.52	-55.37	-60.31	-54.62
6300	-15.68	-17.32	-18.68	-15.96	-20.13	-47.89	-37.63	-55.47	-60.80	-54.54
6400	-13.72	-16.00	-18.26	-16.13	-20.51	-51.47	-37.96	-57.79	-61.30	-55.26
6500	-18.75	-18.32	-18.13	-16.26	-20.58	-52.37	-35.32	-57.57	-60.69	-54.59
6600	-18.50	-17.85	-17.92	-16.76	-20.86	-54.13	-38.79	-59.21	-56.73	-53.68
6700	-15.61	-16.43	-17.01	-16.30	-20.28	-52.74	-41.85	-58.46	-72.09	-53.74
6800	-13.90	-15.44	-16.64	-16.32	-20.75	-50.82	-40.03	-56.50	-62.11	-54.52
6900	-13.48	-15.21	-15.91	-16.05	-20.42	-50.54	-37.52	-53.57	-66.01	-55.24
7000	-16.43	-15.93	-15.99	-16.32	-20.50	-50.84	-35.56	-57.70	-66.14	-55.92
7100	-14.47	-17.10	-19.70	-20.99	-24.90	-50.43	-35.70	-57.35	-69.34	-57.34
7200	-14.43	-17.61	-19.44	-20.48	-25.04	-47.46	-34.68	-53.92	-69.36	-60.86
7300	-19.37	-22.42	-20.90	-21.40	-26.31	-50.12	-32.66	-55.30	-71.60	-61.23
7400	-26.80	-25.19	-24.20	-24.76	-30.27	-49.77	-36.78	-57.82	-70.89	-64.83
7500	-28.21	-30.56	-29.55	-28.38	-36.18	-47.27	-39.46	-55.80	-71.06	-67.72
7600	-46.39	-36.20	-33.63	-32.08	-40.69	-46.28	-35.41	-58.94	-75.34	-75.84
7700	-28.33	-31.79	-37.65	-37.37	-46.57	-51.76	-34.00	-56.38	-75.14	-82.45
7800	-32.81	-38.54	-41.60	-42.16	-52.13	-45.74	-36.08	-53.14	-72.61	-82.15
7900	-38.52	-40.04	-50.41	-49.35	-58.02	-50.23	-35.83	-53.44	-74.34	-83.22
8000	-46.85	-39.06	-55.37	-56.56	-64.16	-48.50	-35.52	-55.04	-71.14	-81.67
8100	-53.49	-38.75	-57.54	-59.41	-66.19	-45.71	-36.91	-51.36	-73.25	-81.76
8200	-47.64	-37.99	-52.94	-57.37	-63.07	-45.19	-35.87	-54.11	-70.64	-82.91
8300	-44.80	-38.68	-53.13	-54.32	-61.53	-45.01	-35.13	-50.09	-70.09	-81.42
8400	-51.48	-38.50	-54.17	-53.43	-61.05	-45.48	-32.83	-53.60	-70.18	-84.20
8500	-44.62	-39.74	-51.04	-53.06	-62.16	-44.68	-31.07	-49.31	-71.46	-86.50
8600	-49.68	-40.15	-51.50	-52.12	-62.85	-47.63	-30.09	-52.21	-71.65	-87.40
8700	-53.55	-41.75	-51.75	-51.70	-64.27	-45.52	-32.30	-52.88	-72.79	-90.37
8750	-48.85	-40.23	-52.35	-51.60	-63.99	-43.93	-32.09	-50.59	-71.35	-88.61
8800	-44.14	-38.70	-52.95	-51.51	-63.71	-42.33	-31.87	-48.30	-69.91	-86.85
8850	-44.79	-38.63	-51.14	-51.60	-63.04	--	--	--	--	--
8900	-45.43	-38.56	-49.32	-51.70	-62.37	--	--	--	--	--
8950	-44.81	-38.78	-49.76	-51.45	-61.78	--	--	--	--	--
9000	-44.20	-39.01	-50.20	-51.20	-61.20	--	--	--	--	--

Signal Generator

SSG-5N9G-RC

Typical Performance Data

Test Conditions: @ Temperature = 50°C.

Freq. (MHz)	Phase Noise vs. Output Frequency (dBc / Hz)				
	1 kHz	10 kHz	100 kHz	1 MHz	10 MHz
5000	-97.91	-108.99	-116.54	-124.28	-134.96
5050	-97.67	-108.96	-116.39	-124.60	-134.99
5100	-97.43	-108.92	-116.24	-124.91	-135.02
5150	-97.46	-108.82	-116.22	-124.68	-134.98
5200	-97.48	-108.72	-116.20	-124.44	-134.93
5300	-97.89	-108.33	-116.06	-123.09	-135.58
5400	-97.15	-108.37	-115.67	-125.16	-135.38
5500	-97.18	-108.00	-115.66	-124.14	-135.75
5600	-97.19	-107.90	-115.52	-124.22	-135.45
5700	-96.82	-107.72	-115.32	-122.07	-135.98
5800	-96.80	-107.60	-115.38	-122.52	-136.09
5900	-96.66	-107.62	-115.15	-121.24	-135.70
6000	-96.71	-107.38	-115.02	-119.94	-135.34
6100	-96.04	-106.98	-114.98	-120.06	-135.91
6200	-95.97	-107.39	-115.16	-120.13	-135.85
6300	-95.95	-107.15	-114.61	-118.22	-135.76
6400	-95.69	-107.01	-115.02	-118.59	-135.32
6500	-95.65	-106.84	-114.58	-118.79	-136.11
6600	-95.50	-106.80	-114.46	-118.53	-136.18
6700	-95.52	-106.68	-114.25	-119.44	-135.90
6800	-95.24	-106.31	-114.08	-119.55	-136.01
6900	-95.49	-106.31	-113.50	-119.50	-135.75
7000	-95.18	-106.01	-113.76	-120.09	-135.92
7100	-94.67	-105.93	-113.81	-119.36	-135.54
7200	-95.17	-105.85	-113.63	-118.70	-135.82
7300	-94.77	-105.63	-113.30	-118.82	-135.36
7400	-94.67	-105.51	-113.34	-116.95	-135.88
7500	-94.51	-105.53	-112.91	-123.08	-135.90
7600	-94.45	-105.57	-113.11	-121.77	-136.55
7700	-94.41	-105.37	-112.56	-121.66	-136.49
7800	-94.34	-105.33	-112.90	-121.53	-135.58
7900	-94.43	-104.97	-112.69	-120.22	-135.87
8000	-94.19	-105.13	-112.99	-120.05	-136.11
8100	-93.49	-104.70	-112.44	-119.61	-136.50
8200	-93.43	-104.89	-112.38	-119.47	-135.33
8300	-93.57	-104.65	-112.18	-119.35	-136.18
8400	-93.74	-104.70	-112.28	-118.45	-136.07
8500	-93.47	-104.61	-112.00	-122.15	-136.16
8600	-93.04	-104.39	-111.58	-122.51	-135.69
8700	-93.48	-104.21	-111.49	-121.15	-135.98
8750	-93.12	-104.14	-111.45	-120.62	-135.73
8800	-92.76	-104.06	-111.41	-120.09	-135.48
8850	-93.03	-103.97	-111.36	-120.48	-135.39
8900	-93.29	-103.88	-111.31	-120.86	-135.30
8950	-93.15	-103.86	-111.33	-120.01	-135.45
9000	-93.00	-103.83	-111.35	-119.15	-135.59

Freq. (MHz)	Power (dBM) Max
5000	24.37
5050	24.46
5100	24.55
5150	24.59
5200	24.63
5300	24.48
5400	24.22
5500	24.13
5600	23.87
5700	23.53
5800	23.38
5900	23.21
6000	23.03
6100	23.00
6200	22.95
6300	22.92
6400	23.05
6500	23.22
6600	23.43
6700	23.77
6800	23.99
6900	24.01
7000	24.06
7100	24.20
7200	24.18
7300	24.19
7400	24.20
7500	24.22
7600	23.99
7700	23.78
7800	23.61
7900	23.52
8000	23.41
8100	23.37
8200	23.35
8300	23.19
8400	23.09
8500	23.10
8600	23.05
8700	22.99
8750	23.04
8800	23.09
8850	23.12
8900	23.15
8950	23.16
9000	23.17

Signal Generator

SSG-5N9G-RC

Typical Performance Data

Test Conditions: @ Temperature = 50°C.

Freq. Offsets (kHz)	Phase Noise vs. Offset Frequency (dBc / Hz)				
	5.0 GHz	6.0 GHz	7.0 GHz	8.0 GHz	9.0 GHz
1	-97.91	-96.71	-95.18	-94.19	-93.00
10	-108.99	-107.38	-106.01	-105.13	-103.83
100	-116.54	-115.02	-113.76	-112.99	-111.35
1000	-124.28	-119.94	-120.09	-120.05	-119.15
10000	-134.96	-135.34	-135.92	-136.11	-135.59

Freq. (MHz)	Spurious (dBc)
5000	-66.32
5050	-66.48
5100	-66.64
5150	-66.80
5200	-66.96
5300	-67.00
5400	-66.76
5500	-66.52
5600	-66.69
5700	-66.86
5800	-66.82
5900	-66.57
6000	-66.31
6100	-66.20
6200	-66.09
6300	-66.45
6400	-67.27
6500	-68.09
6600	-67.62
6700	-67.15
6800	-67.07
6900	-67.40
7000	-67.74
7100	-67.20
7200	-66.66
7300	-66.30
7400	-66.11
7500	-65.92
7600	-66.13
7700	-66.34
7800	-66.40
7900	-66.33
8000	-66.25
8100	-66.58
8200	-66.90
8300	-66.76
8400	-66.16
8500	-65.55
8600	-65.67
8700	-65.80
8750	-65.86
8800	-66.00
8850	-66.15
8900	-66.30
8950	-66.44
9000	-66.59

Note: Spurious was measured in offsets of 100 kHz to 150 MHz.

Signal Generator

Typical Performance Graphs

Test Conditions: @ Temperature = 0°C.







Typical Performance Graphs

Test Conditions: @ Temperature = 0°C.







Typical Performance Graphs

Test Conditions: @ Temperature = 0°C.







Typical Performance Graphs

Test Conditions: @ Temperature = 25°C.







Typical Performance Graphs

Test Conditions: @ Temperature = 25°C.







Typical Performance Graphs

Test Conditions: @ Temperature = 25°C.







Typical Performance Graphs

Test Conditions: @ Temperature = 50°C.







Typical Performance Graphs

Test Conditions: @ Temperature = 50°C.







Typical Performance Graphs

Test Conditions: @ Temperature = 50°C.







Case Style SL

Outline Dimensions SL3643



NOTES:
1. Case material: Aluminum alloy.
2. Case Finish: Nickel Plate.
3. Dimensions are in inches [mm]. Tolerances 2 Pl. ±.03 inch; 3 Pl. ±.015 inches.
4. Weight: 500 grams
5. Marking may contain other features or characters for internal lot control.

Mini-Circuits

www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

This document and its contents are the property of Mini-Circuits

Mini-Circuits

Environmental Specifications **ENV55**

All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-0° to 50° C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-20° to 60° C Ambient Environment	Individual Model Data Sheet
Operating and Storage Humidity	5% to 85% RH (non-condensing)	Ambient
Bench Handling Test	Bench Top Tip 45° & Drop	MIL-PRF-28800F
Transit Drop Test	Free Fall Drop, 20 cm (7.9 inches)	MIL-PRF-28800F Class 3

This document and its contents are the property of Mini-Circuits