



Mini-Circuits

MMIC SURFACE MOUNT


Low Noise Amplifier

TSS1-23ULN+

50Ω 10 to 2000 MHz Shutdown Feature

THE BIG DEAL

- Low Noise Figure, Typ. 0.4 dB
- High Gain, Typ. 20.1 dB
- High OIP3, Typ. +37.2 dBm
- Fast Shutdown Feature, 9.1 ns
- Single Supply Voltage, +5 V at 72.5 mA
- 1.5×1.5 mm 6-Lead QFN-style Package




Generic photo used for illustration purposes only

APPLICATIONS

- Cellular Infrastructure
- Satellite Communications
- Radar, EW, and ECM Defense Systems

FUNCTIONAL DIAGRAM (TOP VIEW)



PRODUCT OVERVIEW

The TSS1-23ULN+ is a pHEMT-based wideband, ultra-low noise MMIC amplifier with high P1dB, high IP3, and voltage-controlled shutdown capability. Operating from 10 to 2000 MHz, this amplifier features typical 0.4 dB noise figure, 20.1 dB gain, +20.6 dBm P1dB, and +37.2 dBm OIP3. This combination of characteristics makes it ideal for sensitive receiver applications. TSS1-23ULN+ operates on a single +5 V supply and comes in a small, low profile, 1.5×1.5 mm QFN-style package for ease of integration into dense circuit board layouts.

KEY FEATURES

Features	Advantages
Ultra-Low Noise Figure, Typ. 0.4 dB	Operating from a single supply, this ultra-low noise MMIC enables low system noise figure performance, without the need for complicated discrete-based solutions.
High Gain, Typ. 20.1 dB	The MMIC amplifier's high gain enables fewer system components in receiver signal chains.
Shutdown Feature	A voltage-controlled shutdown feature allows the part to be quickly disabled to conserve power when not in use.
High Dynamic Range • Gain, Typ. 20.1 dB • OIP3, Typ. +37.2 dBm • P1dB, Typ. +20.6 dBm	The MMIC amplifier's unique combination of low noise figure, high gain, high P1dB, and high OIP3 enables optimum performance in sensitive high dynamic range receivers.
1.5×1.5 mm 6-Lead QFN-Style Package	Small footprint saves space in dense layouts while providing low inductance, repeatable transitions, and excellent thermal contact to the PCB. Industry standard packaging allows for ease of assembly in high volume manufacturing processes.

Mini-Circuits

www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

REV. OR
ECO-030097
TSS1-23ULN+
MCL NY
260518

PAGE 1 OF 16



MMIC SURFACE MOUNT

Low Noise Amplifier

TSS1-23ULN+

Mini-Circuits

50Ω 10 to 2000 MHz Shutdown Feature

ELECTRICAL SPECIFICATIONS¹ AT +25 °C AND $Z_0 = 50\Omega$ UNLESS NOTED OTHERWISE

Parameter	Condition (MHz)	Amplifier - ON $V_{DD} = +5\text{ V}$ ($V_{SHUTDOWN} = 0\text{ V}$)			Amplifier - ON $V_{DD} = +3\text{ V}$ ($V_{SHUTDOWN} = 0\text{ V}$)	Amplifier - OFF ² $V_{DD} = +5\text{ V}$ ($V_{SHUTDOWN} = +5\text{ V}$)	Units
		Min.	Typ.	Max.	Typ.	Typ.	
Frequency Range		10		2000	10-2000	10-2000	MHz
Gain	10	27.8	29.1		27.4	-21.7	dB
	500	23.6	24.7		23.4	-31.0	
	1000	19.0	20.1		19.1	-34.0	
	1500	15.9	17.1		16.1	-31.9	
	2000	13.6	14.8		13.8	-26.1	
Input Return Loss	10		8		7		dB
	500		12		9		
	1000		14		12		
	1500		16		13		
	2000		16		14		
Output Return Loss	10		20		18		dB
	500		14		15		
	1000		13		14		
	1500		12		14		
	2000		12		14		
Isolation	10-2000		27.3		26.2	31.2	dB
Output Power at 1 dB Compression (P1dB)	10		+22.4		+16.6		dBm
	500		+20.9		+15.8		
	1000		+20.6		+16.0		
	1500		+20.9		+16.8		
	2000		+20.1		+16.0		
Output Third-Order Intercept Point ($P_{OUT} = +4\text{ dBm/Tone}$)	10		+33.4		+28.0		dBm
	500		+35.7		+27.0		
	1000		+37.2		+27.4		
	1500		+37.0		+27.9		
	2000		+38.5		+28.1		
Noise Figure ³	10		1.0		0.9		dB
	500		0.4		0.4		
	1000		0.4		0.4		
	1500		0.4		0.4		
	2000		0.5		0.5		
ON Time (50% V_{CTRL} to 90% RF)			16.2				ns
RISE Time (10% RF to 90% RF)			6.7				ns
FALL Time (90% RF to 10% RF)			6.1				ns
OFF Time (50% V_{CTRL} to 10% RF)			9.1				ns
Device Operating Voltage (V_{DD})		+4.75	+5	+5.25	+3	+5	V
Device Operating Current (I_{DD}) ⁴			72.5		38	3	mA
Device Shutdown Voltage ($V_{SHUTDOWN}$)			0		0	+5	V
Device Shutdown Current ($I_{SHUTDOWN}$)			0.02		0.01	137	μA
Device Current Variation vs. Temperature ⁵			0.0004		0.0004		mA/°C
Device Current Variation vs. Voltage ⁶			0.0174		0.0174		mA/mV

1. Tested in Mini-Circuits Characterization Test/Evaluation Board TB-TSS1-23ULNC+. See Figure 2. Board loss de-embedded to the device.

2. Performance is comparable when $V_{DD} = +5\text{ V}$ or $+3\text{ V}$ when amplifier is OFF.

3. Typical value verified and set by averaging performance across multiple measurement setups.

4. Current at $P_{IN} = -25\text{ dBm}$. Increases to 90 mA at P1dB. I_{ADJ} is left floating to achieve device nominal current.

5. (Current at +105 °C - Current at -45 °C) / (+150 °C)

6. (Current at +5.25 V - Current at +4.75 V) / (+0.5 V)







TYPICAL PERFORMANCE GRAPHS

Note: The following data was taken on the Mini-Circuits Characterization Test Board TB-TSS1-23ULNC+ (Figure 2). All data taken at nominal condition of $V_{DD} = +5$ V and at $V_{SHUTDOWN} = 0$ V unless noted otherwise.


GAIN vs. TEMPERATURE
 $P_{IN} = -25$ dBm




GAIN vs. DEVICE VOLTAGE (V_{DD})
 $P_{IN} = -25$ dBm, TEMPERATURE = +25°C




ISOLATION vs. TEMPERATURE
 $P_{IN} = -25$ dBm




ISOLATION vs. DEVICE VOLTAGE (V_{DD})
 $P_{IN} = -25$ dBm, TEMPERATURE = +25°C



INPUT RETURN LOSS vs. TEMPERATURE
 $P_{IN} = -25$ dBm









INPUT RETURN LOSS vs. DEVICE VOLTAGE (V_{DD})
 $P_{IN} = -25$ dBm, TEMPERATURE = +25°C





TYPICAL PERFORMANCE GRAPHS







Note: The following data was taken on the Mini-Circuits Characterization Test Board TB-TSS1-23ULNC+ (Figure 2). All data taken at nominal condition of $V_{DD} = +5$ V and at $V_{SHUTDOWN} = 0$ V unless noted otherwise.





TYPICAL PERFORMANCE GRAPHS







Note: The following data was taken on the Mini-Circuits Characterization Test Board TB-TSS1-23ULNC+ (Figure 2). All data taken at nominal condition of $V_{DD} = +5$ V and at $V_{SHUTDOWN} = 0$ V unless noted otherwise.





TYPICAL LOW VOLTAGE PERFORMANCE GRAPHS

Note: The following data was taken on the Mini-Circuits Characterization Test Board TB-TSS1-23ULNC+ (Figure 2). All data taken at $V_{\text{SHUTDOWN}} = 0$ V unless noted otherwise.





MMIC SURFACE MOUNT


Low Noise Amplifier

TSS1-23ULN+

50Ω 10 to 2000 MHz Shutdown Feature







TYPICAL LOW VOLTAGE PERFORMANCE GRAPHS

Note: The following data was taken on the Mini-Circuits Characterization Test Board TB-TSS1-23ULNC+ (Figure 2). All data taken at $V_{\text{SHUTDOWN}} = 0 \text{ V}$ unless noted otherwise.



TYPICAL CURRENT ADJUST (I_{ADJ}) PERFORMANCE GRAPHS

Note: The following data was taken on the Mini-Circuits Characterization Test Board TB-TSS1-23ULNC+ by varying R_{IADJ} (Figure 3). All data taken at nominal condition of $V_{DD} = +5\text{ V}$ and at $V_{SHUTDOWN} = 0\text{ V}$ unless noted otherwise.





MMIC SURFACE MOUNT

Low Noise Amplifier

TSS1-23ULN+


Mini-Circuits

50Ω 10 to 2000 MHz Shutdown Feature

TYPICAL CURRENT ADJUST (I_{ADJ}) PERFORMANCE GRAPHS

Note: The following data was taken on the Mini-Circuits Characterization Test Board TB-TSS1-23ULNC+ by varying R_{IADJ} (Figure 3). All data taken at nominal condition of $V_{DD} = +5$ V and at $V_{SHUTDOWN} = 0$ V unless noted otherwise.

NOISE FIGURE vs. DEVICE CURRENT (I_{DD})
TEMPERATURE = +25°C





MMIC SURFACE MOUNT

Low Noise Amplifier

TSS1-23ULN+

Mini-Circuits

50Ω 10 to 2000 MHz Shutdown Feature

ABSOLUTE MAXIMUM RATINGS⁷

Parameter	Ratings
Operating Temperature	-45 °C to +105 °C
Storage Temperature	-65 °C to +150 °C
Total Power Dissipation	1.34 W
Junction Temperature ⁸	+150°C
Input Power (CW) $V_{DD} = +5\text{ V}$ & $V_{SHUTDOWN} = 0\text{ V}$ $V_{DD} = +3\text{ V}$ & $V_{SHUTDOWN} = 0\text{ V}$	+21 dBm +21 dBm
DC Voltage on RF-OUT & V_{DD} $V_{SHUTDOWN} = 0\text{ V}$ $V_{SHUTDOWN} = +5\text{ V}$	+10 V +10 V
DC Voltage on RF-IN $V_{SHUTDOWN} = 0\text{ V}$ $V_{SHUTDOWN} = +5\text{ V}$	+1 V +1 V
DC Voltage on $V_{SHUTDOWN}$ $V_{DD} = +5\text{ V}$ $V_{DD} = +3\text{ V}$	+10 V +10 V
DC Current on RF-OUT & V_{DD} $V_{SHUTDOWN} = 0\text{ V}$ $V_{SHUTDOWN} = +5\text{ V}$	100 mA 10 mA
DC Current $V_{SHUTDOWN}$ $V_{DD} = +5\text{ V}$ $V_{DD} = +3\text{ V}$	10 mA 10 mA

7. Permanent damage may occur if any of these limits are exceeded. Maximum ratings are not intended for continuous normal operation.

8. Peak temperature on top of Die.

POWER ON / POWER OFF LOGIC

Amplifier State	V_{DD}			$V_{SHUTDOWN}$		
	Min	Typ.	Max	Min	Typ.	Max
Amplifier - ON ($V_{DD} = +5\text{ V}$)	+2.7 V	+5 V	+5.25 V	0 V	0 V	+1.3 V
Amplifier - OFF ($V_{DD} = +5\text{ V}$)				+1.4 V	+5 V	+5.25 V
Amplifier - ON ($V_{DD} = +3\text{ V}$)	+2.7 V	+3 V	+5.25 V	0 V	0 V	+1.3 V
Amplifier - OFF ($V_{DD} = +3\text{ V}$)				+1.4 V	+3 V	+5.25 V

THERMAL RESISTANCE

Parameter	Ratings
Thermal Resistance (Θ_{JC}) ⁹	33.6 °C/W

9. Θ_{JC} = (Hot Spot Temperature on Die - Temperature at Ground Lead)/Dissipated Power

ESD RATING

	Class	Voltage Range	Reference Standard
HBM	1A	250 V to < 500 V	ANSI/ESDA/JEDEC JS-001-2023
CDM	C3	> 1000 V	ANSI/ESDA/JEDEC JS-002-2022



ESD HANDLING PRECAUTION: This device is designed to be Class 1A for HBM. Static charges may easily produce potentials higher than this with improper handling and can discharge into DUT and damage it. As a preventive measure Industry standard ESD handling precautions should be used at all times to protect the device from ESD damage.

MSL RATING

Moisture Sensitivity: MSL1 in accordance with IPC/JEDEC J-STD-020E /JEDEC J-STD-033C

Mini-Circuits



MMIC SURFACE MOUNT

Low Noise Amplifier

TSS1-23ULN+

50Ω 10 to 2000 MHz Shutdown Feature

FUNCTIONAL DIAGRAM




Figure 1. TSS1-23ULN+ Functional Diagram

PAD DESCRIPTION

Function	Pad Number	Description (Refer to Figure 2)
RF-OUT & V _{DD}	5	RF-OUT & V _{DD} Pad connects to RF-Output port and voltage input port, V _{DD} .
V _{SHUTDOWN}	4	DC Input Pad connects to voltage input port, V _{SHUTDOWN} .
RF-IN	2	RF-IN Pad connects to RF-Input port.
I _{ADJ}	1	DC Pad used to adjust current by adjusting R _{IADJ} . For normal operation I _{ADJ} should be left unconnected.
NC	3 & 6	Not used internally. Connected to ground on test board.
GND	Paddle	Connects to ground.

EVALUATION BOARD




Figure 2. TSS1-23ULN+ Evaluation and Application Circuit

Component	Size	Value	Part Number	Manufacturer
R1-R4	0402	0Ω	RK73Z1ETTP	KOA Speer
R _{IADJ}	0402	DNI	N/A	N/A

Electrical Parameters and Conditions

Gain, Return Loss, Output Power at 1 dB Compression (P1dB), Output IP3 (OIP3), and Noise Figure measured using N5242A PNA-X microwave network analyzer.

Conditions:

- Gain and Return Loss: P_{IN} = -25 dBm
- Output IP3 (OIP3): Two tones, spaced 1 MHz apart, +4 dBm/tone at output.

Power ON/Power OFF Sequence:

Caution: Permanent damage to the device will occur if the Power ON and Power OFF sequences are not followed.

POWER ON:


- Set V_{SHUTDOWN} = 0 V for ON mode or V_{SHUTDOWN} = +5 V for OFF mode.
- Set V_{DD} = +5 V.
- Turn on V_{SHUTDOWN}.
- Turn on V_{DD}.
- Apply RF Signal.

POWER OFF:

- Turn off RF signal.
- Turn off V_{DD}.
- Turn off V_{SHUTDOWN}.



APPLICATION CIRCUIT - CURRENT ADJUST

**Electrical Parameters and Conditions**

Gain, Return Loss, Output Power at 1 dB Compression (P1dB), Output IP3 (OIP3), and Noise Figure measured using N5242A PNA-X microwave network analyzer.


Conditions:

1. Gain and Return Loss: $P_{IN} = -25$ dBm
2. Output IP3 (OIP3): Two tones, spaced 1 MHz apart, +4 dBm/tone at output.

Figure 3. TSS1-23ULN+ Current Adjust Application Circuit

Component	Size	Value	Part Number	Manufacturer
R1-R4	0402	0Ω	RK73Z1ETTP	KOA Speer
RIADJ	0402	200Ω	RK73H1ETTP2000F	KOA Speer
		430Ω	RK73H1ETTP4300F	
		1.5kΩ	RK73H1ETTP1501F	

APPLICATION CIRCUIT - NARROWBAND MATCH

**Electrical Parameters and Conditions**

Gain, Return Loss, Output Power at 1 dB Compression (P1dB), Output IP3 (OIP3), and Noise Figure measured using N5242A PNA-X microwave network analyzer.

Conditions:

1. Gain and Return Loss: $P_{IN} = -25$ dBm
2. Output IP3 (OIP3): Two tones, spaced 1 MHz apart, +4 dBm/tone at output.







Figure 4. TSS1-23ULN+ 700-1000 MHz Application Circuit

Component	Size	Value	Part Number	Manufacturer
R1-R2	0402	0Ω	RK73Z1ETTP	KOA Speer
C1	0402	47 pF	GRM1555C1H470JA01D	Murata
C2	0402	4.7 pF	GRM1555C1H4R7CA01D	Murata
C3	0402	0.1 μF	GRM155R71H104KE14J	Murata
L1	0402	22 nH	LQW15AN22NG00D	Murata



TYPICAL MATCHING TEST BOARD PERFORMANCE GRAPHS

Note: The following data was taken on the Mini-Circuits 700-1000 MHz Matched Characterization Test Board (Figure 4). All data taken at nominal condition of $V_{DD} = +5$ V and at $V_{SHUTDOWN} = 0$ V unless noted otherwise.





MMIC SURFACE MOUNT


Low Noise Amplifier

TSS1-23ULN+

50 Ω 10 to 2000 MHz Shutdown Feature

TYPICAL MATCHING TEST BOARD PERFORMANCE GRAPHS

Note: The following data was taken on the Mini-Circuits 700-1000 MHz Matched Characterization Test Board (Figure 4). All data taken at nominal condition of $V_{DD} = +5$ V and at $V_{SHUTDOWN} = 0$ V unless noted otherwise.





MMIC SURFACE MOUNT


Low Noise Amplifier

TSS1-23ULN+


Mini-Circuits

50Ω 10 to 2000 MHz Shutdown Feature


CASE STYLE DRAWING



TOP VIEW




SIDE VIEW



BOTTOM VIEW

PCB Land Pattern



Suggested Layout,
Tolerance to be within ± 0.050 mm


NOTES:

1. DENOTES METALLIZATION

Weight: 0.0036 grams

Dimensions are in mm [inches]. Tolerances: 2Pl. ± 0.05 mm [0.002 inches].

PRODUCT MARKING



Marking may contain other features or characters for internal lot control.

Mini-Circuits

www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

PAGE 15 OF 16



MMIC SURFACE MOUNT

Low Noise Amplifier

TSS1-23ULN+

Mini-Circuits

50Ω 10 to 2000 MHz Shutdown Feature

ADDITIONAL DETAILED INFORMATION IS AVAILABLE ON OUR DASHBOARD

[CLICK HERE](#)

Performance Data & Graphs	Data Graphs S-Parameter (S2P Files) Data Set (.zip file)
Case Style	KC3011. Plastic package, exposed paddle, Lead Finish: Nickel Palladium Gold
RoHS Status	Compliant
Tape & Reel Standard Quantities Available on Reel	F66 7" Reels with 20, 50, 100, 200, 500, 1000, 2000, or 3000 devices
Suggested Layout for PCB Design	PL-862
Evaluation Board	TB-TSS1-23ULNC+ Gerber File
Environmental Ratings	ENV08T1

NOTES

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits' standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the standard terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/terms/viewterm.html



Typical Performance Data

NOTE: Use PDF Bookmarks to view DATA at required conditions

Definitions:

Input Return Loss = S11 (dB)

Gain = S21 (dB)

Isolation = S12 (dB)

Output Return Loss = S22 (dB)

TEST CONDITIONS: $V_{DD} = +2.7\text{ V}$, $V_{SHUTDOWN} = 0\text{ V}$, $I_{DD} = 32\text{ mA}$, $I_{SHUTDOWN} = 0.0014\text{ }\mu\text{A}$ @ Temperature = +25°C

FREQ	Gain	Isolation	Input Return Loss	Output Return Loss	Stability		1dB Comp. Output	Noise Figure	IP-3 Output $P_{OUT} = +4$ dBm/Tone
(MHz)	(dB)	(dB)	(dB)	(dB)	K	Measure	(dBm)	(dB)	(dBm)
10	26.9	-34.2	-6.3	-16.9	1.1	1.0	15.2	0.9	26.5
20	26.9	-33.4	-6.2	-17.4	1.1	0.9	14.2	0.4	25.8
30	26.9	-33.5	-6.4	-16.8	1.1	0.9	14.1	0.6	25.3
40	26.8	-33.3	-6.4	-16.2	1.1	0.9	14.1	0.4	25.3
50	26.8	-33.1	-6.3	-16.2	1.1	0.9	14.2	0.4	25.5
60	26.7	-32.8	-6.4	-15.9	1.1	0.9	14.1	0.4	25.8
70	26.7	-33.1	-6.4	-15.8	1.1	0.9	14.1	0.6	25.3
80	26.7	-32.6	-6.4	-15.8	1.1	0.9	14.2	0.5	25.0
90	26.6	-32.6	-6.4	-15.4	1.1	0.9	14.1	0.5	24.8
100	26.6	-32.9	-6.5	-15.4	1.1	0.9	14.2	0.5	25.1
200	26.0	-32.0	-6.9	-15.0	1.1	0.9	14.2	0.4	24.9
250	25.5	-31.6	-7.2	-14.9	1.1	0.9	14.0	0.4	25.1
300	25.1	-31.2	-7.5	-14.9	1.1	0.9	14.1	0.4	24.9
350	24.6	-30.6	-7.9	-14.8	1.1	0.8	14.4	0.4	24.9
400	24.1	-30.3	-8.2	-14.9	1.1	0.9	14.4	0.4	25.0
450	23.5	-29.7	-8.6	-15.1	1.1	0.9	14.1	0.4	25.1
500	23.1	-29.3	-8.9	-15.1	1.1	0.9	14.4	0.4	25.1
550	22.6	-28.8	-9.2	-15.2	1.1	0.9	14.5	0.4	25.3
600	22.1	-28.4	-9.5	-15.2	1.1	0.9	14.3	0.4	25.3
650	21.6	-27.9	-9.7	-15.2	1.1	0.9	14.6	0.4	25.2
700	21.2	-27.6	-10.0	-15.3	1.2	0.9	14.6	0.4	25.2
750	20.7	-27.0	-10.1	-15.3	1.1	0.9	14.8	0.4	25.1
800	20.3	-26.8	-10.4	-15.3	1.2	0.9	14.5	0.4	25.2
850	19.9	-26.4	-10.6	-15.3	1.2	0.9	14.7	0.5	25.4
900	19.5	-26.0	-10.7	-15.3	1.2	0.9	14.7	0.5	25.4
950	19.2	-25.7	-10.9	-15.3	1.2	0.9	14.9	0.5	25.3
1000	18.8	-25.4	-11.0	-15.4	1.2	0.9	14.9	0.4	25.5
1050	18.4	-25.0	-11.1	-15.4	1.2	0.9	15.1	0.4	25.4
1100	18.1	-24.7	-11.2	-15.4	1.2	0.9	15.0	0.4	25.1
1150	17.8	-24.4	-11.3	-15.5	1.2	0.9	15.1	0.5	25.5
1200	17.5	-24.1	-11.4	-15.4	1.2	0.9	15.1	0.4	25.3
1250	17.1	-23.8	-11.6	-15.5	1.2	0.9	15.2	0.4	25.4
1300	16.9	-23.5	-11.6	-15.5	1.2	0.9	15.4	0.4	25.4
1350	16.6	-23.3	-11.7	-15.5	1.2	0.9	15.1	0.5	25.5
1400	16.3	-23.1	-11.7	-15.5	1.2	0.9	15.0	0.5	25.7
1450	16.0	-22.8	-11.8	-15.6	1.2	0.9	15.4	0.4	25.6
1500	15.8	-22.5	-11.8	-15.6	1.2	0.9	15.5	0.5	25.8
1550	15.5	-22.3	-11.9	-15.6	1.2	0.9	14.8	0.4	25.8
1600	15.2	-22.0	-11.9	-15.7	1.2	0.9	15.4	0.5	25.8
1650	15.0	-21.8	-11.9	-15.7	1.2	0.9	15.4	0.4	26.0
1700	14.8	-21.6	-11.9	-15.7	1.2	0.9	15.7	0.5	26.1
1750	14.5	-21.4	-12.0	-15.9	1.2	0.9	15.3	0.5	25.9
1800	14.3	-21.1	-12.0	-15.9	1.2	0.9	15.5	0.5	25.8
1850	14.1	-21.0	-12.0	-15.9	1.2	0.9	15.2	0.5	26.1
1900	13.9	-20.7	-12.0	-16.0	1.2	0.9	15.5	0.5	26.1
1950	13.7	-20.5	-12.0	-16.1	1.2	0.9	15.4	0.5	25.8
2000	13.5	-20.4	-12.0	-16.2	1.2	0.9	15.0	0.5	26.1
2100	13.1	-20.0	-11.9	-16.3	1.2	0.9	15.0	0.6	26.0
2200	12.7	-19.6	-11.9	-16.6	1.2	0.9	15.4	0.6	26.0
2300	12.4	-19.3	-11.7	-16.8	1.2	0.9	15.2	0.6	25.9
2400	12.0	-19.0	-11.6	-17.1	1.2	0.9	15.4	0.6	25.6
2500	11.7	-18.7	-11.5	-17.5	1.2	0.9	15.3	0.6	25.6
2600	11.4	-18.4	-11.3	-17.9	1.2	0.9	15.4	0.7	25.5
2700	11.1	-18.1	-11.1	-18.4	1.2	0.9	15.0	0.7	25.7
2800	10.7	-17.8	-10.9	-19.1	1.2	0.9	15.2	0.8	25.5
2900	10.4	-17.6	-10.5	-20.1	1.2	0.9	14.9	0.8	25.5
3000	10.2	-17.3	-10.3	-21.4	1.2	0.9	15.2	0.8	25.7
3100	9.9	-17.1	-10.2	-22.7	1.2	0.9	15.4	0.9	25.8
3200	9.7	-16.8	-10.0	-24.1	1.2	0.9	15.5	0.8	25.7
3300	9.4	-16.7	-9.6	-26.2	1.3	0.9	15.4	1.0	25.9
3400	9.1	-16.5	-9.2	-28.9	1.3	1.0	15.4	1.0	25.7
3500	8.9	-16.2	-8.9	-31.6	1.2	1.0	15.7	1.1	25.9
3600	8.7	-16.0	-8.7	-33.1	1.2	1.0	15.8	1.0	26.4
3700	8.5	-15.8	-8.4	-31.9	1.2	1.0	15.2	1.0	25.8
3800	8.3	-15.6	-8.2	-29.6	1.2	1.0	15.8	1.1	26.0
3900	8.1	-15.4	-8.0	-27.0	1.2	1.0	15.5	1.1	25.8
4000	7.8	-15.3	-7.8	-25.1	1.2	1.0	15.6	1.1	25.9

*Note: Tested with $I_{ADJ} = \text{OPEN}$.

Typical Performance Data

NOTE: Use PDF Bookmarks to view DATA at required conditions

Definitions:

Input Return Loss = S11 (dB)

Gain = S21 (dB)

Isolation = S12 (dB)

Output Return Loss = S22 (dB)

TEST CONDITIONS: $V_{DD} = +3\text{ V}$, $V_{SHUTDOWN} = 0\text{ V}$, $I_{DD} = 38\text{ mA}$, $I_{SHUTDOWN} = 0.0014\text{ }\mu\text{A}$ @ Temperature = +25°C

FREQ	Gain	Isolation	Input Return Loss	Output Return Loss	Stability		1dB Comp. Output	Noise Figure	IP-3 Output $P_{OUT} = +4$ dBm/Tone
(MHz)	(dB)	(dB)	(dB)	(dB)	K	Measure	(dBm)	(dB)	(dBm)
10	27.5	-33.6	-6.7	-17.9	1.1	0.9	16.5	0.9	27.9
20	27.4	-33.3	-6.7	-19.3	1.1	0.9	15.6	0.4	27.3
30	27.4	-33.3	-6.8	-18.3	1.1	0.9	15.5	0.6	27.1
40	27.3	-33.3	-6.9	-17.7	1.1	0.9	15.5	0.4	26.9
50	27.3	-33.3	-6.8	-17.6	1.1	0.9	15.6	0.4	27.0
60	27.3	-33.3	-6.9	-17.3	1.1	0.9	15.4	0.3	26.9
70	27.2	-33.2	-6.9	-17.0	1.1	0.9	15.4	0.5	26.8
80	27.2	-33.1	-6.9	-17.0	1.1	0.9	15.5	0.4	26.4
90	27.2	-33.0	-7.0	-16.6	1.1	0.9	15.4	0.5	26.3
100	27.1	-32.8	-7.0	-16.5	1.1	0.8	15.4	0.4	26.7
200	26.5	-32.5	-7.4	-15.7	1.1	0.8	15.5	0.4	26.6
250	26.0	-32.0	-7.7	-15.4	1.1	0.8	15.3	0.4	26.9
300	25.6	-31.5	-8.1	-15.4	1.1	0.8	15.5	0.4	26.7
350	25.0	-31.2	-8.5	-15.1	1.1	0.8	15.7	0.4	26.8
400	24.5	-30.5	-8.8	-15.1	1.1	0.8	15.7	0.4	26.9
450	24.0	-30.2	-9.2	-15.2	1.1	0.8	15.4	0.4	27.1
500	23.5	-29.7	-9.5	-15.0	1.1	0.8	15.7	0.4	27.0
550	23.0	-29.3	-9.8	-15.1	1.2	0.8	15.7	0.4	27.1
600	22.5	-28.8	-10.2	-14.9	1.2	0.8	15.6	0.3	27.2
650	22.0	-28.4	-10.4	-14.9	1.2	0.8	15.9	0.4	27.1
700	21.6	-28.0	-10.7	-14.9	1.2	0.8	15.8	0.4	27.3
750	21.1	-27.5	-10.9	-14.9	1.2	0.8	16.0	0.5	27.1
800	20.7	-27.2	-11.1	-14.9	1.2	0.8	15.8	0.4	27.2
850	20.3	-26.8	-11.3	-14.8	1.2	0.8	16.0	0.5	27.3
900	19.9	-26.4	-11.4	-14.8	1.2	0.8	16.0	0.3	27.4
950	19.5	-26.1	-11.6	-14.8	1.2	0.8	16.1	0.4	27.4
1000	19.2	-25.7	-11.7	-14.8	1.2	0.8	16.0	0.4	27.5
1050	18.8	-25.3	-11.9	-14.8	1.2	0.8	16.2	0.4	27.3
1100	18.5	-25.0	-12.0	-14.8	1.2	0.8	16.1	0.4	27.2
1150	18.1	-24.7	-12.1	-14.8	1.2	0.8	16.2	0.4	27.4
1200	17.8	-24.4	-12.2	-14.8	1.2	0.8	16.2	0.4	27.2
1250	17.5	-24.1	-12.3	-14.8	1.2	0.8	16.3	0.4	27.3
1300	17.2	-23.8	-12.4	-14.8	1.2	0.8	16.7	0.5	27.5
1350	16.9	-23.6	-12.5	-14.8	1.2	0.8	16.3	0.4	27.6
1400	16.6	-23.3	-12.5	-14.9	1.2	0.8	16.2	0.4	27.7
1450	16.4	-23.1	-12.6	-14.9	1.2	0.8	16.6	0.4	27.8
1500	16.1	-22.8	-12.6	-14.9	1.2	0.8	16.7	0.4	27.9
1550	15.9	-22.6	-12.7	-14.9	1.2	0.8	15.9	0.5	27.8
1600	15.6	-22.3	-12.7	-15.0	1.2	0.8	16.6	0.4	28.1
1650	15.4	-22.1	-12.7	-14.9	1.2	0.8	16.4	0.4	27.9
1700	15.1	-21.9	-12.8	-14.9	1.2	0.8	16.9	0.5	28.2
1750	14.9	-21.7	-12.8	-15.0	1.2	0.8	16.5	0.4	28.1
1800	14.7	-21.4	-12.8	-15.0	1.2	0.8	16.6	0.5	28.0
1850	14.5	-21.2	-12.8	-15.1	1.2	0.9	16.2	0.5	28.1
1900	14.3	-21.0	-12.8	-15.1	1.2	0.9	16.5	0.5	28.4
1950	14.0	-20.8	-12.8	-15.2	1.2	0.9	16.4	0.5	28.2
2000	13.8	-20.6	-12.8	-15.3	1.2	0.9	16.1	0.5	28.2
2100	13.5	-20.2	-12.7	-15.4	1.2	0.9	16.0	0.6	27.8
2200	13.1	-19.9	-12.6	-15.6	1.2	0.9	16.4	0.6	28.1
2300	12.7	-19.5	-12.5	-15.8	1.2	0.9	16.4	0.6	27.8
2400	12.4	-19.2	-12.4	-16.1	1.2	0.9	16.5	0.5	27.8
2500	12.1	-18.9	-12.2	-16.4	1.2	0.9	16.4	0.6	27.7
2600	11.7	-18.6	-12.0	-16.8	1.2	0.9	16.4	0.6	27.8
2700	11.4	-18.3	-11.8	-17.3	1.2	0.9	15.9	0.6	27.7
2800	11.1	-18.1	-11.5	-17.9	1.2	0.9	16.0	0.7	27.6
2900	10.8	-17.8	-11.2	-18.7	1.2	0.9	15.7	0.7	27.7
3000	10.6	-17.5	-10.9	-19.8	1.2	0.9	16.0	0.8	27.6
3100	10.3	-17.2	-10.8	-20.9	1.2	0.9	16.3	0.8	27.7
3200	10.0	-17.1	-10.6	-22.1	1.2	0.9	16.4	0.8	27.8
3300	9.7	-16.9	-10.2	-23.9	1.2	0.9	16.4	0.9	27.7
3400	9.5	-16.6	-9.7	-26.1	1.2	0.9	16.3	1.0	27.7
3500	9.3	-16.4	-9.4	-28.6	1.2	0.9	16.5	0.9	28.0
3600	9.1	-16.2	-9.1	-31.3	1.2	1.0	16.7	1.1	28.3
3700	8.9	-16.0	-8.9	-33.4	1.2	1.0	16.1	0.9	27.7
3800	8.7	-15.8	-8.6	-32.9	1.2	1.0	16.8	1.0	28.1
3900	8.4	-15.6	-8.4	-30.2	1.2	1.0	16.3	1.1	27.9
4000	8.2	-15.5	-8.2	-27.8	1.2	1.0	16.5	1.1	27.6

*Note: Tested with $I_{ADJ} = \text{OPEN}$.

Typical Performance Data

NOTE: Use PDF Bookmarks to view DATA at required conditions

Definitions:

Input Return Loss = S11 (dB)

Gain = S21 (dB)

Isolation = S12 (dB)

Output Return Loss = S22 (dB)

TEST CONDITIONS: $V_{DD} = +3.3\text{ V}$, $V_{SHUTDOWN} = 0\text{ V}$, $I_{DD} = 43\text{ mA}$, $I_{SHUTDOWN} = 0.0014\text{ }\mu\text{A}$ @ Temperature = +25°C

FREQ	Gain	Isolation	Input Return Loss	Output Return Loss	Stability		1dB Comp. Output	Noise Figure	IP-3 Output $P_{OUT} = +4$ dBm/Tone
(MHz)	(dB)	(dB)	(dB)	(dB)	K	Measure	(dBm)	(dB)	(dBm)
10	27.9	-34.8	-7.2	-19.4	1.2	1.0	17.6	0.9	29.8
20	27.9	-33.3	-7.1	-20.8	1.1	0.9	16.8	0.4	29.0
30	27.8	-33.5	-7.3	-19.8	1.1	0.9	16.7	0.6	28.7
40	27.7	-33.9	-7.3	-19.1	1.1	0.9	16.7	0.3	28.6
50	27.7	-33.6	-7.3	-18.8	1.1	0.9	16.6	0.4	28.5
60	27.7	-33.4	-7.3	-18.4	1.1	0.9	16.5	0.4	28.5
70	27.6	-33.1	-7.3	-18.0	1.1	0.8	16.5	0.5	28.2
80	27.7	-33.4	-7.4	-18.1	1.1	0.8	16.6	0.4	28.5
90	27.6	-33.1	-7.4	-17.4	1.1	0.8	16.5	0.5	28.2
100	27.5	-33.2	-7.4	-17.4	1.1	0.8	16.6	0.4	28.4
200	26.9	-32.6	-7.9	-16.2	1.1	0.8	16.7	0.4	28.1
250	26.4	-32.1	-8.2	-15.7	1.1	0.8	16.5	0.4	28.7
300	25.9	-32.1	-8.6	-15.6	1.2	0.8	16.7	0.4	28.4
350	25.4	-31.5	-9.0	-15.2	1.2	0.8	16.9	0.4	28.8
400	24.9	-30.8	-9.3	-15.0	1.1	0.8	16.8	0.4	28.8
450	24.3	-30.7	-9.8	-15.0	1.2	0.8	16.5	0.4	28.8
500	23.8	-30.1	-10.1	-14.8	1.2	0.8	16.8	0.4	28.6
550	23.3	-29.6	-10.4	-14.7	1.2	0.8	16.9	0.4	29.2
600	22.8	-29.2	-10.8	-14.6	1.2	0.8	16.7	0.4	29.2
650	22.3	-28.7	-11.0	-14.5	1.2	0.8	17.0	0.3	29.1
700	21.9	-28.3	-11.3	-14.5	1.2	0.8	16.9	0.4	29.4
750	21.5	-27.9	-11.5	-14.5	1.2	0.8	17.2	0.4	29.1
800	21.0	-27.5	-11.7	-14.4	1.2	0.8	16.9	0.4	29.4
850	20.6	-27.1	-11.9	-14.3	1.2	0.8	17.0	0.4	29.4
900	20.2	-26.7	-12.1	-14.3	1.2	0.8	17.0	0.4	29.4
950	19.8	-26.4	-12.3	-14.3	1.2	0.8	17.1	0.4	29.6
1000	19.5	-26.0	-12.4	-14.2	1.2	0.8	17.1	0.4	29.7
1050	19.1	-25.6	-12.5	-14.2	1.2	0.8	17.2	0.4	29.6
1100	18.8	-25.3	-12.7	-14.2	1.2	0.8	17.2	0.4	29.3
1150	18.4	-25.0	-12.8	-14.2	1.2	0.8	17.3	0.4	29.7
1200	18.1	-24.7	-12.9	-14.1	1.2	0.8	17.3	0.5	29.4
1250	17.8	-24.4	-13.0	-14.2	1.2	0.8	17.4	0.4	29.5
1300	17.5	-24.1	-13.0	-14.1	1.2	0.8	17.7	0.4	29.6
1350	17.2	-23.8	-13.1	-14.2	1.2	0.8	17.3	0.4	29.7
1400	16.9	-23.6	-13.2	-14.2	1.2	0.8	17.2	0.4	30.1
1450	16.7	-23.3	-13.3	-14.2	1.2	0.8	17.5	0.4	30.0
1500	16.4	-23.0	-13.3	-14.2	1.2	0.8	17.6	0.4	30.0
1550	16.1	-22.8	-13.4	-14.2	1.2	0.8	16.9	0.4	29.7
1600	15.9	-22.6	-13.4	-14.3	1.2	0.8	17.6	0.5	30.1
1650	15.6	-22.3	-13.4	-14.2	1.2	0.8	17.4	0.5	30.2
1700	15.4	-22.1	-13.4	-14.2	1.2	0.8	17.8	0.4	30.6
1750	15.2	-21.9	-13.5	-14.3	1.2	0.8	17.4	0.4	30.3
1800	15.0	-21.6	-13.5	-14.3	1.2	0.8	17.6	0.4	30.2
1850	14.7	-21.4	-13.5	-14.3	1.2	0.8	17.1	0.5	30.4
1900	14.5	-21.2	-13.5	-14.4	1.2	0.8	17.5	0.4	30.5
1950	14.3	-21.1	-13.5	-14.4	1.2	0.8	17.4	0.5	30.3
2000	14.1	-20.8	-13.4	-14.5	1.2	0.8	17.0	0.5	30.3
2100	13.7	-20.4	-13.4	-14.6	1.2	0.8	17.0	0.5	30.2
2200	13.4	-20.1	-13.3	-14.8	1.2	0.8	17.4	0.5	30.5
2300	13.0	-19.7	-13.1	-14.9	1.2	0.8	17.3	0.5	30.2
2400	12.7	-19.4	-13.0	-15.2	1.2	0.9	17.4	0.6	29.8
2500	12.3	-19.1	-12.8	-15.5	1.2	0.9	17.3	0.6	30.0
2600	12.0	-18.8	-12.6	-15.9	1.2	0.9	17.2	0.6	30.0
2700	11.7	-18.5	-12.4	-16.3	1.2	0.9	16.8	0.6	29.9
2800	11.4	-18.3	-12.1	-16.8	1.2	0.9	16.8	0.7	29.7
2900	11.1	-18.0	-11.7	-17.6	1.2	0.9	16.4	0.7	29.8
3000	10.8	-17.7	-11.4	-18.5	1.2	0.9	16.8	0.7	29.9
3100	10.6	-17.5	-11.3	-19.4	1.2	0.9	17.1	0.8	30.0
3200	10.3	-17.3	-11.0	-20.5	1.2	0.9	17.2	0.7	30.1
3300	10.0	-17.1	-10.6	-22.0	1.2	0.9	17.1	1.0	30.1
3400	9.8	-16.8	-10.1	-23.8	1.2	0.9	17.0	1.1	29.9
3500	9.6	-16.6	-9.8	-25.7	1.2	0.9	17.3	1.0	30.1
3600	9.4	-16.3	-9.5	-27.9	1.2	0.9	17.5	1.0	30.6
3700	9.2	-16.1	-9.2	-30.8	1.2	0.9	16.9	1.0	29.9
3800	9.0	-15.9	-8.9	-32.6	1.2	1.0	17.5	1.0	30.3
3900	8.7	-15.8	-8.7	-32.5	1.2	1.0	17.0	0.9	30.1
4000	8.5	-15.6	-8.5	-30.6	1.2	1.0	17.2	1.1	29.9

*Note: Tested with $I_{ADJ} = \text{OPEN}$.

Typical Performance Data

NOTE: Use PDF Bookmarks to view DATA at required conditions

Definitions:

Input Return Loss = S11 (dB)

Gain = S21 (dB)

Isolation = S12 (dB)

Output Return Loss = S22 (dB)

TEST CONDITIONS: $V_{DD} = +4.75\text{ V}$, $V_{SHUTDOWN} = 0\text{ V}$, $I_{DD} = 68\text{ mA}$, $I_{SHUTDOWN} = 0.0014\text{ }\mu\text{A}$ @ Temperature = $+25^{\circ}\text{C}$

FREQ	Gain	Isolation	Input Return Loss	Output Return Loss	Stability		1dB Comp. Output	Noise Figure	IP-3 Output $P_{OUT} = +4$ dBm/Tone
(MHz)	(dB)	(dB)	(dB)	(dB)	K	Measure	(dBm)	(dB)	(dBm)
10	29.0	-34.9	-8.4	-22.5	1.1	0.9	21.8	1.0	33.2
20	29.0	-34.2	-8.5	-30.3	1.1	0.8	21.0	0.3	32.5
30	29.0	-34.1	-8.7	-26.8	1.1	0.8	21.0	0.3	32.9
40	28.9	-34.4	-8.7	-24.6	1.1	0.8	20.8	0.3	33.5
50	28.9	-33.7	-8.6	-23.6	1.1	0.8	20.8	0.3	33.7
60	28.9	-34.2	-8.8	-22.4	1.1	0.8	20.7	0.4	33.9
70	28.8	-33.5	-8.7	-21.3	1.1	0.8	20.8	0.5	33.8
80	28.8	-33.9	-8.8	-21.2	1.1	0.8	20.8	0.4	33.1
90	28.7	-33.6	-8.9	-20.2	1.1	0.8	20.7	0.4	33.5
100	28.7	-33.8	-8.9	-19.9	1.1	0.8	20.8	0.5	33.6
200	27.9	-33.1	-9.4	-16.8	1.1	0.7	20.8	0.4	33.7
250	27.4	-33.0	-9.8	-15.8	1.1	0.7	20.7	0.4	33.6
300	26.9	-32.6	-10.2	-15.2	1.2	0.7	20.7	0.4	33.3
350	26.3	-32.2	-10.7	-14.6	1.2	0.7	20.7	0.4	33.6
400	25.8	-31.7	-11.1	-14.2	1.2	0.7	20.6	0.4	33.8
450	25.2	-31.3	-11.5	-13.9	1.2	0.8	20.2	0.4	34.0
500	24.7	-30.9	-11.8	-13.7	1.2	0.8	20.5	0.4	34.4
550	24.1	-30.5	-12.3	-13.5	1.2	0.8	20.4	0.4	34.9
600	23.6	-30.1	-12.6	-13.3	1.2	0.8	20.2	0.4	35.1
650	23.1	-29.5	-12.9	-13.1	1.2	0.8	20.4	0.4	35.3
700	22.7	-29.0	-13.2	-13.0	1.2	0.8	20.3	0.4	35.0
750	22.2	-28.6	-13.4	-12.9	1.2	0.8	20.5	0.4	34.7
800	21.8	-28.3	-13.6	-12.8	1.2	0.8	20.2	0.5	35.2
850	21.3	-27.9	-13.9	-12.7	1.2	0.8	20.2	0.5	35.8
900	20.9	-27.5	-14.0	-12.7	1.2	0.8	20.2	0.4	35.5
950	20.5	-27.2	-14.2	-12.6	1.2	0.8	20.3	0.4	35.1
1000	20.2	-26.8	-14.4	-12.6	1.2	0.8	20.2	0.4	36.5
1050	19.8	-26.4	-14.5	-12.5	1.2	0.8	20.2	0.4	36.3
1100	19.5	-26.1	-14.6	-12.5	1.2	0.8	20.2	0.4	36.0
1150	19.1	-25.8	-14.8	-12.5	1.2	0.8	20.3	0.4	35.8
1200	18.8	-25.4	-14.8	-12.4	1.2	0.8	20.2	0.4	35.5
1250	18.5	-25.2	-15.0	-12.4	1.2	0.8	20.4	0.4	36.3
1300	18.2	-24.8	-15.0	-12.4	1.2	0.8	20.7	0.4	37.0
1350	17.9	-24.6	-15.1	-12.4	1.2	0.8	20.2	0.4	36.7
1400	17.6	-24.3	-15.2	-12.4	1.2	0.8	20.1	0.4	36.4
1450	17.3	-24.1	-15.3	-12.4	1.2	0.8	20.4	0.4	37.1
1500	17.1	-23.8	-15.3	-12.4	1.2	0.8	20.5	0.4	37.9
1550	16.8	-23.5	-15.4	-12.3	1.2	0.8	19.8	0.4	37.8
1600	16.5	-23.3	-15.4	-12.4	1.2	0.8	20.4	0.4	37.7
1650	16.3	-23.0	-15.4	-12.4	1.2	0.8	20.3	0.4	37.6
1700	16.1	-22.8	-15.4	-12.4	1.2	0.8	20.7	0.4	37.5
1750	15.8	-22.6	-15.5	-12.4	1.2	0.8	20.3	0.4	38.0
1800	15.6	-22.4	-15.5	-12.4	1.2	0.8	20.4	0.5	37.6
1850	15.4	-22.2	-15.5	-12.4	1.2	0.8	20.0	0.4	37.3
1900	15.2	-21.9	-15.4	-12.5	1.2	0.8	20.3	0.4	37.8
1950	15.0	-21.7	-15.4	-12.5	1.2	0.8	20.1	0.5	38.3
2000	14.8	-21.5	-15.4	-12.6	1.2	0.8	19.8	0.5	38.6
2100	14.4	-21.1	-15.3	-12.6	1.2	0.8	19.8	0.5	37.7
2200	14.0	-20.8	-15.1	-12.8	1.2	0.8	20.1	0.5	37.4
2300	13.7	-20.4	-14.9	-12.9	1.2	0.8	20.0	0.5	37.2
2400	13.3	-20.1	-14.8	-13.0	1.2	0.8	20.0	0.5	37.5
2500	13.0	-19.8	-14.5	-13.3	1.2	0.8	19.9	0.6	37.9
2600	12.7	-19.4	-14.2	-13.5	1.2	0.8	19.9	0.6	38.7
2700	12.3	-19.2	-14.0	-13.9	1.2	0.8	19.3	0.6	39.6
2800	12.0	-18.9	-13.6	-14.3	1.2	0.8	19.2	0.6	38.5
2900	11.7	-18.6	-13.1	-14.9	1.2	0.9	18.7	0.6	37.5
3000	11.5	-18.3	-12.8	-15.5	1.2	0.9	19.2	0.7	37.6
3100	11.3	-18.0	-12.6	-16.1	1.2	0.9	19.5	0.7	37.8
3200	11.0	-17.8	-12.3	-16.8	1.2	0.9	19.7	0.8	37.7
3300	10.7	-17.6	-11.7	-17.9	1.2	0.9	19.6	0.8	38.8
3400	10.5	-17.4	-11.2	-18.9	1.2	0.9	19.5	1.0	39.0
3500	10.3	-17.1	-10.8	-20.0	1.2	0.9	19.8	1.0	37.5
3600	10.1	-16.9	-10.4	-21.2	1.2	0.9	20.0	1.0	38.7
3700	9.9	-16.6	-10.1	-22.5	1.2	0.9	19.4	0.9	38.1
3800	9.7	-16.5	-9.8	-24.0	1.2	0.9	19.8	0.9	37.3
3900	9.5	-16.3	-9.5	-25.6	1.2	0.9	19.4	0.9	38.3
4000	9.2	-16.1	-9.2	-27.7	1.2	0.9	19.7	1.0	38.2

*Note: Tested with $I_{ADJ} = \text{OPEN}$.

Typical Performance Data

NOTE: Use PDF Bookmarks to view DATA at required conditions

Definitions:

Input Return Loss = S11 (dB)

Gain = S21 (dB)

Isolation = S12 (dB)

Output Return Loss = S22 (dB)

TEST CONDITIONS: $V_{DD} = +5\text{ V}$, $V_{SHUTDOWN} = 0\text{ V}$, $I_{DD} = 72\text{ mA}$, $I_{SHUTDOWN} = 0.0014\text{ }\mu\text{A}$ @ Temperature = +25°C

FREQ	Gain	Isolation	Input Return Loss	Output Return Loss	Stability		1dB Comp. Output	Noise Figure	IP-3 Output $P_{OUT} = +4\text{ dBm/Tone}$
(MHz)	(dB)	(dB)	(dB)	(dB)	K	Measure	(dBm)	(dB)	(dBm)
10	29.2	-35.2	-8.6	-22.9	1.1	0.9	22.3	1.0	30.8
20	29.1	-33.4	-8.5	-29.9	1.0	0.8	21.6	0.3	34.9
30	29.1	-34.4	-8.9	-28.3	1.1	0.8	21.5	0.3	33.8
40	29.0	-34.0	-8.9	-25.5	1.1	0.8	21.5	0.4	33.7
50	29.0	-34.2	-8.8	-24.4	1.1	0.8	21.4	0.3	34.0
60	29.0	-34.1	-8.9	-22.7	1.1	0.8	21.4	0.3	34.9
70	28.9	-33.9	-8.9	-21.8	1.1	0.8	21.3	0.4	33.8
80	28.9	-33.8	-9.0	-21.5	1.1	0.8	21.4	0.4	33.3
90	28.9	-33.9	-9.1	-20.4	1.1	0.8	21.4	0.4	34.5
100	28.8	-33.7	-9.1	-19.9	1.1	0.8	21.3	0.4	34.4
200	28.1	-33.3	-9.7	-16.8	1.1	0.7	21.3	0.4	33.5
250	27.5	-33.1	-10.0	-15.7	1.2	0.7	21.2	0.4	34.4
300	27.0	-32.8	-10.4	-15.1	1.2	0.7	21.2	0.4	35.3
350	26.4	-32.3	-10.9	-14.5	1.2	0.7	21.2	0.4	34.4
400	25.9	-31.8	-11.3	-14.0	1.2	0.7	21.0	0.4	33.7
450	25.3	-31.7	-11.7	-13.8	1.2	0.8	20.7	0.4	35.6
500	24.7	-30.9	-12.1	-13.5	1.2	0.7	20.9	0.4	35.7
550	24.2	-30.5	-12.5	-13.3	1.2	0.8	20.8	0.4	35.0
600	23.7	-30.0	-12.8	-13.1	1.2	0.8	20.6	0.4	35.7
650	23.2	-29.7	-13.1	-13.0	1.2	0.8	20.7	0.4	36.3
700	22.7	-29.2	-13.4	-12.8	1.2	0.8	20.7	0.4	36.2
750	22.3	-28.8	-13.6	-12.7	1.2	0.8	20.9	0.4	36.1
800	21.8	-28.4	-13.9	-12.6	1.2	0.8	20.5	0.4	36.5
850	21.4	-28.0	-14.1	-12.5	1.2	0.8	20.5	0.4	36.9
900	21.0	-27.6	-14.2	-12.5	1.2	0.8	20.6	0.4	37.6
950	20.6	-27.2	-14.5	-12.4	1.2	0.8	20.7	0.4	38.2
1000	20.2	-26.8	-14.6	-12.4	1.2	0.8	20.6	0.4	38.2
1050	19.9	-26.6	-14.7	-12.3	1.2	0.8	20.6	0.4	37.3
1100	19.5	-26.2	-14.9	-12.3	1.2	0.8	20.5	0.4	37.5
1150	19.2	-25.9	-15.0	-12.3	1.2	0.8	20.6	0.4	37.8
1200	18.9	-25.5	-15.1	-12.2	1.2	0.8	20.6	0.4	37.5
1250	18.5	-25.2	-15.2	-12.2	1.2	0.8	20.7	0.4	37.0
1300	18.3	-24.9	-15.3	-12.2	1.2	0.8	21.0	0.4	36.6
1350	18.0	-24.7	-15.4	-12.2	1.2	0.8	20.5	0.4	38.1
1400	17.7	-24.4	-15.5	-12.2	1.2	0.8	20.4	0.4	37.7
1450	17.4	-24.1	-15.6	-12.2	1.2	0.8	20.7	0.4	37.4
1500	17.1	-23.8	-15.5	-12.2	1.2	0.8	20.7	0.4	37.0
1550	16.9	-23.6	-15.6	-12.1	1.2	0.8	20.1	0.4	36.9
1600	16.6	-23.4	-15.7	-12.2	1.2	0.8	20.7	0.5	36.8
1650	16.4	-23.1	-15.6	-12.2	1.2	0.8	20.6	0.4	38.8
1700	16.1	-22.9	-15.7	-12.2	1.2	0.8	21.0	0.4	38.4
1750	15.9	-22.7	-15.7	-12.2	1.2	0.8	20.6	0.4	37.9
1800	15.7	-22.4	-15.7	-12.2	1.2	0.8	20.7	0.4	38.5
1850	15.4	-22.2	-15.7	-12.2	1.2	0.8	20.3	0.4	39.1
1900	15.2	-22.0	-15.6	-12.3	1.2	0.8	20.6	0.4	37.8
1950	15.0	-21.8	-15.7	-12.3	1.2	0.8	20.4	0.5	38.5
2000	14.8	-21.6	-15.6	-12.3	1.2	0.8	20.0	0.5	39.2
2100	14.4	-21.2	-15.5	-12.4	1.2	0.8	20.1	0.5	39.8
2200	14.1	-20.8	-15.3	-12.5	1.2	0.8	20.4	0.5	39.2
2300	13.7	-20.5	-15.1	-12.6	1.2	0.8	20.3	0.5	38.6
2400	13.4	-20.2	-14.9	-12.8	1.2	0.8	20.3	0.5	38.2
2500	13.0	-19.8	-14.8	-13.0	1.2	0.8	20.2	0.6	39.2
2600	12.7	-19.5	-14.4	-13.3	1.2	0.8	20.2	0.6	40.2
2700	12.4	-19.2	-14.2	-13.6	1.2	0.8	19.6	0.7	38.8
2800	12.1	-19.0	-13.8	-14.0	1.2	0.8	19.5	0.7	37.4
2900	11.8	-18.7	-13.3	-14.6	1.2	0.9	19.0	0.7	37.8
3000	11.6	-18.4	-12.9	-15.2	1.2	0.9	19.5	0.7	38.2
3100	11.3	-18.1	-12.8	-15.8	1.2	0.9	19.8	0.7	38.1
3200	11.0	-17.9	-12.4	-16.5	1.2	0.9	20.0	0.8	38.9
3300	10.8	-17.7	-11.9	-17.5	1.2	0.9	19.9	0.8	39.6
3400	10.5	-17.4	-11.3	-18.4	1.2	0.9	19.7	0.8	38.2
3500	10.3	-17.2	-10.9	-19.5	1.2	0.9	20.1	0.9	39.2
3600	10.1	-16.9	-10.5	-20.6	1.2	0.9	20.3	0.9	39.9
3700	9.9	-16.7	-10.2	-21.8	1.2	0.9	19.6	1.0	38.9
3800	9.7	-16.5	-9.9	-23.1	1.2	0.9	20.1	0.8	38.4
3900	9.5	-16.3	-9.6	-24.8	1.2	0.9	19.7	0.9	38.9
4000	9.3	-16.2	-9.3	-26.7	1.2	0.9	19.9	1.0	38.6

*Note: Tested with $I_{ADJ} = \text{OPEN}$.

Typical Performance Data

NOTE: Use PDF Bookmarks to view DATA at required conditions

Definitions:

Input Return Loss = S11 (dB)

Gain = S21 (dB)

Isolation = S12 (dB)

Output Return Loss = S22 (dB)

TEST CONDITIONS: $V_{DD} = +5.25\text{ V}$, $V_{SHUTDOWN} = 0\text{ V}$, $I_{DD} = 76\text{ mA}$, $I_{SHUTDOWN} = 0.0014\text{ }\mu\text{A}$ @ Temperature = +25°C

FREQ	Gain	Isolation	Input Return Loss	Output Return Loss	Stability		1dB Comp. Output	Noise Figure	IP-3 Output $P_{OUT} = +4$ dBm/Tone
(MHz)	(dB)	(dB)	(dB)	(dB)	K	Measure	(dBm)	(dB)	(dBm)
10	29.3	-35.3	-8.8	-23.3	1.1	0.9	22.7	1.0	34.3
20	29.2	-34.3	-8.9	-33.8	1.1	0.8	22.1	0.3	33.5
30	29.2	-34.1	-9.0	-28.8	1.1	0.8	22.1	0.3	36.6
40	29.1	-34.1	-9.0	-26.1	1.1	0.8	22.0	0.4	34.5
50	29.1	-34.0	-9.0	-24.7	1.1	0.8	21.9	0.3	33.3
60	29.1	-34.0	-9.1	-22.9	1.1	0.8	21.9	0.3	34.3
70	29.0	-33.9	-9.0	-22.1	1.1	0.8	21.8	0.5	34.3
80	29.1	-33.8	-9.2	-21.7	1.1	0.8	21.9	0.4	33.4
90	29.0	-34.0	-9.3	-20.6	1.1	0.8	21.9	0.4	37.3
100	28.9	-33.9	-9.3	-20.1	1.1	0.8	21.9	0.4	34.8
200	28.2	-33.5	-9.9	-16.7	1.1	0.7	21.8	0.4	35.3
250	27.6	-33.3	-10.2	-15.7	1.2	0.7	21.7	0.4	35.4
300	27.1	-32.7	-10.6	-15.0	1.2	0.7	21.6	0.4	34.3
350	26.5	-32.4	-11.1	-14.3	1.2	0.7	21.6	0.4	34.8
400	26.0	-31.9	-11.5	-13.9	1.2	0.7	21.4	0.4	34.6
450	25.4	-31.5	-11.9	-13.6	1.2	0.7	21.0	0.4	34.5
500	24.8	-31.0	-12.3	-13.4	1.2	0.7	21.2	0.4	35.5
550	24.3	-30.6	-12.7	-13.2	1.2	0.7	21.1	0.4	36.5
600	23.8	-30.2	-13.1	-12.9	1.2	0.8	20.9	0.4	36.0
650	23.3	-29.8	-13.3	-12.8	1.2	0.8	21.1	0.4	35.4
700	22.8	-29.3	-13.6	-12.7	1.2	0.8	21.0	0.4	35.5
750	22.3	-28.9	-13.8	-12.6	1.2	0.8	21.2	0.4	35.6
800	21.9	-28.5	-14.1	-12.5	1.2	0.8	20.8	0.4	36.5
850	21.5	-28.0	-14.3	-12.4	1.2	0.8	20.8	0.4	37.5
900	21.1	-27.7	-14.5	-12.3	1.2	0.8	20.8	0.4	37.5
950	20.7	-27.3	-14.7	-12.2	1.2	0.8	20.9	0.4	37.5
1000	20.3	-26.9	-14.8	-12.2	1.2	0.8	20.8	0.4	37.5
1050	19.9	-26.6	-14.9	-12.2	1.2	0.8	20.9	0.4	37.5
1100	19.6	-26.2	-15.1	-12.1	1.2	0.8	20.8	0.4	37.4
1150	19.2	-25.9	-15.2	-12.1	1.2	0.8	20.9	0.4	37.3
1200	18.9	-25.6	-15.3	-12.0	1.2	0.8	20.9	0.4	37.1
1250	18.6	-25.3	-15.5	-12.1	1.2	0.8	21.0	0.4	36.9
1300	18.3	-25.0	-15.5	-12.0	1.2	0.8	21.2	0.4	37.6
1350	18.0	-24.8	-15.6	-12.0	1.2	0.8	20.8	0.4	38.3
1400	17.7	-24.5	-15.7	-12.0	1.2	0.8	20.7	0.4	37.8
1450	17.4	-24.2	-15.8	-12.0	1.2	0.8	21.0	0.5	37.3
1500	17.2	-23.9	-15.7	-12.0	1.2	0.8	21.1	0.5	38.2
1550	16.9	-23.7	-15.8	-12.0	1.2	0.8	20.3	0.4	39.2
1600	16.7	-23.4	-15.9	-12.0	1.2	0.8	21.1	0.4	38.1
1650	16.4	-23.2	-15.8	-12.0	1.2	0.8	20.8	0.4	37.1
1700	16.2	-23.0	-15.9	-12.0	1.2	0.8	21.3	0.5	38.1
1750	15.9	-22.8	-15.9	-12.0	1.2	0.8	20.9	0.4	38.2
1800	15.7	-22.5	-15.9	-12.0	1.2	0.8	20.9	0.5	38.3
1850	15.5	-22.3	-15.9	-12.0	1.2	0.8	20.6	0.5	38.6
1900	15.3	-22.1	-15.8	-12.1	1.2	0.8	20.9	0.5	39.0
1950	15.1	-21.9	-15.9	-12.1	1.2	0.8	20.7	0.6	40.4
2000	14.9	-21.7	-15.8	-12.2	1.2	0.8	20.3	0.5	40.5
2100	14.5	-21.3	-15.7	-12.2	1.2	0.8	20.4	0.5	40.6
2200	14.1	-20.9	-15.6	-12.4	1.2	0.8	20.7	0.6	39.4
2300	13.8	-20.6	-15.3	-12.5	1.2	0.8	20.6	0.5	39.1
2400	13.4	-20.3	-15.1	-12.6	1.2	0.8	20.6	0.5	38.8
2500	13.1	-19.9	-14.9	-12.8	1.2	0.8	20.5	0.6	38.9
2600	12.8	-19.6	-14.6	-13.1	1.2	0.8	20.4	0.6	39.0
2700	12.5	-19.3	-14.3	-13.4	1.2	0.8	19.8	0.6	38.7
2800	12.1	-19.0	-13.9	-13.8	1.2	0.8	19.8	0.6	38.3
2900	11.9	-18.8	-13.4	-14.4	1.2	0.8	19.3	0.7	39.5
3000	11.6	-18.4	-13.1	-15.0	1.2	0.9	19.8	0.7	40.7
3100	11.4	-18.2	-12.9	-15.5	1.2	0.9	20.1	0.7	39.5
3200	11.1	-18.0	-12.5	-16.2	1.2	0.9	20.2	0.8	38.4
3300	10.8	-17.8	-12.0	-17.1	1.2	0.9	20.1	0.8	37.9
3400	10.6	-17.5	-11.4	-18.1	1.2	0.9	20.0	0.9	40.8
3500	10.4	-17.2	-11.0	-19.0	1.2	0.9	20.3	1.0	40.1
3600	10.2	-17.0	-10.6	-20.1	1.2	0.9	20.5	1.1	41.0
3700	10.0	-16.8	-10.3	-21.3	1.2	0.9	19.9	0.9	40.8
3800	9.8	-16.6	-10.0	-22.6	1.2	0.9	20.3	0.9	40.1
3900	9.6	-16.4	-9.7	-24.1	1.2	0.9	19.9	0.9	39.1
4000	9.4	-16.2	-9.4	-25.9	1.2	0.9	20.2	1.0	40.5

*Note: Tested with $I_{ADJ} = \text{OPEN}$.

Typical Performance Data

NOTE: Use PDF Bookmarks to view DATA at required conditions

Definitions:

Input Return Loss = S11 (dB)

Gain = S21 (dB)

Isolation = S12 (dB)

Output Return Loss = S22 (dB)

TEST CONDITIONS: $V_{DD} = +5\text{ V}$, $V_{SHUTDOWN} = 0\text{ V}$, $I_{DD} = 73\text{ mA}$, $I_{SHUTDOWN} = 0.0014\text{ }\mu\text{A}$ @ Temperature = -45°C

FREQ	Gain	Isolation	Input Return Loss	Output Return Loss	Stability		1dB Comp. Output	Noise Figure	IP-3 Output $P_{OUT} = +4$ dBm/Tone
(MHz)	(dB)	(dB)	(dB)	(dB)	K	Measure	(dBm)	(dB)	(dBm)
10	30.0	-34.5	-10.7	-24.4	1.1	0.7	22.2	1.1	33.2
20	30.0	-34.9	-10.5	-23.0	1.1	0.8	22.3	0.2	36.4
30	30.0	-34.2	-10.4	-24.4	1.0	0.7	22.0	0.2	34.6
40	30.0	-34.3	-10.5	-24.2	1.0	0.7	21.5	0.2	35.1
50	30.0	-34.5	-10.5	-24.0	1.1	0.7	21.7	0.2	35.2
60	30.0	-34.2	-10.6	-23.2	1.0	0.7	21.5	0.3	35.8
70	29.9	-34.1	-10.6	-23.1	1.0	0.7	21.6	0.3	35.2
80	29.9	-33.7	-10.7	-22.5	1.0	0.7	21.5	0.2	35.8
90	29.8	-33.9	-10.7	-21.9	1.1	0.7	21.6	0.3	34.3
100	29.8	-33.7	-10.7	-21.5	1.0	0.7	21.6	0.3	35.3
200	28.9	-33.1	-11.3	-17.7	1.1	0.6	21.7	0.3	35.3
250	28.4	-33.1	-11.7	-16.6	1.1	0.7	21.6	0.2	35.8
300	27.9	-32.9	-12.1	-15.8	1.1	0.7	21.6	0.3	36.1
350	27.3	-32.1	-12.5	-15.2	1.1	0.7	22.0	0.3	36.1
400	26.7	-32.0	-12.8	-14.7	1.2	0.7	22.0	0.2	36.5
450	26.1	-31.4	-13.1	-14.3	1.2	0.7	21.7	0.3	36.1
500	25.5	-31.0	-13.4	-14.1	1.2	0.7	21.8	0.2	36.1
550	25.0	-30.5	-13.7	-13.9	1.2	0.7	21.8	0.2	36.9
600	24.5	-30.0	-13.9	-13.6	1.2	0.7	21.7	0.2	37.7
650	24.0	-29.6	-14.1	-13.6	1.2	0.7	21.9	0.2	37.3
700	23.5	-29.2	-14.2	-13.4	1.2	0.7	21.9	0.2	36.5
750	23.0	-28.7	-14.4	-13.3	1.2	0.7	22.1	0.3	37.2
800	22.6	-28.3	-14.5	-13.2	1.2	0.7	21.6	0.2	37.9
850	22.1	-27.9	-14.6	-13.1	1.2	0.7	21.7	0.3	38.1
900	21.7	-27.6	-14.7	-13.0	1.2	0.7	21.8	0.2	38.4
950	21.3	-27.1	-14.8	-13.0	1.2	0.7	21.9	0.2	38.9
1000	20.9	-26.8	-14.9	-12.9	1.2	0.7	21.9	0.2	38.7
1050	20.6	-26.5	-15.0	-12.9	1.2	0.7	21.9	0.2	38.6
1100	20.2	-26.1	-15.1	-12.8	1.2	0.7	21.8	0.2	37.6
1150	19.9	-25.8	-15.1	-12.7	1.2	0.7	21.8	0.2	38.0
1200	19.6	-25.4	-15.2	-12.7	1.2	0.7	21.8	0.2	38.4
1250	19.2	-25.1	-15.3	-12.6	1.2	0.7	21.9	0.2	38.5
1300	18.9	-24.9	-15.4	-12.6	1.2	0.7	22.2	0.3	38.7
1350	18.6	-24.6	-15.5	-12.5	1.2	0.7	21.8	0.2	38.8
1400	18.3	-24.3	-15.6	-12.5	1.2	0.7	21.7	0.3	38.9
1450	18.1	-24.0	-15.6	-12.4	1.2	0.7	21.9	0.3	39.2
1500	17.8	-23.8	-15.7	-12.4	1.2	0.7	22.0	0.3	39.6
1550	17.5	-23.5	-15.7	-12.3	1.2	0.7	21.3	0.2	39.0
1600	17.3	-23.3	-15.8	-12.3	1.2	0.7	22.0	0.2	38.4
1650	17.0	-23.0	-15.9	-12.3	1.2	0.8	21.8	0.2	38.7
1700	16.8	-22.7	-15.9	-12.3	1.2	0.7	22.2	0.3	38.9
1750	16.6	-22.6	-15.9	-12.2	1.2	0.8	21.8	0.3	38.9
1800	16.3	-22.3	-15.9	-12.2	1.2	0.8	21.9	0.3	38.9
1850	16.1	-22.1	-15.9	-12.2	1.2	0.8	21.5	0.3	39.2
1900	15.9	-21.9	-15.9	-12.2	1.2	0.8	21.8	0.3	39.4
1950	15.7	-21.7	-15.9	-12.2	1.2	0.8	21.6	0.2	40.2
2000	15.5	-21.5	-15.9	-12.2	1.2	0.8	21.2	0.2	38.4
2100	15.1	-21.1	-15.7	-12.3	1.2	0.8	21.2	0.3	40.1
2200	14.7	-20.7	-15.5	-12.4	1.2	0.8	21.4	0.3	40.8
2300	14.3	-20.4	-15.2	-12.5	1.2	0.8	21.4	0.3	41.5
2400	14.0	-20.1	-14.9	-12.6	1.2	0.8	21.4	0.3	41.1
2500	13.6	-19.8	-14.6	-12.9	1.2	0.8	21.4	0.4	40.4
2600	13.3	-19.4	-14.2	-13.1	1.2	0.8	21.3	0.4	39.7
2700	13.0	-19.2	-13.9	-13.3	1.2	0.8	20.6	0.4	39.8
2800	12.6	-18.9	-13.4	-13.7	1.2	0.8	20.0	0.4	40.0
2900	12.4	-18.6	-13.1	-14.4	1.2	0.8	20.5	0.4	40.6
3000	12.2	-18.3	-12.9	-14.8	1.2	0.8	21.0	0.4	41.1
3100	12.0	-18.0	-12.9	-15.2	1.2	0.8	21.1	0.4	40.5
3200	11.7	-17.8	-12.6	-15.7	1.2	0.8	21.1	0.5	40.0
3300	11.4	-17.6	-12.1	-16.5	1.2	0.8	21.0	0.5	39.5
3400	11.1	-17.4	-11.6	-17.5	1.2	0.9	20.9	0.5	41.9
3500	10.9	-17.1	-11.1	-18.4	1.2	0.9	21.0	0.6	41.3
3600	10.7	-16.9	-10.8	-19.3	1.2	0.9	21.2	0.7	41.1
3700	10.5	-16.6	-10.4	-20.3	1.2	0.9	20.7	0.5	39.8
3800	10.3	-16.4	-10.1	-21.4	1.2	0.9	21.3	0.5	41.2
3900	10.1	-16.2	-9.8	-22.7	1.1	0.9	20.8	0.6	40.7
4000	9.9	-16.1	-9.5	-24.0	1.1	0.9	20.9	0.6	39.7

*Note: Tested with $I_{ADJ} = \text{OPEN}$.

Typical Performance Data

NOTE: Use PDF Bookmarks to view DATA at required conditions

Definitions:

Input Return Loss = S11 (dB)

Gain = S21 (dB)

Isolation = S12 (dB)

Output Return Loss = S22 (dB)

TEST CONDITIONS: $V_{DD} = +5\text{ V}$, $V_{SHUTDOWN} = 0\text{ V}$, $I_{DD} = 72\text{ mA}$, $I_{SHUTDOWN} = 0.0014\text{ }\mu\text{A}$ @ Temperature = $+105^\circ\text{C}$

FREQ	Gain	Isolation	Input Return Loss	Output Return Loss	Stability		1dB Comp. Output	Noise Figure	IP-3 Output $P_{OUT} = +4$ dBm/Tone
(MHz)	(dB)	(dB)	(dB)	(dB)	K	Measure	(dBm)	(dB)	(dBm)
10	28.7	-34.5	-7.8	-19.9	1.1	0.9	21.2	1.2	33.2
20	28.6	-33.9	-7.9	-21.7	1.1	0.8	20.7	0.6	37.9
30	28.5	-33.3	-8.0	-20.1	1.1	0.8	20.8	0.5	33.5
40	28.4	-33.8	-8.0	-19.1	1.1	0.8	20.8	0.5	32.0
50	28.4	-33.2	-8.0	-18.9	1.1	0.8	20.9	0.5	33.9
60	28.4	-33.3	-8.1	-18.3	1.1	0.8	20.9	0.4	32.9
70	28.3	-33.6	-8.1	-18.0	1.1	0.8	20.9	0.6	32.9
80	28.3	-33.3	-8.2	-18.0	1.1	0.8	20.9	0.6	31.9
90	28.2	-33.1	-8.2	-17.2	1.1	0.8	20.9	0.6	34.1
100	28.2	-33.3	-8.2	-17.1	1.1	0.8	20.9	0.5	33.6
200	27.5	-33.0	-8.8	-15.5	1.1	0.8	20.7	0.5	34.0
250	27.0	-33.0	-9.2	-14.9	1.2	0.8	20.3	0.5	34.1
300	26.5	-32.3	-9.6	-14.5	1.2	0.8	20.2	0.5	33.9
350	25.9	-32.1	-10.0	-13.9	1.2	0.8	20.2	0.6	34.6
400	25.4	-31.7	-10.4	-13.7	1.2	0.8	19.9	0.6	34.2
450	24.8	-31.3	-10.8	-13.4	1.2	0.8	19.6	0.6	35.1
500	24.3	-30.8	-11.1	-13.3	1.2	0.8	19.8	0.5	34.6
550	23.8	-30.3	-11.5	-13.2	1.2	0.8	19.7	0.5	34.1
600	23.3	-29.8	-11.9	-12.9	1.2	0.8	19.4	0.5	35.2
650	22.8	-29.5	-12.1	-12.9	1.2	0.8	19.6	0.5	36.4
700	22.3	-29.1	-12.4	-12.8	1.2	0.8	19.5	0.5	35.8
750	21.9	-28.6	-12.6	-12.7	1.2	0.8	19.8	0.6	35.3
800	21.5	-28.2	-12.8	-12.6	1.2	0.8	19.4	0.6	35.4
850	21.0	-27.9	-13.0	-12.5	1.2	0.8	19.4	0.6	35.6
900	20.6	-27.5	-13.2	-12.5	1.2	0.8	19.4	0.6	35.4
950	20.2	-27.1	-13.4	-12.4	1.2	0.8	19.5	0.6	35.2
1000	19.9	-26.7	-13.5	-12.4	1.2	0.8	19.5	0.6	35.9
1050	19.5	-26.4	-13.7	-12.4	1.2	0.8	19.4	0.6	36.5
1100	19.2	-26.1	-13.9	-12.4	1.2	0.8	19.4	0.6	34.8
1150	18.9	-25.8	-14.0	-12.4	1.2	0.8	19.5	0.6	35.6
1200	18.5	-25.5	-14.0	-12.3	1.2	0.8	19.4	0.6	36.4
1250	18.2	-25.2	-14.2	-12.3	1.2	0.8	19.5	0.6	36.0
1300	17.9	-24.9	-14.2	-12.3	1.2	0.8	19.8	0.6	35.6
1350	17.6	-24.6	-14.4	-12.3	1.2	0.8	19.4	0.6	35.9
1400	17.3	-24.4	-14.4	-12.3	1.2	0.8	19.3	0.6	36.2
1450	17.1	-24.1	-14.6	-12.3	1.2	0.8	19.6	0.6	36.8
1500	16.8	-23.8	-14.5	-12.3	1.2	0.8	19.6	0.6	37.4
1550	16.5	-23.6	-14.6	-12.3	1.2	0.8	18.9	0.6	37.3
1600	16.3	-23.3	-14.7	-12.4	1.2	0.8	19.6	0.6	37.2
1650	16.0	-23.1	-14.7	-12.3	1.2	0.8	19.4	0.6	36.7
1700	15.8	-22.8	-14.7	-12.3	1.2	0.8	19.9	0.7	36.2
1750	15.6	-22.6	-14.8	-12.4	1.2	0.8	19.4	0.7	36.3
1800	15.4	-22.4	-14.7	-12.4	1.2	0.8	19.5	0.7	36.4
1850	15.1	-22.2	-14.8	-12.4	1.2	0.8	19.2	0.7	37.0
1900	14.9	-22.0	-14.7	-12.4	1.2	0.8	19.5	0.7	37.7
1950	14.7	-21.8	-14.7	-12.5	1.3	0.8	19.3	0.7	38.0
2000	14.5	-21.6	-14.7	-12.5	1.3	0.8	19.0	0.7	38.3
2100	14.1	-21.2	-14.6	-12.6	1.3	0.8	19.0	0.8	37.8
2200	13.8	-20.9	-14.4	-12.7	1.3	0.8	19.3	0.7	37.3
2300	13.4	-20.5	-14.2	-12.8	1.3	0.8	19.2	0.7	36.8
2400	13.0	-20.2	-14.1	-12.9	1.3	0.8	19.1	0.7	36.4
2500	12.7	-19.8	-14.0	-13.0	1.3	0.8	19.1	0.8	36.5
2600	12.4	-19.5	-13.7	-13.2	1.3	0.8	19.1	0.9	36.5
2700	12.1	-19.3	-13.5	-13.5	1.3	0.9	18.6	0.9	36.3
2800	11.8	-19.0	-13.1	-13.8	1.3	0.9	18.3	1.0	36.1
2900	11.5	-18.7	-12.8	-14.4	1.3	0.9	18.1	1.0	35.9
3000	11.3	-18.4	-12.6	-14.9	1.3	0.9	18.5	1.0	35.8
3100	11.0	-18.2	-12.4	-15.4	1.3	0.9	18.8	1.0	36.7
3200	10.7	-18.0	-12.1	-15.9	1.3	0.9	18.9	1.2	37.7
3300	10.5	-17.7	-11.6	-16.8	1.3	0.9	18.8	1.2	37.4
3400	10.2	-17.5	-11.1	-17.7	1.3	0.9	18.7	1.2	36.5
3500	10.0	-17.2	-10.7	-18.6	1.3	0.9	19.0	1.4	37.6
3600	9.8	-17.0	-10.3	-19.6	1.3	0.9	19.2	1.5	37.5
3700	9.7	-16.8	-10.0	-20.8	1.3	0.9	18.6	1.3	37.1
3800	9.4	-16.6	-9.7	-22.1	1.3	1.0	19.0	1.3	37.7
3900	9.2	-16.4	-9.3	-23.9	1.3	1.0	18.6	1.3	37.2
4000	9.0	-16.2	-9.1	-25.8	1.3	1.0	18.8	1.3	36.6

*Note: Tested with $I_{ADJ} = \text{OPEN}$.

Typical Performance Data

NOTE: Use PDF Bookmarks to view DATA at required conditions

Definitions:

Input Return Loss = S11 (dB)

Gain = S21 (dB)

Isolation = S12 (dB)

Output Return Loss = S22 (dB)

TEST CONDITIONS: $V_{DD} = +5\text{ V}$, $V_{SHUTDOWN} = 0\text{ V}$, $I_{DD} = 44\text{ mA}$, $I_{SHUTDOWN} = 0.0014\text{ }\mu\text{A}$, $R_{IADJ} = 200\Omega$ @ Temperature = $+25^\circ\text{C}$

FREQ	Gain	Isolation	Input Return Loss	Output Return Loss	Stability		1dB Comp. Output	Noise Figure	IP-3 Output $P_{OUT} = +4$ dBm/Tone
(MHz)	(dB)	(dB)	(dB)	(dB)	K	Measure	(dBm)	(dB)	(dBm)
10	27.9	-35.2	-7.5	-15.8	1.2	0.9	21.6	3.8	30.4
20	28.0	-32.8	-7.3	-17.4	1.0	0.8	20.9	1.5	30.5
30	28.0	-33.8	-7.5	-18.0	1.1	0.8	20.9	1.9	30.1
40	28.0	-33.2	-7.5	-17.2	1.1	0.8	21.0	0.9	29.6
50	28.0	-33.3	-7.5	-17.3	1.1	0.8	20.8	2.3	29.9
60	28.0	-32.8	-7.6	-16.9	1.1	0.8	20.9	1.3	29.5
70	27.9	-33.2	-7.6	-16.4	1.1	0.8	20.8	0.8	29.6
80	27.9	-33.2	-7.7	-16.1	1.1	0.8	20.9	0.7	29.3
90	27.9	-33.0	-7.6	-16.0	1.1	0.8	20.7	0.7	29.6
100	27.8	-32.9	-7.6	-15.6	1.1	0.8	20.7	0.4	29.9
200	27.1	-32.7	-8.1	-14.4	1.1	0.8	19.9	0.3	29.6
250	26.7	-32.4	-8.5	-13.9	1.1	0.8	19.7	0.3	29.8
300	26.2	-32.1	-9.0	-13.3	1.1	0.8	19.2	0.2	29.7
350	25.7	-31.9	-9.3	-13.3	1.2	0.8	19.8	0.4	29.7
400	25.1	-31.5	-9.7	-12.8	1.2	0.8	19.7	0.2	30.2
450	24.7	-31.0	-10.1	-12.9	1.2	0.8	19.4	0.3	31.0
500	24.1	-30.7	-10.4	-12.6	1.2	0.8	19.5	0.3	30.8
550	23.6	-30.2	-10.8	-12.5	1.2	0.8	19.5	0.2	31.0
600	23.1	-29.8	-11.0	-12.3	1.2	0.8	19.5	0.2	31.3
650	22.7	-29.4	-11.4	-12.2	1.2	0.8	19.9	0.3	31.0
700	22.2	-29.1	-11.7	-12.2	1.2	0.8	19.8	0.3	31.1
750	21.8	-28.7	-12.0	-12.0	1.2	0.8	20.0	0.2	31.0
800	21.3	-28.3	-12.2	-12.1	1.2	0.8	19.7	0.3	31.3
850	20.9	-27.9	-12.4	-11.9	1.2	0.8	19.8	0.2	31.1
900	20.5	-27.6	-12.6	-12.0	1.2	0.8	19.8	0.2	31.4
950	20.1	-27.2	-12.8	-11.9	1.2	0.8	20.0	0.3	31.4
1000	19.7	-26.9	-13.0	-11.9	1.2	0.8	19.8	0.2	31.3
1050	19.4	-26.6	-13.2	-11.8	1.2	0.8	20.0	0.2	31.5
1100	19.1	-26.3	-13.3	-11.8	1.2	0.8	19.9	0.2	31.5
1150	18.7	-26.0	-13.4	-11.8	1.2	0.8	20.1	0.2	31.3
1200	18.4	-25.6	-13.6	-11.9	1.2	0.8	20.0	0.3	31.3
1250	18.1	-25.3	-13.7	-11.8	1.2	0.8	20.2	0.3	31.2
1300	17.8	-25.1	-13.8	-11.8	1.2	0.8	20.4	0.3	31.4
1350	17.5	-24.8	-13.9	-11.8	1.2	0.8	19.9	0.3	31.6
1400	17.2	-24.5	-14.0	-11.8	1.2	0.8	19.9	0.3	32.3
1450	17.0	-24.2	-14.0	-11.8	1.2	0.8	20.2	0.3	31.8
1500	16.7	-24.0	-14.1	-11.8	1.2	0.8	20.3	0.3	31.8
1550	16.5	-23.8	-14.1	-11.8	1.2	0.8	19.5	0.3	32.7
1600	16.2	-23.5	-14.2	-11.7	1.2	0.8	20.3	0.2	32.2
1650	16.0	-23.3	-14.2	-11.8	1.2	0.8	20.1	0.3	32.5
1700	15.7	-23.0	-14.3	-11.8	1.2	0.8	20.6	0.3	32.6
1750	15.5	-22.8	-14.3	-11.8	1.2	0.8	20.1	0.3	32.5
1800	15.3	-22.6	-14.3	-11.8	1.3	0.8	20.2	0.3	32.3
1850	15.1	-22.4	-14.2	-11.9	1.2	0.8	19.8	0.5	33.2
1900	14.9	-22.2	-14.3	-12.0	1.3	0.8	20.2	0.2	32.9
1950	14.7	-22.0	-14.3	-11.9	1.2	0.8	20.0	0.2	33.0
2000	14.5	-21.8	-14.2	-12.0	1.2	0.8	19.6	0.3	33.1
2100	14.1	-21.4	-14.2	-12.1	1.3	0.8	19.8	0.3	32.9
2200	13.7	-21.1	-14.2	-12.2	1.3	0.8	20.1	0.3	33.0
2300	13.3	-20.7	-14.1	-12.3	1.3	0.8	19.9	0.3	33.0
2400	13.0	-20.4	-13.8	-12.5	1.3	0.8	20.1	0.4	32.7
2500	12.7	-20.0	-13.7	-12.7	1.3	0.8	19.9	0.4	32.5
2600	12.4	-19.7	-13.4	-12.9	1.3	0.9	20.0	0.5	32.5
2700	12.0	-19.5	-13.2	-13.2	1.3	0.9	19.2	0.5	32.7
2800	11.7	-19.3	-12.8	-13.6	1.3	0.9	18.7	0.5	32.2
2900	11.4	-18.9	-12.4	-14.2	1.3	0.9	18.8	0.5	32.8
3000	11.2	-18.6	-12.2	-14.7	1.3	0.9	19.5	0.5	32.9
3100	10.9	-18.4	-11.9	-15.2	1.3	0.9	19.7	0.5	32.7
3200	10.7	-18.1	-11.5	-15.6	1.3	0.9	19.7	0.6	32.8
3300	10.4	-17.9	-11.1	-16.5	1.3	0.9	19.6	0.7	32.8
3400	10.2	-17.7	-10.8	-17.3	1.3	0.9	19.5	0.7	32.6
3500	10.0	-17.4	-10.4	-18.0	1.3	0.9	19.8	0.7	33.1
3600	9.8	-17.2	-10.0	-19.0	1.3	0.9	19.9	0.7	33.0
3700	9.6	-17.0	-9.7	-20.0	1.3	1.0	19.1	0.7	33.4
3800	9.4	-16.8	-9.5	-21.1	1.3	1.0	19.7	0.8	32.9
3900	9.1	-16.6	-9.2	-22.2	1.3	1.0	19.3	0.8	33.2
4000	8.9	-16.4	-9.0	-23.6	1.3	1.0	19.6	0.7	32.5

Typical Performance Data

NOTE: Use PDF Bookmarks to view DATA at required conditions

Definitions:

Input Return Loss = S11 (dB)

Gain = S21 (dB)

Isolation = S12 (dB)

Output Return Loss = S22 (dB)

TEST CONDITIONS: $V_{DD} = +5\text{ V}$, $V_{SHUTDOWN} = 0\text{ V}$, $I_{DD} = 49\text{ mA}$, $I_{SHUTDOWN} = 0.0014\text{ }\mu\text{A}$, $R_{IADJ} = 430\Omega$ @ Temperature = $+25^{\circ}\text{C}$

FREQ	Gain	Isolation	Input Return Loss	Output Return Loss	Stability		1dB Comp. Output	Noise Figure	IP-3 Output P _{OUT} = +4 dBm/Tone
(MHz)	(dB)	(dB)	(dB)	(dB)	K	Measure	(dBm)	(dB)	(dBm)
10	28.1	-33.5	-7.6	-16.4	1.1	0.8	21.7	3.7	31.2
20	28.2	-34.4	-7.8	-19.8	1.1	0.9	21.0	1.4	30.8
30	28.3	-33.2	-7.7	-19.3	1.1	0.8	21.0	1.4	29.9
40	28.2	-34.0	-7.8	-18.8	1.1	0.8	20.9	0.7	30.3
50	28.2	-33.4	-7.8	-18.6	1.1	0.8	20.9	2.1	30.8
60	28.2	-33.2	-7.9	-18.2	1.1	0.8	20.9	1.2	31.3
70	28.2	-33.2	-7.9	-17.7	1.1	0.8	20.8	0.7	30.8
80	28.1	-33.2	-8.0	-17.2	1.1	0.8	21.0	0.6	29.8
90	28.1	-33.3	-7.9	-17.1	1.1	0.8	20.8	0.8	29.9
100	28.0	-33.1	-8.0	-16.6	1.1	0.8	20.7	0.4	30.4
200	27.4	-32.6	-8.5	-15.0	1.1	0.7	19.9	0.3	30.4
250	26.9	-32.7	-8.9	-14.5	1.1	0.8	19.9	0.4	30.9
300	26.4	-32.3	-9.4	-13.7	1.2	0.8	19.7	0.3	30.7
350	25.9	-32.0	-9.6	-13.6	1.2	0.8	19.8	0.4	31.0
400	25.3	-31.6	-10.1	-13.1	1.2	0.8	19.9	0.3	30.4
450	24.8	-31.1	-10.5	-13.1	1.2	0.8	19.5	0.3	31.3
500	24.2	-30.7	-10.8	-12.8	1.2	0.8	19.6	0.2	31.8
550	23.8	-30.3	-11.2	-12.7	1.2	0.8	19.6	0.3	31.8
600	23.3	-29.9	-11.4	-12.5	1.2	0.8	19.7	0.2	32.3
650	22.8	-29.6	-11.8	-12.5	1.2	0.8	20.0	0.2	31.9
700	22.3	-29.2	-12.1	-12.4	1.2	0.8	19.9	0.2	32.2
750	21.9	-28.7	-12.4	-12.2	1.2	0.8	20.1	0.2	31.6
800	21.5	-28.3	-12.6	-12.3	1.2	0.8	19.8	0.2	32.2
850	21.0	-28.0	-12.8	-12.1	1.2	0.8	19.8	0.2	32.3
900	20.6	-27.6	-13.0	-12.1	1.2	0.8	19.8	0.3	32.4
950	20.3	-27.2	-13.2	-12.1	1.2	0.8	20.0	0.2	32.3
1000	19.8	-26.9	-13.4	-12.0	1.2	0.8	19.9	0.2	32.7
1050	19.5	-26.5	-13.6	-12.0	1.2	0.8	20.1	0.2	32.5
1100	19.2	-26.2	-13.7	-11.9	1.2	0.8	20.0	0.2	32.3
1150	18.8	-25.9	-13.8	-11.9	1.2	0.8	20.1	0.2	32.3
1200	18.5	-25.6	-13.9	-12.0	1.2	0.8	20.1	0.3	32.5
1250	18.2	-25.3	-14.0	-11.9	1.2	0.8	20.2	0.2	32.3
1300	17.9	-25.0	-14.1	-11.9	1.2	0.8	20.3	0.2	32.2
1350	17.6	-24.7	-14.2	-11.9	1.2	0.8	19.9	0.3	32.5
1400	17.3	-24.5	-14.3	-11.9	1.2	0.8	19.9	0.3	32.8
1450	17.1	-24.2	-14.4	-11.9	1.2	0.8	20.1	0.2	32.6
1500	16.8	-24.0	-14.4	-11.8	1.2	0.8	20.3	0.3	33.0
1550	16.5	-23.7	-14.5	-11.9	1.2	0.8	19.5	0.3	33.5
1600	16.3	-23.4	-14.6	-11.8	1.2	0.8	20.3	0.2	33.0
1650	16.1	-23.3	-14.6	-11.9	1.2	0.8	20.1	0.2	33.6
1700	15.8	-23.0	-14.6	-11.9	1.2	0.8	20.6	0.3	33.1
1750	15.6	-22.8	-14.6	-11.8	1.2	0.8	20.1	0.3	33.3
1800	15.4	-22.6	-14.7	-11.9	1.2	0.8	20.2	0.3	33.5
1850	15.2	-22.4	-14.5	-11.9	1.2	0.8	19.8	0.3	34.2
1900	15.0	-22.2	-14.6	-12.1	1.2	0.8	20.2	0.3	34.1
1950	14.8	-22.0	-14.6	-12.0	1.2	0.8	20.0	0.3	33.4
2000	14.6	-21.8	-14.6	-12.0	1.2	0.8	19.6	0.4	34.8
2100	14.1	-21.4	-14.6	-12.2	1.2	0.8	19.8	0.3	33.6
2200	13.8	-21.1	-14.5	-12.3	1.3	0.8	20.1	0.4	34.2
2300	13.4	-20.7	-14.4	-12.4	1.3	0.8	19.9	0.3	33.6
2400	13.1	-20.3	-14.1	-12.6	1.2	0.8	20.0	0.3	33.8
2500	12.8	-20.0	-13.9	-12.7	1.2	0.8	19.9	0.4	33.1
2600	12.4	-19.7	-13.7	-13.0	1.3	0.8	19.9	0.4	33.2
2700	12.1	-19.4	-13.5	-13.3	1.3	0.9	19.2	0.4	33.8
2800	11.8	-19.2	-13.0	-13.7	1.3	0.9	18.6	0.5	33.0
2900	11.5	-18.9	-12.6	-14.3	1.3	0.9	18.8	0.6	33.9
3000	11.3	-18.6	-12.4	-14.8	1.3	0.9	19.5	0.5	33.8
3100	11.0	-18.3	-12.1	-15.4	1.3	0.9	19.6	0.6	33.5
3200	10.8	-18.1	-11.7	-15.8	1.3	0.9	19.7	0.7	34.1
3300	10.5	-17.9	-11.3	-16.6	1.3	0.9	19.6	0.7	33.9
3400	10.3	-17.6	-10.9	-17.5	1.3	0.9	19.4	0.7	34.0
3500	10.1	-17.4	-10.5	-18.2	1.3	0.9	19.8	0.7	34.1
3600	9.8	-17.2	-10.2	-19.3	1.3	0.9	19.9	0.7	34.2
3700	9.6	-16.9	-9.8	-20.2	1.2	0.9	19.2	0.8	34.1
3800	9.4	-16.7	-9.6	-21.4	1.2	1.0	19.7	0.8	33.6
3900	9.2	-16.6	-9.4	-22.6	1.2	1.0	19.3	0.8	33.6
4000	9.0	-16.4	-9.1	-24.2	1.3	1.0	19.6	0.9	34.2

Typical Performance Data

NOTE: Use PDF Bookmarks to view DATA at required conditions

Definitions:

Input Return Loss = S11 (dB)

Gain = S21 (dB)

Isolation = S12 (dB)

Output Return Loss = S22 (dB)

TEST CONDITIONS: $V_{DD} = +5\text{ V}$, $V_{SHUTDOWN} = 0\text{ V}$, $I_{DD} = 60\text{ mA}$, $I_{SHUTDOWN} = 0.0014\text{ }\mu\text{A}$, $R_{LADJ} = 1.5\text{ k}\Omega$ @ Temperature = $+25^\circ\text{C}$

FREQ	Gain	Isolation	Input Return Loss	Output Return Loss	Stability		1dB Comp. Output	Noise Figure	IP-3 Output $P_{OUT} = +4$ dBm/Tone
(MHz)	(dB)	(dB)	(dB)	(dB)	K	Measure	(dBm)	(dB)	(dBm)
10	28.6	-35.2	-8.2	-19.6	1.2	0.9	21.8	3.7	33.5
20	28.7	-34.2	-8.2	-23.3	1.1	0.8	21.1	1.4	32.6
30	28.7	-34.2	-8.4	-23.4	1.1	0.8	21.2	1.7	32.1
40	28.7	-34.2	-8.3	-22.3	1.1	0.8	21.2	0.7	32.5
50	28.7	-33.6	-8.4	-21.7	1.1	0.8	21.0	2.2	32.2
60	28.7	-33.3	-8.5	-21.0	1.1	0.8	21.2	1.3	32.7
70	28.6	-33.4	-8.5	-20.1	1.1	0.8	21.1	0.7	32.1
80	28.6	-33.4	-8.6	-19.4	1.1	0.8	21.2	0.6	31.8
90	28.5	-33.2	-8.5	-19.0	1.1	0.7	21.0	0.7	32.0
100	28.5	-33.6	-8.6	-18.6	1.1	0.8	21.0	0.4	32.4
200	27.8	-33.1	-9.1	-16.1	1.1	0.7	20.7	0.3	31.8
250	27.3	-32.7	-9.5	-15.3	1.1	0.7	20.5	0.3	33.5
300	26.7	-32.5	-10.0	-14.4	1.2	0.7	20.4	0.2	32.8
350	26.2	-32.2	-10.3	-14.1	1.2	0.8	20.5	0.4	32.7
400	25.6	-31.9	-10.8	-13.6	1.2	0.8	20.4	0.3	32.8
450	25.1	-31.1	-11.1	-13.5	1.2	0.7	20.0	0.3	32.9
500	24.5	-31.0	-11.5	-13.2	1.2	0.8	20.1	0.2	33.3
550	24.0	-30.5	-11.9	-13.1	1.2	0.8	20.1	0.2	34.3
600	23.5	-30.1	-12.1	-12.9	1.2	0.8	20.1	0.2	33.7
650	23.0	-29.7	-12.5	-12.8	1.2	0.8	20.3	0.2	34.1
700	22.5	-29.3	-12.8	-12.7	1.2	0.8	20.2	0.1	34.2
750	22.1	-28.8	-13.0	-12.5	1.2	0.8	20.4	0.2	33.7
800	21.7	-28.3	-13.3	-12.5	1.2	0.8	20.0	0.1	34.5
850	21.3	-28.0	-13.5	-12.3	1.2	0.8	20.0	0.3	34.3
900	20.8	-27.5	-13.7	-12.4	1.2	0.8	20.0	0.2	34.0
950	20.5	-27.2	-13.9	-12.3	1.2	0.8	20.2	0.2	34.2
1000	20.0	-26.9	-14.1	-12.3	1.2	0.8	20.1	0.2	34.4
1050	19.7	-26.6	-14.2	-12.2	1.2	0.8	20.1	0.2	34.9
1100	19.4	-26.2	-14.3	-12.1	1.2	0.8	20.1	0.2	33.8
1150	19.0	-25.9	-14.5	-12.1	1.2	0.8	20.2	0.2	34.8
1200	18.7	-25.6	-14.6	-12.2	1.2	0.8	20.2	0.3	34.2
1250	18.4	-25.3	-14.7	-12.1	1.2	0.8	20.3	0.2	34.9
1300	18.1	-25.0	-14.8	-12.1	1.2	0.8	20.5	0.3	34.2
1350	17.8	-24.7	-14.9	-12.1	1.2	0.8	20.0	0.3	35.1
1400	17.5	-24.4	-15.0	-12.1	1.2	0.8	20.0	0.2	35.0
1450	17.2	-24.2	-15.0	-12.1	1.2	0.8	20.2	0.3	34.6
1500	17.0	-23.9	-15.1	-12.0	1.2	0.8	20.3	0.2	35.1
1550	16.7	-23.7	-15.1	-12.1	1.2	0.8	19.6	0.2	35.5
1600	16.5	-23.4	-15.2	-12.0	1.2	0.8	20.3	0.2	35.3
1650	16.2	-23.1	-15.2	-12.1	1.2	0.8	20.2	0.3	35.5
1700	16.0	-22.9	-15.2	-12.1	1.2	0.8	20.6	0.3	35.4
1750	15.8	-22.7	-15.2	-12.0	1.2	0.8	20.2	0.3	35.8
1800	15.5	-22.5	-15.2	-12.1	1.2	0.8	20.3	0.2	36.0
1850	15.4	-22.3	-15.1	-12.1	1.2	0.8	19.8	0.3	36.2
1900	15.1	-22.1	-15.2	-12.2	1.2	0.8	20.2	0.3	36.5
1950	14.9	-21.9	-15.2	-12.2	1.2	0.8	20.0	0.4	36.5
2000	14.7	-21.7	-15.1	-12.2	1.2	0.8	19.6	0.3	37.6
2100	14.3	-21.3	-15.1	-12.4	1.2	0.8	19.8	0.4	36.6
2200	13.9	-20.9	-15.0	-12.5	1.2	0.8	20.1	0.4	36.0
2300	13.6	-20.6	-14.9	-12.6	1.2	0.8	19.9	0.3	35.9
2400	13.3	-20.2	-14.6	-12.8	1.2	0.8	20.1	0.3	36.4
2500	12.9	-19.9	-14.4	-12.9	1.2	0.8	19.9	0.4	35.7
2600	12.6	-19.6	-14.1	-13.2	1.2	0.8	19.9	0.4	35.3
2700	12.3	-19.4	-13.9	-13.5	1.2	0.8	19.2	0.4	36.0
2800	11.9	-19.1	-13.4	-13.9	1.3	0.9	18.7	0.4	34.5
2900	11.7	-18.8	-13.0	-14.6	1.2	0.9	18.8	0.5	35.7
3000	11.4	-18.5	-12.7	-15.1	1.2	0.9	19.5	0.6	35.8
3100	11.2	-18.2	-12.4	-15.7	1.2	0.9	19.6	0.6	36.1
3200	10.9	-18.0	-12.0	-16.1	1.2	0.9	19.7	0.7	36.7
3300	10.6	-17.8	-11.6	-16.9	1.2	0.9	19.6	0.6	36.8
3400	10.4	-17.5	-11.2	-17.9	1.2	0.9	19.4	0.6	35.7
3500	10.2	-17.3	-10.7	-18.7	1.2	0.9	19.8	0.8	36.5
3600	10.0	-17.1	-10.4	-19.8	1.2	0.9	19.9	0.8	37.2
3700	9.8	-16.9	-10.0	-20.8	1.2	0.9	19.2	0.6	36.0
3800	9.6	-16.6	-9.8	-22.1	1.2	0.9	19.7	0.8	36.0
3900	9.4	-16.5	-9.6	-23.5	1.2	0.9	19.3	0.7	35.7
4000	9.2	-16.3	-9.2	-25.3	1.2	1.0	19.6	0.7	36.2

Typical Performance Data

NOTE: Use PDF Bookmarks to view DATA at required conditions

Definitions:

Input Return Loss = S11 (dB)

Gain = S21 (dB)

Isolation = S12 (dB)

Output Return Loss = S22 (dB)

TEST CONDITIONS: $V_{DD} = +5\text{ V}$, $V_{SHUTDOWN} = 0\text{ V}$, $I_{DD} = 70\text{ mA}$, $I_{SHUTDOWN} = 0.0014\text{ }\mu\text{A}$, $RI_{ADJ} = \text{OPEN}$ @ Temperature = $+25^{\circ}\text{C}$

FREQ	Gain	Isolation	Input Return Loss	Output Return Loss	Stability		1dB Comp. Output	Noise Figure	IP-3 Output $P_{OUT} = +4$ dBm/Tone
(MHz)	(dB)	(dB)	(dB)	(dB)	K	Measure	(dBm)	(dB)	(dBm)
10	28.9	-35.0	-8.6	-22.2	1.1	0.9	21.8	3.7	33.7
20	29.1	-34.4	-8.7	-28.2	1.1	0.8	21.2	1.2	36.9
30	29.1	-34.4	-8.8	-28.2	1.1	0.8	21.3	1.4	32.6
40	29.0	-34.1	-8.8	-25.9	1.1	0.8	21.3	0.6	32.5
50	29.0	-33.8	-8.8	-24.9	1.1	0.8	21.3	1.5	32.7
60	29.0	-33.7	-9.0	-23.6	1.1	0.8	21.3	1.0	36.2
70	28.9	-33.7	-9.0	-22.4	1.1	0.8	21.3	0.6	33.5
80	28.9	-33.9	-9.1	-21.2	1.1	0.8	21.5	0.5	33.1
90	28.9	-33.6	-9.0	-20.6	1.1	0.8	21.3	0.7	34.4
100	28.8	-33.7	-9.1	-20.1	1.1	0.8	21.3	0.4	34.3
200	28.0	-33.4	-9.6	-16.8	1.1	0.7	21.2	0.3	33.3
250	27.5	-33.1	-10.1	-15.9	1.2	0.7	20.9	0.3	33.4
300	27.0	-32.8	-10.6	-14.9	1.2	0.7	20.8	0.2	33.8
350	26.4	-32.3	-10.9	-14.5	1.2	0.7	20.9	0.4	34.2
400	25.8	-31.8	-11.3	-13.9	1.2	0.7	20.7	0.2	33.9
450	25.3	-31.5	-11.7	-13.9	1.2	0.7	20.3	0.3	34.4
500	24.7	-30.9	-12.0	-13.4	1.2	0.7	20.3	0.2	35.3
550	24.2	-30.5	-12.4	-13.3	1.2	0.8	20.3	0.2	35.4
600	23.7	-30.2	-12.7	-13.1	1.2	0.8	20.3	0.1	36.9
650	23.2	-29.7	-13.0	-13.0	1.2	0.8	20.4	0.2	36.1
700	22.7	-29.2	-13.4	-12.8	1.2	0.8	20.4	0.2	35.8
750	22.3	-28.8	-13.6	-12.6	1.2	0.8	20.5	0.2	36.1
800	21.8	-28.4	-13.8	-12.7	1.2	0.8	20.1	0.2	36.5
850	21.4	-28.0	-14.0	-12.5	1.2	0.8	20.2	0.2	35.5
900	21.0	-27.5	-14.2	-12.5	1.2	0.8	20.2	0.2	35.5
950	20.6	-27.2	-14.5	-12.5	1.2	0.8	20.3	0.2	36.4
1000	20.2	-26.9	-14.6	-12.4	1.2	0.8	20.2	0.2	36.6
1050	19.8	-26.5	-14.8	-12.3	1.2	0.8	20.3	0.2	36.5
1100	19.5	-26.2	-14.8	-12.3	1.2	0.8	20.2	0.2	35.8
1150	19.2	-25.9	-15.0	-12.3	1.2	0.8	20.3	0.2	36.8
1200	18.8	-25.6	-15.1	-12.3	1.2	0.8	20.3	0.3	36.3
1250	18.5	-25.2	-15.2	-12.2	1.2	0.8	20.4	0.2	36.2
1300	18.2	-25.0	-15.3	-12.2	1.2	0.8	20.5	0.2	36.7
1350	17.9	-24.7	-15.4	-12.2	1.2	0.8	20.1	0.2	35.7
1400	17.6	-24.4	-15.4	-12.2	1.2	0.8	20.0	0.2	37.8
1450	17.4	-24.1	-15.5	-12.2	1.2	0.8	20.3	0.2	37.0
1500	17.1	-23.9	-15.5	-12.2	1.2	0.8	20.4	0.2	37.1
1550	16.9	-23.6	-15.6	-12.2	1.2	0.8	19.7	0.2	38.4
1600	16.6	-23.4	-15.7	-12.1	1.2	0.8	20.4	0.2	37.5
1650	16.4	-23.1	-15.6	-12.2	1.2	0.8	20.2	0.2	37.0
1700	16.1	-22.9	-15.7	-12.2	1.2	0.8	20.7	0.3	36.4
1750	15.9	-22.7	-15.6	-12.1	1.2	0.8	20.2	0.2	36.7
1800	15.7	-22.5	-15.7	-12.2	1.2	0.8	20.3	0.3	37.6
1850	15.5	-22.2	-15.6	-12.3	1.2	0.8	19.9	0.4	38.5
1900	15.3	-22.1	-15.6	-12.4	1.2	0.8	20.3	0.3	37.6
1950	15.0	-21.9	-15.6	-12.3	1.2	0.8	20.1	0.3	38.2
2000	14.9	-21.6	-15.5	-12.3	1.2	0.8	19.7	0.3	40.0
2100	14.4	-21.3	-15.5	-12.5	1.2	0.8	19.8	0.3	38.0
2200	14.1	-20.9	-15.4	-12.6	1.2	0.8	20.1	0.4	37.6
2300	13.7	-20.5	-15.3	-12.7	1.2	0.8	20.0	0.4	40.0
2400	13.4	-20.2	-15.0	-12.9	1.2	0.8	20.1	0.4	39.3
2500	13.1	-19.9	-14.7	-13.1	1.2	0.8	20.0	0.5	38.1
2600	12.7	-19.6	-14.4	-13.3	1.2	0.8	20.0	0.4	39.5
2700	12.4	-19.3	-14.2	-13.7	1.2	0.8	19.2	0.5	38.1
2800	12.0	-19.1	-13.7	-14.0	1.2	0.8	18.7	0.4	36.8
2900	11.8	-18.7	-13.2	-14.8	1.2	0.9	18.8	0.4	38.4
3000	11.6	-18.4	-13.0	-15.3	1.2	0.9	19.5	0.5	38.2
3100	11.3	-18.2	-12.7	-15.9	1.2	0.9	19.7	0.5	38.4
3200	11.0	-17.9	-12.3	-16.3	1.2	0.9	19.7	0.6	37.8
3300	10.8	-17.7	-11.8	-17.2	1.2	0.9	19.6	0.6	38.4
3400	10.5	-17.5	-11.4	-18.1	1.2	0.9	19.5	0.7	39.4
3500	10.3	-17.2	-10.9	-19.0	1.2	0.9	19.7	0.7	40.5
3600	10.1	-17.0	-10.6	-20.2	1.2	0.9	19.9	0.7	38.3
3700	9.9	-16.8	-10.2	-21.3	1.2	0.9	19.3	0.7	38.4
3800	9.7	-16.6	-10.0	-22.6	1.2	0.9	19.7	0.8	38.2
3900	9.5	-16.4	-9.7	-24.2	1.2	0.9	19.3	0.8	38.8
4000	9.3	-16.3	-9.4	-26.3	1.2	0.9	19.6	0.7	38.6

Typical Performance Data

NOTE: Use PDF Bookmarks to view DATA at required conditions

Definitions:

Input Return Loss = S11 (dB)

Gain = S21 (dB)

Isolation = S12 (dB)

Output Return Loss = S22 (dB)

TEST CONDITIONS: $V_{DD} = +5\text{ V}$, $V_{SHUTDOWN} = 0\text{ V}$, $I_{DD} = 72\text{ mA}$, $I_{SHUTDOWN} = 0.0014\text{ }\mu\text{A}$ @ Temperature = +25°C


FREQ	Gain	Isolation	Input Return Loss	Output Return Loss	Stability		1dB Comp. Output	Noise Figure	IP-3 Output $P_{OUT} = +4$ dBm/Tone
(MHz)	(dB)	(dB)	(dB)	(dB)	K	Measure	(dBm)	(dB)	(dBm)
10	-34.4	-59.0	-0.9	-0.6	610.8	0.2	-36.2	34.8	
20	-22.4	-67.5	-0.8	-0.6	317.6	0.2	-35.9	16.8	
30	-15.5	-60.6	-0.9	-0.5	62.2	0.2	-22.0	8.3	
40	-10.8	-62.5	-1.0	-0.5	51.6	0.2	-19.2	5.1	
50	-7.0	-63.2	-0.9	-0.6	37.4	0.2	-15.5	1.7	
60	-4.1	-64.1	-1.0	-0.6	32.5	0.2	-12.6	1.3	
70	-1.5	-58.8	-1.0	-0.6	15.2	0.2	-9.7	2.1	
80	0.8	-60.4	-1.0	-0.6	12.5	0.2	-7.6	1.1	
90	2.6	-58.3	-1.1	-0.6	9.8	0.2	-6.2	0.9	
100	4.4	-56.2	-1.1	-0.6	6.3	0.2	-4.6	0.7	
200	15.3	-45.5	-1.8	-0.8	1.7	0.2	-7.8	0.5	
250	18.4	-42.0	-2.4	-1.2	1.4	0.3	12.3	0.5	
300	20.8	-38.3	-3.0	-1.8	1.3	0.3	14.6	0.5	
350	22.3	-36.2	-3.9	-2.9	1.3	0.5	15.8	0.5	
400	23.3	-34.0	-5.0	-4.3	1.2	0.6	16.6	0.4	
450	23.7	-32.9	-6.3	-6.2	1.2	0.7	17.3	0.5	
500	23.9	-31.7	-7.6	-8.6	1.2	0.7	17.6	0.4	36.4
550	23.7	-30.7	-8.8	-11.2	1.2	0.8	18.0	0.4	36.4
600	23.4	-30.1	-10.0	-14.4	1.2	0.8	18.4	0.4	37.0
650	23.0	-29.5	-11.1	-17.8	1.2	0.8	18.6	0.3	37.1
700	22.6	-29.1	-12.0	-20.8	1.2	0.8	18.6	0.4	37.1
750	22.2	-28.6	-12.8	-21.5	1.2	0.8	18.8	0.4	37.3
800	21.8	-28.2	-13.5	-19.9	1.2	0.8	19.0	0.5	37.0
850	21.3	-27.8	-14.1	-18.1	1.2	0.8	19.0	0.4	38.0
900	20.9	-27.4	-14.7	-16.6	1.2	0.8	19.4	0.4	36.4
950	20.5	-27.1	-15.2	-15.4	1.2	0.8	19.3	0.4	37.7
1000	20.1	-26.7	-15.5	-14.5	1.2	0.8	19.6	0.5	38.0
1050	19.7	-26.4	-15.9	-13.6	1.2	0.8	19.4	0.3	37.1
1100	19.4	-26.1	-16.3	-13.0	1.2	0.8	19.5	0.5	39.0
1150	19.0	-25.8	-16.6	-12.5	1.2	0.8	19.9	0.4	36.3
1200	18.6	-25.5	-16.9	-12.0	1.2	0.8	19.8	0.4	36.6
1250	18.3	-25.2	-17.2	-11.6	1.2	0.8	20.1	0.5	36.6
1300	18.0	-24.9	-17.5	-11.3	1.2	0.8	20.1	0.4	36.6
1350	17.7	-24.7	-17.8	-11.0	1.2	0.8	20.1	0.4	37.0
1400	17.4	-24.4	-18.1	-10.7	1.2	0.8	20.1	0.4	38.0
1450	17.1	-24.2	-18.5	-10.5	1.2	0.8	20.3	0.5	37.1
1500	16.8	-23.9	-18.7	-10.3	1.2	0.8	20.2	0.4	37.2
1550	16.5	-23.7	-19.1	-10.1	1.2	0.7	19.9	0.5	38.5
1600	16.3	-23.5	-19.4	-10.0	1.2	0.7	20.4	0.5	37.5
1650	16.0	-23.2	-19.6	-9.8	1.2	0.7	20.3	0.4	38.2
1700	15.8	-23.0	-19.8	-9.7	1.2	0.7	21.1	0.4	37.6
1750	15.5	-22.8	-20.2	-9.6	1.2	0.7	20.5	0.4	37.0
1800	15.3	-22.5	-20.3	-9.5	1.2	0.7	20.5	0.4	37.8
1850	15.1	-22.3	-20.4	-9.5	1.2	0.7	20.2	0.5	37.3
1900	14.9	-22.2	-20.5	-9.4	1.2	0.7	20.8	0.4	38.2
1950	14.6	-21.9	-20.5	-9.4	1.2	0.7	20.4	0.5	39.3
2000	14.4	-21.7	-20.4	-9.4	1.2	0.7	20.2	0.5	39.1
2100	14.0	-21.4	-20.1	-9.4	1.2	0.7	20.1	0.5	38.6
2200	13.7	-21.0	-19.6	-9.4	1.2	0.7	20.5	0.6	38.7
2300	13.3	-20.6	-19.0	-9.4	1.2	0.7	20.5	0.5	42.6
2400	12.9	-20.3	-18.5	-9.4	1.2	0.7	20.4	0.6	37.9
2500	12.6	-20.0	-18.1	-9.5	1.2	0.7	20.4	0.5	38.7
2600	12.3	-19.7	-17.5	-9.5	1.2	0.8	20.3	0.7	38.0
2700	12.0	-19.4	-17.1	-9.6	1.2	0.8	19.7	0.6	38.9
2800	11.7	-19.1	-16.6	-9.7	1.2	0.8	19.2	0.7	38.8
2900	11.4	-18.9	-16.3	-10.0	1.2	0.8	19.1	0.7	37.6
3000	11.2	-18.5	-16.2	-10.2	1.2	0.8	19.6	0.7	38.8
3100	11.0	-18.2	-16.3	-10.4	1.2	0.8	20.0	0.8	37.1
3200	10.7	-18.0	-16.2	-10.8	1.2	0.8	20.2	0.8	38.2
3300	10.5	-17.7	-15.7	-11.2	1.3	0.8	19.9	0.8	37.8
3400	10.3	-17.4	-15.1	-11.7	1.2	0.8	19.7	1.0	38.2
3500	10.1	-17.2	-14.6	-12.3	1.2	0.8	20.2	1.0	38.6
3600	9.9	-16.9	-13.9	-12.9	1.2	0.8	20.3	0.9	40.3
3700	9.7	-16.7	-13.2	-13.6	1.2	0.8	19.7	0.9	40.4
3800	9.5	-16.4	-12.5	-14.5	1.2	0.9	20.0	1.1	41.5
3900	9.3	-16.3	-11.7	-15.4	1.2	0.9	19.7	1.0	41.3
4000	9.1	-16.1	-11.1	-16.4	1.2	0.9	19.9	1.1	39.0

*Note: Tested with $I_{ADJ} = \text{OPEN}$.


Typical Performance Curves

Note: The following data was taken on the Mini-Circuits Characterization Test Board TB-TSS1-23ULNC+ (Figure 2). All data taken at nominal condition of $V_{DD} = +5\text{ V}$ and at $V_{SHUTDOWN} = 0\text{ V}$ unless noted otherwise.


GAIN vs. TEMPERATURE
 $P_{IN} = -25\text{ dBm}$




GAIN vs. DEVICE VOLTAGE (V_{DD})
 $P_{IN} = -25\text{ dBm}$, TEMPERATURE = +25°C




ISOLATION vs. TEMPERATURE
 $P_{IN} = -25\text{ dBm}$




ISOLATION vs. DEVICE VOLTAGE (V_{DD})
 $P_{IN} = -25\text{ dBm}$, TEMPERATURE = +25°C



INPUT RETURN LOSS vs. TEMPERATURE
 $P_{IN} = -25\text{ dBm}$









INPUT RETURN LOSS vs. DEVICE VOLTAGE (V_{DD})
 $P_{IN} = -25\text{ dBm}$, TEMPERATURE = +25°C









Typical Performance Curves

Note: The following data was taken on the Mini-Circuits Characterization Test Board TB-TSS1-23ULNC+ (Figure 2). All data taken at nominal condition of $V_{DD} = +5\text{ V}$ and at $V_{SHUTDOWN} = 0\text{ V}$ unless noted otherwise.









Typical Performance Curves

Note: The following data was taken on the Mini-Circuits Characterization Test Board TB-TSS1-23ULNC+ (Figure 2). All data taken at nominal condition of $V_{DD} = +5\text{ V}$ and at $V_{SHUTDOWN} = 0\text{ V}$ unless noted otherwise.




Typical Performance Curves

Note: The following data was taken on the Mini-Circuits Characterization Test Board TB-TSS1-23ULNC+ (Figure 2). All data taken at $V_{\text{SHUTDOWN}} = 0$ V unless noted otherwise.









Typical Performance Curves

Note: The following data was taken on the Mini-Circuits Characterization Test Board TB-TSS1-23ULNC+ (Figure 2). All data taken at $V_{\text{SHUTDOWN}} = 0 \text{ V}$ unless noted otherwise.



Typical Performance Curves


Note: The following data was taken on the Mini-Circuits Characterization Test Board TB-TSS1-23ULNC+ by varying R_{IADJ} (Figure 3). All data taken at nominal condition of $V_{DD} = +5$ V and at $V_{SHUTDOWN} = 0$ V unless noted otherwise.



Typical Performance Curves







Note: The following data was taken on the Mini-Circuits Characterization Test Board TB-TSS1-23ULNC+ by varying R_{IADJ} (Figure 3). All data taken at nominal condition of $V_{DD} = +5\text{ V}$ and at $V_{SHUTDOWN} = 0\text{ V}$ unless noted otherwise.

NOISE FIGURE vs. DEVICE CURRENT (I_{DD})
TEMPERATURE = +25°C




Typical Performance Curves


Note: The following data was taken on the Mini-Circuits 700-1000 MHz Matched Characterization Test Board (Figure 4). All data taken at nominal condition of $V_{DD} = +5$ V and at $V_{SHUTDOWN} = 0$ V unless noted otherwise.




Typical Performance Curves

Note: The following data was taken on the Mini-Circuits 700-1000 MHz Matched Characterization Test Board (Figure 4). All data taken at nominal condition of $V_{DD} = +5$ V and at $V_{SHUTDOWN} = 0$ V unless noted otherwise.






TOP VIEW




SIDE VIEW



BOTTOM VIEW

PCB Land Pattern



Suggested Layout,
Tolerance to be within ± 0.050 mm

NOTES:

1.  DENOTES METALLIZATION

Weight: .0036 grams

Dimensions are in mm [inches]. Tolerances: 2 Pl. ± 0.05 mm

Notes:

1. Case material: Plastic.
2. Termination finish: NiPdAu ($3\mu\text{m}/0.080\mu\text{m}/0.080\mu\text{m}$).



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site




The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

RF/IF MICROWAVE COMPONENTS



Tape & Reel Packaging TR-F66



Tape Width, mm	Device Cavity Pitch, mm	Reel Size, inches	Devices per Reel see note	
8	4	7	Small quantity standard	20
				50
				100
				200
				500
		7	Standard	1000, 2000, 3000

Note: Please consult individual model data sheet to determine device per reel availability.

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: www.minicircuits.com/pages/pdfs/tape.pdf




INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified

THIRD ANGLE PROJECTION





REVISIONS

REV	ECN No.	DESCRIPTION	DATE	DR	AUTH
OR	ECO-029191	NEW RELEASE	04/16/26	ITG	IL

SUGGESTED MOUNTING CONFIGURATION FOR KC3011 CASE STYLE

3 LAYER STACKUP DETAIL



COMPONENT	SIZE
R1,R2,R3,R4	0402

NOTES:

- PCB IS MULTILAYER PCB, SEE STACK-UP DIAGRAM.
- TRACE WIDTH & GAP ARE SHOWN FOR ROGERS RO4350B WITH DIELECTRIC THICKNESS .010", COPPER: .5 OZ. EACH LAYER. FOR OTHER MATERIALS TRACE WIDTH & GAP MAY NEED TO BE MODIFIED.
- CHIP COMPONENT FOOT PRINTS SHOWN FOR REFERENCE. FOR COMPONENT VALUES REFER TO TB-TSS1-XXULNC+, WHERE XX=23, 43 & 63.



DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER).



DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK.

UNLESS OTHERWISE SPECIFIED

DIMENSIONS ARE IN INCHES

TOLERANCES ON:
2 PL DECIMALS ±
3 PL DECIMALS ± .005
ANGLES ±
FRACTIONS ±



Mini-Circuits®

THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.

ASHEETA1.DWG REV:A DATE:01/12/95





Mini-Circuits®

13 Neptune Avenue
Brooklyn NY 11235


PL, KC3011, TB-TSS1-XXULNC+

SIZE	CODE IDENT	DRAWING NO:	REV:
A	15542	98-PL-862	OR
FILE:	98PL862	SCALE: 6:1	SHEET: 1 OF 1

Evaluation Board and Circuit



DETAIL "A"
LOCATION OF COMPONENTS
ON THE PCB
(SCALE 3:1)



Component	Size	Value	Part Number	Manufacturer
R1,R2,R3,R4	0402	00hm	RK73Z1ETTP	KOA Speer

NOTES:

1. 50 Ohm SMA Female Connectors.
2. PCB Material: Roger RO4350B or equivalent,
Dielectric constant=3.5, Thickness=0.010 inch





All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-40° to 85° C or -45° to 85° C or -55° to 105° C or -40° to 105° C or -40° to 95° C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C or -65° to 150° Ambient Environment	Individual Model Data Sheet
HTOL	1000 hours at 125°C	MIL-STD-883, Method 1005, Condition B
Thermal Shock	-55° to 100°C, 100 cycles	MIL-STD-202, Method 107, Condition A-3, except +100°C
Mechanical Shock	1.5Kg, 0.5 ms, 5 shock pulses, Y1 direction only	MIL-STD-883, Method 2002, Condition B, except Y1 direction only
Vibration (Variable Frequency)	50g peak	MIL-STD-883, Method 2007, Condition B
Autoclave	15 psig, 100% RH, 121°C, 96 hours	JESD22-A102, Condition C
HAST	130°C, 85% RH, 96 hours	JESD22-A110
Solderability	10X Magnification	J-STD-002, Para 4.2.5, Test S, 95% Coverage
Solder Reflow Heat	Sn-Pb Eutetic Process: 240°C peak Pb-Free Process: 260°C peak	J-STD-020, Table 4-1, 4-2 and 5-2; Figure 5-1
Moisture Sensitivity: Level 1	Bake at 125°C for 24 hours Soak at 85°C/85% RH for 168 hours, Reflow 3 cycles at 260°C peak	J-STD-020



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Marking Resistance to Solvents	Isopropyl alcohol + mineral spirits at 25°C; terpene defluxer at 25°C; distilled water + proylene glycol monomethyl ether + monoethanolamine at 63°C to 70°C	MIL-STD-202, Method 215