

Frequency Mixer

Level 17 (LO Power +17 dBm) 50 to 1000 MHz




CASE STYLE: NNN150

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

Operating Temperature	-55°C to 100°C
Storage Temperature	-55°C to 100°C
RF Power	200mW
IF Current	40mA
Permanent damage may occur if any of these limits are exceeded	


LO	4
RF	1
IF	2
GROUND	3
CASE GROUND	3

NOTE: BLUE BEAD INDICATES PIN #1.
PIN NUMBERS DO NOT APPEAR
ON UNIT FOR REFERENCE ONLY.



A	B	C	D	E	F	G
.50	.48	.255	.240	.23	.21	.06
12.70	12.19	6.48	6.10	5.84	5.33	1.52
H	J	K	L	M	N	wt
.100	.09	.16	.020	.09	.005	grams
2.54	2.29	4.06	0.51	2.29	0.03	1.9

Demo Board MCL PIN: TB-201
Suggested PCB Layout (PL-081)



NOTES: 1. TRACE WIDTH IS SHOWN FOR ROGERS RO4350B WITH DIELECTRIC THICKNESS 0.030 IN. 0.001 IN. COOPER: 1/32 IN. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.

2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.

 DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)

 DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

Notes

- Notes:**
- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
 - B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
 - C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCStore/terms.html.

- low conversion loss, 6.20 dB typ.
- excellent L-R isolation, 47 dB typ.; L-I, 44 dB typ.
- good IP3, 21 dBm typ.
- rugged welded construction

- VHF/UHF
- cellular
- ISM/GSM







Frequency (MHz)		Conversion Loss (dB)				LO-RF Isolation (dB)						LO-IF Isolation (dB)						IP3 @ Center Band (dBm)
LO/Rf	IF	Mid-Band m			Total Range Max.	L		M		U		L		M		U		Typ.
f_L, f_U		$\bar{X}$	σ	Max.		Typ.	Min.	Typ.	Min.	Typ.	Min.	Typ.	Min.	Typ.	Min.	Typ.	Min.	
50-1000	DC-1000	6.20	0.22	7.5	9.0	58	40	47	30	42	25	58	35	44	25	28	18	21

1 dB COMP.: +14 dBm typ.

L = 50-100 MHz M = 100-500 MHz U = upper range [$f_U/2$ to f_U]
m = mid band [$2f$, to $f_U/2$]

Frequency (MHz)		Conversion Loss (dB)	Isolation L-R (dB)	Isolation L-I (dB)	VSWR RF Port (:1)	VSWR LO Port (:1)
RF	LO	LO +17dBm	LO +17dBm	LO +17dBm	LO +17dBm	LO +17dBm
5.00	35.00	5.75	73.03	64.57	1.24	1.51
35.15	65.15	5.75	53.95	50.91	1.10	1.53
65.30	95.30	5.78	47.75	44.94	1.10	1.52
125.61	95.61	5.83	45.94	42.85	1.09	1.44
185.91	155.91	5.88	41.73	38.74	1.09	1.43
216.06	186.06	5.87	40.07	37.26	1.10	1.39
276.37	246.37	5.70	37.49	34.59	1.11	1.38
336.67	306.67	5.62	35.70	32.97	1.11	1.40
396.98	366.98	5.78	35.50	32.29	1.12	1.37
457.28	427.28	6.15	33.92	30.55	1.13	1.36
517.58	487.58	5.88	34.70	29.07	1.15	1.37
547.74	517.74	5.91	35.38	29.45	1.15	1.39
608.04	578.04	6.36	34.75	28.29	1.16	1.38
668.34	638.34	6.50	34.53	27.06	1.17	1.38
728.65	698.65	6.30	33.69	25.41	1.20	1.36
788.95	758.95	6.43	32.39	25.21	1.22	1.45
849.26	819.26	7.56	32.23	24.28	1.26	1.49
909.56	879.56	8.59	32.46	23.91	1.34	1.52
969.86	939.86	8.55	32.66	24.30	1.46	1.54
1000.00	970.00	8.57	32.20	24.05	1.62	1.53

The diagram shows a full-bridge rectifier circuit. It consists of four diodes connected in a bridge configuration. The AC input is connected to the two opposite corners of the bridge. The output is taken from the other two opposite corners, connected to an inductor (represented by a coil) and a DC voltage source (represented by two parallel lines of unequal length). The inductor is connected in series with the DC source.



Notes

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



Frequency Mixer

TUF-2HSM+

Typical Performance Data

RF (IN) (MHz)	LO (MHz)	CONVERSION LOSS IF FIXED @IF(OUT)=30MHz (dB)		
		@LO (dBm)		
		+14	+17	+20
10.1	40.1	7.49	6.47	5.90
51.1	81.1	7.47	6.51	6.04
92.0	122.0	7.43	6.46	5.99
133.0	163.0	7.23	6.34	5.92
173.9	203.9	7.31	6.41	5.95
214.9	244.9	7.20	6.25	5.88
255.8	285.8	7.15	6.26	5.95
296.8	326.8	7.13	6.21	5.95
337.7	367.7	7.02	6.23	6.02
378.7	408.7	6.92	6.22	6.08
419.6	449.6	6.92	6.24	6.09
440.1	470.1	6.81	6.19	6.07
481.1	511.1	6.92	6.32	6.20
501.5	531.5	6.87	6.34	6.21
542.5	572.5	6.98	6.51	6.33
563.0	593.0	6.93	6.51	6.35
603.9	633.9	7.06	6.60	6.48
624.4	654.4	7.02	6.60	6.50
665.3	695.3	7.11	6.67	6.58
685.8	715.8	7.10	6.69	6.59
726.8	756.8	7.18	6.79	6.68
747.2	777.2	7.17	6.83	6.72
788.2	818.2	7.29	6.98	6.88
808.7	838.7	7.35	7.05	6.95
849.6	879.6	7.50	7.23	7.16
870.1	900.1	7.62	7.35	7.29
911.1	941.1	7.83	7.54	7.46
931.5	961.5	8.02	7.66	7.56
972.5	1002.5	8.28	7.78	7.64
993.0	1023.0	8.45	7.82	7.63
1033.9	1063.9	8.86	7.89	7.62
1054.4	1084.4	8.95	7.90	7.58
1095.3	1125.3	9.48	8.08	7.63
1115.8	1145.8	9.74	8.18	7.65
1156.8	1186.8	10.38	8.55	7.85
1177.2	1207.2	10.68	8.74	7.85
1218.2	1248.2	11.37	9.29	8.13
1238.7	1268.7	11.52	9.43	8.22
1279.6	1309.6	12.12	9.95	8.64
1300.1	1330.1	12.52	10.30	8.89

RF (IN) (MHz)	LO (MHz)	IP3 INPUT (dBm)		
		@LO (dBm)		
		+14	+17	+20
10.1	40.1	22.26	26.49	29.40
51.1	81.1	22.06	25.46	29.44
92.0	122.0	21.94	25.10	27.69
133.0	163.0	24.06	26.83	25.79
173.9	203.9	23.00	24.77	25.45
214.9	244.9	23.69	23.02	29.32
255.8	285.8	22.91	25.23	24.39
296.8	326.8	20.77	27.16	22.42
337.7	367.7	22.30	27.02	22.54
378.7	408.7	22.94	23.10	22.83
419.6	449.6	23.59	21.83	22.50
440.1	470.1	31.36	20.58	22.15
481.1	511.1	28.73	19.96	21.03
501.5	531.5	25.93	20.35	21.76
542.5	572.5	23.01	20.45	22.47
563.0	593.0	21.92	20.79	23.44
603.9	633.9	20.87	20.57	22.63
624.4	654.4	19.90	20.64	22.49
665.3	695.3	19.63	20.75	22.28
685.8	715.8	19.28	21.10	22.39
726.8	756.8	17.99	20.74	22.66
747.2	777.2	17.76	20.13	22.79
788.2	818.2	16.78	18.38	21.79
808.7	838.7	16.08	17.79	20.93
849.6	879.6	15.61	17.04	18.96
870.1	900.1	15.47	16.96	18.99
911.1	941.1	14.99	16.37	18.59
931.5	961.5	15.16	16.56	18.93
972.5	1002.5	15.19	17.20	20.10
993.0	1023.0	14.97	17.78	21.32
1033.9	1063.9	14.70	19.20	23.21
1054.4	1084.4	14.89	20.00	24.11
1095.3	1125.3	14.18	20.61	25.36
1115.8	1145.8	13.89	20.86	26.17
1156.8	1186.8	13.48	20.13	27.69
1177.2	1207.2	13.08	19.11	28.62
1218.2	1248.2	13.07	17.78	28.45
1238.7	1268.7	13.35	17.81	27.56
1279.6	1309.6	13.53	17.82	24.90
1300.1	1330.1	13.80	17.98	24.60

RF (IN) (MHz)	LO (MHz)	COMPRESSION @RF IN=+14dBm (dB)		
		@LO (dBm)		
		+14	+17	+20
10.1	40.1	0.65	0.28	0.14
51.1	81.1	0.78	0.25	0.13
92.0	122.0	0.53	0.24	0.12
133.0	163.0	0.80	0.31	0.17
173.9	203.9	0.49	0.22	0.15
214.9	244.9	0.69	0.30	0.19
255.8	285.8	0.76	0.36	0.17
296.8	326.8	0.71	0.36	0.19
337.7	367.7	0.89	0.33	0.15
378.7	408.7	0.98	0.36	0.15
419.6	449.6	0.99	0.40	0.18
440.1	470.1	1.06	0.43	0.19
481.1	511.1	1.04	0.39	0.19
501.5	531.5	1.12	0.40	0.18
542.5	572.5	1.08	0.36	0.18
563.0	593.0	1.24	0.39	0.21
603.9	633.9	1.20	0.38	0.21
624.4	654.4	1.29	0.46	0.25
665.3	695.3	1.35	0.49	0.27
685.8	715.8	1.29	0.52	0.26
726.8	756.8	1.40	0.55	0.31
747.2	777.2	1.44	0.57	0.33
788.2	818.2	1.43	0.58	0.34
808.7	838.7	1.47	0.62	0.35
849.6	879.6	1.57	0.72	0.38
870.1	900.1	1.50	0.61	0.35
911.1	941.1	1.56	0.66	0.31
931.5	961.5	1.54	0.61	0.26
972.5	1002.5	1.45	0.60	0.23
993.0	1023.0	1.41	0.65	0.24
1033.9	1063.9	1.32	0.71	0.30
1054.4	1084.4	1.19	0.70	0.34
1095.3	1125.3	0.84	0.74	0.40
1115.8	1145.8	0.68	0.74	0.43
1156.8	1186.8	0.14	0.57	0.45
1177.2	1207.2	-0.07	0.53	0.52
1218.2	1248.2	-0.49	0.31	0.55
1238.7	1268.7	-0.71	0.21	0.55
1279.6	1309.6	-1.10	-0.03	0.43
1300.1	1330.1	-1.25	-0.17	0.39

Frequency Mixer

TUF-2HSM+

Typical Performance Data

IF (OUT) (MHz)	LO (MHz)	CONVERSION LOSS VS. IF FREQUENCY @RF(IN)=500.1MHz (dB)	IF (OUT) (MHz)	LO (MHz)	CONVERSION LOSS VS. IF FREQUENCY @RF(IN)=50.1MHz (dB)	IF (OUT) (MHz)	LO (MHz)	CONVERSION LOSS VS. IF FREQUENCY @RF(IN)=1000.1MHz (dB)
		@LO (dBm)			@LO (dBm)			@LO (dBm)
		+17			+17			+17
400.0	100.1	6.49	10.0	60.1	6.47	950.0	50.1	7.82
390.3	109.9	6.51	30.0	80.1	6.56	930.0	70.1	7.77
380.5	119.6	6.51	50.0	100.1	6.39	910.0	90.1	7.79
370.8	129.4	6.44	70.0	120.1	6.46	890.0	110.1	7.61
361.0	139.1	6.45	90.0	140.1	6.50	870.0	130.1	7.54
351.3	148.9	6.32	110.0	160.1	6.42	850.0	150.1	7.55
341.5	158.6	6.37	130.0	180.1	6.52	830.0	170.1	7.57
331.8	168.4	6.41	150.0	200.1	6.50	810.0	190.1	7.42
322.0	178.1	6.32	170.0	220.1	6.53	790.0	210.1	7.33
312.3	187.9	6.40	190.0	240.1	6.46	770.0	230.1	7.24
302.5	197.6	6.34	210.0	260.1	6.53	750.0	250.1	7.24
292.8	207.4	6.23	230.0	280.1	6.64	730.0	270.1	7.21
283.0	217.1	6.25	250.0	300.1	6.51	710.0	290.1	7.12
273.3	226.9	6.15	270.0	320.1	6.51	690.0	310.1	7.19
263.5	236.6	6.18	290.0	340.1	6.56	670.0	330.1	7.17
253.8	246.4	6.17	310.0	360.1	6.58	650.0	350.1	7.24
244.0	256.1	6.11	330.0	380.1	6.52	630.0	370.1	7.27
234.3	265.9	6.20	350.0	400.1	6.51	610.0	390.1	7.28
224.5	275.6	6.17	370.0	420.1	6.57	590.0	410.1	7.35
214.8	285.4	6.11	390.0	440.1	6.45	570.0	430.1	7.38
205.0	295.1	6.17	410.0	460.1	6.51	550.0	450.1	7.47
195.3	304.9	6.14	430.0	480.1	6.53	530.0	470.1	7.46
185.5	314.6	6.13	450.0	500.1	6.47	510.0	490.1	7.50
175.8	324.4	6.13	470.0	520.1	6.41	490.0	510.1	7.51
166.0	334.1	6.16	510.0	560.1	6.49	450.0	550.1	7.62
156.3	343.9	6.18	530.0	580.1	6.44	430.0	570.1	7.56
146.5	353.6	6.15	570.0	620.1	6.50	390.0	610.1	7.59
136.8	363.4	6.17	590.0	640.1	6.49	370.0	630.1	7.63
127.0	373.1	6.25	630.0	680.1	6.62	330.0	670.1	7.60
117.3	382.9	6.18	650.0	700.1	6.63	310.0	690.1	7.66
107.5	392.6	6.18	690.0	740.1	6.63	270.0	730.1	7.65
97.8	402.4	6.23	710.0	760.1	6.67	250.0	750.1	7.70
88.0	412.1	6.21	750.0	800.1	6.67	210.0	790.1	7.79
78.3	421.9	6.19	770.0	820.1	6.61	190.0	810.1	7.83
68.5	431.6	6.23	810.0	860.1	6.58	150.0	850.1	7.96
58.8	441.4	6.25	830.0	880.1	6.52	130.0	870.1	7.96
49.0	451.1	6.26	870.0	920.1	6.41	90.0	910.1	8.01
39.3	460.9	6.26	890.0	940.1	6.40	70.0	930.1	8.02
19.8	480.4	6.35	930.0	980.1	6.35	30.0	970.1	8.02
10.0	490.1	6.35	950.0	1000.1	6.32	10.0	990.1	7.93

REV. X2
TUF-2HSM+
100818
Page 2 of 5



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED • RoHS compliant
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see



Frequency Mixer

TUF-2HSM+

Typical Performance Data

LO (MHz)	LO-RF ISOLATION (dB)			LO-IF ISOLATION (dB)		
	@LO (dBm)			@LO (dBm)		
	+14	+17	+20	+14	+17	+20
10.1	70.94	74.41	77.00	61.80	62.70	62.57
51.1	59.58	61.76	63.70	58.56	61.13	62.32
92.0	54.72	56.70	58.69	55.36	59.26	60.73
133.0	51.54	53.70	55.84	52.66	57.79	58.69
173.9	49.31	51.39	53.46	50.64	55.36	57.73
214.9	47.65	49.77	52.06	48.67	53.89	55.66
255.8	46.20	48.52	50.91	46.94	52.27	51.68
296.8	45.07	47.28	49.99	45.67	49.91	49.69
337.7	44.10	46.34	49.00	44.42	46.40	47.10
378.7	43.07	45.77	48.27	43.19	43.68	45.07
419.6	42.19	45.45	48.32	41.98	42.27	44.30
440.1	41.91	45.26	48.25	40.44	41.09	43.19
481.1	41.23	44.05	46.60	39.21	39.96	41.81
501.5	40.70	43.75	46.04	38.09	39.19	41.03
542.5	39.97	42.45	44.60	36.96	37.84	39.41
563.0	39.62	41.77	43.92	36.07	37.16	38.63
603.9	39.31	41.20	43.40	35.15	36.61	38.09
624.4	39.06	40.90	43.26	34.40	36.07	37.79
665.3	39.11	41.05	43.23	33.39	35.26	37.35
685.8	38.98	41.24	43.32	32.97	35.02	37.07
726.8	39.34	42.45	44.86	32.24	34.36	36.26
747.2	39.51	42.97	45.53	31.94	34.09	35.89
788.2	39.67	43.16	45.62	31.54	33.58	35.11
808.7	39.66	42.80	44.90	31.21	33.29	34.65
849.6	39.90	42.55	43.90	30.63	32.72	33.75
870.1	39.40	41.79	43.11	30.11	32.22	33.54
911.1	38.93	40.69	41.46	29.52	31.53	32.85
931.5	38.57	40.02	40.79	29.20	31.14	32.49
972.5	37.80	39.09	40.11	28.49	30.16	31.48
993.0	37.22	38.45	39.55	28.27	29.88	31.12
1033.9	36.41	38.02	39.27	27.56	29.04	30.08
1054.4	35.55	37.24	38.80	27.19	28.45	29.63
1095.3	34.37	36.15	37.64	26.67	27.74	28.78
1115.8	33.79	35.65	37.17	26.32	27.41	28.42
1156.8	32.63	34.44	36.07	25.84	26.66	27.60
1177.2	32.28	33.93	35.45	25.65	26.40	27.30
1218.2	31.57	33.17	34.81	25.21	25.83	26.61
1238.7	31.12	32.79	34.48	24.93	25.60	26.37
1279.6	30.72	32.22	33.80	24.70	25.28	25.91
1300.1	30.52	32.09	33.63	24.57	25.33	25.93

RF (IN) (MHz)	LO (MHz)	RF-IF ISOLATION (dB)		
		@LO (dBm)		
		+14	+17	+20
10.1	40.1	47.85	48.27	47.51
51.1	81.1	33.41	33.69	33.99
92.0	122.0	28.69	28.99	29.35
133.0	163.0	25.89	26.38	26.65
173.9	203.9	23.97	24.42	24.83
214.9	244.9	22.67	23.31	23.66
255.8	285.8	21.96	22.51	23.01
296.8	326.8	21.38	22.12	22.50
337.7	367.7	20.91	22.03	22.42
378.7	408.7	20.67	21.84	22.48
419.6	449.6	20.58	21.64	22.43
440.1	470.1	20.98	21.93	22.81
481.1	511.1	21.36	21.95	22.46
501.5	531.5	21.96	22.48	22.67
542.5	572.5	22.32	23.03	23.15
563.0	593.0	22.44	22.95	23.19
603.9	633.9	22.28	22.61	23.13
624.4	654.4	21.65	21.99	22.79
665.3	695.3	20.12	20.56	21.45
685.8	715.8	19.30	19.68	20.55
726.8	756.8	17.63	17.89	18.36
747.2	777.2	17.06	17.13	17.38
788.2	818.2	15.97	15.75	15.60
808.7	838.7	15.55	15.36	15.17
849.6	879.6	14.92	14.60	14.40
870.1	900.1	14.57	14.19	13.93
911.1	941.1	14.18	13.74	13.53
931.5	961.5	13.93	13.51	13.36
972.5	1002.5	13.65	13.27	13.07
993.0	1023.0	13.55	13.15	12.91
1033.9	1063.9	13.36	12.91	12.56
1054.4	1084.4	13.23	12.76	12.37
1095.3	1125.3	13.03	12.53	12.16
1115.8	1145.8	12.86	12.40	12.04
1156.8	1186.8	12.57	12.19	11.89
1177.2	1207.2	12.44	12.14	11.89
1218.2	1248.2	12.18	12.04	11.93
1238.7	1268.7	12.06	12.02	12.01
1279.6	1309.6	11.80	11.91	12.05
1300.1	1330.1	11.63	11.78	11.96

Frequency Mixer

TUF-2HSM+

Typical Performance Data

RF (IN) (MHz)	LO (MHz)	RF VSWR (:1)			LO (MHz)	LO VSWR (:1)			IF (OUT) (MHz)	IF VSWR @LO=1000.1MHz (:1)		
		@LO (dBm)				@LO (dBm)				@LO (dBm)		
		+14	+17	+20		+14	+17	+20		+14	+17	+20
10.1	40.1	1.34	1.14	1.07	10.1	1.09	1.49	2.09	10.0	2.90	2.34	2.10
51.1	81.1	1.36	1.16	1.05	51.1	1.06	1.53	2.29	30.2	2.69	2.14	1.91
92.0	122.0	1.38	1.17	1.05	92.0	1.04	1.47	2.17	50.4	2.56	2.03	1.80
133.0	163.0	1.35	1.15	1.04	133.0	1.06	1.49	2.22	70.6	2.58	2.05	1.82
173.9	203.9	1.35	1.17	1.06	173.9	1.05	1.45	2.10	90.8	2.59	2.06	1.84
214.9	244.9	1.35	1.15	1.07	214.9	1.05	1.46	2.13	111.0	2.64	2.11	1.88
255.8	285.8	1.34	1.15	1.09	255.8	1.06	1.45	2.12	131.2	2.71	2.16	1.92
296.8	326.8	1.36	1.15	1.10	296.8	1.06	1.43	2.07	151.4	2.65	2.11	1.89
337.7	367.7	1.34	1.14	1.11	337.7	1.06	1.46	2.13	171.6	2.56	2.05	1.83
378.7	408.7	1.31	1.12	1.13	378.7	1.07	1.42	2.10	191.8	2.63	2.11	1.89
419.6	449.6	1.31	1.11	1.13	419.6	1.08	1.44	2.10	212.0	2.68	2.16	1.94
440.1	470.1	1.28	1.11	1.14	440.1	1.08	1.45	2.10	232.2	2.61	2.11	1.89
481.1	511.1	1.28	1.10	1.12	481.1	1.08	1.42	2.06	252.4	2.59	2.09	1.87
501.5	531.5	1.25	1.11	1.13	501.5	1.11	1.44	2.07	272.7	2.66	2.15	1.94
542.5	572.5	1.25	1.12	1.14	542.5	1.11	1.46	2.09	292.9	2.64	2.16	1.96
563.0	593.0	1.23	1.12	1.15	563.0	1.12	1.46	2.08	313.1	2.59	2.12	1.92
603.9	633.9	1.23	1.13	1.16	603.9	1.13	1.46	2.08	333.3	2.65	2.16	1.96
624.4	654.4	1.22	1.14	1.17	624.4	1.14	1.47	2.10	353.5	2.66	2.19	1.99
665.3	695.3	1.21	1.14	1.17	665.3	1.15	1.47	2.07	373.7	2.59	2.14	1.96
685.8	715.8	1.19	1.14	1.19	685.8	1.16	1.48	2.07	393.9	2.59	2.14	1.95
726.8	756.8	1.17	1.13	1.17	726.8	1.17	1.50	2.09	434.3	2.60	2.16	2.00
747.2	777.2	1.16	1.12	1.17	747.2	1.18	1.53	2.11	454.5	2.58	2.13	1.97
788.2	818.2	1.14	1.09	1.13	788.2	1.19	1.51	2.08	494.9	2.63	2.19	2.03
808.7	838.7	1.12	1.08	1.12	808.7	1.21	1.53	2.10	515.1	2.54	2.11	1.96
849.6	879.6	1.12	1.05	1.07	849.6	1.21	1.56	2.10	555.5	2.61	2.18	2.02
870.1	900.1	1.12	1.05	1.07	870.1	1.23	1.53	2.09	575.7	2.59	2.17	2.02
911.1	941.1	1.16	1.09	1.10	911.1	1.24	1.55	2.11	616.1	2.57	2.13	1.97
931.5	961.5	1.19	1.12	1.13	931.5	1.25	1.58	2.15	636.3	2.55	2.13	1.98
972.5	1002.5	1.26	1.20	1.22	972.5	1.27	1.56	2.09	676.7	2.60	2.15	1.99
993.0	1023.0	1.30	1.24	1.26	993.0	1.28	1.56	2.09	696.9	2.63	2.17	2.00
1033.9	1063.9	1.40	1.34	1.35	1033.9	1.30	1.59	2.09	737.3	2.50	2.05	1.88
1054.4	1084.4	1.43	1.37	1.38	1054.4	1.31	1.57	2.09	757.6	2.57	2.12	1.93
1095.3	1125.3	1.55	1.47	1.47	1095.3	1.33	1.60	2.10	798.0	2.55	2.07	1.87
1115.8	1145.8	1.61	1.51	1.51	1115.8	1.34	1.62	2.14	818.2	2.52	2.04	1.83
1156.8	1186.8	1.73	1.62	1.60	1156.8	1.35	1.64	2.14	858.6	2.48	2.01	1.81
1177.2	1207.2	1.79	1.67	1.64	1177.2	1.36	1.66	2.15	878.8	2.52	2.04	1.81
1218.2	1248.2	1.91	1.79	1.74	1218.2	1.37	1.69	2.17	919.2	2.49	1.99	1.74
1238.7	1268.7	1.96	1.84	1.79	1238.7	1.37	1.69	2.18	939.4	2.40	1.92	1.68
1279.6	1309.6	2.08	1.96	1.89	1279.6	1.39	1.71	2.20	979.8	2.48	1.99	1.73
1300.1	1330.1	2.13	2.01	1.94	1300.1	1.40	1.74	2.22	1000.0	2.21	1.86	1.77

REV. X2
TUF-2HSM+
100818
Page 4 of 5



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED • RoHS compliant
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, instantly • For detailed performance specs & shopping online see



Harmonics Tables

RF HARMONICS ORDER

	(-dBm)	(-dBc)										
0	-	-	14	31	16	30	40	39	33	36	41	56
1	-	16	+0	23	13	32	28	37	38	32	41	36
2	90	59	51	54	50	61	48	58	84	75	59	57
3	>100	64	52	77	51	63	50	68	56	71	65	64
4	>100	80	>93	82	89	87	86	84	>93	89	86	92
5	>100	>93	86	87	83	87	80	83	79	88	86	>93
6	>100	>93	>93	>93	>93	>93	>93	>93	>93	>93	93	>93
7	>100	>93	>93	>93	>93	>93	>93	>93	>93	>93	>93	>93
8	>100	>93	>93	>93	>93	>93	>93	>93	>93	>93	>93	>93
9	>100	>93	>93	>93	>93	>93	>93	>93	>93	>93	>93	>93
10	>100	>93	>93	>93	>93	>93	>93	>93	>93	>93	>93	>93
	RF CAL	0	1	2	3	4	5	6	7	8	9	10

LO HARMONICS ORDER

Test conditions: RF IN: 500.1 MHz; -1.00 dBm.
LO IN: 530.01 MHz; +17.00 dBm
IF OUT: 29.91 MHz; -7.4 dBm

RF HARMONICS ORDER

	(-dBm)	(-dBc)										
0	-	-	25	44	29	48	53	50	55	48	64	69
1	-	16	+0	25	13	32	28	41	45	40	52	41
2	74	58	46	52	43	64	42	55	65	66	56	59
3	>100	49	37	52	38	46	37	58	50	52	51	48
4	>100	65	65	66	60	61	59	64	56	64	77	77
5	>100	83	53	60	50	62	49	56	48	68	55	70
6	>100	83	80	73	75	72	69	72	69	71	68	77
7	>100	77	86	80	65	66	62	68	62	65	61	73
8	>100	91	97	89	89	85	81	86	77	81	76	79
9	>100	91	93	92	90	82	75	72	70	73	71	72
10	>100	91	94	96	>103	101	96	>103	85	99	83	86
	RF CAL	0	1	2	3	4	5	6	7	8	9	10

LO HARMONICS ORDER

Test conditions: RF IN: 500.1 MHz; 9.00 dBm.
LO IN: 530.01 MHz; +17.00 dBm
IF OUT: 29.91 MHz; 2.61 dBm

- Notes: 1. All Harmonics are in (dBc) relative to IF OUTPUT.
2. + entry denotes harmonics are in (dBc) above IF OUTPUT.
3. RF Cal represent the Harmonics level of the RF input signal to the mixer.

REV. X2
TUF-2HSM+
100818
Page 5 of 5




Frequency Mixer


TUF-2HSM+

Typical Performance Curves


Conversion Loss @ IF=30MHz




Conversion Loss vs. IF @ RF=500.1MHz




Conversion Loss vs. IF @ RF=50.1MHz




Conversion Loss vs. IF @ RF=1000.1MHz



IP3 Input




Compression @ RF IN=+14dBm




Typical Performance Curves


LO-RF Isolation




LO-IF Isolation




RF-IF Isolation




RF VSWR



LO VSWR



IF VSWR



Harmonics Tables

RF HARMONICS ORDER

	(-dBm)	(-dBc)										
0	-	-	14	31	16	30	40	39	33	36	41	56
1	-	16	+0	23	13	32	28	37	38	32	41	36
2	90	59	51	54	50	61	48	58	84	75	59	57
3	>100	64	52	77	51	63	50	68	56	71	65	64
4	>100	80	>93	82	89	87	86	84	>93	89	86	92
5	>100	>93	86	87	83	87	80	83	79	88	86	>93
6	>100	>93	>93	>93	>93	>93	>93	>93	>93	>93	93	>93
7	>100	>93	>93	>93	>93	>93	>93	>93	>93	>93	>93	>93
8	>100	>93	>93	>93	>93	>93	>93	>93	>93	>93	>93	>93
9	>100	>93	>93	>93	>93	>93	>93	>93	>93	>93	>93	>93
10	>100	>93	>93	>93	>93	>93	>93	>93	>93	>93	>93	>93
RF CAL	0	1	2	3	4	5	6	7	8	9	10	

LO HARMONICS ORDER

Test conditions: RF IN: 500.1 MHz; -1.00 dBm.
LO IN: 530.01 MHz; +17.00 dBm
IF OUT: 29.91 MHz; -7.4 dBm

RF HARMONICS ORDER

	(-dBm)	(-dBc)										
0	-	-	25	44	29	48	53	50	55	48	64	69
1	-	16	+0	25	13	32	28	41	45	40	52	41
2	74	58	46	52	43	64	42	55	65	66	56	59
3	>100	49	37	52	38	46	37	58	50	52	51	48
4	>100	65	65	66	60	61	59	64	56	64	77	77
5	>100	83	53	60	50	62	49	56	48	68	55	70
6	>100	83	80	73	75	72	69	72	69	71	68	77
7	>100	77	86	80	65	66	62	68	62	65	61	73
8	>100	91	97	89	89	85	81	86	77	81	76	79
9	>100	91	93	92	90	82	75	72	70	73	71	72
10	>100	91	94	96	>103	101	96	>103	85	99	83	86
RF CAL	0	1	2	3	4	5	6	7	8	9	10	

LO HARMONICS ORDER

Test conditions: RF IN: 500.1 MHz; 9.00 dBm.
LO IN: 530.01 MHz; +17.00 dBm
IF OUT: 29.91 MHz; 2.61 dBm

- Notes: 1. All Harmonics are in (dBc) relative to IF OUTPUT.
2. + entry denotes harmonics are in (dBc) above IF OUTPUT.
3. RF Cal represent the Harmonics level of the RF input signal to the mixer.


REV. X2
TUF-2HSM+
100818
Page 3 of 3




Outline Dimensions

NNN150

NOTE: BLUE BEAD INDICATES PIN #1.
PIN NUMBERS DO NOT APPEAR
ON UNIT.FOR REFERENCE ONLY.



PCB Land Pattern



Suggested Layout,
Tolerance to be within $\pm .002$

CASE #.	A	B	C	D	E	F	G	H	J	K	L	M	N	WT, GRAM
NNN150	.50 (12.70)	.48 (12.19)	.255 (6.48)	.240 (6.10)	.23 (5.84)	.21 (5.33)	.06 (1.52)	.100 (2.54)	.09 (2.29)	.16 (4.06)	.020 (0.51)	.09 (2.29)	.005 (0.13)	1.9

Dimensions are in inches (mm). Tolerances: 2 Pl. $\pm .03$; 3 Pl. $\pm .015$

Notes:

- Header material C.R.S. Pin material #52 alloy.
- Finish: Electro-Tin, hot-oil flowed or electro-Tin-Silver.
- Cover material: Cupro-Nickel.
- Pin's meniscus 0.015 inch max.
- Special Tolerances: Pin diameter $\pm .005$ inch.




INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified

Tape & Reel Packaging TR-F9



Tape Width, mm	Device Cavity Pitch, mm	Reel Size, inches	Devices per Reel
24	16	13	500

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: www.minicircuits.com/pages/pdfs/tape.pdf




INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified


THIRD ANGLE PROJECTION



REVISIONS

REV	ECN No.	DESCRIPTION	DATE	DR	AUTH
OR	M86549	NEW RELEASE	04/15/03	GF	DJ
A	M102713	UPDATED NOTES & DISCRIPTION	01/14/06	GF	IL


**SUGGESTED MOUNTING CONFIGURATION
FOR NNN150 CASE STYLE, "z"/"cm" PIN CONNECTIONS.**



NOTES: 1. TRACE WIDTH IS SHOWN FOR ROGERS R04350B WITH DIELECTRIC THICKNESS 0.030" $\pm$ 0.002"; COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.

2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.

 DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)

 DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

UNLESS OTHERWISE SPECIFIED

INITIALS

DATE

DIMENSIONS ARE IN INCHES

TOLERANCES ON:

2 PL DECIMALS $\pm$ 3 PL DECIMALS $\pm$.005ANGLES $\pm$ FRACTIONS $\pm$
 Mini-Circuits®

THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.

ASHEETA1.DWG REV:A DATE:01/12/95



Mini-Circuits®

13 Neptune Avenue
Brooklyn NY 11235

PL, z/cm NNN150, TUF/TFAS-SM, TB-201


SIZE
ACODE IDENT
15542DRAWING NO:
98-PL-081REV:
A

FILE: 98PL081


SCALE: 6:1

SHEET: 1 OF 1

Evaluation Board and Circuit



TB-201



Schematic Diagram

Notes:

1. SMA Female connectors.
2. PCB Material: Rogers R04350 or equivalent,
Dielectric Constant=3.5, Thickness=.030 inch.

 **Mini-Circuits®**



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-55° to 100°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Thermal Shock	-55° to 100°C, 100 cycles	MIL-STD-202, Method 107, Condition A-3, except +100°C
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes	MIL-STD-202, Method 213, Condition A
Moisture Resistance	10 cycles, 24 hours per cycle	MIL-STD-202, Method 106, Condition A, except 50°C and end point electrical test done within 12 hours
Solderability	10X Magnification	J-STD-002, 95% Coverage
Resistance to Solder Heat	260°C for 10 seconds	MIL-STD-202, Method 210, Condition B
Marking Resistance to Solvents	Isopropyl alcohol + mineral spirits at 25°C; terpene defluxer at 25°C; distilled water + proylene glycol monomethyl ether + monoethanolamine at 63°C to 70°C	MIL-STD-202, Method 215
Terminal Strength	4 1/2 Pound Pull	MIL-STD-202, Method 211, Condition A



Environmental Specifications

ENV30

All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Barometric Pressure	100,000 Feet	MIL-STD-202, Method 105, Condition D