



MMIC DIE

Low Noise Amplifier

TSY-83LN-D+

50Ω 400 to 8000 MHz Bypass Mode Feature


THE BIG DEAL

- Low Loss Bypass Mode Feature
- Low Noise Figure, Typ. 1.4 dB
- High OIP3, Typ. +34.6 dBm
- High P1dB, Typ. +22.8 dBm

APPLICATIONS

- Radar, EW, and ECM Defense Systems
- 5G Sub6, MIMO Wireless Infrastructure Systems
- Test & Measurement Equipment

FUNCTIONAL DIAGRAM



SEE ORDERING INFORMATION ON THE LAST PAGE

PRODUCT OVERVIEW

Mini-Circuits' TSY-83LN-D+ is a GaAs pHEMT-based wideband, bypass mode-capable, low noise MMIC amplifier with a combination of high IP3 and flat gain. Operating from 400 to 8000 MHz, this amplifier features high dynamic range with 1.4 dB noise figure, 23 dB gain, +22.8 dBm P1dB, and +34.6 dBm OIP3. This combination of characteristics makes it ideal for sensitive, high dynamic range receiver applications where a gain stage may need to be quickly bypassed and shut down in the presence of high power RF signals. TSY-83LN-D+ operates on a single +5 V or +6 V supply and is well-matched to 50Ω.

KEY FEATURES

Features	Advantages
Bypass Mode Feature	Allows the user to quickly switch to a low loss bypass path while keeping the power supply at constant voltage to reduce gain and protect the system in the presence of high power RF signals while minimizing power consumption.
Low Noise Figure, Typ. 1.4 dB at 2000 MHz	Extremely low noise figure provides minimal signal-to-noise degradation in amplification mode.
High OIP3, Typ. +34.6 dBm at 2000 MHz	The combination of low noise figure and high IP3 makes this MMIC amplifier ideal for use in sensitive low noise receiver front ends where high dynamic range is of paramount importance.
Wide Bandwidth with Flat Gain: ±0.9 dB over 400 to 6000 MHz	Enables a single amplifier to be used across many applications including aerospace and defense (Radar, SAT-COM, EW), broadband test instrumentation, telecommunications (5G Sub6), and more.
Unpackaged Die	Suitable for chip and wire hybrid assemblies.

REV. OR
ECO-026824
TSY-83LN-D+
MCL NY
250902

www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

PAGE 1 OF 17



MMIC DIE

Low Noise Amplifier

TSY-83LN-D+

Mini-Circuits

50Ω 400 to 8000 MHz Bypass Mode Feature

ELECTRICAL SPECIFICATIONS¹ AT +25°C, V_{DD} = +6 V, AND Z_O = 50Ω UNLESS NOTED OTHERWISE

Parameter	Condition (MHz)	Amplifier - ON			Amplifier - Bypass	Units
		Min.	Typ.	Max.		
Frequency Range		400		8000	400-8000	MHz
Gain	400		22.2		-1.3	dB
	2000		22.8		-0.8	
	4000		23.0		-1.2	
	6000		24.0		-1.6	
	8000 ²		23.8		-3.0	
Input Return Loss	400		13		9	dB
	2000		18		17	
	4000		12		14	
	6000		20		9	
	8000 ²		8		6	
Output Return Loss	400		14		13	dB
	2000		20		17	
	4000		18		20	
	6000		20		10	
	8000 ²		12		6	
Isolation	400-8000		28.7			dB
Output Power at 1 dB Compression (P _{1dB})	400		+22.2		+12.2	dBm
	2000		+22.8		+13.3	
	4000		+22.1		+15.5	
	6000		+21.4		+15.6	
	8000 ²		+21.0		+15.5	
Output Third-Order Intercept Point (P _{OUT} = 0 dBm/Tone)	400		+37.2		+41.9	dBm
	2000		+34.6		+45.7	
	4000		+29.6		+45.0	
	6000		+28.2		+44.8	
	8000 ²		+26.5		+43.5	
Noise Figure	400		2			dB
	2000		1.4			
	4000		1.6			
	6000		1.7			
	8000 ²		1.7			
Device Operating Voltage (V _{DD})			+6		+6	V
Device Operating Current (I _{DD}) ³			104		4	mA
Enable Voltage (V _{EN}) ⁴			+6		0	V
Enable Current (I _{EN})			4.6		1.7	mA
Device Current Adjust (I _{ADJ}) ⁵			13		13	µA
Device Current Variation Vs. Temperature ⁶			-57		-57	µA/°C
Device Current Variation Vs. Voltage ⁷			0.028		0.028	mA/mV

1. Tested on Mini-Circuits Die Characterization 400-6000 MHz Test Board. See Figure 3. Board loss de-embedded.

2. Tested on Mini-Circuits Die Characterization 5500-8000 MHz Test Board. See Figure 4. Board loss de-embedded.

3. Current at P_{IN} = -25 dBm. Increases to 150 mA at P_{1dB}.4. V_{EN} must be equal to V_{DD} in Amplifier - ON mode.5. I_{ADJ} is not intended as a voltage input port. Gain is nominal when I_{ADJ} is left open. When I_{ADJ} is open, there is a measured voltage of +1.4 V on the pin. To change the current, add a shunt resistor (see Figures 3 and 4).

6. (Current at +105°C - Current at -45°C) / (+150 °C).

7. (Current at +6 V - Current at +5 V) / (+6 V - +5 V).

Mini-Circuits®



MMIC DIE

Low Noise Amplifier

TSY-83LN-D+

Mini-Circuits

50Ω 400 to 8000 MHz Bypass Mode Feature

ELECTRICAL SPECIFICATIONS⁸ AT +25°C, V_{DD} = +5 V, AND Z_O = 50Ω UNLESS NOTED OTHERWISE

Parameter	Condition (MHz)	Amplifier - ON			Amplifier - Bypass Typ.	Units
		Min.	Typ.	Max.		
Frequency Range		400		8000	400-8000	MHz
Gain	400		21.7		-1.3	dB
	2000		22.3		-0.9	
	4000		22.4		-1.2	
	6000		23.3		-1.6	
	8000 ⁹		23.1		-3.1	
Input Return Loss	400		12		9	dB
	2000		17		17	
	4000		11		14	
	6000		20		9	
	8000 ⁹		8		6	
Output Return Loss	400		14		13	dB
	2000		20		17	
	4000		16		20	
	6000		20		10	
	8000 ⁹		15		6	
Isolation	400-8000		28.4			dB
Output Power at 1 dB Compression (P _{1dB})	400		+20.1		+12.3	dBm
	2000		+21.0		+13.4	
	4000		+20.0		+15.6	
	6000		+19.3		+15.9	
	8000 ⁹		+19.3		+15.8	
Output Third-Order Intercept Point (P _{OUT} = 0 dBm/Tone)	400		+33.5		+42.4	dBm
	2000		+31.5		+45.9	
	4000		+27.6		+45.1	
	6000		+27.0		+44.6	
	8000 ⁹		+25.1		+43.7	
Noise Figure	400		1.9			dB
	2000		1.4			
	4000		1.5			
	6000		1.6			
	8000 ⁹		1.6			
Device Operating Voltage (V _{DD})			+5		+5	V
Device Operating Current (I _{DD}) ¹⁰			76		3	mA
Enable Voltage (V _{EN}) ¹¹			+5		0	V
Enable Current (I _{EN})			4.5		1.7	mA
Device Current Adjust (I _{ADJ}) ¹²			13		13	µA
Device Current Variation Vs. Temperature ¹³			-37		-37	µA/°C
Device Current Variation Vs. Voltage ¹⁴			0.028		0.028	mA/mV

8. Tested on Mini-Circuits Die Characterization 400-6000 MHz Test Board. See Figure 3. Board loss de-embedded.

9. Tested on Mini-Circuits Die Characterization 5500-8000 MHz Test Board. See Figure 4. Board loss de-embedded.

10. Current at P_{IN} = -25 dBm. Increases to 140 mA at P1dB.11. V_{EN} must be equal to V_{DD} in Amplifier – ON mode.12. I_{ADJ} is not intended as a voltage input port. Gain is nominal when I_{ADJ} is left open. When I_{ADJ} is open, there is a measured voltage of +1.4 V on the pin. To change the current, add a shunt resistor (see Figures 3 and 4).

13. (Current at +105°C - Current at -45°C) / (+150 °C).

14. (Current at +6 V - Current at +5 V) / (+6 V - +5 V).

SWITCHING SPECIFICATIONS¹⁵

Parameter		+6 V Typ.	+5 V Typ.	Units
Amplifier ON to Bypass	OFF Time (50% Control to 10% RF)	16	17	ns
	FALL Time (90% to 10% RF)	17	17	ns
Amplifier Bypass to ON	ON Time (50% Control to 90% RF)	168	168	ns
	RISE Time (10% to 90% RF)	112	112	ns
Control Voltage Leakage		+97	+83	mV

15. Tested on packaged model TSY-83LN+ mounted on Mini-Circuits Characterization Test Board TB-TSY-83LNC+ (see TSY-83LN+ Datasheet for details).

Mini-Circuits®



MMIC DIE







Low Noise Amplifier

TSY-83LN-D+

50Ω 400 to 8000 MHz Bypass Mode Feature

TYPICAL PERFORMANCE GRAPHS IN AMPLIFIER-ON MODE

Note: The following data was taken on the Mini-Circuits Die Characterization 400-6000 MHz Test Board (Figure 3). All data taken at nominal conditions $V_{EN} = V_{DD}$ and $R_{ADJ} = \text{Open}$ unless noted otherwise. For additional over temperature graphs, see TSY-83LN+.





MMIC DIE




Low Noise Amplifier

TSY-83LN-D+

50Ω 400 to 8000 MHz Bypass Mode Feature

TYPICAL PERFORMANCE GRAPHS IN AMPLIFIER-ON MODE

Note: The following data was taken on the Mini-Circuits Die Characterization 400-6000 MHz Test Board (Figure 3). All data taken at nominal conditions $V_{EN} = V_{DD}$ and $R_{IADJ} = \text{Open}$ unless noted otherwise. For additional graphs over temperature, see TSY-83LN+.





MMIC DIE







Low Noise Amplifier

TSY-83LN-D+

50Ω 400 to 8000 MHz Bypass Mode Feature

TYPICAL PERFORMANCE GRAPHS IN AMPLIFIER-ON MODE

Note: The following data was taken on the Mini-Circuits Die Characterization 5500-8000 MHz Test Board (Figure 4). All data taken at nominal conditions $V_{EN} = V_{DD}$ and $R_{IADJ} = \text{Open}$ unless noted otherwise. For additional graphs over temperature, see TSY-83LN+.





MMIC DIE




Low Noise Amplifier

TSY-83LN-D+

50Ω 400 to 8000 MHz Bypass Mode Feature

TYPICAL PERFORMANCE GRAPHS IN AMPLIFIER-ON MODE

Note: The following data was taken on the Mini-Circuits Die Characterization 5500-8000 MHz Test Board (Figure 4). All data taken at nominal conditions $V_{EN} = V_{DD}$ and $R_{LADJ} = \text{Open}$ unless noted otherwise. For additional graphs over temperature, see TSY-83LN+.





MMIC DIE






Low Noise Amplifier

TSY-83LN-D+

50Ω 400 to 8000 MHz Bypass Mode Feature

TYPICAL PERFORMANCE GRAPHS IN AMPLIFIER-ON MODE

Note: The following data was taken of the packaged TSY-83LN+ mounted on Mini-Circuits Characterization Test Board TB-TSY-83LNC+ (see Figure 3). All data taken at nominal conditions $V_{EN} = V_{DD} = +6$ V unless noted otherwise. For additional graphs over temperature, see TSY-83LN+.





MMIC DIE





Low Noise Amplifier

TSY-83LN-D+

50Ω 400 to 8000 MHz Bypass Mode Feature

TYPICAL PERFORMANCE GRAPHS IN AMPLIFIER-ON MODE

Note: The following data was taken of the packaged TSY-83LN+ mounted on Mini-Circuits Characterization Test Board TB-TSY-832LNC+ (Figure 4). All data taken at nominal conditions $V_{EN} = V_{DD} = +6$ V unless noted otherwise. For additional graphs over temperature, see TSY-83LN+.





MMIC DIE

Low Noise Amplifier


TSY-83LN-D+

50Ω 400 to 8000 MHz Bypass Mode Feature


TYPICAL PERFORMANCE GRAPHS IN BYPASS MODE

Note: The following data was taken on Mini-Circuits Die Characterization 400-6000 MHz Test Board (Figure 3). All data taken at nominal conditions $V_{EN} = 0$ V and R_{IADJ} = Open unless noted otherwise. For additional graphs over temperature, see TSY-83LN+.


INSERTION LOSS vs. DEVICE VOLTAGE (V_{DD})
 $P_{IN} = -25$ dBm, TEMPERATURE = +25°C




INPUT RETURN LOSS vs. DEVICE VOLTAGE (V_{DD})
 $P_{IN} = -25$ dBm, TEMPERATURE = +25°C



OUTPUT RETURN LOSS vs. DEVICE VOLTAGE (V_{DD})
 $P_{IN} = -25$ dBm, TEMPERATURE = +25°C



OUTPUT P1dB vs. DEVICE VOLTAGE (V_{DD})
TEMPERATURE = +25°C





MMIC DIE




Low Noise Amplifier

TSY-83LN-D+

50Ω 400 to 8000 MHz Bypass Mode Feature

TYPICAL PERFORMANCE GRAPHS IN BYPASS MODE

Note: The following data was taken on Mini-Circuits Die Characterization 400-6000 MHz Test Board (Figure 3). All data taken at nominal conditions $V_{EN} = 0$ V and $R_{I_{ADJ}} = \text{Open}$ unless noted otherwise. For additional graphs over temperature, see TSY-83LN+.





MMIC DIE

Low Noise Amplifier

TSY-83LN-D+

Mini-Circuits

50Ω 400 to 8000 MHz Bypass Mode Feature

ABSOLUTE MAXIMUM RATINGS¹⁶

Parameter	Ratings	
Operating Temperature ¹⁷	-45°C to +105°C	
Storage Temperature ¹⁸	-65°C to +150°C	
Total Power Dissipation	0.83W	
Junction Temperature ¹⁹	+150°C	
Input Power (CW)	Amplifier - ON	+22 dBm
	Amplifier - Bypass	+29 dBm
DC Voltage on RF-OUT	+14.5 V	
DC Voltage on RF-IN	+22 V	
DC Voltage on V _{DD}	+9 V	
Current I _{DD}	180 mA	
DC Voltage on V _{EN}	+9 V	
Current I _{EN}	60 mA	
Current I _{ADJ}	10 mA	

16. Permanent damage may occur if these limits are exceeded. Maximum ratings are not intended for continuous normal operation.

17. Bottom of Die.

18. For die shipped in Gel-Pak see ENV80 (limited by packaging).

19. Peak temperature at top of Die.

THERMAL RESISTANCE

Parameter	Ratings
Thermal Resistance (Θ_{JC}) ²⁰	54.3°C/W

20. Θ_{JC} = (Hot Spot Temperature on Die - Temperature at Ground Lead)/Dissipated Power

ESD RATING²¹

	Class	Voltage Range	Reference Standard
HBM	1A	250 V to < 500 V	ANSI/ESDA/JEDEC JS-001-2017
CDM	C3	≥ 1000 V	JESD22-C101F



ESD HANDLING PRECAUTION: This device is designed to be Class 1A for HBM. Static charges may easily produce potentials higher than this with improper handling and can discharge into DUT and damage it. As a preventive measure Industry standard ESD handling precautions should be used at all times to protect the device from ESD damage.

21. ESD measured in 3x3 mm 12-Lead QFN-style package.



MMIC DIE

Low Noise Amplifier

TSY-83LN-D+

50Ω 400 to 8000 MHz Bypass Mode Feature

FUNCTIONAL DIAGRAM




Figure 1. TSY-83LN-D+ Functional Diagram

PAD DESCRIPTION

Function	Pad Number	Description
RF-IN	1	RF-IN Pad connects to RF-Input port.
RF-OUT	2	RF-OUT Pad connects to RF-Output port.
V _{DD}	3	DC Input Pad connects to voltage input port, V _{DD} .
V _{EN}	4	DC Input Pad connects to voltage input port, V _{EN} .
I _{ADJ} ²²	5	Current Adjustment Pad connects to port, I _{ADJ} . Port left open for nominal operation. I _{ADJ} can be adjusted with the use of an external resistor (see Figures 3 and 4).
GND	Bottom of Die	Connects to ground.

22. I_{ADJ} port is not intended as a voltage input port. Permanent damage can occur if a voltage is applied to this port.

DIE OUTLINE: inches [mm], Typical




Figure 2. TSY-83LN-D+ Die Outline

DIMENSIONS: inches [mm], Typical

Die Size	0.0328 x 0.0317 [0.8331 x 0.8051]
Die Thickness	0.0040 [0.1016]
Bond Pad Size Pad 1, 2, 3, 4, 5	0.0033 x 0.0033 [0.0838 x 0.0838]
Plating (Pads & bottom of Die)	Gold



MMIC DIE

Low Noise Amplifier

TSY-83LN-D+

Mini-Circuits

50Ω 400 to 8000 MHz Bypass Mode Feature

CHARACTERIZATION BOARD




Figure 3. Wideband Die Characterization and Application Circuit.
Used for characterization of device from 400 to 6000 MHz.

Electrical Parameters and Conditions

Gain, Return Loss, Output Power at 1dB Compression (P_{1dB}), Output IP3 (OIP3), and Noise Figure measured using N5242A PNA-X Microwave Network Analyzer.

Conditions:

1. Gain and Return Loss: P_{IN} = -25 dBm
2. Output IP3 (OIP3): Two tones, spaced 1 MHz apart, 0 dBm/tone at output.

Power ON/Power OFF Sequence

Caution: Permanent damage to the device will occur if the Power ON and Power OFF Sequences are not followed.

Power ON:

- 1) Set V_{DD} = +5 or +6 V.
- 2) Set V_{EN} = +5 or +6 V for Amplifier- ON Mode or V_{EN} = 0 V for Bypass Mode.
- 3) Turn on V_{DD} and V_{EN} (Can be turned on in any order).
- 4) Apply RF signal.

Power OFF:

- 1) Turn off RF signal.
- 2) Turn off V_{DD} and V_{EN} (Can be turned off in any order).

Component	Value	Size	Part Number	Manufacturer
C1	0.01 μF	0402	GRM155R71E103KA01D	Murata
C2	10 pF	0402	GJM1555C1H100JB01D	Murata
C3, C4	100 pF	0402	GRM1555C1H101JA01D	Murata
C5	0.4 pF	0402	GJM1555C1HR40WB01D	Murata
C6	0.3 pF	0402	GJM1555C1HR30WB01D	Murata
R1	0Ω	0402	RK73Z1ETTP	KOA Speer
RI _{ADJ} ²³	Not Populated	0402	--	--
L1	22 nH	0402	LQG15HS22NG02D	Murata
L2	39 nH	0402	0402CS-39NXGRW	Coilcraft

23. RI_{ADJ} resistor not needed for nominal operation. See I_{DD} versus RI_{ADJ} plot in Typical Performance Graphs section for typical current consumption.



MMIC DIE

Low Noise Amplifier

TSY-83LN-D+

Mini-Circuits

50Ω 400 to 8000 MHz Bypass Mode Feature

CHARACTERIZATION BOARD




Figure 4. Narrowband Die Characterization and Application Circuit.
Used for characterization of device from 5500 to 8000 MHz.

Electrical Parameters and Conditions

Gain, Return Loss, Output Power at 1dB Compression (P_{1dB}), Output IP3 (OIP3), and Noise Figure measured using N5242A PNA-X Microwave Network Analyzer.

Conditions:

1. Gain and Return Loss: $P_{IN} = -25$ dBm
2. Output IP3 (OIP3): Two tones, spaced 1 MHz apart, 0 dBm/tone at output.

Power ON/Power OFF Sequence

Caution: Permanent damage to the device will occur if the Power ON and Power OFF Sequences are not followed.

Power ON:

- 1) Set $V_{DD} = +5$ or $+6$ V.
- 2) Set $V_{EN} = +5$ or $+6$ V for Amplifier- ON Mode or $V_{EN} = 0$ V for Bypass Mode.
- 3) Turn on V_{DD} and V_{EN} (Can be turned on in any order).
- 4) Apply RF signal.

Power OFF:

- 1) Turn off RF signal.
- 2) Turn off V_{DD} and V_{EN} (Can be turned off in any order).

Component	Value	Size	Part Number	Manufacturer
C1	0.01 μ F	0402	GRM155R71E103KA01D	Murata
C2	10 pF	0402	GJM1555C1H100JB01D	Murata
C3, C4	100 pF	0402	GRM1555C1H101JA01D	Murata
C5	0.4 pF	0402	GJM1555C1HR40WB01D	Murata
C6	0.3 pF	0402	GJM1555C1HR30WB01D	Murata
R1	0Ω	0402	RK73Z1ETTP	KOA Speer
$R_{I_{ADJ}}^{24}$	Not Populated	0402	--	--
L1	2 nH	0402	0402CS-2N0XGRW	Coilcraft
L2	5.6 nH	0402	0402CS-5N6XGRW	Coilcraft

24. $R_{I_{ADJ}}$ resistor not needed for nominal operation. See I_{DD} versus $R_{I_{ADJ}}$ plot in Typical Performance Graphs section for typical current consumption.



MMIC DIE

Low Noise Amplifier

TSY-83LN-D+

Mini-Circuits

50Ω 400 to 8000 MHz Bypass Mode Feature

ASSEMBLY DIAGRAM




Figure 5. TSY-83LN-D+ Assembly Diagram

- Bond wire diameter: 1 mil
- Bond wire lengths from Die Pad to PCB at RF-IN port: 37 ± 2 mils
- Bond wire lengths from Die Pad to PCB at RF-OUT port: 36 ± 2 mils
- Bond wire length from Die Pad to PCB at V_{DD} port: 37 ± 2 mils
- Bond wire length from Die Pad to PCB at V_{EN} port: 29 ± 2 mils
- Bond wire length from Die Pad to PCB at I_{ADJ} port: 35 ± 2 mils
- Typical Gap from Die edge to PCB edge: 3 mils
- PCB thickness and material: 10 mils Roger RO4350B (Plating: 1 oz copper on each side)

ASSEMBLY AND HANDLING PROCEDURE

1. Storage
Die should be stored in a dry nitrogen purged desiccator or equivalent.
2.  ESD Precautions
MMIC pHEMT amplifier die are susceptible to electrostatic and mechanical damage. Die are supplied in anti-static protected material, which should be opened only in clean room conditions at an appropriately grounded anti-static workstation.
3. Die Handling and Attachment
Devices require careful handling using tools appropriate for manipulating semiconductor chips. It is recommended to handle the chips along the edges with a custom designed collet. The die mounting surface must be clean and flat. Using conductive silver-filled epoxy, apply sufficient adhesive to meet the required bond line thickness, fillet height and coverage around the total periphery of the device. The recommended epoxy is Atrox 800HT5 or equivalent. Parts should be cured in a nitrogen-filled atmosphere per manufacturer's recommended cure profile.
4. Wire Bonding
Openings in the surface passivation above the gold bond pads are provided to allow wire bonding to the die. Thermosonic bonding is recommended with minimized ultrasonic content. Bond force, time, ultrasonic power and temperature are all critical parameters. The suggested interconnect is pure gold, 1 mil diameter wire. Bonds are recommended to be made from the bond pads on the die to the package or substrate. All bond wire length and bond wire height should be kept as short as possible, unless specified by design, to minimize performance degradation due to undesirable series inductance.



MMIC DIE

Low Noise Amplifier

TSY-83LN-D+

50Ω 400 to 8000 MHz Bypass Mode Feature

ADDITIONAL DETAILED INFORMATION IS AVAILABLE ON OUR DASHBOARD

[CLICK HERE](#)

Performance Data & Graphs	Data Graphs S-Parameter (S2P Files) Data Set (.zip file)	
Case Style	Die	
RoHS Status	Compliant	
Die Ordering and Packaging Information	Quantity, Package Gel - Pak: 5, 10, 50, 100 KGD* Medium [†] , Partial wafer: KGD*<1892 Full wafer [†]	Model No. TSY-83LN-DG+ TSY-83LN-DP+ TSY-83LN-DF+
Die Marking	KCY01EF	
Environmental Ratings	ENV80	

* Known Good Die ("KGD") means that the die in question have been subjected to Mini-Circuits DC test performance criteria and measurement instructions and that the parametric data of such die fall within a predefined range. While DC testing is not definitive, it does provide a high degree of confidence that die are capable of meeting typical RF electrical parameters specified by Mini-Circuits.

Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits' standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp
- D. Mini-Circuits does not warrant the accuracy or completeness of the information, text, graphics and other items contained within this document and same are provided as an accommodation and on an AS IS basis, with all faults.
- E. Purchasers of this part are solely responsible for proper storing, handling, assembly and processing of known good die (KGD) (including, without limitation, proper ESD preventative measures, die preparation, die attach, wire bonding and related assembly and test activities), and Mini-Circuits assumes no responsibility therefor or for environmental effects on KGD.
- F. Mini-Circuits and the Mini-Circuits logo are registered trademarks of Scientific Components Corporation d/b/a Mini-Circuits. All other third-party trademarks are the property of their respective owners. A reference to any third-party trademark does not constitute or imply any endorsement, affiliation, sponsorship, or recommendation by any such third-party of Mini-Circuits or its products.



MMIC Amplifier

TSY-83LN-D+

Typical Performance Data

NOTE: Use PDF Bookmarks to view DATA at required conditions

Definitions:

Input Return Loss = S11 (dB)

Gain = S21 (dB)

Isolation = S12 (dB)

Output Return Loss = S22 (dB)

TEST CONDITIONS: $V_{DD} = +4.75$ V, $V_{EN} = +4.75$ V, $I_{DD} = 71$ mA, $I_{EN} = 2.0$ mA @ Temperature = $+25^\circ\text{C}$

See TSY-83LN+ for additional test data.

FREQ (MHz)	Gain (dB)	Isolation (dB)	Input Return Loss (dB)	Output Return Loss (dB)	Stability		1dB Comp. Output (dBm)	3dB Comp. Output (dBm)	Noise Figure (dB)	IP-3 Output Pout = +0 (dBm)
					K	Measure				
200	15.2	-32.7	-1.9	-4.1	1.4	0.9	17.2	20.8	19.8	30.2
300	19.9	-28.0	-5.6	-8.2	1.2	0.8	19.0	20.8	2.6	31.3
400	21.4	-26.5	-11.4	-14.2	1.1	0.7	19.3	21.2	1.9	31.4
500	21.8	-26.2	-17.6	-18.3	1.1	0.6	19.8	21.4	1.6	33.3
600	21.9	-26.2	-21.0	-18.2	1.1	0.6	20.1	21.6	1.5	30.6
700	21.9	-26.1	-19.8	-17.1	1.1	0.6	20.4	21.8	1.4	32.5
800	21.9	-26.1	-18.6	-16.4	1.1	0.6	20.5	21.9	1.4	31.3
900	21.9	-26.2	-17.8	-16.3	1.1	0.6	20.6	22.0	1.3	32.5
1000	21.9	-26.3	-17.2	-16.3	1.1	0.6	20.6	22.1	1.3	32.6
1100	21.9	-26.2	-16.9	-16.5	1.1	0.6	20.7	22.0	1.3	31.6
1200	21.9	-26.3	-16.8	-17.0	1.1	0.6	20.7	22.1	1.3	32.2
1300	21.9	-26.3	-16.9	-17.4	1.1	0.6	20.7	22.2	1.3	31.2
1400	21.9	-26.3	-16.9	-18.2	1.1	0.6	20.7	22.1	1.3	30.7
1500	21.9	-26.5	-16.9	-19.3	1.1	0.7	20.6	22.3	1.3	30.4
1600	21.9	-26.5	-17.0	-20.5	1.1	0.7	20.7	22.2	1.4	31.0
1700	21.9	-26.6	-16.9	-21.7	1.1	0.7	20.7	22.5	1.4	31.0
1800	21.9	-26.6	-17.0	-23.5	1.1	0.7	20.7	22.3	1.4	29.8
1900	21.9	-26.7	-16.8	-25.6	1.2	0.7	20.6	22.3	1.4	29.6
2000	21.9	-26.7	-16.4	-26.6	1.2	0.7	20.4	22.1	1.4	29.6
2100	21.9	-26.6	-15.9	-31.0	1.2	0.7	20.4	22.5	1.5	31.1
2200	21.9	-26.9	-15.3	-30.5	1.2	0.7	20.4	22.4	1.5	31.0
2300	21.9	-26.9	-14.7	-27.8	1.2	0.7	20.4	22.4	1.5	30.0
2400	21.9	-27.1	-14.2	-25.7	1.2	0.7	20.3	22.7	1.5	28.7
2500	21.9	-27.2	-13.8	-23.5	1.2	0.8	20.1	22.8	1.6	29.2
2600	21.9	-27.1	-13.3	-21.5	1.2	0.7	19.9	22.9	1.6	29.7
2700	21.8	-27.3	-13.1	-20.5	1.2	0.8	19.8	22.6	1.6	28.6
2800	21.8	-27.5	-12.5	-19.1	1.2	0.8	19.7	22.5	1.6	29.1
2900	21.8	-27.6	-12.3	-18.5	1.2	0.8	19.6	22.3	1.7	27.6
3000	21.7	-27.5	-11.9	-17.5	1.2	0.8	19.3	22.4	1.7	27.9
3100	21.7	-27.5	-11.6	-16.7	1.2	0.8	19.0	22.5	1.7	27.7
3200	21.7	-27.4	-11.3	-16.1	1.2	0.8	18.8	22.1	1.6	28.6
3300	21.7	-27.6	-11.1	-15.6	1.2	0.8	18.7	22.0	1.6	27.1
3400	21.7	-27.6	-10.8	-15.2	1.2	0.8	18.6	22.0	1.6	27.3
3500	21.7	-27.7	-10.7	-14.8	1.2	0.8	18.6	22.5	1.6	27.2
3600	21.7	-27.7	-10.7	-14.6	1.2	0.8	18.6	22.8	1.6	27.4
3700	21.8	-27.8	-10.7	-14.5	1.2	0.8	18.7	22.3	1.6	26.8
3800	21.8	-27.8	-10.7	-14.6	1.2	0.8	18.9	22.3	1.6	26.8
3900	21.8	-27.8	-10.6	-14.8	1.2	0.8	19.2	22.5	1.6	28.0
4000	21.9	-27.9	-10.5	-14.9	1.2	0.8	19.5	22.7	1.6	26.1
4100	21.9	-28.0	-10.6	-15.1	1.2	0.8	19.5	23.0	1.6	26.8
4200	22.0	-28.1	-10.8	-15.2	1.2	0.8	19.5	22.8	1.6	26.4
4300	22.0	-28.1	-11.1	-15.4	1.2	0.8	19.6	22.7	1.6	27.3
4400	22.0	-28.3	-11.4	-15.6	1.3	0.8	19.7	22.8	1.6	27.2
4500	22.0	-28.1	-11.8	-16.3	1.2	0.8	19.9	22.9	1.6	28.3
4600	22.0	-28.0	-12.5	-17.0	1.2	0.8	19.9	23.2	1.6	27.3
4700	22.1	-28.0	-12.7	-17.8	1.2	0.8	19.6	23.0	1.6	26.4
4800	22.2	-28.0	-12.8	-18.4	1.2	0.8	19.5	22.9	1.6	26.5
4900	22.3	-27.9	-13.0	-19.2	1.2	0.8	19.7	23.2	1.6	27.6
5000	22.4	-28.0	-13.3	-20.0	1.2	0.8	19.9	23.2	1.6	27.8
5100	22.5	-28.2	-13.8	-20.6	1.2	0.8	19.7	23.0	1.6	27.3
5200	22.6	-28.3	-14.2	-21.0	1.2	0.8	19.3	22.7	1.6	26.8
5300	22.7	-28.4	-14.8	-21.5	1.2	0.8	19.3	22.5	1.6	25.9
5400	22.7	-28.6	-15.9	-21.2	1.3	0.8	19.5	22.6	1.6	26.2
5500	22.7	-28.8	-17.3	-21.2	1.3	0.8	19.9	22.8	1.6	26.6
5600	22.6	-28.7	-19.9	-20.8	1.3	0.8	20.1	23.0	1.7	27.4
5700	22.6	-28.6	-22.2	-20.9	1.3	0.8	19.7	22.9	1.6	26.8
5800	22.6	-28.4	-23.7	-21.3	1.3	0.8	19.1	22.7	1.7	26.0
5900	22.7	-28.3	-24.8	-21.6	1.3	0.8	18.8	22.6	1.7	25.2
6000	22.8	-28.5	-24.4	-22.6	1.3	0.8	18.6	22.5	1.7	25.9
6100	23.0	-28.4	-22.9	-24.3	1.2	0.8	18.7	22.3	1.7	25.4
6200	23.1	-28.6	-20.7	-25.8	1.3	0.8	18.8	21.9	1.7	25.5
6300	23.2	-28.8	-18.7	-26.1	1.3	0.8	18.9	21.6	1.8	26.2
6400	23.2	-29.0	-16.9	-25.3	1.3	0.8	18.7	21.4	1.8	25.2
6500	23.2	-29.2	-15.3	-23.0	1.3	0.8	18.4	21.0	1.9	25.2
6600	23.2	-29.4	-13.6	-20.9	1.3	0.8	17.9	20.8	1.9	24.3
6700	23.1	-29.9	-11.8	-18.3	1.3	0.9	17.6	20.4	1.9	24.2
6800	22.8	-30.4	-10.5	-16.2	1.4	0.9	17.7	20.2	2.0	23.9
6900	22.4	-30.8	-10.0	-15.6	1.4	0.9	18.2	19.9	2.1	24.8
7000	22.1	-31.2	-9.4	-15.9	1.5	1.0	18.5	19.6	2.1	25.1
7100	22.4	-30.9	-9.2	-16.0	1.4	1.0	18.3	19.5	2.1	24.1
7200	22.3	-31.0	-8.4	-14.2	1.4	1.0	18.0	19.6	2.1	23.3
7300	22.2	-31.3	-7.9	-13.0	1.5	1.0	17.9	19.7	2.2	23.1
7400	22.1	-31.9	-6.9	-11.5	1.5	1.0	18.2	20.0	2.2	24.3
7500	21.9	-32.3	-6.1	-10.3	1.5	1.0	18.7	19.6	2.3	23.5
7600	21.6	-33.3	-5.4	-9.3	1.6	1.0	19.0	19.8	2.3	23.5
7700	21.1	-34.3	-4.9	-8.4	1.7	1.0	18.8	19.8	2.3	22.3
7800	20.7	-35.5	-4.3	-7.5	1.9	1.0	18.4	19.3	2.4	22.0
7900	20.1	-36.7	-3.9	-6.9	2.0	1.0	18.1	19.3	2.5	21.8
8000	19.3	-38.8	-3.5	-6.3	2.5	1.0	18.0	18.8	2.5	22.4

*Typical Performance Data***NOTE: Use PDF Bookmarks to view DATA at required conditions****Definitions:**

Input Return Loss = S11 (dB)

Gain = S21 (dB)

Isolation = S12 (dB)

Output Return Loss = S22 (dB)

TEST CONDITIONS: V_{DD} = +4.75 V, V_{EN} = +4.75 V, I_{DD} = 73 mA, I_{EN} = 2.05 mA @ Temperature = +25°C

See TSY-83LN+ for additional test data.

FREQ (MHz)	Gain (dB)	Isolation (dB)	Input Return Loss (dB)	Output Return Loss (dB)	Stability		1dB Comp. Output (dBm)	3dB Comp. Output (dBm)	Noise Figure (dB)	IP-3 Output Pout = +0 (dBm)
					K	Measure				
5500	22.2	-29.0	-10.9	-9.7	1.3	0.7	19.9	22.5	1.4	26.7
5600	22.2	-29.0	-11.3	-9.8	1.3	0.7	20.2	22.9	1.4	26.5
5700	22.3	-28.7	-11.5	-10.2	1.2	0.7	20.0	23.0	1.4	26.8
5800	22.4	-28.7	-11.4	-10.6	1.2	0.7	19.3	23.0	1.4	26.1
5900	22.6	-28.6	-11.0	-11.0	1.2	0.7	19.4	22.8	1.4	26.8
6000	22.8	-28.6	-10.8	-11.2	1.2	0.7	19.1	23.0	1.4	26.5
6100	22.9	-28.7	-10.7	-11.3	1.2	0.7	18.5	22.7	1.5	26.2
6200	23.0	-28.8	-10.8	-11.4	1.2	0.7	18.3	22.9	1.5	25.8
6300	23.1	-28.9	-10.7	-11.6	1.2	0.7	17.9	22.5	1.5	24.9
6400	23.2	-29.0	-10.7	-11.7	1.2	0.7	18.2	22.3	1.5	24.6
6500	23.2	-29.2	-10.7	-11.6	1.2	0.7	18.5	22.1	1.5	24.7
6600	23.2	-29.3	-10.9	-11.8	1.2	0.7	19.0	22.1	1.5	25.2
6700	23.2	-29.6	-11.0	-11.8	1.3	0.7	19.4	22.2	1.5	25.4
6800	23.2	-29.5	-11.4	-12.3	1.3	0.8	19.6	22.2	1.6	25.2
6900	23.2	-29.7	-11.7	-12.6	1.3	0.8	19.4	21.8	1.6	25.4
7000	23.3	-29.5	-12.0	-13.2	1.3	0.8	19.6	21.8	1.7	25.3
7100	23.4	-29.5	-12.0	-13.4	1.3	0.8	19.8	21.7	1.6	25.4
7200	23.5	-29.7	-11.8	-13.3	1.3	0.8	19.7	21.6	1.7	26.1
7300	23.5	-29.7	-11.8	-13.4	1.3	0.8	19.5	21.1	1.7	25.7
7400	23.6	-30.0	-11.5	-13.2	1.3	0.8	19.4	20.8	1.7	25.5
7500	23.6	-30.3	-11.3	-13.2	1.3	0.8	19.7	21.0	1.8	25.4
7600	23.6	-30.5	-11.0	-13.2	1.3	0.8	19.3	20.7	1.8	25.9
7700	23.6	-30.9	-10.5	-13.1	1.4	0.8	19.8	20.9	1.9	25.8
7800	23.5	-31.3	-10.1	-13.2	1.4	0.9	19.4	20.6	2.0	26.2
7900	23.3	-31.7	-9.5	-13.4	1.5	0.9	19.2	20.5	2.1	25.9
8000	23.1	-32.1	-8.9	-13.9	1.5	0.9	19.1	20.4	2.2	25.8
8100	22.8	-32.7	-8.2	-14.7	1.6	1.0	19.5	20.7	2.2	25.7
8200	22.4	-33.3	-7.5	-16.3	1.7	1.0	19.3	20.7	2.4	26.1
8300	22.0	-33.5	-7.2	-18.3	1.8	1.1	18.7	20.0	2.5	26.1
8400	21.7	-33.7	-6.7	-20.0	1.8	1.1	18.8	20.1	2.7	26.3
8500	21.5	-33.9	-6.3	-21.4	1.9	1.2	18.3	19.5	2.8	25.5



ISO 9001 ISO 14001 AS 9100 CERTIFIED

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping



The Design Engineers Search Engine

 REV. OR
 TSY-83LN-D+
 8/27/2025
 Page 2 of 24

Typical Performance Data

NOTE: Use PDF Bookmarks to view DATA at required conditions**Definitions:**

Input Return Loss = S11 (dB)

Gain = S21 (dB)

Isolation = S12 (dB)

Output Return Loss = S22 (dB)

TEST CONDITIONS: V_{DD} = +4.75 V, V_{EN} = 0 V, I_{DD} = 3 mA, I_{EN} = 0 mA @ Temperature = +25°C

See TSY-83LN+ for additional test data.

FREQ (MHz)	Gain (dB)	Isolation (dB)	Input Return Loss (dB)	Output Return Loss (dB)	Stability		Noise Figure (dB)
					K	Measure	
200	-3.3	-3.5	-4.2	-7.2	1.1	0.7	2.5
300	-1.9	-2.1	-6.8	-10.2	1.0	0.5	2.7
400	-1.4	-1.5	-9.3	-12.7	1.0	0.4	1.4
500	-1.1	-1.2	-11.8	-14.9	1.0	0.4	1.7
600	-0.9	-1.1	-14.3	-16.8	1.0	0.4	0.9
700	-0.9	-1.0	-17.1	-18.5	1.0	0.4	0.8
800	-0.8	-1.0	-20.4	-19.5	1.0	0.4	1.0
900	-0.8	-1.0	-24.6	-20.0	1.0	0.4	1.1
1000	-0.8	-1.0	-31.2	-20.4	1.0	0.3	0.6
1100	-0.8	-1.0	-45.2	-20.2	1.0	0.3	0.5
1200	-0.8	-1.0	-31.9	-19.8	1.0	0.4	1.0
1300	-0.8	-1.0	-26.9	-19.2	1.0	0.4	0.9
1400	-0.8	-1.0	-23.9	-18.7	1.0	0.4	1.0
1500	-0.8	-1.0	-21.8	-18.2	1.0	0.4	0.8
1600	-0.8	-1.1	-20.7	-17.7	1.0	0.4	0.7
1700	-0.9	-1.1	-19.8	-17.3	1.0	0.4	1.1
1800	-0.9	-1.1	-19.1	-17.1	1.0	0.4	0.9
1900	-0.9	-1.2	-18.3	-17.1	1.0	0.4	1.1
2000	-0.9	-1.2	-17.7	-17.1	1.0	0.4	1.2
2100	-1.0	-1.2	-17.1	-17.3	1.0	0.4	1.2
2200	-1.0	-1.3	-16.6	-17.5	1.0	0.4	1.2
2300	-1.0	-1.3	-16.3	-18.0	1.0	0.4	1.3
2400	-1.0	-1.4	-16.0	-18.5	1.0	0.5	1.4
2500	-1.0	-1.4	-15.7	-18.8	1.0	0.5	1.3
2600	-1.1	-1.5	-15.7	-19.3	1.0	0.5	1.4
2700	-1.1	-1.5	-15.8	-19.8	1.0	0.5	1.1
2800	-1.1	-1.6	-15.8	-20.5	1.1	0.5	1.4
2900	-1.1	-1.6	-15.8	-21.4	1.1	0.5	1.4
3000	-1.1	-1.6	-15.8	-22.4	1.1	0.5	1.4
3100	-1.1	-1.6	-15.8	-23.7	1.1	0.5	1.7
3200	-1.1	-1.6	-15.8	-25.2	1.0	0.5	1.4
3300	-1.1	-1.6	-15.8	-27.4	1.0	0.5	1.7
3400	-1.1	-1.6	-15.8	-30.9	1.0	0.5	1.5
3500	-1.2	-1.6	-15.7	-34.5	1.1	0.5	1.2
3600	-1.2	-1.6	-15.7	-32.4	1.1	0.5	1.4
3700	-1.2	-1.6	-15.4	-28.3	1.1	0.5	1.1
3800	-1.2	-1.6	-15.2	-24.6	1.1	0.5	1.4
3900	-1.2	-1.6	-14.8	-22.1	1.1	0.5	1.4
4000	-1.2	-1.7	-14.4	-20.5	1.1	0.5	1.7
4100	-1.3	-1.7	-14.0	-19.0	1.1	0.5	1.9
4200	-1.3	-1.7	-13.6	-17.7	1.1	0.5	1.3
4300	-1.4	-1.8	-13.1	-16.6	1.1	0.6	1.8
4400	-1.4	-1.8	-12.7	-15.5	1.1	0.6	1.7
4500	-1.4	-1.9	-12.1	-14.5	1.1	0.5	1.8
4600	-1.5	-1.9	-11.6	-13.6	1.1	0.5	2.0
4700	-1.5	-1.9	-11.2	-13.0	1.1	0.5	1.7
4800	-1.5	-2.0	-10.8	-12.4	1.1	0.5	1.9
4900	-1.5	-2.0	-10.5	-11.9	1.1	0.5	1.8
5000	-1.6	-2.1	-10.2	-11.4	1.1	0.5	2.0
5100	-1.6	-2.1	-10.0	-11.0	1.1	0.5	1.5
5200	-1.6	-2.2	-9.8	-10.7	1.1	0.5	1.6
5300	-1.7	-2.2	-9.5	-10.5	1.1	0.5	1.6
5400	-1.7	-2.3	-9.4	-10.2	1.1	0.5	1.6
5500	-1.8	-2.4	-9.2	-10.0	1.1	0.5	2.1
5600	-1.8	-2.4	-9.0	-9.7	1.1	0.5	2.4
5700	-1.8	-2.4	-8.7	-9.5	1.1	0.5	2.4
5800	-1.8	-2.4	-8.5	-9.2	1.1	0.5	2.1
5900	-1.8	-2.4	-8.5	-9.1	1.1	0.5	2.3
6000	-1.8	-2.4	-8.4	-9.0	1.1	0.5	1.4
6100	-1.7	-2.4	-8.4	-8.9	1.1	0.5	1.2
6200	-1.7	-2.4	-8.5	-8.9	1.1	0.5	1.9
6300	-1.8	-2.4	-8.5	-8.9	1.1	0.5	1.9
6400	-1.8	-2.5	-8.6	-9.0	1.1	0.5	2.1
6500	-1.8	-2.5	-8.6	-8.9	1.1	0.5	1.6
6600	-1.8	-2.5	-8.6	-8.9	1.1	0.5	2.3
6700	-1.8	-2.5	-8.8	-9.0	1.1	0.5	2.0
6800	-1.8	-2.6	-8.8	-9.1	1.1	0.5	2.1
6900	-1.8	-2.6	-8.8	-9.0	1.1	0.5	2.2
7000	-1.9	-2.6	-8.8	-9.0	1.1	0.6	2.2
7100	-1.8	-2.6	-8.8	-8.9	1.1	0.5	1.8
7200	-1.8	-2.6	-8.9	-8.9	1.1	0.5	2.7
7300	-1.8	-2.6	-8.9	-8.9	1.1	0.5	2.5
7400	-1.8	-2.6	-8.9	-8.9	1.1	0.5	1.3
7500	-1.8	-2.6	-9.0	-8.8	1.1	0.5	2.3
7600	-1.9	-2.6	-9.0	-8.8	1.1	0.5	2.5
7700	-1.9	-2.7	-9.0	-8.8	1.1	0.5	2.5
7800	-1.9	-2.7	-9.0	-8.8	1.1	0.6	1.4
7900	-2.0	-2.8	-8.9	-8.7	1.1	0.6	2.2
8000	-2.1	-2.8	-8.9	-8.6	1.1	0.6	2.2



ISO 9001 ISO 14001 AS 9100 CERTIFIED

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minic

*Typical Performance Data***NOTE: Use PDF Bookmarks to view DATA at required conditions****Definitions:**

Input Return Loss = S11 (dB)
 Gain = S21 (dB)
 Isolation = S12 (dB)
 Output Return Loss = S22 (dB)

TEST CONDITIONS: V_{DD} = +4.75 V, V_{EN} = 0 V, I_{DD} = 3 mA, I_{EN} = 0 mA @ Temperature = +25°C

See TSY-83LN+ for additional test data.

FREQ (MHz)	Gain (dB)	Isolation (dB)	Input Return Loss (dB)	Output Return Loss (dB)	Stability		Noise Figure (dB)
					K	Measure	
5500	-1.3	-1.9	-18.5	-20.6	1.1	0.6	1.6
5600	-1.2	-1.9	-19.3	-23.5	1.1	0.6	1.6
5700	-1.2	-1.8	-19.6	-27.0	1.1	0.6	1.6
5800	-1.2	-1.8	-19.4	-27.8	1.1	0.6	1.4
5900	-1.1	-1.8	-19.1	-24.9	1.1	0.6	0.9
6000	-1.2	-1.8	-18.5	-22.2	1.1	0.6	1.7
6100	-1.2	-1.8	-17.6	-19.9	1.1	0.6	1.1
6200	-1.2	-1.9	-16.6	-18.1	1.1	0.6	1.6
6300	-1.2	-1.9	-15.6	-16.5	1.1	0.6	1.2
6400	-1.3	-2.0	-14.6	-15.2	1.1	0.6	1.4
6500	-1.3	-2.1	-13.8	-14.2	1.1	0.6	1.7
6600	-1.4	-2.1	-12.9	-13.2	1.1	0.6	2.0
6700	-1.5	-2.2	-12.2	-12.4	1.1	0.6	2.0
6800	-1.6	-2.3	-11.4	-11.5	1.1	0.6	1.5
6900	-1.7	-2.4	-10.7	-10.8	1.1	0.6	1.5
7000	-1.7	-2.5	-10.0	-10.0	1.1	0.6	1.9
7100	-1.8	-2.6	-9.4	-9.3	1.1	0.6	2.1
7200	-1.9	-2.7	-8.9	-8.8	1.1	0.6	1.5
7300	-2.0	-2.8	-8.4	-8.2	1.1	0.6	1.6
7400	-2.2	-3.0	-7.9	-7.8	1.1	0.6	2.1
7500	-2.3	-3.1	-7.5	-7.3	1.1	0.6	1.9
7600	-2.5	-3.3	-7.1	-6.9	1.1	0.6	2.3
7700	-2.7	-3.4	-6.7	-6.5	1.1	0.6	2.1
7800	-2.9	-3.6	-6.3	-6.2	1.1	0.5	2.3
7900	-3.1	-3.8	-5.9	-5.8	1.1	0.5	1.8
8000	-3.3	-4.1	-5.6	-5.5	1.1	0.5	2.0
8100	-3.6	-4.3	-5.2	-5.2	1.1	0.5	2.9
8200	-3.9	-4.6	-4.9	-4.9	1.2	0.6	2.4
8300	-4.2	-4.9	-4.6	-4.6	1.2	0.5	2.3
8400	-4.4	-5.1	-4.3	-4.3	1.2	0.5	2.2
8500	-4.7	-5.4	-4.0	-4.0	1.2	0.5	2.3



ISO 9001 ISO 14001 AS 9100 CERTIFIED

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping
 **The Design Engineers Search Engine** Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minic.com

MMIC Amplifier

TSY-83LN-D+

Typical Performance Data

NOTE: Use PDF Bookmarks to view DATA at required conditions

Definitions:

Input Return Loss = S11 (dB)

Gain = S21 (dB)

Isolation = S12 (dB)

Output Return Loss = S22 (dB)

TEST CONDITIONS: $V_{DD} = +5.0$ V, $V_{EN} = +5.0$ V, $I_{DD} = 77$ mA, $I_{EN} = 2.10$ mA @ Temperature = $+25^\circ\text{C}$

See TSY-83LN+ for additional test data.

FREQ (MHz)	Gain (dB)	Isolation (dB)	Input Return Loss (dB)	Output Return Loss (dB)	Stability		1dB Comp. Output (dBm)	3dB Comp. Output (dBm)	Noise Figure (dB)	IP-3 Output Pout = +0 (dBm)
					K	Measure				
200	15.4	-33.0	-1.9	-4.0	1.4	0.9	17.7	21.4	19.7	31.6
300	20.2	-28.2	-5.7	-8.2	1.2	0.8	19.7	21.3	2.6	31.9
400	21.6	-26.7	-11.7	-14.1	1.1	0.7	20.0	21.7	1.9	32.8
500	22.0	-26.5	-18.0	-17.6	1.1	0.6	20.4	21.9	1.7	33.5
600	22.1	-26.3	-20.4	-17.2	1.1	0.6	20.7	22.1	1.5	32.6
700	22.1	-26.3	-19.0	-16.2	1.1	0.6	20.9	22.3	1.4	33.8
800	22.1	-26.3	-17.8	-15.5	1.1	0.6	21.0	22.4	1.3	32.8
900	22.1	-26.4	-17.0	-15.3	1.1	0.6	21.1	22.5	1.2	33.5
1000	22.1	-26.4	-16.5	-15.4	1.1	0.6	21.2	22.6	1.3	32.8
1100	22.1	-26.5	-16.3	-15.6	1.1	0.6	21.2	22.5	1.4	32.8
1200	22.1	-26.4	-16.3	-16.0	1.1	0.6	21.2	22.6	1.4	32.1
1300	22.1	-26.5	-16.5	-16.4	1.1	0.6	21.2	22.6	1.3	32.7
1400	22.1	-26.6	-16.6	-17.1	1.1	0.6	21.2	22.5	1.3	31.5
1500	22.1	-26.6	-16.8	-18.0	1.1	0.7	21.1	22.8	1.3	31.3
1600	22.1	-26.6	-17.0	-19.0	1.1	0.7	21.2	22.7	1.4	32.2
1700	22.1	-26.7	-17.0	-20.1	1.1	0.7	21.2	22.9	1.4	31.9
1800	22.1	-26.8	-17.2	-21.5	1.1	0.7	21.1	22.8	1.4	31.3
1900	22.1	-26.9	-17.2	-23.3	1.2	0.7	21.1	22.8	1.5	30.9
2000	22.1	-26.8	-16.8	-25.9	1.2	0.7	20.9	22.6	1.4	31.1
2100	22.1	-26.9	-16.4	-29.0	1.2	0.7	20.9	22.9	1.4	31.7
2200	22.1	-27.0	-15.9	-31.4	1.2	0.7	20.9	22.9	1.5	32.1
2300	22.1	-27.1	-15.4	-30.3	1.2	0.7	20.9	22.9	1.5	30.6
2400	22.1	-27.1	-14.9	-28.1	1.2	0.7	20.7	23.2	1.6	29.8
2500	22.1	-27.2	-14.5	-25.3	1.2	0.7	20.6	23.3	1.6	30.1
2600	22.1	-27.4	-13.9	-23.2	1.2	0.7	20.4	23.4	1.6	31.3
2700	22.0	-27.5	-13.7	-22.1	1.2	0.8	20.3	23.1	1.6	29.6
2800	22.1	-27.6	-13.1	-20.4	1.2	0.8	20.2	23.0	1.6	30.3
2900	22.0	-27.6	-12.9	-19.6	1.2	0.8	20.1	22.7	1.7	28.7
3000	22.0	-27.6	-12.4	-18.5	1.2	0.8	19.8	22.9	1.7	29.0
3100	22.0	-27.7	-12.1	-17.6	1.2	0.8	19.6	23.0	1.7	28.5
3200	22.0	-27.6	-11.8	-17.0	1.2	0.8	19.4	22.5	1.7	29.1
3300	22.0	-27.6	-11.5	-16.4	1.2	0.8	19.3	22.4	1.6	28.5
3400	22.0	-27.8	-11.2	-15.9	1.2	0.8	19.3	22.4	1.6	28.0
3500	22.0	-27.8	-11.1	-15.5	1.2	0.8	19.2	23.0	1.6	28.0
3600	22.0	-27.8	-11.1	-15.3	1.2	0.8	19.2	23.2	1.6	28.5
3700	22.1	-27.8	-11.0	-15.3	1.2	0.8	19.3	22.7	1.7	27.6
3800	22.1	-27.9	-11.0	-15.4	1.2	0.8	19.5	22.8	1.6	28.0
3900	22.1	-28.0	-11.0	-15.6	1.2	0.8	19.8	22.9	1.6	28.3
4000	22.2	-28.0	-10.8	-15.7	1.2	0.8	20.1	23.1	1.6	27.1
4100	22.2	-28.1	-10.9	-15.8	1.2	0.8	20.1	23.5	1.6	28.1
4200	22.2	-28.1	-11.1	-16.0	1.2	0.8	20.1	23.2	1.6	27.5
4300	22.3	-28.3	-11.4	-16.2	1.2	0.8	20.2	23.2	1.6	27.9
4400	22.3	-28.4	-11.6	-16.4	1.2	0.8	20.3	23.2	1.6	28.1
4500	22.3	-28.2	-12.1	-17.3	1.2	0.8	20.5	23.4	1.6	28.6
4600	22.3	-28.1	-12.8	-18.1	1.2	0.8	20.5	23.6	1.6	27.9
4700	22.4	-28.1	-13.0	-19.1	1.2	0.8	20.3	23.4	1.6	27.7
4800	22.5	-28.1	-13.1	-19.7	1.2	0.8	20.2	23.3	1.6	27.2
4900	22.6	-28.1	-13.2	-20.7	1.2	0.8	20.3	23.6	1.6	28.4
5000	22.7	-28.2	-13.5	-21.8	1.2	0.8	20.5	23.6	1.6	28.6
5100	22.8	-28.4	-14.0	-22.4	1.2	0.8	20.3	23.5	1.6	27.9
5200	22.9	-28.3	-14.4	-23.0	1.2	0.8	19.9	23.1	1.6	27.6
5300	23.0	-28.5	-15.0	-23.5	1.2	0.8	19.9	22.9	1.6	27.0
5400	23.0	-28.8	-16.1	-23.1	1.3	0.8	20.1	23.0	1.6	27.1
5500	23.0	-28.8	-17.6	-23.1	1.3	0.8	20.5	23.3	1.6	27.2
5600	22.9	-28.9	-20.5	-22.4	1.3	0.8	20.6	23.5	1.7	27.9
5700	22.8	-28.7	-22.6	-22.3	1.3	0.8	20.4	23.3	1.7	27.8
5800	22.9	-28.6	-24.0	-22.6	1.3	0.8	19.8	23.1	1.7	26.7
5900	23.0	-28.4	-25.2	-22.9	1.3	0.8	19.5	23.0	1.7	26.3
6000	23.1	-28.5	-25.3	-24.0	1.2	0.8	19.2	22.9	1.7	26.5
6100	23.3	-28.5	-23.8	-26.2	1.2	0.7	19.3	22.7	1.7	26.2
6200	23.4	-28.7	-21.5	-29.1	1.2	0.8	19.4	22.3	1.8	26.0
6300	23.5	-28.8	-19.4	-30.5	1.2	0.8	19.5	22.0	1.8	26.9
6400	23.5	-28.9	-17.5	-29.6	1.2	0.8	19.3	21.7	1.8	26.0
6500	23.5	-29.2	-15.8	-25.4	1.3	0.8	18.9	21.4	1.9	25.7
6600	23.5	-29.4	-13.9	-22.5	1.3	0.8	18.4	21.2	1.9	25.0
6700	23.4	-30.0	-12.0	-19.2	1.3	0.8	18.1	20.8	1.9	24.8
6800	23.1	-30.6	-10.7	-16.8	1.4	0.9	18.2	20.6	2.0	24.3
6900	22.7	-31.0	-10.2	-16.3	1.4	0.9	18.6	20.3	2.1	25.5
7000	22.4	-31.2	-9.6	-16.6	1.5	1.0	18.9	20.0	2.1	25.6
7100	22.7	-30.9	-9.3	-16.5	1.4	0.9	18.8	19.9	2.1	24.6
7200	22.6	-31.1	-8.6	-14.5	1.4	0.9	18.4	20.1	2.1	23.9
7300	22.5	-31.4	-7.9	-13.2	1.4	1.0	18.3	20.1	2.2	23.7
7400	22.4	-32.0	-7.0	-11.6	1.5	1.0	18.7	20.4	2.2	24.9
7500	22.2	-32.6	-6.1	-10.4	1.5	1.0	19.2	20.1	2.2	24.0
7600	21.9	-33.3	-5.4	-9.3	1.6	1.0	19.5	20.2	2.3	24.1
7700	21.4	-34.6	-4.8	-8.3	1.7	1.0	19.3	20.2	2.3	23.0
7800	20.9	-35.4	-4.3	-7.5	1.8	1.0	18.8	19.7	2.4	22.7
7900	20.3	-36.9	-3.9	-6.8	2.0	1.0	18.5	19.7	2.4	22.5
8000	19.6	-38.6	-3.5	-6.3	2.4	1.0	18.4	19.2	2.5	23.1

*Typical Performance Data***NOTE: Use PDF Bookmarks to view DATA at required conditions****Definitions:**

Input Return Loss = S11 (dB)

Gain = S21 (dB)

Isolation = S12 (dB)

Output Return Loss = S22 (dB)

TEST CONDITIONS: $V_{DD} = +5.0$ V, $V_{EN} = +5.0$ V, $I_{DD} = 80$ mA, $I_{EN} = 2.15$ mA @ Temperature = $+25^\circ\text{C}$

See TSY-83LN+ for additional test data.

FREQ (MHz)	Gain (dB)	Isolation (dB)	Input Return Loss (dB)	Output Return Loss (dB)	Stability		1dB Comp. Output (dBm)	3dB Comp. Output (dBm)	Noise Figure (dB)	IP-3 Output Pout = +0 (dBm)
					K	Measure				
5500	22.5	-29.1	-11.0	-10.0	1.2	0.7	20.3	22.9	1.4	27.3
5600	22.5	-29.1	-11.5	-10.2	1.3	0.7	20.5	23.3	1.4	27.3
5700	22.5	-28.8	-11.6	-10.6	1.2	0.7	20.6	23.4	1.4	27.5
5800	22.7	-28.7	-11.5	-11.0	1.2	0.7	19.9	23.4	1.4	27.0
5900	22.9	-28.7	-11.1	-11.4	1.2	0.7	20.1	23.2	1.4	27.6
6000	23.0	-28.7	-10.9	-11.6	1.2	0.7	19.7	23.4	1.4	27.0
6100	23.1	-28.8	-10.8	-11.7	1.2	0.7	19.2	23.2	1.5	26.9
6200	23.2	-28.9	-10.9	-11.9	1.2	0.7	19.1	23.2	1.5	26.5
6300	23.3	-28.9	-10.9	-12.0	1.2	0.7	18.7	22.8	1.5	25.7
6400	23.4	-29.1	-10.8	-12.0	1.2	0.7	18.8	22.6	1.5	25.3
6500	23.5	-29.3	-10.8	-11.9	1.2	0.7	19.1	22.4	1.5	25.4
6600	23.5	-29.4	-11.1	-12.0	1.2	0.7	19.6	22.4	1.5	25.8
6700	23.5	-29.7	-11.2	-11.9	1.3	0.7	19.9	22.5	1.6	26.0
6800	23.5	-29.6	-11.6	-12.4	1.3	0.7	20.1	22.5	1.5	25.8
6900	23.4	-29.8	-12.0	-12.7	1.3	0.8	19.8	22.1	1.6	25.9
7000	23.5	-29.6	-12.3	-13.2	1.3	0.8	20.1	22.2	1.6	26.0
7100	23.6	-29.6	-12.2	-13.3	1.3	0.8	20.2	22.1	1.6	26.0
7200	23.7	-29.8	-12.0	-13.2	1.3	0.8	20.3	22.0	1.7	26.6
7300	23.8	-29.8	-12.0	-13.1	1.3	0.8	19.9	21.6	1.7	26.1
7400	23.8	-30.1	-11.7	-12.8	1.3	0.8	19.8	21.3	1.7	25.8
7500	23.8	-30.3	-11.5	-12.7	1.3	0.8	20.1	21.4	1.8	25.8
7600	23.8	-30.6	-11.2	-12.7	1.3	0.8	19.7	21.2	1.9	26.4
7700	23.8	-31.0	-10.7	-12.5	1.3	0.8	20.2	21.4	1.9	26.2
7800	23.7	-31.5	-10.2	-12.6	1.4	0.8	19.8	21.0	2.0	26.4
7900	23.5	-31.8	-9.6	-12.8	1.4	0.9	19.6	20.9	2.1	26.1
8000	23.3	-32.4	-9.0	-13.2	1.5	0.9	19.5	20.8	2.2	26.1
8100	23.1	-32.9	-8.3	-14.0	1.6	1.0	19.9	21.2	2.3	25.8
8200	22.6	-33.5	-7.6	-15.5	1.7	1.0	19.7	21.1	2.4	26.2
8300	22.2	-33.7	-7.2	-17.3	1.8	1.1	19.1	20.5	2.5	26.2
8400	21.9	-33.9	-6.8	-18.7	1.8	1.1	19.2	20.5	2.7	26.3
8500	21.7	-34.2	-6.4	-19.9	1.9	1.2	18.7	20.1	2.8	25.5



ISO 9001 ISO 14001 AS 9100 CERTIFIED

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minic

MMIC Amplifier

TSY-83LN-D+

Typical Performance Data

NOTE: Use PDF Bookmarks to view DATA at required conditions

Definitions:

Input Return Loss = S11 (dB)

Gain = S21 (dB)

Isolation = S12 (dB)

Output Return Loss = S22 (dB)

TEST CONDITIONS: V_{DD} = +5.0 V, V_{EN} = 0 V, I_{DD} = 4 mA, I_{EN} = 0 mA @ Temperature = +25°C

See TSY-83LN+ for additional test data.

FREQ	Gain	Isolation	Input Return Loss	Output Return Loss	Stability		Noise Figure
(MHz)	(dB)	(dB)	(dB)	(dB)	K	Measure	(dB)
200	-3.2	-3.5	-4.2	-7.2	1.1	0.7	2.9
300	-1.9	-2.1	-6.8	-10.2	1.0	0.5	2.6
400	-1.4	-1.5	-9.3	-12.7	1.0	0.5	1.6
500	-1.1	-1.2	-11.8	-14.9	1.0	0.4	1.8
600	-0.9	-1.1	-14.3	-16.8	1.0	0.4	1.0
700	-0.9	-1.0	-17.1	-18.5	1.0	0.4	0.7
800	-0.8	-1.0	-20.4	-19.5	1.0	0.4	1.1
900	-0.8	-1.0	-24.6	-20.0	1.0	0.4	1.5
1000	-0.8	-1.0	-31.3	-20.3	1.0	0.4	1.0
1100	-0.8	-1.0	-44.8	-20.1	1.0	0.3	0.9
1200	-0.8	-1.0	-32.0	-19.8	1.0	0.4	1.1
1300	-0.8	-1.0	-26.9	-19.3	1.0	0.4	1.2
1400	-0.8	-1.0	-23.9	-18.7	1.0	0.4	1.1
1500	-0.8	-1.0	-21.9	-18.2	1.0	0.4	1.2
1600	-0.8	-1.1	-20.8	-17.7	1.0	0.4	1.3
1700	-0.9	-1.1	-19.8	-17.3	1.0	0.4	0.9
1800	-0.9	-1.1	-19.1	-17.2	1.0	0.4	1.3
1900	-0.9	-1.2	-18.3	-17.1	1.0	0.4	1.1
2000	-0.9	-1.2	-17.7	-17.1	1.0	0.4	1.0
2100	-0.9	-1.2	-17.1	-17.3	1.0	0.4	0.9
2200	-1.0	-1.3	-16.6	-17.5	1.0	0.4	1.0
2300	-1.0	-1.3	-16.3	-17.9	1.0	0.4	1.2
2400	-1.0	-1.3	-15.9	-18.5	1.0	0.5	1.4
2500	-1.0	-1.4	-15.7	-18.8	1.0	0.5	1.3
2600	-1.1	-1.5	-15.7	-19.3	1.0	0.5	1.2
2700	-1.1	-1.5	-15.8	-19.8	1.0	0.5	1.5
2800	-1.1	-1.6	-15.8	-20.5	1.0	0.5	1.1
2900	-1.1	-1.6	-15.8	-21.4	1.1	0.5	1.6
3000	-1.1	-1.6	-15.8	-22.5	1.1	0.5	1.7
3100	-1.1	-1.6	-15.8	-23.8	1.1	0.5	1.6
3200	-1.1	-1.6	-15.7	-25.2	1.0	0.5	1.5
3300	-1.1	-1.6	-15.8	-27.6	1.0	0.5	1.3
3400	-1.1	-1.6	-15.7	-31.0	1.0	0.5	1.6
3500	-1.1	-1.6	-15.7	-34.9	1.0	0.5	1.8
3600	-1.2	-1.6	-15.6	-32.3	1.1	0.5	1.5
3700	-1.2	-1.6	-15.4	-28.3	1.1	0.5	1.7
3800	-1.2	-1.6	-15.1	-24.7	1.1	0.5	1.7
3900	-1.2	-1.6	-14.8	-22.2	1.1	0.5	1.6
4000	-1.3	-1.6	-14.4	-20.5	1.1	0.5	1.8
4100	-1.3	-1.7	-14.0	-19.0	1.1	0.5	1.6
4200	-1.3	-1.7	-13.5	-17.7	1.1	0.5	1.7
4300	-1.4	-1.8	-13.1	-16.6	1.1	0.5	2.3
4400	-1.4	-1.8	-12.7	-15.5	1.1	0.6	1.6
4500	-1.4	-1.9	-12.1	-14.5	1.1	0.5	2.4
4600	-1.5	-1.9	-11.6	-13.6	1.1	0.5	2.0
4700	-1.5	-1.9	-11.1	-12.9	1.1	0.5	1.0
4800	-1.5	-2.0	-10.8	-12.4	1.1	0.5	2.5
4900	-1.5	-2.0	-10.5	-11.9	1.1	0.5	1.7
5000	-1.6	-2.1	-10.2	-11.4	1.1	0.5	1.8
5100	-1.6	-2.1	-10.0	-11.0	1.1	0.5	1.4
5200	-1.6	-2.2	-9.8	-10.7	1.1	0.5	1.9
5300	-1.6	-2.2	-9.5	-10.5	1.1	0.5	2.4
5400	-1.7	-2.3	-9.4	-10.2	1.1	0.5	1.7
5500	-1.7	-2.4	-9.2	-9.9	1.1	0.5	1.7
5600	-1.8	-2.4	-8.9	-9.7	1.1	0.5	2.1
5700	-1.8	-2.4	-8.7	-9.5	1.1	0.5	2.2
5800	-1.8	-2.4	-8.5	-9.2	1.1	0.5	2.0
5900	-1.8	-2.4	-8.4	-9.1	1.1	0.5	2.3
6000	-1.8	-2.4	-8.4	-9.0	1.1	0.5	1.9
6100	-1.7	-2.4	-8.4	-8.9	1.1	0.5	1.7
6200	-1.7	-2.4	-8.5	-8.9	1.1	0.5	1.9
6300	-1.7	-2.4	-8.5	-8.9	1.1	0.5	1.9
6400	-1.8	-2.5	-8.5	-8.9	1.1	0.5	2.0
6500	-1.8	-2.5	-8.6	-8.9	1.1	0.5	2.2
6600	-1.8	-2.5	-8.6	-8.9	1.1	0.5	1.4
6700	-1.8	-2.5	-8.7	-9.0	1.1	0.5	2.3
6800	-1.8	-2.6	-8.8	-9.1	1.1	0.5	2.1
6900	-1.8	-2.6	-8.8	-9.0	1.1	0.5	2.2
7000	-1.9	-2.6	-8.7	-8.9	1.1	0.6	1.8
7100	-1.8	-2.6	-8.8	-8.8	1.1	0.5	1.7
7200	-1.8	-2.6	-8.9	-8.9	1.1	0.5	2.7
7300	-1.8	-2.6	-8.9	-8.8	1.1	0.5	1.9
7400	-1.8	-2.6	-8.9	-8.9	1.1	0.5	1.8
7500	-1.8	-2.6	-9.0	-8.8	1.1	0.5	2.2
7600	-1.9	-2.6	-9.0	-8.8	1.1	0.5	2.4
7700	-1.9	-2.7	-9.0	-8.8	1.1	0.5	2.3
7800	-1.9	-2.7	-9.0	-8.8	1.1	0.5	2.0
7900	-2.0	-2.8	-8.9	-8.7	1.1	0.6	2.3
8000	-2.1	-2.8	-8.9	-8.6	1.1	0.6	2.4



ISO 9001 ISO 14001 AS 9100 CERTIFIED

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minic

Typical Performance Data

NOTE: Use PDF Bookmarks to view DATA at required conditions

Definitions:

Input Return Loss = S11 (dB)
 Gain = S21 (dB)
 Isolation = S12 (dB)
 Output Return Loss = S22 (dB)

TEST CONDITIONS: V_{DD} = +5.0 V, V_{EN} = 0 V, I_{DD} = 4 mA, I_{EN} = 0 mA @ Temperature = +25°C

See TSY-83LN+ for additional test data.

FREQ (MHz)	Gain (dB)	Isolation (dB)	Input Return Loss (dB)	Output Return Loss (dB)	Stability		Noise Figure (dB)
					K	Measure	
5500	-1.3	-1.9	-18.5	-20.6	1.1	0.6	1.8
5600	-1.2	-1.9	-19.3	-23.6	1.1	0.6	1.4
5700	-1.2	-1.8	-19.6	-27.1	1.1	0.6	1.8
5800	-1.2	-1.8	-19.4	-28.0	1.1	0.6	1.7
5900	-1.1	-1.8	-19.1	-24.9	1.1	0.6	1.0
6000	-1.1	-1.8	-18.4	-22.2	1.1	0.6	1.7
6100	-1.2	-1.8	-17.5	-19.9	1.1	0.6	1.1
6200	-1.2	-1.9	-16.5	-18.1	1.1	0.6	1.5
6300	-1.2	-1.9	-15.6	-16.5	1.1	0.6	1.6
6400	-1.3	-2.0	-14.6	-15.2	1.1	0.6	1.4
6500	-1.3	-2.0	-13.8	-14.2	1.1	0.6	1.4
6600	-1.4	-2.1	-12.9	-13.2	1.1	0.6	1.7
6700	-1.5	-2.2	-12.1	-12.4	1.1	0.6	1.4
6800	-1.6	-2.3	-11.4	-11.5	1.1	0.6	1.7
6900	-1.7	-2.4	-10.7	-10.8	1.1	0.6	1.6
7000	-1.7	-2.5	-10.0	-10.0	1.1	0.6	1.5
7100	-1.8	-2.6	-9.4	-9.3	1.1	0.6	1.4
7200	-1.9	-2.7	-8.9	-8.8	1.1	0.6	1.9
7300	-2.0	-2.8	-8.4	-8.2	1.1	0.6	1.2
7400	-2.2	-2.9	-7.9	-7.8	1.1	0.6	2.0
7500	-2.3	-3.1	-7.5	-7.3	1.1	0.6	1.4
7600	-2.5	-3.3	-7.1	-6.9	1.1	0.6	2.3
7700	-2.7	-3.4	-6.6	-6.5	1.1	0.5	2.1
7800	-2.9	-3.6	-6.3	-6.1	1.1	0.5	2.4
7900	-3.1	-3.8	-5.9	-5.8	1.1	0.5	2.6
8000	-3.3	-4.1	-5.6	-5.5	1.1	0.5	2.4
8100	-3.6	-4.3	-5.2	-5.2	1.1	0.5	2.1
8200	-3.9	-4.6	-4.9	-4.9	1.2	0.6	2.3
8300	-4.2	-4.9	-4.6	-4.6	1.2	0.5	2.6
8400	-4.4	-5.1	-4.2	-4.3	1.2	0.5	1.9
8500	-4.7	-5.4	-4.0	-4.0	1.2	0.5	2.6



ISO 9001 ISO 14001 AS 9100 CERTIFIED

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping
 Mouser Electronics Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minic.com

MMIC Amplifier

TSY-83LN-D+

Typical Performance Data

NOTE: Use PDF Bookmarks to view DATA at required conditions

Definitions:

Input Return Loss = S11 (dB)

Gain = S21 (dB)

Isolation = S12 (dB)

Output Return Loss = S22 (dB)

TEST CONDITIONS: $V_{DD} = +5.25$ V, $V_{EN} = +5.25$ V, $I_{DD} = 84$ mA, $I_{EN} = 2.20$ mA @ Temperature = $+25^\circ\text{C}$

See TSY-83LN+ for additional test data.

FREQ (MHz)	Gain (dB)	Isolation (dB)	Input Return Loss (dB)	Output Return Loss (dB)	Stability		1dB Comp. Output (dBm)	3dB Comp. Output (dBm)	Noise Figure (dB)	IP-3 Output Pout = +0 (dBm)
200	15.6	-33.3	-1.9	-4.0	1.4	0.8	18.1	21.9	19.7	32.8
300	20.4	-28.3	-5.7	-8.2	1.2	0.8	20.3	21.9	2.7	33.1
400	21.8	-26.8	-11.9	-14.0	1.1	0.7	20.5	22.2	1.9	34.0
500	22.2	-26.6	-18.2	-17.0	1.1	0.6	20.9	22.4	1.7	34.3
600	22.2	-26.5	-19.9	-16.4	1.1	0.6	21.2	22.6	1.5	32.6
700	22.2	-26.6	-18.2	-15.5	1.1	0.6	21.4	22.7	1.4	34.5
800	22.2	-26.5	-17.0	-14.8	1.1	0.6	21.5	22.8	1.4	33.3
900	22.2	-26.6	-16.3	-14.7	1.1	0.6	21.6	23.0	1.3	37.5
1000	22.2	-26.7	-15.9	-14.7	1.1	0.6	21.7	23.0	1.4	32.9
1100	22.2	-26.6	-15.7	-14.9	1.1	0.6	21.7	23.0	1.4	34.2
1200	22.2	-26.7	-15.8	-15.2	1.1	0.6	21.7	23.1	1.3	32.9
1300	22.2	-26.7	-16.0	-15.6	1.1	0.6	21.7	23.1	1.4	33.5
1400	22.2	-26.8	-16.2	-16.2	1.1	0.6	21.7	23.0	1.4	32.9
1500	22.2	-26.9	-16.6	-17.1	1.1	0.7	21.6	23.2	1.4	32.7
1600	22.2	-26.8	-16.8	-17.9	1.1	0.7	21.7	23.2	1.4	33.8
1700	22.3	-26.9	-17.0	-18.8	1.1	0.7	21.7	23.4	1.4	32.8
1800	22.3	-27.0	-17.3	-20.1	1.1	0.7	21.6	23.3	1.4	32.6
1900	22.3	-26.9	-17.4	-21.7	1.1	0.7	21.5	23.3	1.4	31.2
2000	22.3	-26.9	-17.2	-23.9	1.1	0.7	21.4	23.1	1.4	32.3
2100	22.3	-27.0	-16.9	-26.5	1.2	0.7	21.4	23.4	1.4	32.7
2200	22.3	-27.1	-16.5	-29.4	1.2	0.7	21.4	23.3	1.5	33.1
2300	22.3	-27.1	-16.0	-30.8	1.2	0.7	21.4	23.4	1.5	31.8
2400	22.3	-27.3	-15.5	-29.7	1.2	0.7	21.2	23.6	1.5	30.6
2500	22.3	-27.3	-15.1	-27.1	1.2	0.7	21.1	23.8	1.5	29.7
2600	22.3	-27.5	-14.6	-24.7	1.2	0.7	20.9	23.8	1.6	32.9
2700	22.3	-27.5	-14.3	-23.6	1.2	0.8	20.8	23.6	1.6	30.9
2800	22.3	-27.7	-13.7	-21.6	1.2	0.8	20.7	23.4	1.7	31.4
2900	22.2	-27.7	-13.4	-20.7	1.2	0.8	20.6	23.2	1.7	29.5
3000	22.2	-27.8	-12.9	-19.4	1.2	0.8	20.3	23.3	1.7	30.0
3100	22.2	-27.7	-12.6	-18.5	1.2	0.8	20.1	23.4	1.7	30.3
3200	22.2	-27.7	-12.3	-17.8	1.2	0.8	19.9	23.0	1.7	29.6
3300	22.2	-27.7	-11.9	-17.1	1.2	0.8	19.9	22.9	1.6	29.2
3400	22.2	-27.8	-11.6	-16.7	1.2	0.8	19.9	22.9	1.7	28.7
3500	22.2	-27.8	-11.5	-16.2	1.2	0.8	19.9	23.4	1.6	28.7
3600	22.2	-28.0	-11.4	-16.0	1.2	0.8	19.9	23.6	1.6	29.3
3700	22.3	-28.1	-11.4	-15.9	1.2	0.8	19.9	23.2	1.6	28.6
3800	22.3	-28.0	-11.4	-16.1	1.2	0.8	20.1	23.2	1.6	29.0
3900	22.3	-28.0	-11.3	-16.3	1.2	0.8	20.4	23.4	1.6	30.0
4000	22.4	-28.1	-11.1	-16.4	1.2	0.8	20.6	23.6	1.6	28.2
4100	22.4	-28.2	-11.2	-16.6	1.2	0.8	20.7	23.9	1.6	28.7
4200	22.5	-28.1	-11.3	-16.8	1.2	0.8	20.7	23.7	1.6	28.5
4300	22.5	-28.4	-11.6	-17.1	1.2	0.8	20.8	23.6	1.6	29.3
4400	22.5	-28.5	-11.9	-17.2	1.2	0.8	20.9	23.6	1.6	28.9
4500	22.5	-28.4	-12.4	-18.2	1.2	0.8	21.0	23.8	1.6	29.7
4600	22.5	-28.2	-13.1	-19.2	1.2	0.8	21.0	24.0	1.6	28.9
4700	22.6	-28.1	-13.2	-20.3	1.2	0.8	20.9	23.8	1.6	28.5
4800	22.7	-28.1	-13.3	-21.1	1.2	0.8	20.9	23.7	1.6	28.2
4900	22.8	-28.2	-13.3	-22.4	1.2	0.8	20.9	24.0	1.6	29.3
5000	22.9	-28.3	-13.7	-23.5	1.2	0.8	21.1	24.0	1.6	29.4
5100	23.0	-28.5	-14.1	-24.4	1.2	0.8	20.9	23.8	1.6	28.6
5200	23.1	-28.4	-14.6	-25.2	1.2	0.8	20.6	23.5	1.6	28.0
5300	23.2	-28.5	-15.2	-25.8	1.2	0.8	20.5	23.4	1.7	27.5
5400	23.2	-28.8	-16.4	-25.3	1.2	0.8	20.6	23.5	1.6	27.9
5500	23.2	-29.0	-17.9	-25.2	1.3	0.8	21.0	23.6	1.7	27.7
5600	23.1	-29.0	-20.9	-24.0	1.3	0.8	21.1	23.8	1.6	28.7
5700	23.0	-28.7	-22.8	-23.6	1.3	0.8	20.9	23.7	1.7	28.2
5800	23.1	-28.5	-23.9	-23.5	1.2	0.8	20.5	23.5	1.7	27.3
5900	23.2	-28.6	-25.0	-24.0	1.3	0.8	20.1	23.4	1.7	26.7
6000	23.3	-28.6	-25.8	-25.0	1.2	0.7	19.9	23.2	1.7	27.3
6100	23.5	-28.5	-24.6	-27.2	1.2	0.7	19.9	23.1	1.7	26.9
6200	23.6	-28.7	-22.4	-32.0	1.2	0.7	19.9	22.6	1.8	26.5
6300	23.7	-28.9	-20.2	-37.6	1.2	0.7	20.0	22.4	1.8	27.1
6400	23.8	-29.0	-18.2	-35.1	1.2	0.8	19.8	22.0	1.9	26.8
6500	23.7	-29.2	-16.3	-27.8	1.2	0.8	19.4	21.7	1.9	26.3
6600	23.7	-29.5	-14.3	-23.8	1.3	0.8	18.8	21.5	1.9	25.6
6700	23.7	-30.0	-12.3	-19.9	1.3	0.8	18.6	21.1	2.0	25.1
6800	23.3	-30.7	-10.9	-17.4	1.4	0.9	18.7	20.9	2.0	24.8
6900	22.9	-31.0	-10.4	-16.9	1.4	0.9	19.1	20.7	2.0	26.0
7000	22.7	-31.2	-9.8	-17.2	1.5	1.0	19.4	20.4	2.1	26.0
7100	22.9	-30.9	-9.5	-16.9	1.4	0.9	19.2	20.4	2.1	25.1
7200	22.9	-31.2	-8.7	-14.7	1.4	0.9	18.8	20.5	2.1	24.3
7300	22.8	-31.5	-8.0	-13.3	1.4	0.9	18.7	20.5	2.2	24.2
7400	22.7	-31.8	-7.0	-11.7	1.4	0.9	19.1	20.8	2.2	25.3
7500	22.5	-32.6	-6.1	-10.4	1.5	1.0	19.6	20.4	2.3	24.6
7600	22.1	-33.7	-5.4	-9.3	1.6	1.0	19.9	20.5	2.3	24.6
7700	21.6	-34.6	-4.8	-8.3	1.7	1.0	19.7	20.5	2.4	23.7
7800	21.2	-35.6	-4.3	-7.5	1.8	1.0	19.2	20.1	2.4	23.1
7900	20.5	-37.3	-3.8	-6.8	2.1	1.0	18.9	20.0	2.5	23.0
8000	19.8	-39.3	-3.5	-6.2	2.5	1.0	18.8	19.5	2.5	23.7

MMIC Amplifier

TSY-83LN-D+

Typical Performance Data

NOTE: Use PDF Bookmarks to view DATA at required conditions

Definitions:

Input Return Loss = S11 (dB)

Gain = S21 (dB)

Isolation = S12 (dB)

Output Return Loss = S22 (dB)

TEST CONDITIONS: $V_{DD} = +5.25$ V, $V_{EN} = +5.25$ V, $I_{DD} = 87$ mA, $I_{EN} = 2.26$ mA @ Temperature = $+25^\circ\text{C}$

See TSY-83LN+ for additional test data.

FREQ (MHz)	Gain (dB)	Isolation (dB)	Input Return Loss (dB)	Output Return Loss (dB)	Stability		1dB Comp. Output (dBm)	3dB Comp. Output (dBm)	Noise Figure (dB)	IP-3 Output Pout = +0 (dBm)
5500	22.7	-29.1	-11.0	-10.4	1.2	0.7	20.7	23.3	1.4	28.0
5600	22.7	-29.2	-11.6	-10.5	1.3	0.7	21.0	23.6	1.4	27.9
5700	22.7	-28.9	-11.7	-11.0	1.2	0.7	21.0	23.8	1.4	28.1
5800	22.9	-28.8	-11.6	-11.4	1.2	0.7	20.5	23.7	1.4	27.4
5900	23.1	-28.7	-11.1	-11.8	1.2	0.7	20.7	23.6	1.4	28.0
6000	23.2	-28.8	-11.0	-12.0	1.2	0.7	20.4	23.7	1.4	27.7
6100	23.4	-28.8	-10.9	-12.1	1.2	0.7	20.0	23.5	1.5	27.4
6200	23.4	-28.9	-11.0	-12.2	1.2	0.7	19.8	23.4	1.5	27.1
6300	23.5	-28.9	-11.0	-12.2	1.2	0.7	19.4	23.0	1.5	26.2
6400	23.6	-29.1	-10.9	-12.2	1.2	0.7	19.4	22.8	1.5	25.8
6500	23.7	-29.3	-10.9	-12.1	1.2	0.7	19.7	22.6	1.5	25.9
6600	23.7	-29.4	-11.2	-12.1	1.2	0.7	20.1	22.8	1.6	26.2
6700	23.7	-29.7	-11.3	-12.0	1.2	0.7	20.3	22.7	1.6	26.4
6800	23.7	-29.7	-11.7	-12.5	1.3	0.7	20.5	22.8	1.6	26.3
6900	23.6	-29.7	-12.2	-12.7	1.3	0.7	20.2	22.4	1.6	26.3
7000	23.7	-29.6	-12.5	-13.1	1.3	0.7	20.5	22.4	1.6	26.3
7100	23.8	-29.6	-12.4	-13.1	1.2	0.7	20.7	22.4	1.6	26.4
7200	23.9	-29.9	-12.2	-12.9	1.3	0.7	20.7	22.4	1.7	26.8
7300	24.0	-29.9	-12.2	-12.8	1.2	0.7	20.4	22.0	1.7	26.4
7400	24.0	-30.1	-11.9	-12.4	1.3	0.7	20.2	21.7	1.8	26.0
7500	24.0	-30.4	-11.6	-12.3	1.3	0.8	20.5	21.8	1.8	26.0
7600	24.0	-30.7	-11.3	-12.2	1.3	0.8	20.2	21.6	1.9	26.4
7700	24.0	-31.0	-10.8	-12.0	1.3	0.8	20.6	21.8	1.9	26.3
7800	23.9	-31.4	-10.3	-12.1	1.4	0.8	20.2	21.5	2.0	26.6
7900	23.7	-31.9	-9.7	-12.3	1.4	0.9	19.9	21.3	2.1	26.0
8000	23.5	-32.4	-9.1	-12.6	1.5	0.9	19.8	21.2	2.2	26.1
8100	23.3	-33.1	-8.3	-13.3	1.6	1.0	20.3	21.6	2.3	25.6
8200	22.8	-33.7	-7.7	-14.8	1.7	1.0	20.1	21.5	2.4	26.2
8300	22.4	-33.9	-7.3	-16.4	1.8	1.1	19.5	20.9	2.5	26.1
8400	22.1	-34.1	-6.8	-17.7	1.8	1.1	19.6	21.0	2.7	26.2
8500	21.9	-34.3	-6.4	-18.7	1.9	1.1	19.1	20.5	2.8	25.5



ISO 9001 ISO 14001 AS 9100 CERTIFIED

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minic.com

Typical Performance Data

NOTE: Use PDF Bookmarks to view DATA at required conditions**Definitions:**

Input Return Loss = S11 (dB)

Gain = S21 (dB)

Isolation = S12 (dB)

Output Return Loss = S22 (dB)

TEST CONDITIONS: V_{DD} = +5.25 V, V_{EN} = 0 V, I_{DD} = 4 mA, I_{EN} = 0 mA @ Temperature = +25°C

See TSY-83LN+ for additional test data.

FREQ (MHz)	Gain (dB)	Isolation (dB)	Input Return Loss (dB)	Output Return Loss (dB)	Stability		Noise Figure (dB)
					K	Measure	
200	-3.3	-3.5	-4.2	-7.2	1.1	0.7	2.7
300	-1.9	-2.1	-6.8	-10.2	1.0	0.5	2.7
400	-1.4	-1.5	-9.3	-12.6	1.0	0.4	1.5
500	-1.1	-1.2	-11.8	-14.9	1.0	0.4	1.7
600	-0.9	-1.1	-14.3	-16.8	1.0	0.4	1.1
700	-0.9	-1.0	-17.1	-18.4	1.0	0.4	0.9
800	-0.8	-1.0	-20.4	-19.5	1.0	0.4	0.7
900	-0.8	-1.0	-24.6	-20.0	1.0	0.4	0.6
1000	-0.8	-1.0	-31.3	-20.3	1.0	0.3	1.0
1100	-0.8	-1.0	-44.4	-20.2	1.0	0.3	0.8
1200	-0.8	-1.0	-31.9	-19.8	1.0	0.4	0.8
1300	-0.8	-1.0	-26.9	-19.3	1.0	0.4	0.8
1400	-0.8	-1.0	-23.9	-18.7	1.0	0.4	0.8
1500	-0.8	-1.0	-21.9	-18.2	1.0	0.4	0.9
1600	-0.8	-1.1	-20.7	-17.7	1.0	0.4	1.1
1700	-0.9	-1.1	-19.9	-17.3	1.0	0.4	1.0
1800	-0.9	-1.1	-19.1	-17.2	1.0	0.4	0.9
1900	-0.9	-1.2	-18.3	-17.1	1.0	0.4	1.2
2000	-0.9	-1.2	-17.7	-17.2	1.0	0.4	1.2
2100	-0.9	-1.2	-17.1	-17.3	1.0	0.4	1.2
2200	-1.0	-1.3	-16.6	-17.6	1.0	0.4	1.0
2300	-1.0	-1.3	-16.3	-18.0	1.0	0.4	1.2
2400	-1.0	-1.4	-15.9	-18.5	1.0	0.5	1.5
2500	-1.0	-1.4	-15.7	-18.9	1.0	0.5	1.6
2600	-1.0	-1.5	-15.7	-19.3	1.0	0.5	1.4
2700	-1.1	-1.5	-15.8	-19.9	1.0	0.5	1.7
2800	-1.1	-1.6	-15.8	-20.6	1.0	0.5	1.5
2900	-1.1	-1.6	-15.8	-21.4	1.1	0.5	1.5
3000	-1.1	-1.6	-15.8	-22.5	1.1	0.5	1.5
3100	-1.1	-1.6	-15.8	-23.7	1.1	0.5	1.3
3200	-1.1	-1.6	-15.7	-25.3	1.0	0.5	1.5
3300	-1.1	-1.6	-15.7	-27.5	1.0	0.5	1.3
3400	-1.1	-1.6	-15.7	-31.0	1.0	0.5	1.2
3500	-1.1	-1.6	-15.6	-34.9	1.0	0.5	1.3
3600	-1.2	-1.6	-15.6	-32.3	1.1	0.5	1.6
3700	-1.2	-1.6	-15.4	-28.4	1.1	0.5	1.8
3800	-1.2	-1.6	-15.1	-24.6	1.1	0.5	1.3
3900	-1.2	-1.6	-14.8	-22.1	1.1	0.5	1.8
4000	-1.2	-1.7	-14.3	-20.4	1.1	0.5	1.9
4100	-1.3	-1.7	-14.0	-19.0	1.1	0.5	1.6
4200	-1.3	-1.7	-13.5	-17.7	1.1	0.5	1.8
4300	-1.3	-1.8	-13.1	-16.5	1.1	0.5	1.9
4400	-1.4	-1.8	-12.6	-15.5	1.1	0.6	1.9
4500	-1.4	-1.9	-12.1	-14.5	1.1	0.5	1.7
4600	-1.5	-1.9	-11.5	-13.6	1.1	0.5	2.0
4700	-1.5	-1.9	-11.1	-12.9	1.1	0.5	1.9
4800	-1.5	-2.0	-10.8	-12.4	1.1	0.5	2.4
4900	-1.5	-2.0	-10.5	-11.9	1.1	0.5	1.6
5000	-1.6	-2.1	-10.2	-11.4	1.1	0.5	1.9
5100	-1.6	-2.1	-9.9	-11.0	1.1	0.5	1.1
5200	-1.6	-2.2	-9.7	-10.7	1.1	0.5	1.1
5300	-1.6	-2.2	-9.5	-10.4	1.1	0.5	1.2
5400	-1.7	-2.3	-9.4	-10.2	1.1	0.5	1.6
5500	-1.7	-2.4	-9.2	-10.0	1.1	0.5	1.4
5600	-1.8	-2.4	-8.9	-9.7	1.1	0.5	2.0
5700	-1.8	-2.4	-8.7	-9.4	1.1	0.5	1.9
5800	-1.8	-2.4	-8.5	-9.2	1.1	0.5	2.0
5900	-1.8	-2.4	-8.4	-9.1	1.1	0.5	1.9
6000	-1.8	-2.4	-8.4	-8.9	1.1	0.5	1.2
6100	-1.7	-2.4	-8.4	-8.9	1.1	0.5	2.2
6200	-1.7	-2.4	-8.5	-8.9	1.1	0.5	2.0
6300	-1.7	-2.4	-8.5	-8.9	1.1	0.5	2.0
6400	-1.8	-2.5	-8.5	-8.9	1.1	0.5	2.6
6500	-1.8	-2.5	-8.5	-8.9	1.1	0.5	2.0
6600	-1.8	-2.5	-8.6	-8.9	1.1	0.5	2.0
6700	-1.8	-2.5	-8.7	-9.0	1.1	0.5	2.3
6800	-1.8	-2.6	-8.8	-9.1	1.1	0.5	2.3
6900	-1.8	-2.6	-8.8	-9.0	1.1	0.5	2.4
7000	-1.9	-2.6	-8.7	-8.9	1.1	0.5	2.4
7100	-1.8	-2.6	-8.8	-8.8	1.1	0.5	2.0
7200	-1.8	-2.6	-8.9	-8.8	1.1	0.5	2.8
7300	-1.8	-2.6	-8.9	-8.8	1.1	0.5	2.3
7400	-1.8	-2.6	-8.9	-8.9	1.1	0.5	2.3
7500	-1.8	-2.6	-9.0	-8.8	1.1	0.5	2.6
7600	-1.9	-2.6	-9.0	-8.8	1.1	0.5	2.1
7700	-1.9	-2.7	-9.0	-8.8	1.1	0.5	2.2
7800	-1.9	-2.7	-9.0	-8.7	1.1	0.5	1.7
7900	-2.0	-2.8	-8.9	-8.7	1.1	0.6	2.3
8000	-2.1	-2.8	-8.9	-8.6	1.1	0.6	2.4



ISO 9001 ISO 14001 AS 9100 CERTIFIED

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minic

*Typical Performance Data***NOTE: Use PDF Bookmarks to view DATA at required conditions****Definitions:**

Input Return Loss = S11 (dB)
 Gain = S21 (dB)
 Isolation = S12 (dB)
 Output Return Loss = S22 (dB)

TEST CONDITIONS: V_{DD} = +5.25 V, V_{EN} = 0 V, I_{DD} = 3 mA, I_{EN} = 0 mA @ Temperature = +25°C

See TSY-83LN+ for additional test data.

FREQ (MHz)	Insertion Loss (dB)	Isolation (dB)	Input Return Loss (dB)	Output Return Loss (dB)	Stability		Noise Figure (dB)
					K	Measure	
5500	-1.3	-1.9	-18.5	-20.7	1.1	0.6	1.7
5600	-1.2	-1.9	-19.3	-23.6	1.1	0.6	1.6
5700	-1.2	-1.8	-19.6	-27.1	1.1	0.6	1.5
5800	-1.2	-1.8	-19.4	-28.0	1.1	0.6	1.6
5900	-1.1	-1.8	-19.1	-25.0	1.1	0.6	1.3
6000	-1.1	-1.8	-18.4	-22.2	1.1	0.6	1.3
6100	-1.2	-1.8	-17.5	-19.9	1.1	0.6	1.3
6200	-1.2	-1.9	-16.5	-18.1	1.1	0.6	1.2
6300	-1.2	-1.9	-15.6	-16.5	1.1	0.6	1.6
6400	-1.3	-2.0	-14.6	-15.2	1.1	0.6	1.4
6500	-1.3	-2.0	-13.8	-14.2	1.1	0.6	1.7
6600	-1.4	-2.1	-12.9	-13.2	1.1	0.6	1.8
6700	-1.5	-2.2	-12.1	-12.4	1.1	0.6	1.6
6800	-1.6	-2.3	-11.3	-11.5	1.1	0.6	1.4
6900	-1.7	-2.4	-10.7	-10.8	1.1	0.6	1.2
7000	-1.7	-2.5	-10.0	-10.0	1.1	0.6	1.9
7100	-1.8	-2.6	-9.4	-9.3	1.1	0.6	1.8
7200	-1.9	-2.7	-8.9	-8.8	1.1	0.6	1.8
7300	-2.0	-2.8	-8.4	-8.2	1.1	0.6	1.3
7400	-2.2	-2.9	-7.9	-7.8	1.1	0.6	2.2
7500	-2.3	-3.1	-7.5	-7.3	1.1	0.6	1.7
7600	-2.5	-3.3	-7.0	-6.9	1.1	0.5	2.1
7700	-2.7	-3.4	-6.6	-6.5	1.1	0.5	1.9
7800	-2.9	-3.6	-6.3	-6.1	1.1	0.5	2.0
7900	-3.1	-3.8	-5.9	-5.8	1.1	0.5	2.3
8000	-3.3	-4.1	-5.5	-5.5	1.1	0.5	2.1
8100	-3.6	-4.3	-5.2	-5.2	1.1	0.5	2.4
8200	-3.9	-4.6	-4.9	-4.9	1.2	0.6	2.1
8300	-4.2	-4.9	-4.6	-4.6	1.2	0.5	2.0
8400	-4.4	-5.1	-4.2	-4.3	1.2	0.5	2.0
8500	-4.7	-5.4	-4.0	-4.0	1.2	0.5	2.4



ISO 9001 ISO 14001 AS 9100 CERTIFIED

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping
 The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minic.com

Typical Performance Data

NOTE: Use PDF Bookmarks to view DATA at required conditions

Definitions:

Input Return Loss = S11 (dB)

Gain = S21 (dB)

Isolation = S12 (dB)

Output Return Loss = S22 (dB)

TEST CONDITIONS: $V_{DD} = +5.75$ V, $V_{EN} = +5.75$ V, $I_{DD} = 98$ mA, $I_{EN} = 2.50$ mA @ Temperature = $+25^\circ\text{C}$

See TSY-83LN+ for additional test data.

FREQ (MHz)	Gain (dB)	Isolation (dB)	Input Return Loss (dB)	Output Return Loss (dB)	Stability		1dB Comp. Output (dBm)	3dB Comp. Output (dBm)	Noise Figure (dB)	IP-3 Output Pout = +0 (dBm)
					K	Measure				
200	15.8	-33.4	-1.9	-3.9	1.4	0.8	18.9	22.8	19.5	33.4
300	20.6	-28.6	-5.9	-8.1	1.2	0.8	21.3	22.8	2.7	34.3
400	22.1	-27.0	-12.3	-13.8	1.1	0.7	21.6	23.1	1.9	35.2
500	22.4	-26.7	-18.3	-16.0	1.1	0.6	21.9	23.3	1.7	35.4
600	22.5	-26.7	-18.7	-15.4	1.1	0.6	22.2	23.4	1.5	35.8
700	22.5	-26.8	-16.9	-14.5	1.1	0.6	22.4	23.5	1.4	37.1
800	22.5	-26.8	-15.9	-13.9	1.1	0.6	22.5	23.7	1.3	35.7
900	22.4	-26.8	-15.3	-13.7	1.1	0.6	22.6	23.8	1.2	34.6
1000	22.4	-26.9	-14.9	-13.7	1.1	0.6	22.6	23.8	1.4	35.7
1100	22.4	-27.0	-14.8	-13.9	1.1	0.6	22.6	23.8	1.4	36.2
1200	22.5	-26.9	-14.9	-14.2	1.1	0.6	22.6	23.9	1.4	35.7
1300	22.5	-26.9	-15.3	-14.5	1.1	0.6	22.6	23.9	1.4	35.2
1400	22.5	-27.0	-15.5	-15.0	1.1	0.6	22.6	23.8	1.3	34.2
1500	22.5	-27.1	-16.0	-15.7	1.1	0.6	22.5	24.0	1.4	34.7
1600	22.5	-27.1	-16.4	-16.5	1.1	0.7	22.6	24.0	1.4	35.4
1700	22.5	-27.1	-16.7	-17.2	1.1	0.7	22.6	24.2	1.4	33.4
1800	22.5	-27.2	-17.1	-18.2	1.1	0.7	22.5	24.1	1.4	34.1
1900	22.6	-27.1	-17.4	-19.5	1.1	0.7	22.4	24.1	1.4	33.6
2000	22.6	-27.2	-17.5	-21.3	1.2	0.7	22.3	23.9	1.5	32.8
2100	22.6	-27.3	-17.4	-23.3	1.2	0.7	22.4	24.2	1.5	33.7
2200	22.6	-27.4	-17.3	-25.6	1.2	0.7	22.4	24.2	1.5	33.3
2300	22.6	-27.4	-17.0	-27.6	1.2	0.7	22.4	24.3	1.5	34.2
2400	22.6	-27.5	-16.5	-29.0	1.2	0.7	22.2	24.4	1.5	32.2
2500	22.7	-27.5	-16.2	-28.2	1.2	0.7	22.1	24.6	1.6	32.7
2600	22.7	-27.7	-15.7	-26.8	1.2	0.7	21.9	24.6	1.6	33.2
2700	22.6	-27.8	-15.3	-26.0	1.2	0.7	21.8	24.4	1.6	32.5
2800	22.6	-27.9	-14.6	-23.6	1.2	0.8	21.7	24.2	1.6	32.9
2900	22.6	-27.8	-14.4	-22.4	1.2	0.8	21.6	24.0	1.7	31.1
3000	22.5	-27.8	-13.8	-21.0	1.2	0.8	21.3	24.1	1.7	31.3
3100	22.5	-27.8	-13.5	-20.0	1.2	0.7	21.1	24.2	1.7	31.3
3200	22.5	-27.8	-13.1	-19.2	1.2	0.7	20.9	23.8	1.7	31.2
3300	22.6	-27.9	-12.6	-18.4	1.2	0.7	21.0	23.7	1.7	30.1
3400	22.6	-28.0	-12.4	-17.8	1.2	0.7	21.0	23.7	1.6	30.3
3500	22.6	-27.9	-12.1	-17.3	1.2	0.7	21.0	24.2	1.8	30.5
3600	22.6	-28.0	-12.0	-17.1	1.2	0.7	21.0	24.3	1.6	30.5
3700	22.6	-28.1	-11.9	-17.1	1.2	0.8	21.0	23.9	1.6	30.0
3800	22.6	-28.0	-11.9	-17.2	1.2	0.7	21.1	24.0	1.6	29.9
3900	22.7	-28.1	-11.8	-17.5	1.2	0.8	21.4	24.2	1.6	30.7
4000	22.7	-28.2	-11.6	-17.6	1.2	0.8	21.7	24.4	1.6	29.5
4100	22.8	-28.3	-11.6	-17.8	1.2	0.8	21.8	24.6	1.6	30.0
4200	22.8	-28.3	-11.7	-18.1	1.2	0.8	21.8	24.4	1.6	29.4
4300	22.8	-28.4	-12.0	-18.5	1.2	0.8	21.8	24.4	1.6	29.9
4400	22.8	-28.6	-12.3	-18.7	1.2	0.8	21.8	24.4	1.6	29.7
4500	22.9	-28.5	-12.8	-19.8	1.2	0.8	22.0	24.6	1.6	30.3
4600	22.8	-28.3	-13.4	-21.2	1.2	0.8	22.0	24.7	1.6	30.0
4700	22.9	-28.2	-13.5	-22.6	1.2	0.8	22.0	24.6	1.6	29.2
4800	23.0	-28.3	-13.5	-23.8	1.2	0.8	22.0	24.5	1.6	29.5
4900	23.1	-28.2	-13.6	-25.5	1.2	0.8	22.0	24.6	1.6	30.4
5000	23.2	-28.4	-13.8	-27.5	1.2	0.8	22.1	24.6	1.6	29.9
5100	23.3	-28.5	-14.3	-28.8	1.2	0.8	21.9	24.5	1.6	29.3
5200	23.4	-28.6	-14.7	-30.6	1.2	0.8	21.6	24.3	1.6	28.8
5300	23.5	-28.7	-15.3	-32.0	1.2	0.8	21.4	24.1	1.6	28.2
5400	23.5	-28.8	-16.7	-30.4	1.2	0.8	21.6	24.2	1.6	28.3
5500	23.5	-29.0	-18.1	-30.3	1.2	0.8	21.9	24.3	1.6	28.1
5600	23.4	-29.1	-20.8	-27.6	1.3	0.8	22.1	24.5	1.7	29.2
5700	23.4	-28.9	-22.7	-26.0	1.3	0.8	21.9	24.3	1.7	28.9
5800	23.4	-28.8	-23.3	-24.8	1.2	0.7	21.5	24.2	1.7	28.5
5900	23.5	-28.7	-24.5	-24.5	1.2	0.7	21.1	23.9	1.7	27.9
6000	23.7	-28.7	-25.6	-25.2	1.2	0.7	20.9	23.6	1.7	27.7
6100	23.9	-28.7	-25.0	-26.5	1.2	0.7	20.9	23.5	1.7	27.2
6200	24.0	-28.8	-23.5	-30.0	1.2	0.7	20.9	23.1	1.8	27.0
6300	24.1	-28.9	-21.3	-33.3	1.2	0.7	21.0	22.9	1.8	27.6
6400	24.2	-29.1	-19.1	-32.7	1.2	0.7	20.8	22.6	1.9	27.0
6500	24.1	-29.4	-17.0	-29.1	1.2	0.8	20.3	22.2	1.9	26.9
6600	24.2	-29.6	-14.9	-24.3	1.2	0.8	19.7	22.1	1.9	26.2
6700	24.1	-30.0	-12.7	-20.4	1.3	0.8	19.4	21.7	1.9	25.7
6800	23.7	-30.6	-11.2	-18.0	1.3	0.9	19.5	21.6	2.0	25.2
6900	23.3	-31.1	-10.6	-17.7	1.4	0.9	20.0	21.3	2.0	26.2
7000	23.1	-31.3	-10.0	-18.1	1.4	0.9	20.2	21.1	2.0	26.5
7100	23.3	-31.0	-9.7	-17.3	1.4	0.9	20.1	21.1	2.1	25.5
7200	23.3	-31.3	-8.8	-14.8	1.4	0.9	19.6	21.2	2.1	24.7
7300	23.2	-31.5	-8.1	-13.4	1.4	0.9	19.5	21.3	2.2	24.5
7400	23.1	-32.0	-7.1	-11.6	1.4	0.9	19.9	21.5	2.2	25.6
7500	22.9	-32.8	-6.1	-10.2	1.5	1.0	20.4	21.1	2.3	24.8
7600	22.5	-33.5	-5.4	-9.1	1.5	1.0	20.6	21.1	2.3	25.1
7700	22.0	-34.8	-4.8	-8.1	1.7	1.0	20.3	21.0	2.4	24.2
7800	21.5	-35.7	-4.2	-7.3	1.7	1.0	19.9	20.6	2.4	23.9
7900	20.9	-37.4	-3.8	-6.7	2.0	1.0	19.5	20.4	2.5	23.6
8000	20.1	-39.3	-3.5	-6.1	2.4	1.0	19.3	19.9	2.5	24.3

MMIC Amplifier

TSY-83LN-D+

Typical Performance Data

NOTE: Use PDF Bookmarks to view DATA at required conditions

Definitions:

Input Return Loss = S11 (dB)

Gain = S21 (dB)

Isolation = S12 (dB)

Output Return Loss = S22 (dB)

TEST CONDITIONS: $V_{DD} = +5.75$ V, $V_{EN} = +5.75$ V, $I_{DD} = 102$ mA, $I_{EN} = 2.47$ mA @ Temperature = $+25^\circ\text{C}$

See TSY-83LN+ for additional test data.

FREQ (MHz)	Gain (dB)	Isolation (dB)	Input Return Loss (dB)	Output Return Loss (dB)	Stability		1dB Comp. Output (dBm)	3dB Comp. Output (dBm)	Noise Figure (dB)	IP-3 Output Pout = +0 (dBm)
5500	23.0	-29.1	-11.1	-11.0	1.2	0.7	21.6	23.9	1.5	28.6
5600	23.0	-29.1	-11.6	-11.1	1.2	0.7	21.9	24.2	1.4	28.4
5700	23.1	-28.9	-11.7	-11.6	1.2	0.7	21.9	24.4	1.4	28.6
5800	23.2	-28.7	-11.6	-12.1	1.2	0.7	21.5	24.1	1.4	28.0
5900	23.4	-28.7	-11.1	-12.5	1.2	0.7	21.7	24.3	1.4	28.4
6000	23.6	-28.8	-11.0	-12.7	1.2	0.7	21.5	24.3	1.4	27.8
6100	23.7	-28.8	-10.9	-12.7	1.2	0.7	21.1	24.0	1.5	28.0
6200	23.8	-28.9	-11.0	-12.7	1.2	0.7	21.0	23.9	1.5	27.6
6300	23.9	-29.0	-11.0	-12.7	1.2	0.7	20.5	23.3	1.5	26.9
6400	24.0	-29.2	-11.0	-12.5	1.2	0.7	20.5	23.1	1.6	26.4
6500	24.0	-29.4	-11.0	-12.3	1.2	0.7	20.7	23.0	1.5	26.3
6600	24.0	-29.5	-11.3	-12.3	1.2	0.7	21.0	23.2	1.6	26.5
6700	24.0	-29.8	-11.5	-12.1	1.2	0.7	21.2	23.2	1.6	26.8
6800	24.0	-29.7	-11.9	-12.4	1.2	0.7	21.3	23.2	1.6	26.8
6900	23.9	-29.9	-12.4	-12.6	1.3	0.7	21.1	22.8	1.6	26.8
7000	24.0	-29.7	-12.7	-12.9	1.2	0.7	21.2	22.9	1.7	26.5
7100	24.1	-29.6	-12.6	-12.7	1.2	0.7	21.4	22.9	1.7	26.8
7200	24.2	-29.9	-12.4	-12.4	1.2	0.7	21.4	23.0	1.7	27.1
7300	24.3	-30.0	-12.4	-12.1	1.2	0.7	21.1	22.6	1.7	26.5
7400	24.4	-30.2	-12.0	-11.7	1.2	0.7	21.0	22.4	1.8	26.1
7500	24.3	-30.5	-11.8	-11.5	1.3	0.7	21.2	22.5	1.8	26.3
7600	24.3	-30.7	-11.5	-11.3	1.3	0.7	20.9	22.3	1.9	26.7
7700	24.3	-31.1	-11.0	-11.1	1.3	0.8	21.4	22.6	2.0	26.3
7800	24.2	-31.5	-10.5	-11.1	1.3	0.8	20.9	22.2	2.0	26.4
7900	24.0	-32.0	-9.8	-11.3	1.4	0.8	20.6	22.1	2.1	26.0
8000	23.9	-32.6	-9.2	-11.6	1.5	0.9	20.5	22.0	2.2	26.0
8100	23.6	-33.2	-8.4	-12.2	1.6	0.9	21.0	22.4	2.3	25.9
8200	23.1	-33.8	-7.7	-13.5	1.7	1.0	20.8	22.2	2.5	26.0
8300	22.8	-34.1	-7.3	-14.9	1.8	1.0	20.2	21.7	2.5	26.0
8400	22.5	-34.2	-6.9	-16.0	1.8	1.1	20.3	21.8	2.7	26.3
8500	22.3	-34.6	-6.4	-16.8	1.9	1.1	19.8	21.4	2.9	25.2



ISO 9001 ISO 14001 AS 9100 CERTIFIED

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping
 The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minic.com

REV. OR
TSY-83LN-D+
8/27/2025
Page 14 of 24

Typical Performance Data

NOTE: Use PDF Bookmarks to view DATA at required conditions**Definitions:**

Input Return Loss = S11 (dB)

Gain = S21 (dB)

Isolation = S12 (dB)

Output Return Loss = S22 (dB)

TEST CONDITIONS: V_{DD} = +5.75 V, V_{EN} = 0 V, I_{DD} = 4 mA, I_{EN} = 0 mA @ Temperature = +25°C

See TSY-83LN+ for additional test data.

FREQ (MHz)	Gain (dB)	Isolation (dB)	Input Return Loss (dB)	Output Return Loss (dB)	Stability		Noise Figure (dB)
					K	Measure	
200	-3.2	-3.5	-4.2	-7.2	1.1	0.7	2.9
300	-1.9	-2.1	-6.8	-10.2	1.0	0.5	2.7
400	-1.4	-1.5	-9.3	-12.7	1.0	0.4	1.3
500	-1.1	-1.2	-11.7	-14.8	1.0	0.4	1.7
600	-0.9	-1.1	-14.3	-16.8	1.0	0.4	1.1
700	-0.9	-1.0	-17.1	-18.5	1.0	0.4	0.8
800	-0.8	-1.0	-20.4	-19.5	1.0	0.4	0.9
900	-0.8	-1.0	-24.6	-20.0	1.0	0.3	1.0
1000	-0.8	-1.0	-31.2	-20.3	1.0	0.3	0.9
1100	-0.8	-1.0	-44.7	-20.1	1.0	0.3	0.6
1200	-0.8	-1.0	-32.0	-19.8	1.0	0.3	0.9
1300	-0.8	-1.0	-27.0	-19.3	1.0	0.3	0.9
1400	-0.8	-1.0	-23.9	-18.7	1.0	0.4	1.1
1500	-0.8	-1.0	-22.0	-18.2	1.0	0.4	1.0
1600	-0.8	-1.1	-20.8	-17.7	1.0	0.4	0.9
1700	-0.9	-1.1	-19.9	-17.3	1.0	0.4	1.1
1800	-0.9	-1.1	-19.1	-17.2	1.0	0.4	0.9
1900	-0.9	-1.2	-18.3	-17.1	1.0	0.4	1.3
2000	-0.9	-1.2	-17.7	-17.2	1.0	0.4	0.9
2100	-0.9	-1.2	-17.1	-17.3	1.0	0.4	1.2
2200	-1.0	-1.3	-16.6	-17.6	1.0	0.4	1.0
2300	-1.0	-1.3	-16.3	-18.0	1.0	0.4	1.5
2400	-1.0	-1.3	-16.0	-18.5	1.0	0.5	1.9
2500	-1.0	-1.4	-15.7	-18.9	1.0	0.5	1.5
2600	-1.0	-1.4	-15.7	-19.3	1.0	0.5	1.6
2700	-1.1	-1.5	-15.8	-19.9	1.0	0.5	1.1
2800	-1.1	-1.6	-15.8	-20.5	1.0	0.5	1.4
2900	-1.1	-1.6	-15.8	-21.4	1.1	0.5	1.4
3000	-1.1	-1.6	-15.8	-22.5	1.1	0.5	1.6
3100	-1.1	-1.6	-15.8	-23.8	1.1	0.5	1.5
3200	-1.1	-1.6	-15.8	-25.3	1.0	0.5	1.7
3300	-1.1	-1.6	-15.8	-27.6	1.0	0.5	1.5
3400	-1.1	-1.6	-15.8	-31.1	1.0	0.5	1.3
3500	-1.1	-1.6	-15.7	-34.7	1.0	0.5	1.5
3600	-1.2	-1.6	-15.6	-32.3	1.1	0.5	1.0
3700	-1.2	-1.6	-15.4	-28.1	1.1	0.5	1.6
3800	-1.2	-1.6	-15.1	-24.5	1.1	0.5	1.8
3900	-1.2	-1.6	-14.8	-22.0	1.1	0.5	1.5
4000	-1.2	-1.6	-14.3	-20.4	1.1	0.5	1.5
4100	-1.3	-1.7	-13.9	-18.9	1.1	0.5	1.9
4200	-1.3	-1.7	-13.5	-17.7	1.1	0.5	1.2
4300	-1.3	-1.8	-13.1	-16.5	1.1	0.5	1.7
4400	-1.4	-1.8	-12.6	-15.4	1.1	0.5	2.0
4500	-1.4	-1.9	-12.0	-14.4	1.1	0.5	2.0
4600	-1.5	-1.9	-11.5	-13.5	1.1	0.5	2.1
4700	-1.5	-1.9	-11.1	-12.9	1.1	0.5	2.0
4800	-1.5	-2.0	-10.8	-12.4	1.1	0.5	2.2
4900	-1.5	-2.0	-10.5	-11.8	1.1	0.5	1.8
5000	-1.5	-2.1	-10.2	-11.4	1.1	0.5	1.3
5100	-1.6	-2.1	-9.9	-11.0	1.1	0.5	1.3
5200	-1.6	-2.2	-9.7	-10.7	1.1	0.5	1.3
5300	-1.6	-2.2	-9.5	-10.4	1.1	0.5	1.4
5400	-1.7	-2.3	-9.3	-10.2	1.1	0.5	2.3
5500	-1.7	-2.3	-9.2	-9.9	1.1	0.5	2.3
5600	-1.8	-2.4	-8.9	-9.7	1.1	0.5	1.3
5700	-1.8	-2.4	-8.7	-9.4	1.1	0.5	1.9
5800	-1.8	-2.4	-8.5	-9.2	1.1	0.5	2.0
5900	-1.8	-2.4	-8.4	-9.1	1.1	0.5	2.3
6000	-1.8	-2.4	-8.4	-8.9	1.1	0.5	1.5
6100	-1.7	-2.4	-8.4	-8.9	1.1	0.5	1.8
6200	-1.7	-2.4	-8.4	-8.9	1.1	0.5	2.0
6300	-1.7	-2.4	-8.5	-8.9	1.1	0.5	2.0
6400	-1.8	-2.5	-8.5	-8.9	1.1	0.5	2.2
6500	-1.8	-2.5	-8.5	-8.9	1.1	0.5	2.4
6600	-1.8	-2.5	-8.6	-8.9	1.1	0.5	2.0
6700	-1.8	-2.5	-8.7	-9.0	1.1	0.5	1.4
6800	-1.8	-2.6	-8.8	-9.1	1.1	0.5	2.1
6900	-1.8	-2.6	-8.7	-9.0	1.1	0.5	2.1
7000	-1.9	-2.6	-8.7	-8.9	1.1	0.5	2.5
7100	-1.8	-2.6	-8.8	-8.8	1.1	0.5	1.7
7200	-1.8	-2.6	-8.8	-8.8	1.1	0.5	2.7
7300	-1.8	-2.6	-8.8	-8.8	1.1	0.5	2.4
7400	-1.8	-2.6	-8.9	-8.8	1.1	0.5	2.1
7500	-1.8	-2.6	-8.9	-8.8	1.1	0.5	2.2
7600	-1.9	-2.6	-9.0	-8.8	1.1	0.5	2.4
7700	-1.9	-2.7	-9.0	-8.7	1.1	0.5	2.2
7800	-1.9	-2.7	-8.9	-8.7	1.1	0.5	2.0
7900	-2.0	-2.8	-8.9	-8.7	1.1	0.6	2.9
8000	-2.1	-2.8	-8.9	-8.6	1.1	0.6	2.4



ISO 9001 ISO 14001 AS 9100 CERTIFIED

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minic

Typical Performance Data

NOTE: Use PDF Bookmarks to view DATA at required conditions

Definitions:

Input Return Loss = S11 (dB)
 Gain = S21 (dB)
 Isolation = S12 (dB)
 Output Return Loss = S22 (dB)

TEST CONDITIONS: V_{DD} = +5.75V, V_{EN} = 0 V, I_{DD} = 4 mA, I_{EN} = 0 mA @ Temperature = +25°C

See TSY-83LN+ for additional test data.

FREQ (MHz)	Insertion Loss (dB)	Isolation (dB)	Input Return Loss (dB)	Output Return Loss (dB)	Stability		Noise Figure (dB)
					K	Measure	
5500	-1.2	-1.8	-18.6	-20.6	1.1	0.6	1.3
5600	-1.2	-1.8	-19.4	-23.7	1.1	0.6	1.4
5700	-1.2	-1.8	-19.7	-27.4	1.1	0.6	1.9
5800	-1.1	-1.8	-19.5	-28.4	1.1	0.6	1.3
5900	-1.1	-1.8	-19.1	-25.3	1.1	0.6	1.1
6000	-1.1	-1.8	-18.5	-22.4	1.1	0.6	1.8
6100	-1.1	-1.8	-17.5	-20.0	1.1	0.6	1.4
6200	-1.2	-1.9	-16.5	-18.2	1.1	0.6	1.9
6300	-1.2	-1.9	-15.5	-16.5	1.1	0.6	1.4
6400	-1.3	-2.0	-14.6	-15.2	1.1	0.6	1.3
6500	-1.3	-2.0	-13.8	-14.2	1.1	0.6	1.3
6600	-1.4	-2.1	-12.9	-13.2	1.1	0.6	1.9
6700	-1.5	-2.2	-12.1	-12.4	1.1	0.6	1.4
6800	-1.6	-2.3	-11.3	-11.5	1.1	0.6	1.6
6900	-1.7	-2.4	-10.6	-10.8	1.1	0.6	1.5
7000	-1.7	-2.5	-10.0	-10.0	1.1	0.6	1.7
7100	-1.8	-2.6	-9.4	-9.3	1.1	0.6	1.7
7200	-1.9	-2.7	-8.9	-8.8	1.1	0.6	1.8
7300	-2.0	-2.8	-8.4	-8.2	1.1	0.6	1.6
7400	-2.1	-2.9	-7.9	-7.8	1.1	0.6	1.5
7500	-2.3	-3.1	-7.5	-7.3	1.1	0.5	2.2
7600	-2.5	-3.3	-7.0	-6.9	1.1	0.5	1.6
7700	-2.7	-3.4	-6.6	-6.5	1.1	0.5	2.4
7800	-2.9	-3.6	-6.2	-6.1	1.1	0.5	1.9
7900	-3.1	-3.8	-5.9	-5.8	1.1	0.5	2.3
8000	-3.3	-4.0	-5.5	-5.4	1.1	0.5	1.8
8100	-3.6	-4.3	-5.2	-5.2	1.1	0.5	1.9
8200	-3.9	-4.6	-4.9	-4.9	1.1	0.6	1.7
8300	-4.2	-4.9	-4.6	-4.6	1.2	0.5	2.1
8400	-4.4	-5.1	-4.2	-4.2	1.2	0.5	2.3
8500	-4.7	-5.4	-3.9	-3.9	1.2	0.5	2.5



ISO 9001 ISO 14001 AS 9100 CERTIFIED

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping
 The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minic.com

MMIC Amplifier

TSY-83LN-D+

Typical Performance Data

NOTE: Use PDF Bookmarks to view DATA at required conditions

Definitions:

Input Return Loss = S11 (dB)

Gain = S21 (dB)

Isolation = S12 (dB)

Output Return Loss = S22 (dB)

TEST CONDITIONS: $V_{DD} = +6.0$ V, $V_{EN} = +6.0$ V, $I_{DD} = 105$ mA, $I_{EN} = 2.60$ mA @ Temperature = $+25^\circ\text{C}$

See TSY-83LN+ for additional test data.

FREQ	Gain	Isolation	Input Return Loss	Output Return Loss	Stability		1dB Comp. Output	3dB Comp. Output	Noise Figure	IP-3 Output Pout = +0
(MHz)	(dB)	(dB)	(dB)	(dB)	K	Measure	(dBm)	(dBm)	(dB)	(dBm)
200	15.9	-33.7	-1.9	-3.9	1.4	0.8	19.3	23.2	19.4	35.1
300	20.7	-28.6	-5.9	-8.1	1.2	0.8	21.8	23.2	2.7	35.3
400	22.2	-27.2	-12.4	-13.7	1.1	0.7	22.1	23.5	2.0	37.3
500	22.5	-26.9	-18.2	-15.7	1.1	0.6	22.4	23.7	1.7	35.5
600	22.5	-26.8	-18.3	-15.0	1.1	0.6	22.6	23.8	1.5	35.8
700	22.5	-26.8	-16.5	-14.1	1.1	0.6	22.8	23.9	1.4	39.0
800	22.5	-26.9	-15.5	-13.6	1.1	0.6	22.9	24.0	1.4	36.1
900	22.5	-26.9	-14.9	-13.4	1.1	0.6	23.0	24.2	1.3	36.7
1000	22.5	-26.9	-14.6	-13.4	1.1	0.6	23.1	24.2	1.4	35.7
1100	22.5	-26.9	-14.5	-13.6	1.1	0.6	23.1	24.1	1.4	36.2
1200	22.5	-27.0	-14.6	-13.9	1.1	0.6	23.1	24.2	1.4	35.1
1300	22.6	-27.1	-15.0	-14.1	1.1	0.6	23.0	24.3	1.4	36.7
1400	22.6	-27.1	-15.3	-14.6	1.1	0.6	23.0	24.2	1.4	34.9
1500	22.6	-27.1	-15.9	-15.3	1.1	0.6	23.0	24.4	1.4	35.4
1600	22.6	-27.2	-16.3	-16.0	1.1	0.7	23.0	24.4	1.4	35.1
1700	22.6	-27.3	-16.6	-16.7	1.1	0.7	23.1	24.5	1.4	34.8
1800	22.6	-27.2	-17.1	-17.6	1.1	0.7	23.0	24.5	1.4	32.6
1900	22.6	-27.2	-17.5	-18.9	1.1	0.7	22.9	24.5	1.4	35.0
2000	22.7	-27.4	-17.6	-20.5	1.2	0.7	22.8	24.3	1.5	33.7
2100	22.7	-27.3	-17.6	-22.3	1.1	0.7	22.8	24.6	1.5	35.8
2200	22.7	-27.4	-17.6	-24.5	1.2	0.7	22.9	24.6	1.5	34.2
2300	22.7	-27.5	-17.4	-26.3	1.2	0.7	22.8	24.6	1.5	33.4
2400	22.7	-27.6	-17.0	-27.9	1.2	0.7	22.6	24.8	1.6	33.1
2500	22.8	-27.5	-16.7	-27.8	1.2	0.7	22.5	25.0	1.6	33.4
2600	22.8	-27.7	-16.1	-27.2	1.2	0.7	22.4	25.0	1.6	34.3
2700	22.7	-27.8	-15.8	-26.6	1.2	0.7	22.3	24.8	1.7	31.8
2800	22.7	-27.8	-15.0	-24.2	1.2	0.7	22.1	24.6	1.7	32.7
2900	22.7	-27.9	-14.7	-22.9	1.2	0.7	22.0	24.4	1.7	31.0
3000	22.7	-27.9	-14.2	-21.5	1.2	0.8	21.8	24.5	1.7	31.5
3100	22.6	-27.9	-13.8	-20.5	1.2	0.7	21.6	24.5	1.7	31.4
3200	22.7	-27.8	-13.4	-19.7	1.2	0.7	21.4	24.1	1.7	30.8
3300	22.7	-28.0	-12.9	-18.8	1.2	0.7	21.4	24.0	1.7	31.4
3400	22.7	-28.0	-12.6	-18.1	1.2	0.7	21.5	24.0	1.7	31.3
3500	22.7	-28.0	-12.3	-17.7	1.2	0.7	21.5	24.6	1.8	29.9
3600	22.7	-28.0	-12.3	-17.5	1.2	0.7	21.5	24.6	1.6	31.6
3700	22.8	-28.1	-12.2	-17.5	1.2	0.7	21.4	24.3	1.7	30.6
3800	22.8	-28.3	-12.2	-17.6	1.2	0.8	21.6	24.4	1.7	30.0
3900	22.8	-28.2	-12.0	-17.9	1.2	0.8	21.9	24.5	1.7	31.5
4000	22.9	-28.3	-11.8	-18.0	1.2	0.8	22.1	24.7	1.6	29.8
4100	22.9	-28.3	-11.8	-18.2	1.2	0.8	22.2	24.9	1.6	30.4
4200	22.9	-28.5	-11.9	-18.5	1.2	0.8	22.2	24.8	1.6	29.9
4300	22.9	-28.5	-12.2	-18.9	1.2	0.8	22.3	24.7	1.6	30.8
4400	23.0	-28.6	-12.5	-19.2	1.2	0.8	22.3	24.7	1.6	30.1
4500	23.0	-28.5	-12.9	-20.5	1.2	0.8	22.4	24.9	1.6	30.2
4600	22.9	-28.3	-13.6	-22.1	1.2	0.8	22.5	25.0	1.6	29.6
4700	23.0	-28.3	-13.6	-23.8	1.2	0.8	22.4	24.9	1.6	29.6
4800	23.1	-28.4	-13.6	-25.2	1.2	0.8	22.4	24.8	1.6	29.5
4900	23.2	-28.4	-13.6	-27.5	1.2	0.8	22.4	24.9	1.6	30.0
5000	23.3	-28.3	-13.8	-29.8	1.2	0.8	22.5	24.9	1.6	30.6
5100	23.4	-28.5	-14.3	-31.9	1.2	0.8	22.4	24.8	1.6	29.6
5200	23.5	-28.6	-14.7	-34.6	1.2	0.8	22.0	24.6	1.6	29.2
5300	23.6	-28.7	-15.3	-36.7	1.2	0.8	21.9	24.5	1.6	28.7
5400	23.7	-29.0	-16.5	-34.8	1.2	0.8	22.0	24.5	1.6	29.2
5500	23.7	-29.1	-18.1	-33.7	1.2	0.8	22.3	24.6	1.6	28.5
5600	23.5	-29.1	-21.0	-28.9	1.3	0.8	22.5	24.7	1.7	29.2
5700	23.5	-29.0	-22.7	-26.6	1.3	0.8	22.3	24.6	1.7	29.1
5800	23.5	-28.8	-22.8	-24.9	1.2	0.7	21.9	24.4	1.7	28.4
5900	23.6	-28.7	-23.8	-24.4	1.2	0.7	21.5	24.2	1.7	27.9
6000	23.8	-28.6	-24.9	-24.7	1.2	0.7	21.3	23.7	1.7	28.1
6100	24.0	-28.7	-24.5	-25.6	1.2	0.7	21.3	23.7	1.8	27.5
6200	24.2	-28.7	-23.5	-27.8	1.2	0.7	21.3	23.2	1.8	27.1
6300	24.3	-28.9	-21.6	-29.3	1.2	0.7	21.4	23.1	1.8	27.7
6400	24.3	-29.0	-19.3	-28.8	1.2	0.7	21.2	22.7	1.9	27.3
6500	24.3	-29.4	-17.2	-27.2	1.2	0.8	20.7	22.4	1.9	27.0
6600	24.3	-29.6	-15.0	-23.7	1.2	0.8	20.1	22.3	1.9	26.1
6700	24.3	-30.0	-12.8	-20.1	1.2	0.8	19.8	21.9	2.0	25.9
6800	23.9	-30.7	-11.3	-18.0	1.3	0.9	19.9	21.8	2.0	25.3
6900	23.5	-31.0	-10.7	-17.9	1.4	0.9	20.4	21.6	2.0	26.4
7000	23.2	-31.2	-10.0	-18.3	1.4	0.9	20.6	21.4	2.1	26.6
7100	23.5	-31.2	-9.7	-17.3	1.4	0.9	20.4	21.4	2.1	25.8
7200	23.5	-31.2	-8.8	-14.7	1.4	0.9	20.0	21.6	2.1	24.7
7300	23.4	-31.4	-8.1	-13.3	1.4	0.9	19.9	21.6	2.2	24.4
7400	23.3	-32.1	-7.0	-11.4	1.4	0.9	20.2	21.8	2.2	25.8
7500	23.1	-32.7	-6.1	-10.1	1.4	0.9	20.7	21.3	2.3	24.9
7600	22.7	-33.7	-5.4	-9.0	1.5	1.0	20.9	21.2	2.3	25.1
7700	22.2	-34.8	-4.8	-8.1	1.6	1.0	20.6	21.1	2.4	24.3
7800	21.7	-35.9	-4.2	-7.2	1.7	1.0	20.1	20.8	2.4	23.9
7900	21.0	-37.6	-3.8	-6.6	2.0	1.0	19.7	20.5	2.5	23.7
8000	20.2	-39.6	-3.4	-6.0	2.4	1.0	19.5	20.0	2.5	24.5



ISO 9001 ISO 14001 AS 9100 CERTIFIED

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping



The Design Engineers Search Engine

Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minic.com

REV. OR
TSY-83LN-D+
8/27/2025
Page 17 of 24

MMIC Amplifier

TSY-83LN-D+

Typical Performance Data

NOTE: Use PDF Bookmarks to view DATA at required conditions

Definitions:

Input Return Loss = S11 (dB)

Gain = S21 (dB)

Isolation = S12 (dB)

Output Return Loss = S22 (dB)

TEST CONDITIONS: $V_{DD} = +6.0$ V, $V_{EN} = +6.0$ V, $I_{DD} = 110$ mA, $I_{EN} = 2.58$ mA @ Temperature = $+25^\circ\text{C}$

See TSY-83LN+ for additional test data.

FREQ (MHz)	Gain (dB)	Isolation (dB)	Input Return Loss (dB)	Output Return Loss (dB)	Stability		1dB Comp. Output (dBm)	3dB Comp. Output (dBm)	Noise Figure (dB)	IP-3 Output Pout = +0 (dBm)
5500	23.1	-29.1	-11.1	-11.2	1.2	0.7	21.9	24.2	1.5	28.8
5600	23.1	-29.0	-11.6	-11.4	1.2	0.7	22.2	24.5	1.4	28.7
5700	23.2	-28.9	-11.7	-11.8	1.2	0.7	22.3	24.5	1.4	28.8
5800	23.3	-28.7	-11.5	-12.3	1.2	0.7	21.8	24.3	1.4	28.4
5900	23.5	-28.7	-11.1	-12.8	1.2	0.7	22.1	24.5	1.4	28.6
6000	23.7	-28.7	-10.9	-12.9	1.2	0.7	21.9	24.4	1.5	28.4
6100	23.8	-28.8	-10.9	-12.9	1.2	0.7	21.5	24.2	1.5	28.0
6200	23.9	-28.8	-11.0	-12.8	1.2	0.7	21.3	24.0	1.5	27.8
6300	24.0	-29.0	-11.0	-12.8	1.2	0.7	20.8	23.5	1.6	27.0
6400	24.1	-29.1	-11.0	-12.6	1.2	0.7	20.9	23.3	1.6	26.5
6500	24.2	-29.3	-11.0	-12.3	1.2	0.7	21.0	23.1	1.5	26.6
6600	24.1	-29.5	-11.3	-12.2	1.2	0.7	21.3	23.3	1.6	26.8
6700	24.1	-29.7	-11.4	-12.0	1.2	0.7	21.5	23.3	1.6	27.0
6800	24.1	-29.7	-11.9	-12.3	1.2	0.7	21.6	23.4	1.6	26.9
6900	24.0	-29.9	-12.3	-12.4	1.2	0.7	21.4	23.0	1.7	27.0
7000	24.1	-29.7	-12.7	-12.6	1.2	0.7	21.7	23.1	1.7	26.7
7100	24.3	-29.7	-12.6	-12.4	1.2	0.7	21.7	23.1	1.7	26.8
7200	24.3	-29.8	-12.4	-12.1	1.2	0.7	21.8	23.2	1.7	27.0
7300	24.4	-29.9	-12.3	-11.8	1.2	0.7	21.4	22.9	1.7	26.5
7400	24.5	-30.2	-12.0	-11.3	1.2	0.7	21.3	22.7	1.8	26.0
7500	24.5	-30.5	-11.8	-11.1	1.2	0.7	21.6	22.8	1.8	26.2
7600	24.5	-30.7	-11.4	-10.9	1.3	0.7	21.2	22.6	1.9	26.4
7700	24.4	-31.2	-10.9	-10.7	1.3	0.7	21.7	22.9	2.0	26.2
7800	24.3	-31.7	-10.4	-10.7	1.3	0.8	21.2	22.5	2.0	26.4
7900	24.2	-32.1	-9.8	-10.8	1.4	0.8	21.0	22.4	2.1	25.9
8000	24.0	-32.7	-9.1	-11.2	1.5	0.9	20.8	22.3	2.2	26.0
8100	23.7	-33.3	-8.4	-11.7	1.6	0.9	21.4	22.7	2.3	25.7
8200	23.3	-33.9	-7.7	-12.9	1.7	1.0	21.1	22.6	2.5	26.1
8300	22.9	-34.0	-7.3	-14.3	1.7	1.0	20.5	22.0	2.6	25.8
8400	22.6	-34.3	-6.9	-15.3	1.8	1.1	20.6	22.1	2.7	26.0
8500	22.4	-34.6	-6.4	-16.0	1.9	1.1	20.1	21.7	2.9	25.1



ISO 9001 ISO 14001 AS 9100 CERTIFIED

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping



The Design Engineers Search Engine

Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minic.com

Typical Performance Data**NOTE: Use PDF Bookmarks to view DATA at required conditions****Definitions:**

Input Return Loss = S11 (dB)

Gain = S21 (dB)

Isolation = S12 (dB)

Output Return Loss = S22 (dB)

TEST CONDITIONS: V_{DD} = +6.0 V, V_{EN} = 0 V, I_{DD} = 4 mA, I_{EN} = 0 mA @ Temperature = +25°C

See TSY-83LN+ for additional test data.

FREQ (MHz)	Gain (dB)	Isolation (dB)	Input Return Loss (dB)	Output Return Loss (dB)	Stability		Noise Figure (dB)
					K	Measure	
200	-3.2	-3.4	-4.2	-7.2	1.1	0.7	2.6
300	-1.9	-2.1	-6.8	-10.2	1.0	0.5	2.8
400	-1.4	-1.5	-9.3	-12.6	1.0	0.4	1.6
500	-1.1	-1.2	-11.8	-14.8	1.0	0.4	1.7
600	-0.9	-1.1	-14.3	-16.8	1.0	0.4	1.0
700	-0.9	-1.0	-17.1	-18.4	1.0	0.4	0.8
800	-0.8	-1.0	-20.3	-19.5	1.0	0.4	0.8
900	-0.8	-1.0	-24.6	-20.1	1.0	0.3	0.8
1000	-0.8	-1.0	-31.2	-20.4	1.0	0.3	0.8
1100	-0.8	-0.9	-45.8	-20.2	1.0	0.3	0.9
1200	-0.8	-1.0	-32.0	-19.9	1.0	0.3	1.0
1300	-0.8	-1.0	-26.9	-19.3	1.0	0.3	0.9
1400	-0.8	-1.0	-23.9	-18.8	1.0	0.4	1.1
1500	-0.8	-1.0	-22.0	-18.2	1.0	0.4	0.8
1600	-0.8	-1.1	-20.8	-17.7	1.0	0.4	0.9
1700	-0.8	-1.1	-19.9	-17.3	1.0	0.4	0.7
1800	-0.9	-1.1	-19.1	-17.2	1.0	0.4	1.2
1900	-0.9	-1.2	-18.3	-17.1	1.0	0.4	0.8
2000	-0.9	-1.2	-17.7	-17.2	1.0	0.4	1.1
2100	-0.9	-1.2	-17.1	-17.3	1.0	0.4	1.1
2200	-1.0	-1.3	-16.6	-17.6	1.0	0.4	1.2
2300	-1.0	-1.3	-16.3	-18.0	1.0	0.4	1.3
2400	-1.0	-1.3	-16.0	-18.5	1.0	0.5	1.3
2500	-1.0	-1.4	-15.8	-18.9	1.0	0.5	1.6
2600	-1.0	-1.4	-15.8	-19.3	1.0	0.5	1.5
2700	-1.1	-1.5	-15.8	-19.9	1.0	0.5	1.0
2800	-1.1	-1.6	-15.8	-20.5	1.0	0.5	1.4
2900	-1.1	-1.6	-15.8	-21.5	1.0	0.5	1.6
3000	-1.1	-1.6	-15.9	-22.6	1.1	0.5	1.8
3100	-1.1	-1.6	-15.8	-23.8	1.0	0.5	1.5
3200	-1.1	-1.6	-15.8	-25.2	1.0	0.5	1.6
3300	-1.1	-1.6	-15.8	-27.6	1.0	0.5	1.1
3400	-1.1	-1.6	-15.8	-31.0	1.0	0.5	1.3
3500	-1.1	-1.6	-15.7	-34.2	1.0	0.5	1.4
3600	-1.2	-1.6	-15.7	-31.9	1.0	0.5	1.2
3700	-1.2	-1.6	-15.4	-28.0	1.1	0.5	1.6
3800	-1.2	-1.6	-15.1	-24.4	1.1	0.5	1.6
3900	-1.2	-1.6	-14.8	-22.0	1.1	0.5	1.5
4000	-1.2	-1.6	-14.3	-20.4	1.1	0.5	2.0
4100	-1.3	-1.7	-14.0	-18.9	1.1	0.5	1.5
4200	-1.3	-1.7	-13.6	-17.6	1.1	0.5	1.5
4300	-1.3	-1.8	-13.1	-16.5	1.1	0.5	1.6
4400	-1.4	-1.8	-12.6	-15.4	1.1	0.5	1.9
4500	-1.4	-1.9	-12.1	-14.4	1.1	0.5	1.8
4600	-1.4	-1.9	-11.5	-13.5	1.1	0.5	1.6
4700	-1.5	-1.9	-11.1	-12.9	1.1	0.5	1.6
4800	-1.5	-2.0	-10.8	-12.3	1.1	0.5	2.1
4900	-1.5	-2.0	-10.4	-11.8	1.1	0.5	1.6
5000	-1.5	-2.1	-10.2	-11.3	1.1	0.5	1.7
5100	-1.6	-2.1	-9.9	-11.0	1.1	0.5	1.7
5200	-1.6	-2.2	-9.7	-10.6	1.1	0.5	1.5
5300	-1.6	-2.2	-9.5	-10.4	1.1	0.5	1.4
5400	-1.7	-2.3	-9.3	-10.1	1.1	0.5	1.8
5500	-1.7	-2.3	-9.2	-9.9	1.1	0.5	2.2
5600	-1.8	-2.4	-8.9	-9.6	1.1	0.5	1.6
5700	-1.8	-2.4	-8.7	-9.4	1.1	0.5	2.0
5800	-1.8	-2.4	-8.5	-9.2	1.1	0.5	2.3
5900	-1.8	-2.4	-8.4	-9.0	1.1	0.5	1.9
6000	-1.8	-2.4	-8.4	-8.9	1.1	0.5	2.3
6100	-1.7	-2.4	-8.4	-8.8	1.1	0.5	1.9
6200	-1.7	-2.4	-8.4	-8.9	1.1	0.5	1.8
6300	-1.7	-2.4	-8.5	-8.9	1.1	0.5	2.2
6400	-1.7	-2.5	-8.5	-8.9	1.1	0.5	1.8
6500	-1.8	-2.5	-8.5	-8.9	1.1	0.5	1.9
6600	-1.8	-2.5	-8.6	-8.9	1.1	0.5	2.1
6700	-1.8	-2.5	-8.7	-9.0	1.1	0.5	2.6
6800	-1.8	-2.6	-8.7	-9.1	1.1	0.5	2.0
6900	-1.8	-2.6	-8.7	-9.0	1.1	0.5	2.2
7000	-1.9	-2.6	-8.7	-8.9	1.1	0.5	2.0
7100	-1.8	-2.6	-8.8	-8.8	1.1	0.5	1.8
7200	-1.8	-2.6	-8.8	-8.8	1.1	0.5	2.3
7300	-1.8	-2.6	-8.8	-8.8	1.1	0.5	2.4
7400	-1.8	-2.6	-8.9	-8.8	1.1	0.5	1.8
7500	-1.8	-2.6	-8.9	-8.8	1.1	0.5	2.4
7600	-1.8	-2.6	-8.9	-8.7	1.1	0.5	2.6
7700	-1.9	-2.7	-8.9	-8.7	1.1	0.5	1.9
7800	-1.9	-2.7	-8.9	-8.7	1.1	0.5	1.8
7900	-2.0	-2.7	-8.9	-8.6	1.1	0.6	2.5
8000	-2.1	-2.8	-8.8	-8.6	1.1	0.6	3.0



ISO 9001 ISO 14001 AS 9100 CERTIFIED

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minic

*Typical Performance Data***NOTE: Use PDF Bookmarks to view DATA at required conditions****Definitions:**

Input Return Loss = S11 (dB)
 Gain = S21 (dB)
 Isolation = S12 (dB)
 Output Return Loss = S22 (dB)

TEST CONDITIONS: $V_{DD} = +6.0$ V, $V_{EN} = 0$ V, $I_{DD} = 4$ mA, $I_{EN} = 0$ mA @ Temperature = $+25^\circ\text{C}$

See TSY-83LN+ for additional test data.

FREQ (MHz)	Gain (dB)	Isolation (dB)	Input Return Loss (dB)	Output Return Loss (dB)	Stability		Noise Figure (dB)
					K	Measure	
5500	-1.2	-1.8	-18.6	-20.6	1.1	0.6	1.9
5600	-1.2	-1.8	-19.5	-23.7	1.1	0.6	1.4
5700	-1.2	-1.8	-19.7	-27.5	1.1	0.6	1.3
5800	-1.1	-1.8	-19.5	-28.7	1.1	0.6	1.9
5900	-1.1	-1.8	-19.2	-25.4	1.1	0.6	1.5
6000	-1.1	-1.8	-18.5	-22.5	1.1	0.6	1.0
6100	-1.1	-1.8	-17.6	-20.1	1.1	0.6	1.5
6200	-1.2	-1.8	-16.5	-18.2	1.1	0.6	1.2
6300	-1.2	-1.9	-15.5	-16.6	1.1	0.6	1.5
6400	-1.2	-1.9	-14.6	-15.3	1.1	0.6	1.9
6500	-1.3	-2.0	-13.7	-14.2	1.1	0.6	1.8
6600	-1.4	-2.1	-12.9	-13.2	1.1	0.6	1.5
6700	-1.5	-2.2	-12.1	-12.4	1.1	0.6	1.4
6800	-1.6	-2.3	-11.3	-11.5	1.1	0.6	1.8
6900	-1.7	-2.4	-10.6	-10.8	1.1	0.6	1.8
7000	-1.7	-2.5	-10.0	-10.0	1.1	0.6	1.9
7100	-1.8	-2.6	-9.4	-9.3	1.1	0.6	1.7
7200	-1.9	-2.7	-8.9	-8.7	1.1	0.6	1.6
7300	-2.0	-2.8	-8.4	-8.2	1.1	0.6	1.3
7400	-2.1	-2.9	-7.9	-7.7	1.1	0.5	2.1
7500	-2.3	-3.1	-7.5	-7.3	1.1	0.5	1.2
7600	-2.5	-3.2	-7.0	-6.9	1.1	0.5	1.7
7700	-2.7	-3.4	-6.6	-6.5	1.1	0.5	2.3
7800	-2.9	-3.6	-6.2	-6.1	1.1	0.5	2.2
7900	-3.1	-3.8	-5.9	-5.8	1.1	0.5	2.3
8000	-3.3	-4.0	-5.5	-5.4	1.1	0.5	1.5
8100	-3.5	-4.3	-5.2	-5.1	1.1	0.5	2.7
8200	-3.9	-4.6	-4.9	-4.9	1.1	0.5	2.4
8300	-4.1	-4.9	-4.5	-4.5	1.2	0.5	2.1
8400	-4.4	-5.1	-4.2	-4.2	1.2	0.5	2.2
8500	-4.7	-5.4	-3.9	-3.9	1.2	0.5	1.6

MMIC Amplifier

TSY-83LN-D+

Typical Performance Data

NOTE: Use PDF Bookmarks to view DATA at required conditions

Definitions:

Input Return Loss = S11 (dB)

Gain = S21 (dB)

Isolation = S12 (dB)

Output Return Loss = S22 (dB)

TEST CONDITIONS: $V_{DD} = +6.25\text{ V}$, $V_{EN} = +6.25\text{ V}$, $I_{DD} = 110\text{ mA}$, $I_{EN} = 2.70\text{ mA}$ @ Temperature = $+25^\circ\text{C}$

See TSY-83LN+ for additional test data.

FREQ	Gain	Isolation	Input Return Loss	Output Return Loss	Stability		1dB Comp. Output	3dB Comp. Output	Noise Figure	IP-3 Output Pout = +0
(MHz)	(dB)	(dB)	(dB)	(dB)	K	Measure	(dBm)	(dBm)	(dB)	(dBm)
200	16.0	-33.6	-1.9	-3.9	1.4	0.8	22.1	23.7	18.1	33.1
300	20.8	-28.8	-5.9	-8.0	1.2	0.8	22.1	23.7	2.7	34.1
400	22.3	-27.3	-12.4	-13.6	1.1	0.7	22.4	24.0	2.0	34.8
500	22.6	-26.9	-18.0	-15.7	1.1	0.6	22.7	24.0	1.7	33.8
600	22.7	-26.8	-17.7	-14.7	1.1	0.6	23.1	24.1	1.5	35.6
700	22.7	-26.9	-16.1	-13.9	1.1	0.6	23.1	24.3	1.4	35.5
800	22.7	-26.9	-15.0	-13.3	1.1	0.6	23.3	24.4	1.4	39.3
900	22.6	-27.0	-14.5	-13.1	1.1	0.6	23.4	24.4	1.4	36.6
1000	22.7	-27.0	-14.2	-13.1	1.1	0.6	23.4	24.5	1.4	34.4
1100	22.7	-27.1	-14.2	-13.3	1.1	0.6	23.4	24.5	1.4	36.3
1200	22.7	-27.0	-14.2	-13.6	1.1	0.6	23.4	24.6	1.4	34.3
1300	22.7	-27.0	-14.5	-13.9	1.1	0.6	23.3	24.8	1.4	34.1
1400	22.7	-27.1	-14.9	-14.5	1.1	0.6	23.3	24.6	1.3	35.9
1500	22.7	-27.2	-15.4	-15.2	1.1	0.6	23.2	24.7	1.4	34.4
1600	22.7	-27.2	-15.4	-15.8	1.1	0.6	23.4	24.8	1.4	37.5
1700	22.8	-27.1	-16.0	-16.3	1.1	0.6	23.4	24.8	1.5	34.6
1800	22.8	-27.1	-16.6	-17.4	1.1	0.6	23.2	25.0	1.5	34.1
1900	22.9	-27.2	-17.0	-18.5	1.1	0.6	23.3	25.0	1.5	38.5
2000	22.9	-27.2	-17.4	-19.9	1.1	0.6	23.0	24.7	1.5	36.1
2100	22.9	-27.3	-17.5	-21.6	1.1	0.7	23.0	24.9	1.6	36.3
2200	22.9	-27.4	-17.4	-23.6	1.1	0.7	23.1	25.0	1.5	34.1
2300	22.9	-27.4	-17.5	-25.1	1.1	0.7	23.3	25.1	1.5	33.0
2400	22.9	-27.4	-17.5	-26.6	1.1	0.7	23.2	25.3	1.6	34.8
2500	23.0	-27.5	-17.2	-27.6	1.2	0.7	23.1	25.3	1.6	33.0
2600	23.0	-27.6	-16.7	-27.3	1.2	0.7	23.0	25.2	1.6	33.7
2700	22.9	-27.7	-16.2	-26.2	1.2	0.7	22.6	24.9	1.7	33.9
2800	22.9	-27.7	-15.7	-24.7	1.2	0.7	22.7	25.2	1.7	32.4
2900	22.9	-27.7	-15.5	-23.5	1.2	0.7	22.5	24.8	1.7	32.0
3000	22.9	-27.7	-14.9	-22.0	1.2	0.7	22.3	24.6	1.7	33.0
3100	22.9	-27.7	-14.1	-20.6	1.2	0.7	22.2	24.5	1.7	32.9
3200	23.0	-27.8	-13.5	-19.8	1.2	0.7	22.1	24.5	1.7	31.4
3300	23.0	-27.8	-13.0	-19.1	1.2	0.7	21.9	24.6	1.7	32.5
3400	23.0	-27.9	-12.5	-18.5	1.2	0.7	21.9	24.7	1.7	31.2
3500	23.0	-28.0	-12.2	-18.1	1.2	0.7	22.2	25.0	1.7	31.5
3600	23.0	-28.0	-12.0	-17.8	1.2	0.7	22.2	24.9	1.7	30.6
3700	23.0	-28.1	-11.8	-17.7	1.2	0.7	21.7	24.3	1.6	31.2
3800	23.0	-28.2	-11.8	-17.6	1.2	0.7	22.0	24.7	1.6	30.5
3900	23.0	-28.3	-12.0	-17.9	1.2	0.7	22.0	24.7	1.6	29.8
4000	23.0	-28.2	-12.2	-18.6	1.2	0.7	22.3	25.0	1.6	31.0
4100	23.0	-28.1	-12.3	-19.2	1.2	0.7	22.6	25.2	1.6	31.3
4200	23.1	-28.1	-12.2	-19.9	1.2	0.7	22.5	25.1	1.6	31.6
4300	23.1	-28.0	-12.1	-20.4	1.2	0.7	22.7	25.1	1.6	30.5
4400	23.2	-28.2	-12.2	-21.1	1.2	0.7	22.7	25.0	1.6	30.9
4500	23.3	-28.2	-12.2	-21.9	1.2	0.7	22.9	25.0	1.6	31.0
4600	23.3	-28.3	-12.3	-22.7	1.2	0.7	22.9	25.0	1.6	30.8
4700	23.4	-28.4	-12.6	-23.6	1.2	0.7	23.0	25.1	1.6	30.3
4800	23.5	-28.4	-13.0	-24.8	1.2	0.7	22.9	25.2	1.6	30.4
4900	23.5	-28.6	-13.8	-25.8	1.2	0.8	23.0	25.2	1.6	29.6
5000	23.5	-28.7	-14.5	-27.4	1.2	0.8	22.8	25.2	1.6	29.8
5100	23.4	-28.6	-15.5	-29.6	1.2	0.8	22.8	25.1	1.6	30.1
5200	23.5	-28.5	-15.9	-31.4	1.2	0.7	22.5	25.0	1.7	29.2
5300	23.6	-28.5	-16.1	-33.2	1.2	0.7	22.3	24.8	1.7	28.7
5400	23.8	-28.5	-16.5	-32.9	1.2	0.7	22.5	24.8	1.6	28.8
5500	23.8	-28.6	-17.5	-31.3	1.2	0.7	22.8	25.0	1.6	28.8
5600	23.9	-28.7	-18.3	-30.8	1.2	0.7	22.8	25.0	1.6	29.4
5700	23.9	-28.7	-19.8	-29.2	1.2	0.7	22.6	24.8	1.6	29.2
5800	24.0	-28.8	-21.8	-29.7	1.2	0.7	21.9	24.5	1.7	29.9
5900	24.0	-28.8	-22.4	-27.0	1.2	0.7	21.8	24.2	1.7	28.2
6000	24.0	-28.8	-25.1	-26.9	1.2	0.7	22.1	24.3	1.7	27.8
6100	24.2	-28.8	-23.8	-27.9	1.2	0.7	21.6	23.8	1.8	27.7
6200	24.3	-28.9	-24.2	-27.9	1.2	0.7	21.7	23.9	1.9	27.1
6300	24.4	-29.1	-21.6	-30.2	1.2	0.7	21.2	23.4	1.8	27.6
6400	24.4	-29.2	-19.5	-29.0	1.2	0.7	21.1	23.1	1.9	27.2
6500	24.4	-29.4	-17.5	-27.1	1.2	0.7	20.9	22.7	1.9	26.7
6600	24.3	-29.6	-16.1	-26.2	1.2	0.8	20.8	22.6	2.0	27.7
6700	24.2	-29.8	-14.3	-23.4	1.2	0.8	20.9	22.6	2.0	27.3
6800	24.3	-29.8	-12.8	-20.9	1.2	0.8	20.9	22.4	2.1	26.4
6900	24.0	-30.2	-11.2	-19.5	1.3	0.8	20.8	22.0	2.1	26.1
7000	24.0	-30.6	-9.7	-17.8	1.3	0.9	21.0	22.0	2.1	26.5
7100	23.9	-30.6	-9.6	-16.8	1.3	0.9	21.3	22.3	2.2	26.3
7200	23.9	-31.2	-8.0	-13.4	1.3	0.9	20.7	21.9	2.2	26.4
7300	23.7	-31.6	-7.3	-12.2	1.3	0.9	20.3	21.5	2.2	25.6
7400	23.5	-32.3	-6.4	-10.8	1.4	0.9	20.5	21.6	2.3	25.6
7500	23.1	-33.0	-5.5	-9.6	1.4	1.0	21.0	21.8	2.3	25.4
7600	22.6	-34.1	-5.0	-8.8	1.5	1.0	20.7	21.4	2.4	25.7
7700	22.2	-35.1	-4.4	-7.9	1.6	1.0	20.6	21.1	2.5	25.4
7800	21.5	-36.4	-4.0	-7.3	1.8	1.0	20.3	20.8	2.5	25.3
7900	20.9	-37.7	-3.7	-6.8	2.1	1.0	20.0	20.4	2.5	24.7
8000	20.2	-39.1	-3.5	-6.4	2.4	1.0	19.7	20.2	2.6	24.5



MMIC Amplifier

TSY-83LN-D+

Typical Performance Data

NOTE: Use PDF Bookmarks to view DATA at required conditions

Definitions:

Input Return Loss = S11 (dB)

Gain = S21 (dB)

Isolation = S12 (dB)

Output Return Loss = S22 (dB)

TEST CONDITIONS: $V_{DD} = +6.25\text{ V}$, $V_{EN} = +6.25\text{ V}$, $I_{DD} = 118\text{ mA}$, $I_{EN} = 2.68\text{ mA}$ @ Temperature = $+25^\circ\text{C}$

See TSY-83LN+ for additional test data.

FREQ (MHz)	Gain (dB)	Isolation (dB)	Input Return Loss (dB)	Output Return Loss (dB)	Stability		1dB Comp. Output (dBm)	3dB Comp. Output (dBm)	Noise Figure (dB)	IP-3 Output Pout = +0 (dBm)
					K	Measure				
5500	23.0	-29.5	-11.2	-11.2	1.3	0.7	22.1	24.1	1.5	28.9
5600	23.0	-29.4	-11.7	-11.4	1.3	0.7	22.4	24.3	1.5	28.5
5700	23.0	-29.3	-11.8	-11.8	1.3	0.7	22.5	24.4	1.5	28.8
5800	23.2	-29.2	-11.6	-12.2	1.2	0.7	22.0	24.1	1.5	28.3
5900	23.4	-29.1	-11.2	-12.6	1.2	0.7	22.2	24.3	1.5	28.7
6000	23.5	-29.3	-11.0	-12.6	1.2	0.7	22.1	24.3	1.5	28.3
6100	23.6	-29.3	-11.0	-12.6	1.2	0.7	21.5	24.0	1.6	28.1
6200	23.7	-29.3	-11.1	-12.5	1.2	0.7	21.3	23.8	1.6	27.8
6300	23.8	-29.4	-11.1	-12.4	1.2	0.7	20.8	23.3	1.6	26.9
6400	23.9	-29.6	-11.1	-12.2	1.2	0.7	20.8	23.0	1.6	26.5
6500	24.0	-29.9	-11.1	-11.9	1.2	0.7	21.0	22.8	1.6	26.4
6600	23.9	-30.0	-11.4	-11.8	1.2	0.7	21.3	23.0	1.6	26.4
6700	23.9	-30.3	-11.7	-11.6	1.3	0.7	21.4	22.9	1.6	26.7
6800	23.9	-30.3	-12.1	-11.9	1.3	0.7	21.6	22.9	1.7	26.5
6900	23.8	-30.5	-12.6	-12.1	1.3	0.8	21.3	22.6	1.7	26.6
7000	23.9	-30.3	-12.9	-12.3	1.3	0.8	21.6	22.7	1.7	26.3
7100	24.1	-30.2	-12.8	-12.1	1.3	0.7	21.7	22.7	1.7	26.6
7200	24.1	-30.5	-12.6	-11.8	1.3	0.7	21.8	22.8	1.8	26.6
7300	24.2	-30.6	-12.5	-11.6	1.3	0.7	21.5	22.6	1.8	26.1
7400	24.3	-30.8	-12.1	-11.2	1.3	0.7	21.4	22.5	1.9	25.7
7500	24.2	-31.1	-11.8	-11.1	1.3	0.8	21.6	22.5	1.9	25.9
7600	24.2	-31.5	-11.5	-11.0	1.3	0.8	21.3	22.4	2.0	26.1
7700	24.2	-31.9	-11.0	-10.8	1.4	0.8	21.7	22.6	2.0	25.7
7800	24.1	-32.4	-10.5	-10.9	1.5	0.8	21.3	22.3	2.1	25.8
7900	23.9	-32.9	-9.8	-11.1	1.5	0.9	21.1	22.3	2.2	25.4
8000	23.7	-33.6	-9.1	-11.6	1.6	0.9	21.0	22.1	2.3	25.4
8100	23.4	-34.1	-8.4	-12.3	1.7	1.0	21.5	22.5	2.4	25.2
8200	22.9	-34.8	-7.6	-13.7	1.9	1.0	21.3	22.3	2.6	25.4
8300	22.5	-35.0	-7.2	-15.3	2.0	1.1	20.8	21.9	2.7	25.4
8400	22.2	-35.3	-6.8	-16.4	2.1	1.1	20.9	22.0	2.8	25.5
8500	21.9	-35.5	-6.3	-17.4	2.1	1.2	20.5	21.6	3.0	24.6



ISO 9001 ISO 14001 AS 9100 CERTIFIED

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping



The Design Engineers Search Engine

Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minic

Typical Performance Data

NOTE: Use PDF Bookmarks to view DATA at required conditions**Definitions:**

Input Return Loss = S11 (dB)

Gain = S21 (dB)

Isolation = S12 (dB)

Output Return Loss = S22 (dB)

TEST CONDITIONS: V_{DD} = +6.25 V, V_{EN} = 0 V, I_{DD} = 4 mA, I_{EN} = 0 mA @ Temperature = +25°C

See TSY-83LN+ for additional test data.

FREQ (MHz)	Insertion Loss (dB)	Isolation (dB)	Input Return Loss (dB)	Output Return Loss (dB)	Stability		Noise Figure (dB)
					K	Measure	
200	-3.2	-3.4	-4.2	-7.2	1.0	0.7	2.8
300	-1.9	-2.1	-6.8	-10.1	1.0	0.5	2.6
400	-1.4	-1.5	-9.3	-12.6	1.0	0.4	1.6
500	-1.1	-1.2	-11.8	-14.8	1.0	0.4	1.7
600	-0.9	-1.1	-14.3	-16.8	1.0	0.4	0.9
700	-0.9	-1.0	-17.1	-18.5	1.0	0.4	0.8
800	-0.8	-1.0	-20.3	-19.6	1.0	0.4	0.9
900	-0.8	-1.0	-24.6	-20.1	1.0	0.3	1.1
1000	-0.8	-0.9	-31.4	-20.4	1.0	0.3	0.9
1100	-0.7	-0.9	-47.5	-20.2	1.0	0.3	0.8
1200	-0.8	-0.9	-32.2	-19.9	1.0	0.3	1.1
1300	-0.8	-1.0	-27.1	-19.4	1.0	0.3	0.8
1400	-0.8	-1.0	-24.0	-18.8	1.0	0.4	0.9
1500	-0.8	-1.0	-22.0	-18.2	1.0	0.4	1.4
1600	-0.8	-1.0	-20.8	-17.7	1.0	0.4	0.9
1700	-0.8	-1.1	-19.9	-17.4	1.0	0.4	0.9
1800	-0.9	-1.1	-19.1	-17.2	1.0	0.4	0.9
1900	-0.9	-1.1	-18.4	-17.2	1.0	0.4	0.8
2000	-0.9	-1.2	-17.7	-17.2	1.0	0.4	0.8
2100	-0.9	-1.2	-17.1	-17.3	1.0	0.4	0.9
2200	-0.9	-1.2	-16.7	-17.6	1.0	0.4	0.9
2300	-1.0	-1.3	-16.3	-18.0	1.0	0.4	1.0
2400	-1.0	-1.3	-16.0	-18.5	1.0	0.4	1.1
2500	-1.0	-1.4	-15.8	-18.9	1.0	0.5	1.4
2600	-1.0	-1.4	-15.8	-19.3	1.0	0.5	1.2
2700	-1.0	-1.5	-15.9	-19.9	1.0	0.5	1.3
2800	-1.1	-1.5	-15.8	-20.6	1.0	0.5	1.4
2900	-1.1	-1.6	-15.9	-21.5	1.0	0.5	1.4
3000	-1.1	-1.6	-15.9	-22.6	1.0	0.5	1.6
3100	-1.1	-1.6	-15.9	-23.7	1.0	0.5	1.1
3200	-1.1	-1.6	-15.8	-25.3	1.0	0.5	1.1
3300	-1.1	-1.5	-15.9	-27.5	1.0	0.5	1.5
3400	-1.1	-1.5	-15.8	-30.8	1.0	0.5	1.5
3500	-1.1	-1.5	-15.7	-34.1	1.0	0.5	1.6
3600	-1.1	-1.6	-15.7	-31.5	1.0	0.5	1.7
3700	-1.1	-1.6	-15.4	-27.9	1.0	0.5	1.8
3800	-1.2	-1.6	-15.2	-24.5	1.1	0.5	1.5
3900	-1.2	-1.6	-14.8	-21.9	1.1	0.5	1.5
4000	-1.2	-1.6	-14.4	-20.3	1.1	0.5	1.8
4100	-1.2	-1.7	-14.0	-18.9	1.1	0.5	1.7
4200	-1.3	-1.7	-13.5	-17.6	1.1	0.5	1.8
4300	-1.3	-1.8	-13.1	-16.5	1.1	0.5	1.5
4400	-1.4	-1.8	-12.6	-15.4	1.1	0.5	1.8
4500	-1.4	-1.8	-12.1	-14.4	1.1	0.5	2.0
4600	-1.4	-1.9	-11.5	-13.5	1.1	0.5	1.4
4700	-1.4	-1.9	-11.1	-12.9	1.1	0.5	1.0
4800	-1.5	-2.0	-10.8	-12.3	1.1	0.5	2.3
4900	-1.5	-2.0	-10.5	-11.8	1.1	0.5	1.6
5000	-1.5	-2.1	-10.2	-11.3	1.1	0.5	1.7
5100	-1.6	-2.1	-9.9	-11.0	1.1	0.5	1.1
5200	-1.6	-2.2	-9.7	-10.6	1.1	0.5	1.1
5300	-1.6	-2.2	-9.5	-10.4	1.1	0.5	1.1
5400	-1.7	-2.3	-9.3	-10.1	1.1	0.5	2.5
5500	-1.7	-2.3	-9.1	-9.9	1.1	0.5	2.0
5600	-1.8	-2.4	-8.9	-9.6	1.1	0.5	1.7
5700	-1.8	-2.4	-8.7	-9.4	1.1	0.5	2.1
5800	-1.8	-2.4	-8.5	-9.2	1.1	0.5	2.1
5900	-1.8	-2.4	-8.4	-9.0	1.1	0.5	1.8
6000	-1.7	-2.4	-8.4	-8.9	1.1	0.5	2.0
6100	-1.7	-2.4	-8.4	-8.8	1.1	0.5	1.3
6200	-1.7	-2.4	-8.4	-8.9	1.1	0.5	1.8
6300	-1.7	-2.4	-8.5	-8.9	1.1	0.5	2.0
6400	-1.7	-2.4	-8.5	-8.9	1.1	0.5	2.3
6500	-1.8	-2.5	-8.5	-8.9	1.1	0.5	1.8
6600	-1.7	-2.5	-8.6	-8.9	1.1	0.5	1.8
6700	-1.7	-2.5	-8.7	-9.0	1.1	0.5	2.1
6800	-1.8	-2.5	-8.7	-9.1	1.1	0.5	2.4
6900	-1.8	-2.6	-8.7	-8.9	1.1	0.5	2.1
7000	-1.9	-2.6	-8.7	-8.9	1.1	0.5	2.3
7100	-1.8	-2.6	-8.8	-8.8	1.1	0.5	2.0
7200	-1.8	-2.6	-8.8	-8.8	1.1	0.5	2.5
7300	-1.8	-2.6	-8.8	-8.8	1.1	0.5	2.2
7400	-1.8	-2.6	-8.9	-8.8	1.1	0.5	2.2
7500	-1.8	-2.6	-8.9	-8.7	1.1	0.5	2.2
7600	-1.8	-2.6	-8.9	-8.7	1.1	0.5	2.3
7700	-1.9	-2.7	-8.9	-8.7	1.1	0.5	2.0
7800	-1.9	-2.7	-8.9	-8.7	1.1	0.5	2.2
7900	-2.0	-2.7	-8.9	-8.6	1.1	0.5	2.7
8000	-2.1	-2.8	-8.8	-8.5	1.1	0.6	2.2



ISO 9001 ISO 14001 AS 9100 CERTIFIED

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minic

*Typical Performance Data***NOTE: Use PDF Bookmarks to view DATA at required conditions****Definitions:**

Input Return Loss = S11 (dB)
 Gain = S21 (dB)
 Isolation = S12 (dB)
 Output Return Loss = S22 (dB)

TEST CONDITIONS: V_{DD} = +6.25 V, V_{EN} = 0 V, I_{DD} = 4 mA, I_{EN} = 0 mA @ Temperature = +25°C

See TSY-83LN+ for additional test data.

FREQ (MHz)	Insertion Loss (dB)	Isolation (dB)	Input Return Loss (dB)	Output Return Loss (dB)	Stability		Noise Figure (dB)
					K	Measure	
5500	-1.2	-1.8	-18.7	-20.6	1.1	0.6	1.7
5600	-1.2	-1.8	-19.6	-23.7	1.1	0.6	1.5
5700	-1.1	-1.8	-19.8	-27.8	1.1	0.6	1.6
5800	-1.1	-1.8	-19.6	-29.0	1.1	0.6	1.6
5900	-1.1	-1.7	-19.2	-25.6	1.1	0.6	1.1
6000	-1.1	-1.8	-18.5	-22.6	1.1	0.6	1.0
6100	-1.1	-1.8	-17.6	-20.1	1.1	0.6	1.3
6200	-1.1	-1.8	-16.5	-18.3	1.1	0.6	1.8
6300	-1.2	-1.9	-15.5	-16.6	1.1	0.6	1.7
6400	-1.2	-1.9	-14.6	-15.3	1.1	0.6	1.7
6500	-1.3	-2.0	-13.7	-14.2	1.1	0.6	1.6
6600	-1.4	-2.1	-12.9	-13.2	1.1	0.6	1.8
6700	-1.5	-2.2	-12.1	-12.4	1.1	0.6	1.3
6800	-1.5	-2.3	-11.3	-11.5	1.1	0.6	1.7
6900	-1.6	-2.4	-10.6	-10.8	1.1	0.6	1.4
7000	-1.7	-2.5	-9.9	-10.0	1.1	0.6	1.6
7100	-1.8	-2.5	-9.4	-9.3	1.1	0.6	1.8
7200	-1.9	-2.7	-8.8	-8.7	1.1	0.6	1.5
7300	-2.0	-2.8	-8.3	-8.2	1.1	0.5	1.5
7400	-2.1	-2.9	-7.9	-7.7	1.1	0.5	2.2
7500	-2.3	-3.1	-7.4	-7.3	1.1	0.5	1.4
7600	-2.5	-3.2	-7.0	-6.9	1.1	0.5	2.0
7700	-2.7	-3.4	-6.6	-6.5	1.1	0.5	1.8
7800	-2.8	-3.6	-6.2	-6.1	1.1	0.5	2.3
7900	-3.1	-3.8	-5.9	-5.8	1.1	0.5	2.1
8000	-3.3	-4.0	-5.5	-5.4	1.1	0.5	2.1
8100	-3.5	-4.3	-5.2	-5.1	1.1	0.5	3.1
8200	-3.8	-4.6	-4.9	-4.9	1.1	0.5	1.9
8300	-4.1	-4.9	-4.5	-4.5	1.2	0.5	2.6
8400	-4.4	-5.1	-4.2	-4.2	1.2	0.5	2.1
8500	-4.6	-5.3	-3.9	-3.9	1.2	0.5	2.2



ISO 9001 ISO 14001 AS 9100 CERTIFIED







P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping
 **The Design Engineers Search Engine** Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minic.com

MMIC Amplifier

TSY-83LN-D+




Typical Performance Curves

Note: The following data was taken on the Mini-Circuits Die Characterization 400-6000 MHz Test Board (Figure 3). All data taken at nominal conditions $V_{EN} = V_{DD}$ and $R_{LADJ} = \text{Open}$ unless noted otherwise. For additional over temperature graphs, see TSY-83LN+.









Typical Performance Curves

Note: The following data was taken on the Mini-Circuits Die Characterization 400-6000 MHz Test Board (Figure 3). All data taken at nominal conditions $V_{EN} = V_{DD}$ and $R_{LADJ} = \text{Open}$ unless noted otherwise. For additional graphs over temperature, see TSY-83LN+.






Typical Performance Curves

Note: The following data was taken on the Mini-Circuits Die Characterization 5500-8000 MHz Test Board (Figure 4). All data taken at nominal conditions $V_{EN} = V_{DD}$ and $R_{LADJ} = \text{Open}$ unless noted otherwise. For additional graphs over temperature, see TSY-83LN+.



Typical Performance Curves

Note: The following data was taken on the Mini-Circuits Die Characterization 5500-8000 MHz Test Board (Figure 4). All data taken at nominal conditions $V_{EN} = V_{DD}$ and $R_{LADJ} = \text{Open}$ unless noted otherwise. For additional graphs over temperature, see TSY-83LN+.








MMIC Amplifier

TSY-83LN-D+





Typical Performance Curves

Note: The following data was taken of the packaged TSY-83LN+ mounted on Mini-Circuits Characterization Test Board TB-TSY-83LNC+ (see Figure 3). All data taken at nominal conditions $V_{EN} = V_{DD} = +6$ V unless noted otherwise. For additional graphs over temperature, see TSY-83LN+.







Typical Performance Curves

Note: The following data was taken of the packaged TSY-83LN+ mounted on Mini-Circuits Characterization Test Board TB-TSY-832LNC+ (Figure 4). All data taken at nominal conditions $V_{EN} = V_{DD} = +6$ V unless noted otherwise. For additional graphs over temperature, see TSY-83LN+.






Typical Performance Curves

Note: The following data was taken on Mini-Circuits Die Characterization 400-6000 MHz Test Board (Figure 3). All data taken at nominal conditions $V_{EN} = 0$ V and R_{LADJ} = Open unless noted otherwise. For additional graphs over temperature, see TSY-83LN+.







Typical Performance Curves

Note: The following data was taken on Mini-Circuits Die Characterization 400-6000 MHz Test Board (Figure 3). All data taken at nominal conditions $V_{EN} = 0$ V and R_{LADJ} = Open unless noted otherwise. For additional graphs over temperature, see TSY-83LN+.






Typical Performance Curves

Note: The following data was taken on Mini-Circuits Die Characterization 5500-8000 MHz Test Board (Figure 4). All data taken at nominal conditions $V_{EN} = 0$ V and R_{LADJ} = Open unless noted otherwise. For additional graphs over temperature, see TSY-83LN+.



Typical Performance Curves

Note: The following data was taken on Mini-Circuits Die Characterization 5500-8000 MHz Test Board (Figure 4). All data taken at nominal conditions $V_{EN} = 0$ V and R_{LADJ} = Open unless noted otherwise. For additional graphs over temperature, see TSY-83LN+.



**Environmental Specifications****ENV80**

All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-40° to 85° C or -40° to 105° C or -55° to 105° C or -45° to 105° C Ambient Environment	Refer to Individual Model Data Sheet
Storage Environment (Die)	-65° to 150°C	Individual Model Data Sheet
Storage Environment(Packaging)	-40° to 70°C and 40 to 60% humidity (In Factory Shipped Package)	