



USB

Solid State SP2T Switch

USB-1SP2T-34

50Ω 0.1 to 30 GHz

THE BIG DEAL

- Super wide bandwidth, solid-state design
- High isolation, 50 dB @ 30 GHz
- USB control and automation
- Daisy-chain control of up to 25 switches

APPLICATIONS

- RF signal routing / switch matrices
- Satellite communications up to Ka band
- Military radio, radar & electronic warfare
- Microwave radio / cellular infrastructure
- Test & measurement systems



Generic photo used for illustration purposes only

Model No.	USB-1SP2T-34
Case Style	NR3244
Connectors	2.92 mm (female) (Compatible with SMA and 3.5 mm)

DOWNLOAD

SOFTWARE PACKAGE

Refer to our website for compliance methodologies and qualifications



PRODUCT OVERVIEW

Mini-Circuits' USB-1SP2T-34 is a fast switching solid-state SP2T covering an ultra-wide bandwidth, from 0.1 to 30 GHz. The solid-state design features an impressive combination of high isolation, low insertion loss and good linearity across the entire band. The switch is supplied in a low profile package with precision 2.92 mm RF connectors.

The daisy-chain control interface with "dynamic addressing" simplifies control integration, allowing multiple switches to be combined into a Master / Slave chain. Simply connect, then power on and the whole chain of up to 25 compatible switches can be controlled independently through a single USB and software interface.

Full software support is provided, including our user-friendly GUI application for Windows and a full API with programming instructions for Windows and Linux environments (both 32-bit and 64-bit systems).

KEY FEATURES

Feature	Advantages
Fast switching sequences	Program automated switching sequences to run with extremely fast transitions and no external control.
High performance	Solid-state design combining high isolation with low insertion loss from 0.1 to 30 GHz
Dynamic daisy-chain control	Control up to 25 switches through a single USB interface.
USB control	USB HID interface provides easy compatibility with a wide range of software setups and programming environments
Full software support	User friendly Windows GUI (graphical user interface) allows manual control straight out of the box, while the comprehensive API (application programming interface) with examples and instructions allows easy automation in most programming environments

Trademarks:

Windows is a registered trademark of Microsoft Corporation in the United States and other countries ; Linux is a registered trademark of Linus Torvalds ; Pentium is a registered trademark of Intel Corporation. Neither Mini-Circuits nor the Mini-Circuits products are affiliated with or endorsed by the owners of the referenced trademarks. Mini-Circuits and the Mini-Circuits logo are registered trademarks of Scientific Components Corporation.



**USB**

Solid State SP2T Switch

USB-1SP2T-34**ELECTRICAL SPECIFICATIONS AT 0 TO 50°C**

Parameter	Ports	Condition (GHz)	Min.	Typ.	Max.	Unit
Frequency Range	-	-	0.1		30	GHz
Insertion Loss	COM to any active port	0.1 - 10	-	1.40	3.20	dB
		10 - 18	-	2.80	4.30	
		18 - 26	-	3.50	5.30	
		26 - 30	-	4.40	6.00	
Isolation	Between ports J1 & J2	0.1 - 10	50	70	-	dB
		10 - 18	50	60	-	
		18 - 26	45	55	-	
		26 - 30	45	55	-	
	COM to any terminated port (including disconnected state)	0.1 - 10	50	60	-	
		10 - 18	50	65	-	
		18 - 26	45	55	-	
		26 - 30	45	55	-	
Return Loss	COM port (in all active states)	0.1 - 10	-	21	-	dB
		10 - 18	-	15.5	-	
		18 - 26	-	14.5	-	
		26 - 30	-	12	-	
	Any port connected to COM	0.1 - 10	-	19	-	
		10 - 18	-	14.5	-	
		18 - 26	-	14	-	
		26 - 30	-	13	-	
	Any terminated port	0.1 - 10	-	19	-	
		10 - 18	-	16.5	-	
		18 - 26	-	13.5	-	
		26 - 30	-	12	-	
Power Input @1 dB Compression ¹	COM to any active port	0.1 - 30	-	27	-	dBm
IP3 ^{2,3}	COM to any active port	0.5 - 30	-	50	-	dBm
Transition Time ⁴	-	-	-	5	20	ns
Minimum Dwell Time ⁵	High-speed mode	-	-	10	-	µs
Switching Time (USB) ⁶	-	-	-	2	-	ms
Supply Voltage (Vcc)	USB port	-	4.75	5	5.25	V _{DC}
Supply Current (Icc) ⁷		-	-	80	120	mA
Current Pass-through ⁸	-	-	-	-	500	mA
Operating RF Input Power ¹	Between COM & active port	Hot switching	-	-	+18	dBm
	Between COM & active port	Cold switching	-	-	+24	
	Into any termination	-	-	-	+24	

1. Max power at hot switching derates linearly from +18 dBm @ 600 MHz to +17 dBm @100 MHz, at all other conditions it derates linearly from +24 dBm @ 600 MHz to +17 dBm @100 MHz.
2. IP3 may degrade below 500 MHz to about +45 dBm.
3. IP3 tested with 1 MHz span between signals, +8 dBm per tone.
4. Transition time spec represents the time that the RF signal paths are interrupted during switching and thus is specified without communication delays.
5. Minimum dwell time is the shortest time that can be achieved between 2 switch transitions when programming an automated switch sequence.
6. Switching time (USB) is the time from issuing a single software command via USB to the switch state changing. The most significant factor is the host PC, influenced by CPU load and USB protocol. The time shown is an estimate for a medium CPU load and USB 2.0 connection.
7. USB current draw for a single unit with no slave units.
8. Pass through current is the maximum supply current handling of a unit with slave modules attached. If controlling a large number of slave modules additional power supplies should be included to ensure this limit is not exceeded. See page 5 for details.





USB

Solid State SP2T Switch

USB-1SP2T-34

ABSOLUTE MAXIMUM RATINGS

Operating Temperature	0°C to 50°C
Storage Temperature	-20°C to 60°C
DC supply voltage max.	6V
DC voltage @ RF Ports	20 V


Permanent damage may occur if any of these limits are exceeded. Operating in the range between operating power limits and absolute maximum ratings for extended periods of time may result in reduced life and reliability.

CONNECTIONS

Port Name	Connector Type
RF Ports (COM, 1 & 2)	2.92 mm female
USB	USB type-C receptacle
Serial In (Digital Control 2 port)	Digital Snap Fit Connector ⁹
Serial Out (Digital Control 1 port)	Digital Snap Fit Connector ⁹

9. Mating connector is Hirose ST40X-10S-CV(30).

BLOCK DIAGRAM






USB

Solid State SP2T Switch

USB-1SP2T-34

OUTLINE DRAWING (NR3244)



OUTLINE DIMENSIONS (INCH / mm)


A	B	C	D	E	F	G	H	J	K	weight
2.30	2.00	0.575	0.10	2.25	2.50	2.05	0.106	0.50	0.65	grams
58.42	50.80	14.610	2.54	57.15	63.50	52.07	2.690	12.70	16.51	100





CONNECTING MULTIPLE MODULES (DAISY CHAIN)

The USB-1SP2T-34 model is designed to connect up to 25 modules in series (daisy chain) using dynamic addressing, meaning there is no need to specifically set the address of the modules. The addresses will be set automatically as part of establishing the communications with the computer. The module connected to the computer's USB port will be assigned address 0 (master), the first module connected to it will get address 1 (slave) and subsequent modules incrementing up to address 24 (slave).



Connections between modules will be made using the serial in/out ports with the module connected to the PC act as a master and all other as slave modules. All control will be through the master module (address 0) which is the only one communicating with the PC. Serial control out port of each module should be connected to the serial control in port of the next module.

Power will be supplied from the PC via the master module up to a maximum of 500 mA. Generally, additional power supply will be needed to keep total current below 500 mA. All power supplies should be connected to the module via the module's USB port. Connecting an additional power supply will automatically cut off power draw from the serial control in port for that module.

The serial master/slave bus allows connecting modules of different types to the same daisy chain as long as all support Mini-Circuits Dynamic addressing setup. To add a new module to the setup, simply connect the module and refresh the address listing, no need to reset any of the existing modules or assign addresses manually.

Note: Different module types may have different current consumption which will change the number of units which can be connected before an additional power supply is needed.




USB

Solid State SP2T Switch


USB-1SP2T-34

TYPICAL PERFORMANCE CURVES


Insertion Loss over Temperature (J1 Active)




Insertion Loss J1 - J2 Active




Isolation Com to J1 (J2 Active)



Isolation Com to J2 (J1 Active)



Isolation J1 to J2 (J1 Active)






USB

Solid State SP2T Switch


USB-1SP2T-34

TYPICAL PERFORMANCE CURVES (CONTINUED)


Return Loss @ COM over Temperature (J1 Active)




Return Loss @ J1 over Temperature (J1 Active)




Return Loss @ J1 over Temperature (J1 Terminated)



Return Loss @ J2 over Temperature (J2 Active)



Return Loss @ J2 over Temperature (J2 Terminated)





SOFTWARE SPECIFICATIONS

SOFTWARE & DOCUMENTATION DOWNLOAD:

- Mini-Circuits' full software and support package including user guide, Windows GUI, DLL files, programming manual and examples can be downloaded free of charge from: <https://www.minicircuits.com/softwaredownload/solidstate.html>
- Please contact testsolutions@minicircuits.com for support

MINIMUM SYSTEM REQUIREMENTS:

Parameter	Requirements	
Interface	USB HID or Daisy-Chain dynamic addressing	
System Requirements	GUI	Windows 7 or later
	USB API DLL	Windows 7 or later and programming environment with ActiveX or .NET support
	USB Direct Programming	Linux, Windows 7 or later
	Daisy Chain dynamic addressing	An additional Mini-Circuits model supporting dynamic addressing
Hardware	Intel i3 (or equivalent) or later	

APPLICATION PROGRAMMING INTERFACE (API)

USB SUPPORT (WINDOWS):

- ActiveX COM DLL file for creation of 32-bit programs
- .NET library DLL file for creation of 32 / 64-bit programs
- Supported by most common programming environments


USB SUPPORT (LINUX):

- Direct USB programming using a series of USB interrupt codes
- Full programming instructions and examples available for a wide range of programming environments / languages.




GRAPHICAL USER INTERFACE (GUI) FOR WINDOWS - KEY FEATURES

- Connect via USB
- Run GUI in "demo mode" to evaluate software without a hardware connection



- View and set switch states at the click of a button
- Control up to 25 units from a single USB control
- Configure and run timed switching sequences
- Set start-up switch state





USB

Solid State SP2T Switch


USB-1SP2T-34

Mini-Circuits

ORDERING INFORMATION

Please contact Mini-Circuits' Test Solutions department for price and availability: testsolutions@minicircuits.com

Model	Description
USB-1SP2T-34	USB RF SP2T switch

Included Accessories	Part No.	Description
	USB-CBL-AC-3+	3.3 ft (1.0 m) USB cable: USB type A (Male) to USB type C (Male)

OPTIONAL ACCESSORIES

USB-CBL-AC-3+	3.3 ft (1.0 m) USB Cable: USB type A (Male) to USB type C (Male)
CBL-1.5FT-MMD+	1.5 ft (0.45 m) cable assembly for serial control Daisy Chain with snap fit connectors
USB-AC/DC-5	AC/DC +5V power adaptor with USB connector ^{10, 11}

10. The power adaptor may be used to provide additional power via USB port when connecting several units in daisy chain.

11. Includes power plugs for US, UK, EU, IL, AU & China. Plugs for other countries are also available. If you need a power cord for a country not listed please contact testsolutions@minicircuits.com

NOTES:

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at <https://www.minicircuits.com/terms/viewterm.html>



Solid State USB SPDT Switch

USB-1SP2T-34

Typical Performance Data

TEST CONDITIONS: @Temperature = 0°C, Pin = 8dBm

Frequency (MHz)	Insertion Loss (dB)		VSWR, Active Ports (:1)			VSWR, Internally Terminated Ports (:1)	
	COM-1	COM-2	J1	J2	COM	J1	J2
100	0.72	0.72	1.09	1.09	1.09	1.10	1.10
500	0.87	0.86	1.08	1.08	1.09	1.11	1.11
1000	0.96	0.96	1.06	1.06	1.10	1.14	1.14
1500	1.02	1.02	1.03	1.03	1.08	1.16	1.16
2000	1.08	1.07	1.05	1.05	1.06	1.17	1.17
2500	1.12	1.12	1.10	1.10	1.06	1.15	1.15
3000	1.18	1.18	1.13	1.13	1.07	1.13	1.13
3500	1.22	1.22	1.13	1.13	1.08	1.11	1.11
4000	1.27	1.27	1.12	1.12	1.10	1.11	1.12
4500	1.32	1.33	1.12	1.12	1.14	1.12	1.13
5000	1.38	1.39	1.13	1.14	1.17	1.13	1.13
5500	1.44	1.45	1.13	1.14	1.18	1.12	1.13
6000	1.49	1.50	1.12	1.13	1.15	1.09	1.10
6500	1.53	1.55	1.08	1.10	1.10	1.07	1.07
7000	1.58	1.59	1.05	1.07	1.05	1.06	1.05
7500	1.63	1.65	1.03	1.05	1.03	1.09	1.07
8000	1.69	1.71	1.03	1.04	1.04	1.13	1.10
8500	1.76	1.77	1.08	1.06	1.06	1.17	1.14
9000	1.84	1.85	1.13	1.11	1.09	1.19	1.17
9750	1.97	1.98	1.22	1.19	1.15	1.21	1.19
10500	2.10	2.11	1.26	1.24	1.21	1.19	1.18
11250	2.21	2.24	1.22	1.21	1.23	1.13	1.13
12000	2.34	2.37	1.13	1.15	1.25	1.05	1.07
12750	2.48	2.51	1.05	1.06	1.29	1.07	1.06
13500	2.64	2.66	1.19	1.14	1.33	1.20	1.16
14250	2.76	2.77	1.26	1.20	1.31	1.31	1.24
15000	2.84	2.86	1.22	1.16	1.14	1.34	1.27
15750	2.97	2.99	1.26	1.21	1.06	1.30	1.24
16500	3.09	3.10	1.38	1.34	1.21	1.20	1.16
17250	3.11	3.12	1.37	1.33	1.25	1.12	1.09
18000	3.08	3.10	1.18	1.18	1.12	1.16	1.12
18750	3.16	3.17	1.08	1.12	1.09	1.17	1.12
19500	3.27	3.28	1.15	1.17	1.14	1.10	1.05
20250	3.31	3.32	1.07	1.08	1.06	1.09	1.10
21000	3.36	3.37	1.09	1.13	1.12	1.23	1.26
21500	3.42	3.43	1.17	1.20	1.19	1.30	1.33
22000	3.49	3.50	1.21	1.23	1.23	1.35	1.37
22500	3.53	3.54	1.19	1.20	1.20	1.33	1.33
23000	3.56	3.57	1.15	1.17	1.16	1.25	1.24
23500	3.60	3.61	1.14	1.18	1.15	1.13	1.11
24000	3.64	3.64	1.12	1.18	1.14	1.06	1.03
24500	3.68	3.68	1.09	1.17	1.10	1.12	1.16
25000	3.74	3.74	1.10	1.19	1.02	1.23	1.31
25500	3.79	3.79	1.17	1.25	1.08	1.33	1.42
26000	3.83	3.84	1.23	1.31	1.16	1.37	1.46
26500	3.86	3.86	1.28	1.33	1.19	1.40	1.46
27000	3.91	3.90	1.32	1.30	1.17	1.43	1.43
27500	4.01	3.97	1.31	1.23	1.17	1.43	1.35
28000	4.14	4.09	1.30	1.22	1.24	1.42	1.31
28500	4.28	4.25	1.31	1.30	1.36	1.43	1.34
29000	4.38	4.40	1.32	1.41	1.47	1.45	1.44
29500	4.44	4.48	1.34	1.48	1.54	1.48	1.56
30000	4.45	4.49	1.37	1.51	1.58	1.57	1.70

Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions. **USB-1SP2T-34**
- C. The parts covered by this specification document are subject to Mini-Circuits' standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



Solid State USB SPDT Switch

USB-1SP2T-34

Typical Performance Data

TEST CONDITIONS: @Temperature = 0°C, Pin = 8dBm

Frequency (MHz)	Isolation @ Active states (dB)			Isolation @ Disconnected state (dB)		
	COM-1	COM-2	J1-J2	COM-1	COM-2	J1-J2
100	89.58	87.90	93.63	85.41	82.18	100.66
500	77.32	78.63	85.32	75.10	74.73	94.33
1000	71.41	71.02	77.45	68.72	68.68	88.71
1500	68.05	68.13	74.07	65.25	65.38	84.15
2000	66.05	66.28	71.74	63.49	63.49	82.96
2500	64.86	64.77	70.08	62.41	62.54	80.53
3000	63.78	64.08	69.89	61.74	61.73	80.32
3500	63.21	63.24	69.33	61.31	61.64	77.02
4000	62.53	62.72	69.79	61.24	61.28	76.61
4500	61.98	62.01	70.70	61.10	61.14	76.90
5000	61.31	61.38	66.94	61.10	61.13	78.45
5500	60.87	60.84	65.68	60.78	60.86	77.37
6000	60.59	60.63	65.31	60.72	60.87	78.22
6500	60.85	60.65	65.54	60.70	61.03	76.53
7000	61.34	61.42	65.69	60.75	61.00	75.51
7500	62.63	62.64	65.79	61.10	61.21	74.06
8000	63.84	64.14	66.11	61.06	61.50	73.36
8500	65.23	65.74	66.07	61.39	61.99	73.11
9000	66.19	67.28	66.24	61.56	62.48	73.27
9750	66.95	68.57	65.76	62.35	63.69	73.39
10500	67.46	68.37	65.42	63.34	65.16	73.77
11250	67.79	68.96	64.80	64.64	66.73	74.39
12000	69.47	70.53	64.08	66.77	69.48	75.03
12750	73.78	74.90	63.10	69.80	72.45	74.32
13500	78.29	77.10	62.30	72.22	77.33	74.36
14250	79.05	82.49	61.21	72.40	74.80	70.99
15000	77.18	75.45	60.69	69.73	69.94	70.14
15750	73.10	74.83	59.61	65.65	67.67	72.81
16500	69.11	68.40	58.34	64.57	64.39	70.43
17250	66.44	66.33	57.30	62.23	62.31	68.88
18000	64.04	64.07	56.68	59.98	59.87	68.84
18750	63.06	62.64	56.05	58.48	58.31	67.86
19500	62.68	62.44	55.48	57.09	57.02	67.20
20250	61.69	62.13	55.19	55.96	55.86	67.81
21000	60.07	60.72	54.85	55.37	55.11	67.38
21500	58.99	59.50	54.92	55.00	54.79	67.91
22000	58.63	58.95	54.97	54.48	54.18	68.82
22500	58.72	58.99	54.89	54.01	53.69	68.85
23000	58.85	59.18	54.65	53.57	53.13	67.43
23500	58.63	59.46	54.35	53.12	52.70	66.46
24000	57.95	59.08	54.15	52.63	52.28	66.29
24500	57.41	58.56	53.91	52.19	51.82	65.91
25000	57.34	58.49	53.70	51.84	51.52	65.24
25500	57.46	58.65	53.57	51.60	51.22	64.85
26000	57.54	58.71	53.41	51.50	51.09	64.57
26500	57.45	57.98	53.40	51.54	51.20	64.24
27000	57.10	57.15	53.53	51.84	51.48	64.29
27500	56.62	56.86	53.69	52.12	51.68	64.09
28000	56.56	57.30	54.16	52.63	52.13	64.71
28500	57.28	58.19	54.61	53.32	52.76	64.94
29000	58.49	58.98	54.96	53.87	53.46	65.94
29500	59.94	59.36	55.48	54.40	54.32	67.26
30000	60.19	59.14	55.89	55.13	55.07	68.09

Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions. **USB-1SP2T-34**
- C. The parts covered by this specification document are subject to Mini-Circuits' standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



Solid State USB SPDT Switch

USB-1SP2T-34

Typical Performance Data

TEST CONDITIONS: @Temperature = +25°C, Pin = 8dBm

Frequency (MHz)	Insertion Loss (dB)		VSWR, Active Ports (:1)			VSWR, Internally Terminated Ports (:1)	
	COM-1	COM-2	J1	J2	COM	J1	J2
100	0.76	0.76	1.10	1.10	1.10	1.09	1.09
500	0.92	0.91	1.09	1.09	1.10	1.10	1.10
1000	1.01	1.01	1.07	1.07	1.10	1.14	1.13
1500	1.07	1.07	1.04	1.04	1.09	1.16	1.16
2000	1.14	1.14	1.05	1.05	1.07	1.16	1.16
2500	1.19	1.19	1.10	1.10	1.07	1.15	1.15
3000	1.25	1.25	1.13	1.13	1.08	1.13	1.13
3500	1.29	1.29	1.14	1.14	1.08	1.11	1.11
4000	1.35	1.35	1.14	1.14	1.11	1.11	1.11
4500	1.40	1.41	1.14	1.14	1.13	1.11	1.12
5000	1.45	1.46	1.14	1.15	1.16	1.11	1.12
5500	1.50	1.51	1.14	1.15	1.16	1.11	1.12
6000	1.59	1.60	1.13	1.15	1.14	1.10	1.11
6500	1.61	1.62	1.11	1.13	1.11	1.07	1.08
7000	1.66	1.67	1.07	1.09	1.07	1.05	1.04
7500	1.73	1.74	1.03	1.06	1.05	1.09	1.07
8000	1.79	1.80	1.05	1.05	1.05	1.13	1.10
8500	1.86	1.88	1.08	1.07	1.07	1.15	1.13
9000	1.96	1.97	1.13	1.11	1.09	1.19	1.16
9750	2.12	2.13	1.23	1.20	1.14	1.22	1.20
10500	2.25	2.26	1.26	1.24	1.18	1.19	1.18
11250	2.42	2.44	1.22	1.22	1.21	1.14	1.14
12000	2.56	2.59	1.11	1.13	1.24	1.05	1.07
12750	2.72	2.74	1.03	1.03	1.30	1.06	1.03
13500	2.92	2.93	1.14	1.10	1.33	1.17	1.12
14250	3.01	2.99	1.23	1.17	1.28	1.28	1.22
15000	3.07	3.06	1.23	1.17	1.17	1.32	1.26
15750	3.11	3.11	1.22	1.18	1.04	1.25	1.21
16500	3.21	3.19	1.30	1.27	1.21	1.17	1.14
17250	3.23	3.21	1.32	1.30	1.23	1.11	1.09
18000	3.25	3.24	1.14	1.13	1.12	1.14	1.12
18750	3.29	3.29	1.09	1.13	1.14	1.12	1.09
19500	3.37	3.36	1.10	1.13	1.16	1.10	1.06
20250	3.38	3.36	1.04	1.05	1.05	1.10	1.09
21000	3.43	3.41	1.08	1.11	1.13	1.19	1.22
21500	3.52	3.51	1.15	1.18	1.22	1.26	1.29
22000	3.48	3.47	1.18	1.20	1.24	1.30	1.33
22500	3.62	3.61	1.16	1.18	1.22	1.29	1.30
23000	3.62	3.60	1.11	1.13	1.16	1.21	1.21
23500	3.65	3.63	1.08	1.12	1.12	1.13	1.09
24000	3.72	3.71	1.06	1.13	1.11	1.09	1.04
24500	3.76	3.75	1.05	1.14	1.05	1.12	1.13
25000	3.82	3.81	1.10	1.20	1.03	1.20	1.27
25500	3.90	3.90	1.18	1.28	1.10	1.31	1.41
26000	3.91	3.91	1.26	1.35	1.17	1.39	1.49
26500	3.93	3.92	1.28	1.34	1.19	1.40	1.48
27000	4.06	4.03	1.29	1.28	1.16	1.40	1.41
27500	4.12	4.07	1.30	1.21	1.16	1.41	1.33
28000	4.23	4.18	1.30	1.22	1.20	1.41	1.29
28500	4.40	4.37	1.31	1.31	1.34	1.43	1.34
29000	4.54	4.55	1.31	1.41	1.49	1.45	1.43
29500	4.66	4.69	1.32	1.48	1.54	1.45	1.53
30000	4.77	4.80	1.39	1.54	1.56	1.54	1.69

Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions. **USB-1SP2T-34**
- C. The parts covered by this specification document are subject to Mini-Circuits' standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



Solid State USB SPDT Switch

USB-1SP2T-34

Typical Performance Data

TEST CONDITIONS: @Temperature = +25°C, Pin = 8dBm

Frequency (MHz)	Isolation @ Active states (dB)			Isolation @ Disconnected state (dB)		
	COM-1	COM-2	J1-J2	COM-1	COM-2	J1-J2
100	86.58	86.29	91.97	82.82	83.62	106.71
500	77.44	77.76	84.19	75.28	75.09	99.01
1000	70.96	71.13	76.19	68.31	68.15	86.90
1500	67.37	67.68	72.79	64.62	64.79	83.41
2000	65.52	65.80	71.12	62.62	62.84	82.13
2500	64.20	64.62	69.77	61.64	61.55	81.01
3000	63.27	63.58	69.34	61.03	60.81	79.19
3500	62.61	63.01	69.44	60.63	60.45	78.16
4000	62.11	62.20	68.58	60.31	60.38	76.76
4500	61.52	61.58	68.14	60.19	60.25	77.43
5000	60.97	61.03	66.57	59.92	60.15	77.87
5500	60.47	60.51	65.68	59.89	60.12	79.67
6000	60.16	60.17	65.37	59.83	60.00	78.86
6500	60.46	60.50	65.52	59.76	59.97	78.44
7000	60.99	61.00	65.86	59.97	60.24	76.62
7500	61.95	62.07	66.23	60.09	60.34	75.92
8000	63.12	63.47	66.26	60.25	60.41	74.80
8500	64.06	64.80	66.69	60.32	60.97	74.02
9000	64.71	65.63	66.66	60.71	61.53	74.33
9750	65.50	67.08	66.70	61.22	62.34	74.60
10500	66.04	67.29	65.97	62.04	63.54	75.14
11250	66.44	67.78	65.50	63.12	64.99	75.53
12000	67.67	69.14	64.77	64.93	66.93	75.67
12750	70.72	72.20	63.66	67.34	69.15	75.89
13500	72.46	74.90	63.05	70.20	72.52	75.52
14250	72.52	82.48	61.96	74.20	71.67	72.56
15000	77.31	80.09	61.09	74.69	70.52	72.09
15750	77.42	76.58	60.04	69.23	70.91	73.83
16500	71.61	70.97	58.70	67.11	66.45	71.44
17250	68.47	67.51	57.81	64.45	63.50	69.63
18000	65.66	64.83	57.28	61.80	61.30	69.46
18750	63.77	63.32	56.51	59.68	59.38	68.35
19500	63.16	63.30	55.99	58.17	58.17	68.05
20250	62.38	63.02	55.67	56.89	56.76	68.47
21000	60.70	61.53	55.30	56.32	55.97	67.93
21500	59.58	60.15	55.48	55.81	55.44	68.84
22000	59.03	59.52	55.42	55.19	54.85	69.40
22500	59.15	59.64	55.32	54.66	54.32	68.94
23000	59.24	59.88	55.03	54.17	53.75	68.01
23500	59.06	59.83	54.69	53.71	53.27	67.10
24000	58.26	59.36	54.61	53.28	52.86	66.51
24500	57.88	59.07	54.39	52.82	52.38	65.99
25000	57.62	58.92	54.22	52.50	52.07	65.36
25500	57.83	59.19	54.05	52.20	51.82	65.26
26000	58.08	59.23	53.93	52.24	51.75	64.97
26500	57.91	58.31	54.06	52.17	51.71	64.51
27000	57.25	57.92	54.38	52.43	51.99	64.62
27500	56.92	57.61	54.16	52.82	52.33	65.19
28000	57.09	57.77	54.69	53.21	52.72	64.26
28500	57.96	59.03	55.23	53.97	53.35	65.33
29000	59.07	59.50	55.77	54.45	54.12	67.09
29500	60.19	59.53	56.54	55.31	54.99	67.51
30000	60.85	59.35	56.91	55.93	55.50	68.63

Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions. **USB-1SP2T-34**
- C. The parts covered by this specification document are subject to Mini-Circuits' standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



Solid State USB SPDT Switch

USB-1SP2T-34

Typical Performance Data

TEST CONDITIONS: @Temperature = +50°C, Pin = 8dBm

Frequency (MHz)	Insertion Loss (dB)		VSWR, Active Ports (:1)			VSWR, Internally Terminated Ports (:1)	
	COM-1	COM-2	J1	J2	COM	J1	J2
	100	0.78	0.79	1.10	1.11	1.10	1.09
500	0.94	0.95	1.09	1.10	1.11	1.10	1.10
1000	1.03	1.05	1.07	1.07	1.11	1.14	1.13
1500	1.10	1.12	1.04	1.04	1.09	1.16	1.15
2000	1.16	1.19	1.06	1.06	1.07	1.16	1.16
2500	1.21	1.24	1.11	1.11	1.06	1.15	1.14
3000	1.27	1.30	1.14	1.14	1.07	1.12	1.12
3500	1.32	1.35	1.14	1.14	1.08	1.10	1.11
4000	1.37	1.40	1.13	1.14	1.11	1.10	1.10
4500	1.42	1.46	1.13	1.13	1.15	1.11	1.11
5000	1.49	1.53	1.13	1.14	1.18	1.11	1.12
5500	1.55	1.59	1.14	1.15	1.19	1.11	1.12
6000	1.60	1.65	1.13	1.14	1.16	1.09	1.10
6500	1.66	1.71	1.10	1.12	1.11	1.06	1.07
7000	1.71	1.76	1.06	1.09	1.06	1.05	1.04
7500	1.77	1.83	1.03	1.06	1.04	1.08	1.06
8000	1.84	1.90	1.03	1.04	1.04	1.13	1.10
8500	1.93	2.00	1.09	1.07	1.06	1.17	1.14
9000	2.02	2.10	1.14	1.12	1.08	1.20	1.17
9750	2.19	2.27	1.22	1.20	1.13	1.21	1.19
10500	2.35	2.45	1.26	1.24	1.18	1.19	1.19
11250	2.51	2.62	1.22	1.23	1.23	1.15	1.16
12000	2.67	2.77	1.14	1.16	1.28	1.07	1.09
12750	2.80	2.88	1.01	1.05	1.31	1.03	1.01
13500	2.92	2.95	1.12	1.06	1.31	1.15	1.10
14250	2.99	3.00	1.21	1.14	1.27	1.26	1.19
15000	3.02	3.02	1.20	1.14	1.13	1.30	1.23
15750	3.08	3.07	1.24	1.20	1.05	1.26	1.21
16500	3.14	3.12	1.33	1.30	1.18	1.17	1.13
17250	3.13	3.12	1.30	1.28	1.22	1.10	1.08
18000	3.11	3.12	1.13	1.13	1.12	1.14	1.11
18750	3.18	3.19	1.10	1.12	1.11	1.15	1.11
19500	3.28	3.29	1.16	1.17	1.13	1.08	1.04
20250	3.33	3.34	1.08	1.10	1.05	1.07	1.09
21000	3.40	3.43	1.09	1.12	1.11	1.22	1.23
21500	3.47	3.50	1.15	1.17	1.17	1.28	1.30
22000	3.54	3.57	1.18	1.18	1.19	1.32	1.32
22500	3.60	3.63	1.16	1.16	1.16	1.29	1.29
23000	3.65	3.68	1.13	1.15	1.13	1.20	1.19
23500	3.70	3.75	1.13	1.17	1.14	1.09	1.07
24000	3.76	3.80	1.11	1.16	1.12	1.07	1.06
24500	3.83	3.88	1.08	1.16	1.08	1.16	1.19
25000	3.91	3.96	1.11	1.18	1.00	1.26	1.31
25500	3.98	4.04	1.17	1.25	1.10	1.32	1.40
26000	4.03	4.10	1.20	1.28	1.16	1.33	1.42
26500	4.07	4.14	1.23	1.29	1.17	1.34	1.40
27000	4.16	4.21	1.27	1.27	1.15	1.36	1.37
27500	4.29	4.32	1.30	1.23	1.16	1.39	1.33
28000	4.46	4.48	1.32	1.23	1.24	1.41	1.30
28500	4.62	4.66	1.31	1.29	1.35	1.43	1.33
29000	4.73	4.81	1.30	1.37	1.43	1.42	1.40
29500	4.79	4.90	1.29	1.42	1.48	1.43	1.49
30000	4.81	4.92	1.32	1.45	1.50	1.47	1.59

Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions. **USB-1SP2T-34**
- C. The parts covered by this specification document are subject to Mini-Circuits' standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



Solid State USB SPDT Switch

USB-1SP2T-34

Typical Performance Data

TEST CONDITIONS: @Temperature = +50°C, Pin = 8dBm

Frequency (MHz)	Isolation @ Active states (dB)			Isolation @ Disconnected state (dB)		
	COM-1	COM-2	J1-J2	COM-1	COM-2	J1-J2
100	85.30	86.12	91.99	81.99	82.68	106.44
500	76.84	77.82	84.59	74.28	75.55	96.71
1000	70.71	70.63	76.36	67.77	67.56	86.50
1500	67.39	67.19	72.33	64.18	63.87	83.68
2000	65.14	65.02	70.35	62.24	62.14	81.01
2500	64.06	63.90	68.72	60.98	60.91	80.34
3000	62.91	62.83	68.05	60.36	60.20	78.09
3500	62.37	62.36	67.49	59.84	59.81	77.97
4000	61.64	61.63	67.08	59.58	59.58	77.24
4500	61.17	61.19	67.19	59.42	59.28	77.10
5000	60.72	60.61	66.68	59.14	59.10	79.11
5500	60.14	60.05	66.42	59.15	59.12	79.41
6000	59.92	59.88	65.79	58.98	59.11	80.45
6500	59.97	59.87	65.85	59.07	59.12	80.41
7000	60.55	60.45	65.82	59.06	59.17	78.67
7500	61.31	61.36	65.92	59.14	59.33	78.20
8000	62.14	62.53	66.32	59.30	59.48	76.26
8500	63.06	63.45	66.52	59.48	59.77	76.36
9000	63.62	64.45	66.97	59.75	60.28	76.17
9750	64.40	65.50	67.09	60.18	61.04	75.90
10500	64.84	66.27	66.51	60.95	62.17	76.02
11250	65.54	66.24	65.95	61.95	63.12	76.95
12000	66.31	67.06	65.20	63.10	64.47	77.66
12750	69.22	69.84	64.03	65.04	66.29	77.02
13500	72.86	72.13	63.23	67.24	68.14	76.34
14250	73.55	76.82	62.48	70.53	69.44	74.44
15000	74.26	80.17	60.89	72.86	70.66	73.40
15750	75.93	77.87	60.32	70.19	73.48	73.94
16500	72.65	73.21	58.94	68.93	68.40	71.69
17250	69.69	69.49	58.08	65.09	65.32	70.40
18000	66.87	66.61	57.52	62.61	62.88	70.07
18750	64.69	64.77	56.81	60.72	60.70	69.04
19500	63.84	64.23	56.34	59.08	59.24	68.85
20250	63.12	63.88	55.92	57.77	57.80	69.03
21000	61.50	62.37	55.59	57.04	56.94	68.58
21500	60.25	60.88	55.72	56.45	56.27	69.37
22000	59.55	60.22	55.72	55.84	55.49	69.97
22500	59.64	60.28	55.61	55.23	54.92	69.13
23000	59.68	60.53	55.40	54.66	54.35	68.17
23500	59.53	60.54	55.05	54.12	53.69	67.20
24000	58.80	59.98	54.87	53.65	53.20	66.81
24500	58.17	59.62	54.68	53.15	52.80	66.57
25000	57.99	59.55	54.57	52.88	52.40	65.84
25500	58.26	59.75	54.37	52.58	52.14	65.37
26000	58.49	59.74	54.35	52.43	52.04	65.04
26500	58.27	59.01	54.37	52.57	52.17	64.73
27000	57.56	58.07	54.47	52.86	52.34	64.34
27500	57.29	57.96	55.05	53.11	52.74	65.16
28000	57.48	58.41	55.33	54.00	53.20	65.42
28500	58.36	59.07	55.84	54.55	54.08	65.59
29000	59.62	60.13	56.77	55.24	54.87	66.71
29500	60.31	60.18	57.22	55.81	55.45	68.43
30000	60.69	58.97	57.77	56.61	56.15	69.07

Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions. **USB-1SP2T-34**
- C. The parts covered by this specification document are subject to Mini-Circuits' standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp




Solid State USB SPDT Switch

USB-1SP2T-34


Typical Performance Curves

TEST CONDITIONS: @Temperature = 0°C, Pin = 8 dBm


Insertion Loss




Isolation @ Active states




Isolation @ Disconnected state



VSWR, Active Ports



VSWR, Terminated Ports



Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits' standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp




Solid State USB SPDT Switch

USB-1SP2T-34


Typical Performance Curves

TEST CONDITIONS: @Temperature = +25°C, Pin = 8 dBm


Insertion Loss




Isolation @ Active states




Isolation @ Disconnected state



VSWR, Active Ports



VSWR, Terminated Ports



Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits' standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp




Solid State USB SPDT Switch

USB-1SP2T-34


Typical Performance Curves

TEST CONDITIONS: @Temperature = +50°C, Pin = 8 dBm


Insertion Loss




Isolation @ Active states




Isolation @ Disconnected state



VSWR, Active Ports



VSWR, Terminated Ports




Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits' standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



Outline Dimensions

NR3244



CASE#	A	B	C	D	E	F	G	H	J	K	WT. GRAMS
NR3244	2.30 (58.42)	2.00 (50.80)	.575 (14.61)	.100 (2.54)	2.250 (57.15)	2.50 (63.50)	2.050 (52.07)	.106 (2.69)	.500 (12.70)	.650 (16.51)	100

Dimensions are in inches (mm). Tolerances: 2PL. +/- .03; 3PL. +/- .015

Notes:

- Case material: Nickel Plated Aluminum.

Mini-Circuits®

INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified



Environmental Specifications **ENV55**

All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-0° to 50° C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-20° to 60° C Ambient Environment	Individual Model Data Sheet
Operating and Storage Humidity	5% to 85% RH (non-condensing)	Ambient
Bench Handling Test	Bench Top Tip 45° & Drop	MIL-PRF-28800F
Transit Drop Test	Free Fall Drop, 20 cm (7.9 inches)	MIL-PRF-28800F Class 3